

Catalog Correction Notice

December 3, 2012

No. 2012308E

Catalog

The mistake of the print and the description is found in the catalog that our company issued. It apologizes.

[Name of catalog]

“ CJ2 family Catalog “ < Publication in Apr, 2012 > < Catalog number P059-E1-09 >
“ Sysmac Integrated Catalog “ < Publication in Aug, 2012 > < Catalog number P072-E1-05 >

[Page of publishing]

Page 44 “ Combination XW2 with PLC ” CJ1 family Catalog
Page 152 “ Applicable Connector-terminal block conversion unit “ Sysmac Integrated Catalog

[Correction method]

We'll revise them on the next version.

[Content of correction]

It's not correct about the connecting cable described in Table.

We revise the recommendable model of the connecting cable for the units below.

- 1) XW2F-40G7-IN32 connected with CJ1W-ID231 and CJ1W-ID261
- 2) XW2F-40G7-OUT32 connected with CJ1W-OD231 and CJ1W-OD261

Before	After																										
Recommendable model of connecting cable 1) XW2Z-□□□B 2) XW2Z-□□□B	Recommendable model of connecting cable 1) XW2Z-□□□B-A 2) XW2Z-□□□B-B <table border="1"><thead><tr><th>Model</th><th>Cable Length(m)</th></tr></thead><tbody><tr><td colspan="2" style="text-align:center">XW2Z-□□□B-A</td></tr><tr><td>XW2Z-100B-A</td><td>1</td></tr><tr><td>XW2Z-150B-A</td><td>1.5</td></tr><tr><td>XW2Z-200B-A</td><td>2</td></tr><tr><td>XW2Z-300B-A</td><td>3</td></tr><tr><td>XW2Z-500B-A</td><td>5</td></tr><tr><td colspan="2" style="text-align:center">XW2Z-□□□B-B</td></tr><tr><td>XW2Z-100B-B</td><td>1</td></tr><tr><td>XW2Z-150B-B</td><td>1.5</td></tr><tr><td>XW2Z-200B-B</td><td>2</td></tr><tr><td>XW2Z-300B-B</td><td>3</td></tr><tr><td>XW2Z-500B-B</td><td>5</td></tr></tbody></table>	Model	Cable Length(m)	XW2Z-□□□B-A		XW2Z-100B-A	1	XW2Z-150B-A	1.5	XW2Z-200B-A	2	XW2Z-300B-A	3	XW2Z-500B-A	5	XW2Z-□□□B-B		XW2Z-100B-B	1	XW2Z-150B-B	1.5	XW2Z-200B-B	2	XW2Z-300B-B	3	XW2Z-500B-B	5
Model	Cable Length(m)																										
XW2Z-□□□B-A																											
XW2Z-100B-A	1																										
XW2Z-150B-A	1.5																										
XW2Z-200B-A	2																										
XW2Z-300B-A	3																										
XW2Z-500B-A	5																										
XW2Z-□□□B-B																											
XW2Z-100B-B	1																										
XW2Z-150B-B	1.5																										
XW2Z-200B-B	2																										
XW2Z-300B-B	3																										
XW2Z-500B-B	5																										

As of December, 2012

In the interest of product improvement, specifications are subject to change without notice.

Reference; Revised content of “Sysmac Integrated Catalog” (P072-E1-05)

Product name	Applicable Units			Branch	Connector Cable	Common Terminal	Terminal Type	XW2 Model	Standards
	I/O Unit Model	Specifications I/O Points	+/-						
Connector-terminal block conversion unit	CJ1W-ID231	IN 32 Points	NPN /PNP	No	XW2Z-□□□B (1 unit)	No	Screw	XW2D-40G6	UC
				2	XW2Z-□□□D (1 unit)	Yes	Screwless (Cramp)	XW2F-40G7	
	CJ1W-ID232/233	IN 32 Points	NPN /PNP	No	XW2Z-□□□K (1 unit)	No	Screw	XW2D-40G6	
				2	XW2Z-□□□N (1 unit)	Yes	Screwless (Cramp)	XW2F-40G7-IN32 *	
	CJ1W-OD231	OUT 32 Points	NPN	No	XW2Z-□□□B (1 unit)	No	Screw	XW2D-40G6	
				2	XW2Z-□□□L (1 unit)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32	
	CJ1W-OD232	OUT 32 Points	PNP	No	XW2Z-□□□K (1 unit)	No	Screw	XW2D-40G6	
				2	XW2Z-□□□N (1 unit)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32	
	CJ1W-OD233/234	OUT 32 Points	NPN	No	XW2Z-□□□K (1 unit)	No	Screw	XW2D-40G6	
				2	XW2Z-□□□N (1 unit)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32	
	CJ1W-ID261	IN 64 Points	NPN /PNP	No	XW2Z-□□□B (2 units)	No	Screw	XW2D-40G6 (2 Units needed)	
				2	XW2Z-□□□D (2 units)	Yes	Screwless (Cramp)	XW2F-40G7 (2 Units needed)	
	CJ1W-ID262	IN 64 Points	NPN /PNP	No	XW2Z-□□□K (2 units)	No	Screw	XW2D-40G6 (2 Units needed)	
				2	XW2Z-□□□N (2 units)	Yes	Screwless (Cramp)	XW2F-40G7-IN32 (2 Units needed) *	
	CJ1W-OD261	OUT 64 Points	NPN	No	XW2Z-□□□B (2 units)	No	Screw	XW2D-40G6 (2 Units needed)	
				2	XW2Z-□□□L (2 units)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32 (2 Units needed)	
	CJ1W-OD262	OUT 64 Points	PNP	No	XW2Z-□□□K (2 units)	No	Screw	XW2D-40G6 (2 Units needed)	
				2	XW2Z-□□□N (2 units)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32 (2 Units needed)	
	CJ1W-OD263	OUT 64 Points	NPN	No	XW2Z-□□□K (2 units)	No	Screw	XW2D-40G6 (2 Units needed)	
				2	XW2Z-□□□N (2 units)	Yes	Screwless (Cramp)	XW2F-40G7-OUT32 (2 Units needed)	

* For PNP inputs, reverse the polarity of the external power supply connections to the power supply terminals on the Connector-Terminal Block Conversion Unit.