CSM_A3S_DS_E_8_5

Pushbutton Switch Series with Square 40-mm Body

- Combines miniature design with distinct but soft sense of operation.
- Easy panel mounting from the front and simple lamp replacement without tools.



Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 17.

List of Models

Lighted Pushbutton Switches

A	ppearance	Model
Rectangular	A3SJ	
Square		A3SA


■ Specifications: Refer to page 11.

■ Accessories: Refer to pages 9 to 10.

■ Dimensions: Refer to page 13.

Model Number Structure

Model Number Legend The model numbers used to order sets are illustrated below. One set comprises the Operation Unit, Lamp, and Socket Unit. For more information, refer to Ordering Information (pages 3 to 4). Some forms may not be available for order depending on the combination of functions and specifications described below. Contact your OMRON sales representative for more detailed information.



Symbol

(1) Shape of **Operation Unit**

Sym- bol	Shape
J	Rectan- gular
Α	Square

Standard Load

Symbol	Operation		
Α	Momentary	SPDT	
В	Alternate	SEDI	
С	Momentary	DPDT	
D	Alternate	וטוטו	

Microload

	Symbol	Operati	on
E F		Momentary	SPDT
		Alternate	SEDI
	G	Momentary	DPDT
Н		Alternate	וטרטו

- Standard Load 250 VAC, 2 A 125 VDC, 0.4 A
- Microload 125 VAC, 0.1 A 30 VDC, 0.1 A

Minimum applicable load 5 VDC, 1 mA

- Momentary operation ...Self-resetting
- Alternate operation ...Self-holding

(3) Screen Pattern Illumination-only models

Screen pattern

	Single screen
1	
	Vertical 2-split screen
3	
	(rectangular models only)

- Models with colored illumination can be ordered individually. Refer to page 5 for details.
- Colored Illumination



The built-in LED is colored.

Number of Built-in LEDs


Model	odel Screen pattern	
,	Single screen 2	
A3SJ	Vertical 2-split screen	2
A3SA	Single screen	1

(4) Lighting Method - (5) Operation Unit Color **LED-lighted Models** For LED

Symbol	Rated voltage
05E	5 VDC
12E	12 VDC
24E	24 VDC

Symbol	Color
R	Red
Υ	Yellow
G	Green
W	White *

^{*} The color cap is transparent.



Ordering as a SetThe model numbers used to order sets of Units are given in the following tables. One set comprises the Operation Unit, Lamp, and Socket Unit. Not all combinations are possible. Ask your OMRON representative

Standard Loads



Single screen 1

Vertical 2-split screen

2

Single screen

Contact type		Standard load (250 VAC, 2 A; 125 VDC 0.4 A)		Operation Unit	
Output	Lighting	Operation	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Operation Unit color symbol
		5 VDC	A3SJ-90A1-05E□	A3SJ-90B1-05E□	Enter the desired color
SPDT	LED	12 VDC	A3SJ-90A1-12E□	A3SJ-90B1-12E□	symbol for the Pushbutton
		24 VDC	A3SJ-90A1-24E□	A3SJ-90B1-24E□	in □. R (Red)
		5 VDC	A3SJ-90C1-05E□	A3SJ-90D1-05E□	Y (Yellow)
DPDT	LED	12 VDC	A3SJ-90C1-12E□	A3SJ-90D1-12E□	G (Green)
		24 VDC	A3SJ-90C1-24E□	A3SJ-90D1-24E□	W (White)

Vertical 2-split screen

		Contact type	Standard load (250 VA	Operation Unit	
Output	Lighting	Operation	Momentary operation (Self-resetting)	Alternate operation (Self-holding)	color symbol
SPDT	LED	24 VDC	A3SJ-90A3-24E□□	A3SJ-90B3-24E□□	Enter the desired color symbol for the Pushbutton in □□.
DPDT	LED	24 VDC	A3SJ-90C3-24E□□	A3SJ-90D3-24E□□	Y (Yellow) G (Green) W (White)

Microloads

Single screen

Output		ontact type Operation phting	Microload (125 VAC, 0.1 A; 30 VDC 0.1 A) Momentary operation (Self-resetting)	Operation Unit color symbol
SPDT	LED	12 VDC	A3SJ-90E1-12EY	Enter the desired color symbol
		24 VDC	A3SJ-90E1-24E□	for the Pushbutton
DPDT	LED	5 VDC	A3SJ-90G1-05EW	in □. R (Red) Y (Yellow)
וטוטו		24 VDC	A3SJ-90G1-24E□	G (Green) W (White)

Vertical 2-split screen

Output		ntact type Operation hting	Microload (125 VAC, 0.1 A; 30 VDC 0.1 A) Momentary operation (Self-resetting)	Operation Unit color symbol
SPDT	LED	24 VDC	A3SJ-90E3-24E	Enter the desired col- or symbol for the Pushbutton
DPDT	LED	24 VDC	A3SJ-90G3-24E□□	in □□. R (Red) Y (Yellow) G (Green) W (White)

Individual models: Refer to pages 6 to 8.

(The Pushbutton, Lamp, and Switch can be ordered separately.)

■ Specifications: Refer to page 11. ■ Dimensions: Refer to page 13.

■ Accessories: Refer to pages 9 to 10.

Ordering as a Set The model numbers used to order sets of Units are given in the following tables. One set comprises the Operation Unit, Lamp, and Socket Unit. Not all combinations are possible. Ask your OMRON representative

Standard Loads



Single screen

		Contact type	Standard load (250 VA	Omeration Unit	
Output	, , ,		Momentary operation (Self-resetting)	Alternate operation (Self-holding)	Operation Unit color symbol
		5 VDC	A3SA-90A1-05E□	A3SA-90B1-05E□	Enter the desired color
SPDT	LED	12 VDC	A3SA-90A1-12E□	A3SA-90B1-12E□	symbol for the Pushbutton
		24 VDC	A3SA-90A1-24E□	A3SA-90B1-24E□	in □. R (Red)
		5 VDC	A3SA-90C1-05E□	A3SA-90D1-05E□	Y (Yellow)
DPDT	LED	12 VDC	A3SA-90C1-12E□	A3SA-90D1-12E□	G (Green)
		24 VDC	A3SA-90C1-24E□	A3SA-90D1-24E□	W (White)

Microloads

Single screen

Output	Lighting	Contact type Operation	Microload (125 VAC, 0.1 A; 30 VDC 0.1 A) Momentary operation (Self-resetting)	Operation Unit color symbol
SPDT	LED	5 VDC 24 VDC	A3SA-90E1-05E A3SA-90E1-24E	Enter the desired color symbol for the Pushbutton in \square .
DPDT	LED	5 VDC 12 VDC 24 VDC	A3SA-90G1-05EY A3SA-90G1-12E□ A3SA-90G1-24E□	R (Red) Y (Yellow) G (Green) W (White)

Individual models: Refer to pages 6 to 8.

(The Pushbutton, Lamp, and Switch can be ordered separately.)


■ Specifications: Refer to page 11. ■ Dimensions: Refer to page 13.

■ Accessories: Refer to pages 9 to 10.

Illumination-only and Colored-illumination LED Models


[Illumination only] describes LED models for which the screen color is the same whether the LED is lit or not. The screen simply becomes brighter when the LED lights.

Example: Red LED



Colored illumination describes LED models for which the screen color is white when the LED is not lit and changes to the color of the LED lamp when the LED is lit.

Example: Red LED




OrderingWith colored-illumination models, order the Display (Operation Unit), Lamp, and Socket Unit as shown in the following table.

Disp	lay (Operation Ur	nit)	LED	Socket Unit
Single screen	Rectangular models A3SJ-5801			
	Square models	A3SA-5801	Select the LED lamps to suit your desired	Select from the Switches on page 8.
2-split screen	Rectangular models only	A3SJ-5921	coloration from the selection on page 8.	

Ordering Individually....... Operation Units, Lamps, and Socket Units can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

Ordering Specify a model number from the following page.



Ordering set combinations: Refer to pages 3 to 4.

■ Specifications: Refer to page 11.
 ■ Dimensions: Refer to page 13.
 ■ Accessories: Refer to pages 9 to 10.

Ordering Individually Operation Units, Lamps, and Socket Units can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

Operation Unit LED-lighted Models

(LED is not built in.)

			Appearance	Rectangular Models (2 LEDs)	Square Models (1 LED)	
	Saraan nattar	_	Diaplay color	(transparent legend plate built in)	(transparent legend	
•	Screen patter	П	Display color		plate built in)	
			White	A3SJ-5801	A3SA-5801	
Single	screen		Red	A3SJ-5802	A3SA-5802	
			Green	A3SJ-5803	A3SA-5803	
			Yellow	A3SJ-5805	A3SA-5805	
	Standard split screen		White/red	A3SJ-5901		
			White/green	A3SJ-5902		
			White/yellow	A3SJ-5904	_	
			Red/green	A3SJ-5905		
			Red/yellow	A3SJ-5907		
			Green/yellow	A3SJ-5909		
0 !!/			Red/white	A3SJ-5911		
2-split screen *	Reverse		Green/white	A3SJ-5912		
3010011	split	ليلليا	Green/red	A3SJ-5915	-	
	screen		Yellow/red	A3SJ-5917		
			Yellow/green	A3SJ-5919		
			White/white	A3SJ-5921		
	One-color		Red/red	A3SJ-5922		
	2-split screen		Green/green	A3SJ-5923	_	
	22.00		Yellow/yellow	A3SJ-5925		

Ordering set combinations: Refer to pages 3 to 4.

■ Specifications: Refer to page 11. ■ Dimensions: Refer to page 13.

■ Accessories: Refer to pages 9 to 10.

Note: The color cap is transparent when the display color is white.

* Two-split screen configurations are given with the OMRON surface of the case downward.

Ordering Individually....... Operation Units, Lamps, and Socket Units can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs.

Lamp

LED Lamp

Operating voltage	5 VDC	12 VDC	24 VDC	
Color	Model (DC only)	Model (DC only)	Model (DC only)	
Red	SLL-05ER	SLL-12ER	SLL-24ER	
Yellow	SLL-05EY	SLL-12EY	SLL-24EY	
Green	SLL-05EG	SLL-12EG	SLL-24EG	
White	SLL-05EW	SLL-12EW	SLL-24EW	

Note: The A3SJ (M2SJ) requires two LEDs for each Switch. The A3SA (M2SA) requires one LED.

Switch (LED models)

Cont	act type	Number of outputs	Appearance Operation	Rectan- gular models	Square models	Selection precautions
		1	Momentary operation	A3SJ-8010	A3SA-7010	Use the Socket Unit in
Stan- dard	Silver	•	Alternate operation	A3SJ-8020	A3SA-7020	combination with the same shape Operation Unit
load	contacts	cts 2	Momentary operation	A3SJ-8030	A3SA-7030	(rectangular or square). Example:
			Alternate operation	A3SJ-8040	A3SA-7040	For the A3SJ-5801 Rectan- gular Operation Unit, select
			Momentary operation	A3SJ-8050	A3SA-7050	the A3SJ-8□□0
Micro-	Gold alloy	•	Alternate operation		A3SA-7060	Socket Unit. • Momentary operation is
load	contacts	2	Momentary operation	A3SJ-8070	A3SA-7070	self-resetting, and alternate operation is self-holding (i.e.,
		2	Alternate operation	A3SJ-8080	A3SA-7080	push-on, push-off).

$\label{eq:Accessories} \textbf{Accessories}, \textbf{Replacements}, \textbf{and Tools}$

Accessories for Rectangular Models

Name	Appearance	Classification	Model	Application precautions
		Short edge Barriers (1 pair)	A3SA-4001	The purpose of a Barrier is to prevent malfunctioning
Barrier		Short intermediate Barriers	A3SA-4002	and to improve design image of the mounting panel. There is one intermediate Barrier and one pair of
Darrier		Long edge Barriers (1 pair)	A3SJ-4003	edge Barriers (2 Barriers). Mount Short Barriers horizontally. Mount Long Barriers vertically.
		Long intermediate Barriers	A3SJ-4004	Would comp barriers vertically.
Switch Guard		-	A3SJ-5050	Cannot be used with Barrier or Seal Cover.
Seal Cover		-	A3SJ-5060	Cannot be used with Barrier or Switch Guard. Cap material: Vinyl chloride
Long Mounting Plate		1 pair	A3SJ-3002	Use when vertically mounting individual (with Barrier) or multiple Switches (in standard mounting style and with Barrier). A Short Mounting Plate is attached to the Switch; replace it with the long one.

Accessories for Square Models

Name	Appearance	Classification	Model	Application precautions
Barrier	44	Short Edge Barriers (1 pair)	A3SA-4001	The purpose of the Barrier is to prevent malfunctioning and to improve design image of the mounting
Darrier		Short Intermediate Barrier	A3SA-4002	panel.
Switch Guard		-	A3SA-5050	Cannot be used with Barrier or Seal Cover.
Seal Cover		-	A3SA-5060	Cannot be used with Barrier or Switch Guard. Cap material: Vinyl chloride

■ Accessory mounting: Refer to page 18.

Accessories, Replacements, and Tools Replacements for Rectangular Models

Name	Appearance	Classification		Model	Application precautions
	67	Wire-wrap terminals		A3SJ-4104	
Socket		PCB terminals		A3SJ-4105	Sockets cannot be used for multiple mounting.
	1 1/11/11	Solder termina	ls	A3SJ-4106	
Dispersion plate		Milk-white	Single screen	A3SJ-5107	-
	2000	Transparent		A3SJ-5600	
		White	Single screen	A3SJ-5601	
		Red		A3SJ-5602	
		Green		A3SJ-5603	Contact your OMRON representative for color
Color cap		Yellow		A3SJ-5605	changes or inscribing.
•	1	Transparent		A3SJ-5630	If LEDs are to be used, use a color cap that matches the LED color.
		Green	2-split screen	A3SJ-5633	
		Yellow		A3SJ-5635	
Legend plate		Transparent Milk-white		A3SJ-4204	A transparent legend plate is mounted on the
Legend plate				A3SJ-4203	Operation Unit.

Replacements for Square Models

Name	Appearance	Classification	Model	Application precautions	
		Wire-wrap terminals	A3SA-4101		
Socket		PCB terminals	A3SA-4102	Sockets cannot be used for multiple mounting.	
		Solder terminals	A3SA-4103		
Dispersion plate		Milk-white	A3SA-5107	-	
-		Transparent	A3SA-5600		
		White	A3SA-5601	Contact your OMRON representative for color	
Color cap		Red	A3SA-5602	changes or inscribing.	
Color Cap		Green	A3SA-5603	If LED colors are to be used, use a color cap that	
		Blue	A3SA-5604	matches the LED color.	
		Yellow	A3SA-5605		
Legend plate		Transparent A3SA-4204		A transparent color cap is mounted to a standard	
Legend plate		Milk-white	A3SA-4203	Display.	

Tools

Name	Appearance	Classification	Model	Application precautions
Extractor		_	A3PJ-5080	Convenient for extracting the Operation Unit.

■ Accessory mounting: Refer to page 18.

Specifications

Approved Standard Ratings UL (File No. E41515), CSA (File No. LR45258)

3 A at 125 VAC Standard Load: 2 A at 250 VAC 0.1 A at 125 VAC Microload: 0.1 A at 30 VDC

Note: Certification has been obtained for the Switch Unit.

For detailed information on individual products that have received

certification, consult your supplier.

Ratings

For Standard Loads

	Non-	induct	Non-inductive load (A)				Inductive load (A)			
Rated voltage	Resistive load		Lamp load		Inductive load		Motor load			
	NC	NO	NC	NO	NC	NO	NC	NO		
125 VAC		3		0.7	2		1.5	1		
250 VAC	2	2		0.5	1.5		1	0.7		
8 VDC	:	3	1		2	2	1	.5		
14 VDC	3	3	1		1.5		1.5			
30 VDC	2		1		1.5		1			
125 VDC	0	0.4		0.05		0.4		0.05		
250 VDC	0	.2	0.	03	0	.2	0.03			

- Note: 1. The above values are for steady-state currents.
 2. Inductive load: Power factor = 0.4; time constant = 7 ms.
 - 3. The lamp load has an inrush current of 10 times the steady-state
 - 4. The motor load has an inrush current of 6 times the steady-state current.

The rated values are for testing conducted under the following conditions.

(1) Ambient temperature: 20±2°C

(2) Ambient humidity: 65% ±5%RH

(3) Operating frequency: 20 times/min

For Microloads

	0.1 A at 30 VDC (resistive load); 0.1 A at 125 VAC (resistive load)
Minimum applicable load	1 mA at 5 VDC

LED Lamp

Туре	Applied voltage	Rated voltage	Rated current	Built-in limiting resistance
	5 VDC±5%	5 VDC	30 mA	39 Ω
DC only	12 VDC±5%	12 VDC	15 mA	270 Ω
	24 VDC±5%	24 VDC	12.5 mA	1300 Ω

Characteristics

The content of the
resistance Microload 50 mΩ max. (initial value) Between terminals of same polarity 1,000 VAC, 50/60 Hz for 1 minute Between terminals of different polarity 2,000 VAC, 50/60 Hz for 1 minute Between current-carrying metal part 2,000 VAC, 50/60 Hz for 1 minute
Between terminals of same polarity Between terminals of different polarity Between current-carrying metal part Between terminals 2,000 VAC, 50/60 Hz for 1 minute
of same polarity Between terminals of different polarity Between current-carrying metal part 1,000 VAC, 50/60 Hz for 1 minute 2,000 VAC, 50/60 Hz for 1 minute 2,000 VAC, 50/60 Hz for 1 minute 2,000 VAC, 50/60 Hz for 1 minute
of different polarity Between current- carrying metal part 2,000 VAC, 50/60 Hz for 1 minute 2,000 VAC, 50/60 Hz for 1 minute
Dielectric carrying metal part 2,000 VAC, 50/60 Hz for 1 minute
•
Between each terminal and non-current-carrying metal part 2,000 VAC, 50/60 Hz for 1 minute
Between lamp terminals 1,000 VAC, 50/60 Hz for 1 minute *2
Vibration resistance Malfunction 10 to 55 Hz, 1.5-mm double amplitude *3
Shock Destruction 500 m/s² max.
resistance Malfunction 200 m/s² max. *3
Life expectancy Mechanical Mechanical Mechanical Mechanical Momentary operation models: 1,000,000 operations min. Alternate operation models: 100,000 operations min. (One operation consists of set and reset operations.)
Electrical 100,000 operations min. (rated load
Weight Approx. 10 g
Inrush NC Standard load: 10 A max.
current NO Standard load: 10 A max.
Ambient operating temperature −10 to 50°C (with no icing or condensation)
Ambient operating humidity 35% to 85% RH
Ambient storage temperature -25 to 65°C (with no icing or condensation)
Degree of protection IP00
Electric shock protection class Class I
PTI (proof tracking index) 175
Pollution degree 3 (IEC 60947-5-1)

^{*1.} With alternate operation models, 60 operations/min max. One operation cycle consists of set and reset operations.
*2. With no LED lamp mounted.

Operating Characteristics

Operating characteristics	Operation	Momentary operation models	Alternate operation models
Operating force	OF max.	3.92 N	4.90 N
Releasing force	RF min.	0.49 N	0.294 N
Total travel	TT	Approx. 3 mm	Approx. 3 mm
Pretravel	PT max.	2.2 mm	2.2 mm
Lock travel alternate	LTA min.	-	0.5 mm


Contact Form


Name	Contact Form
Double-throw contacts	COM NO

^{*3.} Malfunction: 1 ms max.

Nomenclature

Model Structure Operation Unit Structure






Note: Unless specified, a tolerance of ± 0.4 mm applies for all dimensions. Use a mounting panel thickness of 1 to 4 mm.

Terminal Arrangement

Bottom View (All are shown with the OMRON logo facing down.)



Note: The arrangements given above are not indicated on the Socket Unit.

Contact Type

LED Lamp-lighted Models

Type Model	Rectangular Models (A3SJ)	Square Models (A3SA)	
	BOTTOM VIEW TOP VIEW	BOTTOM VIEW TOP VIEW	
SPDT	Terminal arrangement Lighting block	Terminal arrangement Lighting block	
		0 0 0	
	BOTTOM VIEW TOP VIEW	BOTTOM VIEW TOP VIEW	
DPDT	NOT NC2 AANOTEB NOVE NC2 AANOTEB CI C2	NC	
	Terminal arrangement Lighting block	Terminal arrangement Lighting block	

Dimensions (Unit: mm)

Panel Cutout (If using a Switch Guard or Seal Cover, refer to the panel cutout diagrams on page 16.) **Rectangular Models (A3SJ)**

Classification		Mounting design	Panel cutout	Remarks	
_	Individual mounting, horizontal	17.8±0.2	16.2±0.2 j 22.4±0.2	Panel cutout spacing between rows of Units:	
	Multiple mounting, horizontal	17.8±0.2 1 2 n	16.2±0.2	_ > - 3 min.	
Flange mount models	Individual mounting, vertical	Mount to Long Mounting Plate (A3SJ-3002) before use.	22.4±0.2	6 min.	
	Multiple mounting, vertical	Mount to Long Mounting Plate (A3SJ-3002) before use.	22.4±0.2 17.8n-1.6±0.2		
Barrier mount models	Individual mounting, horizontal	19.8	16.2±0.2	Panel cutout spacing between rows of Units:	
	Multiple mounting, horizontal	19.8 1 2 n	16.2±0.2 ± 25.3n+1.6±0.2	1.4	
	Individual mounting, vertical	Mount to Long Mounting Plate (A3SJ-3002) before use.	22.4±0.2 20.7±0.2	6 min	
	Multiple mounting, vertical	Mount to Long Mounting Plate (A3SJ-3002) before use.	22.4±0.2 19.1n+1.6±0.2	Dotted line indicates the position of each mounting Barrier.	

^{*} If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating.

Square Models (A3SA)


Cla	ssification	Mounting design	Panel cutout	Remarks
Flange mount models	Individual mounting	17.8±0.2 17.8±0.2	16.2±0.2	Panel cutout spacing between rows of Units:
	Multiple mounting	17.8±0.2 1 2 3 n	16.2±0.2 17.8n-1.6±0.2	
Barrier mount models	Individual mounting	19.8	16.2±0.2 10.2±0.2	Panel cutout spacing between rows of Units:
	Multiple mounting	19.8 1 2 3 n	16.2±0.2 19.1n+1.6±0.2	Dotted line indicates the position of each mounting Barrier.

 $^{^{\}star}$ If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating.

Dimensions (Unit: mm)

Accessory Mounting Dimensions


Legend Plate Rectangular Models A3SJ-4203/-4204



Square Models A3SA-4203/-4204




Extractor A3PJ-5080






Socket-mounting Dimensions Rectangular Models


Wire-wrap Terminals A3SJ-4104



Solder Terminals A3SJ-4106




PCB Terminals A3SJ-4105



Terminal Hole Dimensions



PCB Cutout (Bottom View)




Dimensions (Unit: mm)


Square Models

Wire-wrap Terminals Solder Terminals PCB Terminals A3SA-4101 A3SA-4103 A3SA-4102 -212 17.6 -15 -8.2 15.7±0.6 0.5-**PCB Cutout Terminal Hole Dimensions** (bottom view) Eight, 1.5-dia. holes The OMRON logo is downward on the Socket Unit.

Switch and Guard Mounting Dimensions



Seal Cover Mounting Dimensions



Note: 1. Recommended panel thickness: 1.0 to 3.3 mm

Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

Safety Precautions

Refer to Safety Precautions for All Pushbutton Switches/Indicators.

Precautions for Correct Use

Mounting

 Always make sure that the power is turned OFF before mounting, removing, or wiring the Switch, or performing maintenance. Electric shock or fire may occur.

Wiring

- For wiring, use a wire size that is appropriate for the applied voltage and the supplied current. Be sure to perform soldering according to the following conditions. Using the Switch with incomplete soldering may result in errors and heat, which may cause fire.
- (1) Manual soldering: Use a soldering iron with a tip temperature of 350°C maximum and complete soldering within 3 seconds.
- (2) Dip soldering: Solder at 350°C for 3 s or less.

Wait for one minute after soldering before exerting any external force on the solder.

- Use non-corrosive liquid rosin as the flux.
- If screw-tightened terminals are used, hold the Socket Unit Set or Socket Unit and install the lead wiring applying a torque of less than 0.98 N·m to the Socket Unit. Applying a torque of more than 0.98 N·m may result in damage. The tightening torque is 0.59 to 0.78 N·m.
- Make sure that the insulating sheath of the wires does not come in contact with the Unit. If wiring is performed with the insulating sheath of the wires coming in contact with the Unit, use wire with a minimum heat resistance of 100°C.
- After wiring the Switch, make sure that there is a suitable isolation distance.

Operating Environment


 Do not use in locations that are subject to dust, oil, or metal fillings, because these may penetrate the interior the Switch and cause malfunction.

Using Microloads

• Using a standard load switch when a microload circuit is opened or closed may cause wear on the contacts. Use the switch within the operating range. (Refer to the diagram below.) Even when using microload models within the operating range shown below, if inrush current occurs when the contacts are opened or closed, it may cause the contact surface to become rough, and so decrease life expectancy. Therefore, insert a contact protection circuit where necessary.

The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% (λ 60) (conforming to JIS C5003).

The equation λ 60 = 0.5 x 10⁻⁶/time indicates that the estimated malfunction rate is less than 1/2,000,000 with a reliability level of 60%.



LED Lamp

 A current-limiting resistor for the LED lamp is built in, so no external resistor is required.

Rated voltage	Built-in limiting resistance
5 VDC	39 Ω
12 VDC	270 Ω
24 VDC	1300 Ω

Operation

 Always mount the Operation Unit before operating the Switch.
 (Using your fingers or tweezers to operate moving parts of the Switch may deform internal parts and cause malfunctions.)

Character Film

• If the character film is to be specially prepared, use heat-resistant film with a maximum thickness of 0.2 mm.



Others


 If the panel is to be finished (e.g., coated), make sure that the panel meets the specified dimensions after the coating.

Application


Replacing LED Lamps and Panel Mounting

Removing the Display

- Grasp the groove on the color cap surface, and pull it firmly toward you to remove the Display.
- An Extractor (A3PJ-5080) is available to conveniently remove the Display.




Mounting and Replacing LED Lamps



Inserting the Display into the Socket Unit


Insert the Operation Unit in the proper direction. With the OMRON logo downward, insert the Operation Unit so that the lamp/LED terminals on the inside surface of the Unit case and the contactors of the Display.

Terminals for LED lamp (built into the case)



Rated Voltage and Color of LED


The LED voltage rating is indicated on the base. Use the LED within $\pm 5\%$ of voltage range.



Mounting to the Switch Panel


Mount the Socket Unit to the panel by inserting it from the front of the panel.

Mount the Socket Unit so that the OMRON logo is downward.



Barrier Mounting

- Place the Edge Barrier on the side of the Socket Unit, and then insert it into the panel.
- Insert the Intermediate Barrier between the Switches after inserting the Socket Units into the panel.



Inscribing Legend Plate Characters Inscribing

A3SJ (M2SJ)

- Inscription depth: 0.5 mm max.
- The legend plate is made of polycarbonate, so apply an alcoholbased paint coating, such as melamine, phthalate, or acrylic resin paint when marking the legend.




Legend plate

• When replacing the legend plate, be careful that the coil spring in the Display does not become removed.


Assembling the Legend Plate (Plunger) A3SA (M2SA)

(LED Lamp)

(1) Assemble the color plate to the plunger, and then assemble the legend plate on top.



(2) Assemble the color cap to the inscribed plunger.



(3) Push in the color in the direction of the arrow to assemble the plunger and the lamp holder.

Lighted Square Pushbutton Switches

A3SA

Perform the assembly so that the wide groove and the hook on the plunger are in the same direction.



Indicator

M2SA

Perform the assembly so that the wide groove and the hook on the plunger are in the same direction.



Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2024.4

In the interest of product improvement, specifications are subject to change without notice.