Proximity Sensor with All-stainless Housing

E2EF

Metal Head for long-distance Detection that Withstands Harsh Environments Where the Workpiece Can Rub against the Sensor

- · Completely stainless-steel housing
- Long-distance detection equivalent to or greater than Proximity Sensors with Resin Heads *1
- More than 20 times *2 the durability of Proximity Sensors with Resin Heads
- · Spatter-resistant Models with fluororesin coating are available.
- · Aluminum chip immunity
- · Pre-wired Smartclick Connector Models are also available.
- *1. The actual sensing distance will vary with the size or material of the object. For details, refer to Engineering Data.
 *2. Test results for stainless-steel brush rotating at 130 rpm.

Be sure to read *Safety Precautions* on page

Note: Models with a fluororesin coating also use vinyl chloride for the cable material and require separate protection.

Ordering Information

Sensors [Refer to Dimensions on page 5.] Standard Models (Completely stainless-steel housing)

Connection method	Appearanc	e	Sensing distance	Output	Operation mode	Model	
	Shielded	M8	2 mm		E2EF-X2D1 2M *2		
Pre-wired Models		M12	3 mm			E2EF-X3D1 2M *1	
(2m)		M18	7 mm			E2EF-X7D1 2M *1	
		M30	12mm	DC 2-Wire	NO	E2EF-X12D1 2M *1	
	Shielded	M8 2mm (polarity)		E2EF-X2D1-M1TGJ 0.3M *2			
Pre-wired Smartclick Connector Models (M12)		M12	3mm			E2EF-X3D1-M1TGJ 0.3M *1	
		M18	7 mm			E2EF-X7D1-M1TGJ 0.3M *1	
		M30	12mm			E2EF-X12D1-M1TGJ 0.3M *1	

*1. Have been discontinued at the end of March 2025.

*2. Orders will be accepted until the end of March 2026.

Spatter-resistant Models (Completely stainless-steel housing with fluororesin coating)

Connection method	Appearanc	е	Sensing distance	Output	Operation mode	Model	
	Shielded M8 2mm		2mm E2EF-0		E2EF-QX2D1 2M *2		
Pre-wired Models (2m)		M12	3mm	DC 2-Wire (polarity)	NO	E2EF-QX3D1 2M *1	
		M18	7 mm			E2EF-QX7D1 2M *1	
		M30	12mm			E2EF-QX12D1 2M *1	
Pre-wired Smartclick Connector Models (M12)	Shielded	M8	2 mm			E2EF-QX2D1-M1TGJ 0.3M *2	
		M12	3mm			E2EF-QX3D1-M1TGJ 0.3M *1	
		M18	7mm			E2EF-QX7D1-M1TGJ 0.3M *1	
		M30	12mm			E2EF-QX12D1-M1TGJ 0.3M *1	

*1. Have been discontinued at the end of March 2025.

*2. Orders will be accepted until the end of March 2026.

Note: Vinyl chloride is used for the cable material, and separate protection is required.

Accessories (Order Separately)

Sensor I/O Connectors

Smart Click Connectors

Cable connec- tion direction	Cable specifications	Cable length	No. of cable conductors	Model	Applicable Proximity Sensor model number	
Straight	Elamo rotardant flovible cable	2m	4	XS5F-D421-D80-F	E2EF-X D1-M1TGJ	
	r lame-relardant, liexible cable	5m	4	XS5F-D421-G80-F	E2EF-QXD1-M1TGJ	





Ratings and Specifications

	Size	M	M8 M12		12	M19		M20		
	Shielded			Shie		Ided		inico		
	Exterior	Completely stainless- steel housing	Fluororesin coating	Completely stainless- steel housing	Fluororesin coating	Completely stainless- steel housing	Fluororesin coating	Completely stainless- steel housing	Fluororesin coating	
		E2EF-X2D1	E2EF-QX2D1	E2EF-X3D1	E2EF-QX3D1	E2EF-X7D1	E2EF-QX7D1	E2EF-X12D1	E2EF-	
Item	Model	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	(-M1TGJ)	
Sensing di	stance	2mm±10%		3mm±10%		7mm±10%		12mm±10%		
Set distance	e	0 to 1.4 mm		0 to 2.1mm		0 to 4.9mm		0 to 8.4mm		
Differential	travel	15% max. of ser	nsing distance							
Sensing ob	oject	Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on page 6.)								
Standard s	ensing object	Iron, $12 \times 12 \times 12$	1 mm	Iron, $12 \times 12 \times$	1 mm	Iron, 30 \times 30 \times	1 mm	Iron, $54 \times 54 \times 10^{-1}$	1 mm	
Response	frequency *	200Hz		80Hz		100Hz		50Hz		
Power sup	ply voltage	10 to 30 VDC, ri	ipple (p-p) : 10%	max.						
Leakage cu	urrent	0.8 mA max.								
Output con	figuration	With polarity								
Control	Switching capacity	3 to 100 mA								
output	Residual voltage	3 V max.(Load o	current : 100 mA	max., Cable leng	th : 2 m)					
Indicators		Operation indica	ator (red LED), S	etting indicator (g	reen LED)					
Operation ((with sensi approaching)	mode ing object ing)	NO(normally op	NO(normally open)							
Protection	circuits	Surge suppress	Surge suppressor, Load short-circuit protection							
Ambient te range	mperature	Operating : –10 to 70°C, Storage : –25 to 70°C (with no icing or condensation)								
Ambient hu	umidity range	Operating/Storage : 35% to 95% (with no condensation)								
Temperatu	re influence	$\pm 20\%$ max. of sensing distance at 23°C in the temperature range of –10 to 70°C.								
Voltage inf	luence	$\pm 1\%$ max. of sensing distance at rated voltage in the rated voltage $\pm 15\%$ range								
Insulation I	resistance	50 M Ω min. (at §	500 VDC) betwe	en current-carryin	g parts and case					
Dielectric s	strength	1,000 VAC, 50/6	60 Hz for 1 minut	te between currer	nt-carrying parts a	and case				
Vibration re	esistance	Destruction : 10	to 55 Hz, 1.5-mi	m double amplitud	de for 2 hours ea	ch in X, Y, and Z	directions			
Shock resistance Destruction : 500 m/s ² 10 times each in X, Y, and Z directions Destruction : 1,000 m/s ² 10 times each in X, Y, and Z directions										
Degree of p	protection	IEC 60529 IP67								
Connection	n method	Unmarked : Pre-wired Models (Standard cable length : 2 m) Models ending with -M1TGJ : Pre-wired Connector Models (Standard cable length : 300 mm)								
Weight	Pre-wired Models (2 m)	Approx. 105 g Approx. 190 g Approx. 215 g Approx. 295 g								
(packed state)	Pre-wired Connector Models	Approx. 65 g Approx. 85 g Approx. 110 g Approx. 190 g								
	Case	Stainless steel (Stainless steel (SUS303) (E2EF-QX⊡D : SUS303, with fluororesin coating)							
	Sensing surface	Stainless steel (Stainless steel (SUS303) (E2EF-QX□D : SUS303, with fluororesin coating)							
	(thickness)	0.2mm		0.4mm		0.4mm		0.5mm		
Materials	Clamping nuts	Stainless steel (SUS303) (E2EF	-QX□D : SUS303	, with fluororesin	coating)				
	Toothed washer	Zinc-plated iron								
	Cable	PVC (flame reta	rdant)							
Accessorie	s	Instruction manual								

* The response frequency of the DC switching section is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

I/O Circuit Diagrams



E2EF **Engineering Data (Reference Value)**





-QX12D1





Residual Output Voltage

E2EF-XD1



Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

<u> WARNING</u>

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Never use this product with an AC power supply. Otherwise, explosion may result.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation. 1. Do not use the Sensor in an environment where inflammable or

- explosive gas is present.
- 2. Do not attempt to disassemble, repair, or modify any Sensors.
- Power Supply Voltage
 Do not use a voltage that exceeds the rated operating voltage
 range. Applying a voltage that is higher than the operating voltage
 range may result in explosion or fire.
- 4. Incorrect Wiring

5. Connection without a Load

If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.

Precautions for Correct Use

Do not use the Sensor under ambient conditions that exceed the ratings.

- 1. Do not use the Sensor in the following locations.
 - (1) Outdoor locations directly subject to sunlight, rain, snow, or water droplets
 - (2) Locations subject to atmospheres with chemical vapors, in particular solvents and acids
 - (3) Locations subject to corrosive gas
- The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Refer to the OMRON website (www.ia.omron.com/) for typical measures.
- Laying the Sensor wiring in the same conduit or duct as highvoltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- 4. Cleaning

Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.

AND Connection of Proximity Sensors (DC 2-wire)

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors (DC 2-wire)

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.



Design

Influence of Surrounding Metal

When the Proximity Sensor is embedded in metal, make sure that the clearances given in the following table are maintained. The values depend on the type of nuts used for mounting. Be sure to use the supplied nuts (SUS303).





					(011	ι. mmn)
	ltem					
Model	Embedding material	I	d	D	m	n
	Iron	0	8	0	8	30
	Aluminum	uminum 10 50		10	8	50
	Iron	0	12	0	12	40
EZEF-(Q)ASD1	Aluminum 10 50 10 8 Iron 0 12 0 12 Aluminum 16 70 16 12 Iron 0 18 0 28	12	70			
	Iron	0	18	0	28	60
	Aluminum	16	80	16	28	80
	Iron	0	30	0	48	100
E2EF-(Q)X12D1	2D1 Aluminum 24 120	24	48	120		

Note: The influence from other non-magnetic surrounding metals is nearly the same as that from aluminum.

Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.

Mutual Interference

When installing two or more Sensors face-to-face or side-by-side, ensure that the minimum distances given in the following table are maintained.

	(Unit	:: mm)	
Model Iten	1 A	В	│ ─ ━ { ^{··} ─┼ <mark>┃</mark> [·] } → · · f ─┼)━
E2EF-(Q)X2D1	35	35	· · · · · · · · · · · · · · · · · · ·
E2EF-(Q)X3D1	40	35	
E2EF-(Q)X7D1	65	60	
E2EF-(Q)X12D1	110	100	
			-

Chips from Cutting Aluminum

Normally, chips from cutting aluminum will not cause a detection signal to be output even if it adheres to or accumulates on the detection surface. In the following cases, however, a detection signal may be output. Remove the cutting chips in these cases.

1. If $d \ge \frac{2}{3}D$ at the center of the detection sur-

face where d is the cutting chip size and D is the

(Unit: mm)

		(/
Model	Dimension	D
E2EF-(Q)X2D1		6
E2EF-(Q)X3D1		10
E2EF-(Q)X7D1		16
E2EF-(Q)X12D1		28

Pressed down

Ч

D

0

Cutting chip

Detection

surface

2.If the cutting chips are pressed down

Mounting

Do not tighten the nut with excessive force. A washer must be used with the nut. Do not use tightening force that exceeds the values in the following table.

Model	Torque
E2EF-(Q)X2D1	9 N∙m
E2EF-(Q)X3D1	30 N∙m
E2EF-(Q)X7D1	70 N∙m
E2EF-(Q)X12D1	180 N·m



Dimensions

E2EF

Sensors Pre-wired Models





*1. The E2EF-QX_D type Clamping nut (optional accessory) is grooved to identify the material (SUS303, with fluororesin coating).

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2012-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_4_6 Cat. No. D114-E1-04 0425 (0912)