


CE

Chip-immune Inductive Proximity Sensor

- Correct operation even with aluminum or iron chips sticking to the Sensor.
 Only the consistent existence of the senser.
- Only the sensing object is detected.
- Pre-wired Smartclick Connector Models also available.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



Ordering Information

Sensors [Refer to *Dimensions* on page 8.] Pre-wired Models

					Output configuration	Model Operation mode		
Appearance		Sensing distance		ce				
						NO	NC	
	M12	2 mm)		DC 2-Wire Models	E2EZ-X2D1-N 2M	E2EZ-X2D2-N 2M	
					DC 3-wire, NPN	E2EZ-X4C1 2M	_	
Shielded	Shielded M18	4 mi	nm		DC 3-wire, PNP	E2EZ-X4B1 2M	_	
				DC 2-wire	E2EZ-X4D1-N 2M	E2EZ-X4D2-N 2M		
M30					DC 3-wire, NPN	E2EZ-X8C1 2M	_	
	M30		8 mm		DC 3-wire, PNP	E2EZ-X8B1 2M	_	
					DC 2-wire	E2EZ-X8D1-N 2M	E2EZ-X8D2-N 2M	

Pre-wired Smartclick Connector Models (M12)

Appearance				Mod	Model		
		Sensing distar	oce Output configuration	Operation	mode		
				NO	NC		
	M12	2 mm	DC 2-wire, (3)-(4) pin arrangement	E2EZ-X2D1-M1TJ 0.3M	_		
	10112	2 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X2D1-M1TGJ 0.3M	_		
Shielded	M18	4	DC 2-wire, (3)-(4) pin arrangement	E2EZ-X4D1-M1TJ 0.3M	—		
	IVI TO	4 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X4D1-M1TGJ 0.3M	_		
	M30	M20	0	DC 2-wire, (3)-(4) pin arrangement	E2EZ-X8D1-M1TJ 0.3M	_	
	WI50	8 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X8D1-M1TGJ 0.3M	—		

Pre-wired Connector Models (M12)

Appearance				Model		
		Sensing distance	Output configuration	Operation m	ode	
				NO	NC	
	M12		DC 2-wire, (3)-(4) pin arrangement	E2EZ-X2D1-M1J 0.3M	_	
	IVI I Z	2 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X2D1-M1GJ 0.3M	_	
Shielded M18			DC 2-wire, (3)-(4) pin arrangement	E2EZ-X4D1-M1J 0.3M	—	
	M18	4 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X4D1-M1GJ 0.3M	—	
-			DC 3-wire, PNP	E2EZ-X4B1-M1J 0.3M	_	
			DC 2-wire, (3)-(4) pin arrangement	E2EZ-X8D1-M1J 0.3M	_	
	M30	8 mm	DC 2-wire, (1)-(4) pin arrangement	E2EZ-X8D1-M1GJ 0.3M	_	
			DC 3-wire, PNP	E2EZ-X8B1-M1J 0.3M	_	

Accessories (Order Separately)

Sensor I/O Connectors (M12, Sockets on One Cable End)

(Models for Pre-wired Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.) [Refer to Dimensions on XS2, XS5.]

Appearance	Cable length	Sensor I/O Connector model number	Applicable Proximity Sensor model number
Straight	2 m	XS2F-D421-DD0	
and the second second	5 m	XS2F-D421-GD0	E2EZ-X□D1-M1J
L-shape	2 m	XS2F-D422-DD0	
	5 m	XS2F-D422-GD0	
Straight	2 m	XS2F-D421-DA0-F	
	5 m	XS2F-D421-GA0-F	E2EZ-X□D1-M1GJ
L-shape	2 m	XS2F-D422-DA0-F	
	5 m	XS2F-D422-GA0-F	
Straight	2 m	XS2F-D421-DC0-F	
a and a second	5 m	XS2F-D421-GC0-F	E2EZ-X□B1-M1J
L-shape	2 m	XS2F-D422-DC0-F	
	5 m	XS2F-D422-GC0-F	
Smartclick	2 m	XS5F-D421-D80-F	E2EZ-X□D1-M1TJ
Connector Straight	5 m	XS5F-D421-G80-F	E2EZ-X□D1-M1TGJ

Mounting Brackets Protective Covers

Sputter Protective Covers

Refer to Y92 / for details.


Ratings and Specifications


Item	Model	E2EZ-X2D E2EZ-X2D E2EZ-X2D -M1GJ	E2EZ-X4D -N E2EZ-X4D -M1J E2EZ-X4D -M1GJ	E2EZ-X8D E2EZ-X8D E2EZ-X8D -M1GJ	E2EZ-X4C1 E2EZ-X4B1 E2EZ-X4B1-M1J	E2EZ-X8C1 E2EZ-X8B1 E2EZ-X8B1-M1J	
Sensing	distance	2 mm ±10%	4 mm ±10%	8 mm ±10%	4 mm ±10%	8 mm ±10%	
Set dista	ance ^{*1}	0 to 1.6 mm	0 to 3.2 mm	0 to 6.4 mm	0 to 3.2 mm	0 to 6.4 mm	
Different	tial travel	20% max. of sensing distant	ce				
Detectab	ble object	Ferrous metal (The sensing	distance decreases with no	n-ferrous metal. Refer to <i>El</i>	ngineering Data on page 4.)		
Standard sensing object		Iron, $12 \times 12 \times 1$ mm	Iron, $30 \times 30 \times 1 \text{ mm}$	Iron, $54 \times 54 \times 1 \text{ mm}$	Iron, $30 \times 30 \times 1 \text{ mm}$	Iron, $54 \times 54 \times 1 \text{ mm}$	
Respons frequence	se cy ^{*2}	200 Hz	100 Hz	30 Hz	12 Hz	8 Hz	
Power supply volt- age (operating voltage range) 12 to 24 VDC (10 to 30 VDC), ripple (p-p): 10% max.			12 to 24 VDC (10 to 30 VD	C), ripple (p-p): 10% max.			
Current consum	urrent onsumption				15 mA max.		
Leakage	e current	0.8 mA max.					
Con- trol	Load cur- rent	3 to 100 mA max.				PNP open-collector output 12 VDC (30 VDC max.) 24 VDC (30 VDC max.)	
output	Residual voltage	3 V max. (Load current: 100	3 V max. (Load current: 100 mA, Cable length: 2 m) 2 V max. (Load cu				
Indicato	rs	D1 Models: Operation indica D2 Models: Operation indica		green)	Detection indicator (red)		
	on mode nsing ob- roaching)						
Protection circuits	on	Load short-circuit protection, Surge suppressor Load short-circuit protection, Reverse polarity prot Surge suppressor					
Ambient tempera	t iture range	Operating/Storage: 0 to 50°C (with no icing or condensation)					
Ambient humidity		Operating/Storage: 35% to 9	95% (with no condensation)				
Tempera influence		±20% max. of sensing dista	nce at 23°C in the temperat	ure range of 0 to 50°C			
Voltage	influence	±2.5% max. of sensing dista	nce at rated voltage in the	ated voltage $\pm 10\%$ range			
Insulation resistant		50 M Ω min. (at 500 VDC) be	etween current-carrying part	s and case			
Dielectri	ic strength	1,000 VAC, 50/60 Hz for 1 n	ninute between current-carr	ying parts and case			
Vibration		Destruction: 10 to 55 Hz, 1.5	5-mm double amplitude for 2	2 hours each in X, Y, and Z	directions		
Shock re	esistance	Destruction: 1,000 m/s ² 10 t	imes each in X, Y, and Z dii	rections			
Degree of protection		IEC 60529 IP67, in-house st	andards: oil-resistant				
Connect method		Pre-wired Models (Standard	cable length: 2 m) and Pre	-wired Connector Models			
Weight (packed	state)	E2EZ-X2D□-N: Approx. 70 g E2EZ-X2D□-M1J: Approx. 40 g E2EZ-X2D□-M1GJ: Approx. 40 g	E2EZ-X4D -N: Approx. 160 g E2EZ-X4D -M1J: Approx. 90 g E2EZ-X4D -M1GJ: Approx. 90 g	E2EZ-X8DN: Approx. 220 g E2EZ-X8DM1J: Approx. 160 g E2EZ-X8DM1GJ: Approx. 160 g	Approx. 170 g	Approx. 270 g	
	Case	Nickel-plated brass					
Materi-	Sensing surface	РВТ			Heat-resistant ABS		
als	Clamp- ing nuts	Zinc-plated iron					
	Toothed washer	Zinc-plated iron					
Accesso	ories	Instruction manual					


*1. Use the Sensor within the range in which the green indicator is ON.
*2. The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

Engineering Data (Reference Value)

Sensing Area









Influence of Sensing Object Size and Material
















Side length of sensing object: d (mm)

Residual Output Voltage


E2EZ-X D -N





I/O Circuit Diagrams

DC 2-Wire Models



DC 3-wire Models

Operation mode	Model	Timing chart	Output circuit
NO	E2EZ-X4C1 E2EZ-X8C1	Sensing object Present Not present Operate	Black +V Black +V U V V V V V V V V V V V V V
	E2EZ-X4B1 E2EZ-X8B1	Load Reset ON OFF	Brown Proximity Black 0 utput 0 utput 0 utput 0 v Note: Pin 2 is not used.

Connections for Sensor I/O Connectors

Pr	oximity Ser	nsor	Sensor I/O Connectors		
Model	Operation mode	Model	Model	Connections	
DC 2-Wire Models (IEC pin wiring)	NO		E2EZ-X□D1-M1GJ	XS2F-D42 	E2EZ XS2F O Brown (+)
DC 2-Wire Models (previous pin wir- ing)		E2EZ-X□D1-M1J	1: Straight 2: L-shape XS2F-D42□-□D0	E2EZ XS2F	
DC 2-Wire Models (IEC pin wiring)		E2EZ-X⊡D1- M1TGJ	. XS5F-D421-□80-F	E2EZ XS5F	
DC 2-Wire Models (previous pin wir- ing)		E2EZ-X□D1-M1TJ	XS5F-D421-L80-F D: 2-m cable G: 5-m cable	D: 2-m cable	E2EZ XS5F
DC 3-Wire Models		E2EZ-X□B1-M1J	XS2F-D42 -CC0 C0 C2: L-shape D: 2-m cable G: 5-m cable	E2EZ XS2F	

Note: Different from Proximity Sensor wire colors.

Refer to Introduction to Sensor I/O Connectors/Sensor Controllers for details.

Safety Precautions

Refer to Warranty and Limitations of Liability.

<u> WARNING</u>

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.




Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.

Design

Influence of Surrounding Metal

When mounting the Sensor within a metal panel, ensure that the clearances given in the following table are maintained. Failure to maintain these distances may cause deterioration in the performance of the Sensor.



Influence of Surrounding Metal (Unit: mm)


	ltem					
Model	Embedded material	I	d	D	m	n
E2EZ-X2	Iron	0	12	0	8	18
	Aluminum	2	25	2	0	36
E2EZ-X4	Iron	0	18	0	16	27
	Aluminum	5	40	5	10	54
E2EZ-X8	Iron	0	30	0	32	45
	Aluminum	10	70	10	52	90

Mutual Interference

When installing Sensors face-to-face or side-by-side, ensure that the minimum distances given in the following table are maintained.

Mutual Interference (Unit: mm)

		•	,
Model	ltem	Α	В
E2EZ-X2		30	20
E2EZ-X4		40	50
E2EZ-X8		60	100



Aluminum and Iron Cuttings

Normally aluminum or iron cuttings will not be detected even if they adhere to or accumulate on the sensing surface.


Detection signals may be output for the following:

- If this occurs, remove the cuttings from the sensing surface.
- 1. Relationship between the Size of the Cutting (d) and the Size of the Sensing Surface (D)

Cuttings of the size $d \ge \frac{2}{3}D$ on the sensing surface *

Cuttings of the size d* (Unit: mm)

Model	Size	D
E2EZ-X2		10 *
E2EZ-X4		16
E2EZ-X8		28




* E2EZ-X2: d $\geq \frac{1}{3}$ D on the sensing surface.

2. Cuttings Pressed against the Sensing Surface



Mounting

Do not tighten the nut with excessive force. A washer must be used with the nut.




- Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)
 - 2. The following torque assume washers are being used.

Tightening Torque	Pa	Part B	
Model	Dimension (mm)	Torque	Torque
E2EZ-X2D			
E2EZ-X4D	70 N·m		
E2EZ-X8D	180 N·m		
E2EZ-X4C1 E2EZ-X4B1	20	15 N∙m	29 N∙m
E2EZ-X8C1 E2EZ-X8B1	22	29 N∙m	39 N∙m


E2EZ

E2EZ-X2D -N





indicator (red)

Pre-wired Connector Models (-M1J/M1GJ)




*1. 4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm², Insulator diameter: 1.3 mm), Standard length: 2 m
 *2. D1 Models: Operation indicator (red), Setting indicator (green), D2 Models: Operation





Model	F (mm)
E2EZ-X2	12.5 dia. +0.5
E2EZ-X4	18.5 dia. +0.5
E2EZ-X8	30.5 dia. +0.5



OMRON

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company