Solid State Contactors for Heaters

G3PE-Three-phase

CSM_G3PE-Three-phase_DS_E_4_11

Compact, Slim-profile SSRs with Heat Sinks. Solid State Contactors for Three-phase Heaters Reduced Installation Work with DIN Track Mounting.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

- RoHS compliant.
- Surge pass protection improved surge dielectric strength for output currents. (OMRON testing)
- Slim design with 3-phase output and built-in heat sinks.
- DIN Track mounting types and screw mounting types are available. All DIN Track mounting types mount to DIN Track (applicable DIN Track: TR35-15Fe (IEC 60715)).
- Conforms to cULus standards and EN standards (TÜV certification).

⚠ **Refer to *Safety Precautions for All G3PE Models*.**

Ordering Information

List of Models

Models with Built-in Heat Sinks

Number of phases	Insulation method	Operation indicator	Rated input voltage	Zero cross function	Type	Applicable load *1	Number of poles	Model
Three-phase	Phototriac coupler	Yes (yellow)	12 to 24 VDC	Yes	DIN track mounting ✻2	15 A, 100 to 240 VAC	3	**G3PE-215B-3N DC12-24** ✻3
							2	**G3PE-215B-2N DC12-24** ✻3
						25 A, 100 to 240 VAC	3	**G3PE-225B-3N DC12-24** ✻3
							2	**G3PE-225B-2N DC12-24** ✻3
						35 A, 100 to 240 VAC	3	**G3PE-235B-3N DC12-24** ✻3
							2	**G3PE-235B-2N DC12-24** ✻3
						45 A, 100 to 240 VAC	3	**G3PE-245B-3N DC12-24** ✻3
							2	**G3PE-245B-2N DC12-24** ✻3
						15 A, 200 to 480 VAC	3	**G3PE-515B-3N DC12-24** ✻3
							2	**G3PE-515B-2N DC12-24** ✻3
						25 A, 200 to 480 VAC	3	**G3PE-525B-3N DC12-24** ✻3
							2	**G3PE-525B-2N DC12-24** ✻3
						35 A, 200 to 480 VAC	3	**G3PE-535B-3N DC12-24** ✻3
							2	**G3PE-535B-2N DC12-24** ✻3
						45 A, 200 to 480 VAC	3	**G3PE-545B-3N DC12-24** ✻3
							2	**G3PE-545B-2N DC12-24** ✻3
					Screw mounting	15 A, 100 to 240 VAC	3	**G3PE-215B-3 DC12-24**
							2	**G3PE-215B-2 DC12-24** ✻3
						25 A, 100 to 240 VAC	3	**G3PE-225B-3 DC12-24**
							2	**G3PE-225B-2 DC12-24**
						35 A, 100 to 240 VAC	3	**G3PE-235B-3 DC12-24**
							2	**G3PE-235B-2 DC12-24**
						45 A, 100 to 240 VAC	3	**G3PE-245B-3 DC12-24**
							2	**G3PE-245B-2 DC12-24**
						15 A, 200 to 480 VAC	3	**G3PE-515B-3 DC12-24**
							2	**G3PE-515B-2 DC12-24** ✻3
						25 A, 200 to 480 VAC	3	**G3PE-525B-3 DC12-24**
							2	**G3PE-525B-2 DC12-24**
						35 A, 200 to 480 VAC	3	**G3PE-535B-3 DC12-24**
							2	**G3PE-535B-2 DC12-24**
						45 A, 200 to 480 VAC	3	**G3PE-545B-3 DC12-24**
							2	**G3PE-545B-2 DC12-24**

✻1. The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.
✻2. The applicable DIN Track is the TR35-15Fe (IEC 60715). For details, refer to the mounting information in the *Safety Precautions for All G3PE Models*.
✻3. DIN Track or Screw mounting.

Models with Externally Attached Heat Sinks

Number of phases	Insulation method	Operation indicator	Rated input voltage	Zero cross function	Type	Applicable load ✻	Number of poles	Model
Three-phase	Phototriac coupler	Yes (yellow)	12 to 24 VDC	Yes	Externally attached heat sinks	15 A, 100 to 240 VAC	3	**G3PE-215B-3H DC12-24**
							2	**G3PE-215B-2H DC12-24**
						25 A, 100 to 240 VAC	3	**G3PE-225B-3H DC12-24**
							2	**G3PE-225B-2H DC12-24**
						35 A, 100 to 240 VAC	3	**G3PE-235B-3H DC12-24**
							2	**G3PE-235B-2H DC12-24**
						45 A, 100 to 240 VAC	3	**G3PE-245B-3H DC12-24**
							2	**G3PE-245B-2H DC12-24**
						15 A, 200 to 480 VAC	3	**G3PE-515B-3H DC12-24**
							2	**G3PE-515B-2H DC12-24**
						25 A, 200 to 480 VAC	3	**G3PE-525B-3H DC12-24**
							2	**G3PE-525B-2H DC12-24**
						35 A, 200 to 480 VAC	3	**G3PE-535B-3H DC12-24**
							2	**G3PE-535B-2H DC12-24**
						45 A, 200 to 480 VAC	3	**G3PE-545B-3H DC12-24**
							2	**G3PE-545B-2H DC12-24**

✻ The rated load current depends on the heat sink or radiator that is mounted. It also depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature*.

Accessories (Order Separately)

Heat Sink

Heat resistance Rth (s-a) (°C/W)	Model
1.67	**Y92B-P50**
1.01	**Y92B-P100**
0.63	**Y92B-P150**
0.43	**Y92B-P200**
0.36	**Y92B-P250**

Specifications

Certification

cULus (File No.E64562) and TÜV (File No.R50124433, EN60947-4-3)

Ratings (at an Ambient Temperature of 25°C)

Operating Circuit (All Models)

ItemModel	Same for all models
Rated operating voltage	12 to 24 VDC
Operating voltage range	9.6 to 30 VDC
Rated input current (impedance)	10 mA max. (24 VDC) ✻1
Must-operate voltage	9.6 VDC max.
Must-release voltage	1 VDC min.
Insulation method	Phototriac
Operation indicator	Yellow LED

✻1. For details, refer to *Input Voltage vs. Input Impedance and Input Voltage vs. Input Current* in *Engineering Data* on page 5.

Main Circuit of Models with Built-in Heat Sinks

Model / Item	G3PE-215B-3(N)	G3PE-215B-2(N)	G3PE-225B-3(N)	G3PE-225B-2(N)	G3PE-235B-3(N)	G3PE-235B-2(N)	G3PE-245B-3(N)	G3PE-245B-2(N)	G3PE-515B-3(N)	G3PE-515B-2(N)	G3PE-525B-3(N)	G3PE-525B-2(N)	G3PE-535B-3(N)	G3PE-535B-2(N)	G3PE-545B-3(N)	G3PE-545B-2(N)
Rated load voltage	100 to 240 VAC								200 to 480 VAC							
Operating voltage range	75 to 264 VAC								180 to 528 VAC							
Rated load current ✻1	15 A (at 40°C)		25 A (at 40°C)		35 A (at 25°C)		45 A (at 25°C)		15 A (at 40°C)		25 A (at 40°C)		35 A (at 25°C)		45 A (at 25°C)	
Minimum load current	0.2 A				0.5 A											
Inrush current resistance (peak value)	150 A (60 Hz, 1 cycle)		220 A (60 Hz, 1 cycle)		440 A (60 Hz, 1 cycle)				220 A (60 Hz, 1 cycle)				440 A (60 Hz, 1 cycle)			
Permissible I^2t (reference value)	$121A^2s$		$260A^2s$		$1,260A^2s$				$260A^2s$				$1,260A^2s$			
Applicable load (resistive load: AC1 class) ✻2	5.1 kW (at 200 VAC)		8.6 kW (at 200 VAC)		12.1 kW (at 200 VAC)		15.5 kW (at 200 VAC)		12.5 kW (at 480 VAC)		20.7 kW (at 480 VAC)		29.0 kW (at 480 VAC)		37.4 kW (at 480 VAC)	

✻1. The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.

✻2. Applicable Load
Use the following formula to calculate the maximum total capacity of a heater load for a three-phase balanced load with delta connections.
Maximum load capacity = Load current × Load voltage × $\sqrt{3}$
Example: 15 A × 200 V × $\sqrt{3}$ = 5,196 W ≅ 5.1 kW
Example: 15 A × 400 V × $\sqrt{3}$ = 10,392 W ≅ 10.3 kW

Main Circuit of Models with Externally Attached Heat Sinks

Model / Item	G3PE-215B-3H	G3PE-215B-2H	G3PE-225B-3HH	G3PE-225B-2H	G3PE-235B-3H	G3PE-235B-2H	G3PE-245B-3H	G3PE-245B-2H	G3PE-515B-3H	G3PE-515B-2H	G3PE-525B-3H	G3PE-525B-2H	G3PE-535B-3H	G3PE-535B-2H	G3PE-545B-3H	G3PE-545B-2H
Rated load voltage	100 to 240 VAC								200 to 480 VAC							
Operating voltage range	75 to 264 VAC								180 to 528 VAC							
Rated load current ✻	15 A (at 40°C)		25 A (at 40°C)		35 A (at 25°C)		45 A (at 25°C)		15 A (at 40°C)		25 A (at 40°C)		35 A (at 25°C)		45 A (at 25°C)	
Minimum load current	0.2 A				0.5 A											
Inrush current resistance (peak value)	150 A (60 Hz, 1 cycle)		220 A (60 Hz, 1 cycle)		440 A (60 Hz, 1 cycle)				220 A (60 Hz, 1 cycle)				440 A (60 Hz, 1 cycle)			
Permissible I^2t (reference value)	$121A^2s$		$260A^2s$		$1,260A^2s$				$260A^2s$				$1,260A^2s$			
Applicable load (resistive load: AC1 class)	Refer to *Engineering Data* on page 5.															

✻ The rated load current depends on the heat sink or radiator that is mounted. It also depends on the ambient temperature.
For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.

Characteristics

Models with Built-in Heat Sinks

Item \ Model	G3PE-215B-3(N)	G3PE-215B-2(N)	G3PE-225B-3(N)	G3PE-225B-2(N)	G3PE-235B-3(N)	G3PE-235B-2(N)	G3PE-245B-3(N)	G3PE-245B-2(N)	G3PE-515B-3(N)	G3PE-515B-2(N)	G3PE-525B-3(N)	G3PE-525B-2(N)	G3PE-535B-3(N)	G3PE-535B-2(N)	G3PE-545B-3(N)	G3PE-545B-2(N)
Operate time	1/2 of load power source cycle + 1 ms max.															
Release time	1/2 of load power source cycle + 1 ms max.															
Output ON voltage drop	1.6 V (RMS) max.								1.8 V (RMS) max.							
Leakage current ✻	10 mA max. (at 200 VAC)								20 mA max. (at 480 VAC)							
Insulation resistance	100 MΩ min. (at 500 VDC)															
Dielectric strength	2,500 VAC, 50/60 Hz for 1 min															
Vibration resistance	• DIN Track mounting: 10 to 55 to 10 Hz, 0.175-mm single amplitude (0.35-mm double amplitude) • Screw mounting: 10 to 55 to 10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude)															
Shock resistance	294 m/s^2 (When mounted to a DIN track in reverse: 98 m/s^2)															
Ambient storage temperature	–30 to 100°C (with no icing or condensation)															
Ambient operating temperature	–30 to 80°C (with no icing or condensation)															
Ambient operating humidity	45% to 85%															
Sealing	IP20															
Weight	Approx. 1.25 kg		Approx. 1.45 kg	Approx. 1.25 kg	Approx. 1.65 kg	Approx. 1.45 kg	Approx. 2.0 kg	Approx. 1.65 kg	Approx. 1.25 kg		Approx. 1.45 kg	Approx. 1.25 kg	Approx. 1.65 kg	Approx. 1.45 kg	Approx. 2.0 kg	Approx. 1.65 kg
MTTFd (Reference value)	1,000 years min.															

✻ The leakage current of phase S will be approximately √3 times larger if the 2-element model is used.

Models with Externally Attached Heat Sinks

Item \ Model	G3PE-215B-3H	G3PE-215B-2H	G3PE-225B-3H	G3PE-225B-2H	G3PE-235B-3H	G3PE-235B-2H	G3PE-245B-3H	G3PE-245B-2H	G3PE-515B-3H	G3PE-515B-2H	G3PE-525B-3H	G3PE-525B-2H	G3PE-535B-3H	G3PE-535B-2H	G3PE-545B-3H	G3PE-545B-2H
Operate time	1/2 of load power source cycle + 1 ms max.															
Release time	1/2 of load power source cycle + 1 ms max.															
Output ON voltage drop	1.6 V (RMS) max.								1.8 V (RMS) max.							
Leakage current ✻	10 mA max. (at 200 VAC)								20 mA max. (at 480 VAC)							
Insulation resistance	100 MΩ min. (at 500 VDC)															
Dielectric strength	2,500 VAC, 50/60 Hz for 1 min															
Vibration resistance	10 to 55 to 10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude)															
Shock resistance	Destruction: 294 m/s^2															
Ambient storage temperature	–30 to 100°C (with no icing or condensation)															
Ambient operating temperature	–30 to 80°C (with no icing or condensation)															
Ambient operating humidity	45% to 85%															
Sealing	IP20															
Weight	Approx. 300 g															
MTTFd (Reference value)	1,000 years min.															

✻ The leakage current of phase S will be approximately √3 times larger if the 2-element model is used.


Heat Sinks

Model	Weight
Y92B-P50	Approx. 450 g
Y92B-P100	Approx. 450 g
Y92B-P150	Approx. 600 g
Y92B-P200	Approx. 850 g
Y92B-P250	Approx. 1,200 g


Engineering Data

Input Voltage vs. Input Impedance and Input Voltage vs. Input Current

G3PE-2□□B-□□




G3PE-5□□B-□□




Load Current vs. Ambient Temperature

Models with Built-in Heat Sinks

G3PE-215B-3(N), G3PE-225B-3(N)
G3PE-215B-2(N), G3PE-225B-2(N)
G3PE-515B-3(N), G3PE-525B-3(N)
G3PE-515B-2(N), G3PE-525B-2(N)




G3PE-235B-3(N), G3PE-245B-3(N)
G3PE-235B-2(N), G3PE-245B-2(N)
G3PE-535B-3(N), G3PE-545B-3(N)
G3PE-535B-2(N), G3PE-545B-2(N)




✻ The dotted lines in the charts are the UL derating curves for the G3PE-235B-3(N), G3PE-245B-3(N), G3PE-235B-2(N), G3PE-245B-2(N), G3PE-535B-3(N), G3PE-545B-3(N), G3PE-535B-2(N), G3PE-545B-2(N).

Models with Externally Attached Heat Sinks

G3PE-215B-3H(-2H)
G3PE-225B-3H(-2H)
G3PE-515B-3H(-2H)
G3PE-525B-3H(-2H)




G3PE-235B-3H(-2H)
G3PE-245B-3H(-2H)
G3PE-535B-3H(-2H)
G3PE-545B-3H(-2H)




Inrush Current Resistance: Non-repetitive

Keep the inrush current to below the inrush current resistance value (i.e., below the broken line) if it occurs repetitively.


G3PE-215B-3(N)(H)
G3PE-215B-2(N)(H)



G3PE-225B-3(N)(H), G3PE-525B-3(N)(H)
G3PE-225B-2(N)(H), G3PE-525B-2(N)(H)
G3PE-515B-3(N)(H),
G3PE-515B-2(N)(H),




G3PE-235B-3(N)(H), G3PE-535B-3(N)(H)
G3PE-235B-2(N)(H), G3PE-535B-2(N)(H)
G3PE-245B-3(N)(H), G3PE-545B-3(N)(H)
G3PE-245B-2(N)(H), G3PE-545B-2(N)(H)




Heat Sink Area vs. Load Current (40°C and 80°C)

G3PE-225B-3H



G3PE-525B-3H



Note: The heat sink area is the combined area of all surfaces of the heat sink that radiate heat.
For the G3PE-525B-3H, when a current of 18 A flows through the SSR at 40°C, the graph shows that a heat sink area of about 2,500 cm^2 would be required. Therefore, if the heat sink is square, one side of an aluminum plate in the heat sink must be 36 cm or longer ($\sqrt{2,500}$ (cm^2)/2 = 36 cm (rounded to a whole number)).

Models with Externally Attached Heat Sinks Heat Resistance Rth (Junction/SSR Back Surface)

Model	Rth (°C/W)
G3PE-215B-3H	1.05
G3PE-225B-3H	0.57
G3PE-235B-3H	0.57
G3PE-245B-3H	0.57

Heat Resistance of Heat Sinks

Model	Rth (°C/W)
Y92B-P50	1.67
Y92B-P100	1.01
Y92B-P150	0.63
Y92B-P200	0.43
Y92B-P250	0.36

Note: If a commercially available heat sink is used, use one that has a heat resistance equal to or lower than a standard OMRON Heat Sink.


Dimensions


Note: All units are in millimeters unless otherwise indicated.


Solid State Relays

Models with DIN Track Mounting

G3PE-215B-3N
G3PE-215B-2N
G3PE-225B-2N
G3PE-515B-3N
G3PE-515B-2N
G3PE-525B-2N








Note: Without terminal cover.


Note: With terminal cover.



DIN Track or screw mounting


Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-215B-3N




G3PE-2□5B-2N



G3PE-515E-3N





G3PE-5□5B-2N




Models with DIN Track Mounting

G3PE-225B-3N
G3PE-235B-2N
G3PE-525B-3N
G3PE-535B-2N








Note: Without terminal cover.


Note: With terminal cover.



DIN Track or screw mounting


Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-225B-3N




G3PE-235B-2N



G3PE-525B-3N



G3PE-535B-2N




Models with DIN Track Mounting


G3PE-235B-3N
G3PE-245B-2N
G3PE-535B-3N
G3PE-545B-2N




DIN Track or screw mounting




Note: Without terminal cover.




Note: With terminal cover.




Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-235B-3N




G3PE-245B-2N



G3PE-535B-3N



G3PE-545B-2N




Models with DIN Track Mounting


G3PE-245B-3N
G3PE-545B-3N




DIN Track or screw mounting




Note: Without terminal cover.




Note: With terminal cover.




Mounting Holes






Terminal Arrangement/Internal Circuit Diagram

G3PE245B-3N



G3PE-545B-3N




Models with Screw Mounting


G3PE-215B-2
G3PE-515B-2




DIN Track or screw mounting




Note: Without terminal cover.




Note: With terminal cover.




Mounting Holes






Terminal Arrangement/Internal Circuit Diagram

G3PE-215B-2




G3PE-515B-2




Models with Screw Mounting


G3PE-215B-3
G3PE-225B-2
G3PE-515B-3
G3PE-525B-2




For screw mounting only




Note: Without terminal cover.




Note: With terminal cover.




Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-215B-3




G3PE-225B-2



G3PE-515B-3



G3PE-525B-2




Models with Screw Mounting


G3PE-225B-3
G3PE-235B-2
G3PE-525B-3
G3PE-535B-2



For screw mounting only





Note: Without terminal cover.



Note: With terminal cover.


Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-225B-3




G3PE-235B-2



G3PE-525B-3



G3PE-535B-2




Models with Screw Mounting


G3PE-235B-3
G3PE-245B-2
G3PE-535B-3
G3PE-545B-2



For screw mounting only





Note: Without terminal cover.



Note: With terminal cover.


Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-235B-3




G3PE-245B-2



G3PE-535B-3



G3PE-545B-2




Models with Screw Mounting


G3PE-245B-3
G3PE-545B-3



For screw mounting only





Note: Without terminal cover.



Note: With terminal cover.


Mounting Holes






Terminal Arrangement/Internal Circuit Diagram

G3PE-245B-3




G3PE-545B-3




Models with Externally Attached Heat Sinks


G3PE-215B-3H
G3PE-215B-2H
G3PE-225B-3H
G3PE-225B-2H
G3PE-235B-3H
G3PE-235B-2H
G3PE-245B-3H
G3PE-245B-2H
G3PE-515B-3H
G3PE-515B-2H
G3PE-525B-3H
G3PE-525B-2H
G3PE-535B-3H
G3PE-535B-2H
G3PE-545B-3H
G3PE-545B-2H




Note: Without terminal cover.




Note: With terminal cover.




Mounting Holes






Terminal Arrangement/Internal Circuit Diagram


G3PE-2□5B-3H




G3PE-2□5B-2H



G3PE-5□5B-3H




G3PE-5□5B-2H






Accessories (Order Separately)


Heat Sink
Y92B-P50 (Mounts to DIN Track.)
For G3PE-215B-2H and G3PE-515B-2H




Heat Sink
Y92B-P100
For G3PE-215B-3H, G3PE-225B-2H, G3PE-515B-3H, and G3PE-525B-2H




Heat Sink
Y92B-P150
For G3PE-225B-3H, G3PE-235B-2H, G3PE-525B-3H, and G3PE-535B-2H



Heat Sink
Y92B-P200
For G3PE-235B-3H, G3PE-245B-2H, G3PE-535B-3H, and G3PE-545B-2H



Heat Sink
Y92B-P250
For G3PE-245B-3H and G3PE-545B-3H



Terms and Conditions Agreement

Read and understand this catalog.
Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.
(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE
PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.
Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.
See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.
OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.
Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.
Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.
NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.
Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.
Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.
Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.
Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2026.11

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation
Industrial Automation Company

http://www.ia.omron.com/

(c)Copyright OMRON Corporation 2026 All Right Reserved.