
EE-SPY31/41

CSM_EE-SPY31_41_DS_E_5_4

Accurately detects objects placed in front of shiny Background.

- A shiny background can be used as long as the distance between the sensor and the background is 20 mm or more.
- Detects minute objects such as a 0.05-mm-dia. pure copper wire.
- Small dispersion in sensing distance.
- Light modulation effectively reduces external light interference.
- Wide operating voltage range: 5 to 24 VDC





Be sure to read *Safety Precautions* on page 4.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensors Infrared light

| Appearance | Sensing method | Sensir | ng distance | Output type | Output configuration | Model |
|---|----------------------------|----------|-------------|-------------|----------------------|-----------|
| Horizontal type | Convergent reflective type | | | NPN output | Dark-ON | EE-SPY311 |
| < 3 5 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 | | 2 to 5 r | | | Light-ON | EE-SPY411 |
| Vertical type | | | 2 to 5 mm | | Dark-ON | EE-SPY312 |
| | | | | | Light-ON | EE-SPY412 |

Accessories (Order Separately)


| Туре | | Cable length | Model | |
|------------------------------|----------------------|-----------------------|----------------|--|
| Connector | | | EE-1001 | |
| | | | EE-1009 * | |
| | | 1 m | EE-1006 1M | |
| | Connector with Cable | | EE-1010 1M * | |
| | | 2 m | EE-1006 2M | |
| | | | EE-1010 2M * | |
| Connector with Robo | Connector with Robot | 1 m | EE-1010-R 1M * | |
| | Cable | 2 m | EE-1010-R 2M * | |
| NPN/PNP Conversion Connector | | 0.46 m (total length) | EE-2002 | |

Note: Refer to Accessories for details.

EE-1009- or EE-1010-series Connectors have a builtin locking mechanism to prevent cable disconnection when only the cable is pulled. To remove the Connector from the Sensor, grip the top and bottom of the Connector firmly and push into the Sensor once before pulling out. The locking mechanism prevents the Connector from being removed by pulling on the cable only and enables removal only when the Connector (housing) is pulled.


Ratings and Specifications


| Item | Models | EE-SPY311, EE-SPY411, EE-SPY312, EE-SPY412 | |
|---------------------------|--------|--|-----|
| Sensing distance | | 2 to 5 mm (Reflection factor: 90%; white paper 15 × 15 mm) | • |
| Minimum sensing object | | Pure copper wire (0.05 mm dia.) | • |
| Distance to background *1 | | 20 mm max. (glass with aluminum deposition) | *1. |
| Differential dist | ance | 0.2 mm (with a sensing distance of 3 mm, horizontally) | • |
| Light source | | GaAs infrared LED with a peak wavelength of 940 nm | |
| Indicator *2 | | Light indicator (red) | |
| Supply voltage | | 5 to 24 VDC ±10%, ripple (p-p): 5% max. | |
| Current consun | nption | Average: 15 mA max., Peak: 50 mA max. | |
| Control output | | NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max. | *2. |
| Response frequency *3 | | 100 Hz min. | • |
| Ambient illumination | | 3,000 lx max. with incandescent light or sunlight on the surface of the receiver | |
| Ambient temperature range | | Operating: -10 to +55°C Storage: -25 to +65°C | |
| Ambient humidity range | | Operating: 5% to 85% Storage: 5% to 95% | |
| Vibration resistance | | Destruction: 10 to 50 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions | • |
| Shock resistance | | Destruction: 500m/s² for 3 times each in X, Y, and Z directions | |
| Degree of protection | | IEC IP50 | • |
| Connecting method | | Special connector (soldering not possible) | |
| Weight | | Approx. 2.6 g | • |
| Material C | ase | Polycarbonate | • |
| | older | Polybutylene phthalate (PBT) | |




- *2. The indicator is a GaP red LED (peak wavelength: 700 nm).

 *3. The response frequency was measured by detecting the following rotating disk.







I/O Circuit Diagrams


NPN Output

| Model | Output configuration | Timing charts | Output circuit | |
|------------------------|----------------------|--|---|--|
| EE-SPY411 EE-SPY412 | Light-ON | Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases Load 2 | * Voltage output (when the sensor is connected to a transistor circuit) | |
| EE-SPY311 EE-SPY312 | Dark-ON | Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases Load 2 | | |


Engineering Data (Reference Value)

Operating Range Characteristics


EE-SPY311/411




EE-SPY311/411



EE-SPY312/412




EE-SPY312/412




Sensing Distance vs. Object Area Characteristics

EE-SPY ...




Sensing Angle vs. Sensing Distance Characteristics

EE-SPY312/412



Receiver Output vs. Sensing Distance Characteristics

EE-SPY ...



Safety Precautions

Refer to Warranty and Limitations of Liability.

⚠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.




Precautions for Correct Use

Make sure that this product is used within the rated ambient environment conditions.

Wiring

 Connection is made using a connector. Do not solder to the pins (leads).

- When extending the cable, use an extension cable with conductors having a total cross-section area of 0.3 mm². The total cable length must be 2 m maximum.
- To use a cable length longer than 2 m, attach a capacitor with a capacitance of approximately 10 μF to the wires as shown below. The distance between the terminal and the capacitor must be within 2 m. (Use a capacitor with a dielectric strength that is at least twice the Sensor's power supply voltage.)



• Make sure the total length of the power cable connected to the product is less than 10 m even if a capacitor is inserted.

(Unit: mm)


Dimensions

Tolerance class IT16 applies to dimensions in this datasheet unless otherwise specified.

Sensors








Terminal Arrangement

| (1) | + | Vcc |
|-----|-----|-----------|
| (2) | OUT | OUTPUT |
| (3) | - | GND (0 V) |

EE-SPY312 EE-SPY412





Terminal Arrangement

| (1) | + | Vcc |
|-----|-----|-----------|
| (2) | OUT | OUTPUT |
| (3) | _ | GND (0 V) |

Accessories (Order Separately)

^{*} Refer to Accessories for details.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.
Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2023.4

In the interest of product improvement, specifications are subject to change without notice.