Slot-type Photomicrosensor (Non-modulated) +1

EE-SX47/67

Global Standard Slot-type photomicrosensors with 50- to 100-mA direct switching capacity.

- · Series includes models that enable switching between dark-ON and light-ON operation.
- Response frequency as high as 1 kHz.
- · Easy operation monitoring with bright light indicator.
- Wide operating voltage range: 5 to 24 VDC
- · Models in which the light indicator turns ON for dark-ON operation are also available.
- A wide range of variations in eight different shapes.
- Flexible robot cable is provided as a standard feature. *2

Be sure to read Safety Precautions on page 5.

*1. Pre-wired Models are available only in the EE-SX67 Series.

*2. Only for Pre-wired Models.

Ordering Information

Connector	Consira	Connect			Output		Мо	Infrared ligh			
Appearance	Sensing method	Connect- ing method	Sensing distance		Output configuration	Indicator mode	NPN output	PNP output			
Standard					Dark-ON/Light-ON	Incident light	EE-SX670	EE-SX670P			
					(selectable) *3 *4	No incident light	EE-SX670A	EE-SX670R			
61088						Light-ON	Incident light	EE-SX470			
L-shaped					Dark-ON/Light-ON	Incident light	EE-SX671	EE-SX671P			
					(selectable) *3 *4	No incident light	EE-SX671A	EE-SX671R			
1111					Light-ON	Incident light	EE-SX471				
T-shaped,					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX672	EE-SX672P			
slot center 7 mm	9					No incident light	EE-SX672A	EE-SX672R			
					Light-ON	Incident light	EE-SX472	_			
Close-	Through- beam type (with slot)	Connector (4 poles)			Dark-ON/Light-ON	Incident light	EE-SX673	EE-SX673P			
mounting				(slot width)	(selectable) *3 *4	No incident light	EE-SX673A	EE-SX673R			
3 6 8 U					Light-ON	Incident light	EE-SX473				
Close-					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX674	EE-SX674P			
mounting						No incident light	EE-SX674A	EE-SX674R			
2000					Light-ON	Incident light	EE-SX474				
T-shaped, slot center 10 mm						Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX675	EE-SX675P		
F-shaped				-					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX676
R-shaped					Dark-ON/Light-ON (selectable) *3 *4	Incident light	EE-SX677	EE-SX677P			

*3. Dark-ON when the L terminal of the connector is opened, and light-ON when the L terminal and positive (+) terminal are connected. Do not connect the L terminal to 0 V when using dark-ON operation. When using light-ON, it is useful to select the connector EE-1001-1. The L terminal and positive (+) terminal of this connector are connected in advance.

*4. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Pre-wired Model	5							Infrared lig
Appearance	Sensing method	Sensing	distance	Output configura- tion	Indicator mode	Connecting method	Mc NPN output	PNP output
Standard							EE-SX670-WR 1M	EE-SX670P-WR 1M
L-shaped						EE-SX671-WR 1M	EE-SX671P-WR 1M	
T-shaped, slot center 7 mm		5 mm				Pre-wired Models (1m)	EE-SX672-WR 1M	EE-SX672P-WR 1M
Close- mounting	Through- beam						EE-SX673-WR 1M	EE-SX673P-WR 1M
Close- mounting	type (with slot)						EE-SX674-WR 1M	EE-SX674P-WR 1M
T-shaped, slot center 10 mm						EE-SX675-WR 1M EE-SX676-WR 1M	EE-SX675P-WR 1M	
F-shaped							EE-SX676P-WR 1M	
R-shaped						EE-SX677-WR 1M	EE-SX677P-WR 1M	

*1. Dark-ON operation can be used when the L terminal is left unconnected or Light-ON operation can be used when the L terminal and positive (+) terminal are connected to each other. Do not connect the L terminal to 0 V when using dark-ON operation.

Accessories (Order Separately) Connector Models

Type		Cable length	Model	Remarks
Connector		EE-1001		
		EE-1001-1	L terminal and positive (+) terminal are already short-circuited.	
			EE-1009 *	
		1 m	EE-1006 1M	
	Connector with Cable	1 m	EE-1010 1M *	
		2 m	EE-1006 2M	
		2 111	EE-1010 2M *	
	Connector with Robot	1 m	EE-1010-R 1M *	
	Cable	2 m	EE-1010-R 2M *	
Connector Hold-down Clip			EE-1006A	Applicable Photomicrosensors For EE-SX670 and 470 only. (Can be used only with EE-1006 Connectors for the Photomicrosensors listed above.)


Note: 1. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect

the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.
2. For details, refer to the Photomicro Sensors Accessories on EE
which can be accessed from your OMRON website.
* EE-1009- or EE-1010-series Connectors have a builtin locking mechanism to prevent cable disconnection when only the cable is pulled. To remove the Connector from the Sensor, grip the top and bottom of the Connector firmly and push into the Sensor once before pulling out. The locking mechanism prevents the Connector from the Sensor are before pulled. from being removed by pulling on the cable only and enables removal only when the Connector (housing) is pulled.


Ratings and Specifications

Туре		Standard	L-shaped	T-shaped, slot center 7 mm	Close-m	ounting	T-shaped, slot center 10 mm	F-shaped	R-shaped	
	NPN models	Connector models	EE-SX670 EE-SX670A EE-SX470	EE-SX671 EE-SX671A EE-SX471	EE-SX672 EE-SX672A EE-SX472	EE-SX673 EE-SX673A EE-SX473	EE-SX674 EE-SX674A EE-SX474	EE-SX675	EE-SX676	EE-SX677
	models	Pre-wired models		EE-SX671- WR	EE-SX672- WR	EE-SX673- WR	EE-SX674- WR	EE-SX675- WR	EE-SX676- WR	EE-SX677- WR
	PNP		EE-SX670P EE-SX670R	EE-SX671P EE-SX671R	EE-SX672P EE-SX672R	EE-SX673P EE-SX673R	EE-SX674P EE-SX674R	EE-SX675P	EE-SX676P	EE-SX677P
ltem	models	Pre-wired models	EE-SX670P- WR	EE-SX671P- WR	EE-SX672P- WR	EE-SX673P- WR	EE-SX674P- WR	EE-SX675P- WR	EE-SX676P- WR	EE-SX677P- WR
Sensi	ng distan	се	5 mm (slot width	n)						
Sensi	ng object		Opaque: 2×0.8	3 mm min.						
Differe	ential dist	ance	0.025 mm							
<u> </u>	source			th a peak wavele	0					
Indica	itor *1		,	, (0	upted for models	with A or R suffi	x)		
Suppl	y voltage			0%, ripple (p-p):	10% max.					
Curre	nt consun	nption	12 mA max.							
Control output NPN open collector: 5 to 24 VDC, 100 mA max. 100 mA load current with a residual voltage of 0.8 V max. 40 mA load current with a residual voltage of 0.4 V max. OFF current (leakage current): 0.5 mA max. PNP open collector: 5 to 24 VDC, 50 mA max. 50 mA load current with a residual voltage of 1.3 V max. OFF current (leakage current): 0.5 mA max.										
Protec	Protection circuits Load short circuit protection									
	onse frequ		1 kHz min. (3 kł	• /						
	ent illumir		1,000 lx max. with fluorescent light on the surface of the receiver.							
		rature range				(with no icing or o	,			
Ambie	ent humid	ity range	-			no icing or cond	ensation)			
Vibrat	ion resist	ance	Destruction: 20 to 2,000 Hz (peak acceleration: 100 m/s ²) 1.5-mm double amplitude for 2 h (4-min periods) each in X, Y, and Z directions							
	<pre>c resistand</pre>		Destruction: 500 m/s ² for 3 times each in X, Y, and Z directions							
Degre	e of prote	ection	IEC60529 IP50							
Conne	ecting me	thod	Connector Models (direct soldering possible), Pre-wired Models (Standard cable length: 1 m), Models with Connectors (Standard cable length: 0.1 m)							
Wei-	Connect	or models	Approx. 3.1 g	Approx. 3 g	Approx. 2.4 g	Approx. 2.3 g	Approx. 3 g	Approx. 2.7 g	Approx. 2.2 g	Approx. 2.2 g
ght	Pre-wire	d models	•		Approx. 17.8 g	Approx. 16.8 g	Approx. 17.1 g	Approx. 18.3 g	Approx. 16.9 g	Approx. 16.9 g
Ma-	Case		Polybutylene ph	nthalate (PBT)						
teri-	Cover		Polycarbonate							

*1. The indicator is a GaP red LED (peak wavelength: 690 nm).
*2. The response frequency was measured by detecting the rotating disk shown at the right.



Engineering Data (Reference Value)



I/O Circuit Diagrams

NPN Output				
Model	Output configuration	Timing charts	Terminal connections	Output circuit
EE-SX67□	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (e.g., relay) Releases	Short-circuited between ① terminal and positive ⊕ terminal	EE-SX67D EE-SX67DA
EE-SX67□-WR	Dark-ON	N light indicator ON (red) OFF Load Operates Load Operates N Open between ① terminal and positive ⊕ terminal *1*2	*The terminal arrangement depends on the model. Check the dimensional diagrams.	
EE-SX670A EE-SX671A EE-SX672A EE-SX673A EE-SX674A	Light-ON	Light indicator ON (red) OFF Uturustor OFF Output ON transistor OFF Load Operates	Short-circuited between ℂ terminal and positive ⊕ terminal	EE-SX67D-WR
	Dark-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (e.g., relay) Releases	Open between © terminal and positive ⊕ terminal *1 *2	*The terminal arrangement depends on the model. Check the dimensional diagrams.
EE-SX470 EE-SX471 EE-SX472 EE-SX473 EE-SX474	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (relay) Releases		Light indicator (red) Main circuit Circuit

*1. Do not connect the L terminal to 0 V when using dark-ON operation.
*2. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.

PNP Output Model	Output configuration	Timing charts	Terminal connections	Output circuit		
EE-SX67□P	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (relay) Releases	Short-circuited between © terminal and positive ⊕ terminal			
EE-SX67⊡P-WR	Dark-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (relay) Releases	Open between © terminal and positive ⊕ terminal *1 *2			
EE-SX670R EE-SX671R EE-SX672R	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (e.g., relay) Releases	Short-circuited between ℚ terminal and positive ⊕ terminal	*The terminal arrangement depends on the model. Check the dimensional diagrams.		
EE-SX672R EE-SX673R EE-SX674R	Dark-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load Operates (e.g., relay) Releases	Open between			

*1. Do not connect the L terminal to 0 V when using dark-ON operation.

*2. If you do not use the L terminal wire ((2) pink) when you use a Connector with Cable for an EE-1006 or EE-1010-series Photomicrosensor, noise may affect the Photomicrosensor. To prevent the effects of noise, cut the unused L terminal wire at the base of the connector and wrap it with insulating tape to prevent it from coming in contact with other terminals.

Safety Precautions

Refer to Warranty and Limitations of Liability.


This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Precautions for Safe Use

• Operating Environment

These Photomicrosensors have an IP50 (conforms to IEC) enclosure and do not have a water-proof or dust-proof structure. Therefore, do not use them in applications in which the sensor will be subjected to splashes from water, oil, or any other liquid. Liquid entering the Sensor may result in malfunction.



Precautions for Correct Use

Make sure that this product is used within the rated ambient environment conditions.

Installation

- When direct soldering to the terminals, use the following guidelines.
 Soldering Conditions
 - Soldering Conditions


Item	ature	time	Remarks
Soldering iron	350°C max.	3 s max.	The portion between the base of the terminals and the position 1.5 mm from the terminal base must not be soldered.

 The terminal base uses a polycarbonate resin, which could be deformed by excessive soldering heat, resulting in damage to the product's functionality.

Lot Number and Model Number Legend

In the following diagrams, 343U indicates the lot number and factory where the product was manufactured. Do not include this code with the model number when ordering.

The QR code on connector models is used by OMRON only.




(Unit: mm)


Dimensions


Tolerance class IT16 applies to dimensions in this datasheet unless otherwise specified.


Sensors



OMRON







Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company