CSM\_VB\_DS\_E\_1\_4

## A New Monoblock Multiple Limit Switch Incorporating a Head Box with a Tough **Head and Ensuring High Sealing** Performance and a Mechanical **Durability of 5,000,000 Operations**

- Used for the sequential control of a variety of engineering machines and belt conveyor lines.
- · Built-in oil filter shuts out oil and water.
- · Approved by EN, IEC (Ground terminal models only.) and CCC (Chinese standard). Ask your OMRON representative for information on approved models.
- Ground terminal models bear the CE mark.





Be sure to read the "Safety Precautions" on page 4 and the "Precautions for All Limit Switches".

## **Model Number Structure**

## **Model Number Legend**



### 1. Number of Plungers

- 2 plungers
- 3. 3 plungers
- 4. 4 plungers
- 5: 5 plungers
- 6 plungers

### 2. Actuator

- Bevel plunger 1:
- 2: Roller plunger

### 3. Switch Box

- Flange switch box with two conduit holes on the side
- 2: Flange switch box with four conduit holes
- 4: Non-flange switch box with two conduit holes on the side
- 5: Non-flange switch box with four conduit holes

### 4. Scraper

1: NBR scraper

2: FPM scraper

## 5. Contact

None: 10 A (standard) 0.1 A (micro load)

### 6. Ground Terminal

None: Without ground terminal With ground terminal

## Ordering Information

### **List of Models**

	Shape of box	With flange	Without flange
Actuator *	Conduit	Мо	del
Roller plunger		VB-2211	VB-2241
(with a 6.8-dia. roller)		VB-3211	VB-3241
R	Two on the side	VB-4211	VB-4241
	0.00	VB-5211	VB-5241
		VB-6211	VB-6241
		VB-2221	VB-2251
		VB-3221	VB-3251
	Four	VB-4221	VB-4251
		VB-5221	VB-5251
		VB-6221	VB-6251
Bevel plunger		VB-2111	VB-2141
$\wedge$	Two on the side	VB-3111	VB-3141
		VB-4111	VB-4141
		VB-5111	VB-5141
		VB-6111	
		VB-2121	VB-2151
		VB-3121	VB-3151
	Four	VB-4121	VB-4151
		VB-5121	
		VB-6121	

Note: 1. Other than the above models, minute load models switching 0.1 A are available. When ordering a minute load model, add the suffix A to the model number (i.e., VB-2211A for example).

- 2. SC connectors can be connected to VB models.
- 3. Models with ground terminals are also available. When ordering a ground terminal model, add the suffix E to the model number (i.e., VB-2211E for
- \* Since the actuator is incorporated into the monoblock switch, the actuator cannot be replaced

### Replaceable Switch Unit

Rating	Model
Standard load model	VB-S101N

## **Specifications**

## **Approved Standards**

Agency	Standards	File No.	Approved models
TÜV Rheinland	EN60947-5-1 (IEC947-5-1)	J50062491	Only models with ground terminals
CCC (CQC)	GB/T14048.5	Contact your OMRON representative for details.	Ask your OMRON representative for information on approved models.

## Ratings Standard Model

Rated voltage	Resistive load		
	NC	NO	
125 VAC 250 VAC	10 A 10 A		
125 VDC	0.6 A		
250 VDC	0.6 A 0.3 A		

Note: The above currents are steady-state currents.

Inrush	NC	24 A max.
current	NO	24 A max.

### **Micro Load Ratings**

Rated voltage	Resistive load
125 VAC	
8 VDC 30 VDC	0.1 A

## Approved Standard Ratings TÜV (EN60947-5-1) (Grand terminal models only) Standard Model

Applicable category	AC-15	DC-15
Rated operating current (le)	2 A	2 A
Rated operating voltage (Ue)	250 V	48 V

### **Micro Load Model**

Applicable category	AC-14	DC-15
Rated operating current (le)	0.1 A	0.1 A
Rated operating voltage (Ue)	125 V	30 V

## CCC (GB/T14048.5)

Applicable category and ratings
AC-15 2 A/250 VAC

### **Characteristics**


Degree of pro	otection	IP67	
	Mechanical	5,000,000 operations min.	
Durability * Electrical		300,000 operations min. (10 A at 250 VAC, resistive load)	
Operating sp	eed	0.1 mm to 0.5 m/s	
Operating	Mechanical	120 operations min.	
frequency	Electrical	30 operations min.	
Rated freque	ncy	50/60 Hz (AC)	
Insulation re	sistance	100 MΩ min. (at 500 VDC)	
Contact resis	stance	15 mΩ max. (initial value)	
	Between terminals of same polarity	1,000 VAC/U <sub>imp</sub> 4,000 VAC	
	Between current- carrying metal parts and ground	1,500 VAC/U <sub>imp</sub> 4,000 VAC	
Dielectric strength	Between each terminal and non- current-carrying metal part	1,500 VAC/Uimp 4,000 VAC	
	Between terminals of different polarity	U <sub>imp</sub> 4 kV (EN60947-5-1)	
Rated insulation voltage (Ui)		300 VAC (EN60947-5-1)	
Switching overvoltage		1,000 V max. (EN60947-5-1)	
Pollution degree (operating environment)		3 (EN60947-5-1)	
Short-circuit (SCPD)	protective device	10 A fuse type gG or gl (IEC269)	
Conditional	short-circuit current	100 A (EN60947-5-1)	
Conventiona current (Ithe)	l enclosed thermal	5 A, 0.5 A (EN60947-5-1)	
Protection against electric shock		Insulation class I (Use the grounding terminal or ground on the machine side.)	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude	
Shock Destruction resistance Malfunction		1,000 m/s² min.	
		200 m/s <sup>2</sup> min.	
Ambient ope	rating temperature	-10°C to 80°C (with no icing)	
Ambient operating humidity		35% to 95%	
Weight		Approx. 580 g (in the case of VB-4211)	
Note: The above values are initi		iol voluce	

Note: The above values are initial values.

## **Engineering Data**

# Electrical Durability (with more than 300,000 Operations)


(Ambient temperature: 5°C to 35°C; Ambient humidity: 40% to 70%)



<sup>\*</sup>The values are calculated at an operating temperature of 5°C to 35°C, and an operating humidity of 40% to 70%. Contact your OMRON sales representative for more detailed information on other operating environments.

## **Structure and Nomenclature**

## Structure (VB-2211)



### **Contact Form**



### Position of conduit


- Two on the side .... A and B
- Four.....A, B, and C




## **Dimensions and Operating Characteristics**

(Unit: mm)


Switches The actual model numbers of each of the above VB models have a figure 2 to 6, which indicate the number of plungers.




### Bevel Plunger VB-□141



# Roller Plunger VB-□211



### Roller Plunger VB-□241



Note: Unless otherwise indicated, a tolerance of  $\pm 0.4$  mm applies to all dimensions.

Operating characteristic	Model	VB-□221	VB-□251	VB-□121	VB-□151
	s	VB-□211	VB-□241	VB-□111	VB-□141
Operating force Release force Pretravel Overtravel *1 Movement Differential	OF max.	14.71 N	14.71 N	14.71 N	14.71 N
	RF min.	4.90 N	4.90 N	4.90 N	4.90 N
	PT max.	1.5 mm	1.5 mm	1.5 mm	1.5 mm
	OT min.	(3.5 mm)	(3.5 mm)	(3.5 mm)	(3.5 mm)
	MD max.	0.5 mm	0.5 mm	0.5 mm	0.5 mm
Operating Position Free Position *1	OP	32±0.4 mm	19±0.4 mm	26±0.4 mm	13±0.4 mm
	FP max.	(33 mm)	(20 mm)	(27 mm)	(14 mm)

**Note:** The operating characteristic values apply to a single switch.

\*1 The OT and FP values are reference values. The actual model numbers of each of the above VB models have a figure 2 to 6, which indicate the number of plungers.

Number of plungers	Size H (mm)
2	58
3	70
4	82
5, 6 *2	106

**\*2** When five plungers are mounted in series, no outer actuator will be provided.

## **Safety Precautions**

### Refer to Safety Precautions for All Limit Switches.

### Precautions for Safe Use

### Connection

- Be sure to connect a fuse with a breaking current 1.5 to 2 times larger than the rated current to the Switch in series in order to protect the Switch from damage due to short-circuiting.
- If the VB is used for EN ratings, use a gl or gG 10-A fuse approved by IEC269.

### Operation


Make sure the notch of the plunger is not pressed into the scraper when operating the VB Multiple Limit Switch, otherwise chips or dust may penetrate into the VB Multiple Limit Switch.

### Sealing

 The switch box and cover are made of die-cast aluminum and the mounting part of the Switch is covered with a seal cap, and ensure a sealing performance of more than 98×10<sup>3</sup> Pa for the VB Multiple Limit Switch.

The filter on the side of the head prevents oil and water from penetrating into the interior of the VB Multiple Limit Switch while preventing the internal pressure of the VB Multiple Limit Switch from rising when the plunger is pressed.


The seal scraper on the tip of the actuator prevents chips and dust from penetrating into the moving parts of the VB Multiple Limit Switch.



- Apply extra tightening to the cap screw on the conduit.
- In order to protect the plunger from abrasion and prolong its service life, apply a small amount of grease to the plunger and dog or cam that come into contact with the plunger. (Molybdenum disulfide grease is recommended.)

### **Appropriate Tightening Torque**

- Tighten each cover mounting screw to a torque of 1.18 to 1.37 N·m.
- 2. Tighten each switch terminal screw to a torque of 0.19 to 0.29 N·m if the mounting screw is M3 in size.



Be sure to wire each solderless terminal correctly with a screw as shown below.

Correct




Incorrect


3. Apply a torque of 5.88 to 6.86 N·m to tighten each mounting bolt of the casing if the mounting bolt is an Allen-head bolt that is M6 in size. Apply a torque of 8.04 to 9.22 N·m instead if the mounting bolt is an Allen-head bolt that is M8 in size.

### **Mounting Holes**

### With a Flange Switch Box




### Without a Flange Switch Box




### Wiring

Connect a cable with a thickness of  $0.75\ \text{mm}^2$  to the VB Multiple Limit Switch through the M3 round solderless terminals with insulation covers.

### **Dimensions of Round Solderless Terminal**



### **Wiring (Ground Terminal Models)**



Consult your OMRON representative for details on models with 3 to 6 plungers.

### **Others**

- Carefully connect a conduit to each conduit hole and apply a seal
  or tape to seal the conduit hole so that cuttings or other materials
  will not penetrate through the conduit hole.
- Use the SC Connector. Consult your OMRON representative for details on SC Connectors.
- Make sure that the position of the actuator that is traveling does not exceed the overtravel (OT) position. Make sure that the operating stroke is 70% to 100% of the specified OT distance.

### Terms and Conditions Agreement

### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

### Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <a href="http://www.omron.com/global/">http://www.omron.com/global/</a> or contact your Omron representative for published information.

### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2024.3

In the interest of product improvement, specifications are subject to change without notice.