
Slot-type Reflective Photomicrosensor EE-SPX301/401 EE-SPY30/40

(€ 91°

Photomicrosensor with light modulation is not influenced by external light.

- · Voltage-output models with wide operating voltage range (5 to 24 VDC).
- · Fitted with an easy-to-adjust optical axis mark.
- · Easy adjustment and optical axis monitoring with a light indicator.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Be sure to read Safety Precautions on page 5.

Ordering Information

Sensors

Sensors	Infrared light				
Appearance	Sensing method	Sensing distance	Output type	Output configuration	Model
	Through-beam type (with slot)			Dark-ON	EE-SPX301
		3.6 mm (slot width)		Light-ON	EE-SPX401
Horizontal type	Reflective type	5 mm	NPN	Dark-ON	EE-SPY301
			output	Light-ON	EE-SPY401
Vertical type	Reflective type			Dark-ON	EE-SPY302
	Tenecuve type	5 mm		Light-ON	EE-SPY402

Accessories (Order Separately)

	Туре	Cable length	Model	Remarks
Connector			EE-1002	
Connector	Connector with Cable	1 m	EE-1003	
NPN/PNP Conversion Connector 0.46 m (total length)		EE-2001		
Connector Hold-down Clip		EE-1003A	For EE-1003 only.	


* Refer to Accessories for details.


EE-SPX301/401 EE-SPY30/40


Ratings and Specifications

Sensing method	Through-beam type (with slot)	Reflective type		
Item Models	EE-SPX301, EE-SPX401	EE-SPY301, EE-SPY401 EE-SPY302, EE-SPY402		
Sensing distance	3.6 mm (slot width)	5 mm (Reflection factor: 90%; white paper 15×15 mm) *1		
Sensing object	Opaque: 1×0.5 mm min.			
Differential distance	0.05 mm max.	0.2 mm max. (with a sensing distance of 3 mm, horizontally)		
Light source	GaAs infrared LED with a peak wavelength of 940 nm			
Indicator *2	Light indicator (red)			
Supply voltage	5 to 24 VDC ±10%, ripple (p-p): 5% max.			
Current consumption	Average: 15 mA max., Peak: 50 mA max.			
Control output	 NPN voltage output: Load power supply voltage: 5 to 24 VDC Load current: 80 mA max. OFF current: 0.5 mA max. 80 mA load current with a residual voltage of 1.0 V max. 10 mA load current with a residual voltage of 0.4 V max. 			
Response frequency *3	500 Hz min.	100 Hz min.		
Ambient illumination	3,000 Ix max. with incandescent light or sunlight on the surface of the receiver			
Ambient temperature range	Operating: -10 to +55°C Storage: -25 to +65°C (with no icing)			
Ambient humidity range	Operating: 5% to 85% Storage: 5% to 95% (with no condensation)			
Vibration resistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 h each in X, Y, and Z directions			
Shock resistance	Destruction: 500 m/s ² for 3 times each in X, Y, and Z directions			
Degree of protection	IEC IP50			
Connecting method	Special connector (soldering not possible)			
Weight	Approx. 2.6 g			
Material Case	Polycarbonate			

*1. Operation may not be possible near the Sensor.
*2. The indicator is a GaP red LED (peak wavelength: 700 nm).
*3. The response frequency was measured by detecting the following rotating disk.









Engineering Data (Reference Value)

Operating Range Characteristics


EE-SPY301, EE-SPY401




EE-SPY301, EE-SPY401




EE-SPY302, EE-SPY402






Sensing Position Characteristics

EE-SPX301 (Z Direction)




EE-SPX301 (Y Direction)




Receiver Output Excess Gain vs. Sensing Distance Characteristics






Sensing Angle vs. Sensing Distance Characteristics

EE-SPY




Sensing Distance vs. Object Area Characteristics

EE-SPY



Dependency on Cable Length for

Operation Distance/Release Distance



I/O Circuit Diagrams

NPN Output


Model	Output configuration	Timing charts	Output circuit
EE-SPX401 EE-SPY401 EE-SPY402	Light-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases	Light indicator (red)
EE-SPX301 EE-SPY301 EE-SPY302	Dark-ON	Incident Interrupted Light indicator ON (red) OFF Output ON transistor OFF Load 1 Operates (relay) Releases	* Voltage output (when the sensor is connected to a transistor circuit)

Safety Precautions

Refer to Warranty and Limitations of Liability.

<u> WARNING</u>

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes



Make sure that this product is used within the rated ambient environment conditions.


Mounting

The sensing distance for the EE-SPY Reflective-type Photomicrosensor with built-in amplifier varies from 8 to 20 mm depending on the product (90% reflective white paper). Do not place glossy objects in the background of the sensing object.

Wiring

- Connection is made using a connector. Do not solder to the pins (leads).
- When extending the cable, use an extension cable with conductors having a total cross-section area of 0.3 mm². The total cable length must be 2 m maximum.
- To use a cable length longer than 2 m, attach a capacitor with a capacitance of approximately 10 μF to the wires as shown below. The distance between the terminal and the capacitor must be within 2 m.

(Use a capacitor with a dielectric strength that is at least twice the Sensor's power supply voltage.)



[•] Make sure the total length of the power cable connected to the product is less than 10 m even if a capacitor is inserted.

EE-SPX301/401 EE-SPY30/40


(Unit: mm)

Dimensions Tolerance class IT16 applies to dimensions in this datasheet unless otherwise specified.

Sensors


EE-SPX301 EE-SPX401













EE-SPY302 EE-SPY402







Terminal Arrangement	
----------------------	--

(1)	\oplus	Vcc
(2)	OUT	OUTPUT
(3)	Φ	GND (0 V)

Accessories (Order Separately)

* Refer to Accessories for details.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company