Solid-state Timer

CSM_H3DS_DS_E_5_3

DIN Track Mounted, Standard 17.5-mm Width Timer Range

- A wide AC/DC power supply range (24 to 230 VAC/ 24 to 48 VDC) reduces the number of timer models kept in stock. (24 to 230 VAC/VDC with H3DS-XL□)
- Smart Dial/Selector-locking Mechanism: Prevents the dials and selectors on the Timer's front panel from being inadvertently operated or being operated without authorization. The lock can only be unlocked and locked with an optional pen-type Lock Key.
- Screw-Less Clamp type available. (H3DS-□LC)
- Sticker provided for easy timer identification and management.
- Terminal clamp left open when delivered (screw terminal type).
- Finger protection terminal block to meet VDE0106/P100.
- Enables easy sequence checks through instantaneous outputs for a zero set value at any time range.
- Incorporates environment-friendly, cadmium-free contacts.
- Conforms to EN61812-1 and IEC60664-1 4 kV/2 for Low Voltage, and EMC Directives.

■Broad Line-up of H3DS Series

H3DS



Standard Timer H3DS-M (eight multi-modes) H3DS-S (four multi-modes) H3DS-A (single mode)



H3DS-F



Star-delta Timer H3DS-G



Two-wired Timer H3DS-X

Contents

Solid-state Timer

H3DS-M/-S/-A	2
H3DS-F	13
H3DS-G	20
H3DS-X	27
Common to ALL Timers	
Installation of Screw-Less Clamp Models	33
Accessories	36
Proportions	2

Solid-state Multi-functional Timer H3DS-M/-S/-A

- Eight operating modes (H3DS-M) and four operating modes (H3DS-S) cover a wide range of applications.
- A wide time setting range of 0.10 s to 120 h.
- Two LEDs indicate power and relay status respectively.



Model Number Structure

■ Model Number Legend

H3DS -
$$\frac{L}{1}$$
 $\frac{L}{2}$ $\frac{\Box}{3}$

1. M: Multi-function type

S: Standard type

A: Single-function type

2. L: Smart lock mechanism

None: Screw terminal type
 C: Screw-Less Clamp type

Ordering Information

■List of Models

Supply voltage	Control output	Input type	Operating mode (see note)	Model	
				Screwterminal type	Screw-Less Clamp type
24 to 48 VDC (time-limit output SP-	Voltage input	Eight multi-modes: A, B, B2, C, D, E, G, J	H3DS-ML	H3DS-MLC	
	DT)	No-input available	Four multi-modes: A, B2, E, J	H3DS-SL	H3DS-SLC
			Single mode: A	H3DS-AL	H3DS-ALC

Note: The operating modes are as follows:

A: ON-delay

B: Flicker OFF start

B2: Flicker ON start

C: Signal ON/OFF-delay

D: Signal OFF-delay

E: Interval

G: Signal ON/OFF-delay

J: One shot

■Accessories (Order Separately)

Lock Key		Y92S-38	
Mounting Track	50 cm (I) x 7.3 mm (t)	PFP-50N	
	1 m (l) x 7.3 mm (t)	PFP-100N	
	1 m (I) x 16 mm (t)	PFP-100N2	
End Plate	·	PFP-M	
Spacer		PEP-S	

Specifications

■General

Item	H3DS-ML□	H3DS-SL□	H3DS-AL□
Operating mode	A: ON-delay (Signal or Power) B: Flicker OFF start (Signal or Power) B2: Flicker ON start (Signal or Power) C: Signal ON/OFF-delay D: Signal OFF-delay E: Interval (Signal or Power) G: Signal ON/OFF-delay J: One-shot (Signal or Power)	A: ON-delay B2: Flicker ON start E: Interval J: One-shot	A: ON-delay (fixed)
Input type	Voltage input		
Output type	Relay: SPDT		
External connections	Screw terminal, Screw-Less Clamp		
Terminal block	Screw terminal type: Clamps two 2.5-mm² max. bar terminals without sleeves. Screw-Less Clamp type: Clamps two 1.5-mm² max. bar terminals without sleeves.		
Terminal screw tightening torque	0.98 N·m max.		
Mounting method	DIN track mounting (see note)		
Attachment	Nameplate label		
Approved standards	UL508, CSA C22.2 No.14 Conforms to EN61812-1, IEC60664-1 4 kV/2, VDE0106/P100		

Note: Can be mounted to 35-mm DIN Track with a plate thickness of 1 to 2.5 mm.

■Time Ranges

Time scale display	Time range
0.1 s	0.1 to 1.2 s
1 s	1 to 12 s
0.1 m	0.1 to 1.2 min
1 m	1 to 12 min
0.1 h	0.1 to 1.2 h
1 h	1 to 12 h
10 h	10 to 120 h

Note: When the time setting dial is set to "0" for any time scale, the output will operate instantaneously.

■Ratings

Rated supply voltage (see notes 1 and 2)	24 to 230 VAC (50/60 Hz)/24 to 48 VDC
Operating voltage range	85% to 110% of rated supply voltage
Power reset	Minimum power-off time: 0.1 s
Reset voltage	2.4 VAC/DC max.
Power consumption (see note 3)	AC: 32 VA max./3.0 W max. (typical: 30 VA/2.7 W) at 230 VAC DC: 0.7 W max. (typical: 0.6 W) at 24 VDC 1.4 W max. (typical: 1.3 W) at 48 VDC
Voltage input	Max. permissible capacitance between inputs lines (terminals B1 and A2): 2,000 pF Load connectable in parallel with inputs (terminals B1 and A1). H-level: 20.4 to 253 VAC/20.4 to 52.8 VDC L-level: 0 to 2.4 VAC/DC
Control output	Contact output: 5 A at 250 VAC with resistive load (cosφ = 1) 1 A at 250 VAC with inductive load (cosφ = 0.3) 5 A at 30 VDC with resistive load (cosφ = 1) 0.15 A max. at 125 VDC with resistive load, 0.1 A max. at 125 VDC with L/R of 7 ms. The minimum applicable load is 10 mA at 5 VDC (P reference value). Contact materials : Ag-alloy
Ambient temperature	Operating: -10°C to 55°C (with no icing) Storage: -25°C to 65°C (with no icing)
Ambient humidity	Operating: 35% to 85%

Note: 1. DC ripple rate: 20% max.

- 2. Since an inrush current of 0.5 A will occur when using the power supply voltage at 24 VDC, pay careful attention when turning on or off the power supply to the Timer with a solid-state output such as a sensor.
- 3. The power consumption is for mode A after the Timer counts the time-up time and for the AC input at 50 Hz. The power consumption of the H3DS-ML includes the input circuit with the B1 and A1 terminals short-circuited.

■Characteristics


Accuracy of operating time	±1% max. of FS (±1% ±10 ms max. at 1.2-s range)		
Setting error	±10% ±50 ms max. of FS		
Signal input time	50 ms min.		
Influence of voltage	±0.7% max. of FS (±0.7% ±10 ms max. at 1.2-s range)		
Influence of temperature	±5% max. of FS (±5%±10 ms max. at 1.2-s range)		
Insulation resistance	100 MΩ min. at 500 VDC		
Dielectric strength	Between current-carrying metal parts and exposed non-current-carrying metal parts: 2,000 VAC for 1 min. Between control output terminals and operating circuit: 2,000 VAC for 1 min. Between contacts not located next to each other: 1,000 VAC for 1 min.		
Vibration resistance	Malfunction: 0.5-mm single amplitude at 10 to 55 Hz Destruction: 0.75-mm single amplitude at 10 to 55 Hz		
Shock resistance	Malfunction: 100 m/s² 3 times each in 6 directions Destruction: 1,000 m/s² 3 times each in 6 directions		
Impulse withstand voltage	5 kV (between power terminals) 5 kV (between current-carrying metal parts and exposed non-current-carrying metal parts)		
Noise immunity	Square-wave noise generated by noise simulator (pulse width: 100 ns/1 μs, 1-ns rise) ±1.5 kV		
Static immunity	Malfunction: 4 kV Destruction: 8 kV		
Life expectancy	Mechanical: 10 million operations min. (under no load at 1,800 operations/h) Electrical: 100,000 operations min. (5 A at 250 VAC, resistive load at 360 operations/h) (see note)		
ЕМС	(EMI)EN61812-1Emission Enclosure:EN55011 Group 1 class BEmission AC Mains:EN55011 Group 1 class BHarmonic Current:EN61000-3-2Voltage Fluctuation and Flickering:EN61000-3-3(EMS)EN61812-1Immunity ESD:IEC61000-4-2Immunity RF-interference:IEC61000-4-3Immunity Burst:IEC61000-4-4Immunity Surge:IEC61000-4-5Immunity Conducted Disturbance:IEC61000-4-6Immunity Voltage Dip/Interruption:IEC61000-4-11		
Case color	Light gray (5Y7/1)		
Degree of protection	IP30 (Terminal block: IP20)		
Weight	Approx. 70 g		

Note: For reference: In both cases, a life of 100,000 operations can be expected.


Connections

■Block Diagram

H3DS-ML□




H3DS-SL□/-AL□



■I/O Functions

Item		H3DS-ML□	H3DS-SL□/-AL□
Input	Start	Starts operation.	No input is available.
Output			Outputs are turned ON according to designated output mode when preset value is reached.

■Terminal Arrangement




Note: 1. DC supply voltage does not require the designation of polarity.

2. The contact symbol for the H3DS is indicated with pecause it offers multiple operating modes and is different from the delayed contact for conventional timers.

■Input Connections

The inputs of the H3DS-ML $\!\square$ are voltage (voltage imposition or open) inputs.



Voltage Input Signal Levels

	No-contact	1. Transistor ON Residual voltage: 1 V max. (Voltage between terminals B_1 and A_2 must be more than the rated "H-level" voltage (20.4 VDC min.).)	
	input	2. Transistor OFF Leakage current: 0.01 mA max. (Voltage between terminals B ₁ and A ₂ must be less than the rated "L-level" voltage (2.4 VDC max.).)	
		When contacts are ON: 20.4 to 253 VAC/20.4 to 52.8 VDC	

Operation

■Basic Operation

Setting of Selector

The selectors can be turned clockwise and counterclockwise to select the desired time scale, or operating mode.

Each selector has a snap mechanism that secures the selector at a given position. Set the selector at a position at which it is secured. Do not set it midway between two securing positions or a malfunction could result from improper setting.

Selection of Operating Mode (except for H3DS-AL)

The H3DS-ML/-SL can be set to any one of the operating modes A to J. Turn the operating mode selector with a screwdriver until the desired operating mode appears in the operating mode display window.

H3DS-ML (8 modes): A, B, B2, C, D, E, G, J

(In order of appearance)

H3DS-SL (4 modes): A, E, B2, J, E, E, J, J

(In order of appearance)


Note: Letters that appear more than once indicate exactly the same operating mode.

Selection of Time Scale

The time scale is selected by turning the time scale selector. The time scales will appear in the following order in the time scale display window on the left of the selector:


1 s, 0.1 s, 1 h, 0.1 h, 10 h, 1 h, 1 m, 0.1 m.

Note: The time scale "1h" appears twice. Both instances indicate exactly the same time scale.




Locking/Unlocking of Selectors and Time Setting Dial

The time setting dial, time scale selector, and operating mode selector can be locked using the Y92S-38 Lock Key, a special pen type tool that is sold separately. To lock the dial or selectors, insert the Lock Key in the keyhole to the lower right of the dial or selector and turn it clockwise until the dial or selector is completely covered with the red cover. To unlock, turn the Lock Key in the opposite direction.




■Timing Chart

- Note: 1. The minimum power reset time is 0.1 s and the minimum signal input time is 0.05 s.
 - 2. The letter "t" in the timing charts stands for the set time and "t-a" means that the period is less than the time set.
 - **3.** There is no start input for H3DS-SL□/-AL□ models. Operation starts at power-on.




Note: The start input of the H3DS-ML□ model is activated by applying a voltage to B1 and A2 terminals.

The voltage can be applied by turning on the contact between B1 and A1 (Refer to *Terminal Arrangement*).




Note: The start input of the H3DS-ML□ model is activated by applying a voltage to B1 and A2 terminals. The voltage can be applied by turning on the contact between B1 and A1 (Refer to *Terminal Arrangement*).


Nomenclature



H3DS-MLC/-SLC




H3DS-AL□




(Front View)

H3DS-ALC




(Front View)



Attach the enclosed label here as a nameplate. (The label is attached to the Timer's DIN Track hook section at the time of shipment.)

Dimensions

Note: All units are in millimeters unless otherwise indicated.



ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Solid-state Twin Timer

H3DS-F

- Operates in flicker-OFF or flicker-ON start mode with one Unit.
- Independent ON- and OFF-time settings.
 Combinations of long ON- or OFF-time and short OFF- or ON-time setting are possible.
- Long time range from 0.1 s to 12 h for both ON and OFF time settings.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Structure

■Model Number Legend

H3DS $\frac{-F}{1}$ $\frac{L}{2}$ $\frac{\Box}{3}$

1. F: Twin timers

2. L: Smart lock mechanism3. None: Screw terminal typeC: Screw-Less Clamp type

Ordering Information

■List of Models

Operating mode	Supply voltage	Model	
		Screw terminal type	Screw-Less Clamp type
Flicker-OFF/Flicker-ON start	24 to 230 VAC (50/60 Hz)/24 to 48 VDC	H3DS-FL	H3DS-FLC

■Accessories (Order Separately)

Lock Key Y92S-38		Y92S-38
Mounting Track	50 cm (I) x 7.3 mm (t)	PFP-50N
	1 m (l) x 7.3 mm (t)	PFP-100N
	1 m (l) x 16 mm (t)	PFP-100N2
End Plate		PFP-M
Spacer		PEP-S

Specifications

■General

Item	H3DS-F	
Operating mode	Flicker-OFF/Flicker-ON start	
Output type	Relay: SPDT	
External connections	Screw terminal, Screw-Less Clamp	
Terminal block	Screw terminal type: Clamps two 2.5-mm² max. bar terminals without sleeves. Screw-Less Clamp type: Clamps two 1.5-mm² max. bar terminals without sleeves.	
Terminal screw tightening torque	0.98 N·m max.	
Mounting method	DIN track mounting (see note)	
Attachment	Nameplate label	
Approved standards	UL508, CSA C22.2 No.14 Conforms to EN61812-1, IEC60664-1 4 kV/2, VDE0106/P 100	

Note: Can be mounted to 35-mm DIN Track with a plate thickness of 1 to 2.5 mm.

■Time Ranges

Time scale display	Time range
0.1 s	0.1 to 1.2 s
1 s	1 to 12 s
0.1 m	0.1 to 1.2 min
1 m	1 to 12 min
0.1 h	0.1 to 1.2 h
1 h	1 to 12 h

Note: When the time setting dial is set to "0" for any time scale, the output will operate instantaneously.

■Ratings

Rated supply voltage (See note.)	24 to 230 VAC (50/60 Hz)/24 to 48 VDC	
Operating voltage range	85% to 110% of rated supply voltage	
Power reset	Minimum power-off time: 0.1 s	
Reset voltage	2.4 VAC/DC max.	
Power consumption	AC: 33 VA max./2.2 W max. (typical: 31 VA/2.0 W) at 230 VAC DC: 0.7 W max. (typical: 0.6 W) at 24 VDC 1.4 W max. (typical: 1.2 W) at 48 VDC	
Voltage input	Max. permissible capacitance between inputs lines (terminals B1 and A2): 2,000 pF Load connectable in parallel with inputs (terminals B1 and A1). H-level: 20.4 to 253 VAC/20.4 to 52.8 VDC L-level: 0 to 2.4 VAC/DC	
Control output	Contact output: 5 A at 250 VAC with resistive load (cosφ = 1) 1 A at 250 VAC with inductive load (cosφ = 0.3) 5 A at 30 VDC with resistive load (cosφ = 1)	
Ambient temperature	Operating: –10°C to 55°C (with no icing) Storage: –25°C to 65°C (with no icing)	
Ambient humidity	Operating: 35% to 85%	

Note: DC ripple rate: 20% max.

■Characteristics


Accuracy of operating time	\pm 1% max. of FS (\pm 1% \pm 10 ms max	. at 1.2-s range)	
Setting error	$\pm 10\% \pm 50$ ms max. of FS		
Influence of voltage	±0.5% max. of FS (±0.5% ±10 ms max. at 1.2-s range)		
Influence of temperature	±5% max. of FS (±5% ± 10 ms max	c. at 1.2-s range	
Insulation resistance	100 MΩ min. at 500 VDC		
Dielectric strength	, , , ,	ts and exposed	non-current-carrying metal parts: 2,000 VAC (50/60 Hz) for 1
	min.	nd aparating aire	cuit: 2,000 VAC (50/60 Hz) for 1 min.
	Between contacts not located next		
Impulse withstand voltage	3 kV (between power supply termin	nals)	
	<u> </u>		xposed non-current-carrying metal parts)
Noise immunity		oise simulator (p	oulse width: 100 ns/1 μs, 1-ns rise) ±1.5 kV
Static immunity	Malfunction: 4 kV Destruction: 8 kV		
Vibration resistance	Malfunction: 0.5-mm single amplitu Destruction: 0.75-mm single amplit		
Shock resistance	· '		IZ
SHOCK resistance	Malfunction: 200 m/s², 3 times each Destruction: 300 m/s², 3 times each		
Life expectancy	Mechanical: 10 million operations r Electrical: 100,000 operations mi		ad at 1,800 operations/h) AC, resistive load at 360 operations/h) (see note)
EMC	(EMI)	EN61812-1	
	Emission Enclosure:	EN55011 Grou	
	Emission AC Mains: Harmonic Current:	EN55011 Grou EN61000-3-2	p 1 class B
	Voltage Fluctuation and Flickering:		
	(EMS)	EN61812-1	
	Îmmunity ESD:	EN61000-4-2:	6 kV contact discharge (level 3) 8 kV air discharge (level 3)
	Immunity RF-interference from AM Radio Waves:		
	EN61000-4-3: 10 V/m (80 MHz to 1 GHz) (level 3)		
	Immunity Burst:	EN61000-4-4:	2 kV power port and output port (level 3) 1 kV control port with capacitive clamp (level 3)
	Immunity Surge:	FN61000-4-5	2 kV common mode (level 3)
			1 kV differential mode (level 3)
Case color	Light gray (5Y7/1)		· ·
Degree of protection	IP30 (IP20 for terminal block)		
Weight	Approx. 70 g		
_			

Note: For reference:

A maximum current of 0.15 A can be switched at 125 VDC (cosφ=1). A maximum current of 0.1 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 10 mA at 5 VDC (failure level: P).

Connections


■Block Diagram



■I/O Function

Inputs Flicker-ON start operation begins when inputs are turned ON.		Flicker-ON start operation begins when inputs are turned ON.	
Outputs	Control output	Outputs are turned ON/OFF according to the time set by the ON-and OFF-time setting dial.	

■Terminal Arrangement



Note: 1. If voltage is applied to terminal B1, or if terminals A1 and B1 are shorted, the operating mode is switched to flicker-ON start mode. If these terminals are disconnected, the mode switches to flicker-OFF start mode.

2. DC supply voltage does not require the designation of polarity.

Operation

■Basic Operation

Setting of Selector

The selectors can be turned clockwise and counterclockwise to select the desired time scale, or operating mode.

Each selector has a snap mechanism that secures the selector at a given position. Set the selector at a position at which it is secured. Do not set it midway between two securing positions or a malfunction could result from improper setting.

Settings for ON/OFF Start


If voltage is applied to terminal B1, or if terminals A1 and B1 are shorted, the operating mode is switched to flicker-ON start mode. If these terminals are disconnected, the mode switches to flicker-OFF start mode. The operating mode will not change if the state of the applied voltage changes during timer operation.

Selection of Time Scale

The time scale is selected by turning the ON-time scale selector and OFF-time scale selector. The time scales will appear in the following order in each time scale display window on the left of the selector:

0.1 s, 1 h, 0.1 h, 1 m, 1 s, 0.1 h, 0.1 m, 1 s.

Note: The time scales "1 s" and "0.1 h" appear twice. Both instances indicate exactly the same time scale.




Time Setting

Use the ON/OFF-time setting dials to set the ON/OFF time.

Locking/Unlocking of Selectors and Time Setting Dial

The ON/OFF-time setting dials and time scale selectors can be locked using the Y92S-38 Lock Key, a special pen type tool that is sold separately. To lock the dials or selectors, insert the Lock Key in the keyhole to the lower right of the dial or selector and turn it clockwise until the dial or selector is completely covered with the red cover. To unlock, turn the Lock Key in the opposite direction.




■Timing Charts


Operating mode	Timing chart
Flicker-OFF start (See note 1.)	Power (A ₁ and A ₂) ON OFF Output relay: NO 15 and 18 (ON indicator) Output relay: NC 15 and 16 OFF indicator OFF OFF
Flicker-ON start (See note 1.)	Power (A ₁ and A ₂) OFF Signal (B ₁ and A ₂) Output relay: NO 15 and 18 (ON indicator) Output relay: NC 15 and 16 OFF OFF OFF OFF OFF OFF OFF O

Note: 1. If voltage is applied to terminal B1, or if terminals A1 and B1 are shorted, the operating mode is switched to flicker-ON start mode. If these terminals are disconnected, the mode switches to flicker-OFF start mode.

- 2. The reset time requires a minimum of 0.1 s.
- 3. When power is supplied in flicker-ON start mode, the OFF indicator lights momentarily. This, however, has no effect on the performance of the Timer.


Nomenclature







Dimensions


H3DS-FL





H3DS-FLC





ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Solid-state Star-delta Timer

H3DS-G

• A wide star-time range (up to 120 seconds) and star-delta transfer time range (up to 1 second)





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Structure

■Model Number Legend

H3DS -G L $\frac{\Box}{1}$ $\frac{\Box}{2}$ $\frac{\Box}{3}$

1. G: Star-delta timer

2. L: Smart lock mechanism

3. None: Screw terminal typeC: Screw-Less Clamp type

Ordering Information

■List of Models

Operating mode	Supply voltage	Model	
		Screw terminal type	Screw-Less Clamp type
Star-delta operation	24 to 230 VAC (50/60 Hz)/24 to 48 VDC	H3DS-GL	H3DS-GLC

■ Accessories (Order Separately)

Lock Key		Y92S-38	
Mounting Track	50 cm (I) x 7.3 mm (t)	PFP-50N	
1 m (l) x 7.3 mm (t)		PFP-100N	
	1 m (l) x 16 mm (t)	PFP-100N2	
End Plate		PFP-M	
Spacer		PEP-S	

Specifications

■General

Item	H3DS-G		
Operating mode	Star-delta operation		
Operating/Reset method	Time-limit operation/Self-reset		
External connections	Screw terminal, Screw-Less Clamp		
Terminal block	Screw terminal type: Clamps two 2.5-mm² max. bar terminals without sleeves. Screw-Less Clamp type: Clamps two 1.5-mm² max. bar terminals without sleeves.		
Terminal screw tightening torque	0.98 N·m max.		
Output type	(Star operation circuit) Relay: SPST-NO (Delta operation circuit) Relay: SPST-NO		
Mounting method	DIN track mounting (see note)		
Attachment	Nameplate label		
Approved standards	UL508, CSA C22.2 No.14 Conforms to EN61812-1, IEC60664-1 4 kV/2, VDE0106/P100		

Note: Can be mounted to 35-mm DIN Track with a plate thickness of 1 to 2.5 mm.

■Time Ranges

Time scale Star operation time ranges	
x 1	1 to 12 s
x 10	10 to 120 s

Star-delta transfer time	Programmable at 0.05 s, 0.1 s, 0.5 s, or 1 s

■Ratings

Rated supply voltage (see note)	24 to 230 VAC (50/60 Hz)/24 to 48 VDC	
Operating voltage range	85% to 110% of rated supply voltage	
Power reset	Minimum power-off time: 0.5 s	
Reset voltage	2.4 VAC/DC max.	
Power consumption	AC: 21 VA max./1.7 W max. (typical: 20 VA/1.6 W) at 230 VAC DC: 1.3 W max. (typical: 1.2 W) at 24 VDC 0.7 W max. (typical: 0.6 W) at 48 VDC	
Control output	Contact output: 5 A at 250 VAC with resistive load (cosφ = 1) 1 A at 250 VAC with inductive load (cosφ = 0.3) 5 A at 30 VDC with resistive load (cosφ = 1)	
Ambient temperature	Operating: -10°C to 55°C (with no icing) Storage: -25°C to 65°C (with no icing)	
Ambient humidity	Operating: 35% to 85%	

Note: DC ripple rate: 20% max.

■Characteristics

Accuracy of operating time	±1% max. of FS		
Setting error	$\pm 10\% \pm 50$ ms max. of FS		
Total tolerance of transfer time	± (25% FS + 5 ms) max.		
Influence of voltage	±0.5% max. of FS		
Influence of temperature	±5% max. of FS		
Insulation resistance	100 MΩ min. at 500 VDC		
Dielectric strength	Between current-carrying metal parts and exposed non-current-carrying metal parts: 2,000 VAC (50/60 Hz) for 1 min. Between control output terminals and operating circuit: 2,000 VAC (50/60 Hz) for 1 min. Between contacts not located next to each other: 1,000 VAC (50/60 Hz) for 1 min.		
Impulse withstand voltage	3 kV (between power supply termin 4.5 kV (between current-carrying m		xposed non-current-carrying metal parts)
Noise immunity	Square-wave noise generated by n	ioise simulator (p	pulse width: 100 ns/1 μs, 1-ns rise) ±1.5 kV
Static immunity	Malfunction: 4 kV Destruction: 8 kV		
Vibration resistance	Malfunction: 0.5-mm single amplitude at 10 to 55 Hz Destruction: 0.75-mm single amplitude at 10 to 55 Hz		
Shock resistance	Malfunction: 200 m/s², 3 times each in 6 directions Destruction: 300 m/s², 3 times each in 6 directions		
Life expectancy	Mechanical: 10 million operations r Electrical: 100,000 operations mi		ad at 1,800 operations/h) AC, resistive load at 360 operations/h) (see note)
EMC	(EMI) Emission Enclosure: Emission AC Mains: Harmonic Current: Voltage Fluctuation and Flickering: (EMS) Immunity ESD: Immunity RF-interference from AM Immunity Burst: Immunity Surge:	EN61812-1 EN61000-4-2: Radio Waves: EN61000-4-3: EN61000-4-4:	
Case color	Light gray (5Y7/1)		
Degree of protection	IP30 (IP20 for terminal block)		
Weight	Approx. 70 g		


Note: For reference:

A maximum current of 0.15 A can be switched at 125 VDC ($\cos\phi$ =1).

A maximum current of 0.16 A can be switched at 125 VBG (cosy-A maximum current of 0.1 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 10 mA at 5 VDC (failure level: P).

Connections


■Block Diagram



■I/O Functions

Inputs		
Outputs		Star output is turned OFF when the dial set value is reached and delta output is ON after the preset transfer time elapses

■Terminal Arrangement



 $\textbf{Note:} \ \mathsf{DC} \ \mathsf{supply} \ \mathsf{voltage} \ \mathsf{does} \ \mathsf{not} \ \mathsf{require} \ \mathsf{the} \ \mathsf{designation} \ \mathsf{of} \ \mathsf{polarity}.$

Operation

■Basic Operation

Setting of Selector


The selectors can be turned clockwise and counterclockwise to select the desired time scale, or operating mode.

Each selector has a snap mechanism that secures the selector at a given position. Set the selector at a position at which it is secured. Do not set it midway between two securing positions or a malfunction could result from improper setting.

Selection of Time Unit and Time Scale

The star-delta transfer time and star operation time scale are set with the same selector. The star-delta transfer time can be set to 0.05, 0.1, 0.5, or 1. The star operation time scale can be set to a multiplication factor of 1 or 10. If the star-delta transfer time is displayed in the display window in white letters, this means that the star operation time scale is "x10". Refer to the example below.

Star-delta transfer time	Star operation time scale
0.05 s	x1
0.1 s	
0.5 s	
1 s	
0.05 s	x10
0.1 s	
0.5 s	
1 s	




Time Setting


The star operation time of the Timer is set with the time setting dial.

Locking/Unlocking of Selectors and Time Setting Dial

The time setting dial and time scale selector can be locked using the Y92S-38 Lock Key, a special pen type tool that is sold separately. To lock the dial or selectors, insert the Lock Key in the keyhole to the lower right of the dial or selector and turn it clockwise until the dial or selector is completely covered with the red cover. To unlock, turn the Lock Key in the opposite direction.




■Timing Charts




Note: The reset time requires a maximum of 0.5 s.

Nomenclature





Dimensions

H3DS-GL



H3DS-GLC





ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

Solid-state Two-wired Timer

H3DS-X

• Covers wide range of supply voltage (24 to 230 VAC/VDC).



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Structure

■Model Number Legend

H3DS -X L 1 2 3

X: Two-wired timer
 L: Smart lock mechanism

3. None: Screw terminal type Screw-Less Clamp type

Ordering Information

■List of Models

Supply voltage	Input type	Operating mode	Model	
			Screw terminal type	Screw-Less Clamp type
24 to 230 VAC/VDC (50/60 Hz)	No-input available	ON-delay	H3DS-XL	H3DS-XLC

■ Accessories (Order Separately)

Lock Key		Y92S-38	
Mounting Track	50 cm (I) x 7.3 mm (t)	PFP-50N	
	1 m (I) x 7.3 mm (t)	PFP-100N	
	1 m (I) x 16 mm (t)	PFP-100N2	
End Plate	·	PFP-M	
Spacer		PEP-S	

Specifications

■General

Item	H3DS-X	
Operating mode	ON-delay	
Operating/Reset method	Time-limit operation/self-resetting	
Output type	SCR output	
External connections	Screw terminal, Screw-Less Clamp	
Terminal block	Screw terminal type: Clamps two 2.5-mm² max. bar terminals without sleeves. Screw-Less Clamp type: Clamps two 1.5-mm² max. bar terminals without sleeves.	
Terminal screw tightening torque	0.98 N·m max.	
Mounting method	DIN track mounting (see note)	
Attachment	Nameplate label	
Approved standards	UL508, CSA C22.2 No.14 Conforms to EN61812-1, IEC60664-1 4 kV/2, VDE0106/P100	

Note: Can be mounted to 35-mm DIN Track with a plate thickness of 1 to 2.5 mm.

■Time Ranges

Time scale display	Time range
0.1 s	0.1 to 1.2 s
1 s	1 to 12 s
0.1 m	0.1 to 1.2 min
1 m	1 to 12 min
0.1 h	0.1 to 1.2 h
1 h	1 to 12 h
10 h	10 to 120 h

Note: When the time setting dial is set to "0" for any time scale, the output will operate instantaneously.

■Ratings

Rated supply voltage (see note)	24 to 230 VAC/VDC (50/60 Hz)	
Operating voltage range	85% to 110% of rated supply voltage	
Power reset	Minimum power-off time: 0.1 s	
Reset voltage	1.0 VAC/VDC max.	
Reset current	5 mA max.	
Power consumption	5 mA max.	
Control output	SCR output:5 mA to 0.7 A	
Ambient temperature	Operating: -10°C to 55°C (with no icing) Storage: -25°C to 65°C (with no icing)	
Ambient humidity	Operating: 35% to 85%	


 $\textbf{Note:} \ \mathsf{The \ ripple \ in \ DC \ power \ supply \ must \ be \ 5\% \ max}.$

■Characteristics

Accuracy of operating time	±1% max. of FS (±1% ±10 ms max. at 1.2-s range)		
Setting error	$\pm 10\% \pm 50$ ms max. of FS		
Reset time	0.1 s max.		
Influence of voltage	±0.5% max. of FS (±0.5%±10 ms max. at 1.2-s range)		
Influence of temperature	±5% max. of FS (±5%±10 ms max. at 1.2-s range)		
Insulation resistance	100 MΩ min. at 500 VDC		
Dielectric strength	Between current-carrying metal parts and exposed non-current-carrying metal parts: 2,000 VAC for 1 min		
Impulse withstand voltage	3 kV (between power supply terminals) 4.5 kV (between current-carrying metal parts and exposed non-current-carrying metal parts)		
Noise immunity	Square-wave noise generated by noise simulator (pulse width: 100 ns/1 μ s, 1-ns rise) \pm 1.5 kV (between power supply terminals)		
Static immunity	Malfunction: 4 kV Destruction: 8 kV		
Vibration resistance	Malfunction: 0.5-mm single amplitude at 10 to 55 Hz Destruction: 0.75-mm single amplitude at 10 to 55 Hz		
Shock resistance	Malfunction: 200 m/s², 3 times each in 6 directions Destruction: 300 m/s², 3 times each in 6 directions		
EMC	(EMI) Emission Enclosure: Emission AC Mains: Harmonic Current: Voltage Fluctuation and Flickering: (EMS) Immunity ESD: Immunity RF-interference from AM Immunity Burst: Immunity Surge:	EN61812-1 EN61000-4-2: Radio Waves: EN61000-4-3: EN61000-4-4:	p 1 class B 6 kV contact discharge (level 3) 8 kV air discharge (level 3)
Case color	Light gray (5Y7/1)		
Degree of protection	IP30 (IP20 for terminal block)		
Weight	Approx. 70 g		

Connections

■Block Diagram



■I/O Functions

Inputs		
Outputs	Control output	Outputs are turned ON when the preset value is reached.

■Terminal Arrangement

H3DS-XLC H3DS-XL A1 A1 A2 A2

Note: DC supply voltage does not require the designation of polarity.

Operation

■Basic Operation

Setting of Selector

The selectors can be turned clockwise and counterclockwise to select the desired time scale, or operating mode.


Each selector has a snap mechanism that secures the selector at a given position. Set the selector at a position at which it is secured. Do not set it midway between two securing positions or a malfunction could result from improper setting.

Selection of Time Scale

The time scale is selected by turning the time scale selector. The time scales will appear in the following order in the time scale display window on the left of the selector:


1 s, 0.1 s, 1 h, 0.1 h, 10 h, 1 h, 1 m, 0.1 m.

Note: The time scale "1h" appears twice. Both instances indicate exactly the same time scale.




Locking/Unlocking of Selectors and Time Setting Dial


The time setting dial and time scale selector can be locked using the Y92S-38 Lock Key, a special pen type tool that is sold separately. To lock the dial or selectors, insert the Lock Key in the keyhole to the lower right of the dial or selector and turn it clockwise until the dial or selector is completely covered with the red cover. To unlock, turn the Lock Key in the opposite direction.




■Timing Charts




Nomenclature






Dimensions


H3DS-XL





H3DS-XLC





ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.


Installation of Screw-Less Clamp Models

■ Tools

A flat-blade screwdriver should be used to mount the cables.

Applicable Screwdriver

● Flat-blade, Parallel-tip, 2.5 mm diameter



Examples: FACOM AEF.2.5 × 75E

VESSEL No. 9900-(-)2.5 × 75

WAGO 210-119 WIHA 260/2.5 × 40

■Applicable Wires

Applicable Wire Sizes


0.2 to 1.5 mm², AWG24 to AWG16

Applicable Wire Type

Solid wires, stranded wires, flexible wires, or wires with ferules can be used.

(See note 1) < $1.8 \le Diameter D (mm) \le 3.0$ (see note 2)

Conductor diameter d (mm) or length of sides a and b (mm) ≤ 1.6



Note: 1. If the overall diameter of the wire is less than 1.8 mm, do not insert the wire past the conductor. Refer to the following diagrams.



If the overall diameter of the wire is over 2.8 mm, it will be difficult to use double wiring.

■Wiring

Use wires of the applicable sizes specified above. The length of the exposed conductor should be 6 to 7 mm.




Fig. 1 Exposed Conductor Length

Use the following wiring procedure.

1. Insert the specified screwdriver into the release hole located beside the wire connection hole where the wire is to be inserted.




Fig. 2 Wire Connection Holes and Release Holes






Fig. 3 Section A-A of Fig. 2



2. Insert the exposed conductor into the wire connection hole.




3. Pull out the screwdriver.




■Precautions

Always insert the screwdriver straight into the hole, never at an angle. The clamp spring may be deformed if the screwdriver is not straight.



Do not move the screwdriver side to side in the clamp hole. The clamp spring may be deformed if the screwdriver is moved sideways.





Accessories (Order Separately)


Note: All units are in millimeters unless otherwise indicated.

■Dimensions


Lock Key Y92S-38







Note: The values shown in parentheses are for the PFP-50N.



Safety Precautions

■Changing of Setting

∕!\ CAUTION

Do not change the time scale or operating mode, while the Timer is in operation or malfunction could result.

■Power Supplies

The H3DS Series is provided with a transformerless power supply system. An electric shock may be received if the input terminal is touched while power is being supplied.

Use the bar terminal for wiring the H3DS. Using a stranded-wire terminal may cause a short-circuit due to a stray wire entering into the

Both AC and DC power supplies can be connected to the power input terminals without regarding polarity.

With the H3DS only, a DC power supply must be connected to the power input terminals as designated according to the polarity of the terminals


A DC power supply can be connected if its ripple factor is 20% or less and the mean voltage is within the rated operating voltage range of the Timer

Make sure that the voltage is applied within the specified range, otherwise the internal elements of the Timer may be damaged.

Connect the power supply voltage through a relay or switch in such a way that the voltage reaches a fixed value at once or the Timer may not be reset or a timer error could result.


Be sure that the capacity of the power supply is large enough, otherwise the Timer may not start due to inrush current (approx. 3 A) that may flow for an instant when the Timer is turned on.

For the power supply of an input device of the H3DS-ML, use an isolating transformer, of which the primary and secondary windings are mutually isolated and the secondary winding is not grounded.



■Installation


If the load current is continuously being supplied to the Timer for a long period of time, be sure to provide the mounting clearance as shown in the figure below. If used under the conditions other than those specified below (except for the H3DS-XL \square), the life of internal components may be shortened due to an excessive rise in the internal temperature.




Switching Current vs. Ambient Temperature

(When Mounting Two or More H3DS Units Side-by-Side)

• H3DS-ML□/-SL□/-AL-□




• H3DS-FL□/-GL□



■Input/Output

Relationship between Input and Power Supply Circuits (H3DS-ML□)




Since the input circuit and the power supply circuit are configured independently, the input circuit can be turned on or off irrespective of the on/off state of the power supply.

It must be noted that a voltage equivalent to the power supply voltage is applied to the input circuit.

When connecting a relay or a transistor as an external signal input device, pay attention to the following points to prevent short-circuiting due to a sneak current to the transformerless power supply.

If a relay or transistor is connected to two or more Timers, the input terminals of those Timers must be wired properly so that they will not be different in phase or the terminals will be short-circuited to one another (refer to the figures below).



The H3DS Series is provided with a transformerless power supply system.

H3DS-ML□

Input Wires

The input wires must be as short as possible. If the floating capacity of wires exceeds 2,000 pF (approx. 17 m for cables with 120 pF/m), the operation will be affected. Pay particular attention when using shielded cables.

■ Precautions for EN61812-1 Conformance

The H3DS as a built-in timer conforms to EN61812-1 provided that the following conditions are satisfied:

The output section of the H3DS is provided only with basic isolation. To ensure reinforced isolation required by the EN61812-1, provide supplementary basic isolation on the load side connected to the output.

The H3DS itself is designed according to the following:

- · Overvoltage category III
- Pollution degree 2

On the above basis:

Operation parts on the front and bottom: Reinforced isolation

 With clearance of 5.5 mm and creepage distance of 5.5 mm at 230 VAC

Output: Basic isolation

 With clearance of 3 mm and creepage distance of 3 mm at 230 VAC

Environment

When using the Timer in an area with excess electronic noise, separate the Timer, wiring, and the equipment which generates the input signals as far as possible from the noise sources. It is also recommended to shield the input signal wiring to prevent electronic interference

Organic solvents (such as paint thinner), as well as very acidic or basic solutions can damage the outer casing of the Timer.

Do not use the Timer in places where it is exposed to dust, corrosive gas, or direct sunlight.

When storing the Timer, make sure that the ambient temperature and humidity are within the rated values. Leave the Timer at room temperature for at least three hours before using the Timer if it has been stored at an ambient temperature of -10° C or below.

Leaving the Timer with outputs ON at a high temperature for a long time may hasten the degradation of internal parts (such as electrolytic capacitors). Therefore, use the product in combination with relays and avoid leaving the product as long as more than 1 month with the output turned ON.

■Others

If the Timer is mounted on a control board, dismount the Timer from the control board or short-circuit the circuitry of the power board before carrying out a voltage withstand test between the electric circuitry and non current-carrying metal part of the Timer, in order to prevent the internal circuitry of the Timer from damage.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

In the interest of product improvement, specifications are subject to change without notice.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2024.1

In the interest of product improvement, specifications are subject to change without notice.