

Programmable Terminals

### **NS Series**

NS, the HMI brand you can rely on



» Machine Management

realrzing

#### NS, the HMI brand you can rely on

### Machine Control at Your Fingertips. On-screen Machine Management.

Expanding markets in emerging countries, short product cycles, and diversifying customer needs are just some of the factors that create drastic changes for the production industry. To win in severe global market competition, you have to continue to grasp industry changes quickly, understand user needs accurately, and provide diverse forms of added value. OMRON will help you handle ever-changing customer needs with the three keywords of the NS Series.

#### Let Your Machines Evolve

#### **Best Match**

OMRON has provided even greater compatibility with OMRON PLCs and components to provide an advanced design process that lets you achieve appealing machines.


#### **Machine Management**

The NS Series transforms machine HMIs from simple operation panels and turns them into machine management tools.

#### Proven Reliability

The NS-series PTs have a proven track record that will take your machines to a higher level of reliability.







#### The Best Match Possible

The amount of work and cost of connecting to OMRON PLCs and components have been greatly reduced. The results is an incredible range of features that is possible only when unifying to one manufacturer.



#### **Machine Management Tool**

The machine designer can easily implement PLC troubleshooting, machine troubleshooting, settings for servo drives, temperature controllers, and other control components, status monitoring of connected devices, and uploading/downloading of parameters.



#### **Proven Reliability**

In the ten years since initial marketing, OMRON has globally supplied numerous HMI solutions with the highly reliable NS Series at over 200 sales and service centers around the world.



### NS Series Lineup

This powerful lineup showcases OMRON's unique value. Choose from 3 types to match your application and requirements.

#### NS Series

**Standard Models** 

Plentiful screen variations and diverse functions allow use in a wide variety of applications.



#### **NSH** Series

Hand-held Models



Equipped with a red switch for an emergency stop input.Emergency stop (3 inputs)



A hand-held version of the NS5 is now available to perform operations at the production site.

Equipped with a gray switch for a stop input. Emergency stop (3 inputs) Hand-held PT Cable



#### **NSJ** Series

Integrated Controller Models PT is unified with the Controller into one package to greatly help standardize equipment and reduce size.



#### Software CX-Designer



Without screen creation and ladder programming, the CX-Designer Screen Design Software is so easy-to-use that anyone can master it.

#### **NS-Runtime**



This software enables PLC communications from a personal computer by manipulating PT screens created using the CX-Designer.

### A Revolutionary Best Ma

The NS-series PTs provide revolutionary compatibility with the road-proven CS/CJ-series the new NJ/NX-series Controllers to achieve even greater added value in user machines.



#### EtherNet/IP

#### The NJ/NX-series Machine **Automation Controllers Revolutionize Productivity**

You can create a flexible, high-speed, high-precision system based on the NJ-series Machine Automation Controllers. Use tags to access any memory areas, or troubleshoot machines and systems by using the NS-series PTs to make the most of the strengths of the NJ/NX-series Controllers and to manage machines.

EtherCAT

lant ontrol panel Abort

lant air condition Abort

Panel capture

500:

5003

5004

Abort

ontro

Palleti:


/alue o

	Test Run (JOG)				
	Test Run (Direct)	Ale mory Op. Monitor	Ax1	Ax2	
	Present Comnd Posit Comnd Units			153	
	Present Comnd Spd Domnd Units/s			45	
	Preset Use Comnd Posit Comnd Units			8	
	JOG Operation	~	$\rightarrow$		
	Stop Type	Immediate Stop	Decel Stop		
	Unit Menu	est Run (JOC		rect Op. Ionitor	
	Main Menu	Fest Run (Direct		nory Op. onitor	
-					

•

Reset er

### tch PLCs and



Features are provided to easily connect to CS/CJ-series PLCs to take advantage of their proven track record.

Many features that do not require screen creation or programming support everything from design through maintenance to take advantage of the compatibility of OMRON PLCs and PT and to serve as the face of your machines.



0990 0990


1

TREND SCREEN

<u>100</u> **3780** 256

### Power Support for All User

From conceptual designs through commissioning, operation, and maintenance, the NS



502

Needs

Series supports every user need.

### Startup/Operation



4 4 7

NJ/NX Controller

#### For Machine Automation Controllers NJ/NX-series

Use Integrated NS-series PT simulation or NJ troubleshoot by using the NS-series PTs to make the most of the strengths of the NJ/NX-series Controllers and to manage machines.

#### **NJ Troubleshooter**

#### **Controller Errors**

#### **Standard Feature for NJ/NX-series Controllers**

Errors are automatically detected and displayed on-screen along with corrective actions for the CPU Unit function modules, EtherCAT slaves, and CJ-series Units that are connected in the NJ/NX-series Controller. Whenever an error might occur, you can recover normal operation quickly to reduce downtime without using user manuals or Support Software on a computer.

#### **User-defined Errors**

#### No Work Is Required to Create Alarm Screens.

Frames for alarm screens are provided as standard features in the NS-series PTs. You do not need to create screens to complete alarm screens. Management of the meanings of alarms is unified on the Controller, so you do not have to register, add, or correct addresses on the NS-series PTs.



#### **Integrated NS-series PT simulation**


#### Improved debugging efficiency

"Integrated simulation" of Sysmac Studio enables offline debugging of the screen data for the NS-series PTs and sequence program for the NJ/NX-series on the computer.

\* Sysmac Studio version 1.02 or higher (CX-Designer version 3.41 or higher) is required.







Please clean the reading part glass

in the maintenance box. Please exchange the reading units when not improving it even if it cleans

by using alcohol and the cotton waste

#### Troubleshooter

STOP

Note: Alarms, PLC/PT memory, and other items can be selected for the switching trigger.

Alarm bit 10.02 ON

(printing error)


Desigr

#### **Best Match with OMRON Products**

NS Series is the most suitable HMI for the system that comprises OMRON components. The advantage is the "compatibility (reducing programming and screen data creation work)" which will reduce the amount of designing work.



No Screen Designing / No Programming








Temperature Controllers

PLC



#### Smart Active Parts (SAP Library)

#### Dramatically reduces the effort required to create ladder programming and screens.

More than 3,000 Library parts (Smart Active Parts) are available, which can directly access OMRON PLCs and components. The objects can just be pasted from the Smart Active Parts (SAP Library) Library to the screen; it is completely unnecessary to create screens and ladder programming.

SAP Library, Temperature Controller Parts

**CX-Designer Screen** Design Software





#### Support tool objects can be incorporated to check for errors and make settings. even without a computer.

Plenty of support tool objects (the Tool Function SAP Library) are available, which can be easily incorporate support tool functions in the NS-series PT. Just paste the support tool objects in the screen to check for errors and make settings, even without a computer.



#### **CPU Bus Unit and Special I/O Unit Troubleshooting Can Be Also Performed** with the SAP Library.

A Troubleshooter SAP Library is available to troubleshoot each Unit in the PLC. When an error occurs in a Unit, the Troubleshooter SAP Library provides an easy-to-understand explanation of the cause of the error as well as the countermeasures.

Note: The Troubleshooter SAP Library is included as a standard feature for the CX-One and CX-Designer. For details, refer to page 56. Successive development for Ethernet Units and MC Units is planned for the future. The Temperature Controller's setting and monitor screens are completed in no time.



PLC CPU Unit monitoring screen NCF Unit setting screen DeviceNet monitoring screen

Example screens using support tool objects (Tool Function SAP Library)

#### Troubleshooter SAP for a Position Control Unit



Startup/Uperation

Maintenance

**NS-Runtime** 


Hand-held PT

#### **EtherNet/IP**


#### Support for data structures

This special feature is made possible by combining an OMRON CJ2/NJ/NX PLC with an NS-series PT. The data structures that you define on the Programming Tool can be used on the CX-Designer simply by dragging and dropping them.

Note: When connecting to each controller with EtherNet / IP, check the version of CX-Designer and NS on page 15 "Connectable Devices".




#### **Tag access**



#### Simultaneous and parallel engineering


STOP

The host applications can be designed using the tag names of the PLC and PT. Parallel development will shorten the design time.



#### Minimize side effect of address changes

It is possible to access memory with tags, so the PT and host application are not affected even if the address of data in the PLC is changed.




Specifications

#### **Direct Connection to Temperature Controllers**

#### **Connect OMRON Temperature Controllers directly to the NS-series PT.**

OMRON Temperature Controllers can be connected directly to the NS-series PT's RS-232C port. Data does not pass through the PLC, so ladder programming is not required. Also, there are plenty of objects in the SAP Library for Temperature Controllers, and Temperature Controller screens can be created easily just by pasting objects from the SAP Library to the screens.

Note: An RS-422A Serial Adapter is needed to connect directly to a Temperature Controller. Refer to page 53 for a list of the Temperature Controllers that can be connected. A Conversion Unit is not required to connect to the RS-422A/485 serial interface of the NS15.



CJ1W-CIF11 RS-422A Serial Adapter



OMRON Temperature

OMRON Temperature Controllers





#### Face Plate Auto-Builder for NS

NS Series

### Screens for Loop Controllers can be easily and automatically created.


Significantly reduces the effort required to combine a Loop Controller with an NS-series PT.

Easy automatic generation of faceplates, such as faceplates for PV monitoring and SV setting, as well as tuning screens, such as screens to set and autotune PID constants.

A total of 17 function blocks are supported, with eleven function blocks, such as Ratio Setting and Motor Manipulators newly supported (version 3 of higher).

Comments are automatically entered for automatically assigned unit and scale settings when a project is generated (version 3 and higher).

SYSMAC CS/CJ-series Loop Controller



Creation of other required

screens

Note: Refer to the PLC-based Process Control Catalog (Cat. No. P051) and the Loop-control CPU Unit Catalog (Cat. No. R128) for details on Loop Controllers.

#### **Multi-language Support**

#### Support 42 languages and switch the language of the labels among up to 16 languages.

Unicode is supported and 42 Asian and European languages can be combined in screens. Also, it is possible to switch between up to 16 labels using the label switching function, so it is possible to support up to 16 languages in a single screen just by specifying the language to be displayed in each label.

#### Multi-language CSV data



The labels' text attributes can also be reflected when importing

When screen data is imported, text attributes can be applied to the specified labels and attributes such as the font and text color can be reflected to other languages labels.

Impor


#### **NS Series**

STOP



#### Multi-language conversion has become much easier.


The screen data in the source language is exported to a CSV file and sent to a translation agency by e-mail for translation. Later, the translated CSV file is just imported to easily provide multi-language support.



Note: Windows XP (Service Pack3 or higher), Vista or 7 is required for multi-language support.

#### Multi-language System Messages. **Eight Languages Supported as Standard Feature**

The system program of NS-series PTs supports Chinese and European languages. All eight languages are a standard feature, including Chinese (traditional and simplified), Spanish, Italian, German, and French, in addition to the previous Japanese and English. Along with maintenance menus, messages for communications errors, communications settings, and screen transfers can be displayed in any of eight languages. Maintenance can be performed in the desired language. The language can be easily set using the NS-series PT or screen data.





Specifications

X

#### **Multifunction Objects**


#### Execute up to 32 functions with one Multifunction Object Multifunction Objects support Write Bit, Write Word, object control, and etc

Multifunction Objects combine the functions of multiple objects into one object. Multiple functions can be executed by pressing one button without using troublesome macros. Setup is easy. For example, a setting can be made on-screen using the Support Software to turn ON a bit to start a machine, set a value, and then change the screen.


Easy On-screen Setup with Support Software!



Multifunction execution with one object




Execute multiple functions with one button.



### Multifunction Objects support four useful functions Switches that do not immediately operate when touched can be easily made without ladder programming. ON delay Turns ON when the button is pressed for at least a specified time. Ľ

Relay status



OFF!

	Touch Button pressed
	Delay: 0.5 to 15 s
Double-press	Turns ON when the button is pressed twice within the specified time.
	Button pressed
	Relay status Acceptance time: 0.5 to 30 s
Simultaneous pressing prohibited	Does not turn ON when the button is pressed at the same time as another button.
OFF delay	Turns OFF after a specified time lapses after the button is released.
	Button pressed

#### 18


#### **Plentiful Graphing Functions**

#### **Data Log Graph (Trend Graph)**

Up to 128 data can be collected in the cycle of 500ms. Logging data is stored as a CSV file in the Memory Card inserted in the NS-series PT.

Logging data is stored as a CSV file in the Memory Card mounted in the NS-series PT. The data stored in the Memory Card can be read or deleted from the screen.

A log can be saved automatically, without any programming, just by selecting the Save the data periodically Option in the Data Log Setting Window.



Suffixes are automatically added to file names set in the CX-Designer.

Memory Card

Logging data for each day (43,200 points) is saved in the Memory Card in CSV format.

LOG001.CSV 04/06/04 10:00 L0G002.CSV 04/06/05 10:00 L0G003.CSV 04/06/06 10:00 L0G004.CSV 04/06/07 10:00 LOG005.CSV 04/06/08 10:00 L0G006.CSV 04/06/09 10:00 L0G007.CSV 04/06/10 10:00

It is possible to make a one-week log by automatically saving the data seven times.

#### **Line Graph Function**

The data logged by the PLC can be displayed in overlapping graphs, so a device's operation can be compared for evaluation and analysis. In addition, up to 1,000 words of consecutive data can be displayed as a line graph, data can be displayed together, and any region can be magnified.


#### (1) Graphs can be superimposed.

000

	Data Trace	MEMU
Luad Data Start	Change points 1000 500 100	
550		
Ø		
<	~	>> >


(2) The display can be magnified.





#### **Continuous Line Function**

Any position from the host (PLC) can be plotted as a graph. A graph can be plotted in any position by specifying the X and Y coordinates of the vertices. Also, the graph can be moved on the screen by specifying the movements from the PLC.



19

Specifications

## 757 481 145 186

#### **Screen Data Security Functions**

### Protect important screen data with a password.

If password protection is set in the data transfer security settings when the screen data is designed, a password must be entered to download or upload the screen data, so important screen data can be protected.



If a password has been set, the password is required to transfer screen data (download or upload) with the Memory Card.

#### Security password



A password between 4 and 64 characters long can be set. The download/upload will start if the user inputs the password that was set when the screen was designed. (Password input will be disabled if the wrong password is input 3 times in a row.)





#### **Device Data Transfer**

### Easy Data Exchange between the PLC and Components

For example, temperature controller alarm values can be transferred to the DM Area of the PLC's CPU Unit. No communications programming or macros are required.

#### **Multi-vendor Support**

Devices from multiple vendors are supported. Data can be easily exchanged with PLCs from other companies and Modbus devices.

#### **Easy Settings**

To make the settings, simply specify the device and addresses of the transfer source and transfer destination in the CX-Designer. Settings can be made using the same procedure as for setting the addresses for normal components.


### Easier Operation when Combining SAP Library Objects

SAP data can also be exchanged. SAP data can be exchanged by checking the address of the SAP data in the dialog box of the SAP object pasted in the CX-Designer and specifying that address as the transfer source address.


Note 1: EtherNet/IP tags are not supported.

Note 2: CX-Designer version 3.1 or higher is required. NS system version 8.2 or higher is required.


#### Multi-vendor Support



oompan



CX-Designer Select Device Data Transfer Setting from the PT Menu.



#### **NS Screen Templates**

The CX-Designer of version 3.5 or higher provides the palette to display objects and templates. Refer to the next page for details of the palette.

#### **Even Simpler**


STOP

Templates can be read into the screen by just dragging and dropping thumbnails displayed on the palette.

The template consisting of multiple screens allows multiple screens to be read by dragging and dropping it once.

The Address Setting Dialog Box that is displayed to read templates is useful for changing addresses all at once.

#### **Easy Reading from Palette**




**Address Setting Dialog Box** 

**POP** (default)

#### **Even More Beautiful**

The refined templates enable you to use the NS Series with the screens that have a sense of unity in design.

Three different types of templates besides default screens are provided. The design can be changed easily with "Theme Name" that is displayed when dragging and dropping.



#### "Cool" Objects

Backgrounds, buttons, labels, message boxes, and other objects are also provided for various themes. 99999 99995 99999 99999 99999 99999 \$9999 \$9999 99999 99999 99999 99999 \$\$\$99 \$\$999 99999 \$9999



Design

#### **CX-Designer, Screen Design Software**

#### **User-friendly Screen Creation**

Without screen creation and ladder programming, the CX-Designer Screen Design Software is so easy-to-use that anyone can master it. Quickly create the required screen by dragging and dropping objects. OMRON' s unified development environment lets you drastically reduce the work required to create screens.

Note: The same type of Project Workspace and Output Window as in the CX-Programmer are provided for the user interface.

#### All addresses and comments can be managed using a single Symbol Table.


Shows a list of addresses, names, and comments used in project screen data. Addresses, names, and I/O comments for the CX-Programmer can also be imported.



Improved Icons and Help

#### Objects and templates can be selected easily from the palette.

Easy-to-use, well-designed, and super-beautiful objects and templates can be read into the screen by dragging and dropping. Templates can be chosen from four different designs.




• Reusing screens from other projects is easy with the CX-Designer.

• Settings for alarms, data logs, communications, and other functions can be easily accessed.

Switches, lamps, and templates are registered in the palette. Just drag and drop them on the new or existing screen to add.


Note. CX-Designer version 3.5 or higher is required.




## 11

#### **Reading Another Project's Screens** and Objects

Resources from another project can be easily reused by just selecting the screen or objects that you want to read and dragging and dropping it, so screens can be created intuitively.







#### **Reading CAD Files**

It is possible to import DXF files by dragging and dropping them. The files are read as a diagram, and so less capacity is used than with images. It is also easy to customize the diagram by changing the shape or color.

### The screen data and ladder program can be checked simultaneously in the computer.

The CX-Designer and CX-Programmer interconnects the test functions in the computer through the CX-Simulator. The screens and ladder program checks are performed simultaneously, which significantly increases debugging efficiency. The CX-Programmer also has a new button for integrated simulation. And, work efficiency is further improved with the ability to keep required work screens pinned on front and to zoom in or out as desired.





Startup/Operation

Maintenance

**NS-Runtime** 

Hand-held PT


Features

Network

System Contiguration

Ordering Information

Specifications



STOP

## Startup/Operation 481 45 18

#### 260,000-color Video Display

### Equipment and workpiece movements can also be displayed in beautiful video

#### NS-CA001 Video Input Unit


Four video inputs or CCD cameras can be connected and up to four images can be displayed simultaneously if the image size is 320x240 pixels. The NS-CA001 cannot be used with the NS5 or the NS15.

#### NS-CA002 RGB/Video Input Unit

There is an analog RGB input terminal in addition to the two video input terminals. Either of the video signals or the analog RGB signal can be displayed on the NS-series PT. The NS-CA002 cannot be used with the NS5.

Note: Video input cannot be used with the NS15. Only RGB input can be used.

#### Also Compatible with OMRON Vision Sensors.





#### **Analog RGB Output**

### The NS screen is seen by another monitor.

The NS15 screen (XGA) can be displayed on an on-site display that has RGB inputs.

Note: Only NS15



#### **FTP Function**


STOP

### You can partially replace text and pictures from your computer.

FTP (File Transfer Protocol) has been added! Texts, lists, and recipes can be replaced with the put/get command from your computer! You can even replace BMP files from your computer easily.

Replace

he wafer



2 on 4.bm

Level 1

Level 2

Level 3

Level 4

Level 5

200209.txt

Handle

on.

the wafer

with gloves

Operator passwords are

characters long and the

level number increases.

Passwords can be up to 16


access rights increase as the

managed in 5 levels.

**User Security Functions** 

### Operator access rights and the operating format can be set to one of five password levels.

Each operator can be given one of 5 password levels using the User Security (level authentication) function. A password level can be set for each object, so various objects can be made inoperable or hidden based on the operator's access level.



12 on 4.br

200209.txt

Replace

the wafe**r** 



The operator cannot manipulate objects with a password level (authentication level) higher than the operator's login level.

#### **LED** backlight

#### NS5 color-type models (SQ/TQ models), NS8 models, NS10 models, NS12 models, NS15 models with LED backlight are newly released.\*

LED backlight allows backlight brightness adjustment of up to 32 levels. The brightness can be adjusted from the operation screens, and the RUN indicator changes its luminance according to the settings of the backlight brightness; it is favorable for ship and vessel applications.

\*LotNo.15Z0 or later of NS5 color-type models, LotNo.28X1 or later of NS8 models, LotNo.11Y1 or later of NS10 models, LotNo.14Z1 or later of NS12 models, LotNo.31114K or later of NS15 models.

#### Conventional three-level adjustment

PT動作	設定し、人	<u> </u>	終了
タッチスイ	( ッチ入力音	2/6) ←	→
ON	OFF		
ブザー音			
ON	OFF	ERR ON	
バックライ			
高輝度	中輝度(	輝度	
		書きい	3

#### New 32-level adjustment

PT動作	設定	XII ~	終了
タッチスィ	′ッチ入力		$\leftarrow \rightarrow$
ON	OFF		
ブザー音			
ON	OFF	ERR I	NC
バックライト輝度			
高輝度	中輝度	低輝度	32段階
			さ込み

	PT動作設定 メニュー 終了			
	(2/6) ← → タッチスイッチ入力音			
	ON	OFF		
	ブザー音			
J	ON	OFF	ERR ON	
- 1	ハックライ	ト輝度	>>	O CORHK
			32	3段階
1	書き込み			

Desigr

Specifications


### Maintenance

#### Comparison

#### The on-site NS screen can be compared with the computer screen.

The comparison function of the CX-Designer enables the following comparison. CX-Designer project  $\rightleftharpoons$  Project in the computer CX-Designer project  $\rightleftharpoons$  NS project





Same

Different

Same in screen

Different in screen

#### **Single Port Multi Access (SPMA)**

Note: Communications across network layers can be performed.


### Transfer ladder program data to the PLC via the PT. Perform online editing via the PT.


Computer (Serial/USB) → NS-series PT (Ethernet) → PLC (Ethernet or Controller Link) → PLC

#### Transfer screen data via the PLC.

Computer (Serial) →

PLC (Ethernet or Controller Link) → NS-series PT





**CX-Designer** 

USB relay cable

(IP65 oil-proof type) (sold separately: NS-USBEXT-1M)

Commercially available USB

cable

NS

### Using a USB relay cable greatly improves debugging at equipment startup.

Use a USB relay cable to enable performing maintenance from in front of the control panel.

#### **Easy Automatic Connection**

A search is automatically made for the PLCs connected to the PT and the results are displayed using the automatic online connection function in the CX-Programmer. Just select a PLC from the list to connect. This function is also supported for PLCs over network layers.


CX-Programmer



- Note 1: SPMA can be used in CS/CJ-series PLCs with lot number 030201 or later.
- Note 2: SPMA via a PLC is not supported when a CP-series PLC is connected. (SPMA via an NS-series PT is supported with a CP-series PLC.)
- Note 3: CX-Programmer version 8.2 and higher support automatic online connection via the PT. NS system version 8.2 or higher is required.



**CX-Programme** 




PLCs registered to the PT are automatically searched for. Make the connection simply by selecting from the PLC list.

#### **PLC Data Trace**

### The PLC data trace function can be used without a computer.

The PLC Data Trace function is built into the PT in addition to the Ladder Monitor and Device Monitor. A bit's status and operation can be viewed in a time chart just by setting the desired PLC bit's address in the PT. It is also now possible to display word data, save data in CSV files, and save time chart screens in BMP files.

- Note 1: There are differences between this Data Trace function and the CX-Programmer's Data Trace function. Refer to the NS-series Programmable Terminal Programming Manual (Cat. No. V073) for details.
- Note 2: The PLC data trace function cannot be used with the 5.7-inch model.
- Note 3: The PLC data trace function is not supported for connection with a CP1E/CP2E PLC.




CS/CJ/CP-series PLC



#### **Operating log**

#### What Was Touched When? can be recorded.

Functionality has been improved with the addition of a log to record operators' use of the panels. It is now possible to record and display the time, date, and operation details for buttons (i.e., hardware switches) pressed on the control panel in addition to operations on the touch panel. The operation log can be saved in a CSV file on a Memory Card mounted in the NS-series PT.



Desigr

### Maintenance

#### **Ladder Monitor**

### The ladder program can be monitored without a computer.

Ladder programs with I/O comments can be monitored on the PT's screen and the ladder program can also be edited with the Programming Console function.



CS/CJ/CP-series PL(

### Also meets the requirements of users who need to display devices onsite

#### **Switch Box Function**


The operator can check the PLC status by displaying just the I/O comments and status.

#### **Device Monitor Function**

Displays the device's contents, allowing settings to be input and checked and making startup operations more efficient.

### so no extra work to show I/O comments


Read I/O comments directly from the PLC. I/O comments do not have to be stored in a Memory Card.



#### Switch Box Function




# Device Monitor Function




### Easy checking the alarm bit and shortens searching time.


When an alarm occurs, touch the message to automatically search for the alarm bit (output bit) for the alarm. This enables you to quickly check the alarm address and investigate why the bit turned ON.



#### "Find Back", "Find Next", useful Function Supported by the NS-series.

Reduced Time to Investigate Which Output or Input Is Causing the Problem.





#### Force-setting and force-resetting are possible

Locations that have been force-set are displayed in pink and can be checked at a glance.

 1.Select the input bit for which the output will be forced ON.
 2. Select the address by touching the panel.
 3. Select the Forced Set Option and then press the Update Button.

 Image: I

Minor changes in values of timers or counters can be made without Support Software.

start

#### Check and Change I/O While You View the Ladder Diagram on the I/O Monitor

Display and change the present value by specifying the address. It is also possible to force-set/reset bits with the I/O monitor.



4. Forced ON

nge Value			
	4810.88	ForceCancA)	
		Update	
		Cance1	

Can

Design

Note: The Ladder Monitor function is not supported by the 5.7-inch models.


### **NS-Runtime**

#### NS-NSRCL (NS-Runtime)

### Achieve machine/line monitoring and data logging on your office computer.

#### **Machine Viewer**

Machine monitoring in an office environment. There is no need to create complex host applications. Moreover, when an alarm occurs, a PDF file can be displayed as maintenance information. NS Series screens can be reused on the computer, and screens can be also newly created independently of touch panels at the production site.



#### Wide Screen

Computer output can be displayed on another wide-screen monitor. XGA (1,024 x 768 dots) and up to a a maximum screen size of 3,840 x 2,400 is supported. Alarms occurring in devices or the line can be monitored.



Log large amounts of data using a personal computer. Data can be logged through background processing, with up to 160,000 points stored in one file. The logged data is stored in CSV format, and data can be displayed on data log graphs.



#### Example: 160,000 Points


Data can be logged for approximately 7.4 days, assuming data is logged every two seconds for 12 hours a day. By using automatic file saving, data logging can be continued even longer than 7.4 days.

#### **Recipe Handling**

Checking machine data or switching processes from a host computer is easy. Parameter groups in the PLC can be transferred together to a computer, and the transferred data can be checked and edited in CSV format, e.g., using Excel. The edited data can then be transferred together back to the PLC.



	A	В
1	001	CJIG
2	002	CPM2A
3	003	D4JL
4	004	E5CN
5	005	F3SJ




#### **Easy Installation**

To get started, just install the NS-Runtime in the computer and place the screen data in the applicable folder. NS/NSJ-series screens and NS-Runtime screens can all be managed using one single tool.

Note: The NS-Runtime will operate in a computer environment even if the CX-Designer installed is not installed. The hardware key (USB dongle) that is supplied with the NS-Runtime is required for operation.




Screen Data



Screen designer: CX-Designer (CX-One)

#### **Application Startup Function**

User applications can be started from NS-Runtime. Applications can be started simply by pressing buttons on the screen.



Write to PLC

Print

Note 1: If the screen data is converted for the NS Series, NS-Series PT system versions must be 8.1 or earlier. The screen data of system version 8.2 can not be converted for the NS-Runtime. Note 2: Do not use this product for 24-hour operation in an FA environment. OMRON shall not be responsible if the computer or application does not operate properly due to noise or other causes. OMRON shall not be responsible for any problems that may be caused by any applications other than OMRON products.

Read from PLC


6

Design

Specifications

#### **NSH5 Series**

A hand-held version of the NS5 is now available to perform operations at the production site. The NS-series PT's have a complete set of functions that can be used at the production site, such as the SAP Library, multi-language support, and Programming Console functions.



### Precautions for Emergency Stop Switches

When using a hand-held NSH5 that will be installed and removed from a control panel or Removable Box, always use the specified Stop Switch (Gray/NSH5-SQG10B-V2) to conform to Safety Standards (EN 60204-1).

#### **Options**

#### **Removable Box**

A separate external circuit is not required because the Removable Box has been configured so that the emergency stop switch line will not turn OFF (i.e., so that the emergency stop circuit will operate) even when the NSH5 is removed.

#### Visor

Use when the NSH5 is in direct sunlight.

#### Mounting Bracket

Use to attach the NSH5 to a control panel.









Programmable Terminals NS Series

#### Even Simpler Equipment Operation with Outstanding Synergy.



5.7 inches Color TFT STN monochrome

10.4 inches Color TFT

15 inches Color TFT

12.1 inches Color TFT

8.4 inches Color TFT

#### Features

- 5.7 to 12.1 inch sizes are available.
- A hand-held version of the NS5 is now available to perform operations at the production site. The NS-series PT's have a complete set of functions that can be used at the production site.
- The Smart Active Parts(SAP Library) makes it easy to connect to OMRON PLCs and components, OMRON provides a development environment that requires with no programming and no screen designing.
- When an error occurs in a Unit in the OMRON PLCs, the Troubleshooter SAP Library provides an easy-tounderstand explanation of the cause of the error as well as the countermeasures.
- Ladder Monitor come as a Standard Feature. The ladder program can be monitored onsite without a laptop! Ladder monitor lets you monitor PLC program status, search for addresses or instructions, monitor multiple I/O points, and much more.
- Provides the FA integrated tool package "CX-One" for a Screen Design Software Integrated Simulation come as a Standard Feature. The integrated simulation function simulates ladder programs and screen data simultaneously even without the actual hardware.
- Screens support 42 languages and the Support Software supports eight. System messages can be displayed in eight languages.
- Single Port Multi Access (SPMA) come as a Standard Feature. The ladder program and screen data can be transferred from a single port!
- Connectable PLCs and devices appear one after another.
   Has become connectable with the PLCs of Mitsubishi Electric Corporation and the Inverters of OMRON

Has become connectable with the PLCs of Mitsubishi Electric Corporation and the Inverters of OMRON Corporation.


Specifications

OMRON

#### NS Series

#### Network

Provides serial NT Link communications supporting both 1:1 and 1:N connections. The NT Link has more efficient communications than Host Link and its capabilities are especially apparent in applications with multiple PTs connect to the PLC. The NS-series PTs can also support communications with multiple PLCs and multiple NS-series PTs through Controller Link and Ethernet connections, so the network can be configured freely to match the requirements and scale of the application. In addition, using the NS-Runtime makes it possible to monitor machine status and log data from the host.




#### Configuration of CJ2 series, NJ series and NX series


#### 1 EtherNet/IP Connection (Tag accesses)

If an Ethernet-compatible NS-series PT is used, the PT can connect to a Controller with built-in EtherNet/IP and an Option Unit is not needed to connect at the PT.




Design





## **System Configuration**

## NS5/NS8/NS10/NS12/NS15



**\*1.** Bar Code Reader (V520-RH21-6) was discontinued at the end of August 2016. **\*2.** Wireless (WE70) is final order entry date at the end of June 2020.

Design


Startup/Operation

Maintenance

MONITORING LINE A MARKET STATE	Any one of the following Units the expansion bus interface.	can be mounted to	
	Controller Link Interface Unit	Controller Link	
RATE 87%     Transaction of a Mail Constant of	NS-CLK21		i e Maria
O 1 O 1 O 1 O 1 O 1 O 1 O 1 O 1 O 1 O 1	Video Input Unit	NTSC/PAL	PLC
CONTRO 20131 INC 20130 INC 2013	NS-CA001		Vision
	RGB/Video Input Unit	NTSC/PAL	Sensor
RUN STOP DETAIL RESET MENU HISTORY	NS-CA002		
Expansion bus		RGB output	
interface			
			Personal computer

Note: Video Input Units and RGB Video Input Units cannot be used with some models.

## Multi-vendor



Note: Whether an RS-422A or RS-485 connection is supported depends on the device that you are connecting to. For details, refer to the Connectable Devices page or NS-Series Programmable Terminals HOST CONNECTION MANUAL Multivendor Connection (Cat.V092). **NSH5 Hand-held PT** USB Commercially available USB cable. Memory USB Slave Card interface OMRON Personal computer **NSH5 PT** Memory Card **RS-232C** PLC cable RS-232C RS-232C Connecting Cable for the NSH5 NSH5-232CW-3M (Length: 3 m) RS-232C Connecting Cable for the NSH5 NSH5-232CW-10M (Length: 10 m) RS-422A PLC cable **RS-422A** RS-422A Connecting Cable for the NSH5 NSH5-422CW-10M (Length: 10 m) RS-232C PLC cable RS-232C RS-232C Connecting Cable for the NSH5 NSH5-232UL-3M (Length: 3 m) RS-232C Connecting Cable for the NSH5 **UL-listed Cables** NSH5-232UL-10M (Length: 10 m) **RS-422A** PLC cable RS-422A RS-422A Connecting Cable for the NSH5 NSH5-422UL-10M (Length: 10 m) USB Commercially available USB cable. Memory USB Slave Card interface OMRON NSH5 PT Personal computer Memory Card Removable Box Connected Removable Box RS-232C cable RS-422A RS-232C Connecting Cable for the NSH5 NSH5-232CN-3M (Length: 3 m) RS-232C Connecting Cable for the NSH5 NSH5-232CN-10M (Length: 10 m) System Configuration (Removable Box Connected) Up to eight NSH5s can be connected at a time. NSH5 (See note.) PLC RS-232C connection (Cable length: 3 or 10 m) Removable Box Control panel RS-422A connection (Total cable length: 500 m max.) Up to 15 Removable Boxes can be connected.

Note: Before removing the NSH5 from the Removable Box,

be sure to first turn OFF the power supply key on the Removable Box.

## **Ordering Information**

### **International Standards**

- The standards are availabled as follows: U: UL, U1: UL (Class I Division 2 Products for Hazardous Locations), C: CSA, UC: cULus, UC1: cULus (Class I Division 2 Products for Hazardous Locations), CU: cUL, N: NK, L: Lloyd, and CE: EC Directives.
- Contact your OMRON representative for further details and applicable conditions for these standards.

## **Programmable Terminals**

Product name		Specification	s		Model	Standards	up/(
Product name	Effective display area	Number of dots	Ethernet	Case color	Model	Standards	artup/Operation
NS5-V2 *1			No	lvory	NS5-SQ10-V2		atio
	5.7-inch *2 TFT color		INO	Black	NS5-SQ10B-V2		_
	LED backlight		Yes	lvory	NS5-SQ11-V2		
		$320 \times 240 \text{ dots}$	Tes	Black	NS5-SQ11B-V2	UC1, CE, N, L,	$\leq$
133-12	5.7-inch *2	320 × 240 0015	No	lvory	NS5-TQ10-V2	UL Type4	Maintenance
	High-luminance		INO	Black	NS5-TQ10B-V2		enar
	TFT color		N	lvory	NS5-TQ11-V2		lce
	LED backlight		Yes	Black	NS5-TQ11B-V2		
NS8-V2			NI-	lvory	NS8-TV00-V2		
	8.4-inch *2	$640 \times 480 \text{ dots}$	No	Black	NS8-TV00B-V2	UC1, CE, N, L	
	TFT LED backlight		Yes	lvory	NS8-TV01-V2		-SN
				Black	NS8-TV01B-V2	-	NS-Runtime
		640 × 480 dots	No Yes	lvory	NS10-TV00-V2		time
1040.1/0	10.4-inch *2			Black	NS10-TV00B-V2		
NS10-V2	TFT LED backlight			lvory	NS10-TV01-V2		
				Black	NS10-TV01B-V2		
			No	lvory	NS12-TS00-V2	UC1, CE,	Hai
NS12-V2	12.1-inch *2 TFT	$800 \times 600$ dots		Black	NS12-TS00B-V2	N, L, UL Type4	nd-h
NS12-V2	LED backlight	$800 \times 600$ dots	Yes	lvory	NS12-TS01-V2	OL Type4	Hand-held PT
			Yes	Black	NS12-TS01B-V2		PT
N045 V0	15-inch		N	Silver	NS15-TX01S-V2		
NS15-V2	TFT	$1,024 \times 768 \text{ dots}$	Yes	Black	NS15-TX01B-V2		
NSH5-V2 *1	5.7-inch	$320 \times 240 \text{ dots}$	No	Black (Emergency stop button: Red)	NSH5-SQR10B-V2	UC, CE	Features
Hand-held	TFT	320 × 240 001s	NO	Black (Stop button: Gray)	NSH5-SQG10B-V2	_ 00, 0E	res

\*1. As of July 2008, the image memory has been increased to 60 MB.

\*2. Lot No. 15Z0 or later of NS5 color-type models, Lot No. 28X1 or later of NS8 models, Lot No. 11Y1 or later of NS10 models, Lot No. 14Z1 or later of NS12 models, LotNo.31114K or later of NS15 models.

### NS-Runtime

Product name	Specifications			Model	Standards
NS-Runtime		1license		NS-NSRCL1	
	NS-Runtime Installer, PDF manual, hardware key (See note.)	3 licenses	CD	NS-NSRCL3	
		10 licenses		NS-NSRCL10	

Note: A hardware key (USB dongle) is required for NS-Runtime operation.

### System Requirements

Item	Specifications
OS *	Windows 7 (32-bit/64-bit version)/Windows 8 (32-bit/64-bit version)/Windows 10 (32-bit/64-bit version)
CPU	Celeron, 1.3 GHz or higher (Recommended)
	HDD: 50 MB min., RAM: 512 MB min. (Windows 7: 1 GB min.). 50 MB is required for the Runtime alone. (An additional 280 MB is required if CX-Server is not already installed.)

\* Ver. 1.30 or later of NS Runtime do not support Windows XP (Service Pack 3 or higher) and Windows Vista.

Design

## Software

### How to Select Required Support Software for Your Controller

The required Support Software depends on the Controller to connect. Please check the following table when purchasing the Support Software.

Item	Omron PLC System	Omron Machine Automation Controller System
Controller CS, CJ, CP, and other series NJ-series		NJ-series and NX-series
Programmable Terminals	NS-series	NS-series with an Ethernet port
Software	FA Integrated Tool Package CX-One	Automation Software Sysmac Studio

### ●FA Integrated Tool Package CX-One

			n		
Product name	Specifications	Number of licenses	Media	Model	Standards
FA Integrated Tool Package CX-One Ver.4.⊡	The CX-One is a comprehensive software package that integrates Support Software for OMRON PLCs and components. CX-One runs on the following OS. Windows XP (Service Pack 3 or higher, 32-bit version) / Windows Vista (32-bit/ 64-bit version) / Windows 7 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version) / Windows 8.1 (32-bit/64-bit version) / Windows 10 (32-bit/64-bit version) CX-One Version 4 includes CX-Designer Ver.3 For details, refer to the CX-One catalog (Cat. No. R134)	1 license *	DVD	CXONE-AL01D-V4	-

\* Multi licenses (3, 10, 30, or 50 licenses) and DVD media without licenses are also available for the CX-One.

### Automation Software Sysmac Studio

Please purchase a DVD and required number of licenses the first time you purchase the Sysmac Studio. DVDs and licenses are available individually. Each model of licenses does not include any DVD.

	Specifications	Specifications				
Product name		Number of licenses	Media	Model	Standards	
	The Sysmac Studio provides an integrated development environment to set up, program, debug, and maintain NJ/NX Series CPU Units, NY-series Industrial PC, Controllers and other Machine Automation Controllers, as	- (Media only)	Sysmac Studio (32-bit) DVD	SYSMAC-SE200D	_	
Sysmac Studio Standard Edition Ver.1.□	well as EtherCAT slaves. Sysmac Studio runs on the following OS. Windows 7 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version) / - Windows 8.1 (32-bit/64-bit version) / Windows 10 (32-bit/64-bit version) *1 The Sysmac Studio Standard Edition DVD includes Support Software to set up EtherNet/IP Units, DeviceNet slaves, Serial Communications Units, and Support Software for creating screens on HMIs (CX-Designer). Refer to your OMRON website for details.	- (Media only)	Sysmac Studio (64-bit) DVD	SYSMAC-SE200D-64	_	
		1 license *2	_	SYSMAC-SE201L	_	

Note: To connect the NJ5 Controller, NS system version 8.5 or higher is required. CX-Designer version 3.3 or higher is also required. To connect the NJ1/NJ3 Controller, NS system version 8.61 or higher is required. CX-Designer version 3.4 or higher is also required. To connect the NX7 Controller, NS system version 8.9 or higher is required. CX-Designer version 3.64 or higher is also required. To connect the NX1 controller, NS system version 8.96 or higher is required. CX-Designer version 3.70 or higher is also required. To connect the NX1 controller, NS system version 8.96 or higher is required. CX-Designer version 3.70 or higher is also required. To connect the NX1 controller, NS system version 8.93 or higher is required. CX-Designer version 3.70 or higher is also required.

\*1. Model "SYSMAC-SE200D-64" runs on Windows 10 (64 bit).

\*2. Multi licenses are available for the Sysmac Studio (3, 10, 30, or 50 licenses).

Cable

Product name	Specifications		Model	Standards
able *1	Screen transfer cable for DOS/V (CX-Designer $\leftrightarrow$ PT)	Length: 2 m	XW2Z-S002	-
~	USB-Serial Conversion Cable	Length: 0.5 m	CS1W-CIF31	N
	USB relay cable	Length: 1 m	NS-USBEXT-1M	
	RS-422A cable (loose wires + D-Sub 9-pin)	Length: 10 m	NSH5-422CW-10M	_
NSH5 Cables	RS-232C cable (loose wires + D-Sub 9-pin)	Length: 3 m	NSH5-232CW-3M	
	RS-232C cable (loose wires + D-Sub 9-pin)	Length: 10 m	NSH5-232CW-10M	
UL-compliant NSH5 Cable	RS-422A cable (loose wires)	Length: 10 m	NSH5-422UL-10M	
	RS-232C cable (loose wires + relay cable)	Length: 3 m	NSH5-232UL-3M	CU
	RS-232C cable (loose wires + relay cable)	Length: 10 m	NSH5-232UL-10M	
	PT connection: 9 pins	Length: 2 m	XW2Z-200T	
PT-to-PLC	PLC connection: 9 pins	Length: 5 m	XW2Z-500T	
Connecting Cable *2	PT connection: 9 pins	Length: 2 m	XW2Z-200T-2	
	PLC peripheral port	Length: 5 m	XW2Z-500T-2	
ISH5 Removable Box	RS-232C Cable (connectors)	Length: 3 m	NSH5-232CN-3M	_
Cable	HS-2320 Gable (connectors)	Length: 10 m	NSH5-232CN-10M	
ISH5 Removable Box	-		NSH5-AL001	
NSH5 Wall-mounting Bracket	-	-		
NSH5 Visor	-	NSH5-ATT01		

Use a standard USB cable to connect the NS series PT to a PictBridge-compatible printer. USB cable type depends on the printer.
 \*2. To connect the NS series PT to NJ series Controller, using a commercially available 10/100-BASE-TX twisted-pair cable. For detail, refer to the NS series SETUP MANUAL (Cat. No.V083).

Network

Features

## **Options**

Pro	duct name	Specifications		Model	Standards			
Video Input Unit	S. S. S.	Inputs: 4 channels Signal type: NTSC/PAL		NS-CA001	UC1, CE			
		Input channels: 2 video channels and 1 RGB channel *1 Signal type: NTSC/PAL						
Controlle Unit	er Link Interface	For Controller Link Communications	NS-CLK21	UC1, CE				
RS-422A Adapter		NS-AL002	_					
		CJ1W-CIF11	UC1, N, L, CE					
			NS15	NS15-KBA04				
	Anti-reflection Sheets	NS12/10	NS12-KBA04					
		(5 surface sheets)	NS8	NS7-KBA04				
			NS5	NT30-KBA04				
Sheet/Co	over *2	Protective Covers (5 pack) (anti-reflection coating)	NS12/10	NS12-KBA05				
			NS8	NS7-KBA05				
			NS5	NT31C-KBA05				
		Protective Covers (1 cover included) (Transparent)	NS15	NS15-KBA05N				
		Protective Covers	NS12/10	NS12-KBA05N	_			
		(5 covers included)	NS8	NS7-KBA05N				
		(Transparent) NS5		NT31C-KBA05N				
		NT625C/631/631C Series to NS12/10 Series		NS12-ATT01				
		NT625C/631/631C Series to NS12/NS10 Series (Black)		NS12-ATT01B				
Attachm	ent	NT610C Series to NS12/10 Series		NS12-ATT02				
		NT620S/620C/600S Series to NS8 Series		NS8-ATT01				
		NT600M/600G/610G/612G Series to NS8 Series	NS8-ATT02					
Memory		128 MB		HMC-EF183				
Card		256 MB		HMC-EF283				
		512 MB		HMC-EF583				
Memory	Card Adapter			HMC-AP001	CE			
Replacer	ment Battery	Battery life: 5 years (at 25°C)		CJ1W-BAT01				
Bar Code	e Reader *3	CCD handheld bar code reader (RS-232C interface)		V520-RH21-6				

\*1. One screen cannot display two video inputs simultaneously.
\*2. A Chemical-resistant Cover (NT30-KBA01) is available only for the NS5.
\*3. Bar Code Reader (V520-RH21-6) was discontinued at the end of August 2016.

Design

# **General Specifications**

## NS5/NS8/NS10/NS12/NS15

Series	NS5-V2	NS8-V2	NS10-V2	NS12-V2	NS15-V2						
Rated power supply voltage	24 VDC		1		1						
Allowable voltage range	20.4 to 27.6 VDC (24 VDC	o 27.6 VDC (24 VDC ±15%) ගු									
Power consumption	15 W max.	nax. 25 W max. 45 W max.									
Ambient operating temperature	Note: The ambient opera the mounting angle Mounting angle of • When no Expans • When a Video In operating temper	Imax.       25 W max.       45 W max.       45 W max.         0° C (See note on the next page.)       ************************************									
Storage temperature	–20 to 60 °C *1										
Ambient operating humidity	Humidity 20 to 90%RH (0 to 40 °C) No condensation         Humidity 20 to 90%RH (0 to 50 °C) No condensation         Humidity 20 to 90%RH (0 to 50 °C)           20 to 60%RH (40 to 50 °C)         Continuous operation 240 h         No condensation           20 to 60%RH (40 to 50 °C)         Vertice         No condensation										
Operating environment	No corrosive gases.										
Noise immunity	Conforms to IEC61000-4-	4, 2 kV (power lines).									
Vibration resistance (during operation)	10 to 57 Hz, 0.075 mm an	nplitude, 57 to 150 Hz, 9.8 n	n/s² 30 min each in X, Y, an	d Z directions	5 to 8.4 Hz, 3.5 mm single amplitude, 8.4 to 150 Hz, 9.8 m/s <sup>2</sup> 10 min times each in X, Y, and Z directions	NS-Runtime					
Shock resistance (during operation)	147 m/s <sup>2</sup> 3 times each in o	lirection of X, Y, and Z									
Weight	1.0 kg max.	2.0 kg max.	2.3 kg max.	2.5 kg max.	4.2 kg max.	т					
Degree of protection		5 oil-proof type and NEMA4 ble in locations with long-te			·	Hand-held					
Ground	Ground to 100 $\Omega$ or less.					ld PT					
Battery life	5 years (at 25 °C): Replac	e battery within 5 days after	the battery runs low (indica	ator lights orange).		-					
Applicable standards	Certified for conformance	to UL 508, UL 1604, EMC [	Directive, NK, and LR Stand	lards.							

**\*1.** Operate the PT within the temperature and humidity ranges shown in the right diagram. **\*2.** Support for NS5, NS10, NS12 and NS15.

## NSH5 Hand-held PT

Series	NSF	I5-V2	etwork
Туре	5.7-inch Color TFT	(Hand-held Version)	
Case color	Black		
Built-in Ethernet port	No		
Model	NSH5-SQR10B-V2 (Emergency stop button: Red)	NSH5-SQG10B-V2 (Stop button: Gray)	
Rated power supply voltage	24 VDC		Sys
Allowable voltage range	20.4 to 27.6 VDC (24 VDC ±15%)		tem
Power consumption	10 W max.		Cor
Ambient operating temperature	0 to 40°C		System Configuration
Storage temperature	-20 to 60°C		lion
Ambient operating humidity	35% to 85% (0 to 40°C) with no condensation		0r
Operating environment	No corrosive gases.		deri
Noise immunity	Common mode: 1,000 Vp-p (between power supply terminals and $\mu$ Normal mode: 300 Vp-p Pulse width: 100 ns to 1 $\mu s,$ Rise time: 1-ns pulse	panel)	Ordering Information
Vibration resistance (during operation)	10 to 57 Hz, 0.075 mm amplitude, 57 to 150 Hz, 9.8 m/s $^2$ 30 min ea	ch in X, Y, and Z directions	ation
Shock resistance (during operation)	147 m/s $^2$ 3 times each in direction of X, Y, and Z		Sp
Weight	1.1 kg max.		ecif
Degree of protection	Equivalent to IP65.		icat
Ground	Ground to 100 $\Omega$ or less.		Specifications
Battery life	5 years (at 25°C): Replace battery within 5 days after the battery ru	ns low (indicator lights orange).	
Applicable standards	Certified for conformance to UL 508, EMC Directive, and EN 60204	-1	

Humidity (%RH) 95% 80%

60%

40%

35% 20% 10%

80

Features

Ne

Operation

Temperature (°C)

Sto

30 40 50 60

Temperature (°C)

ade

## **NS** Series

## **Performance/Specifications**

### NS5

Series					NS	5-V2			1	
Model		NS5-SQ10-V2	NS5-SQ11-V2	NS5-SQ10B-V2	NS5-SQ11B-V2	NS5-TQ10-V2	NS5-TQ11-V2	NS5-TQ10B-V2	NS5-TQ11B-V2	
Built-in Ether	net port	No	Yes	No	Yes	No	Yes	No	Yes	
Case color		Ivory Black				Ivory Black				
Display devic	e	TFT color LCD				Color High-lum	inance TFT *1			
Effective disp	olay area	Width 115.2 $\times$ h	eight 86.4 mm (5	5.7 inches)						
Display color	s	256 colors								
Number of do	ots	320 dot horizon	tal $ imes$ 240 dot ver	tical						
View angle		<b>U</b>	op: 80°, Bottom:	60° *5						
Screen data o	apacity	60 Mbytes								
Image data (BMP or JPG	• /	32,768 colors								
Memory Card		Supported								
Ladder Monit		Not supported								
Video Input U		Not supported								
Controller Lir Unit (Wired) s	support	Not supported								
	Service life * 3	75,000 hours m	in.							
Backlight *2	Brightness adjustment	Three-level or 3	2-level brightnes	s adjustment fro	m the touch pane	el screen. * 4				
-	Backlight error detection *5	Error is detected	d automatically, a	and the RUN ind	icator flashes gre	een as notification	n.			
	Method	Matrix resistive	Matrix resistive membrane type							
Touch panel (matrix type)	Number of switches/ resolution	300 (20 horizontal $ imes$ 15 vertical) 16 $ imes$ 16 dots for each switch								
iype)	Input	Pressure-sensitive								
	Service life	1,000,000 touch	operations.							
	Labels	Can be specifie	d in CX-Designe	r. Font, style, an	d size can be spe	ecified.				
Display text	Numerals, alarms, and character strings	Scalable Gothic:         Magnification: 6 to 255 points           Rough:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Standard:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Fine:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Fine:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Fine:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Fine:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8           Fine:         Magnification: 1×1, 1×2, 2×1, 2×2, 3×3, 4×4, 8×8								
	Supported languages (42 languages)	Japanese, simp Finnish, Norweg Bulgarian, Bela	Scalable Gothic, rough, standard, and fine can be used for 42 languages. Japanese, simplified Chinese, traditional Chinese, Korean, English, French, German, Italian, Portuguese, Spain, Swedish, Dutch, Finnish, Norwegian, Basque, Catalan, Danish, Albanian, Croatian, Czech, Hungarian, Polish, Romanian, Slovak, Slovenian, Bulgarian, Belarusian, Russian, Serbian, Macedonian, Ukrainian, Georgian, Icelandic, Afrikaans, Faroese, Indonesian, Greek, Turkish, Estonian, Latvian, Lithuanian, Thai (supported only with scalable Gothic font)							
	Color	256 colors								
Text	Font style (only when vector font is specified)	Bold or italic								
attributes	Vertical alignment	Top, center, or	pottom							
	Horizontal alignment	Left-justified, ce	ntered, or right-ji	ustified						
Flicker	Objects supporting flicker	Functional objects:		up to 10 types of three flicker type		r settings. The fli	cker speed and f	licker range can	be set.	
Numeral units settings	s and scale	1.000 max.								
Alarm/event	settings	5,000 max.								
Expansion in	terface	For Expansion	nterface Units (E	Beginning with ur	its produced in F	eb. 2018, conne	ctors are not mo	unted)		

\*1.NS5-TQ series (high luminance TFT) luminance is better than that of NS5-SQ series by about 110 cd/m<sup>2</sup>.

\*2. Contact your nearest OMRON representative to replace the backlight.

\*3. This is the estimated time before brightness is reduced by half at room temperature and humidity. It is not a guaranteed value. The service life will be dramatically shortened if PT is used at low temperatures. For example, using the PT at temperatures of 0°C will reduce the service life to approximately 10,000 hours (reference value).

\*4. Lot No. 15Z0 or later of NS5 models.

\*5. This function does not indicate that the service life has been reached. It detects when the backlight is not lit due to a disconnection or other errors.

Backlight error detection indicates that all backlights (2) are OFF.

12

### NS8/NS10/NS12/NS15

				3-V2				0-V2				2-V2		_	5-V2
Model		NS8- TV00- V2	NS8- TV01- V2	NS8- TV00B -V2	NS8- TV01B -V2	NS10- TV00- V2	NS10- TV01- V2	NS10- TV00B -V2	NS10- TV01B -V2	NS12- TS00- V2	NS12- TS01- V2	NS12- TS00B -V2	NS12- TS01B -V2	NS15- TX01S- V2	NS15- TX01B- V2
Built-in Ether	net port	No	Yes	No	Yes	No	Yes	No	Yes	No	Yes	No	Yes	Yes	Yes
ase color		lvory		Black		lvory		Black		lvory		Black		Silver	Black
isplay devic	e	High-de	finition TF	T color L	CD	High-de	efinition TI	FT color L	CD	High-de	finition TI	T color L	CD	High-defin color LCD	
ffective disp	olay area	Width 17 (8.4 inch		ight 128.2	2 mm	Width 2 (10.4 in	211.2  imes he iches)	ight 158.4	4 mm	Width 2 (12.1 in		ight 184.5	5 mm	Width 304 228.1 mm (15 inche	
isplay colors	S	256 colo	ors												•
umber of do	ots				ot vertical		_			vertical		$1 \times 600 d$	ot	$1,024 dot \times 768 dot$	vertical
/iew angle		Left/righ Bottom:	t: 80°, To 60° *3	p: 80°,		Left/rigi Bottom	nt: 70°, To : 65° *3	p: 65°,		Left/righ Bottom:	nt: 80°, To 80° *3	p: 80°,		Left/right: 70°, Botto	
Screen data c	capacity	60 Mbyt	es							1					
mage data	imana)	32,768 0	colors												
BMP or JPG Memory Card		Support	ed												
adder Monite		Support													
ideo Input U	Jnit support	Support	ed (Image	e displave	ed via vide	eo input	is 260,000	) colors)						(Only RGE	3 input is
Controller Lin	 hk Interface			. ,				,						enabled.)	
Unit (Wired) s		Not sup	ported			Suppor	ted								
	Service life * 2	50,000 ł	nours min	ì.											
	Brightness adjustment	Three-le	evel or 32	-level brig	htness a	djustmer	nt from the	e touch pa	anel scree	en. * 3					
Backlight *1	Backlight														
	error	Error is	detected	automatio	cally, and	the RUN	l indicato	r flashes g	green as i	notificatio	n.				
	detection *4													Analog res	viotivo
	Method	Matrix re	esistive m	nembrane	type									membrane	
Fouch panel	Number of	768 (32	horizonta	$1 \times 24$ ve	rtical)	1 200 (	40 horizor	$tal \times 30$ v	(ertical)	1 900 (	0 horizor	ntal $ imes$ 38 v	(ertical)	Resolution	: 1,024
matrix type)	switches/ resolution			each swite			dots for e					each swite		(horizonta (vertical)	) × 1,024
	Input	Pressure-sensitive													
-	Service life			operation	s.										
	Labels		•		-		e, and size		specified.						
Display text	Numerals, alarms, and character strings	Rough: Standar Fine: Ma	e Gothic: Magnifica d: Magnif agnificatic ent displa	ation: 1 ication: 1 on: 1	×1, 1×2, 2 ×1, 1×2, 2 ×1, 1×2, 2	2×1, 2×2, 2×1, 2×2 2×1, 2×2,	255 points 3×3, 4×4 , 3×3, 4×4 3×3, 4×4 umerals, d	, 8×8 , 8×8 , 8×8	times						
Display lext		-		-			an be use			3.					
	Supported languages (42 languages)	Japanes Finnish, Bulgaria	se, simplif Norwegia In, Belaru	fied Chine an, Basqu sian, Rus	ese, tradit ue, Catala ssian, Ser	ional Ch an, Danis bian, Ma	inese, Ko sh, Albania cedonian	rean, Eng an, Croati , Ukrainia	lish, Fren an, Czecl In, Georgi	ich, Gern h, Hunga ian, Icela	rian, Polis ndic, Afrik	sh, Romai	nian, Slov	ain, Swedis /ak, Sloven donesian, G	an,
	Color			i, Latvian,	Linuania	an, inai	(supporte	u only wit	III SCAIADI	e Gothic	iont)				
Text	Font style (only when vector font is specified)	256 colors Bold or italic													
attributes	Vertical alignment	Top, cer	nter, or bo	ottom											
	Horizontal	Left-justified, centered, or right-justified													
	alignment	Functional objects: Select from up to 10 types of registered flicker settings. The flicker speed and flicker range can be set. Fixed objects: Select from three flicker types.							et.						
Flicker	Objects supporting			Select											
Numeral units	Objects supporting flicker		ojects:	Select											
lumeral units ettings llarm/event s	Objects supporting flicker s and scale settings	Fixed ot 1.000 m 5,000 m	ojects: ax. ax.												
Flicker Numeral units settings Alarm/event s Expansion int	Objects supporting flicker s and scale settings	Fixed ot 1.000 m 5,000 m	ojects: ax. ax.	Select terface U											
lumeral units ettings Jarm/event s xpansion int 1. Contact y 2. This is the The servic the servic	Objects supporting flicker s and scale settings	Fixed of 1.000 m 5,000 m For Exp MRON re before camatica kimately	ax. ax. ansion In epresent brightn Illy short 10,000	terface U tative to ess is re ened if F hours (re	nits replace educed b 2T is use eference	by half a d at low value).	at room to v tempera	atures. F	or exam	iple, usii	ng the P	T at temp	perature	s of 0 °C v	

\*4. This function does not indicate that the service life has been reached. It detects when the backlight is not lit due to a disconnection or other errors. Backlight error detection indicates that all backlights (2) are OFF.

\*5. An analog touch panel is used with the NS15. Do not press the touch panel in two or more places simultaneously.

If the touch panel is pressed in two or more places simultaneously, it may activate a switch between the points that are pressed.

Specifications

## **Communications**

## NS5/NS8/NS10/NS12/NS15

		Interface	One ATA-Compact Flash interface slot						
Memory Card		Functions	Used to transfer and store screen data, store logging data, and store history data. (Alarm/Event History, Operation Log, and Error Log generated during Macro execution).						
		Connector	Conforms to EIA RS-232C. D-Sub female 9-pin connector 5-V output (250 mA max.) through pin 6. The 5-V outputs of serial ports A and B cannot be used at the same time.						
Serial Communications	Port A	Functions	Host (PLC) access: 1:N NT Links (connections with CS/CJ/CP-series PLCs and C200HX/HG/HE(-Z) PLCs), 1:1 NT Links, or Host Link (connections with C Series or CVM1/CV-series PLCs) Direct access to Temperature Controllers using Smart Active Parts: CompoWay / F and bar code reader connections (Read directly from display.)						
		Connector	Conforms to EIA RS-232C. D-Sub female 9-pin connector. 5-V output (250 mA max.) through pin 6. The 5-V outputs of serial ports A and B cannot be used at the same time.						
	Port B	Functions	Host (PLC) access: 1:N NT Links (connections with CS/CJ/CP-series PLCs and C200HX/HG/HE(-Z) PLCs) or 1:1 NT Links (connections with C Series or CVM1/CV-series PLCs) Direct access to Temperature Controllers using Smart Active Parts: CompoWay / F and bar code reader connections (Read directly from display.)						
		USB rating	USB1.1						
USB			TYPE-B (Slave)						
SLAVE Specifications		Functions	Connection with the CX-Designer (for screen data transfers) Connecting to a PictBridge-compatible Printer Recommended printers: EPSON: PM-G4500, PX-G5300, PX-5600, EP-901F Canon: PIXUS MX7600, PIXUS iP100, PIXUS iX5000						
		USB rating	USB1.1						
USB HOST		Connector	TYPE-A (Host)						
Specifications *1		Functions	Connection with a printer (for hard copies) Recommended printers: EPSON: PX-G930						
Built-in Ethernet Specifications *2		Conformance standards	Conforms to IEEE 802.3/Ethernet (10 Base-T/100 Base-TX).						
Specifications 2		Functions	Host (PLC) access and connection with the CX-Designer (for screen data transfers)						
0		Baud rate	2 M/1 M/500 K bps						
Controller Link (W type) Specifications *3	irea-	Transmission path	Shielded twisted-pair cable (special cable)						
opoolinoutione o		Functions	Host (PLC) access and data links						
		Resolution	NS-CA001: 320×240, 640×480, 800×600 dots NS-CA002: User-defined size						
Video Input Specif *4	ications	Input signal	NS-CA001: NTSC composite video or PAL NS-CA002: NTSC composite video or PAL						
		Number of video inputs	NS-CA001: Number of cameras: 4 max. NS-CA002: 2 cameras + RGB						

## **Connectable Devices**

### Supported OMRON PLCs

	DLO madal nama		RS-232C *1		Eth	nernet		
PLC series	PLC model name	1:1 NT Link	1:N NT Link	Host Link	FINS *2	EtherNet/IP *3	Controller Link *4	
	CQM1	Yes	No	Yes	No	No	No	-
	CQM1H	Yes	Yes	Yes	No	No	Yes	0
	CPM1	Yes	No	Yes	No	No	No	o manage o por service
	CPM1A	Yes	No	No	No	No	No	0
0 0 ·	CPM2A	Yes	No	Yes	No	No	No	5
C Series	CPM2C	Yes	No	Yes	No	No	No	
	C200HS	Yes	No	Yes	No	No	No	
C200H	C200HE (-Z)	Yes	Yes	Yes	No	No	Yes	-
	C200HG (Z)	Yes	Yes	Yes Yes No No	Yes			
	C200HX (-Z)	Yes	Yes	Yes	No	No	Yes	Maintenance
CVM1/CV	CV500/1000/2000	Yes	No	Yes	Yes	No	Yes	nce
Series	CVM1	Yes	No	Yes	Yes	No	Yes	
	CS1H	No	Yes	Yes	Yes	Yes	Yes	
CS Series	CS1G	No	Yes	Yes	Yes	Yes	Yes	
	CS1D	No	Yes	Yes	Yes	Yes	Yes	Ċ
	CJ1H	No	Yes	Yes	Yes	Yes	Yes	
	CJ1G	No	Yes	Yes	Yes	Yes	Yes	
CJ Series	CJ1M	No	Yes	Yes	Yes	Yes	Yes	
	CJ2H	No	Yes	Yes	Yes	Yes *5	Yes	
	CJ2M	No	No Yes	Yes	Yes	Yes *5	Yes	
	CP1H	No	Yes	Yes	Yes	Yes	No	Ģ
0 D 0 ·	CP1L	No	Yes	Yes	Yes	No	No	\$
CP Series	CP1E	No	Yes	Yes	No	No	No	
	CP2E	No	Yes	Yes	Yes	No	No	-
NJ Series	NJ5/NJ3/NJ1	Yes *6	Yes *6	Yes *6	No	Yes *7	No	
NX Series	NX7/NX1/NX1P	No	No	No	No	Yes *8	No	

Note: Including models whose production were discontinued.

\*1. To connect a NS with a PLC via a RS-422A connection, OMRON's NS-AL002, or CJ1W-CIF11 RS-232C/RS-422A Converter can be used to convert the RS-232C port on the NS to RS-422A.

\*2. A NS with Ethernet port is necessary.

When connecting a PLC with the NS, an Ethernet port is necessary on the PLC, too. Use a PLC CPU Unit with a built-in Ethernet port, or add an Ethernet Unit.

**\*3.** A NS with Ethernet port is necessary.

When connecting a PLC with the NS, an EtherNet/IP port is necessary on the PLC, too. Use a PLC CPU Unit with a built-in EtherNet/IP port, or add an EtherNet/IP Unit.

\*4. Install a Controller Link Interface Unit on the NS. A Controller Link Unit is necessary for the PLC.

\*5. For CJ2, CX-Designer version 3.2 or later, and NS system version 8.4 or later are required.

**\*6.** Mount a Serial Communications Unit on the NJ-series Controller. A NS can access only to the Controller's memory used for CJ-series unit. **\*7.** When using a EtherNet/IP Unit to connect the NJ-series Controller, NJ Troubleshooter is not supported.

For NJ5, CX-Designer version 3.3 or later, and NS system version 8.5 or later are required.

For NJ3, CX-Designer version 3.3 or later, and NS system version 8.5 or later are required. For NJ3, CX-Designer version 3.4 or later, and NS system version 8.61 or later are required. Moreover, the multidimensional array is supported in the combination with NJ.

\*8. For NX7, CX-Designer version 3.64 or later, and NS system version 8.9 or later are required. For NX1P, CX-Designer version 3.70 or later, and NS system version 8.93 or later are required. For NX1, CX-Designer version 3.70 or later, and NS system version 8.96 or later are required. Moreover, the multidimensional array is supported in the combination with NX. Features

OMRON

PLC series	PLC model name	Ladder Monitor	Device Monitor/ Switch Box	PLC Data Trace	SPMA	SAP	EtherNet/IP Tag access (Network symbols)	PLC Troubleshooter	NJ Troubleshooter Integrated NS-series PT simulation *4
	CQM1	No	No	No	No	No	No	No	No
	CQM1H	No	No	No	No	No	No	No	No
	CPM1	No	No	No	No	No	No	No	No
	CPM1A	No	No	No	No	No	No	No	No
C series	CPM2A	No	No	No	No	No	No	No	No
	CPM2C	No	No	No	No	No	No	No	No
	C200HS	No	No	No	No	No	No	No	No
	C200HE (-Z)	No	No	No	No	No	No	No	No
	C200HG (-Z)	No	No	No	No	No	No	No	No
	C200HX (-Z)	No	No	No	No	No	No	No	No
CVM1/CV series	CV500/1000/2000	No	No	No	No	No	No	No	No
	CVM1	No	No	No	No	No	No	No	No
	CS1H	Yes	Yes	Yes	Yes	Yes	No	Yes	No
CS series	CS1G	Yes	Yes	Yes	Yes	Yes	No	Yes	No
	CS1D	Yes	Yes	Yes	Yes	Yes	No	Yes	No
	CJ1H	Yes	Yes	Yes	Yes	Yes	No	Yes	No
	CJ1G	Yes	Yes	Yes	Yes	Yes	No	Yes	No
CJ series	CJ1M	Yes	Yes	Yes	Yes	Yes	No	Yes	No
	CJ2H	Yes	Yes	Yes	Yes	Yes	Yes	Yes	No
	CJ2M	Yes	Yes	Yes	Yes	Yes	Yes	Yes	No
	CP1H	Yes	Yes	Yes	Yes *1	Yes	No	No	No
	CP1L	Yes	Yes	Yes	Yes *1	Yes	No	No	No
CP series	CP1E	No	No	No	Yes *1	No	No	No	No
	CP2E	No	No	No	Yes *1	No	No	No	No
NJ series	NJ5/NJ3/NJ1	No	Yes *2	No	No	Yes *3	Yes	No	Yes
NX Series	NX7/NX1/NX1P	No	No	No	No	No	Yes	No	Yes

### **Function Comparison**

Note: Including models whose production were discontinued.

\*1. The SPMA relaying a PLC is not supported.
\*2. Only Device Monitor function is supported. Monitoring function that uses tags (variables) is not supported.
\*3. The SAP for CJ-series Special I/O Units and CPU Bus Units that can be used with NJ-series Controller is supported.

**\*4.** Sysmac Studio version 1.02 or higher (CX-Designer version 3.41 or higher) is required.

Design

### **Connectable Inverters**

S-485 terminal on the Inverter) S-485 connector on the Inverter) S-485 terminal on the Inverter)	RS-485 (2-wire)	1:N
1	RS-485 (2-wire)	1:N
S-485 terminal on the Inverter)		
Controllers		
	eries PT*	
	e Controllers be connected directly to an NS-s	e Controllers be connected directly to an NS-series PT*.

## **Connectable Temperature Controllers**

Unit name	Series	Model	Remarks	
Modular Temperature Controller	EJ1	EJ1-EDU End Unit		·
Modular Temperature Controller	E5ZN	E5ZN-SCT24S Terminal Unit		Ma
Digital Controllor	E5AC	E5AC-000SM-000		Maintenance
Digital Controller	E5EC	E5EC-000SM-000		nano
		E5CNT-FLK Multi-input (Thermocouple/Resistance Thermometer) Type		ce
	E5AN/E5EN/E5CN (Basic Model)	E5CN-DDDL-FLK Analog Input Type		
		E5ENT-FLK Multi-input (Thermocouple/Resistance Thermometer) Type	SAP screens are	NS
		E5EN-DDDL-FLK Analog Input Type	available.	-Rur
Temperature Controller (Digital Controller)		E5ANT-FLK Multi-input (Thermocouple/Resistance Thermometer) Type		NS-Runtime
(g		E5AN-		
	E5AN-H/E5EN-H/	E5CN-H		
	E5CN-H	E5EN-H		
	(Advanced Model)	E5AN-H		fanc
	E5GN	E5GN-DDTC-FLK Thermocouple Input Type		Hand-held
	LOGIN	E5GN-DDP-FLK Resistance Thermometer Input Type		eld PT

Note: Including models whose production were discontinued.

\* The NS-Runtime cannot be connected directly to a Temperature Controller.

Features

Network


Connecting to	Another	Company's	s PLC
---------------	---------	-----------	-------

Manufacturer	Series	CPU	Communication Unit/Adapter/Board	Connection diagram	
	A Series	A1SHCPU A2USCPU A2USHCPU-S1	Computer Link Unit A1SJ71UC24-R A1SJ71UC24-PRF	RS-232C, - RS422A/485 *1	1:1
		A2ACPU	Computer Link Unit AJ71UC24	N34227/403 I	
	FX Series	FX0N FX1S FX1N FX1NC FX2N FX3UC FX3G	Communication special adapter FX3U-232-ADP FX2NC-232ADP FX0N-232-ADP Communication expansion board FXD-232-BD	RS-232C, RS422A/485 *1	1:1
Mitsubishi Electric		Q00CPU Q01CPU	RS-232C port on the CPU Module	RS-232C	1:1
	Q/QnA Series	Q00CPU Q01CPU Q00JCPU Q02CPU Q02HCPU Q06HCPU Q12HCPU Q03UDCPU Q03UDCPU Q06UDHCPU Q13UDHCPU	Serial Communications Module QJ71C24N-R2 QJ71C24N-R4 QJ71C24N	RS-232C, RS-485 (4-wire) *2	1:N
		Q2ASCPU Q2ASCPU-S1 Q2ASHCPU Q2ASHCPU-S1	Serial Communications Module A1SJ71QC24N		
		F3SC23-1F	CPU built-in RS-232C port	RS-232C	
Yokogawa Electric	FA-M3(R) Series	F3SP21-0N F3SP28-3S F3SP58-6S F3SP67-6S	Personal Computer Link Module F3LC11-1F F3LC12-1F F3LC12-2F	RS-232C, RS-422A/485 *1	1:1
Siemens	S7-300 Series	CPU313 CPU315-2DP CPU317-2PN/DP	SIMATIC S7 HMI Adapter 6ES7 972-0CA1□-0XA0	RS-232C	1:1
	SLC500	SLC5/03 SLC5/04 SLC5/05	RS-232C port on the CPU Module	RS-232C	1:1
Rockwell	MicroLogix	MicroLogix 1500	RS-232C port on the CPU Module	RS-232C	1:1
(Allen-Bradley)	ControlLogix	Logix5555	RS-232C port on the CPU Module	RS-232C	1:1
	CompactLogix	1769-L31	RS-232C port on the CPU Module	RS-232C	1:1
	PLC-5	PLC-5/20	RS-232C port or RS-485 port on the CPU Module	RS-232C/RS-485 (4-wire)	1:N

\*1. To connect using RS-422A/485, an RS-232C/422A converter (e.g. NS-AL002, CJ1W-CIF11) is required.
\*2. To connect using RS-485, an RS-232C/422A converter (e.g. NS-AL002, CJ1W-CIF11) is required. Up to 32 sequencers can be connected when using RS-485.

## **Component Names and Options**

## **NS15**



USB HOST (for printer)

\*Bar Code Reader (V520-RH21-6) was discontinued at the end of August 2016.

Hand-held PT


OMRON

Startup/Operation

Maintenance


**NS-Runtime** 

### NS5



\* Bar Code Reader (V520-RH21-6) was discontinued at the end of August 2016.

## NSH5



## **Optional Products**



Video Input Unit NS-CA001 (with Cover)



Communications Cable XW2Z-S002



RGB/Video Input Unit NS-CA002 (with Cover)



Protective Cover/Anti-reflection Sheet for NS-series PT NS-KBA0 (N) NT30/NT31C-KBA05 (N)



Controller Link Interface Unit NS-CLK21 (with Cover)



USB Serial Conversion Cable CS1W-CIF31



RS-422A Adapter CJ1W-CIF11



USB relay cable (IP65 oil-proof type) NS-USBEXT-1M



RS-232C/RS-422A Conversion Unit NS-AL002




OMRON

## **NS** Series


## **Dimensions**





OMRON

### Hand-held NS5



#### NS-CLK21 NS-CA002 NS-CA001 **Controller Link Interface Unit** Video Input Unit Video Input Unit 81.3 | | (102.7) 81.3 (102.7) ₽ 151.5 9.6‡ 21.4 (183) 9.6 যুত্ত 21.4 - 164 · -5 164 -5 (169) (169) 31.5 (1.9) -127.3 (1.9)97 (22.3) -5 164 20.4 120.4 11 • 50.3 + 9.7 - 68.3 --- 86.3 ---(169) 10.6 39.3 (1.9) 10.8 (33.9) - 57.3 -. . - 82.8 --104.3 - 118.3 -95.6

## **Related Manuals**

Cat. No.	Model	Manual
V083	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals SETUP MANUAL
V073	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals PROGRAMMING MANUAL
V099	NS-CXDC1-V3	CX-Designer Ver.3. USER'S MANUAL
V082	NS	NS-Series Ladder Monitor OPERATION MANUAL (Ladder Monitor I/O Comment Extracting Tool)
V086	NS-CA002	NS-Series RGB and Video Input Unit OPERATION MANUAL
V090	NSH5	NSH5-Series Hand-held Programmable Terminal OPERATION MANUAL
V098	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals HOST CONNECTION MANUAL (Host Link) OPERATION MANUAL
V085	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals HOST CONNECTION MANUAL
V092	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals HOST CONNECTION MANUAL Multivendor Connection
V075	NS15/NS12/NS10/NS8/NS5	NS-Series Programmable Terminals Macro Reference
V093	NS-NSRCL	NS-NSRCL NS-Runtime Software USERS MANUAL

### **Read and Understand This Catalog**

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

### Warranty and Limitations of Liability

#### WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

#### LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

### **Application Considerations**

#### SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### **PROGRAMMABLE PRODUCTS**

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

### Disclaimers

### CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

#### DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

#### PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

#### ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

Note: Do not use this document to operate the Unit.

### OMRON Corporation Industrial Automation Company Kyoto, JAPAN Contact: www.ia.omron.com

#### Regional Headquarters OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands

Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ASIA PACIFIC PTE. LTD. No. 438A Alexandra Road # 05-05/08 (Lobby 2), Alexandra Technopark, Singapore 119967 Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON ELECTRONICS LLC 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200 Authorized Distributor:

© OMRON Corporation 2011-2021 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM\_12\_12 Cat. No. V405-E1-20