

Introducing the New Safety Edge - Friendly to Human and Machines





EDGE

SAFETY EDGE & EDGE CONTROLLER

SGE Safety Edge



Introducing the New Safety Edge - Friendly to Human and Machines

The SGE Safety Edge, mounted to moving parts such as doors and fences of mechanical equipment, will stop hazards from moving parts or undergo a complete system shutdown upon detection of contact with persons or objects. Its elastic material and shock absorption properties soften the impact on such persons or objects. The SCC Edge Controller conforms to PLd/Safety Category 3. Occurrance of any short-circuits and/or breaks are continually monitored and the status shown with LED indicators.

A P P L I C A T I O N Protecting people in such areas like:

Shutter Door

The Safety Edge mounted to the end of a shutter door stops the downside movement of the shutter to prevent shearing of a person or object when it detects a contacts with them.








Protective Door of a Processing Machine

The Safety Edge, mounted to the moving part of a protective door, will stop door movement to prevent jamming of persons or objects upon detection of contact with them.

Reciprocating Table of a Machine Tool

The Safety Edge, mounted to the moving part of a recipro- cating table, will stop the table's movement to prevent collision with the moving part or jamming between the moving part and structures such as walls or poles upon detection of contact with workers.




Note: For details, refer to "Model Number Structure" on page 4 or later.





- Dedicated SCC Edge Controller enables establishment of a safety system conforming to PLd/Safety Category 3 (when hazards are directly blocked by built-in relays)
- Any short-circuits or breaks in the system are monitored and its status is indicated with LED.
- Authentificated under major safety standards

TUV NORD CE



Note: For details on LED indicators, refer to "Connection" on page 13.

Safety Edge/Edge Controller

Safety sensors to detect contacts by mounting to moving parts of hazards

 Conforms to PLd/Safety Category 3 in combination with the dedicated controller.
 (applied when internal relays with forcibly guided contacts)

disable hazard source directly)

- Simple one-unit structure integrating sensor and cover.
- Resistant to the side force.
- Certified standard: EN ISO 13856-2 (Safety Edge Standard)

Be sure to read the *"Safety Precautions"* on page 19.

Model Number Structure



Safety Edge

| SGE - | |) - 🗆 - | | |
|-------------------------|-------------------------------|-------------------------------------|-------------------------|-----------------------|
| 1 Code (3 digits) | | 2 Config. No. Wiring | 3 Code (4 digits) | 4 Code (None/L) |
| I | Cross-sectional dimensions | Configuration/ Cable Termination | Sensor Length | 1 |
| | | Model | | |

1. Type

| Code | Cross-section dimensions (including standard mounting base) | | | |
|---------------|--|--|--|--|
| 125 | 15 mm × 34 mm | | | |
| 225 | 25 mm × 39 mm | | | |
| 245 | 25 mm × 60 mm | | | |
| 245L * | 25 mm × 74 mm (including sealing cover) | | | |
| 365 * | 35 mm × 80 mm | | | |

Note: 1. For dimensions including L-shaped base, refer to "Dimensions/Terminal Arrangement" on page 14.

 Models with sealing cover to reduce liquid splash to the inside and outside of the door are available (SGE-245L). These models can be used in applications where sensors are installed on moving doors of machines.

2. Wiring Configuration and Cable Termination

| Configuration No. | Specification | Terminal code | | |
|-------------------|---|------------------|------|--|
| 0 | 2-wire cable on both sides | С | С | |
| 2 | 2-wire cable on one side, terminating resistor on the other side | С | None | |
| 3 * | Connector cable on one side (male), connector cable on the other side (female) | М | F | |
| 4 * | Connector cable on one side (male), terminating resistor on the other side | М | None | |
| 5 * | 2-wire cable on one side, connector cable on the other side (female) | С | F | |

3. Sensor Length

| Number | Specification | | | | |
|----------------|---|--|--|--|--|
| 4-digit number | 0150 to 6,100 mm (in increments of 50 mm) | | | | |


4. Mounting Base

| Code | Specification | | | | | | |
|--------------------|---|--|--|--|--|--|--|
| None | Standard Mounting Base | | | | | | |
| L* | L-shaped Mounting Base | | | | | | |
| Note: Only the Sta | Note: Only the Standard Mounting Base is available for the SGE-125. | | | | | | |

When specifying a type that includes the ***** symbol, we accept orders for a minimum of 10 pcs. Please contact your OMRON representative.



CE



Specification

5 and 6. Cable Length and Terminal Treatment • Cable Length

For the cable length at each end of the safety edge, three types are available: 1 m, 5 m and 10 m.

Code length is indicated by five digits.

| Cable | 5 | | | 6 | |
|--------|----------------------------|---------------|---|----------------------------|------------------|
| Length | Cable Length (5 digits) | Terminal code | | Cable Length (5 digits) | Terminal code |
| 1 m | 01000 | С | - | 01000 | C, None |
| 5 m | 05000 | С | - | 05000 | C, None |
| 10 m | 10000 | С | - | 10000 | C, None |

Note: 1. Left and right have the same cable length.

2. When a terminating resistor is used, the cable length on the 6 side is not specified.

3. For other lengths, contact your OMRON representative.

Cable Termination

| Cable Termination |
|--------------------------|
| 2-wire cable |
| Connector cable (male) |
| Connector cable (female) |
| |

Note: For internal terminal registor side, there is no cable. Cable length is not specified.

7. Direction of Cable Connection

| Code | Direction of Cable Connection | | | | | | | |
|-------------|-------------------------------|-----------------------------|--|--|--|--|--|--|
| Coue | SGE-125 | Other models | | | | | | |
| | Right (standard) | Bottom (standard) | | | | | | |
| None | 5 | 6 | | | | | | |
| latas Canto | a COF 405 the sight disest | an in standard, and fan sti | | | | | | |

Note: For type SGE-125, the right direction is standard, and for other models the bottom direction is standard. For a cable pull-out direction other than the standard direction,

For a cable pull-out direction other than the standard direction, please contact your OMRON representative.

Ordering Information

safety edge

Choose the sensor length.

* When specifying a type other than one in the following table, we accept orders for a minimum of 10 pcs.

Determine the length of a safety edge.

Choose any length from 0150 mm* to 6100 mm with increments of 50 mm.

* When the length is less than 1,000 mm, zero "0" is added on the top of the number to make it four digits.

Note: 1. The user cannot cut the safety edge.

2. For other lengths, contact your OMRON representative.

| | Mate | Actuation | Cross- sectional area * 2 | Wiring Configuration/ Cable Termination | Cable Length | Model | | | | | | | | | | | | | | | | | | |
|-----------------|--------|----------------|---|---|-----------------|-------|---------|---|------|---------------------------|-------------|-----------------------|--------|---|---|-----|---|--------|-----|--|--|--------|--|--|
| Appearance rial | | distance *1 | 1 | 2 | 5, 6 | | se d | 1 cross- ctiona limen sions | I C | 2 Wiri Conf rati | ing figu | 3 Sensor Length | 4 | 5 Cable Length/ Terminal code | 6 Cable Length/ Terminal code | 7 | | | | | | | | |
| | | | | 2-wire cable on | 1 m | SGE | - | 125 | - | C |) - | | | 01000C | - 01000C | | | | | | | | | |
| | | | | both sides | 5 m | SGE | - | 125 | - | C |) - | | | 05000C | - 05000C | | | | | | | | | |
| | TPE | 2.6 mm | 15 	imes 34 | | 10 m | SGE | - | 125 | - | C |) - | | | 10000C | - 10000C | | | | | | | | | |
| | | 2.0 | one side terminat | 2-wire cable on | 1 m | SGE | - | 125 | - | 2 | 2 - | | | 01000C | | | | | | | | | | |
| | | | | terminating resistor | 5 m | SGE | - | 125 | - | 2 | 2 - | | | 05000C | | | | | | | | | | |
| | | | | on the other side | 10 m | SGE | - | 125 | - | 2 | 2 - | | | 10000C | | | | | | | | | | |
| | | | | | 1 m | SGE | - | 225 | - | C |) - | | | 01000C | - 01000C | | | | | | | | | |
| | | | | 2-wire cable on both sides | 5 m | SGE | - | 225 | - | С |) - | | | 05000C | - 05000C | | | | | | | | | |
| | | 3.9 mm | 25 	imes 39 | | 10 m | SGE | - | 225 | - | C |) - | | | 10000C | - 10000C | | | | | | | | | |
| | | 5.9 mm | (mm) | | 1 m | SGE | - | 225 | - | 2 | 2 - | | | 01000C | | | | | | | | | | |
| | | | | one side, terminating resistor | 5 m | SGE | - | 225 | - | 2 | 2 - | | | 05000C | | | | | | | | | | |
| | | | | | | | | on the other side | 10 m | SGE | - | 225 | - | 2 | 2 - | | | 10000C | | | | | | |
| | EPDM | | | | 1 m | SGE | - | 245 | - | C |) - | | | 01000C | - 01000C | | | | | | | | | |
| • | | | | 2-wire cable on both sides | 5 m | SGE | - | 245 | - | C |) - | | | 05000C | - 05000C | | | | | | | | | |
| 7.4 | 7.4 mm | 25 × 60 | | 10 m | SGE | - | 245 | - | C |) - | | | 10000C | - 10000C | | | | | | | | | | |
| | | 7.4 mm (mm) | 7.4 mm (n | (mm) | 2-wire cable on | 1 m | SGE | - | 245 | - | 2 | 2 - | | | 01000C | | | | | | | | | |
| \square | | | | one side, terminating resistor | 5 m | SGE | - | 245 | - | 2 | 2 - | | | 05000C | | | | | | | | | | |
| | | | | | | | | | | | | on the other side | 10 m | SGE | - | 245 | - | 2 | 2 - | | | 10000C | | |

*1. Values of actuation distance and actuation force are characteristic values tested according to EN ISO 13856-2 using a test object of φ80 mm and actuating point C3 under a test temperature of 20°C and test speed v = 10 mm/s. Refer to "*Characteristics*" on page 11 for details.
 *2. Includes the standard mounting base.

Note: 1. The SGE-225 can be used for finger protection. The actuation force is 20 N when the SGE-225 is used for finger protection.

(Characteristic values tested according to EN ISO 13856-2 using a test object of φ 20 mm and actuating point C3 under a test temperature of 20°C and test speed v = 10 mm/s)

- 2. For the differences in characteristics, refer to "Specifications" on page 8.
- 3. A base with more than 1.2 m is cut and split before delivery as shown below.

| Sensor length = LEN (mm) | Mounting base cut length (mm) | No. of split bases |
|--------------------------|-------------------------------|--------------------|
| 0150 to 1200 | LEN | 1 |
| 1210 to 2400 | 1/2 LEN | 2 |
| 2410 to 3600 | 1/3 LEN | 3 |
| 3610 to 4800 | 1/4 LEN | 4 |
| 4810 to 6000 | 1/5 LEN | 5 |
| 6010 to 6100 | 1/6 LEN | 6 |

(Example) When the sensor length LEN is 2,700 mm, three 900 mm mounting bases will be provided.

Edge Controller

| Product | Appearance | Safety output | Auxiliary output | Rated voltage | Terminal block type | Model |
|----------------------------------|------------|---------------|------------------|----------------------------|---------------------|-----------|
| Safety Mat/ Edge Controller * | | SPDT-NO | SPST-NO | 120 VAC or 24 VAC/DC | Screw terminals | SCC-1224A |

*Can also be connected with UMA-series Safety Mats.

Refer to the SCC-1224A Safety Mat/Edge Controller User Manual (Cat. No. Z394) for details.

Wiring Configuration and Configuration Example

Cable Wiring Configuration

Determine a wiring configuration according to the number of safety edges (sensor) in series.

Up to 5 safety edges can be connected in series.

There are five types of cable termination for both ends of the safety edge. The method can be selected from the combinations of 2-wire cable, cable with M8 connector (male or female), and terminating resistor as shown below.

* For connector cable types with configuration Nos. 3, 4, and 5, we accept orders for a minimum of 10 pcs.

| Configuration No. | Outline drawing | Wiring configuration and cable termination |
|-------------------|---|--|
| 0 | 2-wire cable 2-wire cable Safety edge | 2-wire cable on both sides |
| 2 | 2-wire cable Safety edge Terminating resistor | 2-wire cable on one side, terminating resistor on the other side (8.2k Ω 0.25W) |
| 3 * | Connector cable (male) Connector cable (female) | Connector cable on one side (male), connector cable on the other side (female) |
| 4 * | Connector cable (male) | Connector cable on one side (male), terminating resistor on the other side (8.2kΩ 0.25W) * |
| 5 * | 2-wire cable Connector cable (female) Safety edge | 2-wire cable on one side, connector cable on the other side (female) |

Note: 1. To connect safety edges in series, two types of methods are available: Using a 2-wire cable or M8 connector.

2. To connect with an edge controller, a 2-wire cable should be used. There is no polarity.

3. When using one safety edge, use Configuration No. 2.


When connecting safety edges in series, use Configuration No. 2 or Configuration No. 4 with a built-in terminating resistor for the last series-connected safety edge.

See the configuration example below for more information.

Configuration Example Example of configuration 2-wire cable connection Using one safety edge (Configuration No. 2 × 1)




Using two safety edges Connecting using 2-wire cables (Config. No. 0 × 1) + (Config. No. 2 × 1)



Using N safety edges (Up to 5 units connected in series) Connecting using 2-wire cables


(Config. No. 0 × (N - 1)) + (Config. No. 2 × 1)



Connecting using connectors


Using two safety edges

(Config. No. 5×1) + (Config. No. 4×1)



SCC Edge Controller

Using N safety edges (Up to 5 units connected in series) (Config. No. 5×1) + (Config. No. $3 \times (N - 2)$) + (Config. No. 4×1)



* For the L-shaped mounting type, we accept orders for a minimum of 10 pcs.

Specifications

Edge Controller SCC-1224A Power Input

| Power supply voltage* | 120 VAC 50/60Hz (Terminals A1 and A2) 24 VAC 50/60Hz or 24 VDC (Terminals B1 and B2) |
|--|--|
| Operating voltage range | -10% to +10% of rated power supply voltage |
| Power consumption (with sensors connected) | 120 VAC: 3.8 VA max. 50 Hz, 3.5 VA max. 60 Hz 24 VAC: 1.2 VA max., 24 VDC: 1.5 W max. |

* Select either Terminals A1 and A2 or Terminals B1 and B2 according to the power supply voltage applied. Never apply both voltages simultaneously.

Inputs

| Sensor input SGE Safety Edge: A maximum of 5 edges can be connected in series. Maximum wiring length: 25 m max. | |
|--|--|
|--|--|

Contacts

| Safety output | 230 VAC 3 A, 24 VDC 3 A (resistive load) 230 VAC 1 A (AC-15), 24 VDC 2 A (DC-13) (inductive load) |
|------------------|--|
| Auxiliary output | 24 VAC/DC 2A (resistive load) |

Characteristics

| Startup time *1 | | 300 ms max. | | | | |
|----------------------------|--------------------------|---|--|--|--|--|
| Operating time (Ope | en to closed) * 2 | 550 ms max. | | | | |
| Response time (Clo | sed to open) *3 | 13 ms max. | | | | |
| Vibration resistance | 9 | Malfunction: 10 to 55 Hz, Sinus, 0.15 mm amplitude, 10 cycles | | | | |
| Shock resistance | | Malfunction: 147 m/s ² | | | | |
| | Mechanical | 1,000,000 cycles min. | | | | |
| Durability Electrical | | AC-15: 800,000 cycles min. (230 VAC, 1A) DC-13: 250,000 cycles min. (24 VDC, 2A) | | | | |
| Ambient operating | temperature | -20 to 55°C (-4 to 131°F) (with no icing or condensation) | | | | |
| Ambient operating humidity | | 0% to 90% | | | | |
| Degree of protection | | IP20 | | | | |
| Material (Housing) | | Polyamide PA6.6, self-extinguishing according to UL 94-V2 | | | | |
| Protection type | | Class II (protective insulation) | | | | |
| Pollution degree | | 2 | | | | |
| Overvoltage catego | ry (IEC/EN 60664-1) | ≡ | | | | |
| Rated insulation vo | Itage | 250 V | | | | |
| Rated impulse volta | age resistance | 4 kV | | | | |
| Dielectric strength | | 1.5 kVAC | | | | |
| Terminal tightening | torque | 0.5 to 0.6 N• m | | | | |
| Weight | | approx. 210 g (7.4 oz) | | | | |
| | Conforming to Standards | EN ISO 13856-2, EN ISO 13849-1: 2015, EN 61000-6-2, EN 61000-6-3, ANSI/UL 508, CSA C22.2 No.14 | | | | |
| Conformity PFHd | | 6.5×10 ⁻⁹ (Nop 17,520) | | | | |
| MTTFd | | 195 years | | | | |
| | DC | 99% (Nop 17,520) | | | | |

*1. The startup time is the delay time from power-on to when the SCC-1224A Safety Mat/Edge Controller is ready to operate.
*2. The operating time is the time it takes for the safety output contacts to be closed after the sensor is deactivated and the manual reset input contacts are closed. The contact bounce time is not included.
*3. The response time is the time it takes for the safety output contacts to open after the sensor is activated. Contact bounce time is included.


Safety Edge

| Model Item | SGE-125 | SGE-225 *5 | SGE-245 SGE-245L | SGE-365 | | | | | |
|--|--|--|---|-----------|--|--|--|--|--|
| Material *1 | TPE | EPDM | | | | | | | |
| Material hardness | 65 Shore A | 68 Shore A | | | | | | | |
| Max. length of a single safety edge | 6.1 m | | | | | | | | |
| Actuation distance *2 | 2.6 mm | 3.9 mm | 7.4 mm | 5.2 mm | | | | | |
| Actuation force *2 | 42 N | 57 N | 68 N | 78 N | | | | | |
| Maximum allowable load | 500N | | | | | | | | |
| Overtravel distance *2 (400 N) | 9.5 mm | 6.7 mm | 18.3 mm | 33.8 mm | | | | | |
| Maximum operation angle | 2 x 30° 2 x 45° | | | | | | | | |
| Inactive end region *3 | 20 mm | 40 mm | 20 mm | | | | | | |
| Connecting cable | 2 conductors, 0.34 mm ² , Al Cable Specifications Type External diameter Number of conductors Cross-section of conduct Insulator diameter | Iowable bending radius: R3 : PUR (Polyurethane) Ro : 3.5 dia. : 2 conductors to : 0.34 mm ² : 1.2 dia. | | | | | | | |
| Mechanical durability | 10,000 operations min. | | | | | | | | |
| Ambient temperature | During operation: -10 to 55° | C (with no icing), During stora | ge: -25 to 75°C (with no icing) |) | | | | | |
| Operating ambient humidity | 0 to 90%RH | | | | | | | | |
| Degree of protection | IP65 | | | | | | | | |
| Unit weight *4 | 0.18 kg/m | 0.51 kg/m | 0.77 kg/m (SGE-245) 0.82 kg/m (SGE-245L) | 1.10 kg/m | | | | | |

*1. TPE: Thermoplastic Elastomer

EPDM: Ethylene Propylene Rubber

*2. Values of actuation distance and actuation force are characteristic values tested according to EN ISO 13856-2 using a test object of φ80 mm and actuating point C3 under a test temperature of 20°C and test speed v = 10 mm/s. Refer to "Characteristics" on page 11 for details. ***3.** There is an inactive region (including an end cap) in both ends of the safety edge.





*4. Values are for the unit weight of TPE or EPDM devices. The weight does not include the aluminum base, cables, or connectors.

*5. The SGE-225 can be used for finger protection. The actuation force is 20 N when the SGE-225 is used for finger protection. (Characteristic values tested according to EN ISO 13856-2 using a test object of φ20 mm and actuating point C3 under a test temperature of 20°C and test speed v = 10 mm/s)

Mechanical Force

| Material | | | TF | ΡE | | | EPDM | | | | | | |
|---|---|-----------------------------------|----|----|---|---|------|---|---|---|---|---|--|
| Model | | SGE-125 SGE-225, SGE-245, SGE-365 | | | | | | , | | | | | |
| Features Strength * | 1 | 2 | 3 | 4 | 5 | 6 | 1 | 2 | 3 | 4 | 5 | 6 | |
| Tear Strength (Resistance) | | | 3 | | | | | | 3 | | | | |
| Ultimate Tensile Strength | | | 3 | | | | | | 3 | | | | |
| Rebound Elasticity at 20°C | | 2 | | | | | | 2 | | | | | |
| Resistance Against Permanent Deformation | | | 3 | 4 | | | | 2 | | | | | |
| Abrasion | | | 3 | | | | | | 3 | | | | |
| Elongation at Tear | | | | 4 | 5 | | | | 3 | | | | |
| Cold Flexibility | | 2 | | | | | | 2 | | | | | |

Note: 1 = Excellent 2 = Very good 3 = Good

4 = Fair 5 = Poor

6 = Very poor

Environmental Resistance

| Material | TPE | | | | | EPDM | | | | | | |
|-----------------------------|-----|---|---|---|------------------------------|------|---|---|---|---|---|---|
| Model | | | | | SGE-225, SGE-245, SGE-365 | | | | | | | |
| Features Tolerance * | 1 | 2 | 3 | 4 | 5 | 6 | 1 | 2 | 3 | 4 | 5 | 6 |
| Heat Stability | | | | 4 | | | | 2 | | | | |
| Oxidation Stability | 1 | | | | | | 1 | | | | | |
| UV Stability | 1 | | | | | | 1 | | | | | |
| Weather/Ozone Resistance | 1 | | | | | | 1 | | | | | |
| Flame Resistance | | | | | | 6 | | | | | | 6 |
| Gas Permeability | | | 3 | | | | | | | 4 | | |

Note: 1 = Excellent

2 = Very good 3 = Good 4 = Fair 5 = Poor

6 = Very poor

Chemical Resistance

| Material | | TPE | | | | | | | EP | DM | | |
|--|---|-----|---|---|------------------------------|---|---|---|----|----|---|---|
| Model | | | | | SGE-225, SGE-245, SGE-365 | | | | , | | | |
| Features Effects * | 1 | 2 | 3 | 4 | 5 | 6 | 1 | 2 | 3 | 4 | 5 | 6 |
| Water Resistance | 1 | | | | | | 1 | 2 | | | | |
| Diluted Acids | 1 | | | | | | | 2 | | | | |
| Diluted Bases | 1 | | | | | | | 2 | | | | |
| Non-Oxidizing Acids | | 2 | | | | | | 2 | | | | |
| Oxidizing Acids | | 2 | | | | | | | | 4 | | |
| ASTM Oil #3 | | 2 | | | | | | | | | | 6 |
| Vegetable Oils | 1 | 2 | | | | | | | | | 5 | |
| Organic Solvents | | | | | | | | 2 | | | | |
| Ester Solvents | | 2 | 3 | | | | | 2 | | | | |
| Ketone Solvents (Containing Oxygen) | | 2 | 3 | | | | | | 3 | | | |
| Aliphatic Hydrocarbons Solvents (Gasoline) | | | | | | | | | | | 5 | |
| Aromatic Hydrocarbons | | | | | | | | | | | | 6 |
| Hydrocarbons | | 2 | 3 | | | | | | | | 5 | 6 |
| Alcohol | 1 | | | | | | 1 | | | | | |

Note: 1 = No Effects, Permanent Contact

2 = Few Effects, Some Contact


2 = Pew Effects, Some Contact
3 = Medium Effects, Some Contact
4 = Noticeable Effects, Reduced Contact
5 = Severe Effects, Very Brief Contact

6 = Extreme Effects, Avoid Contact

Characteristics

Force Distance

SGE-225: Characteristic Values for Test Speed v = 10 mm/s) Test Temperature +20°C



SGE-125: Characteristic Values for Test Speed v = 10 mm/s

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 42 |
| Actuating Distance SB (mm) | 2.6 |
| Overtravel Distance Sv at 250N in mm | 8.1 |
| Overtravel Distance Sv at 400N in mm | 9.5 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

SGE-225: Characteristic Values for Test Speed v = 10 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 57 |
| Actuating Distance SB (mm) | 3.9 |
| Overtravel Distance Sv at 250N in mm | 2.3 |
| Overtravel Distance Sv at 400N in mm | 6.7 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

SGE-245: Characteristic Values for Test Speed v = 10 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 68 |
| Actuating Distance SB (mm) | 7.4 |
| Overtravel Distance Sv at 250N in mm | 15.8 |
| Overtravel Distance Sv at 400N in mm | 18.3 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

SGE-365: Characteristic Values for Test Speed v = 10 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 78 |
| Actuating Distance SB (mm) | 5.2 |
| Overtravel Distance Sv at 250N in mm | 29.8 |
| Overtravel Distance Sv at 400N in mm | 33.8 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

| Explanation of Terms | | |
|----------------------|---|--|
| Actuating Force | : Operating force required for turning safety | |
| | output from ON to OFF | |
| Actuating Distance | : Pressing distance required for turning | |
| | safety output from ON to OFF | |
| Overtravel Distance | : Allowable excess pushing distance after reversal of safety output (ON to OFF) | |
| | | |

SGE-125: Characteristic Values for Test Speed v = 100 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 43 |
| Actuating Distance SB (mm) | 6.4 |
| Overtravel Distance Sv at 250N in mm | 7.7 |
| Overtravel Distance Sv at 400N in mm | 8.6 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

SGE-225: Characteristic Values for Test Speed v = 100 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 63 |
| Actuating Distance SB (mm) | 4.4 |
| Overtravel Distance Sv at 250N in mm | 2.7 |
| Overtravel Distance Sv at 400N in mm | 7.2 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

SGE-245: Characteristic Values for Test Speed v = 100 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 83 |
| Actuating Distance SB (mm) | 7.8 |
| Overtravel Distance Sv at 250N in mm | 15.2 |
| Overtravel Distance Sv at 400N in mm | 17.7 |

Note: Tested according to EN ISO 13856-2, test object of φ 80mm, actuating point C3.

SGE-365: Characteristic Values for Test Speed v = 100 mm/s)

| Test Temperature | +20°C |
|---|-------|
| Actuating Force FA (N) | 107 |
| Actuating Distance SB (mm) | 6.2 |
| Overtravel Distance Sv at 250N in mm | 28.3 |
| Overtravel Distance Sv at 400N in mm | 32.7 |

Note: Tested according to EN ISO 13856-2, test object of φ80mm, actuating point C3.

Installation


Safety edges must only be installed by authorized persons.

 To facilitate installation of the safety edge, the mounting base may only be attached to even surfaces. If the safety edge is mounted in a bend, the radius must not be less than the specified minimum.




2. The mounting base must be fitted with countersunk screws or rivets. A diameter of 4 mm is sufficient. The holes of 4.5 mm must be evenly distributed over the entire length of the mounting base with distances between them not exceeding 300 mm. They have to be countersunk according to the screw size.

For SGE-225/245 (L-shaped) For SGE-365 (L-shaped)



When using SGE-125, drill a pilot hole to the groove such that the head of a countersunk screw can go through (approx. 8 mm).


For SGE-125



3. Pan- or round-head screws should not be used. Otherwise the connecting wire in the mounting base could be damaged.




 In order to lead the connecting wire through the mounting base, an 8 mm hole has to be drilled in the appropriate place. Carefully remove the burr from both sides.




5. The connecting wire and the cable end with the terminal resistor have to be placed in the mounting base.


6. In order to make fitting the safety edge easier, the mounting base and the safety edge should be sprayed with soapy water. Once the soap suds have evaporated, the safety edge is firmly fitted in the aluminum base. To prevent a subsequent slipping of the safety edge, talcum powder, oils or similarly durable lubricants must not be used.



7. Safety edges with a C-base (SGE-365) have to be clipped with one side into the mounting base. Then press in the complete c-base. Pulling or pushing the safety edge into the mounting base can cause damage to the safety edge and should be avoided at all costs.



8. Safety edges with T-bases (SGE-125/-225/-245/-245L) have to be inserted from the side along the groove of the mounting base.




Any other methods of fastenings are only permitted on prior agreement with the manufacturer.


Connections

SCC-1224A

Internal Connection Diagram



Wiring of Inputs and Outputs



Terminals


| Signal | Terminal | Overview | Wiring |
|--------------------------|----------|---|--|
| Supply Voltage 120 VAC | A1, A2 | Input terminals of 120 VAC supply voltage. | Do not connect a supply voltage of 24 VAC or 24 VDC. |
| Supply Voltage 24 VAC/DC | B1, B2 | Input terminals of 24 VAC or 24 VDC supply voltage. | Do not connect a supply voltage of 120 VAC. When using 24 VDC, connect 24 VDC line to B1 and 0 VDC line to B2. |
| Connection Sensor | X1, X2 | Input terminals of sensor signal. | Connect signal lines of SGE Safety Edge. |
| Connection Sensor | X3, X4 | - Input terminais of sensor signal. | Do not connect any lines. |
| Manual Reset | Z1, Z2 | Input terminals of a reset switch (NO contact). Also used as external device monitoring (EDM) terminals of contactors. | Do not connect any lines when in the automatic reset mode. Connect NC contacts of contactors when using the external device monitoring (EDM) function. |
| Safety Output 1 | 13-14 | Closed or open according to sensor and manual reset | Do not connect any lines when not used. |
| Safety Output 2 | 23-24 | inputs. | Remove the factory-installed jumper between terminals 14 and 23 if safety outputs 1 and 2 are not connected in series. |
| Auxiliary Output | 31-32 | In the auxiliary output without delay mode, the auxiliary output is closed without delay when the safety outputs are open. In the auxiliary output delayed mode, the auxiliary output is closed with a delay of 0.5 s after the safety outputs are open, and remains closed for 3 s. | Do not connect any lines when not used. Do not use this as safety output. |

LEDs

| Label | Color | Name | Status | Description |
|-------------|----------------------|----------------------|---------------------------------|--|
| Power | Green | Power LED | ON | Operating state |
| Fower | Green | FowerLED | Flashing | Fault alarm |
| | | Red Sensor Input LED | ON | Sensor activated (Safety output OFF) |
| CH1 | Ded | | Fast flashing (approx. 4 Hz) | Sensor faulty |
| СПІ | Red | | Slow flashing (approx. 1 Hz) | Waiting for reset switch input (Safety output OFF) |
| | | | OFF | Released from interlocked state (Safety output ON) |
| AUX1 Yellow | Auxiliary output LED | ON | Auxiliary output contact closed | |
| | | OFF | Auxiliary output contact open | |

Dimensions/Terminal Arrangement

Edge Controller




Safety Edge


SGE-125




SGE-225










Mounting Bases

For SGE-125








Application Examples

| Highest achievable PL/ safety category | Model | Stop category | Reset |
|---|--|---------------|--------|
| PLd/3 equivalent | Safety Edge SGE series Safety Mat/Edge Controller SCC-1224A | 0 | Manual |

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.


Application Overview

- The power supply to the motor M is turned OFF when a safety edge is activated.
- The power supply to the motor M is kept OFF until the reset switch S1 is pressed after the safety edge is deactivated.



S1: Reset switch KM1, KM2: Magnetic contactor M: Motor

Timing Chart




| Highest achievable PL/ safety category | Model | Stop category | Reset |
|---|--|---------------|-------|
| PLd/3 equivalent | Safety Edge SGE series Safety Mat/Edge Controller SCC-1224A Safety Relay Unit G9SA-301 | 0 | Auto |

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when a safety edge is activated.
- The power supply to the motor M is kept OFF until the safety edge is deactivated.
 - Automatic reset (DIP Switch1: ON)
 - Auxiliary output without delay mode

(DIP Switch 2: ON)




| Highest achievable PL/ safety category | Model | Stop category | Reset |
|---|--|---------------|--------|
| PLd/3 equivalent | Safety Edge SGE series Safety Mat/Edge Controller SCC-1224A | 0 | Manual |

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.


Application Overview

- A slide door installed with the safety edge is operated.
- The power supply to the motor M is turned OFF when a safety edge is activated.
- The power supply to the motor M is kept OFF until the reset switch S1 is pressed after the safety edge is deactivated.



S1:Reset switchKM1, KM2:Magnetic contactorM:Motor

Timing Chart



Safety Precautions

Safety Category

The SGE-series Safety Edge is certified for PLd and Safety Category 3 when used with an SCC-1224A Safety Mat/Edge Controller or a G9SP-series Safety Controller.

To implement a Safety Category 3 and PLd safety circuit with an external safety relay or magnet contactor connected, a safety controller is required separately when using the Safety Edge with an SCC-1224A Safety Mat/Edge Controller which is selected automatic reset mode.

Standards

SGE + SCC-1224A EN ISO 13856-2 EN ISO 13849-1 PLd/Safety Category 3 SGE + G9SP-EN ISO13849-1 PLd/Safety Category 3

Do not use this document to operate the Unit.

For precautions for correct use and other information, refer to your local Omron website and the SCC-1224A Safety Mat/Edge Controller User Manual (Cat. No. Z394).

Related Manuals

| Man. No. | Model | Manual name |
|----------|-----------|--|
| Z394 | SCC-1224A | SCC-1224A Safety Mat/Edge Controller User Manual |

For details of the SGE-series Safety Edge, refer to your local Omron website.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-2711 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2220 Fax: (86) 21-5037-2200 Authorized Distributor:

©OMRON Corporation 2019-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_9_3 Cat. No. F088-E1-09 1222 (1109)