

## Catalog Correction Notice

Issue Date  
November 1, 2018

No. 2018003DE

Catalog

The mistake of the print and the description is found in the catalog that our company issued. We apologize.

### [ Name of catalog ]

" Vision System FH series CATALOG " < Publication in August, 2018 > < Catalog number Q197-E1-09 >

### [ Page of publishing ]

Page 30 " Maximum Extension Length Using Cable Extension Units FZ-VSJ "

### [ Correction method ]

The catalog is revised.

### [ Content of correction ]

	Item	Model	Transmission speed (*1)	No. of CH used for connection (*2)	Maximum cable length using 1 Camera Cable (*1)	Max. number of connectable Extension Units	Using Cable Extension Units FZ-VSJ	
							Max. cable length	Connection configuration
Before	Digital CMOS Cameras	FH-SM21R/SC21R	Standard	1	15 m (Using FZ-VS4/VSL4)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
				2	15 m (Using FZ-VS4/VSL4)	4 (*3)	45 m	[Configuration 2] Camera cable: 15 m X 6 Extension Unit: 4
			High speed	1	15 m (Using FZ-VS4/VSL4)	2	15 m	[Configuration 3] Camera cable: 5 m X 3 Extension Unit: 2
				2	5 m (Using FZ-VS□/VSL□)	4 (*3)	15 m	[Configuration 4] Camera cable: 5 m X 6 Extension Unit: 4
		FH-SM05R/SC05R	---	---	15 m (Using FZ-VS□/VSL□)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
		FZ-S5M3/SC5M3	---	---	5 m (Using FZ-VS□/VSL□)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
	Digital CCD Cameras	FZ-S/SC FZ-S2M/SC2M	---	---	15 m (Using FZ-VS4/VSL4)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
		FZ-S5M2	---	---	5 m (Using FZ-VS□/VSL□)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
After	Digital CMOS Cameras	FH-SM21R/SC21R	Standard	1	15 m (Using FZ-VS4/VSL4)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
				2	15 m (Using FZ-VS4/VSL4)	4 (*3)	45 m	[Configuration 2] Camera cable: 15 m X 6 Extension Unit: 4
			High speed	1	15 m (Using FZ-VS4/VSL4)	2	15 m	[Configuration 3] Camera cable: 5 m X 3 Extension Unit: 2
				2	5 m (Using FZ-VS□/VSL□)	4 (*3)	15 m	[Configuration 4] Camera cable: 5 m X 6 Extension Unit: 4
		FH-SM05R/SC05R	---	---	15 m (Using FZ-VS□/VSL□)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
		FZ-S5M3/SC5M3	---	---	5 m (Using FZ-VS□/VSL□)	2	15 m	[Configuration 3] Camera cable: 5 m X 3 Extension Unit: 2
	Digital CCD Cameras	FZ-S/SC FZ-S2M/SC2M	---	---	15 m (Using FZ-VS4/VSL4)	2	45 m	[Configuration 1] Camera cable: 15 m X 3 Extension Unit: 2
		FZ-S5M2	---	---	5 m (Using FZ-VS□/VSL□)	2	15 m	[Configuration 3] Camera cable: 5 m X 3 Extension Unit: 2

Specifications in this product news are as of the issue date and are subject to change without notice.

Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.