

**Global Service and
Support Catalog for OMRON
Control Devices**

OMRON



Global Service Support Catalog



Making Manufacturing
Reliable Worldwide

realizing



OMRON's Total Service Support with Global Connections

OMRON seeks to help the manufacturing industry in locations throughout the world.

Planning and Design

Inspection

Services are tailored for specific customer needs

Repairs and Maintenance

Commissioning and Technical Support

Planning and Design



Inspection



Sales and Distribution



Commissioning and Technical Support



Repairs and Maintenance



Consulting

We use the latest technologies and product portfolios to provide our customers with the support they need, from selecting the optimal products and system design, to troubleshooting and repairs.



Tsunagi Laboratories

We can test the connections between your devices and OMRON Programmable Controllers.

*As of February 2013, this service is available only in Japan, China, and the Netherlands.



Inventory Centers

OMRON has approximately 20 inventory centers at various locations around the world. We can quickly support our customers with product portfolios that are suitable for the needs of each particular site.



Onsite Support Service

Our service engineers will travel to your facility and assist you in the event of any problems or to help you get your system commissioned, and also to provide the support required for the stable ongoing operation of your system.



Repairs

We have maintenance facilities across the globe to reduce the lead time for repairs. We will help you get your facilities back into operation as quickly as possible.

Sales and Distribution

Services for All Your Needs

e-learning

Technical consultation

Training

Internet

*Not all services are available in all countries and areas. Refer to page 6 and after for details.

Complete Support



e-learning

Learn about OMRON products through our completely free online learning service courses available in thirteen languages. Courses range from introductory to advanced levels.

*Available Languages
Japanese, English, Chinese, Korean, Vietnamese, Thai, Indonesian, Portuguese, French, Spanish, Italian, German, and Russian.



Technical Consultation

We are happy to provide consultation if you have any questions about our products, from selecting the right products, to setup and troubleshooting.



Training


We provide a variety of courses at our locations worldwide, such as regularly scheduled and customized seminars. Our training is also provided in your local native language.



Internet

OMRON has approximately 40 websites in different regions around the world. We also have catalogs and manuals available in your native language.

**OMRON has a support network of 150 locations in 40
 These locations are also partnered with
 local distributors to provide a full range of services.**



INDEX

GREATER CHINA Page 6 to 9

CHINA	Page 6 to 8
HONG KONG	Page 9
TAIWAN	Page 9

KOREA and JAPAN Page 10 to 12

KOREA	Page 10
JAPAN	Page 11 to 12

ASIA PACIFIC Page 13 to 17

INDIA	Page 14	THAILAND	Page 16
INDONESIA	Page 14	VIETNAM	Page 17
MALAYSIA	Page 15		
PHILIPPINES	Page 15		
SINGAPORE	Page 16		

OCEANIA Page 17 to 18

AUSTRALIA	Page 18
NEW ZEALAND	Page 18

countries and regions.



JAPAN

NORTH, CENTRAL and SOUTH AMERICA

OCEANIA

	Sales HQ/ representative offices
	Sales offices

NORTH, CENTRAL and SOUTH AMERICA

Page 19 to 20

- UNITED STATES Page 19
- CANADA Page 20
- MEXICO Page 20
- BRAZIL Page 20
- ARGENTINA Page 20

EUROPE

Page 21 to 26

- | | | | |
|------------------------|---------------------|------------------|------------------------|
| AUSTRIA Page 22 | FRANCE Page 23 | NORWAY Page 24 | SWEDEN Page 25 |
| BELGIUM Page 22 | GERMANY Page 23 | POLAND Page 24 | SWITZERLAND Page 26 |
| CZECH REPUBLIC Page 22 | HUNGARY Page 23 | PORTUGAL Page 25 | TURKEY Page 26 |
| DENMARK Page 22 | ITALY Page 24 | RUSSIA Page 25 | UNITED KINGDOM Page 26 |
| FINLAND Page 23 | NETHERLANDS Page 24 | SPAIN Page 25 | |

AFRICA

Page 27

- SOUTH AFRICA Page 27


*The information in this catalog was last updated in January 2015.
 Visit the Sales Network section of our website at <http://www.fa.omron.co.jp/> for the latest information and updates.

GREATER CHINA



CHINA

Sales HQ	OMRON INDUSTRIAL AUTOMATION(CHINA) CO., LTD.
Address	Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China
TEL/FAX	TEL : 86-21-5037-2222 FAX : 86-21-5037-2200
Languages	Chinese and English
Web site	www.fa.omron.com.cn/



Sales Office Locations

● Beijing	TEL : 86-10-5739-5399	FAX : 86-10-5739-5366	● Zhengzhou	TEL : 86-371-65585192	FAX : 86-371-65585197
● Tianjin	TEL : 86-22-83191580	FAX : 86-22-83191568	● Hefei	TEL : 86-551-63639629	FAX : 86-551-63632093
● Qingdao	TEL : 86-532-66775819	FAX : 86-532-66775820	● Nanchang	TEL : 86-791-86304711	FAX : 86-791-86304733
● Jinan	TEL : 86-531-82929795	FAX : 86-531-82922707	● Changsha	TEL : 86-731-84585551	FAX : 86-731-84585550
● Yantai	TEL : 86-535-6865018	FAX : 86-535-6865016	● Guangzhou	TEL : 86-20-8755-7798	FAX : 86-20-8755-3058
● Tangshan	TEL : 86-315-6328518	FAX : 86-315-6328519	● Dongguan	TEL : 86-769-22423200	FAX : 86-769-22423260
● Shijiazhuang	TEL : 86-311-86918122	FAX : 86-311-86918216	● Shenzhen	TEL : 86-755-2694-8238	FAX : 86-755-2694-8538
● Taiyuan	TEL : 86-351-5229870	FAX : 86-351-5229860	● Foshan	TEL : 86-757-83305268	FAX : 86-757-83305628
● Dalian	TEL : 86-411-39948181	FAX : 86-411-39948182	● Zhongshan	TEL : 86-760-8822-4545	FAX : 86-60-8822-8105
● Liaoning	TEL : 86-24-22815131	FAX : 86-24-22815130	● Shantou	TEL : 86-754-88706001	FAX : 86-754-88706654
● Changchun	TEL : 86-431-81928301	FAX : 86-431-81928300	● Fuzhou	TEL : 86-591-88088551	FAX : 86-591-88088553
● Harbin	TEL : 86-451-53009917	FAX : 86-451-53009920	● Xiamen	TEL : 86-592-2686709	FAX : 86-592-2682320
● Kunshan	TEL : 86-512-50110866	FAX : 86-512-50116667	● Nanning	TEL : 86-771-5531371	FAX : 86-771-5553114
● Suzhou	TEL : 86-512-6866-9277	FAX : 86-512-6866-9280	● Chengdu	TEL : 86-28-86765345	FAX : 86-28-86527365
● Wuxi	TEL : 86-510-85169303	FAX : 86-510-82793748	● Fuzhou	TEL : 86-816-2687-423	FAX : 86-816-2687-423
● Nanjing	TEL : 86-25-8324-0556	FAX : 86-25-8324-2303	● Zigong	TEL : 86-813-8255-616	FAX : 86-813-8255-626
● Zhangjiagang	TEL : 86-512-5631-3157	FAX : 86-512-56313160	● Chongqing	TEL : 86-23-68796406	FAX : 86-23-68796409
	TEL : 86-512-5631-3158		● Guiyang	TEL : 86-851-4812320	FAX : 86-851-4812647
	TEL : 86-512-5631-3159		● Kunming	TEL : 86-871-63527224	FAX : 86-871-63527260
● Xuzhou	TEL : 86-516-83736516	FAX : 86-516-83759516	● Xi'an	TEL : 86-29-8885-1505	FAX : 86-29-8538-1151
● Hangzhou	TEL : 86-571-8765-2855	FAX : 86-571-8765-2858	● Yinchuan	TEL : 86-951-5670-076	FAX : 86-951-5670-076
● Ningbo	TEL : 86-574-2788-8220	FAX : 86-574-2788-8221	● Lanzhou	TEL : 86-931-8720101	FAX : 86-931-8733535
● Wenzhou	TEL : 86-577-88919195	FAX : 86-577-88919198	● Urumchi	TEL : 86-991-5198587	FAX : 86-991-5198577
● Wuhan	TEL : 86-27-8228-2145	FAX : 86-27-8228-2140			
	TEL : 86-27-8228-2146				
	TEL : 86-27-8228-2147				
	TEL : 86-27-8228-2148				

Contact your local sales headquarters or sales location for more information.

Services

Technical Consultation	<p>Operating hours: 08:30 to 19:00 Monday through Friday (excluding holidays)</p> <p>Chinese Technical Consultation Center</p> <p>TEL : 400-820-4535 (Languages: Chinese and English) FAX : 86-21-50504618 E-mail : customer_support@gc.omron.com</p> <p>OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, FAX, or e-mail.</p>
Onsite Support Service	<p>Our technicians will travel to your location to provide a full range of support from commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.</p>
Training	<p>Courses: 20 in all, including courses on Controllers, motion control, Sensors, and more.</p> <p>A lot of e-learning and video training courses are also available.</p> <p>Language: Chinese</p> <p>Locations: Shanghai, Beijing, Guangzhou, Wuxi, Qingdao, Wuhan, Xi'an, Xiamen, and Chengdu</p>
Repairs	<p>Repair Center TEL : 021-5050-9988 extension 2127</p> <p>Repairs can be completed possibly within four working days (for onsite repairs).</p> <p>Our technicians will travel to your location to provide trouble diagnosis, trouble shooting and explain a handling.</p>
Documents	<p>Catalogs, manuals, and FAQs are available in Chinese.</p>

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

China [Beijing] TEL : 86-10-5739-5399 (Extension: 1808)	China [Dalian] TEL : 86-411-3994-8181 (Extension: 216)	China [Shenzhen] TEL : 86-755-2694-8238 (Extension: 509)
China [Tianjin] TEL : 86-22-8319-1580 (Extension: 127)	China [Shanghai, Jiangsu, Zhejiang] TEL : 86-21- 5037-2222 (Extension: 2673, 2663)	China [Guangzhou] TEL : 86-20-8755-7798 (Extension: 211)

This is the support desk for our Taiwanese corporate customers.

Taiwan Desk

China
TEL : 86-21-6100-6051
(Extension: 2687)

This is the support desk for our Korean corporate customers.

Korea Desk

China
TEL : 86-21-6100-6051
(Extension: 2180)

GREATER CHINA

Full-range Service and Support Network in China

OMRON aims to never be out of your reach with a complete support network for OMRON products via phone, the Web, or seminars.

Planning
and
Design

Consulting

Inspection

Commissioning
and
Technical Support

Repairs
and
Maintenance



Technical Consultation

New extended hours from 08:30 to 19:00.

For our Chinese Technical Consultation Center, call 400-820-4535. An automated guidance system is available 24 hours a day.



You can find answers to frequently asked questions on our website or in our information pamphlets. We have twelve different pamphlets available depending on the type of product (Controllers, Sensors, etc.).



Connection Testing at Tsunagi Laboratories, Shanghai

OMRON is here to support the connections between our Programmable Controllers and other third-party devices. Connection guides are also available in Chinese.

We also provide a guided tour of our OMRON Shanghai Factory where you can see OMRON's ideas at work.



Solving Problems in the Solution Plaza

Customers can come into this showroom and use actual OMRON products together with OMRON representatives to determine the best plan of action for their manufacturing needs.



Repairs

OMRON provides fast system repair support. OMRON can provide feedback of the initial consultation results with photographs (location of malfunction, time to repair, and cost) within 24 hours and can complete repairs possibly in four working days. You can view the results of the initial consultation and repair reports on the Web.

Emergency Shipment

When you need a replacement products, Emergency Shipment service is available (not free)

Free Pickup Service

OMRON will travel directly to your location to pick up the product for repair within one hour. This service has a 96% customer satisfaction rate.

Short Message Service

OMRON can contact you via SMS for pickup, initial consultation, completion of repairs, or return of the product.

HONG KONG



Sales HQ	OMRON ELECTRONICS (HK) LTD.
Address	1603A-04, Tower 5, China Hong Kong City, 33 Canton Road, Tsim Sha Tsui, Kowloon, Hong Kong.
TEL/FAX	TEL : 852-2375-3827 FAX : 852-2375-1475
Languages	Chinese and English
Web site	www.fa.omron.com.cn/

Contact your local sales headquarters for more information. Feel free to ask us about the services available in Hong Kong.

TAIWAN



Sales HQ	OMRON TAIWAN ELECTRONICS INC.
Address	6F, Home Young Bldg., No.363, Fu-Shing N.Road, Taipei, Taiwan R.O.C
TEL/FAX	TEL : 886-2-2715-3331 FAX : 886-2-2712-6712
Languages	Chinese, English and Japanese
Web site	www.omron.com.tw/

Sales Office Locations

- Hsinchu TEL : 886-3-667-5557 FAX : 886-3-667-5558
- Taichung TEL : 886-4-2325-0834 FAX : 886-4-2325-0734
- Tainan TEL : 886-6-226-2208 FAX : 886-6-226-1751

Services

Technical Consultation	Operating hours: 08:30 to 12:00 and 13:00 to 18:00 Monday through Friday (excluding holidays) Toll-free in Taiwan: 008-0186-3102 (Languages: Chinese and English) FAX : 002-86-21-50504618 OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 12 in all, including courses on Controllers, motion control, Sensors, and more. Language: Chinese Locations: Taipei, Taichung, Tainan, and Hsinchu
Repairs	Repairs can be completed possibly within four working days (for onsite repairs).
Documents	Catalogs and manuals are available in Chinese, English, and Japanese.

Contact your local sales headquarters or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Taiwan [Taipei]
TEL : 886-2-2715-3331
(Extension: 770)

KOREA



KOREA

Sales HQ	OMRON Electronics Korea CO., LTD.
Address	21Floor, Kyobo Tower B Wing, 1303-22, Seocho-Dong, Seocho-Gu, Seoul, Republic of Korea
TEL/FAX	TEL : 82-2-3483-7789 FAX : 82-2-3483-7788
Languages	Korean and Japanese
Web site	www.ia.omron.co.kr/



Sales Office Locations

- Busan TEL : 82-51-635-3988 FAX : 82-51-634-3987
- Cheonan TEL : 82-41-554-7161 FAX : 82-41-554-7164
- Gumi TEL : 82-54-478-8300 FAX : 82-54-478-8301

Services

Technical Consultation	Operating hours: 09:00 to 18:00 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Technicians from OMRON as well as our affiliated and other entrusted companies will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 5 in all, including courses on Controllers, motion control, and more. Language: Korean Location: Seoul, Busan, Cheonan
Repairs	The product is received from the customer and repairs are performed at the production factory. A substitute product can be provided on loan if necessary.
Documents	Catalogs and manuals are available in Korean, Japanese, and English.


We also provide a variety of services in Japanese for Japanese companies. We have approximately 40 staff members in Korea who can provide Japanese support, so feel free to call whenever you need support.

Japan Desk

Korea [Seoul]
TEL : 82-2-3483-7723
TEL : 82-2-3483-7789

Contact your local sales headquarters or sales location for more information.

JAPAN



JAPAN

Sales HQ	OMRON Corporation Industrial Automation Company
Address	2-3-13, Kounan, Minato-ku, Tokyo Shinagawa Front Building 7F
Language	Japanese
Web site	www.fa.omron.co.jp/



Sales Office Locations

● Sendai ····· TEL : 81-22-265-0571	FAX : 81-22-265-1631	● Osaka ····· TEL : 81-6-6347-5811	FAX : 81-6-6347-5901
● Morioka ····· TEL : 81-19-604-7122	FAX : 81-19-604-7123	● Shiga ····· TEL : 81-77-588-9500	FAX : 81-77-588-9926
● Tokyo ····· TEL : 81-3-6718-3501	FAX : 81-3-6718-3514	● Kyoto ····· TEL : 81-75-325-1092	FAX : 81-75-325-1095
● Kashiwa ····· TEL : 81-4-7148-0690	FAX : 81-4-7148-0695	● Okayama ····· TEL : 81-86-231-3623	FAX : 81-86-231-2530
● Omiya ····· TEL : 81-48-645-8855	FAX : 81-48-645-9990	● Hiroshima ····· TEL : 81-82-247-0310	FAX : 81-82-247-0330
● Takasaki ····· TEL : 81-27-326-3456	FAX : 81-27-326-3459	● Takamatsu ····· TEL : 81-87-851-7737	FAX : 81-87-822-6155
● Utsunomiya ····· TEL : 81-28-633-5424	FAX : 81-28-637-2648	● Fukuoka ····· TEL : 81-92-414-3212	FAX : 81-92-414-3201
● Tachikawa ····· TEL : 81-42-524-6776	FAX : 81-42-524-6545	● Kitakyusyu ····· TEL : 81-93-511-8171	FAX : 81-93-511-8172
● Yokohama ····· TEL : 81-45-411-7285	FAX : 81-45-411-7284	● Kumamoto ····· TEL : 81-96-355-1611	FAX : 81-96-324-3262
● Atsugi ····· TEL : 81-46-297-3605	FAX : 81-46-297-3657		
● Matsumoto ····· TEL : 81-263-32-6561	FAX : 81-263-36-3219		
● Nagoya ····· TEL : 81-52-561-8670	FAX : 81-52-562-1729		
● Numazu ····· TEL : 81-55-977-9029	FAX : 81-55-977-9066		
● Shizuoka ····· TEL : 81-54-253-6182	FAX : 81-54-251-1036		
● Hamamatsu ····· TEL : 81-53-455-0081	FAX : 81-53-455-0082		
● Kariya ····· TEL : 81-566-23-9760	FAX : 81-566-23-9721		
● Kanazawa ····· TEL : 81-76-233-4770	FAX : 81-76-233-5010		
● Toyama ····· TEL : 81-76-441-1170	FAX : 81-76-442-2202		

Contact your local sales location for more information.

Services

Technical Consultation	Open 365 Days 08:00 to 21:00 Toll-free in Japan: 0120-919-066 TEL : 81-55-982-5015 (Languages: Japanese) FAX : 81-55-982-5051 OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from commissioning to the introduction and adjustment (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 18 in all, including courses on Sysmac NJ series, Controllers, motion control, Sensors, HMIs, and more. Language: Japanese Locations: 30 locations throughout Japan
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in Japanese and English.

Non-stop Customer Service, 365 Days a Year

We provide a full range of support for OMRON products.

Planning
and
Design

Consulting



Technical Consultation

Call any time between 08:00 and 21:00, 365 days a year.
For our Japanese Technical Consultation Center, call 0120-919-066.

We will respond to your problems as quickly as we can. We also provide free trial test devices of Sensors and other products so that you can be confident when making your purchase.

Inspection



Connection Testing at Tsunagi Laboratories, Kusatsu

OMRON is here to support the connections between our Programmable Controllers and other third-party company devices. Connection instructions for tested devices and device settings are detailed and provided in customized network connection guides and sample programming. You can also experience the motion control capabilities of the latest control devices first-hand.

We also provide
guided tours of our
Kusatsu Factory.

Commissioning
and
Technical Support



Onsite Support Service

Our highly qualified service engineers will travel to the site of your problem within 24 hours (and possibly as soon as four hours) to provide support for your repair needs.

Emergency Shipment



Required products will be shipped that same day. We have a standard inventory of over 10,000 different models, including models that are no longer in production.

Repairs
and
Maintenance



Repairs

OMRON provides fast system repair support. You can also check the progress of your requested repairs or analyses on the Web 24 hours a day.

Free Pickup Service

OMRON will travel directly to your location to pick up the product for repair. Our specified delivery provider (Yamato Transport) will handle the packaging for shipment.

For Questions about Our Onsite Services, Emergency Shipment, and Repairs

Call any time between 08:00 and 21:00, 365 days a year.
Toll-free in Japan: Please call to 0120-919-066.

ASIA PACIFIC



Inspection

Tsunagi Laboratory India

Tsunagi Laboratory India is established to support the customers for their machines to confirm Interoperability between Omron Masters & third party slaves. We also provide them different customized Connection guides & sample programs for various networks. We provide value addition by performance improvement to customer's Machines through Tsunagi Activity with different Vendors & networks.

Tsunagi Laboratory India ▶



Complete Support

Complete Support Network for Localization

OMRON has sales offices in the following seven countries in the Asia-Pacific region: India, Indonesia, Malaysia, Philippines, Singapore, Thailand, and Vietnam. We also have other local sales and representative offices that provide support for even greater reliability in using OMRON products. OMRON understands that localization is a common point of concern for our customers, and that is why we strive to provide a local means for purchasing our products, training engineers, and even discovering new local partners. Comprehensive support is provided for commissioning new systems in particular. Contact your local sales headquarters or office for more information.



Comprehensive Product Training

OMRON provides comprehensive product training for local technicians at our regional branch locations. We also provide training kits that use OMRON products to educational organizations in order to help promote the training of future technicians in the field. Our customers can also participate in free online training courses in Thai, Vietnamese, and Indonesian.

◀ Seminars in Vietnam

INDIA

Sales HQ	OMRON AUTOMATION PVT. LTD.
Address	THE QUBE 5th Floor, Unit No.501-504, MV Road, Marol, Andheri (EAST), Mumbai-MH-400059, India
TEL/FAX	TEL : 91-22-7128-8400 FAX : 91-22-7115-5602
Languages	English and Hindi
Web site	www.omron-ap.co.in/



Sales Office Locations

- Bangalore ···· TEL : 91-80-67096400 / 67096406 FAX : 91-80-6709-6403
- Gurgaon ···· TEL : 91-124-4921-700 FAX : 91-124-4921-777
- Chennai ···· TEL : 91-44-4902-6100 FAX : 91-44-4351-9446
- Pune ···· TEL : 91-20-4148-4600 FAX : 91-20-6620-6474

Services

Technical Consultation	Operating hours: 09:00 to 17:30 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 7 in all, including courses on Controllers, Motion Control, HMIs, and more. Language: English Locations: Bangalore, Gurgaon, and Pune
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in English.

Contact your local sales headquarters or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

India [Mumbai]
TEL : 91-22-7128-8400

INDONESIA

Sales HQ	PT. OMRON ELECTRONICS
Address	Menara Bidakara 1, Lt. 22 Jl. Jend. Gatot Subroto Kav. 71-73 Pancoran, Jakarta 12870 INDONESIA
TEL/FAX	TEL : 62-21-2949-7500 FAX : 62-21-2949-7555
Languages	English and Indonesian
Web site	www.omron.co.id/



Services

Technical Consultation	Operating hours: 08:30 to 17:15 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: Two Controller courses. Language: Indonesian Location: Jakarta
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in English.

Contact your local sales headquarters for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Indonesia
TEL : 62-21-2949-7500

* Say "Please, Japan desk," if you are greeted in the local language.

ASIA PACIFIC

MALAYSIA

Sales HQ	OMRON ELECTRONICS SDN. BHD.
Address	Unit 1101, Level 11, Uptown 1, No. 1, Jalan SS21/58, Damansara Uptown, 47400 Petaling Jaya, Selangor Darul Ehsan, Malaysia
TEL/FAX	TEL : 60-3-7688-2888 FAX : 60-3-7688-2833
Languages	English, Malay, Chinese and Japanese
Web site	www.omron-ap.com.my/



Sales Office Locations

● **Johor** TEL : 60-7-356-8388 FAX : 60-7-357-3488

● **Penang** TEL : 60-4-643-5382 FAX : 60-4-644-9382

Services

Technical Consultation	Operating hours: 08:30 to 17:30 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support for design, commissioning, introduction (including Vision Sensors), and onsite repairs.
Training	Courses: 5 in all, including courses on Controllers, motion control, Sensors, HMIs, and more. Language: English Location: Petaling Jaya
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in English.

Contact your local sales headquarters or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

PHILIPPINES

Representative office	OMRON ASIA PACIFIC PTE. LTD. MANILA REPRESENTATIVE OFFICE
Address	2F, Kings Court II Building, 2129 Don Chino Roces Avenue, corner Dela Rosa Street, 1231 Makati City, Metro Manila, Philippines
TEL/FAX	TEL : 632-811-2831/2836 FAX : 632-811-2583
Languages	English and Tagalog
Web site	www.omron-ap.com.ph/



Services

Technical Consultation	Operating hours: 08:30 to 17:30 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 5 in all, including courses on Controllers, Sensors, HMIs, and more. Languages: English and Tagalog Location: Manila
Repairs	The product is received from the customer and repairs are performed at the production factory.
Documents	Catalogs and manuals are available in English.

Contact your local representative office for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

SINGAPORE

Sales HQ	OMRON ELECTRONICS PTE. LTD.
Address	438A Alexandra Road, #05-05/08,(Lobby 2) Alexandra Technopark, Singapore 119967
TEL/FAX	TEL : 65-6-547-6789 FAX : 65-6-547-6769
Languages	English and Chinese
Web site	www.omron-ap.com/



Services	
Technical Consultation	Operating hours: 08:30 to 17:15 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support from design, commissioning, introduction (including Vision Sensors), onsite repairs, and maintenance.
Training	Courses: 3 in all, including courses on Controllers, motion control, and more. Language: English Location: Singapore
Repairs	The product is received from the customer and repairs are performed at the production factory.
Documents	Catalogs and manuals are available in English.

Contact your local sales headquarters for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

THAILAND

Sales HQ	OMRON ELECTRONICS CO., LTD.
Address	Rasa Tower 2, 16th Floor, 555 Phaholyothin Road, Kwaeng Chatuchak, Khet Chatuchak, Bangkok 10900, THAILAND
TEL/FAX	TEL : 66-2-937-0500 FAX : 66-2-937-0501
Languages	English and Thai
Web site	www.omron-ap.co.th/



Sales Office Locations

- Rayong TEL : 66-38-346-070 FAX : 66-38-346-071

Services	
Technical Consultation	Operating hours: 08:30 to 17:30 Monday through Friday (excluding holidays) Thai Technical Consultation Center TEL 66-2-942-6700 OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support for commissioning, introduction (including Vision Sensors), onsite repairs, and other technical issues.
Training	Courses: 8 in all, including courses on Controllers, motion control, and more. Language: Thai Location: Bangkok
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs, manuals, and datasheets are available in English. Some manuals are available in Thai.

Contact your local sales headquarters for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Thailand
TEL : 66-2-942-6700

* Say "Please, Japan desk," if you are greeted in the local language.

ASIA PACIFIC

VIETNAM

Representative office	OMRON ASIA PACIFIC PTE. LTD. HANOI REPRESENTATIVE OFFICE
Address	9th floor, Mipec Tower, 229 Tay Son, Dong Da, Hanoi, Vietnam
TEL/FAX	TEL : 844-35563444 FAX : 844-35563443
Languages	English and Vietnamese
Web site	www.omron.com.vn/



Sales Office Location

● Ho Chi Minh ··· TEL : 84-8-39204338 FAX : 84-8-39204335

Services

Technical Consultation	Operating hours: 08:00 to 17:00 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support for design, commissioning, introduction (including Vision Sensors), and onsite repairs.
Training	Courses: 5 in all, including courses on Controllers, Sensors, HMIs, and more. Language: Vietnamese Locations: Hanoi and Ho Chi Minh
Repairs	Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in English. Some manuals are available in Vietnamese.

Contact your local representative office or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

OCEANIA



OCEANIA

AUSTRALIA

Sales HQ	OMRON ELECTRONICS PTY. LTD.
Address	Unit 6, 108 Silverwater Road, Silverwater Sydney Nsw 2128 Australia
TEL/FAX	TEL : 61-2-9878-6377
Language	English
Web site	www.omron.com.au/



Sales Office Locations

- **Brisbane** TEL : 1300-766-766 FAX : 1300-434-682
- **Melbourne** TEL : 1300-766-766 FAX : 1300-434-682
- **Adelaide** TEL : 1300-766-766 FAX : 1300-434-682

Services

Technical Consultation	Operating hours: 08:30 to 17:00 Monday through Friday (excluding holidays) Australian Technical Consultation Center TEL : 1300-766-766 FAX : 1300-434-682 OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support for commissioning, introduction (including Vision Sensors), onsite repairs, and other technical issues.
Training	Courses: 5 in all, including courses on Controllers, Sensors, HMIs, and more. Language: English Locations: Sydney, Brisbane and Melbourne
Repairs	Repairs can be completed possibly within three working days (for onsite repairs).
Documents	Catalogs, manuals, and datasheets are available in English.

Contact your local sales headquarters or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

NEW ZEALAND

Sales HQ	OMRON ELECTRONICS LTD.
Address	65 Boston Road, Mt Eden Auckland New Zealand
TEL/FAX	TEL : 64-9-358-4400 FAX : 64-9-358-4411
Language	English
Web site	www.omron-ap.co.nz/



Sales Office Location

- **Christchurch** TEL : 64-3-366-5091 FAX : 64-3-366-5090

Services

Technical Consultation	Operating hours: 08:00 to 17:00 Monday through Friday (excluding holidays) OMRON will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, or FAX.
Onsite Support Service	Our technicians will travel to your location to provide a full range of support for commissioning, introduction (including Vision Sensors), onsite repairs, and other technical issues.
Training	Courses: Two Controller courses. Language: English Locations: Wellington and Christchurch
Repairs	The product is received from the customer and repairs are performed at the production factory.
Documents	Catalogs, manuals, and datasheets are available in English.

Contact your local sales headquarters or sales location for more information.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Singapore
TEL : 65-6835-3011

* Say "Please, Japan desk," if you are greeted in the local language.

NORTH, CENTRAL & SOUTH AMERICA



Inventory Centers

• United States	Chicago
	California*
• Canada	Toronto
• Brazil	Sao Paulo

4 locations
*Safety products only.

UNITED STATES

Sales HQ	OMRON ELECTRONICS LLC
Address	2895 Greenspoint Parkway, Suite 200, Hoffman Estates, IL 60169 U.S.A.
TEL/FAX	TEL : 1-847-843-7900 / 1-800-556-6766 FAX : 1-847-843-8261
Languages	English and Spanish
Web site	industrial.omron.us



Sales Office Location

- Fremont TEL : 1-510-608-3400 FAX : 1-847-285-8035

Services

Technical Consultation	Toll-free in United States: 1-800-556-6766 Operating hours: 07:00 to 19:00 Monday through Friday (excluding holidays) Emergency Support Line 365days 24hours : 1-800-367-4584 (pay service) E-mail English : ia.techsupport@omron.com Spanish : soportetecnico@omron.com French : soutienTechnique@omron.com
Training	Courses: Controller, Motion Control, HMI, Vision and more are provided. Language: English
Repairs	Repairs can be completed possibly within ten working days (for onsite repairs).
Documents	Catalogs and manuals are available in English.

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Support in United States, Canada, Brazil, Argentina
United States

TEL : 1-224-374-4162

Contact your local sales headquarters or sales location for more information.

CANADA

Sales HQ	OMRON CANADA INC.
Address	885 Milner Avenue, Scarborough, Ontario, M1B 5V8 CANADA
TEL/FAX	TEL : 1-416-286-6465 / Toll-free in Canada (08:00-18:00) : 1-866-986-6766 FAX : 1-416-286-6648
Languages	English, Spanish and French
Web site	industrial.omron.ca




Sales Office Location

- Montreal ····· TEL : 1-514-636-6676 FAX : 1-514-636-2959

MEXICO

Sales HQ	OMRON ELECTRONICS DE MEXICO
Address	Lamartine 238, 4th floor, Col. Chapultepec Morales, Mexico Df, Zip 11570, Mexico
TEL/FAX	TEL : 52-55-5901-4300 / Toll-free in Mexico : 01-800-226-6766 FAX : 52-55-5901-4300
Language	Spanish, English
Web site	industrial.omron.mx



Sales Office Location

- Monterrey ····· TEL : 52-81-1156-9910 FAX : 52-81-1086-2020

Japan Desk

Mexico
TEL : 52-47-2723-8900
(Extension: 8995)

BRAZIL

Sales HQ	OMRON ELETRONICA DO BRASIL LTDA.
Address	Sergeant Avenue Lourival Alves de Souza, 157 - Garden Taquaral 04675-020 Sao Paulo - SP, Brazil
TEL/FAX	TEL : 55-11-2101-6300 FAX : 55-11-2101-6301
Language	Portuguese, English
Web site	industrial.omron.com.br



Sales Office Locations

- Curitiba ····· TEL : 55-41-2105-5966 FAX : 55-41-2105-5901
- Campinas ····· TEL : 55-19-3031-2040 FAX : 55-19-3031-2032

ARGENTINA

Representative office	OMRON ELECTRONICS LLC BUENOS AIRES REPRESENTATIVE OFFICE
Address	Blanco Encalada 5188, Piso 6 Buenos Aires C1431CDP, Argentina
TEL/FAX	TEL : 54-11-4521-8630 / Toll-free in Argentina : 0800-444-4259
Language	Spanish
Web site	industrial.omron.mx

Contact your local sales headquarters, representative office, or sales location for more information. Feel free to ask us about the services available in each country.

EUROPE

Sales HQ
 Sales offices
 Inventory Centers



Inventory Centers

- Netherlands 's-Hertogenbosch
- Turkey Istanbul
- Russia Moscow

3 locations

Services	
Technical Consultation	Our European sales offices will provide consultation regarding product selection, operation, setup, troubleshooting, and maintenance via phone, FAX, or e-mail. Refer to pages 22 to 26 for contact information for each country.
Onsite Support Service	Our technicians will travel from our European office locations to your worksite to provide a full range of support for design, commissioning, introduction (including Vision Sensors), onsite repairs, and other technical issues.
Training	Educational courses on Controllers, motion control, Sensors, and more are also provided at our European offices in English and local native languages.
Repairs	Repairs are performed at our European Repair Center in the Netherlands. Repairs can be completed possibly within five working days (for onsite repairs).
Documents	Catalogs and manuals are available in localized and English versions.
Internet	Localized regional websites are available for individual countries and the OMRON Europe website (industrial.omron.eu) is available in English.

Contact your local sales headquarters or office (pages 22 to 26) if you wish to use this service.

We also provide a variety of services in Japanese for Japanese companies across all of Europe.

Japan Desk

Netherlands

T E L : 31 23 568 1343
E-mail : Japan.desk.Europe@eu.omron.com

Inspection

Repairs and Maintenance

Connection Testing at Tsunagi Laboratories, NETHERLANDS

OMRON is here to support the connections between our Programmable Controllers and other third-party devices.



Repairs

Repairs for the European region are performed at OMRON's large-scale European Repair Center located in the Netherlands. Repairs can be completed possibly within five working days in order to get your system back into operation as quickly as possible.



Free Pickup Service

Our specified delivery provider (DHL) will travel to your location to pick up the product to be repaired and will deliver the repaired product back to you within five working days.

AUSTRIA


Sales HQ	OMRON ELECTRONICS G.m.b.H		
Address	Liebermannstraße A01 118 2345 Brunn am Gebirge Austria		
TEL/FAX	TEL : 43 2236 377 800 FAX : 43 2236 377 800 160		
Mail	omron.austria@eu.omron.com	Languages	German and English
Web site	industrial.omron.at/		

BELGIUM

Sales HQ	OMRON ELECTRONICS NV/SA		
Address	Bayauxlaan 12 B-8300 Knokke-Heist Belgium		
TEL/FAX	TEL : 32 2 466 2480		
Mail	info.be@eu.omron.com	Languages	French, Dutch and English
Web site	industrial.omron.be/		

CZECH REPUBLIC

Sales HQ	OMRON ELECTRONICS SPOL. S R.O.		
Address	Jankovcova 53 170 00 Praha 7 Czech Republic		
TEL/FAX	TEL : 420 234 602 602 FAX : 420 234 602 607		
Mail	office@omron.cz	Languages	Czech and English
Web site	industrial.omron.cz/		



DENMARK

Sales HQ	OMRON ELECTRONICS A/S		
Address	Theilgaards Torv 3, 1st floor, 4600 Køge, Denmark		
TEL/FAX	TEL : 45 43 440 011 FAX : 45 43 440 211		
Mail	omron.dk@eu.omron.com	Languages	Danish and English
Web site	industrial.omron.dk/		



Sales Office Location

- Aarhus ····· TEL : 45 43 440 011 FAX : 45 43 440 211

Contact your local sales headquarters or sales location for more information. Feel free to ask us about the services available in each country.

EUROPE

FINLAND

Sales HQ	OMRON ELECTRONICS OY
Address	Bertel Jungin aukio 7 b FI-02600 Espoo Finland
TEL/FAX	TEL : 35 820 746 4200 FAX : 35 820 746 4250
Mail	info.fi@eu.omron.com
Web site	industrial.omron.fi/
Languages	Finnish and English



FRANCE

Sales HQ	OMRON ELECTRONICS S.A.S.
Address	14 rue de Lisbonne 93561 Rosny Sous Bois cedex France
TEL/FAX	TEL : 33 1 5663 7000 FAX : 33 1 4855 9086
Mail	info_produit@eu.omron.com
Web site	industrial.omron.fr/
Languages	French and English



Sales Office Locations

- Nantes ······ TEL : 0 825 825 679 FAX : 33 1 4855 9428
- Lyon ······ TEL : 0 825 825 679 FAX : 33 1 4855 9428

GERMANY

Sales HQ	OMRON ELECTRONICS GmbH
Address	Elisabeth-Selbert-Strasse 17 40764 Langenfeld Germany
TEL/FAX	TEL : 49 2173 680 00 FAX : 49 2173 680 0400
Mail	info.de@eu.omron.com
Web site	industrial.omron.de/
Languages	German and English



Sales Office Locations

- Langenfeld ···· TEL : 49 2173 68000 FAX : 49 2173 6800400

HUNGARY

Sales HQ	OMRON ELECTRONICS KFT.
Address	Vaci ut. 45. C/6 1134 Budapest Hungary
TEL/FAX	TEL : 36 1 399 3050 FAX : 36 1 399 3060
Mail	infohun@eu.omron.com
Web site	industrial.omron.hu/
Languages	Hungarian and English



Contact your local sales headquarters or sales location for more information. Feel free to ask us about the services available in each country.

*The information in this catalog was last updated in January 2015.

Visit the Sales Network section of our website at <http://www.fa.omron.co.jp/> for the latest information and updates.

ITALY

Sales HQ	OMRON ELECTRONICS S.P.A.
Address	Viale Certosa 49 20149 Milano Italy
TEL/FAX	TEL : 39 02 326 81 FAX : 39 02 326 8282 Operating hours: 08:30 to 17:30 Monday through Friday (excluding holidays) Technical Consultation Center TEL : 39 02 326 8525
Mail	contact_by_web@eu.omron.com
Web site	industrial.omron.it/

Languages

Italian and English



Sales Office Locations

- **Milano** ····· TEL : 39 02 3268777 FAX : 39 02 3268211
- **Bologna** ····· TEL : 39 051 6136611 FAX : 39 051 6130565
- **Terni** ····· TEL : 39 07 4454511 FAX : 39 0744 401865

NETHERLANDS

Sales HQ	OMRON ELECTRONICS B.V.
Address	Wegalaan 61 2132 JD Hoofddorp The Netherlands
TEL/FAX	TEL : 31 23 568 1100 FAX : 31 23 568 1188
Mail	omron-nl@eu.omron.com
Web site	industrial.omron.nl/

Languages

Dutch and English



NORWAY

Sales HQ	OMRON ELECTRONICS NORWAY A/S
Address	Ole Deviks vei 6b, NO-0666 Oslo Norway
TEL/FAX	TEL : 47 22 657 500
Mail	omron.norway@eu.omron.com
Web site	industrial.omron.no/

Languages

Norwegian and English



Sales Office Locations

- **Aalesund** ····· TEL : 47 70 151200
- **Stavanger** ····· TEL : 47 51 81 61 00

POLAND

Sales HQ	OMRON ELECTRONICS SP. Z O.O.
Address	ul. Cybernetyki 7A Budynek Luminar 02-677 Warszawa Poland
TEL/FAX	TEL : 48 22 458 6666 FAX : 48 22 458 6660
Mail	info.pl@eu.omron.com
Web site	industrial.omron.pl/

Languages

Polish and English



Contact your local sales headquarters or sales location for more information. Feel free to ask us about the services available in each country.

EUROPE

PORTUGAL

Sales HQ	OMRON ELECTRONICS IBERIA S.A.U.		
Address	Edificio mar do Oriente Alameda dos Oceanos, Lote 1.07.1 - L 3.2 1990-616 Lisboa Portugal		
TEL/FAX	TEL : 351 21 942 9400 FAX : 351 21 941 7899		
Mail	info.pt@eu.omron.com	Languages	Portuguese and English
Web site	industrial.omron.pt/		




Sales Office Location

- Porto TEL : 351 22 715 5900 FAX : 351 22 713 5152

RUSSIA

Sales HQ	OMRON ELECTRONICS		
Address	Pravdy street 26 125040 Moscow Russia		
TEL/FAX	TEL : 7 495 648 9450 FAX : 7 495 648 9451		
Mail	omron_russia@eu.omron.com	Languages	Russian and English
Web site	industrial.omron.ru/		



SPAIN

Sales HQ	OMRON ELECTRONICS IBERIA S.A.U.		
Address	c/Arturo Soria 95 28027 Madrid Spain		
TEL/FAX	TEL : 34 902 100 221 FAX : 34 902 361 817		
Mail	omron@omron.es	Languages	Spanish and English
Web site	industrial.omron.es/		



Sales Office Locations

- Madrid TEL : 34 902 100 221 FAX : 34 902 361 817
- Barcelona TEL : 34 902 100 221 FAX : 34 902 361 817
- Sevilla TEL : 34 902 100 221 FAX : 34 902 361 817
- Valencia TEL : 34 902 100 221 FAX : 34 902 361 817
- Vitoria TEL : 34 902 100 221 FAX : 34 902 361 817

SWEDEN

Sales HQ	OMRON ELECTRONICS AB		
Address	Färögatan 7 164 40 Kista Sweden		
TEL/FAX	TEL : 46 8 632 3500 FAX : 46 8 632 3540		
Mail	omron.sweden@eu.omron.com	Languages	Swedish and English
Web site	industrial.omron.se/		



Sales Office Locations

- Gothenburg TEL : 46 8 632 3500 FAX : 46 8 632 3540
- Malmö TEL : 46 8 632 3500 FAX : 46 8 632 3540

Contact your local sales headquarters or sales location for more information. Feel free to ask us about the services available in each country.

*The information in this catalog was last updated in January 2015.

Visit the Sales Network section of our website at <http://www.fa.omron.co.jp/> for the latest information and updates.

SWITZERLAND

Sales HQ	OMRON ELECTRONICS AG		
Address	Grafenastrasse 7 Postfach 4319 6304 Zug Switzerland		
TEL/FAX	TEL : 41 41 748 1313 FAX : 41 41 748 1346		
Mail	info.ch@eu.omron.com	Languages	German and English
Web site	industrial.omron.ch/		

TURKEY

Sales HQ	OMRON ELECTRONICS LTD.		
Address	Silkar Plaza Maltepe Cad. No:6 kat:4, 34030 Topkapı Bayrampasa Istanbul Turkey		
TEL/FAX	TEL : 90 212 467 3000 FAX : 90 212 467 3030		
Mail	info.tr@eu.omron.com	Languages	Turkish and English
Web site	industrial.omron.com.tr/		



UNITED KINGDOM

Sales HQ	OMRON ELECTRONICS LTD.		
Address	Opal Drive Fox Milne MK15 ODG Milton Keynes United Kingdom		
TEL/FAX	TEL : 44 1908 258 258 FAX : 44 1908 258 158		
Mail	uk@eu.omron.com	Language	English
Web site	industrial.omron.co.uk/		



Contact your local sales headquarters or sales location for more information. Feel free to ask us about the services available in each country.

*The information in this catalog was last updated in January 2015.
Visit the Sales Network section of our website at <http://www.fa.omron.co.jp/> for the latest information and updates.

AFRICA

Sales HQ
 Sales offices
 Inventory Center



Inventory Center

•South Africa **Johannesburg**

1 location

SOUTH AFRICA

Sales HQ	OMRON ELECTRONICS (Pty) LTD.
Address	22 Friesland Drive Longmeadow Office Park South Modderfontein, 1640 South Africa
TEL/FAX	TEL : 27-11-579-2600 FAX : 27-11-608-3515
Mail	info.sa@eu.omron.com
Language	English
Web site	industrial.omron.co.za/



Sales Office Locations

- Cape Town TEL : 27 21 551 2448 FAX : 27 21 552 9521
- Durban TEL : 27 31 275 3000 FAX : 27 31 279 3150

We also provide a variety of services in Japanese for Japanese companies.

Japan Desk

Netherlands

T E L : 31 23 568 1343
E-mail : Japan.desk.Europe@eu.omron.com

Contact your local sales headquarters or sales location for more information.

“Working for the benefit of society”

– Omron will continue putting this core value into practice by innovating to find solutions to emerging social needs.



A challenging spirit – Omron’s inimitable “DNA”

Omron traces its beginnings to 1933, when founder Kazuma Tateisi began production of his independently developed X-ray timers at Tateisi Electric Manufacturing Co. Since that time, Omron has produced a steady stream of breakthroughs in automation technology that have contributed to the improvement of productivity in a variety of industries.

Omron’s consistent efforts to accurately anticipate the potential needs of society and develop businesses to satisfy them have made the Omron Group what it is today.


Kazuma Tateisi’s passion and progressive attitude live on in the hearts of today’s Omron employees as they continuously rise to each new challenge.

Leading the world in monozukuri innovation.

Omron is a global supplier of products and services designed for manufacturing businesses, from factory automation (FA) systems for all types of production lines to electronic components contained in end products. A reliable partner for manufacturing businesses around the world, Omron applies its proprietary Sensing & Control technologies to its pursuit of innovation of both production processes and products.

A diverse product range meeting the demands of manufacturers the world over.

The shift from manual to automated production is accelerating throughout the world in response to growing demand for rapid delivery of a diverse range of products to an ever greater number of people. Omron provides a comprehensive line of products that are essential for automated production operations, including sensors that serve as sensory organs providing “sight,” “tactile perception,” etc.; controllers that serve as “brains;” motion equipment and drives that serve as “hands and feet;” and networks that serve as “nervous systems” to connect them. Omron offers solutions to varying levels of automation needs to customers around the world, from entry-level automation to state-of-the-art automated lines.



* The information in this catalog was last updated in January 2015.

Visit the Sales Network section of our website at <http://www.fa.omron.co.jp/> for the latest information and updates.

OMRON Corporation Industrial Automation Company

Tokyo, JAPAN

Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A
Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2),
Alexandra Technopark,
Singapore 119967
Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2015 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

Cat. No. GSCC-009C

0115 (0313) (W)