Key-type Selector Switch (Detachable) (Cylindrical 16-dia.)

# Separate Construction with Cylindrical 16-dia. Body

- Short mounting depth, less than 28.5 mm below panel
- Wide range of switching capacity from standard to microload
- Oil-resistant IP65 models



Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 11.

### **List of Models**

/!`

		Model	
	Rectangular	Square	Round
Solder terminals	A165K-J Series	A165K-A Series	A165K-T Series
Screw- less clamp connector	A165K-J Series	A165K-A Series	A165K-T Series

### **Model Number Structure**

Model Number Legend...... The model numbers used to order sets of Units are illustrated below. One set comprises the Selector, Switch, and 2 Keys.

For information on combinations, refer to Ordering Information on page 2.

(1) Shape of Selector —			
Symbol	Shane	Color	

Symbol	Snape	COIOI
J	Rectangular	
А	Square	Black
Т	Round	

#### (2) Number of Notches/Resetting Method

Symbol	No. of notches	Reset method	Key release position
2ML			Left
2MR	2 notches	Automatic	Right
2M	Z HUICHES		Left and right
2AL			Left
3MC			Center
3MR			Right
3ML	3 notches	Manual	Left
3M			Left, right, and center
3AC	3 notches	Automatic	Center

#### (3) Contact Configuration

• •		0
Symbol	Туре	Terminal
1	SPDT	Solder Terminal
2	DPDT	
2S	DPDT	Screw-less Clamp

Note: Only DPDT contacts are available with 3-notch models.

### Ordering as a Set ...... The model numbers used to order sets of Units are given in the following tables. One set comprises the

Solder Terminals

Rectangular Models Oil-resistant IP65



Selector, Switch and 2 Keys.

A165K-J

Number of notches	Output	Reset method		Key release position	Model
				Left	A165K-J2ML-1
	SPDT	Manual	$\sim$	Right	A165K-J2MR-1
	SFDT			Left and right	A165K-J2M-1
2 notches		Automatic	$\diamond$	Left	A165K-J2AL-1
2 holdnes			inual 🗸	Left	A165K-J2ML-2
	DPDT	Manual		Right	A165K-J2MR-2
	DFDT			Left and right	A165K-J2M-2
		Automatic	$\diamond$	Left	A165K-J2AL-2
				Center	A165K-J3MC-2
3 notches	DPDT	Manual		Right	A165K-J3MR-2
STICICITES	DFDT	wanual	$\checkmark$	Left	A165K-J3ML-2
				Left, right, and center	A165K-J3M-2

Square Models

Oil-resistant IP65



A165K-A

Number of notches	Output	Reset meth	od	Key release position	Model
				Left	A165K-A2ML-1
	SPDT	Manual	$\checkmark$	Right	A165K-A2MR-1
	SFDT			Left and right	A165K-A2M-1
2 notches		Automatic	$\diamond$	Left	A165K-A2AL-1
2 Hotones			$\checkmark$	Left	A165K-A2ML-2
	DPDT	Manual		Right	A165K-A2MR-2
	DFDT			Left and right	A165K-A2M-2
		Automatic	$\diamond$	Left	A165K-A2AL-2
				Center	A165K-A3MC-2
3 notches	DPDT	Manual		Right	A165K-A3MR-2
3 HOLCHES	DPDT	Ivialiual	$\checkmark$	Left	A165K-A3ML-2
				Left, right, and center	A165K-A3M-2

Round Models

Oil-resistant IP65



Number of notches	Output	Reset met	thod	Key release position	Model
				Left	A165K-T2ML-1
	SPDT	Manual	$\sim$	Right	A165K-T2MR-1
	SFDT		-	Left and right	A165K-T2M-1
2 notches		Automatic	$\diamond$	Left	A165K-T2AL-1
2 Holdnes			$\sim$	Left	A165K-T2ML-2
	DPDT	Manual		Right	A165K-T2MR-2
	DFDT			Left and right	A165K-T2M-2
		Automatic	$\diamond$	Left	A165K-T2AL-2
				Center	A165K-T3MC-2
3 notches	DPDT	Manual		Right	A165K-T3MR-2
STICICITES	DFDI	wanud	$\checkmark$	Left	A165K-T3ML-2
				Left, right, and center	A165K-T3M-2

Ordering as a Set ...... The model numbers used to order sets of Units are given in the following tables. One set comprises the Selector, Switch and 2 Keys.

#### Screw-less clamp connector

Rectangular Models **Oil-resistant IP65** 



Number of notches	Output	Reset method	Key release position	Model
			Left	A165K-J2ML-2S
2 notches	DPDT	Manual 🗸 🗸	Right	A165K-J2MR-2S
			Left and right	A165K-J2M-2S
3 notches	DPDT	Manual	Left	A165K-J3ML-2S
3 HOICHES	DFDT		Left, right, and center	A165K-J3M-2S



**Oil-resistant IP65** 



Number of notches	Output	Reset met	thod	Key release position	Model
		Manual		Left	A165K-A2ML-2S
2 notches	DPDT	Mariua		Left and right	A165K-A2M-2S
		Automatic	$\diamond$	Left	A165K-A2AL-2S
3 notches	DPDT	Manual	$\checkmark$	Left, right, and center	A165K-A3M-2S

Round Models

Oil-resistant IP65



		V			
Number of notches	Output	Reset met	hod	Key release position	Model
				Left	A165K-T2ML-2S
2 notches	DPDT	Manual	$\sim$	Right	A165K-T2MR-2S
2 holdnes	DFDT			Left and right	A165K-T2M-2S
		Automatic	$\diamond$	Left	A165K-T2AL-2S
				Center	A165K-T3MC-2S
3 notches	DPDT	Manual	$\checkmark$	Left	A165K-T3ML-2S
				Right	A165K-T3MR-2S

Ordering Individually ........ Selectors and Switches can be ordered separately. Combinations that are not available as sets can be created using individual Units. Also, store the parts as spares for maintenance and repairs. Operation Units (Listed on Page 5.) Rectangular (A165K-J) Square (A165K-A) Round (Standard condition when shipped) (A165K-T) Switches with 2 Notches Switches with 3 Notches (45°) (45°) (45°) (45°) (75°) - 90°-FF ·Two keys are provided. Note: The figures in parentheses are for self-resetting models. FP: Free position Switches (Listed on Page 5.) PCB terminals Solder terminals Screw-less clamp connector

Ordering Individually ........ Selectors and Switches can be ordered separately. Combinations that are not available as sets can be created

#### Selectors

using individual Units. Also, store the parts as spares for maintenance and repairs.

Appearance	Number of notches	Reset method	Key release position	Model
ectangular			$\bigcirc$	A165K-J2ML
A165K-J)	2 notches	Manual	$\bigcirc$	A165K-J2MR
E Star	2 notches		8	A165K-J2M
		Automatic 🚫	$\bigcirc$	A165K-J2AL
			()	A165K-J3MC
( and a second s		Manual	$\bigcirc$	A165K-J3MR
	3 notches	Manual	$\bigcirc$	A165K-J3ML
			*	A165K-J3M
		Automatic (1)	0	A165K-J3AC
quare		<u> </u>	$\odot$	A165K-A2ML
A165K-A)	2 notches	Manual	$\bigcirc$	A165K-A2MR
	2 notches		$\otimes$	A165K-A2M
		Automatic 🚫	$\bigcirc$	A165K-A2AL
Ema			1	A165K-A3MC
A STORE		Manual	$\bigcirc$	A165K-A3MR
$\sim$	3 notches	Manual	$\bigcirc$	A165K-A3ML
			*	A165K-A3M
		Automatic (1)	1	A165K-A3AC
ound			$\bigcirc$	A165K-T2ML
\165K-Т)	2 notches	Manual	$\bigcirc$	A165K-T2MR
P	2 notches		$\otimes$	A165K-T2M
		Automatic 🚫	$\overline{\bigcirc}$	A165K-T2AL
		0	1	A165K-T3MC
		Manual	$\bigcirc$	A165K-T3MR
V	3 notches	IVIAI IUAI	$\odot$	A165K-T3ML
			*	A165K-T3M
		Automatic (1)	(1)	A165K-T3AC

#### Switches

Appearance		Classif	lication		Model	
		2 notches	SPDT		A16S-2N-1	
		Z Hotones	DPDT	Solder terminal	A16S-2N-2	
	Switches	3 notches	DPDT		A16S-3N-2	
			2 notoboo	SPDT		A16S-2N-1P
		2 notches	DPDT	PCB terminal	A16S-2N-2P	

#### Switch Units with Screw-less Clamp Connectors

Appearance	Classification				Model	Remarks
	Common to standard	DPDT	2 notches	Non-lighted	A16-2S	Common to ones for pushbutton switches.
	load and microload.	וסיש	3 notches	Non-ngrited	A16S-3N-2LS	

### Accessories and Tools (Order Separately) Accessories

Name	Appearance	Classification	Model	Remarks
Panel Plugs		Rectangular	A16ZJ-3003	Used for covering the panel cutouts for future panel expansion.
		Square	A16ZA-3003	
		Round	A16ZT-3003	Degree of protection: IP40 Color: Black

#### Tools

			Applicable types					
Name Appearance	Appearance	nce Model	Pushbutton Switch	Knob-type Selector Switch	Key-type Selector Switch	Emergency Stop Switch	Indicator	Remarks
Screw Fitting	â	A16Z-3004	Yes	Yes	Yes	Yes	Yes	Convenient for ganged installation.
Extractor		A16Z-5080	Yes	Yes	Yes	Yes	Yes	Convenient for extracting the Lamp from a Solder-terminal Socket Unit.

#### Key

Appearance	Model
	A165K-KEY

Note: Two Keys are provided.

Ordering as a Set: Refer to page 2 to 3.

Specifications, and dimensions: Refer to page 7 to 10.
Accessories, replacements, and tools: Refer to this page.

### Specifications

#### **Approved Standard Ratings**

#### UL, cUL (File No. E41515)

5 A at 125 VAC, 3 A at 250 VAC (general use) 3 A at 30 VDC (resistive)

Note: Certification has been obtained for the Switch Unit. For detailed information on individual products that have received certification, consult your supplier.

## Ratings

### Contacts

Rated voltage	Resistive load
125 VAC	5 A
250 VAC	3 A
30 VDC	3 A

Minimum applicable load: 1 mA at 5 VDC

Rated values are obtained from tests conducted under the following conditions.

1. Load: Resistive load

2. Mounting conditions: No vibration and no shock

3. Temperature: 20±2°C

4. Operating frequency: 20 times/min

#### Characteristics Socket Units

#### **Key-type Selector Switch** Item Туре Allowable Mechanical 20 operations/minute max. operating frequency Electrical 10 operations/minute max. Insulation resistance 100 MΩ min. (at 500 VDC) **Contact resistance** 100 mΩ max. (intial value) Between terminals 1,000 VAC, 50/60 Hz for 1 minute of same polarity Dielectric **Between terminals** 2,000 VAC, 50/60 Hz for 1 minute strength of different polarity Between each ter-2,000 VAC, 50/60 Hz for 1 minute minal and ground Vibration 10 to 55 Hz, 1.5-mm double amplitude Malfunction resistance (malfunction within 1 ms) Destruction 500 m/s<sup>2</sup> max. Shock resistance Malfunction 150 m/s<sup>2</sup> max. (malfunction within 1 ms) 250,000 operations min. (durability of key: Mechanical 10,000 operations min.) Durability Electrical 100,000 operations min. Electric shock protection Class II class PTI (tracking characteristic) 175 Degree of contamination 3 (IEC60947-5-1) Approx. 26.5 g (in the case of a DPDT Weight switch key) Ambient operating 10°C to 55°C temperature (with no icing or condensation) 35% to 85%RH Ambient operating humidity Ambient storage -25°C to 65°C (with no icing or condensation) temperature

#### Screw-less Clamp

Item	Туре	Screw-less Clamp				
Recomme	nded wire size	0.5 mm <sup>2</sup> twisted wire or 0.8 mm-dia. solid wire				
Usable	Twisted wire	0.3 mm <sup>2</sup>	0.5 mm <sup>2</sup>	0.5 mm <sup>2</sup> 0.75 mm <sup>2</sup> 1.2		
wires and tensile	Solid wire	0.5 mm dia.	0.8 mm dia.	1.0 mm dia.		
strength	Tensile strength	10 N	20 N	30 N	40 N	
Length of exposed wire		10 ±1 mm				
Compliant standards		JIS C 2811 Terminal Blocks for Industrial Use				

#### TÜV (EN60947-5-1) (Low Voltage Directive)

3 A at 250 VAC 3 A at 30 VDC

#### CCC (GB/T14048.5)

5 A at 125 VAC 3 A at 250 VAC 3 A at 30 VDC


#### **Contact Form**

Name	Contact form
SPDT	сом по

#### **Operating Characteristics**

Туре	Key-type Selector Switch		
Characteristics	2 notches	3 notches	
Operating torque (OF) max.	0.1 N·m		
Set position (SP)	90±5° 45° <sup>+10</sup>		

#### **Operation Angle**



FP: Free position

#### **Contact Configuration**

	Contact configuration					
No. of	SPDT			DPDT		
notches	Posi- tion	sw	Posi- tion	SW2	SW1	MRON
2	$\bigcirc$	~	$\bigcirc$	~	~	
notches	$\bigcirc$	\$•	$\bigcirc$	\$•	\$•	
			$\bigcirc$	• ⁄>	•••	
3 notches	-		$(\uparrow)$	~	~	
			$\oslash$	Ŷ°	~•	


SW2 SW1

U

Note: The angle used for automatic reset is shown in parentheses.

### Nomenclature


### **Model Structure**



## The flange can be rotated to easily change the operation angle of the knob.

For information on rotating the flange, refer to the A165S/W datasheet.

Example: Knob-type Selector Switch with Two Notches





Note: The angle is  $75^{\circ}$  for self-resetting models.


### Dimensions The Dimension shows 2-switch outputs.

### Rectangular A165K-J

Solder terminals (tab terminals #110)








Lock ring

\* Refer to the A165S/W for Panel cutouts.

### Square A165K-A Solder terminals (tab terminals #110)




\* Refer to the A165S/W for Panel cutouts.

#### Round A165K-T Solder terminals (tab terminals #110) M16×1 -0-1.5 \_\_\_\_ 12.2 -10.8 9.5 -21.1 34.5± -28.5 124 15.8 1 Model, rating, standard Packing (t0.5) Mounting nut

\* Refer to the A165S/W for Panel cutouts.

### Dimensions • The Dimension shows 2-switch outputs. • The lamp terminal is also provided with non-lighted models. • A rectangular model is listed as an example. (Unit: mm)



#### **Terminal Arrangement**

For information on the terminal arrangement, refer to the A165S/W datasheet.

#### Panel Mounting and Socket Unit Mounting and Removal

Refer to the A16 Pushbutton Switch datasheet.

#### **Flange Rotation**

Refer to the A165S/W datasheet.

### **Safety Precautions**

#### Refer to Safety Precautions for All Pushbutton Switches/Indicators.

#### **Precautions for Correct Use**

#### Mounting

- Always make sure that the power is turned OFF before mounting, removing, or wiring the Switch, or performing maintenance.
- Do not tighten the mounting nut more than necessary using tools such as pointed-nose pliers. Doing so will damage the mounting nut.
- The tightening torque is 0.29 to 0.49 N·m.

#### Wiring

- Solder terminals and quick-connect terminals (#110) are commonly used for terminals.
- Be sure to use electrical wires that are a size appropriate for the applied voltage and carry current (conductor size is 0.5 to 0.75 mm<sup>2</sup>). Perform soldering according to the conditions provided below. If the soldering is not properly performed, the lead wires will become detached, resulting in short-circuits.
- 1. Hand soldering:  $350^{\circ}C$ , within 3 s
- 2. Dip soldering: 350°C, within 3 s
- Wait for one minute after soldering before exerting any external force on the solder.
- Use non-corrosive resin fluid as the flux.
- Make sure that the electric cord is wired so that it does not touch the Unit. If the electric cord touches the Unit, then electric wires with a heat resistance of 100°C min. must be used.
- After wiring the Switch, maintain an appropriate clearance and creepage distance.


#### **Operating Environment**

• The IP65 model is designed with a degree of protection so that it will not sustain damage if it is subjected to water from any direction to the front of the panel.

#### Using the Microload

- Insert a contact protection circuit, if necessary, to prevent the reduction of life expectancy due to extreme wear on the contacts caused by loads where inrush current occurs when the contact is opened and closed.
- The A16 allows both a standard load (125 V at 5A, 250 V at 3 A) and a microload. If a standard load is applied, however, the microload area cannot be used. If the microload area is used with a standard load, the contact surface will become rough, and the opening and closing of the contact for a microload may become unreliable.
- The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% ( $\lambda$  60) (conforming to JIS C5003).

The equation,  $\lambda$  60 = 0.5  $\times$  10<sup>-6</sup>/operations indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.



#### Screw-less Clamp Wiring Procedure

#### **Connecting Wires**


- 1. Strip the wires for 10 mm (allowable range:  $10\pm 1$  mm).
- 2. If braided wire is used, twist the wire to straighten it out.
- 3. Insert the wire into the insertion hole while pressing the release button at the side of the hole. (Using a precision screwdriver is recommended.)
- 4. Let go of the release button to lock the wire into place.
- After locking, pull on the wire gently to confirm that it is securely locked.

#### **Removing Wires**

 Remove wires by pulling them while pressing the release button.
Note: When reusing wires that have already been locked one, cut off the end of the wire and strip the wire again before using.

#### Others

- The oil-resistant IP65 uses NBR rubber and is resistant to general cutting oil and cooling oil. Some particular oils cannot be used with the oil-resistant IP65, however, so contact your OMRON representative for details.
- If the panel is to be finished with coating, etc., make sure that the panel meets the specified dimensions after the coating.
- Do not subject the Switch to extreme shock or vibration. Doing so will cause malfunctions and damage to the Switch. Do not let sharp objects come into contact with the Switches that are made of resin. Doing so will damage the Switches, causing scratches on the outside of the operating parts, and malfunction.



4 Hammer Sc drive

Do not operate the Switch with hard or sharp objects.

#### Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company