
Pushbutton Switches/Selector Switches/Indicators A22N/M22N/A30N

Control panel miniaturization through a more compact design and modified wiring direction

Addition of Push-In Plus terminal blocks for easy wiring Workability and safety improvements



Pushbutton Switches

<u> A22NN/A22NL</u>

22-mm dia. Pushbutton Switches
Control panel miniaturization through a more
compact design and modified wiring direction.
Addition of Push-In Plus terminal blocks for
easy wiring.



Easy to Use

- Improved wiring visibility through to a modified wiring direction. (Push-In Plus terminal block type)
- Screw terminal block structure is compatible with round crimp terminals. (Screw terminal block type)
- The terminals can be secured even when a contact block is mounted. (Screw terminal block type)
- Contact Blocks can be attached in any direction for easy assembly.

Miniaturization

- No need for extra lateral space because of the modified wiring direction.
 (Push-In Plus terminal block type)
- · Compact design.
- A22NL (lighted models) are the same size as A22NN (non-lighted models).

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenance-free use. (Push-In Plus terminal block type)

Product Lineup

- Meet global safety standards.
- Can be installed in two types of panel hole dimensions: 22.3 and 25.5 dia.
- The buttons and bezels come in a wide variety of colors, shapes, and materials.
- Compliant with IEC IP66, Certified for UL508 Type 4X, 13.



Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 85.

Button Colors

	Non-lighted A22NN-□□□-N□ Switches Opaque		Red	Green	Yellow	White	Blue	Black	
	Lighted Switches A22NL-□□□-T□ Transparent	When not lit	Red	Green	Yellow	White	Blue	Orange	White
		When lit	Red	Green	Yellow	White	Blue	Orange	Opaque white*

^{*} The colors when the Switches are lit are for transparent white buttons (code: TW) and yellow LED Lamps (code: Y).

List of Models

Screw Terminal Blocks/Push-In Plus Terminal Blocks							
Plastic bezels	Brushed metal bezels						
A22N□-BN	A22N□-MN						
Flat	Flat						
A22N□-BP	A22N□-MP						
Projected	Projected						
A22N□-BG	A22N□-MG						
Full guard	Full guard						
A22N□-BM	A22N□-MM						
Mushroom	Mushroom						

A22NN/A22NL

Model Number Structure

Model Number Legend----- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

For information on combinations, refer to Ordering Information on pages 5 to 8.

Model Numbers for Sets

									(7)			
A22N L	-	ΒN	M	-	TR	Α	-	G	100	_	R	В

(1) Type

Code	Description
N	Non-lighted
L	Lighted

(2) Bezel Material and Button Shape

Code	Bezel material	Button shape
BN	Plastic	Flat
BP	Plastic	Projected
BG	Plastic	Full guard
ВМ	Plastic	Mushroom
MN	Brushed metal	Flat
MP	Brushed metal	Projected
MG	Brushed metal	Full guard
MM	Brushed metal	Mushroom

(3) Switch Action

Code	Description
М	Momentary
Α	Alternate

(4) Button Transparency and Color and (8) LED Lamp Color

Lighted/non-lighted	ighted/non-lighted Code (4) Code (8)		Transparency	Button color	LED lamp color
	NR	N	Opaque	Red	
	NG	N	Opaque	Green	
Non-lighted	NY	N	Opaque	Yellow	
	NW	N	Opaque	White	
	NA	N	Opaque	Blue	
	NB	N	Opaque	Black	ĺ
	TR	R	Transparent	Red	Red
	TG	G	Transparent	Green	Green
	TY	Υ	Transparent	Yellow	Yellow
Lighted	TW	W	Transparent	White	White
	TA	Α	Transparent	Blue	Blue
	TO	0	Transparent	Orange	Orange
	TW	Υ	Transparent	White *	Yellow

^{*} The color is opaque white when the Switch is lit.

(5) Degree of Protection

	Code	Description
•	Α	Compliant with IEC IP66, Certified for UL508 Type 4X, 13

(6) Contacts and Terminals Specifications

Code	Specification
G	General/Screw terminal block
Р	General/Push-In Plus Terminal Block

(7) Contacts

	Con	Contact		Unit position							
Code	Blo	cks	Noi	n-ligh	ted		Lighted				
	NO	NC	1	2	3	1	2	3			
100	1	0	NO			NO	Lighting Unit				
002	0	1			NC		Lighting Unit	NC			
101	2	0	NO		NO	NO	Lighting Unit	NO			
102	1	1	NO		NC	NO	Lighting Unit	NC			
202	0	2	NC		NC	NC	Lighting Unit	NC			
111	3	0	NO	NO	NO			•			
112	2	1	NO	NO	NC						
122	1	2	NO	NC	NC						
222	0	3	NC	NC	NC						

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.

2. Refer to the following figure for Unit positions.



(9) LED Lamp Voltage

Code	LED Lamp voltage
N	Non-lighted
Α	6 VAC/DC
В	12 VAC/DC
С	24 VAC/DC
D	100/110/120 VAC
E	200/220/230/240 VAC

- Specifications: Refer to page 12.
- Dimensions: Refer to pages 14 to 16.

- Precautions for correct use: Refer to pages 85 to 96.
- Accessories and tools: Refer to pages 80 to 81.

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Flat Switches

Annoaranco	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Plastic bezels	1	A22NN-BNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-G(7)(7)(7)-NN		100
	ı.	A22NN-BNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-P(7)(7)(7)-NN		002
	2	A22NN-BNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-G(7)(7)(7)-NN		101 102
	2	A22NN-BNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-P(7)(7)(7)-NN		202
	3	A22NN-BNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-G(7)(7)(7)-NN	NR: Opaque, red	111 112
	3	A22NN-BNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BNA-(4)(4)A-P(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	122 222
Brushed metal	1	A22NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-G(7)(7)(7)-NN	NW:Opaque, white	100
bezels	Į.	A22NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-P(7)(7)(7)-NN	NA: Opaque, blue NB: Opaque, black	002
	_	A22NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-G(7)(7)(7)-NN		101
	2	A22NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-G(7)(7)(7)-NN		111 112
	3	A22NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MNA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Flat Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage	
		Model	Model			color	LLD Lamp Tollago	
Plastic bezels	1	A22NL-BNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BNA- (4)(4)A-G(7)(7)(7)-(8)(9)		100		A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC	
		A22NL-BNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BNA- (4)(4)A-P(7)(7)(7)-(8)(9)		002			
	2	A22NL-BNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BNA- (4)(4)A-G(7)(7)(7)-(8)(9)	TR: Transparent, red	101 102 202	R: Red G: Green Y: Yellow W: White A: Blue O: Orange		
		A22NL-BNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BNA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow				
Brushed metal bezels	1	A22NL-MNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MNA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	100			
	'	A22NL-MNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MNA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO:Transparent, orange	002			
	2	A22NL-MNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MNA- (4)(4)A-G(7)(7)(7)-(8)(9)		101			
	2	A22NL-MNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MNA- (4)(4)A-P(7)(7)(7)-(8)(9)		102 202			

Note: Normally, the Button and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Button and yellow LED. A22N \square - \square \square - \underline{TW} A- \square \square - \underline{Y} \square

[■] Subassemblies: Refer to pages 9 to 11 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 12.

[■] Dimensions: Refer to pages 14 to 16.

[■] Accessories and tools: Refer to pages 80 to 81.

A22NN/A22NL

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Projected Switches

Annogranos	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Plastic bezels	s	A22NN-BPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-G(7)(7)(7)-NN		100
	'	A22NN-BPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-P(7)(7)(7)-NN		002
	2	A22NN-BPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-G(7)(7)(7)-NN		101
	2	A22NN-BPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-BPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-G(7)(7)(7)-NN	NR: Opaque, red	111 112
	3	A22NN-BPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BPA-(4)(4)A-P(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	122 222
Brushed metal	1	A22NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-G(7)(7)(7)-NN	NW:Opaque, white NA: Opaque, blue	100
oezels	'	A22NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-P(7)(7)(7)-NN	NB: Opaque, black	002
	_	A22NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-G(7)(7)(7)-NN		101
	2	A22NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-G(7)(7)(7)-NN		111 112
	3	A22NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MPA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Projected Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding) Model (4)(4) Button col		(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage	
		Model	Model			color		
Plastic bezels	tic bezels	A22NL-BPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BPA- (4)(4)A-G(7)(7)(7)-(8)(9)		100			
		A22NL-BPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BPA- (4)(4)A-P(7)(7)(7)-(8)(9)		002		A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC	
	2	A22NL-BPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BPA- (4)(4)A-G(7)(7)(7)-(8)(9)	TR: Transparent, red	101 102 202 100 002	R: Red G: Green Y: Yellow W: White A: Blue O: Orange		
		A22NL-BPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BPA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow				
Brushed metal bezels	4	A22NL-MPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MPA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue				
	'	A22NL-MPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MPA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange				
	2	A22NL-MPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MPA- (4)(4)A-G(7)(7)(7)-(8)(9)		101 102			
	2	A22NL-MPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MPA- (4)(4)A-P(7)(7)(7)-(8)(9)		202			

Note: Normally, the Button and LED Lamp with the same color are combined.

[■] Subassemblies: Refer to pages 9 to 11 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 12.

[■] Dimensions: Refer to pages 14 to 16.

[■] Accessories and tools: Refer to pages 80 to 81.

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Full-guard Switches

Annogrange	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Plastic bezels	1	A22NN-BGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-G(7)(7)(7)-NN		100
	ı	A22NN-BGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-P(7)(7)(7)-NN		002
	2	A22NN-BGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-G(7)(7)(7)-NN		101 102 202
	2	A22NN-BGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-P(7)(7)(7)-NN		
	3	A22NN-BGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-G(7)(7)(7)-NN	NR: Opaque, red	111 112
		A22NN-BGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BGA-(4)(4)A-P(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	122 222
Brushed metal	1	A22NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-G(7)(7)(7)-NN	NW:Opaque, white	100
bezels	ı	A22NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-P(7)(7)(7)-NN	NA: Opaque, blue NB: Opaque, black	002
		A22NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-G(7)(7)(7)-NN		101
	2	A22NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-G(7)(7)(7)-NN		111 112
	3	A22NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MGA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Full-guard Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage
		Model	Model	Button color	Contacts	color	LLD Lamp Voltage
Plastic bezels	1	A22NL-BGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BGA- (4)(4)A-G(7)(7)(7)-(8)(9)		100		A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC
	2	A22NL-BGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BGA- (4)(4)A-P(7)(7)(7)-(8)(9)		002		
	2	A22NL-BGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BGA- (4)(4)A-G(7)(7)(7)-(8)(9)	TR: Transparent, red	101 102 202	R: Red G: Green Y: Yellow W: White A: Blue O: Orange	
		A22NL-BGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BGA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, red TY: Transparent, yellow			
Brushed metal bezels	1	A22NL-MGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MGA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	100		
DEZEIS	'	A22NL-MGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MGA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	002		
	2	A22NL-MGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MGA- (4)(4)A-G(7)(7)(7)-(8)(9)		101		
	2	A22NL-MGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MGA- (4)(4)A-P(7)(7)(7)-(8)(9)		102 202		

Note: Normally, the Button and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Button and yellow LED. A22N - D - TWA - D D - Y

[■] Subassemblies: Refer to pages 9 to 11 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 12.

[■] Dimensions: Refer to pages 14 to 16.

[■] Accessories and tools: Refer to pages 80 to 81.

A22NN/A22NL

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Mushroom Switches

Annogrance	Contacto	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Plastic bezels	1	A22NN-BMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-G(7)(7)(7)-NN		100
	1	A22NN-BMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-P(7)(7)(7)-NN		002
	2	A22NN-BMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-G(7)(7)(7)-NN		101
	2	A22NN-BMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-BMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-G(7)(7)(7)-NN	NR: Opaque, red	111 112
		A22NN-BMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-BMA-(4)(4)A-P(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	122 222
Brushed metal	1	A22NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-G(7)(7)(7)-NN	NW:Opaque, white	100
bezels	'	A22NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-P(7)(7)(7)-NN	NA: Opaque, blue NB: Opaque, black	002
		A22NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-G(7)(7)(7)-NN	-1 1 /	101
	2	A22NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-P(7)(7)(7)-NN		102 202
	3	A22NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-G(7)(7)(7)-NN		111 112
	3	A22NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A22NN-MMA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Mushroom Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage
		Model	Model	Button color	Contacts	color	LED Lamp voitage
Plastic bezels	1	A22NL-BMM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BMA- (4)(4)A-G(7)(7)(7)-(8)(9)		100		
		A22NL-BMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BMA- (4)(4)A-P(7)(7)(7)-(8)(9)	TR: Transparent, red	002		A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC
	2	A22NL-BMM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-BMA- (4)(4)A-G(7)(7)(7)-(8)(9)		101 102 202	R: Red G: Green Y: Yellow W: White A: Blue O: Orange	
		A22NL-BMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-BMA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow			
Brushed metal bezels	1	A22NL-MMM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MMA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	100		
SOLOIS .	_	A22NL-MMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MMA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	002		
	2	A22NL-MMM- (4)(4)A-G(7)(7)(7)-(8)(9)	A22NL-MMA- (4)(4)A-G(7)(7)(7)-(8)(9)		101 102		
	2	A22NL-MMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A22NL-MMA- (4)(4)A-P(7)(7)(7)-(8)(9)		202		

Note: Normally, the Button and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Button and yellow LED. A22N \(\subseteq - \subseteq \subseteq \) - \(\subseteq \subseteq


[■] Subassemblies: Refer to pages 9 to 11 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 12.

[■] Dimensions: Refer to pages 14 to 16.

[■] Accessories and tools: Refer to pages 80 to 81.

Switch Structure---- You can order Operation Units, LED Lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.



- Subassemblies (Common): Refer to page 78.
- Accessories and tools: Refer to pages 80 to 81.

A22NN/A22NL

Ordering Information

Subassemblies -----You can order Operation Units, LED Lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.

Operation Units

			Plastic, flat		Plastic, projected		
Bezel material and button shape							
	Swit	ch Action	Momentary	Alternate	Momentary	Alternate	
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model	
	Opaque	Red	A22NZ-BNM-NRA	A22NZ-BNA-NRA	A22NZ-BPM-NRA	A22NZ-BPA-NRA	
	Opaque	Green	A22NZ-BNM-NGA	A22NZ-BNA-NGA	A22NZ-BPM-NGA	A22NZ-BPA-NGA	
Non lighted	Opaque	Yellow	A22NZ-BNM-NYA	A22NZ-BNA-NYA	A22NZ-BPM-NYA	A22NZ-BPA-NYA	
Non-lighted	Opaque	White	A22NZ-BNM-NWA	A22NZ-BNA-NWA	A22NZ-BPM-NWA	A22NZ-BPA-NWA	
	Opaque	Blue	A22NZ-BNM-NAA	A22NZ-BNA-NAA	A22NZ-BPM-NAA	A22NZ-BPA-NAA	
	Opaque	Black	A22NZ-BNM-NBA	A22NZ-BNA-NBA	A22NZ-BPM-NBA	A22NZ-BPA-NBA	
	Transparent	Red	A22NZ-BNM-TRA	A22NZ-BNA-TRA	A22NZ-BPM-TRA	A22NZ-BPA-TRA	
	Transparent	Green	A22NZ-BNM-TGA	A22NZ-BNA-TGA	A22NZ-BPM-TGA	A22NZ-BPA-TGA	
Limbtod	Transparent	Yellow	A22NZ-BNM-TYA	A22NZ-BNA-TYA	A22NZ-BPM-TYA	A22NZ-BPA-TYA	
Lighted	Transparent	White	A22NZ-BNM-TWA	A22NZ-BNA-TWA	A22NZ-BPM-TWA	A22NZ-BPA-TWA	
	Transparent	Blue	A22NZ-BNM-TAA	A22NZ-BNA-TAA	A22NZ-BPM-TAA	A22NZ-BPA-TAA	
	Transparent	Orange	A22NZ-BNM-TOA	A22NZ-BNA-TOA	A22NZ-BPM-TOA	A22NZ-BPA-TOA	

			Plastic, full-guard		Plastic, mushroom	
Bezel material and button shape						
	Swit	tch Action	Momentary	Alternate	Momentary	Alternate
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model
	Opaque	Red	A22NZ-BGM-NRA	A22NZ-BGA-NRA	A22NZ-BMM-NRA	A22NZ-BMA-NRA
	Opaque	Green	A22NZ-BGM-NGA	A22NZ-BGA-NGA	A22NZ-BMM-NGA	A22NZ-BMA-NGA
Non-lighted	Opaque	Yellow	A22NZ-BGM-NYA	A22NZ-BGA-NYA	A22NZ-BMM-NYA	A22NZ-BMA-NYA
Non-lighted	Opaque	White	A22NZ-BGM-NWA	A22NZ-BGA-NWA	A22NZ-BMM-NWA	A22NZ-BMA-NWA
	Opaque	Blue	A22NZ-BGM-NAA	A22NZ-BGA-NAA	A22NZ-BMM-NAA	A22NZ-BMA-NAA
	Opaque	Black	A22NZ-BGM-NBA	A22NZ-BGA-NBA	A22NZ-BMM-NBA	A22NZ-BMA-NBA
	Transparent	Red	A22NZ-BGM-TRA	A22NZ-BGA-TRA	A22NZ-BMM-TRA	A22NZ-BMA-TRA
	Transparent	Green	A22NZ-BGM-TGA	A22NZ-BGA-TGA	A22NZ-BMM-TGA	A22NZ-BMA-TGA
Limbtod	Transparent	Yellow	A22NZ-BGM-TYA	A22NZ-BGA-TYA	A22NZ-BMM-TYA	A22NZ-BMA-TYA
Lighted	Transparent	White	A22NZ-BGM-TWA	A22NZ-BGA-TWA	A22NZ-BMM-TWA	A22NZ-BMA-TWA
	Transparent	Blue	A22NZ-BGM-TAA	A22NZ-BGA-TAA	A22NZ-BMM-TAA	A22NZ-BMA-TAA
	Transparent	Orange	A22NZ-BGM-TOA	A22NZ-BGA-TOA	A22NZ-BMM-TOA	A22NZ-BMA-TOA

- Model numbers of sets: Refer to pages 5 to 8.
- Subassemblies (Common): Refer to page 78.
- Specifications: Refer to page 12.
- Dimensions: Refer to pages 14 to 16.
- Accessories and tools: Refer to pages 80 to 81.

Subassemblies -----You can order Operation Units, LED Lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.

			Brushed metal, flat		Brushed metal, projected	
Beze	I material and but	ton shape		0		
	Swit	ch Action	Momentary	Alternate	Momentary	Alternate
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model
	Opaque	Red	A22NZ-MNM-NRA	A22NZ-MNA-NRA	A22NZ-MPM-NRA	A22NZ-MPA-NRA
	Opaque	Green	A22NZ-MNM-NGA	A22NZ-MNA-NGA	A22NZ-MPM-NGA	A22NZ-MPA-NGA
Nam limbtod	Opaque	Yellow	A22NZ-MNM-NYA	A22NZ-MNA-NYA	A22NZ-MPM-NYA	A22NZ-MPA-NYA
Non-lighted	Opaque	White	A22NZ-MNM-NWA	A22NZ-MNA-NWA	A22NZ-MPM-NWA	A22NZ-MPA-NWA
	Opaque	Blue	A22NZ-MNM-NAA	A22NZ-MNA-NAA	A22NZ-MPM-NAA	A22NZ-MPA-NAA
	Opaque	Black	A22NZ-MNM-NBA	A22NZ-MNA-NBA	A22NZ-MPM-NBA	A22NZ-MPA-NBA
	Transparent	Red	A22NZ-MNM-TRA	A22NZ-MNA-TRA	A22NZ-MPM-TRA	A22NZ-MPA-TRA
	Transparent	Green	A22NZ-MNM-TGA	A22NZ-MNA-TGA	A22NZ-MPM-TGA	A22NZ-MPA-TGA
11.14.4	Transparent	Yellow	A22NZ-MNM-TYA	A22NZ-MNA-TYA	A22NZ-MPM-TYA	A22NZ-MPA-TYA
Lighted	Transparent	White	A22NZ-MNM-TWA	A22NZ-MNA-TWA	A22NZ-MPM-TWA	A22NZ-MPA-TWA
	Transparent	Blue	A22NZ-MNM-TAA	A22NZ-MNA-TAA	A22NZ-MPM-TAA	A22NZ-MPA-TAA
	Transparent	Orange	A22NZ-MNM-TOA	A22NZ-MNA-TOA	A22NZ-MPM-TOA	A22NZ-MPA-TOA

			Brushed metal, full-guard		Brushed metal, mushroom		
Beze	el material and but	ton shape					
	Swit	tch Action	Momentary	Alternate	Momentary	Alternate	
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model	
	Opaque	Red	A22NZ-MGM-NRA	A22NZ-MGA-NRA	A22NZ-MMM-NRA	A22NZ-MMA-NRA	
	Opaque	Green	A22NZ-MGM-NGA	A22NZ-MGA-NGA	A22NZ-MMM-NGA	A22NZ-MMA-NGA	
Non-lighted	Opaque	Yellow	A22NZ-MGM-NYA	A22NZ-MGA-NYA	A22NZ-MMM-NYA	A22NZ-MMA-NYA	
Non-lighted	Opaque	White	A22NZ-MGM-NWA	A22NZ-MGA-NWA	A22NZ-MMM-NWA	A22NZ-MMA-NWA	
	Opaque	Blue	A22NZ-MGM-NAA	A22NZ-MGA-NAA	A22NZ-MMM-NAA	A22NZ-MMA-NAA	
	Opaque	Black	A22NZ-MGM-NBA	A22NZ-MGA-NBA	A22NZ-MMM-NBA	A22NZ-MMA-NBA	
	Transparent	Red	A22NZ-MGM-TRA	A22NZ-MGA-TRA	A22NZ-MMM-TRA	A22NZ-MMA-TRA	
	Transparent	Green	A22NZ-MGM-TGA	A22NZ-MGA-TGA	A22NZ-MMM-TGA	A22NZ-MMA-TGA	
Lightod	Transparent	Yellow	A22NZ-MGM-TYA	A22NZ-MGA-TYA	A22NZ-MMM-TYA	A22NZ-MMA-TYA	
Lighted	Transparent	White	A22NZ-MGM-TWA	A22NZ-MGA-TWA	A22NZ-MMM-TWA	A22NZ-MMA-TWA	
	Transparent	Blue	A22NZ-MGM-TAA	A22NZ-MGA-TAA	A22NZ-MMM-TAA	A22NZ-MMA-TAA	
	Transparent	Orange	A22NZ-MGM-TOA	A22NZ-MGA-TOA	A22NZ-MMM-TOA	A22NZ-MMA-TOA	

[■] Model numbers of sets: Refer to pages 5 to 8.

[■] Subassemblies (Common): Refer to page 78.

[■] Specifications: Refer to page 12.

[■] Dimensions: Refer to pages 14 to 16.

[■] Accessories and tools: Refer to pages 80 to 81.

A22NN/A22NL

Specifications

Certified Safety Standard Ratings

UL508 Type 4X, 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC

TÜV (EN60947-5-1)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

CCC (GB/T14048.5)

AC-15 3 A 240 VAC DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation volt	age	600 V						
Rated carry current		10 A	10 A					
Rated voltage		24 V	120 V	240 V	380 V	440 V		
AC at 50/60 Hz	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A		
AC at 50/60 HZ	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A		
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A				
	Inductive load (DC-13)	4 A	1.1 A	0.55 A				

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute
 2. Minimum applicable load: 10 mA at 5 VDC.

LED Lamps

Rated voltage	Applied voltage	Rated current
6 VAC/DC	6 VAC/DC ±10%	Approx. 11 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
12 VAC/DC	12 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
24 VAC/DC	24 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
100 VAC	100 VAC ±10%	
110 VAC	110 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
120 VAC	100 to 130 VAC	7 Approx. o Hist (write of grooti)
200 VAC	200 VAC ±10%	
220 VAC	220 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue)
230 VAC	230 VAC ±10%	Approx. 5 mA (white or green)
240 VAC	220 to 250 VAC	

Specifications

Characteristics

Туре		Pushbutton Switches		
Item		Non-lighted models	Lighted models	
Allowable operating	Mechanical	60 operations/minute max.		
frequency	Electrical	30 operations/minute max.		
Insulation resistance		100 MΩ min. (at 500 VDC)	Not available for lighting units	
Contact resistance		100 mΩ max. (initial value)		
Dielectric strength	Between terminals of same polarity	2,500 VAC at 50/60 Hz for 1 min. (initial value)	Not available for lighting units	
	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial	al value)	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude	(malfunction within 1 ms)	
Shock resistance	Malfunction	1,000 m/s² max. (malfunction within 1 ms)		
Mechanical		Momentary action: 5,000,000 operations min. Alternate action: 500,000 operations min.		
Durability	Electrical	500,000 operations min. (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)		
Ambient operating ten	nperature*1	−25 to 70°C	−25 to 55°C	
Ambient operating hur	nidity	35% to 85% RH		
Ambient storage temp	erature* ¹	−40 to 80°C		
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 4X, 13		
Electric shock protection class		Class II		
PTI (tracking characteristic)		175		
Degree of contaminati	on (application environment)	3 (EN 60947-5-1)		
Weight		Approx. 50 g (for 1NC/1NO)	Approx. 65 g (for 1NC/1NO)	

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Pushbutton Switches
Item	Lighted/non-lighted
Total travel force (torque) (maximum TTF)	18 N
Total travel (TT)	6 mm max.
Resetting force (torque) (RF)	

Examples of Linked Contact Blocks (Screw terminal block type)

Contact Blocks	Lighting Units
Contact Blocks	Lighting Units

	Pushbutton Switches				
	Mome	entary	Alternate		
	Lighted	Non-lighted	Lighted	Non-lighted	
Linking example	Operation Unit Mounting Collar OBES OBE	Operation Unit Mounting Collar	Operation Unit	Operation Unit Mounting Collar	
				Operation Unit Mounting Collar	

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.


^{*1.} With no icing or condensation.
*2. Degree of protection from the front of the panel.

Indicators M22N


A22NN/A22NL

Dimensions (Unit: mm)


Lighted and Non-lighted Pushbutton Switches



A22NL-BN□-T□A-G□-□□









Projected Switches with Plastic Bezels A22N□-**BP**□-□**A**-**G**□-□□






A22N□-**BP**□-□**A**-**P**□-□□






Full-guard Switches with Plastic Bezels








A22N□-**BG**□-□**A**-**P**□-□□






Mushroom Switches with Plastic Bezels


 $A22N \square -BM \square - \square A -G \square - \square \square$





A22N□-**BM**□-□**A**-**P**□-□□






Dimensions (Unit: mm)

Flat Switches with Brushed Metal Bezels


A22NN-MN□-N□A-G□-NN

A22NN-MN□-N□A-P□-NN




A22NL-MN□-T□A-G□-□□





A22NL-MN□-T□A-P□-□□






Projected Switches with Brushed Metal Bezels


A22N□-MP□-□A-G□-□□












Full-guard Switches with Brushed Metal Bezels


A22N□-MG□-□A-G□-□□












Mushroom Switches with Brushed Metal Bezels


A22N□-MM□-□**A**-**G**□-□□














Depth with Linked Units (Screw terminal block type)



Depth when a double-contact unit is mounted (Push-In Plus terminal block type)



Terminal Arrangement BOTTOM VIEW (Screw terminal block type)



Terminal Connection Diagrams

Non-limbted Conitabae (ONO/ANO)	Limbted Societables (ANO(ANO)
Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102
Bottom View	Bottom View
	(X) (3) (ED) (LED) (Lamp)


Note: The above shows a terminal connection diagram for a screw terminal block type.

BOTTOM VIEW (Push-In Plus terminal block type)

Non-lighted Switches

(2NO/1NC) Contact configuration code:112	Contact configuration code:102
20 10 -10 - No No 31.9 Contact Blocks	Lighting Unit Lighting Unit 31.9 Contact Blocks
*	Contact Blocks

Double-contact unit Non-lighted (2NO/2NO/2NC)



Selector Switches

A22NS/A22NW

22-mm dia. Knob-type Selector Switches
Control panel miniaturization through a more
compact design and modified wiring
direction.

Addition of Push-In Plus terminal blocks for easy wiring.







Easy to Use

- Improved wiring visibility through to a modified wiring direction. (Push-In Plus terminal block type)
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)
- The terminals can be secured even when a contact block is mounted. (Screw terminal block type)

Miniaturization

- No need for extra lateral space because of the modified wiring direction.
 (Push-In Plus terminal block type)
- · Compact design.
- A22NW (lighted models) are the same size as A22NS (non-lighted models).

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenance-free use. (Push-In Plus terminal block type)

Product Lineup

- Meets global safety standards.
- Can be installed in two types of panel hole dimensions: 22.3 and 25.5 dia.
- The buttons and bezels come in a wide variety of colors, shapes, and materials.
- Compliant with IEC IP66, Certified for UL508 Type 4X, 13.

Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 85.

Operation Unit Colors

			Red	Green	Black				
Non-lighted Switches	A22NS-□□□ Opaque		•	•	•				
			Red	Green	Yellow	White	Blue	Orange	White
Lightod	Lighted A22NW-□□-T□ Switches Transparent	When not lit	•	•		•	•	•	•
			Red	Green	Yellow	White	Blue	Orange	Opaque white*
	When lit				•			•	

^{*} The colors when the Switches are lit are for transparent white Operation Units (code: TW) and yellow LED Lamps (code: Y).

List of Models

	Screw Terminal Blocks	/Push-In Plus Terminal Blocks	
	Pla	stic bezels	
A22N	S-□B	A22N	W-□B
Non-lighted Two Positions	Three Positions	Lighted Two Positions	Three Positions
		/Push-In Plus Terminal Blocks	
	Brushe	d Metal bezels	
A22N	S-□M	A22N	W-□M
Non-lighted Two Positions	Three Positions	Lighted Two Positions	Three Positions

A22NS/A22NW

Model Number Structure

Model Number Legend - - Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

For information on combinations, refer to Ordering Information on pages 23 to 24.

Model Numbers for Sets

G 101 - R A NRA 2 B M

(1) Type

Code	Туре
S	Non-lighted
W	Lighted

(5) Degree of Protection

Code	Protection
Α	Compliant with IEC IP66, Certified for UL508 Type 4X, 13

(6) Contacts and Terminals Specifications

Code Specification						
	G	General/Screw Terminal Block				
	Р	General/Push-In Plus Terminal Block				

Lighted

3

NC

NC

NO

NC

No. of positions

positions

Yes

Yes

Yes

Yes

positions

Yes

Yes

Yes

Unit position

2

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

(2) Number of Positions and Bezel Material

()										
Code	No. of positions	Bezel material								
2B	2	Plastic								
2M	2	Brushed metal								
3B	3	Plastic								
3M	3	Brushed metal								

(3) Reset Method

(3) Reset Method												
Code	Reset method											
М	Manual	Two-position manual										
IVI	Mariuai	Three-position manual										
	Automatic	Two-position automatic										
L	reset on left	Three-position left automatic										
R	Automatic reset on right	Three-position right automatic										
В	Automatic reset on left and right	Three-position left or right automatic	***									

(4) Operation Unit Transparency and Color and (8) LED Lamp Color

			` ,		
Lighted/ non- lighted	Code (4)	Code (8)	Transparency	Opera- tion Unit color	LED Lamp color
	NR			Red	
Non- lighted	NG	N	Opaque	Green	
gou	NB			Black	
	TR	R		Red	Red
	TG	G		Green	Green
	TY	Υ		Yellow	Yellow
Lighted	TW	W	Transparent	White	White
	TA	Α		Blue	Blue
	TO O			Orange	Orange
	TW	Υ		White*	Yellow

^{*} The color is opaque white when the Switch is lit.

(7) Contact Configuration

		Contact Non-lighted							
_	Code		cks	Unit	t posi	tion	No posi	. of tions	
_		NO	NC	1	2	3	Two positions	Three positions	1
-	100	1	0	NO			Yes		NO
	002	0	1			NC	Yes		
	101	2	0	NO		NO	Yes	Yes	NO
	102	1	1	NO		NC	Yes	Yes	NO
	201	1	1	NC		NO		Yes	NC
	202	0	2	NC		NC	Yes	Yes	NC
	110	2	0	NO	NO			Yes	
	111	3	0	NO	NO	NO	Yes	Yes	
	112	2	1	NO	NO	NC	Yes	Yes	
	210	1	1	NC	NO			Yes	
	211	2	1	NC	NO	NO		Yes	
	212	1	2	NC	NO	NC		Yes	
	011	2	0		NO	NO		Yes	
	012	1	1		NO	NC		Yes	
	120	1	1	NO	NC			Yes	
ı	121	2	1	NO	NC	NO		Yes	
_	122	1	2	NO	NC	NC	Yes	Yes	
•	220	0	2	NC	NC			Yes	
	221	1	2	NC	NC	NO		Yes	
	222	0	3	NC	NC	NC	Yes	Yes	
	021	1	1		NC	NO		Yes	
_	022	0	2		NC	NC		Yes	
_								· . — — —	

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.

2. Refer to the following figure for the Unit positions.



(9) LED Lamp Voltage

Code	LED Lamp voltage
N	Non-lighted
Α	6 VAC/DC
В	12 VAC/DC
С	24 VAC/DC
D	100/110/120 VAC
Е	200/220/230/240 VAC

- Specifications: Refer to page 12
- Dimensions: Refer to page 30.


- Characteristics: Refer to page 29.
- Precautions for correct use: Refer to pages 85 to 96.

Structure

Contact Configuration Table Two Positions

No. of		Contact	Unit		Pos	ition
outputs	Code	configuration	position	Contacts	1	2
			1	NO		ON
1	100	SPST-NO	2		-	
			3			
			1			
1	002	SPST-NC	2			
			3	NC	ON	
		ODOT NO	1	NO		ON
2	102	SPST-NO/ SPST-NC	2			
		3, 3, 1,	3	NC	ON	
	101	101 DPST-NO	1	NO		ON
2			2			
			3	NO		ON
	202	DPST-NC	1	NC	ON	
2			2			
			3	NC	ON	
			1	NO		ON
3	111	3PST-NO	2	NO		ON
			3	NO		ON
			1	NC	ON	
3	222	3PST-NC	2	NC	ON	
			3	NC	ON	
		ODOT NO	1	NO		ON
3	122	SPST-NO/ DPST-NC	2	NC	ON	
		3. 33	3	NC	ON	
		DDOT NG	1	NO		ON
3	112	DPST-NO/ SPST-NC	2	NO		ON
		31 31-110	3	NC	ON	

Operation Angle



Three Positions

No. of	Code	Contact	Unit	Contacts		Position			
outputs	Code	configuration	position		1	0	2		
			1	NO	ON				
2	110	DPST-NO	2	NO	ON		ON		
			3						
			1						
2	011	11 DPST-NO	2	NO	ON		ON		
			3	NO			ON		
	101				1	NO	ON		
2		DPST-NO	2						
			3	NO			ON		
		220 DPST-NC	1	NC		ON	ON		
2	220		2	NC		ON			
			3						
			1						
2	022	022 DPST-NC	2	NC		ON			
			3	NC	ON	ON			


						Danition	
No. of outputs	Code	Contact configuration	Unit position	Contacts	1	Position 0	2
- Carpaio		- Comiguration	1	NC		ON	ON
2	202	DPST-NC	2				
_		DI 01 140	3	NC	ON	ON	
			1	NO	ON	0.1	
2	120	SPST-NO/	2	NC	3. .	ON	
	120	SPST-NC	3				
			1	NO	ON		
2	102	SPST-NO/	2				
		SPST-NC	3	NC	ON	ON	
			1	NC		ON	ON
2	210	SPST-NO/ SPST-NC	2	NO	ON		ON
		SPST-NC	3				
			1	NC		ON	ON
2	201	SPST-NO/ SPST-NC	2				
		SPST-NC	3	NO			ON
			1				
2	012	SPST-NO/ SPST-NC	2	NO	ON		ON
		SPS1-NC	3	NC	ON	ON	
2			1		-		
	021	SPST-NO/ SPST-NC	2	NC		ON	
			3	NO			ON
	111		1	NO	ON		
3		3PST-NO	2	NO	ON		ON
			3	NO			ON
			1	NC		ON	ON
3	222	3PST-NC	2	NC		ON	
			3	NC	ON	ON	
		ODOT NO	1	NO	ON		
3	122	SPST-NO/ DPST-NC	2	NC		ON	
			3	NC	ON	ON	
		SPST-NO/	1	NC		ON	ON
3	212	DPST-NC	2	NO	ON		ON
			3	NC	ON	ON	
		SPST-NO/	1	NC		ON	ON
3	221	DPST-NC	2	NC		ON	
			3	NO			ON
		DPST-NO/	1	NC		ON	ON
3	211	SPST-NC/	2	NO	ON		ON
			3	NO			ON
		DPST-NO/	1	NO	ON		
3	121	SPST-NC/	2	NC		ON	
		-	3	NO			ON
		DPST-NO/	1	NO	ON		
3	112	SPST-NC/	2	NO	ON		ON
	l .	1	^	NO	ON	ON.	1

ON

NC

ON

Operation Angle



Model Numbers for Sets ----Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. **Non-lighted, Two-position, Selector Switches**

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact configuration
Plastic bezels		1	A22NS-2B(3)-(4)(4)A-G(7)(7)(7)-NN			100
		'	A22NS-2B(3)-(4)(4)A-P(7)(7)(7)-NN			002
			A22NS-2B(3)-(4)(4)A-G(7)(7)(7)-NN			102
	2B	2	A22NS-2B(3)-(4)(4)A-P(7)(7)(7)-NN		NR: Opaque red NG: Opaque green NY: Opaque yellow	101 202
W. C.			A22NS-2B(3)-(4)(4)A-G(7)(7)(7)-NN	M: Manual		111 222
		3	A22NS-2B(3)-(4)(4)A-P(7)(7)(7)-NN			122 112
Brushed metal bezels		4	A22NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN	L: Automatic reset on left		100
		1	A22NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			002
			A22NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN			102
	2M	2	A22NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			101 202
The state of the s			A22NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN			111 222
-		3	A22NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			122 112

Non-lighted, Three-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact configuration
Plastic bezels		2	A22NS-3B(3)-(4)(4)A-G(7)(7)(7)-NN			110 011 101 220 022 202
	3В	-	A22NS-3B(3)-(4)(4)A-P(7)(7)(7)-NN			120 102 210 201 012 021
	3M	3	A22NS-3B(3)-(4)(4)A-G(7)(7)(7)-NN		NR: Opaque red NG: Opaque green NY: Opaque yellow	111 222 122 212
			A22NS-3B(3)-(4)(4)A-P(7)(7)(7)-NN	M: Manual L: Automatic reset on left R: Automatic reset on		221 211 121 112
Brushed metal bezels		2 3M	A22NS-3M(3)-(4)(4)A-G(7)(7)(7)-NN	right B: Automatic reset on left and right		110 011 101 220 022 202
			A22NS-3M(3)-(4)(4)A-P(7)(7)(7)-NN			120 102 210 201 012 021
		3	A22NS-3M(3)-(4)(4)A-G(7)(7)(7)-NN			111 222 122 212
			A22NS-3M(3)-(4)(4)A-P(7)(7)(7)-NN			221 211 121 112

A22NS/A22NW

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp, Mounting Collar, Contact Block, and Lighting Unit.

Lighted, Two-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact Configuration	(8) LED Lamp color	(9) LED Lamp voltage	
Plastic bezels		4	A22NW-2B(3)- (4)(4)A-G(7)(7)(7)-(8)(9)			100			
	2B	•	A22NW-2B(3)- (4)(4)A-P(7)(7)(7)-(8)(9)		TR: Transparent red TG: Transparent green TY: Transparent yellow	002		A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120	
	25	2	A22NW-2B(3)- (4)(4)A-G(7)(7)(7)-(8)(9)	M: Manual		102 101	R: Red G: Green Y: Yellow		
			A22NW-2B(3)- (4)(4)A-P(7)(7)(7)-(8)(9)			202			
Brushed metal bezels			1	A22NW-2M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)	reset on left	TW: Transparent white TA: Transparent blue	100	A: Blue O: Orange	VAC E: 200/220/230/
		'	A22NW-2M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)		TO: Transparent orange	002 W	W: White	240 VAC	
	ZIVI	2M 2	A22NW-2M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)			102			
			A22NW-2M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)			101 202			

Lighted, Three-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact Configuration	(8) LED Lamp color	(9) LED Lamp voltage
Plastic bezels								
	3B	2	A22NW-3B(3)- (4)(4)A-G(7)(7)(7)-(8)(9)			101 202		
	35		A22NW-3B(3)- (4)(4)A-P(7)(7)(7)-(8)(9) M: Manual L: Automatic reset on left R: Automatic	TR: Transparent red TG: Transparent green TY: Transparent yellow	102 201	R: Red G: Green Y: Yellow A: Blue O: Orange W: White	A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/ 240 VAC	
Brushed metal bezels		A22NW-3M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)	reset on right B: Automatic reset on left and right		101 202			
	3M	2	A22NW-3M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)			102 201		

Note: Normally, the Operation Unit and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Operation Unit and yellow LED. A22N \(\text{-} \subseteq \text{-} \subseteq \text{-} \subseteq \text{-} \subseteq \subseteq \text{-} \subseteq \text{-} \subseteq \subseteq \subseteq \text{-} \subseteq \subseteq \subseteq \subseteq \subseteq \subseteq \text{-} \subseteq \subseteq

■ Subassemblies: Refer to pages 25 to 27 and 78.


(You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 12 ■ Characteristics: Refer to page 29.

[■] Dimensions: Refer to page 30.

[■] Accessories and tools: Refer to pages 80 to 81.

Subassemblies ----You can order Operation Units, LED Lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.



A22NS/A22NW

Ordering Information

Subassemblies -----

 You can order Operation Units, Mounting Collars, and Contact Blocks individually. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.

Operation Unit Non-lighted Switches

			Plastic	Brushed metal
	Bezel ma	terial and shape		
No. of positions	Reset method	Operation Unit color	Model	Model
2	Manual		A22NZ-2BM-NRA	A22NZ-2MM-NRA
	Automatic reset on left		A22NZ-2BL-NRA	A22NZ-2ML-NRA
	Manual	Opaque red	A22NZ-3BM-NRA	A22NZ-3MM-NRA
3	Automatic reset on left		A22NZ-3BL-NRA	A22NZ-3ML-NRA
3	Automatic reset on right		A22NZ-3BR-NRA	A22NZ-3MR-NRA
	Automatic reset on left and right		A22NZ-3BB-NRA	A22NZ-3MB-NRA
2	Manual		A22NZ-2BM-NGA	A22NZ-2MM-NGA
	Automatic reset on left		A22NZ-2BL-NGA	A22NZ-2ML-NGA
	Manual	Opaque	A22NZ-3BM-NGA	A22NZ-3MM-NGA
3	Automatic reset on left	green	A22NZ-3BL-NGA	A22NZ-3ML-NGA
3	Automatic reset on right		A22NZ-3BR-NGA	A22NZ-3MR-NGA
	Automatic reset on left and right		A22NZ-3BB-NGA	A22NZ-3MB-NGA
2	Manual		A22NZ-2BM-NBA	A22NZ-2MM-NBA
2	Automatic reset on left		A22NZ-2BL-NBA	A22NZ-2ML-NBA
	Manual	Opaque	A22NZ-3BM-NBA	A22NZ-3MM-NBA
3	Automatic reset on left	black	A22NZ-3BL-NBA	A22NZ-3ML-NBA
3	Automatic reset on right		A22NZ-3BR-NBA	A22NZ-3MR-NBA
	Automatic reset on left and right		A22NZ-3BB-NBA	A22NZ-3MB-NBA

[■] Model numbers of sets: Refer to pages 23 to 24.

[■] Specifications: Refer to page 12.

[■] Characteristics: Refer to page 29.

[■] Dimensions: Refer to page 30.

[■] Subassemblies (Common): Refer to page 78.

[■] Accessories and tools: Refer to pages 80 to 81.

Subassemblies ---

- You can order Operation Units, LED Lamps, Mounting Collars, Contact Blocks, and Lighting Units separately.
 Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.

Lighted Switches

			Plastic	Brushed metal
	Bezel ma	terial and shape		
No. of positions	Reset method	Operation Unit color	Model	Model
2	Manual		A22NZ-2BM-TRA	A22NZ-2MM-TRA
	Automatic reset on left		A22NZ-2BL-TRA	A22NZ-2ML-TRA
	Manual	Transparent	A22NZ-3BM-TRA	A22NZ-3MM-TRA
3	Automatic reset on left	red	A22NZ-3BL-TRA	A22NZ-3ML-TRA
	Automatic reset on right		A22NZ-3BR-TRA	A22NZ-3MR-TRA
	Automatic reset on left and right		A22NZ-3BB-TRA	A22NZ-3MB-TRA
2	Manual		A22NZ-2BM-TGA	A22NZ-2MM-TGA
_	Automatic reset on left		A22NZ-2BL-TGA	A22NZ-2ML-TGA
	Manual	Transparent	A22NZ-3BM-TGA	A22NZ-3MM-TGA
3	Automatic reset on left	green	A22NZ-3BL-TGA	A22NZ-3ML-TGA
	Automatic reset on right		A22NZ-3BR-TGA	A22NZ-3MR-TGA
	Automatic reset on left and right		A22NZ-3BB-TGA	A22NZ-3MB-TGA
2	Manual	Transparent yellow	A22NZ-2BM-TYA	A22NZ-2MM-TYA
	Automatic reset on left		A22NZ-2BL-TYA	A22NZ-2ML-TYA
	Manual		A22NZ-3BM-TYA	A22NZ-3MM-TYA
3	Automatic reset on left		A22NZ-3BL-TYA	A22NZ-3ML-TYA
3	Automatic reset on right		A22NZ-3BR-TYA	A22NZ-3MR-TYA
	Automatic reset on left and right		A22NZ-3BB-TYA	A22NZ-3MB-TYA
2	Manual		A22NZ-2BM-TWA	A22NZ-2MM-TWA
	Automatic reset on left		A22NZ-2BL-TWA	A22NZ-2ML-TWA
	Manual	Transparent	A22NZ-3BM-TWA	A22NZ-3MM-TWA
3	Automatic reset on left	white	A22NZ-3BL-TWA	A22NZ-3ML-TWA
3	Automatic reset on right		A22NZ-3BR-TWA	A22NZ-3MR-TWA
	Automatic reset on left and right		A22NZ-3BB-TWA	A22NZ-3MB-TWA
2	Manual		A22NZ-2BM-TAA	A22NZ-2MM-TAA
	Automatic reset on left		A22NZ-2BL-TAA	A22NZ-2ML-TAA
	Manual	Transparent	A22NZ-3BM-TAA	A22NZ-3MM-TAA
3	Automatic reset on left	blue	A22NZ-3BL-TAA	A22NZ-3ML-TAA
3	Automatic reset on right		A22NZ-3BR-TAA	A22NZ-3MR-TAA
	Automatic reset on left and right		A22NZ-3BB-TAA	A22NZ-3MB-TAA
2	Manual		A22NZ-2BM-TOA	A22NZ-2MM-TOA
	Automatic reset on left		A22NZ-2BL-TOA	A22NZ-2ML-TOA
	Manual	Transparent	A22NZ-3BM-TOA	A22NZ-3MM-TOA
3	Automatic reset on left	orange	A22NZ-3BL-TOA	A22NZ-3ML-TOA
3	Automatic reset on right		A22NZ-3BR-TOA	A22NZ-3MR-TOA
—	Automatic reset on left and right		A22NZ-3BB-TOA	A22NZ-3MB-TOA

[■] Model numbers of sets: Refer to pages 23 to 24.

[■] Specifications: Refer to page 12.

[■] Characteristics: Refer to page 29.

[■] Dimensions: Refer to page 30.

[■] Subassemblies (Common): Refer to page 78.

[■] Accessories and tools: Refer to pages 80 to 81.

A22NS/A22NW

Specifications

Certified Safety Standard Ratings

UL508 Type 4X, 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC

TÜV (EN60947-5-1)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

CCC (GB/T14048.5)

AC-15 3 A 240 VAC DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation volta	age	600 V				
Rated carry current		10 A				
Rated voltage		24 V	120 V	240 V	380 V	440 V
AC at 50/60 Hz	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A
	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A		
	Inductive load (DC-13)	4 A	1.1 A	0.55 A		

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute

 2. Minimum applicable load: 10 mA at 5 VDC.

LED Lamps

<u> </u>		
Rated voltage	Applied voltage	Rated current
6 VAC/DC	6 VAC/DC ±10%	Approx. 11 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
12 VAC/DC	12 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
24 VAC/DC	24 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
100 VAC	100 VAC ±10%	
110 VAC	110 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
120 VAC	100 to 130 VAC	Typrox. o mix (winte or groom)
200 VAC	200 VAC ±10%	
220 VAC	220 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue)
230 VAC	230 VAC ±10%	Approx. 5 mA (white or green)
240 VAC	220 to 250 VAC	

Specifications

Characteristics

Туре		Selector Switches				
Item		Non-lighted models	Lighted models			
Allowable operating	Mechanical	30 operations/minute max.				
frequency	Electrical	30 operations/minute max.				
Insulation resistance		100 MΩ min. (at 500 VDC)	Not available for lighting units			
Contact resistance		100 mΩ max. (initial value)				
Dielectric strength	Between terminals of same polarity	2,500 VAC at 50/60 Hz for 1 min. (initial value)	Not available for lighting units			
	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial value)				
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)				
Shock resistance	Malfunction	1,000 m/s² max. (malfunction within 1 ms)				
	Mechanical	500,000 operations min. (Switches with 3 positions: 300,000 operations				
Durability	Electrical	500,000 operations min. (Switches with 3 positions: 300,000 operations m (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)				
Ambient operating tem	perature*1	−25 to 70°C	−25 to 55°C			
Ambient operating hum	nidity	35% to 85% RH				
Ambient storage tempe	rature*1	-40 to 80°C				
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 4X, 13				
Electric shock protection class		Class II				
PTI (tracking characteristic)		175				
Degree of contamination (application environment)		3 (EN 60947-5-1)				
Weight		Approx. 50 g (for 1NC/1NO)	Approx. 60 g (for 1NC/1NO)			

^{*1.} With no icing or condensation.

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Selector	Switches	
Item	Manual reset	Automatic reset	
Total travel force (torque) (maximum TTF)	0.6 N·m	0.6 N·m	
Total travel (TT)	2 positions: Approx. 90°, 3 positions: Approx. 45°		
Resetting force (torque) (RF)	0.5 N·m max.		

Examples of Linked Contact Blocks (Screw terminal block type)

Contact Blocks

-	Lighting	Units
- 1	Lighting	Office

		Selector Switches					
	2 pos	itions	3 pos	itions			
	Lighted	Non-lighted	Lighted	Non-lighted			
Linking example	Operation Unit Mounting Collar	Operation Unit Mounting Collar Operation Unit Mounting Collar *	Operation Unit Mounting Collar	Operation Unit Mounting Collar			

^{*} If you use three Contact Blocks in stage 1, you can add one more Contact Block in the middle of stage 2.

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.

^{*2.} Degree of protection from the front of the panel.


A22NS/A22NW

Dimensions (Unit: mm)

Lighted and Non-lighted Selection Switches


Two-position Switches with Plastic Bezels A22N□-2B□-□□A-G






A22N□-2B□-□□A-P







Three-position Switches with Plastic Bezels A22N□-3B□-□□A-G □□




A22N□-3B□-□□A-P






Two-position Switches with Brushed Metal Bezels A22N□-2M□-□□A-G







A22N□-2M□-□□A-P







Three-position Switches with Brushed Metal Bezels A22N□-3M□-□□A-G






A22N□-3M□-□□A-P






Depth with Linked Units (Screw terminal block type)



Depth when a double-contact unit is mounted (Push-In Plus terminal block type)



Terminal Arrangement BOTTOM VIEW (Screw terminal block type)

Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102
Contact Blocks DS DS DS Six M3.5 Phillips/slotted/screws	Six, M3.5 Phillips/slotted screws Contact Blocks

Terminal Connection Diagrams

	•
Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102
Bottom View	Bottom View
	① X)— 3 X)— LED Lamp 2 X2— 4

Note: The above shows a terminal connection diagram for a screw terminal block type.

BOTTOM VIEW (Push-In Plus terminal block type)

Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configurationcode:102	Double-contact unit Non-lighted (2NO/2NO/2NC)
20 10 - 10 - 10 - 10 - 10 - 10 - 10 - 10 -	Lighting Unit Lighting Unit No. 31.9 Contact Blocks	19.0 38.6

OMRON

Key-type Selector Switches A 22 N K

22-mm dia. Key-type Selector Switches
Control panel miniaturization through a more
compact design and modified wiring direction.
Addition of Push-In Plus terminal blocks for easy
wiring.

C UL US LISTED TO SEE









Easy to Use

- You can connect up to three Contact Blocks in one stage for multistage expansion.
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)
- The terminals can be secured even when a contact block is mounted. (Screw terminal block type)
- · Contact Blocks can be attached in any direction for easy assembly.

Miniaturization

- No need for extra lateral space because of the modified wiring direction. (Push-In Plus terminal block type)
- · Compact design.

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenancefree use. (Push-In Plus terminal block type)

Product Lineup

- Meet global safety standards.
- Can be installed in two types of panel hole dimensions: 22.3 and 25.5 dia.
- The buttons and bezels come in a wide variety of colors, shapes, and materials.
- Compliant with IEC IP66, Certified for UL508 Type 13.



Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 85.

List of Models

Screw Terminal Blocks/Push-In Plus Terminal Blocks

Plastic bezels

A22NK-□B

Three Positions





Screw Terminal Blocks/Push-In Plus Terminal Blocks

Brushed metal bezels

A22NK-□M

Two Positions

Three Positions





Model Number Structure

Model Number Legend ----- Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. For information on combinations, refer to Ordering Information on page 36.

Model Numbers for Sets

(1) Type

Code

2B

2M

3B

Code	Туре
K	Key-type Selector Switch

Bezel material

Plastic

Brushed metal

Plastic

Brushed metal

Reset method Twopositions manual

Threepositions manual Two-

positions

automatic

Three-

positions left

automatic Three-

positions

right

automatic

Three-

positions left

or right

automatic

Bezel Material

No. of

positions

2

3

(3) Reset Method

Manual

Automatic

Automatic

Automatic

reset on

left and

right

reset on

right

reset on

left

R

(4) Key Number

	Code	No.
-	01	No.1

(2) Number of Positions and (5) Key Release Position *

Code	Release position	Two positions	Three positions
Α	All positions		
В	Left	•	
С	Right	• 0	• • •
D	Center		
G	Left and right		

O: Release position : Locked position The key can only be removed when in the free position for automatic reset models.

(6) Degree of Protection

	Code	Protection
-	Α	Compliant with IEC IP66, Certified for UL508 Type 13

(7) Contacts and Terminals Specifications

Code Specification				
	G	General/Screw Terminal Block		
	Р	General/Push-In Plus Terminal Block		


(8) Contact Configuration

Code	Con	tact cks	Unit	posi	tion	Two	Three	
	NO	NC	1	2	3	positions	positions	
100	1	0	NO			Yes		
002	0	1			NC	Yes		
101	2	0	NO		NO	Yes	Yes	
102	1	1	NO		NC	Yes	Yes	
201	1	1	NC		NO		Yes	
202	0	2	NC		NC	Yes	Yes	
110	2	0	NO	NO			Yes	
111	3	0	NO	NO	NO	Yes	Yes	
112	2	1	NO	NO	NC	Yes	Yes	
210	1	1	NC	NO			Yes	
211	2	1	NC	NO	NO		Yes	
212	1	2	NC	NO	NC		Yes	
011	2	0		NO	NO		Yes	
012	1	1		NO	NC		Yes	
120	1	1	NO	NC			Yes	
121	2	1	NO	NC	NO		Yes	
122	1	2	NO	NC	NC	Yes	Yes	
220	0	2	NC	NC			Yes	
221	1	2	NC	NC	NO		Yes	
222	0	3	NC	NC	NC	Yes	Yes	
021	1	1		NC	NO		Yes	
022	0	2		NC	NC		Yes	

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.


2. Refer to the following figure for Unit positions.

Operation Angle



- Specifications: Refer to page 12.
- Dimensions: Refer to page 41.

- Characteristics: Refer to page 40.
- Precautions for correct use: Refer to pages 85 to 96.



Structure

A22NK

Contact Configuration Table Two Positions


No. of	Code	Contact	Unit	Contacts	Pos	ition
outputs	Code	configuration	position	Contacts	1	2
			1	NO		ON
1	100	SPST-NO	2			
			3			
			1			
1	002	SPST-NC	2			
			3	NC	ON	
		ODOT NO	1	NO		ON
2	102	SPST-NO/ SPST-NC	2			
		3. 3	3	NC	ON	
		01 DPST-NO	1	NO		ON
2	101		2			
			3	NO		ON
2	202	DPST-NC	1	NC	ON	
			2			
			3	NC	ON	
			1	NO		ON
3	111	3PST-NO	2	NO		ON
			3	NO		ON
			1	NC	ON	
3	222	3PST-NC	2	NC	ON	
			3	NC	ON	
		ODOT NO	1	NO		ON
3	122	SPST-NO/ DPST-NC	2	NC	ON	
		2. 23	3	NC	ON	
		DDOT NO	1	NO		ON
3	112	DPST-NO/ SPST-NC	2	NO		ON
3						

3

NC

ON

Operation Angle



Three Positions

SPST-NC

No. of	Code	Contact	Unit	Contacts		Position	
outputs	Code	configuration	position	Contacts	1	0	2
			1	NO	ON		
2	110	DPST-NO	2	NO	ON		ON
			3				
			1				
2	011	DPST-NO	2	NO	ON		ON
			3	NO			ON
	101		1	NO	ON		
2		DPST-NO	2				
			3	NO			ON
			1	NC		ON	ON
2	220	DPST-NC	2	NC		ON	
			3				
			1		-		
2	022	DPST-NC	2	NC		ON	
			3	NC	ON	ON	

Subassemblies (Common)

Accessories and Tools

Operation Angle

Three Positions

No. of		Contact	Unit			Position		
outputs	Code	configuration	position	Contacts	1	0	2	
			1	NC		ON	ON	
2	202	DPST-NC	2					
			3	NC	ON	ON		
		0007.1107	1	NO	ON			
2	120	SPST-NO/ SPST-NC	2	NC		ON		
	2 120	0.01.10	3					
		ODOT NO	1	NO	ON			
2	102	SPST-NO/ SPST-NC	2					
		5. 5	3	NC	ON	ON		
		ODOT NO	1	NC		ON	ON	
2	210	SPST-NO/ SPST-NC	2	NO	ON		ON	
		0.01.10	3					
		0007.1107	1	NC		ON	ON	
2	201	SPST-NO/ SPST-NC	2					
		01 01 140	3	NO			ON	
			1					
2	012	SPST-NO/ SPST-NC	2	NO	ON		ON	
		01 01 110	3	NC	ON	ON		
		0007.1107	1					
2	021	SPST-NO/ SPST-NC	2	NC		ON		
			3	NO			ON	
	111		1	NO	ON			
3		3PST-NO	2	NO	ON		ON	
			3	NO			ON	
			1	NC		ON	ON	
3	222	3PST-NC	2	NC		ON		
			3	NC	ON	ON		
			1	NO	ON			
3	122	SPST-NO/ DPST-NC	2	NC		ON		
		DEST-INC	3	NC	ON	ON		
			1	NC		ON	ON	
3	212	SPST-NO/ DPST-NC	2	NO	ON		ON	
		DI 01-140	3	NC	ON	ON		
			1	NC		ON	ON	
3	221	SPST-NO/ DPST-NC	2	NC		ON		
		DI 01-140	3	NO			ON	
			1	NC		ON	ON	
3	211	DPST-NO/ SPST-NC	2	NO	ON		ON	
		O1 01-140	3	NO			ON	
			1	NO	ON			
3	121	DPST-NO/ SPST-NC	2	NC		ON		
		OF OT-INC	3	NO			ON	
			1	NO	ON			
3	112	DPST-NO/ SPST-NC	2	NO	ON		ON	
		OF OT-INC	3	NC	ON	ON		
			1				1	

■ Specifications: Refer to page 12.

■ Dimensions: Refer to page 41.

■ Characteristics: Refer to page 40.

■ Precautions for correct use: Refer to pages 85 to 96.

A22NK

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. **Two-position, Key-type Selector Switches**

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(5) Key release positions	(8)(8)(8) Contact configuration
Plastic bezels		1	A22NK-2B(3)-01(5)A-G(8)(8)(8)			100
Plastic bezels		!	A22NK-2B(3)-01(5)A-P(8)(8)(8)			002
		2	A22NK-2B(3)-01(5)A-G(8)(8)(8)			102 101
	2B	2	A22NK-2B(3)-01(5)A-P(8)(8)(8)		A: All positions B: Left C: Right	202
		3	A22NK-2B(3)-01(5)A-G(8)(8)(8)	M: Manual L: Automatic reset on left		111 222
			A22NK-2B(3)-01(5)A-P(8)(8)(8)			122 112
Brushed metal bezels	2M	1	A22NK-2M(3)-01(5)A-G(8)(8)(8)			100
Brushed metal bezels			A22NK-2M(3)-01(5)A-P(8)(8)(8)			002
1		2	A22NK-2M(3)-01(5)A-G(8)(8)(8)			102 101
		2	A22NK-2M(3)-01(5)A-P(8)(8)(8)			202
		3	A22NK-2M(3)-01(5)A-G(8)(8)(8)			111 222
			A22NK-2M(3)-01(5)A-P(8)(8)(8)			122 112

Three-position, Key-type Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(5) Key release positions	(8)(8)(8) Contact configuration
Plastic bezels		3	A22NK-3B(3)-01(5)A-G(8)(8)(8)	M: Manual L: Automatic reset on left R: Automatic reset on right B: Automatic reset on left and right	A: All positions B: Left C: Right D: Center G: Left and right	110 011 101 220 022 202
	3B		A22NK-3B(3)-01(5)A-P(8)(8)(8)			120 102 210 201 012 021
			A22NK-3B(3)-01(5)A-G(8)(8)(8)			111 222 122 212
			A22NK-3B(3)-01(5)A-P(8)(8)(8)			221 211 121 112
Brushed metal bezels	3М	2	A22NK-3M(3)-01(5)A-G(8)(8)(8)			110 011 101 220 022 202
			A22NK-3M(3)-01(5)A-P(8)(8)(8)			120 102 210 201 012 021
		3	A22NK-3M(3)-01(5)A-G(8)(8)(8)			111 222 122 212
			A22NK-3M(3)-01(5)A-P(8)(8)(8)			221 211 121 112

[■] Subassemblies: Refer to pages 37 to 38 and 82. (You can order Operation Units, Mounting Collars, and Contact Blocks individually.)


[■] Specifications: Refer to page 13 ■ Characteristics: Refer to page 40.

[■] Dimensions: Refer to page 41.

[■] Accessories and tools: Refer to pages 84 to 85.

Ordering Information

Subassemblies ---- You can order Operation Units, Mounting Collars, and Contact Blocks individually. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance parts.



- Model numbers of sets: Refer to page 36.
- Specifications: Refer to page 12.
- Characteristics: Refer to page 40

- Dimensions: Refer to page 41.
- Subassemblies (Common): Refer to page 78.
- Accessories and tools: Refer to pages 80 to 81.

A22NK

Ordering Information

Subassemblies -----You can order Operation Units, Mounting Collars, and Contact Blocks individually. Use them in combination for models that are not available as assembled Switches. They can also be used as inventory for maintenance

Operation Units

Bezel material and shape		Plastic	Brushed metal	(1) Key release positions
No. of positions	Reset method	Model	Model	
	Manual	A22NZ-2BM-01(1)A	A22NZ-2MM-01(1)A	A: All positions
2	Automatic reset on left	A22NZ-2BL-01(1)A	A22NZ-2ML-01(1)A	B: Left C: Right
	Manual	A22NZ-3BM-01(1)A	A22NZ-3MM-01(1)A	
3	Automatic reset on left	A22NZ-3BL-01(1)A	A22NZ-3ML-01(1)A	A: All positions B: Left
	Automatic reset on right	A22NZ-3BR-01(1)A	A22NZ-3MR-01(1)A	C: Right D: Center
	Automatic reset on left and right	A22NZ-3BB-01(1)A	A22NZ-3MB-01(1)A	G: Left and right

[■] Model numbers of sets: Refer to page 36.

[■] Specifications: Refer to page 12.

[■] Characteristics: Refer to page 40.

[■] Dimensions: Refer to page 41.

[■] Subassemblies (Common): Refer to page 78.

[■] Accessories and tools: Refer to pages 80 to 81.

Specifications

Certified Safety Standard Ratings

UL508 Type 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC

TÜV (EN60947-5-1)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

CCC (GB/T14048.5)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation v	oltage	600 V					
Rated carry currer	nt	10 A	10 A				
Rated voltage		24 V	120 V	240 V	380 V	440 V	
AC at 50/60 Hz	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A	
	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A	
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A			
DC	Inductive load (DC-13)	4 A	1.1 A	0.55 A			

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute
 2. Minimum applicable load: 10 mA at 5 VDC.

A22NK

Specifications

Characteristics

	Туре	Mary frame Colorator Switches	
Item		Key-type Selector Switches	
Allowable operating	Mechanical	30 operations/minute max.	
frequency	Electrical	30 operations/minute max.	
Insulation resistance		100 M Ω min. (at 500 VDC)	
Contact resistance		100 m $Ω$ max. (initial value)	
Dielectric strength	Between terminals of same polarity	2,500 VAC at 50/60 Hz for 1 min. (initial value)	
Dielectric strength	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial value)	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)	
Shock resistance	Malfunction	1,000 m/s ² max. (malfunction within 1 ms)	
	Mechanical	500,000 operations min. (Switches with 3 positions: 300,000 operations min.)	
Durability	Electrical	500,000 operations min. (Switches with 3 positions: 300,000 operations min.) (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)	
Ambient operating ter	mperature*1	−25 to 70°C	
Ambient operating hu	ımidity	35% to 85% RH	
Ambient storage temp	perature*1	-40 to 80°C	
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 13	
Electric shock protection class		Class II	
PTI (tracking characteristic)		175	
Degree of contamination (application environment)		3 (EN 60947-5-1)	
Weight		Approx. 65 g (for 1NC/1NO)	

- *1. With no icing or condensation.
- *2. Degree of protection from the front of the panel.

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Key-type Selector Switches		
Item	Manual reset	Automatic reset	
Total travel force (torque) (maximum TTF)	0.6 N·m	0.6 N·m	
Total travel (TT)	2 positions: Approx. 90°, 3 positions: Approx. 45°		
Resetting force (torque) (RF)	0.5 N·m max.		

Examples of Linked Contact Blocks (Screw terminal block type)


Contact Blocks

	Key-type Sele	ctor Switches
	2 positions	3 positions
Linking example	Operation Unit Mounting Collar	Operation Unit Mounting Collar

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.

Dimensions (Unit: mm)


Lighted and Non-lighted Key-type Selection Switches
















Three-position Switches with Plastic Bezels A22NK-3B□-01□A-G




A22NK-3B□-01□A-P






Two-position Switches with Brushed Metal Bezels






A22NK-2M□-01□A-P






Three-position Switches with Brushed Metal Bezels A22NK-3M□-01□A-G







A22NK-3M□-01□A-P



Depth with Linked Units (Screw terminal block type)




Depth when a double-contact unit is mounted (Push-In Plus terminal block type)



Terminal Arrangement

BOTTOM VIEW (Screw terminal block type)

2NO/1NC Contact configuration code:112



BOTTOM VIEW (Push-in Plus terminal block type)

(71-7
2NO/1NC Contact configuration code:112	Double-contact unit (2NO/2NO/2NC)
20 -10 +	23 - 23 - 19.0 - 23 - 24 - 19.0 - 24 - 24 - 19.0 - 25 - 24 - 19.0 - 25 - 25 - 25 - 19.0

Terminal Connection Diagrams

2NO/1NC Contact configuration code:112

Bottom View

(1) (3) (3) (4) (4)

Note: The above shows a terminal connection diagram for a screw terminal block type.


Indicators M22N

22-mm dia. Indicators
Control panel miniaturization through a
more compact design and modified
wiring direction.

Addition of Push-In Plus terminal blocks for easy wiring.



- Improved wiring visibility through to a modified wiring direction. (Push-In Plus terminal block type)
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)



- No need for extra lateral space because of the modified wiring direction. (Push-In Plus terminal block type)
- · Compact design.

Product Lineup

- · Meet global safety standards.
- Can be installed in two types of panel hole dimensions: 22.3 and 25.5 dia.
- The indicators come in a wide variety of colors and shapes.
- Compliant with IEC IP66, Certified for UL508 Type 4X, 13.

Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 85.

Indicator Unit Colors

	Red	Green	Yellow	White	Blue	Orange	White
When not lit							
When lit	Red	Green	Yellow	White	Blue	Orange	Opaque white*

^{*} The colors when the Switches are lit are for transparent white Indicator Units (code: TW) and yellow LED Lamps (code: Y).



M22N

List of Models

Screw Terminal Blocks/Push-In Plus To	erminal Blocks
Appearance	Model
Plastic flat	M22N-BN
Plastic projected	M22N-BP
Plastic semi-spherical	M22N-BG
Plastic flat etched	M22N-BC

Model Number Structure

Model Number Legend --Shipped as a set that includes the Indicator Unit, LED Lamp, and Socket Unit.

For information on combinations, refer to *Ordering Information* on page 46.

Model Numbers for Sets

(1) Indicator Unit Shape

Code Shape	
BN	Plastic flat
BP	Plastic projected
BG	Plastic semi-spherical
ВС	Plastic flat etched

(2) Indicator Color and (4) LED Lamp Color

e (2)	Code (4)	Indicator color	LED Lamp color
R	R	Red	Red
G	G	Green	Green
Υ	Υ	Yellow	Yellow
W	W	White	White
A	Α	Blue	Blue
0	0	Orange	Orange
W	Υ	White*	Yellow
	e (2) R G Y W A O	R R G G G Y Y W W A A A O O	R R Red G G Green Y Y Yellow W W White A A Blue O O Orange

^{*} The color is opaque white when the Indicator is lit.

(3) Degree of Protection

Code	ode Protection		
Α	Compliant with IEC IP66, Certified for UL508 Type 4X, 13		

(5) LED Lamp Voltage

Code	LED Lamp voltage		
Α	6 VAC/DC		
В	12 VAC/DC		
С	24 VAC/DC		
D	100/110/120 VAC		
Е	200/220/230/240 VAC		

(6) Terminals Specifications

Code	Specification		
No Code	Screw Terminal Block		
Р	Push-In Plus Terminal Block		

[■] Specifications: Refer to page 47.

[■] Accessories and tools: Refer to pages 80 to 81.

[■] Dimensions: Refer to page 48.

[■] Precautions for correct use: Refer to pages 85 to 96.

M22N

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Indicator Unit, LED Lamp, and Socket Unit.

Indicators

Appearance	Rated voltage	Model	(2)(2) Indicator color	(4) LED lamp color
Plastic flat	CVACIDO	M22N-BN-(2)(2)A-(4)A		
	6 VAC/DC	M22N-BN-(2)(2)A-(4)A-P	-	
	40.VAC/DC	M22N-BN-(2)(2)A-(4)B		
	12 VAC/DC	M22N-BN-(2)(2)A-(4)B-P		
	24.\\\\C\\DC	M22N-BN-(2)(2)A-(4)C		
	24 VAC/DC	M22N-BN-(2)(2)A-(4)C-P		
	100, 110, or 120 VAC	M22N-BN-(2)(2)A-(4)D		
	100, 110, 01 120 VAC	M22N-BN-(2)(2)A-(4)D-P		
	200, 220, 230, or 240 VAC	M22N-BN-(2)(2)A-(4)E		
	200, 220, 230, 01 240 VAC	M22N-BN-(2)(2)A-(4)E-P		
Plastic projected	6 VAC/DC	M22N-BP-(2)(2)A-(4)A		
	0 VAC/DC	M22N-BP-(2)(2)A-(4)A-P		
	12 VAC/DC	M22N-BP-(2)(2)A-(4)B		R: Red G: Green Y: Yellow W:White A: Blue O: Orange
	12 VAC/DC	M22N-BP-(2)(2)A-(4)B-P		
	24 VAC/DC	M22N-BP-(2)(2)A-(4)C		
	24 VAO/DC	M22N-BP-(2)(2)A-(4)C-P		
	100, 110, or 120 VAC	M22N-BP-(2)(2)A-(4)D		
	100, 110, 01 120 VAC	M22N-BP-(2)(2)A-(4)D-P		
	200, 220, 230, or 240 VAC	M22N-BP-(2)(2)A-(4)E	TR: Transparent red TG: Transparent green TY: Transparent yellow	
	200, 220, 230, 01 240 VAC	M22N-BP-(2)(2)A-(4)E-P		
Plastic semi-spherical	6 VAC/DC	M22N-BG-(2)(2)A-(4)A	TW:Transparent white TA: Transparent blue	
The same of the sa	0 VAC/DC	M22N-BG-(2)(2)A-(4)A-P	TO: Transparent orange	
	12 VAC/DC	M22N-BG-(2)(2)A-(4)B		
	12 VAO/DO	M22N-BG-(2)(2)A-(4)B-P		
	24 VAC/DC	M22N-BG-(2)(2)A-(4)C		
	Z4 VAOIDO	M22N-BG-(2)(2)A-(4)C-P		
	100, 110, or 120 VAC	M22N-BG-(2)(2)A-(4)D		
	100, 110, 01 120 VAC	M22N-BG-(2)(2)A-(4)D-P		
	200, 220, 230, or 240 VAC	M22N-BG-(2)(2)A-(4)E		
	200, 220, 230, 01 240 VAC	M22N-BG-(2)(2)A-(4)E-P		
Plastic flat etched	6 VAC/DC	M22N-BC-(2)(2)A-(4)A		
Extended 1	0 VAC/DO	M22N-BC-(2)(2)A-(4)A-P		
	12 VAC/DC	M22N-BC-(2)(2)A-(4)B		
	12 VAO/DO	M22N-BC-(2)(2)A-(4)B-P		
	24 VAC/DC	M22N-BC-(2)(2)A-(4)C		
	24 VAO/DO	M22N-BC-(2)(2)A-(4)C-P		
	100, 110, or 120 VAC	M22N-BC-(2)(2)A-(4)D		
	100, 110, 01 120 VAC	M22N-BC-(2)(2)A-(4)D-P		
	200, 220, 230, or 240 VAC	M22N-BC-(2)(2)A-(4)E		
	200, 220, 200, 01 240 VAC	M22N-BC-(2)(2)A-(4)E-P		

Note: Normally, the Indicator Unit and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Indicator Unit and yellow LED. M22N-B□-TWA-Y□-□

- Specifications: Refer to page 47.
- Accessories and tools: Refer to pages 80 to 81.
- Dimensions: Refer to page 48.
- Precautions for correct use: Refer to pages 85 to 96.

Ratings and Specifications

Certified Standard Ratings

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

UL508 Type 4X, 13 (File No.E76675), CSA C22.2 No.14

12 mA 6 VAC/DC

12 mA 12 VAC/DC

12 mA 24 VAC/DC

12 mA 100-120 VAC

12 mA 200-240 VAC

TÜV (EN60947-5-1)

80 mA 6 VAC/DC

40 mA 12 VAC/DC

20 mA 24 VAC/DC

10 mA 100-120 VAC

5 mA 200-240 VAC

CCC (GB/T14048.5)

6, 12, 24 VAC/DC

100-120, 200-240 VAC

Ratings

LED Lamps

Rated voltage	Applied voltage	Current
6 VAC/DC	6 VAC/DC ±10%	Approx. 11 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
12 VAC/DC	12 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
24 VAC/DC	24 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
100 VAC	100 VAC ±10%	
110 VAC	110 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
120 VAC	100-130 VAC	The prox. of the (write of green)
200 VAC	200 VAC ±10%	
220 VAC	220 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue)
230 VAC	230 VAC ±10%	Approx. 5 mA (white or green)
240 VAC	220-250 VAC	

Characteristics

	Туре	Indicator		
Item		mulcator		
Allowable operating	Mechanical			
frequency	Electrical			
Insulation resistance				
Contact resistance				
Dielectric strength	Between terminals of same polarity			
Dielectric strength	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial value)		
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude		
Shock resistance	Malfunction	1,000 m/s² max.		
Durahilitu	Mechanical			
Durability	Electrical			
Ambient operating temp	perature*1	−25 to 55°C		
Ambient operating hum	idity	35% to 85% RH		
Ambient storage tempe	rature*1	-40 to 80°C		
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 4X, 13		
Electric shock protection	on class	Class II		
PTI (tracking characteri	stic)	175		
Degree of contaminatio	n (application environment)	3 (EN 60947-5-1)		
Weight		Approx. 30 g		

^{*1.} With no icing or condensation.

^{*2.} Degree of protection from the front of the panel.


M22N

Dimensions (Unit: mm)

Indicators


Plastic Flat Indicators M22N-BN-□□A-□□







M22N-BN-□□A-□□-P







Plastic Semi-spherical Indicators M22N-BG-□□A-□□







M22N-BG-□□A-□□-P






Plastic Projected Indicators M22N-BP-□□A-□□






M22N-BP-□□A-□□-P






Plastic Flat Etched Indicators M22N-BC-□□A-□□





M22N-BC-□□A-□□-P







Terminal Arrangement

BOTTOM VIEW

BOTTOM VIEW



Terminal Connection Diagrams





Pushbutton Switches

A30NN/A30NL

30-mm dia. Pushbutton Switches Control panel miniaturization through a more compact design and modified wiring direction.

Addition of Push-In Plus terminal blocks for easy wiring. Workability and safety improvements.



Easy to Use

- You can connect up to three Contact Blocks in one stage for multistage expansion. (Screw terminal block type)
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)
- The terminals can be secured even when a contact block is mounted. (Screw terminal block type)
- Contact Blocks can be attached in any direction for easy assembly.

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenance-free use. (Push-In Plus terminal block type)

Product Lineup

• The buttons and bezels come in a wide variety of colors and shapes.

Refer to Safety Precautions for All Pushbutton Switches/
Indicators and Safety Precautions on page 85.

Button Colors

			Red	Green	Yellow	White	Blue	Black	
Non-lighted Switches									
			Red	Green	Yellow	White	Blue	Orange	White
Lighted	A30NL- □□□- T □	When not lit							
Switches	Transparent	sparent	Red	Green	Yellow	White	Blue	Orange	Opaque white*
	Whe								

^{*} The colors when the Switches are lit are for transparent white buttons (code: TW) and yellow LED Lamps (code: Y).

A30NN/A30NL

List of Models

Screw Terminal Blocks/Push-In Plus Terminal Blocks

Brushed metal bezels

A30N□-MN

Flat





A30N□-MP

Projected





A30N□-MG

Full guard





A30N□-MM

Mushroom





Model Number Structure

Model Number Legend ---- Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.

Model Numbers for Sets

(1) Type

Code	Description
N	Non-lighted
L	Lighted

(2) Bezel Material and Button Shape

Code	Bezel material	Button shape	
MN	Brushed metal	Flat	
MP	Brushed metal	Projected	
MG	Brushed metal	Full guard	
MM	Brushed metal	Mushroom	

(3) Switch Action

Code Function				
М	Momentary Action: Self-Resetting			
Α	Alternate Action: Self-Holding			

(4) Button Transparency and Color and (8) LED Lamp Color

Lighted/non-lighted	Code (4) Code (8)		Transparency	Button color	LED lamp color	
	NR	N	Opaque	Red		
	NG	N	Opaque	Green		
Non liabted	NY	N	Opaque	Yellow		
Non-lighted	NW	N	Opaque	White		
	NA	N	Opaque	Blue		
	NB	N	Opaque	Black		
	TR	R	Transparent	Red	Red	
	TG	G	Transparent	Green	Green	
	TY	Υ	Transparent	Yellow	Yellow	
Lighted	TW	W	Transparent	White	White	
	TA	Α	Transparent	Blue	Blue	
	TO	0	Transparent	Orange	Orange	
	TW	Y	Transparent	White *	Yellow	

^{*} The color is opaque white when the Switch is lit.

(5) Degree of Protection

Code	Description
Α	Compliant with IEC IP66, Certified for UL508 Type 4X, 13

(6) Contacts and Terminals Specifications

Code	Specification
G	General/Screw Terminal Block
Р	General/Push-In Plus Terminal Block

(7) Contacts

	Contact Blocks		Unit position					
Code			Non-lighted			Lighted		
	NO	NC	1	2	3	1	2	3
100	1	0	NO			NO	Lighting Unit	
002	0	1			NC	1	Lighting Unit	NC
101	2	0	NO		NO	NO	Lighting Unit	NO
102	1	1	NO		NC	NO	NO Lighting Unit	
202	0	2	NC		NC	NC	Lighting Unit	NC
111	3	0	NO	NO	NO			1
112	2	1	NO	NO	NC			
122	1	2	NO	NC	NC			
222	0	3	NC	NC	NC			

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.

2. Refer to the following figure for Unit positions.



(9) LED Lamp Voltage

Code	LED Lamp voltage
N	Non-lighted
Α	6 VAC/DC
В	12 VAC/DC
С	24 VAC/DC
D	100/110/120 VAC
Е	200/220/230/240 VAC

- Specifications: Refer to page 56.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.
- Dimensions: Refer to page 58.
- Accessories and tools: Refer to pages 80 to 81.

A30NN/A30NL

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Flat Switches

Appearance	Contacts	Momentary action (self-resetting) Model	Alternate action (self-holding) Model	(4)(4) Button color	(7)(7)(7) Contacts
Brushed metal bezels	1	A30NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-G(7)(7)(7)-NN		100
	ľ	A30NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-P(7)(7)(7)-NN	NR: Opaque, red	002
	2	A30NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-G(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	101 102 202 111 112
	2	A30NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-P(7)(7)(7)-NN	NW:Opaque, white NA: Opaque, blue	
	3	A30NN-MNM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-G(7)(7)(7)-NN	NB: Opaque, black	
	3	A30NN-MNM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MNA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Flat Switches

Appearance	Contacts	Momentary action Alternate action (self-resetting) (self-holding)		(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage
		Model	Model	2411011 00101		color	
Brushed metal bezels	1	A30NL-MNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MNA- (4)(4)A-G(7)(7)(7)-(8)(9)	- TR: Transparent, red	100	R: Red	
	ı	A30NL-MNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MNA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow TW: Transparent, white TA: Transparent, blue	002	G: Green Y: Yellow W: White A: Blue	A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC
	2	A30NL-MNM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MNA- (4)(4)A-G(7)(7)(7)-(8)(9)		101 102		
		A30NL-MNM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MNA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	202	O: Orange	

Non-lighted, Projected Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Brushed metal bezels	1	A30NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-G(7)(7)(7)-NN		100
	'	A30NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-P(7)(7)(7)-NN	NR: Opaque, red	002
	2	A30NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-G(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	101
	2	A30NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-P(7)(7)(7)-NN	NW:Opaque, white NA: Opaque, blue	102 202
	2	A30NN-MPM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-G(7)(7)(7)-NN	NB: Opaque, black	111 112
	3	A30NN-MPM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MPA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Projected Switches

Appearance	Contacts	Momentary action (self-resetting) (self-holding)		(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage
		Model	Model	Button color	Contacts	color	LLD Lamp Voltage
Brushed metal bezels	1	A30NL-MPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MPA- (4)(4)A-G(7)(7)(7)-(8)(9)	TR: Transparent, red	100	R: Red	
	ı	A30NL-MPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MPA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow	002	G: Green Y: Yellow	A: 6 VAC/DC B: 12 VAC/DC
	2	A30NL-MPM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MPA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	101 102	W: White A: Blue	C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC
		A30NL-MPM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MPA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	202	O: Orange	

Note: Normally, the Button and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Button and yellow LED. A30N□-□□□-<u>TW</u>A-□□□□-<u>Y</u>□

- Subassemblies: Refer to pages 55 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)
- Specifications: Refer to page 56. Dimensions: Refer to page 58.
- Accessories and tools: Refer to pages 80 to 81.

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp (lighted models only), Mounting Collar, Contact Block, and Lighting Unit (lighted models only).

Non-lighted, Full-guard Switches

Annogrance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model	Model	Button color	Contacts
Brushed metal bezels	1	A30NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-G(7)(7)(7)-NN		100
	'	A30NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-P(7)(7)(7)-NN	NR: Opaque, red	002
	2	A30NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-G(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	101 102
	2	A30NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-P(7)(7)(7)-NN	NW:Opaque, white NA: Opaque, blue	202
	3	A30NN-MGM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-G(7)(7)(7)-NN	NB: Opaque, black	111 112
	3	A30NN-MGM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MGA-(4)(4)A-P(7)(7)(7)-NN		122 222

Lighted, Full-guard Switches

Appearance	Contacts	Momentary action (self-resetting) (self-holding) Model Model		(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp color	(9) LED Lamp voltage
				Button color	Comacis		
Brushed metal bezels	1	A30NL-MGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MGA- (4)(4)A-G(7)(7)(7)-(8)(9)	TR: Transparent, red	100	R: Red	
	'	A30NL-MGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MGA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, green TY: Transparent, yellow	002	G: Green Y: Yellow	A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC
	2	A30NL-MGM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MGA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	101 102	W: White A: Blue	D: 100/110/120 VAC E: 200/220/230/240 VAC
	2	A30NL-MGM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MGA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	202	O: Orange	

Non-lighted, Mushroom Switches

Annearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4)	(7)(7)(7)
Appearance	Contacts	Model Model		Button color	Contacts
Brushed metal bezels	1	A30NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-G(7)(7)(7)-NN		100
		A30NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-P(7)(7)(7)-NN	NR: Opaque, red	002
	2	A30NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-G(7)(7)(7)-NN	NG: Opaque, green NY: Opaque, yellow	101 102
	2	A30NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-P(7)(7)(7)-NN	NW:Opaque, white NA: Opaque, blue	202 111 112 122 222
	3	A30NN-MMM-(4)(4)A-G(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-G(7)(7)(7)-NN	NB: Opaque, black	
		A30NN-MMM-(4)(4)A-P(7)(7)(7)-NN	A30NN-MMA-(4)(4)A-P(7)(7)(7)-NN		

Lighted, Mushroom Switches

Appearance	Contacts	Momentary action (self-resetting)	Alternate action (self-holding)	(4)(4) Button color	(7)(7)(7) Contacts	(8) LED Lamp	(9) LED Lamp voltage
		Model Model		Button color	Contacts	color	LED Lamp voltage
Brushed metal bezels	1	A30NL-MMM- (4)(4)A-G(7)(7)(7)-(8)(9) A30NL-MMA- (4)(4)A-G(7)(7)(7)-(8)		- TR: Transparent, red	100	R: Red	
	ı	A30NL-MMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MMA- (4)(4)A-P(7)(7)(7)-(8)(9)	TG: Transparent, red TG: Transparent, green TY: Transparent, yellow	002	G: Green Y: Yellow	A: 6 VAC/DC B: 12 VAC/DC
	2	A30NL-MMM- (4)(4)A-G(7)(7)(7)-(8)(9)	A30NL-MMA- (4)(4)A-G(7)(7)(7)-(8)(9)	TW: Transparent, white TA: Transparent, blue	101 102		C: 24 VAC/DC D: 100/110/120 VAC E: 200/220/230/240 VAC
		A30NL-MMM- (4)(4)A-P(7)(7)(7)-(8)(9)	A30NL-MMA- (4)(4)A-P(7)(7)(7)-(8)(9)	TO: Transparent, orange	202	O: Orange	

Note: Normally, the Button and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Button and yellow LED. A30N□-□□□-<u>TW</u>A-□□□□-<u>Y</u>□


■ Subassemblies: Refer to pages 55 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

- Specifications: Refer to page 56. Dimensions: Refer to page 58.
- Accessories and tools: Refer to pages 80 to 81.

A30NN/A30NL

Ordering Information

Switch Structure ---- Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.



- Specifications: Refer to page 56.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.
- Dimensions: Refer to page 58.
- Accessories and tools: Refer to pages 80 to 81.

Ordering Information

Subassemblies ---- Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.

Operation Units

		Brushed metal, flat		Brushed metal, projected		
Beze	Bezel material and button shape					
	Swit	ch Action	Momentary	Alternate	Momentary	Alternate
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model
	Opaque	Red	A30NZ-MNM-NRA	A30NZ-MNA-NRA	A30NZ-MPM-NRA	A30NZ-MPA-NRA
	Opaque	Green	A30NZ-MNM-NGA	A30NZ-MNA-NGA	A30NZ-MPM-NGA	A30NZ-MPA-NGA
Non-lighted	Opaque	Yellow	A30NZ-MNM-NYA	A30NZ-MNA-NYA	A30NZ-MPM-NYA	A30NZ-MPA-NYA
Non-lighted	Opaque	White	A30NZ-MNM-NWA	A30NZ-MNA-NWA	A30NZ-MPM-NWA	A30NZ-MPA-NWA
	Opaque	Blue	A30NZ-MNM-NAA	A30NZ-MNA-NAA	A30NZ-MPM-NAA	A30NZ-MPA-NAA
	Opaque	Black	A30NZ-MNM-NBA	A30NZ-MNA-NBA	A30NZ-MPM-NBA	A30NZ-MPA-NBA
	Transparent	Red	A30NZ-MNM-TRA	A30NZ-MNA-TRA	A30NZ-MPM-TRA	A30NZ-MPA-TRA
	Transparent	Green	A30NZ-MNM-TGA	A30NZ-MNA-TGA	A30NZ-MPM-TGA	A30NZ-MPA-TGA
Limbtod	Transparent	Yellow	A30NZ-MNM-TYA	A30NZ-MNA-TYA	A30NZ-MPM-TYA	A30NZ-MPA-TYA
Lighted	Transparent	White	A30NZ-MNM-TWA	A30NZ-MNA-TWA	A30NZ-MPM-TWA	A30NZ-MPA-TWA
	Transparent	Blue	A30NZ-MNM-TAA	A30NZ-MNA-TAA	A30NZ-MPM-TAA	A30NZ-MPA-TAA
	Transparent	Orange	A30NZ-MNM-TOA	A30NZ-MNA-TOA	A30NZ-MPM-TOA	A30NZ-MPA-TOA

			Brushed metal, full-guard		Brushed metal, mushroom	
Bezel	I material and but	ton shape	Ó			
	Swit	ch Action	Momentary	Alternate	Momentary	Alternate
Lighted/ non-lighted	Transparency	Color	Model	Model	Model	Model
	Opaque	Red	A30NZ-MGM-NRA	A30NZ-MGA-NRA	A30NZ-MMM-NRA	A30NZ-MMA-NRA
	Opaque	Green	A30NZ-MGM-NGA	A30NZ-MGA-NGA	A30NZ-MMM-NGA	A30NZ-MMA-NGA
Non limbtod	Opaque	Yellow	A30NZ-MGM-NYA	A30NZ-MGA-NYA	A30NZ-MMM-NYA	A30NZ-MMA-NYA
Non-lighted	Opaque	White	A30NZ-MGM-NWA	A30NZ-MGA-NWA	A30NZ-MMM-NWA	A30NZ-MMA-NWA
	Opaque	Blue	A30NZ-MGM-NAA	A30NZ-MGA-NAA	A30NZ-MMM-NAA	A30NZ-MMA-NAA
	Opaque	Black	A30NZ-MGM-NBA	A30NZ-MGA-NBA	A30NZ-MMM-NBA	A30NZ-MMA-NBA
	Transparent	Red	A30NZ-MGM-TRA	A30NZ-MGA-TRA	A30NZ-MMM-TRA	A30NZ-MMA-TRA
	Transparent	Green	A30NZ-MGM-TGA	A30NZ-MGA-TGA	A30NZ-MMM-TGA	A30NZ-MMA-TGA
Limband	Transparent	Yellow	A30NZ-MGM-TYA	A30NZ-MGA-TYA	A30NZ-MMM-TYA	A30NZ-MMA-TYA
Lighted	Transparent	White	A30NZ-MGM-TWA	A30NZ-MGA-TWA	A30NZ-MMM-TWA	A30NZ-MMA-TWA
	Transparent	Blue	A30NZ-MGM-TAA	A30NZ-MGA-TAA	A30NZ-MMM-TAA	A30NZ-MMA-TAA
	Transparent	Orange	A30NZ-MGM-TOA	A30NZ-MGA-TOA	A30NZ-MMM-TOA	A30NZ-MMA-TOA

- Specifications: Refer to page 56.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.
- Dimensions: Refer to page 58.
- Accessories and tools: Refer to pages 80 to 81.

A30NN/A30NL

Specifications (When the Operation Unit, LED Lamp, Mounting Collar, Contact Blocks, and Lighting Unit Are Combined)

Certified Safety Standard Ratings

UL508 Type 4X, 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC

TÜV (EN60947-5-1)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC CCC (GB/T14048.5)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation voltage		600 V					
Rated carry cu	rrent	10 A					
Rated voltage	ed voltage 24 V 120 V 240 V 380 V				440 V		
AC at 50/60	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A	
Hz	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A	
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A			
	Inductive load (DC-13)	4 A	1.1 A	0.55 A			

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute

 2. Minimum applicable load: 10 mA at 5 VDC.

LED Lamps

Rated voltage	Applied voltage	Rated current
6 VAC/DC	6 VAC/DC ±10%	Approx. 11 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
12 VAC/DC ±10%		Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
24 VAC/DC ±10%		Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
100 VAC	100 VAC ±10%	
110 VAC	110 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)
120 VAC	100 to 130 VAC	Typrox. 6 his (white or green)
200 VAC	200 VAC ±10%	
220 VAC	220 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue)
230 VAC	230 VAC ±10%	Approx. 5 mA (white or green)
240 VAC	220 to 250 VAC	

Specifications (When the Operation Unit, LED Lamp, Mounting Collar, Contact Blocks, and Lighting Unit Are Combined)

Characteristics

Туре		Pushbutton Switches		
Item		Non-lighted models	Lighted models	
Allowable operating Mechanical		60 operations/minute max.		
frequency	Electrical	30 operations/minute max.		
Insulation resistance		100 MΩ min. (at 500 VDC)	Not available for lighting units	
Contact resistance		100 mΩ max. (initial value)		
Dielectric strength Between terminals of same polarity		2,500 VAC at 50/60 Hz for 1 min. (initial value)	Not available for lighting units	
	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (init	ial value)	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)		
chock resistance Malfunction 1,000 m/s² max. (malfunction within 1 ms)		ms)		
Mechanical		Momentary action: 5,000,000 operations min. Alternate action: 500,000 operations min.		
Durability	Electrical	500,000 operations min. (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)		
Ambient operating ten	nperature*1	–25 to 70°C	–25 to 55°C	
Ambient operating hu	midity	35% to 85% RH		
Ambient storage temp	erature*1	−40 to 80°C		
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 4X, 13		
Electric shock protection class		Class II		
PTI (tracking characteristic)		175		
Degree of contaminati	on (application environment)	3 (EN 60947-5-1)		
Weight		Approx. 60 g (for 1NC/1NO)	Approx. 75 g (for 1NC/1NO)	

^{*1.} With no icing or condensation.

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Pushbutton Switches
Item	Lighted/non-lighted
Total travel force (torque) (maximum TTF)	18 N
Total travel (TT)	6 mm max.
Resetting force (torque) (RF)	

Examples of Linked Contact Blocks (Screw terminal block type)

Contact Blocks

Lighting Office		Lighting	Units
-----------------	--	----------	-------

		Pushbutto	n Switches	
	Mome	entary	Alter	rnate
	Lighted	Non-lighted	Lighted	Non-lighted
Linking example	Operation Unit Mounting Collar Ober Obe	Operation Unit	Operation Unit	Operation Unit
				Operation Unit

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.


^{*2.} Degree of protection from the front of the panel.

A30NN/A30NL


Dimensions

Lighted and Non-lighted Pushbutton Switches


Flat Switches with Brushed Metal Bezels $A30N\Box -MN\Box -N\Box A-G\Box -\Box\Box$ A30N - MN - N A-P - -1.8



Projected Switches with Brushed Metal Bezels










(Unit: mm)

Mushroom Switches with Brushed Metal Bezels A30N□-MM□-□□A-G□-□□






Depth with Linked Units (Screw terminal block type)



Depth when a double-contact unit is mounted (Push-In Plus terminal block type)



Terminal Arrangement BOTTOM VIEW (Screw terminal block type)

,	31 /
Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102
20 Contact Blocks Six, M3.5 Phillips/slotted screws	Six, M3.5 Phillips/slotted screws Contact Blocks

Terminal Connection Diagrams

1 01111111	ai ooi	incono	ii Diag	iaiiis
Non-lighted Contact co				Switches (1NO/1NC) configuration code:102
Во	ottom Vie	w	1	Bottom View
1	3	3	1	X) 3 X LED Lamp
2	4	4	2	(X2)— (4)

Note: The above shows a terminal connection diagram for a screw terminal block type.

BOTTOM VIEW (Push-In Plus terminal block type)

-		•
Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102	Double-contact unit Non-lighted (2NO/2NO/2NC)
20 -10	Lighting Unit Lighting Unit No. 31.9 Contact Blocks	19.0 19

Selector Switches A30NS/A30NW

30-mm dia. Knob-type Selector Switches Control panel miniaturization through a more compact design and modified wiring direction. Addition of Push-In Plus terminal blocks for easy wiring.

Workability and safety improvements.

Easy to Use

- You can connect up to three Contact Blocks in one stage for multistage expansion. (Screw terminal block type)
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenance-free use. (Push-In Plus terminal block type)

Product Lineup


• The buttons and bezels come in a wide variety of colors and shapes.

Operation Unit Colors

			Red	Green	Black				
Non-lighted Switches	A30NS-□□□-N□ Opaque		•	•	•				
			Red	Green	Yellow	White	Blue	Orange	White
Lighted Switches	A30NW-□□□-T□	When not lit	•	•		•	•	•	•
	Transparent		Red	Green	Yellow	White	Blue	Orange	Opaque white*
		When lit							•

^{*} The colors when the Switches are lit are for transparent white Operation Units (code: TW) and yellow LED Lamps (code: Y).

List of Models





Refer to Safety Precautions for All Pushbutton Switches/ Indicators and Safety Precautions on page 85.

Model Number Structure

Model Number Legend ---- Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.

Model Numbers for Sets

(1) Type

Code	Туре
S	Non-lighted
W	Lighted

(5) Degree of Protection

Code	Protection
Α	Compliant with IEC IP66, Certified for UL508 Type 4X, 13

(6) Contacts and Terminals Specifications

Code Specification		Specification
	G	General/Screw Terminal Block
	Р	General/Push-In Plus Terminal Block

Unit position

2

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

Lighting Unit

Lighted

3

NC

NO

NC

No. of positions

positions

Yes

Yes

Yes

Yes

Two

positions

Yes

Yes

Yes

Yes

(2) Number of Positions and Bezel Material

Code	No. of positions	Bezel material	
2M	2	Brushed metal	
3M	3	Brushed metal	

(3) Reset Method

Code	Reset method							
Code		ixeset illetillou						
М	Manual	Two-position manual	\/					
IVI	iwanuai	Three-position manual						
	Automatic	Two-position automatic						
L	reset on left	Three-position left automatic	→					
R	Automatic reset on right	Three-position right automatic						
В	Automatic reset on left and right	Three-position left or right automatic	\Diamond					

(4) Operation Unit Transparency and Color and (8) LED Lamp Color

Lighted/ non- lighted	Code (4)	Code (8)	Transparency	Operation Unit color	LED Lamp color
	NR			Red	
Non- lighted	NG	N	Opaque	Green	
	NB			Black	
	TR	R		Red	Red
	TG	G		Green	Green
	TY	Υ		Yellow	Yellow
Lighted	TW	W	Transparent	White	White
	TA	Α		Blue	Blue
	TO	0		Orange	Orange
	TW	Υ		White*	Yellow

^{*} The color is opaque white when the Switch is lit.

(7) Contact Configuration

	Com	tact	Non-lighted					
Code		cks	Unit	t posi	ition		. of tions	
	NO	NC	1	2	3	Two positions	Three positions	1
100	1	0	NO			Yes		N
002	0	1			NC	Yes		
101	2	0	NO		NO	Yes	Yes	N
102	1	1	NO		NC	Yes	Yes	N
201	1	1	NC		NO		Yes	N
202	0	2	NC		NC	Yes	Yes	N
110	2	0	NO	NO			Yes	
111	3	0	NO	NO	NO	Yes	Yes	
112	2	1	NO	NO	NC	Yes	Yes	
210	1	1	NC	NO			Yes	
211	2	1	NC	NO	NO		Yes	
212	1	2	NC	NO	NC		Yes	
011	2	0		NO	NO		Yes	
012	1	1		NO	NC		Yes	
120	1	1	NO	NC			Yes	
121	2	1	NO	NC	NO		Yes	
122	1	2	NO	NC	NC	Yes	Yes	
220	0	2	NC	NC			Yes	
221	1	2	NC	NC	NO		Yes	
222	0	3	NC	NC	NC	Yes	Yes	
021	1	1		NC	NO		Yes	
022	0	2		NC	NC		Yes	

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.

- 2. Refer to the following figure for the Unit positions.
- 3. Refer to Contact Configuration Table on page 21.



(9) LED Lamp Voltage

LED Lamp voltage
Non-lighted
6 VAC/DC
12 VAC/DC
24 VAC/DC
100/110/120 VAC
200/220/230/240 VAC

- Specifications: Refer to page 56.
- Dimensions: Refer to page 68.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 67.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96

A30NS/A30NW

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. Non-lighted, Two-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact configuration
Brushed metal bezels		1	A30NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN	I : Automatic reset on left	NR: Opaque red NG: Opaque green NB: Opaque black	100
	2M		A30NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			002
		vi 2	A30NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN			102 101
			A30NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			202
		3	A30NS-2M(3)-(4)(4)A-G(7)(7)(7)-NN			111 222
			A30NS-2M(3)-(4)(4)A-P(7)(7)(7)-NN			122 112

Non-lighted, Three-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact configuration
Brushed metal bezels		2	A30NS-3M(3)-(4)(4)A-G(7)(7)(7)-NN		NR: Opaque red NG: Opaque green NB: Opaque black	110 011 101 220 022 202
	3M	2	A30NS-3M(3)-(4)(4)A-P(7)(7)(7)-NN	M: Manual L: Automatic reset on left R: Automatic reset on right B: Automatic reset on left		120 102 210 201 012 021
		3	A30NS-3M(3)-(4)(4)A-G(7)(7)(7)-NN	and right		111 222 122 212
			A30NS-3M(3)-(4)(4)A-P(7)(7)(7)-NN			221 211 121 112

[■] Subassemblies: Refer to pages 65 and 78. (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.)

[■] Specifications: Refer to page 56. ■ Characteristics: Refer to page 67. ■ Dimensions: Refer to page 68.

[■] Accessories and tools: Refer to pages 80 to 81.

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, LED Lamp, Mounting Collar, Contact Block, and Lighting Unit.

Lighted, Two-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact Configuration	(8) LED Lamp color	(9) LED Lamp voltage
Brushed metal bezels		1	A30NW-2M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)		atic TW: Transparent white	102 G Y A 102 O	R: Red G: Green Y: Yellow A: Blue O: Orange W: White	A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC
	2M	•	A30NW-2M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)	M: Manual L: Automatic reset on left				
	ZIVI	2	A30NW-2M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)					D: 100/110/120 VAC E: 200/220/230/
		2	A30NW-2M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)			202		240 VAC

Lighted, Three-position, Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(4)(4) Operation Unit color	(7)(7)(7) Contact Configuration	(8) LED Lamp color	(9) LED Lamp voltage
Brushed metal bezels	214		A30NW-3M(3)- (4)(4)A-G(7)(7)(7)-(8)(9)	M: Manual L: Automatic reset on left R: Automatic	TR: Transparent red TG: Transparent green TY: Transparent yellow	101 202	R: Red G: Green Y: Yellow	A: 6 VAC/DC B: 12 VAC/DC C: 24 VAC/DC
	3M	2	A30NW-3M(3)- (4)(4)A-P(7)(7)(7)-(8)(9)	reset on right B: Automatic reset on left and right	TW: Transparent white TA: Transparent blue TO: Transparent orange	202 102 201	A: Blue	D: 100/110/120 VAC E: 200/220/230/ 240 VAC

Note: Normally, the Operation Unit and LED Lamp with the same color are combined.

However, opaque white is available by combining a white Operation Unit and yellow LED. A30N□-□□□-<u>TW</u>A-□□□-<u>Y</u>□

 Subassemblies: Refer to pages 65 and 78.
 (You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually.) ■ Specifications: Refer to page 56. ■ Characteristics: Refer to page 67.


■ Dimensions: Refer to page 68.

■ Accessories and tools: Refer to pages 80 to 81.

A30NS/A30NW

Ordering Information

Switch Structure----Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.



- Specifications: Refer to page 56.
- Dimensions: Refer to page 68.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 67.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.

Ordering Information

Subassemblies ---- Please order Operation Units, LED lamps (lighted models only), Mounting Collars, Contact Blocks, and Lighting Units (lighted models only) separately. LED lamps, Mounting Collars, Contact Blocks, Lighting Units, and Lock Ring can also be used with the A22N series.

Operation Units Non-lighted Switches

			Brushed metal
	Bezel mate		
No. of positions	Reset method	Operation Unit color	Model
2	Manual		A30NZ-2MM-NRA
2	Automatic reset on left		A30NZ-2ML-NRA
	Manual		A30NZ-3MM-NRA
	Automatic reset on left	Opaque red	A30NZ-3ML-NRA
3	Automatic reset on right		A30NZ-3MR-NRA
	Automatic reset on left and right		A30NZ-3MB-NRA
2	Manual		A30NZ-2MM-NGA
2	Automatic reset on left		A30NZ-2ML-NGA
	Manual		A30NZ-3MM-NGA
	Automatic reset on left	Opaque	A30NZ-3ML-NGA
3	Automatic reset on right	green	A30NZ-3MR-NGA
	Automatic reset on left and right		A30NZ-3MB-NGA
2	Manual		A30NZ-2MM-NBA
2	Automatic reset on left		A30NZ-2ML-NBA
	Manual		A30NZ-3MM-NBA
	Automatic reset on left	Opaque black	A30NZ-3ML-NBA
3	Automatic reset on right	DIACK	A30NZ-3MR-NBA
	Automatic reset on left and right		A30NZ-3MB-NBA

Lighted Switches

			Dahaadaadal	
			Brushed metal	
	Bezel mate	rial and shape		
No. of positions	Reset method	Operation Unit color	Model	
2	Manual		A30NZ-2MM-TRA	
2	Automatic reset on left		A30NZ-2ML-TRA	
	Manual		A30NZ-3MM-TRA	
	Automatic reset on left	Transparent red	A30NZ-3ML-TRA	
3	Automatic reset on right	reu	A30NZ-3MR-TRA	
	Automatic reset on left and right		A30NZ-3MB-TRA	
2	Manual		A30NZ-2MM-TGA	
	Automatic reset on left		A30NZ-2ML-TGA	
	Manual		A30NZ-3MM-TGA	
	Automatic reset on left	Transparent green	A30NZ-3ML-TGA	
3	Automatic reset on right	green	A30NZ-3MR-TGA	
	Automatic reset on left and right		A30NZ-3MB-TGA	
2	Manual		A30NZ-2MM-TYA	
_	Automatic reset on left		A30NZ-2ML-TYA	
	Manual	_	A30NZ-3MM-TYA	
	Automatic reset on left	Transparent vellow	A30NZ-3ML-TYA	
3	Automatic reset on right	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	A30NZ-3MR-TYA	
	Automatic reset on left and right		A30NZ-3MB-TYA	
2	Manual		A30NZ-2MM-TWA	
	Automatic reset on left		A30NZ-2ML-TWA	
	Manual		A30NZ-3MM-TWA	
	Automatic reset on left	Transparent white	A30NZ-3ML-TWA	
3	Automatic reset on right	-	A30NZ-3MR-TWA	
	Automatic reset on left and right		A30NZ-3MB-TWA	
2	Manual		A30NZ-2MM-TAA	
_	Automatic reset on left		A30NZ-2ML-TAA	
	Manual		A30NZ-3MM-TAA	
	Automatic reset on left	Transparent blue	A30NZ-3ML-TAA	
3	Automatic reset on right		A30NZ-3MR-TAA	
	Automatic reset on left and right		A30NZ-3MB-TAA	
2	Manual		A30NZ-2MM-TOA	
_	Automatic reset on left		A30NZ-2ML-TOA	
	Manual		A30NZ-3MM-TOA	
	Automatic reset on left	Transparent orange	A30NZ-3ML-TOA	
3	Automatic reset on right		A30NZ-3MR-TOA	
	Automatic reset on left and right		A30NZ-3MB-TOA	

- Specifications: Refer to page 56.
- Dimensions: Refer to page 68.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 67.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.

A30NS/A30NW

Specifications

Certified Safety Standard Ratings

UL508 Type 4X, 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC

TÜV (EN60947-5-1)

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

CCC (GB/T14048.5)

AC-15 3 A 240 VAC DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation volt	age	600 V				
Rated carry current		10 A				
Rated voltage		24 V	120 V	240 V	380 V	440 V
AC at 50/60 Hz	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A
AC at 50/60 HZ	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A		
	Inductive load (DC-13)	4 A	1.1 A	0.55 A		

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute
 2. Minimum applicable load: 10 mA at 5 VDC.

LED Lamps

Rated voltage	Applied voltage	Rated current	
6 VAC/DC	6 VAC/DC ±10%	Approx. 11 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)	
12 VAC/DC	12 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)	
24 VAC/DC	24 VAC/DC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)	
100 VAC	100 VAC ±10%		
110 VAC	110 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue) Approx. 5 mA (white or green)	
120 VAC	100 to 130 VAC	7 Approx. o Hist (write of grooti)	
200 VAC	200 VAC ±10%		
220 VAC	220 VAC ±10%	Approx. 12 mA (red, orange, yellow, or blue)	
230 VAC	230 VAC ±10%	Approx. 5 mA (white or green)	
240 VAC	220 to 250 VAC		

Specifications (When the Operation Unit, LED Lamp, Mounting Collar, Contact Blocks, and Lighting Unit Are Combined)

Characteristics

Туре		Selector Switches	
Item		Non-lighted models	Lighted models
Allowable operating	Mechanical	30 operations/minute max.	
frequency	Electrical	30 operations/minute max.	
Insulation resistance		100 MΩ min. (at 500 VDC)	Not available for lighting units
Contact resistance		100 mΩ max. (initial value)	
Dielectric strength	Between terminals of same polarity	2,500 VAC at 50/60 Hz for 1 min. (initial value)	Not available for lighting units
	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial value)	
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)	
Shock resistance	Malfunction	1,000 m/s² max. (malfunction within 1 ms)	
	Mechanical	500,000 operations min. (Switches with 3 positions: 300,000 operations n	
Durability	Electrical	500,000 operations min. (Switches with 3 positions: 300,000 operations m (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)	
Ambient operating temp	perature*1	−25 to 70°C	−25 to 55°C
Ambient operating hum	idity	35% to 85% RH	
Ambient storage tempe	rature*1	-40 to 80°C	
Degree of protection*2		Compliant with IEC IP66, Certified for UL508 Type 4X, 13	
Electric shock protection class		Class II	
PTI (tracking characteristic)		175	
Degree of contamination (application environment)		3 (EN 60947-5-1)	
Weight		Approx. 60 g (for 1NC/1NO)	Approx. 75 g (for 1NC/1NO)

^{*1.} With no icing or condensation.

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Selector Switches	
Item	Manual reset	Automatic reset
Total travel force (torque) (maximum TTF)	0.6 N·m	0.6 N·m
Total travel (TT)	2 positions: Approx. 90°, 3 positions: Approx. 45°	
Resetting force (torque) (RF)	0.5 N·m max.	

Examples of Linked Contact Blocks (Screw terminal block type)

(Screw terminal bloc	k type)		Contact Blocks	Lighting Units
		Selector	Switches	
	2 pos	itions	3 posi	tions
	Lighted	Non-lighted	Lighted	Non-lighted
Linking example	Operation Unit Mounting Collar	Operation Unit Mounting Collar Operation Unit Mounting Collar	Operation Unit Mounting Collar	Operation Unit Mounting Collar

If you use three Contact Blocks in stage 1, you can add one more Contact Block in the middle of stage 2.

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.


^{*2.} Degree of protection from the front of the panel.

A30NS/A30NW


Dimensions (Unit: mm)

Lighted and Non-lighted Selection Switches

Two-position Switches with Brushed Metal Bezels A30N□-2M□-□□A-G□-□□



A30N□-2M□-□□A-P□-□□




-22.7

41


Three-position Switches with Brushed Metal Bezels A30N□-3M□-□□A-G□-□□

22.7


46.8




A30N□-3M□-□□A-P□-□□




Depth with Linked Units (Screw terminal block type)



Depth when a double-contact unit is mounted (Push-In Plus terminal block type)




Terminal Arrangement BOTTOM VIEW (Screw terminal block type)



BOTTOM VIEW (Push-In Plus terminal block type)

Non-lighted Switches (2NO/1NC) Contact configuration code:112	Lighted Switches (1NO/1NC) Contact configuration code:102
20 10 10 10 10 10 10 10 10 10 10 10 10 10	Lighting Unit Lighting Unit Contact Blocks

Double-contact unit Non-lighted (2NO/2NO/2NC)



Terminal Connection Diagrams

Non-lighted Switches (2NO/1NC Contact configuration code:112	
Bottom View	Bottom View
	① X1 3 LED Lamp 4

Note: The above shows a terminal connection diagram for a screw terminal block type.

Key-type Selector Switches

30-mm dia. Key-type Selector Switches Control panel miniaturization through a more compact design and modified wiring direction. Addition of Push-In Plus terminal blocks for easy wiring.

Workability and safety improvements.

Easy to Use

- You can connect up to three Contact Blocks in one stage for multistage expansion. (Screw terminal block type)
- Screw terminal structure is compatible with round crimp terminals. (Screw terminal block type)
- The terminals can be secured even when a contact block is mounted. (Screw terminal block type)
- Contact Blocks can be attached in any direction for easy assembly.

Safety

- Easy-to-operate lock lever for secure locking.
- Easy-mounting Contact Blocks provide finger protection.
- No loose connections of wiring means maintenance-free use. (Push-In Plus terminal block type)

Product Lineup

• The buttons and bezels come in a wide variety of colors and shapes.

Refer to Safety Precautions for All Pushbutton Switches/
Indicators and Safety Precautions on page 85.

List of Models

Screw Terminal Blocks/Push-In Plus Terminal Blocks Brushed metal bezels

A30NK

Two Positions

Three Positions





- Specifications: Refer to page 56.
- Dimensions: Refer to page 76.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 75.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.



Model Number Structure

Model Number Legend ----- Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. For information on combinations, refer to Ordering Information on page 72.

Model Numbers for Sets

(1) Type

(4) Key Number

Code	Туре
K	Key-type Selector Switch

Ī	Code	No.
	01	No.1

(2) Number of Positions and **Bezel Material**

Code	No. of positions	Bezel material
2M	2	Brushed metal
3M	3	Brushed metal

(3) Reset Method

Code		Reset method		
М	Manual	Two- positions manual	\/	
IVI	Manual	Three- positions manual		
ı	Automatic reset on	Two- positions automatic		
L	left	Three- positions left automatic		
R	Automatic reset on right	Three- positions right automatic		
В	Automatic reset on left and right	Three- positions left or right automatic		

(5) Key Release Position

Code	Release position	Two positions	Three positions
Α	All positions		
В	Left	•	
С	Right	•	•
D	Center		•
G	Left and right		
0.	<u> </u>		1 1 20

○: Release position : Locked position * The key can only be removed when in the free position for automatic reset models.

(6) Degree of Protection

_	Code	Protection
	Α	Compliant with IEC IP66, Certified for UL508 Type 13

(7) Contacts and Terminals Specifications

Code	Specification				
G	General/Screw Terminal Block				
Р	General/Push-In Plus Terminal Block				

(8) Contact Configuration


Code	Contact Blocks		Unit position			Two positions	Three positions	
	NO	NC	1	2	3	positions	positions	
100	1	0	NO			Yes		
002	0	1			NC	Yes		
101	2	0	NO		NO	Yes	Yes	
102	1	1	NO		NC	Yes	Yes	
201	1	1	NC		NO		Yes	
202	0	2	NC		NC	Yes	Yes	
110	2	0	NO	NO			Yes	
111	3	0	NO	NO	NO	Yes	Yes	
112	2	1	NO	NO	NC	Yes	Yes	
210	1	1	NC	NO			Yes	
211	2	1	NC	NO	NO		Yes	
212	1	2	NC	NO	NC		Yes	
011	2	0		NO	NO		Yes	
012	1	1		NO	NC		Yes	
120	1	1	NO	NC			Yes	
121	2	1	NO	NC	NO		Yes	
122	1	2	NO	NC	NC	Yes	Yes	
220	0	2	NC	NC			Yes	
221	1	2	NC	NC	NO		Yes	
222	0	3	NC	NC	NC	Yes	Yes	
021	1	1		NC	NO		Yes	
022	0	2		NC	NC		Yes	

Note: 1. NO (blue): Normally open, NC (orange): Normally closed.

- 2. Refer to the following figure for Unit positions.
- 3. Refer to Contact Configuration Table on page 34.

Two Positions

Operation Angle



- Specifications: Refer to page 56.
- Dimensions: Refer to page 76.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 75.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96

A30NK

Ordering Information

Model Numbers for Sets---- Shipped as a set that includes the Operation Unit, Mounting Collar, and Contact Block. **Two-position, Key-type Selector Switches**


Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(5) Key release positions	(8)(8)(8) Contact configuration
Brushed metal bezels	2М	1	A30NK-2M(3)-01(5)A-G(8)(8)(8)	M:Manual L:Automatic reset on left	A: All positions B: Left C: Right	100
Diusileu illetai bezeis			A30NK-2M(3)-01(5)A-P(8)(8)(8)			002
		2	A30NK-2M(3)-01(5)A-G(8)(8)(8)			102 101
			A30NK-2M(3)-01(5)A-P(8)(8)(8)			202
		3	A30NK-2M(3)-01(5)A-G(8)(8)(8)			111 222
			A30NK-2M(3)-01(5)A-P(8)(8)(8)			122 112

Three-position, Key-type Selector Switches

Appearance	Bezel material	No. of outputs	Model	(3) Reset method	(5) Key release positions	(8)(8)(8) Contact configuration
Brushed metal bezels	3M	2	A30NK-3M(3)-01(5)A-G(8)(8)(8)	M: Manual L: Automatic reset on left R: Automatic reset on right B: Automatic reset on left and right	A: All positions B: Left C: Right D: Center G: Left and right	110 011 101 220 022 202
			A30NK-3M(3)-01(5)A-P(8)(8)(8)			120 102 210 201 012 021
		3	A30NK-3M(3)-01(5)A-G(8)(8)(8)			111 222 122 212
			A30NK-3M(3)-01(5)A-P(8)(8)(8)			221 211 121 112

Ordering Information

Subassemblies ---- Order Operation Units, Mounting Collars, and Contact Blocks individually. The same Mounting Collars and Contact Blocks are also used for the A22N Series.



- Specifications: Refer to page 56.
- Dimensions: Refer to page 76.
- Accessories and tools: Refer to pages 80 to 81.
- Characteristics: Refer to page 75.
- Subassemblies (Common): Refer to page 78.
- Precautions for correct use: Refer to pages 85 to 96.

A30NK

Subassemblies -----Order Operation Units, Mounting Collars, and Contact Blocks individually. The same Mounting Collars and Contact Blocks are also used for the A22N Series.

Operation Units

Bezel material and shape		Brushed metal Bezel material and shape	
No. of positions	Reset method	Model	
2	Manual	A30NZ-2MM-01(5)A	A: All positions B: Left
2	Automatic reset on left	A30NZ-2ML-01(5)A	C: Right
	Manual	A30NZ-3MM-01(5)A	A AII 30
3	Automatic reset on left	A30NZ-3ML-01(5)A	A: All positions B: Left
	Automatic reset on right	A30NZ-3MR-01(5)A	C: Right D: Center G: Left and right
	Automatic reset on left and right	A30NZ-3MB-01(5)A	O. Left and fight

Specifications

Certified Safety Standard Ratings

UL508 Type 13 (File No. E76675), CSA C22.2 No.14

6 A 240 VAC, 10 A 120 VAC **TÜV (EN60947-5-1)**

AC-15 3 A 240 VAC

DC-13 4 A 24 VDC

CCC (GB/T14048.5)

AC-15 3 A 240 VAC DC-13 4 A 24 VDC

Application Standards

UL1059 and UL486E (Push-In Plus terminal block type)

Ratings

Contacts (Standard Load)

Rated insulation v	ted insulation voltage 600 V							
Rated carry current		10 A	10 A					
Rated voltage		24 V	120 V	240 V	380 V	440 V		
AC at 50/60 Hz	Resistive load (AC-12)	10 A	10 A	6 A	2A	2 A		
	Inductive load (AC-15)	10 A	6 A	3 A	1.9 A	1.6 A		
DC	Resistive load (DC-12)	8 A	2.2 A	1.1 A				
	Inductive load (DC-13)	4 A	1.1 A	0.55 A				

Note: 1. The above ratings were obtained by conducting tests under the following conditions.

- (1) Ambient temperature: 20 ±2°C
- (2) Ambient humidity: 65% ±5% RH
- (3) Operating frequency: 30 operations/minute
- 2. Minimum applicable load: 10 mA at 5 VDC.

Specifications (When Operation Unit, Mounting Collar, and Contact Blocks Are Combined)

Characteristics

Type Item		Key-type Selector Switches			
Allowable operating		30 operations/minute max.			
		30 operations/minute max.			
Insulation resistance		100 MΩ min. (at 500 VDC)			
Contact resistance		100 mΩ max. (initial value)			
Dialoctric strongth	Between terminals of same polarity	2,500 VAC at 50/60 Hz for 1 min. (initial value)			
Dielectric strength	Between each terminal and ground	2,500 VAC at 50/60 Hz for 1 min. (initial value)			
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude (malfunction within 1 ms)			
Shock resistance	Malfunction	1,000 m/s² max. (malfunction within 1 ms)			
	Mechanical	500,000 operations min. (Switches with 3 positions: 300,000 operations min.)			
Durability	Electrical	500,000 operations min. (Switches with 3 positions: 300,000 operations min.) (250 VAC, 3 A, with an inductive load having power factor $\cos \theta = 0.4$)			
Ambient operating te	mperature*1	−25 to 70°C			
Ambient operating hu	umidity	35% to 85% RH			
Ambient storage tem	perature*1	−40 to 80°C			
Degree of protection*	2	Compliant with IEC IP66, Certified for UL508 Type 13			
Electric shock protect	tion class	Class II			
PTI (tracking characteristic)		175			
Degree of contamination (application environment)		3 (EN 60947-5-1)			
Weight		Approx. 75 g (for 1NC/1NO)			
*4 \\/;th====:=:========					

^{*1.} With no icing or condensation.

Operating Characteristics (for SPST-NO/SPST-NC)

Туре	Key-type Selector Switches			
Item	Manual reset	Automatic reset		
Total travel force (torque) (maximum TTF)	0.6 N·m	0.6 N·m		
Total travel (TT)	2 positions: Approx. 90°, 3 positions: Approx. 45°			
Resetting force (torque) (RF)	0.5 N·m max			

Examples of Linked Contact Blocks (Screw terminal block type)

	Key-type Selector Switches			
	2 positions	3 positions		
Linking example	Operation Unit Mounting Collar	Operation Unit Mounting Collar		

Note: If you increase the number of Contact Blocks, evaluate the Switch under actual working conditions before permanent installation and use the Switch within a number of switching operations that will not adversely affect the Switch's performance.

Contact Blocks


^{*2.} Degree of protection from the front of the panel.

A30NK


Dimensions (Unit: mm)

Key-type Selection Switches


Two-position Switches with Brushed Metal Bezels A30NK-2M□-01□A-G□

















Three-position Switches with Brushed Metal Bezels A30NK-3M□-01□A-G□

A30NK-3M□-01□A-P□










Depth with Linked Units (Screw terminal block type)

Depth when a double-contact unit is mounted (Push-In Plus terminal block type)





Terminal Arrangement BOTTOM VIEW (Screw terminal block type)




BOTTOM VIEW (Push-In Plus terminal block type)

2NO/1NC Contact configuration code:112	Double-contact unit (2NO/2NO/2NC)
20 -10 -10 -10 -10 -10 -10 -10 -10 -10 -1	19.0 19.0 19.0 38.6

Terminal Connection Diagrams

2NO/1NC Contact configuration code:112

Bottom View



Note: The above shows a terminal connection diagram for a screw terminal block type.

Subassemblies (Common)

Ordering Information

Subassemblies - - - You can order Operation Units, LED Lamps, Mounting Collars, and Contact Blocks individually. Use them in combination for models that are not available as assembled Units. These can also be used as inventory for maintenance parts.

LED Lamps

The LED lamps are exclusively for use with the A22N series, M22N series, and A30N series.

	Rated voltage		Model					
Appearance	Color	6 VAC/DC	12 VAC/DC	24 VAC/DC	100/110/120 VAC	200/220/230/240 VAC		
	Red	A22NZ-L-RA	A22NZ-L-RB	A22NZ-L-RC	A22NZ-L-RD	A22NZ-L-RE		
A 1523	Green	A22NZ-L-GA	A22NZ-L-GB	A22NZ-L-GC	A22NZ-L-GD	A22NZ-L-GE		
	Yellow	A22NZ-L-YA	A22NZ-L-YB	A22NZ-L-YC	A22NZ-L-YD	A22NZ-L-YE		
	White	A22NZ-L-WA	A22NZ-L-WB	A22NZ-L-WC	A22NZ-L-WD	A22NZ-L-WE		
	Blue	A22NZ-L-AA	A22NZ-L-AB	A22NZ-L-AC	A22NZ-L-AD	A22NZ-L-AE		
	Orange	A22NZ-L-OA	A22NZ-L-OB	A22NZ-L-OC	A22NZ-L-OD	A22NZ-L-OE		

Mounting Collar

Appearance	Model
	A22NZ-H-01

Contact Blocks

Appearance	Terminals Specifications	Contacts	Model
1	Screw terminal block	SPST-NO (blue)	A22NZ-S-G1A
	Screw terminal block	SPST-NC (orange)	A22NZ-S-G1B
		SPST-NO (blue)	A22NZ-S-P1A
	Push-In Plus terminal block	SPST-NC (red)	A22NZ-S-P1B
3		DPST-NO (blue)	A22NZ-S-P2A
	Push-In Plus terminal block	DPST-NC (red)	A22NZ-S-P2B
		SPST-NO/SPST-NC (white)	A22NZ-S-P2C


Lighting Units


Appearance	Terminals Specifications	Rated voltage	Model
A		6 VAC/DC	A22NZ-T-A
1		12 VAC/DC	A22NZ-T-B
2000	Screw terminal block	24 VAC/DC	A22NZ-T-C
22		100/110/120 VAC	A22NZ-T-D
		200/220/230/240 VAC	A22NZ-T-E
		6 VAC/DC	A22NZ-T-AP
		12 VAC/DC	A22NZ-T-BP
	Push-In Plus terminal block	24 VAC/DC	A22NZ-T-CP
		100/110/120 VAC	A22NZ-T-DP
		200/220/230/240 VAC	A22NZ-T-EP

Subassemblies (Common)


Dimensions (Unit: mm)


LED Lamps A22NZ-L-□□






Mounting Collar A22NZ-H-01







Screw terminal block


Contact Blocks A22NZ-S-G1□






Lighting Units A22NZ-T-□







Push-In Plus Terminal Blocks


Contact Blocks (Single Contact) A22NZ-S-P1□







Contact Blocks (Double Contact) A22NZ-S-P2□





Lighting Units A22NZ-T-□P





Accessories and Tools

Ordering Information

A22N/M22N/A30N

Accessories and Tools (Order Separately)

Item	Appearance	Classi	fication	Model	Remarks
Protective Cover				A22NZ-A-303	A protector designed to prevent incorrect operation. Cannot be used together with other accessories. (Rubber seal included.) For 22.3 and 25.5-mm panel holes diameter. Key-type selector switches cannot be used.
Plastic Hole Plug		Round		A22NZ-A-401	Can be plugged into precut panel holes for future expansion. Applicable panel thickness: 0.8 to 3.0 mm For 22.3-mm panel hole diameter.
Metal Hole Plug		Ro	und	A22NZ-A-402	Can be plugged into precut panel holes for future expansion. Applicable panel thickness: 0.8 to 6.0 mm (Rubber seal included.) For 22.3-mm panel hole diameter.
Lock Ring		Round		A22NZ-A-403	Used when a more secure lock is required to prevent rotation inside the Operation Unit. (Rubber seal included.) For 22.3-mm panel hole diameter. Can be used together with the A22NZ-A-50501 Lock Ring.
Lock Ring	O			A22NZ-A-50501	Used when a more secure lock is required to prevent rotation of the Operation Unit. Can be used together with the A22NZ-A-403 Lock Ring. Can be used with the A22N Series and the A30N Series.
Reinforcement Plate	Gerel			A22NZ-A-C01	Used to reinforce Contact Blocks and Lighting Units, Refer to page 92 for mounting instructions.
Key	Near No.			A22NZ-K-01	Used with a key-type selector switch.
		1 hole		A22NZ-A-B101	
		1 hole, yellow box		A22NZ-A-B201	For 22.3-mm panel hole diameter, A30N□ cannot be
				A22NZ-A-B101Y A22NZ-A-B01Y	used. Two switches for screw terminal block type cannot be
Control Box				A22NZ-A-B102	linked. The A22NZ-A-B01Y and The A22NZ-A-B2□ model
	201	2 h	oles	A22NZ-A-B202	cannot be used for a double-contact unit of the Push-In
		3 h	oles	A22NZ-A-B103	Plus terminal block type.
		STICIES		A22NZ-A-B203	
Connector		Suitable Cable	7 to 9 dia.	A22Z-3500-1	Plastic connector used to extend a cable from the switch box.
		Diameter (mm)	9 to 11 dia.	A22Z-3500-2	Refer to page 95 for details.
Sealing Caps		For flat models		A22Z-3600F	Used to prevent dust or water from entering the Operation Unit.
		For projection models		A22Z-3600T	Color: opaque Material: silicon For 22.3 and 25.5-mm panel holes diameter.
		For full-guard models		A22Z-3600G	Knob-type and key-type selector switches cannot be used. Cannot be used together with legend plate frame.
Resin Attachment for 30 dia.		Round		A22Z-A30	Use when mounting to a panel with a 30-dia. hole. Refer to page 96 for details. Purchase and mount a separate Lock Ring when using an indicator.

Safety Precautions

Key-type Selector Switches Subassemblies A30N (Common)

Accessories and Tools


Ordering Information


Item	Appearance	Classification	Model	Remarks
Small Legend Plate Frame		Black	A22NZ-A-50103	Legend Plate with no text on black background included. For 22.3-mm panel hole diameter.
			A22Z-3443B	Black
		NAPal and	A22Z-3443R	Red
		Without text	A22Z-3443W	White
			A22Z-3443C	Transparent
		0	A22Z-3443R-2	Mile to the second by a least one of
		STOP	A22Z-3443R-4	White text on red background
Small Legend Plates			A22Z-3443B-1	
(Standard Size)		START	A22Z-3443B-3	
		ON	A22Z-3443B-5	
		OFF	A22Z-3443B-6	Mile to the death and a second
		UP	A22Z-3443B-7	White text on black background
		DOWN	A22Z-3443B-8	
		POWER ON	A22Z-3443B-9	
		OFF-ON	A22Z-3443B-10	
Large Legend Plate Frame		Black	A22NZ-A-51103	Legend Plate with no text on black background included. For 22.3-mm panel hole diameter.
			A22Z-3453B	Black
Large Legend Plates		Without text	A22Z-3453W	White
3 3			A22Z-3453C	Transparent
Tightening Wrench	0		A22NZ-A-301	Used to tighten Mounting Nuts from the back of the panel.
LED Lamp Extractor			A22NZ-A-302	Made of rubber and used to easily remove and attach LED Lamps.
Cap Tightening Wrench	6		A22Z-3908	Used to replace the Caps on Flat, Projected, and Full-guard Pushbutton Switches.

Accessories and Tools

Dimensions (Unit: mm)


Protective Cover A22NZ-A303






Plastic Hole Plug A22NZ-A-401






Metal Hole Plug A22NZ-A-402






Lock Ring A22NZ-A-403







Lock Ring A22NZ-A-50501





Reinforcement Plate A22NZ-A-C01







Two, 16.1-dia. (Bottom lead hole)

Two, 4.4-dia (Oval mounting

Control Box A22NZ-A-B101 A22NZ-A-B101Y











Control Box (2 holes) A22NZ-A-B102












Accessories and Tools


Dimensions (Unit: mm)


Control Box A22NZ-A-B201 A22NZ-A-B01Y






Control Box (2 holes) A22NZ-A-B202






Control Box (3 holes) A22NZ-A-B203







Sealing cap For Flat Models A22Z-3600F



For projection models A22Z-3600T



For full-guard models A22Z-3600G




Accessories and Tools


Dimensions (Unit: mm)


Resin Attachment for 30 dia.






Legend Plate Frames General A22NZ-A-50103






Large A22NZ-A-51103






Legend Plates General A22Z-3443□-□






Large A22Z-3453□






Tightening Wrench A22NZ-A-301




LED Lamp Extractor A22NZ-A-302



Cap Tightening Wrench A22Z-3908





Safety Precautions

Refer to Safety Precautions for All Pushbutton Switches/Indicators.

Signal Word Definitions

Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction, or undesirable effects on product performance.

Precautions for Safe Use

For both the Screw terminal block type and the Push-In Plus terminal block type

- Do not perform wiring with power supplied to the Switch/Indicator.
 Do not touch the terminals or other charged parts while power is being supplied. Doing so may result in electric shock.
- Do not disassemble or modify the Switch/Indicator under any circumstances.
- Doing so may prevent the Switch/Indicator from functioning to its full capability. Do not drop the Switch/Indicator. Do not apply pressure that may deform or alter the Switch/Indicator.
- The durability of the Switch varies considerably depending on the switching conditions. Always test the Switch/Indicator under actual working conditions before application and use the Switch/Indicator only for the number of switching operations allowed.
- Do not allow the load voltage and current to exceed the rated value. This may damage or burn out the Switch/Indicator.
- Do not use the Switch/Indicator in locations where explosive or flammable gases or liquid may be present or scattered. The electric ark or the heat caused by switching contacts may cause a fire or explosion.
- Do not use the Switch/Indicator in locations where toxic gases, such as H₂S, SO₂, NH₃, HNO₃, and Cl₂, may be present, or in locations subject to high temperature or humidity. Doing so may damage the Switch/Indicator due to contact failure or corrosion.
- Do not use the Switch/Indicator submersed in oil or water, or in locations continuously subject to splashes of oil or water. Doing so may result in oil or water entering and damaging the Switch/ Indicator.
- Do not use or keep the Switch/Indicator under the following conditions:
 - Subject to severe temperature changes.
 - · Subject to high humidity or condensation.
 - · Subject to severe vibration or shock.
 - Where direct rays of the sun strike.
 - Where sea breeze may be present.
- Make sure that a rubber washer is present between the Operation Unit and the panel. Otherwise, the specifications of the protective structure may not be satisfied.
- Do not apply excessive force to the Switch or wiring.
 A damaged or deformed contact block may cause contact failure.
- Use an appropriate wire and ferrule.
- Exercise caution to avoid wiring errors when connecting the terminals.

 To prevent wiring materials from smoking or igniting, confirm wire ratings and use the wiring materials given in the following table.

A22N/M22N/A30N

Model	Wire Type	Wire	Recommended Wires	Stripped length
A22N, M22N (Screw terminal block)	Solid wire/ stranded wire	Copper	1.25 to 2.5 mm ² / AWG 16 to 14	8 mm
A22N-P, M22N-P (Push-In Plus terminal block)		Соррег	0.25 to 1.5 mm ² / AWG 24 to 16	Ferrules not used: 8 mm

Use wiring crimp terminals and ferrule terminals of the specified size.

- For Push-In Plus terminal blocks, use only one wire per terminal.
 For screw terminal blocks, use no more than two wires of the same size and type with no more than two crimp terminals per terminal.
- After storing the product for a long time exceeding 1 year, perform, at a minimum, inspections of the operating characteristics, contact resistance, insulation resistance, and dielectric strength as well as evaluate the product under the working conditions.
- This Switch/Indicator is intended for indoor use only.
 Using the Switch/Indicator outdoors may result in failure.

Push-In Plus Terminal Blocks

- Do not wire anything to the release holes.
- Do not tilt or twist a flat-blade screwdriver while it is inserted into a release hole on the terminal block. The terminal block may be damaged.
- Insert a flat-blade screwdriver into the release holes at an angle.
 The terminal block may be damaged if you insert the screwdriver straight in.
- Do not allow the flat-blade screwdriver to fall out while it is inserted into a release hole.
- Do not bend a wire past its natural bending radius or pull on it with excessive force.
- Doing so may cause the wire disconnection.
- Do not insert more than one wire into each terminal insertion hole.
- Do not mount A22N-P Push-In Plus terminal contact blocks on A22N screw terminal blocks. Doing so may result in unsatisfactory performance.

Precautions for Correct Use

Mounting

• Do not tighten the Mounting Nut more than necessary using tools such as pointed-nose pliers. Doing so will damage the Mounting Nut. (The tightening torque of the Mounting Nut is 1.0 to 2.0 N·m.)


Wiring (Screw terminal block)

- Terminal screws must be M3.5 Phillips or slotted screws with a square washer.
- The terminal screw tightening torque is 1.0 to 1.3 N·m.
- Solid wires, stranded wires, and crimp terminals can be connected to the Switch/Indicator.

Bare Crimp Terminals




Crimp Terminals with Insulating Sheathes




Wiring (Push-in Plus terminal block)

1. Connecting Wires to the Push-In Plus Terminal Block

Part Names of the Terminal Block <A22N>




<M22N>



Connecting Wires with Ferrules and Solid Wires


- Insert the solid wire or ferrule straight into the terminal block until the end strikes the terminal block. The angle should be approximately 6°.
- If a wire is difficult to connect because it is too thin, use a flat-blade screwdriver in the same way as when connecting stranded wires.

<A22N>



The wiring for the Lighting Unit and Contact Block (2 contacts) are the same as for the Contact Block (1 contact) shown in the above illustration.

<M22N>




Connecting Stranded Wires

Use the following procedure to connect the wires to the terminal block.


- Hold a flat-blade screwdriver at an angle and insert it into the release hole.
 - The angle should be approximately 6°. If the flat-blade screwdriver is inserted correctly, you will feel the spring in the release hole.
- With the flat-blade screwdriver still inserted into the release hole, insert the wire into the terminal hole until the end strikes the terminal block.
- 3. Remove the flat-blade screwdriver from the release hole.

<A22N>



The wiring and screwdriver angles for the Lighting Unit and Contact Block (2 contacts) are the same as for the Contact Block (1 contact) shown in the above illustration.

<M22N>



Checking Connections

- After the insertion, pull gently on the wire to make sure that it will not come off and it is securely fastened to the terminal block.
- If you use a ferrule with a conductor length of 10 mm, part of the conductor may be visible after the ferrule is inserted into the terminal block, but the product insulation distance will still be satisfied.


2. Removing Wires from the Push-In Plus Terminal Block

A22N/M22N/A30N

Use the following procedure to remove wires from the terminal block. The same method is used to remove stranded wires, solid wires, and ferrules.


- Hold a flat-blade screwdriver at an angle and insert it into the release hole. The angle should be approximately 6°.
- With the flat-blade screwdriver still inserted into the release hole, remove the wire from the terminal insertion hole.
- 3. Remove the flat-blade screwdriver from the release hole.

<A22N>



The wiring and screwdriver angles for the Lighting Unit and Contact Block (2 contacts) are the same as for the Contact Block (1 contact) shown in the above illustration.


<M22N>



3. Recommended Ferrules and Crimp Tools Recommended ferrules


Applic		Ferrule Conductor	Stripped length (mm)	Recor	nmended f	ended ferrules	
(mm²)	(AWG)	Length (mm)	(Ferrules used)	Phoenix Contact product	Weidmuller product	Wago product	
0.25	24	8	10	AI 0,25-8	H0.25/12	216-301	
0.23	24	10	12	AI 0,25-10			
0.34	22	8	10	AI 0,34-8	H0.34/12	216-302	
0.34	22	10	12	AI 0,34-10			
0.5	20	8	10	AI 0,5-8	H0.5/14	216-201	
0.5 20	10	12	AI 0,5-10	H0.5/16	216-241		
0.75	18	8	10	AI 0,75-8	H0.75/14	216-202	
0.73	10	12	AI 0,75-10	H0.75/16	216-242		
1/1.25	18/17	8	10	AI 1-8	H1.0/14	216-203	
1/1.23	10/17	10	12	AI 1-10	H1.0/16	216-243	
1.25/1.5	17/16	8	10	AI 1,5-8	H1.5/14	216-204	
1.23/1.3	17/10	10	12	AI 1,5-10	H1.5/16	216-244	
Recommended Crimp Tools		CRIMPFOX6 CRIMPFOX6T-F CRIMPFOX10S	PZ6 roto	Variocrimp4			

- Note: 1. Make sure that the outer diameter of the wire coating is smaller than the inner diameter of the insulation sleeve of the recommended ferrule.
 - 2. Make sure that the ferrule processing dimensions conform to the following figures.



Recommended Flat-Blade Screwdrivers

Use a flat-blade screwdriver to connect and remove wires. Use one of the following flat-blade screwdrivers. The following table shows manufacturers and models as of 2015/Dec.



Model	Manufacturer
ESD 0,40 x 2,5	Wera
SZS 0,4 x 2,5 SZF 0-0,4 x 2,5 *	Phoenix Contact
0.4 x 2.5 x 75 302	Wiha
AEF.2,5 x 75	Facom
210-719	Wago
SDI 0.4 x 2.5 x 75	Weidmuller


- OMRON's exclusive purchase model XW4Z-00B is available to order as SZF 0-0,4 x 2,5 (manufactured by Phoenix Contact).
- After wiring the Switch/Indicator, provide a sufficient insulation distance.

The following information applies to both screw terminal blocks and Push-In Plus terminal blocks.

LED Lamps

- A current-limiting resistor is built in the LED lamp, so the installation of an external resistance is not required. A diode bridge is equipped in 6, 12, and 24 V specifications. As such, there is no specific polarity. Use only AC power for 100 and 200 V specifications.
- Lighting malfunction of the LED lamp A micro-current of approximately 0.1 mA or less is sufficient to turn on the LED lamps. Take a countermeasure like adding a resistor to prevent mis-lighting in parallel to the LED lamp. The micro-current varies with the machine (leak current or stray capacity between cables, etc.). Select resistance value and allowable power consumption that meet the actual current.

(Example of lighting malfunction prevention circuit) When using a 24-VAC/VDC lighted unit



Key-Type Selector Switches

. Make sure to insert the key to the bottom of the cylinder before turning it.

Button Operation

• Do not rotate or pull on the button on a Mushroom Switch. The button may come off, preventing operation.

Application

Mounting to the Panel Panel Hole Dimensions


<A22N>


- Panel hole dimensions are given below.
- The recommended panel thicknesses are given below.

Panel hole dimension	Panel thickness *
22.3 dia.	0.8 to 5 mm
25.5 dia.	0.8 to 6 mm


- * Panel thickness without accessories (Lock Ring, etc.)
- If outer surface treatment such as coating is performed for the panel, the panel dimensions after outer surface treatment must meet the specified panel dimensions.
- The following figure gives pitch dimension A and pitch dimension B between the centers of the mounting holes.

Panel Hole Dimensions for 22.3 Diameter





Panel Hole Dimensions for 25.5 Diameter



Note: Dimensions A and B are the same.

Dimension A

Wire type	Number of linked Contact Blocks	Number of wires per terminal	Minimum allowable pitch Dimension A (mm) or larger
Leads (stranded wire / solid wire)	1	1	50
Bare crimp terminals	1	1	50
Crimp terminals with insulating sheathes	1	1	60

Note: The minimum mounting pitch is based on three Contact Blocks in stage 1 with one wire attached to each terminal. If the Mounting Collar lock levers all face the same direction at the minimum mounting pitch, be sure to note the order the mounting collars are attached to the Operation Unit. If you attach two wires or link Units, determine the mounting pitch based on the dimensions diagrams and ease of operation

Dimension A When Using Accessory

- Dimension A is 50 mm minimum when a Standard Legend Plate Frame is attached.
- Dimension A is 51 mm minimum when a Large Legend Plate Frame is attached
- Dimension A is 75 mm minimum when a Protective Cover is attached.

Dimension B


Operation Unit shape	Dimension B
Mushroom	40 mm min.
Other than the above	30 mm min.

A22N/M22N/A30N


<M22N>

- Panel hole dimensions are given below.
- Acceptable panel thickness is between 0.8 and 6 mm.
- If outer surface treatment such as coating is performed for the panel, the panel dimensions after outer surface treatment must meet the specified panel dimensions.

Panel Hole Dimensions for 22.3 Diameter




Panel Hole Dimensions for 25.5 Diameter



<A30N>

- · Panel hole dimensions are given below.
- · Acceptable panel thickness is between 0.8 and 6 mm.
- · If outer surface treatment such as coating is performed for the panel, the panel dimensions after outer surface treatment must meet the specified panel dimensions.
- The following figure gives pitch dimension A and pitch dimension B between the centers of the mounting holes.

Panel Hole Dimensions



Dimension A

Wire type	Number of linked Contact Blocks	Number of wires per terminal	Minimum allowable pitch Dimension A (mm) or larger
Leads (stranded wire / solid wire)	1	1	50
Bare crimp terminals	1	1	50
Crimp terminals with insulating sheathes	1	1	60

Note: The minimum mounting pitch is based on three Contact Blocks in stage 1 with one wire attached to each terminal. If the Mounting Collar lock levers all face the same direction at the minimum mounting pitch, be sure to note the order the mounting collars are attached to the Operation Unit. If you attach two wires or link Units, determine the mounting pitch based on the dimensions diagrams and ease of operation and wiring.


Dimension B

Operation Unit shape	Dimension B
Mushroom	40 mm min.
Other than the above	35 mm min.


Mounting the Operation Unit

<A22N>

Panel Hole of 22.3-mm Diameter
Insert the Operation Unit from the front of the panel, insert the
Lock Ring and Mounting Nut from the back of the panel, and
tighten the Mounting Nut. Before tightening, check that the rubber
washer is present between the Operation Unit and the panel.




Panel Hole of 25.5-mm Diameter
 Do not use the Lock Ring, and tighten the Mounting Nut while confirming that the projecting part (see following figure) on the Mounting Nut is aligned with mounting hole. Before tightening, check that the rubber washer is present between the Operation Unit and the panel.



 Align the Lock Ring with the slot on the case and insert it so that the edge is flush with the panel.

<A30N>


 Insert the Operation Unit from the front of the panel, insert the Lock Ring and Mounting Nut from the back of the panel, and tighten the Mounting Nut. Before tightening, check that the rubber washer is present between the Operation Unit and the panel.




Mounting the Indicator Unit

<M22N>

Panel Hole of 22.3-mm Diameter
Insert the Indicator Unit from the front of the panel, insert the
Mounting Nut from the back of the panel, and tighten the Mounting
Nut. Before tightening, check that the rubber washer is present
between the Indicator Unit and the panel.




Panel Hole of 25.5-mm Diameter
 Tighten the Mounting Nut while confirming that the projecting part
 (see following figure) on the Mounting Nut is aligned with mounting
 hole. Before tightening, verify that the rubber washer is present
 between the Operation Unit and the panel.




Mounting the Lock Ring

<A22N/A30N>


 Align the grooves on the Operation Unit with the protruding parts of the Lock Ring and mount.




- When experiencing difficulties when mounting a Lock Ring, use the following procedure.
 - 1. Insert the Lock Ring into groove A on the Operation Unit.



When the Lock Ring is in the position shown in the figure below, rotate it to insert the protruding part of the Lock Ring into groove B on the Operation Unit.




When the Lock Ring is in the position shown in the figure below, move it in the direction indicated by the arrow.



Mounting the Contact Block to the Operation Unit <A22N/A30N>


 Insert the Operation Unit into the Mounting Collar, aligning the TOP mark inscribed on the Operation Unit with the lever on the Mounting Collar, and then turn the lever in the direction indicated by the arrow in the following figure all of the way until it clicks into place.


A22N/M22N/A30N



Removing the Mounting Collar <A22N/A30N>


 Press the lock lever in from the back side to release the lock, and then hook the Mounting Collar with a screwdriver, move it in the direction indicated at (2), and remove it. Turn the lever all of the way until it clicks into place.






Attaching the Switch Unit to the Indicator Unit <M22N>

 Align the "TOP" marks on the Indicator Unit and Switch Unit and insert the Indicator Unit into the Switch Unit. Insert it all the way until it clicks into place.




Removing the Switch Unit <M22N>


 Insert a screwdriver into the tab on the Switch Unit. Move the screwdriver in direction (2) to remove the Switch Unit.



Contact Block and Lighting Unit Attaching the Contact Block and Lighting Unit

 Catch the projection on the opposite side of the Mounting Collar from the lever side and press the Contact Block in the direction indicated at (1). Attach the Lighting Unit at Unit position 2 on the Mounting Collar.







When attached

Removing the Contact Block and Lighting Unit


 Insert a screwdriver into the gap between the Mounting Collar and Contact Block and press it inward in the direction shown at (2). A Lighting Unit can be removed at Unit position 2 on the Mounting Collar





Attaching the Reinforcement Plate (Screw terminal block type)

• To link Contact Blocks together, attach a Reinforcement Plate in the direction shown in the following figure. To remove the Plate, insert a screwdriver in the direction indicated at (1) and rotate it in the direction indicated at (2).




Engraving (Except for Non-Lighted / Opaque Types)

- Engrave legends on the Legend Plates.
 Do so with the straight part of the Legend Plate positioned on the right and left.
- The characters must be engraved no deeper than 0.5 mm. Use an alcohol-based paint, such as a melamine, phthalic acid, or acrylic resin based paint.

<A22N/A30N>

Projected, Full-guard, or Mushroom Switches	Flat Switches
15.4 dia.	17.7 dia.


<M22N>




Attaching Character Films (Except for Non-Lighted / Opaque Types) <A22N/A30N>

• To attach a character film, remove the Button and attach the film, aligning it with the straight portions of the Legend Plate.


Projected Switches Full-guard Switches



Mushroom Switches



Flat Switches



 Prepare films of the following sizes depending on the type of Legend Plate.


A22N/M22N/A30N

• The films must be provided by the user.

Projected, Full-guard, or Mushroom Switches	Legend Plate dimensions	Display range 15.4 dia. 1.6 5.15 15.9 dia.
	Film dimensions	17.1% dia. 17.4% T = 0.1 to 0.2 mm
Flat Switches	Legend Plate dimensions	Display range 17.7 dia.
Flat Switches	Film dimensions	19.6° _{0.2} dia. 19.6° _{0.2} dia. 17.5° _{0.2} T = 0.1 to 0.2 mm


<M22N>

• To attach a character film, remove the Button and attach the film, aligning it with the straight portions of the Legend Plate.




Semi-spherical Switches

Сар



Projected Switches




 Film processing dimensions should be as per the indications below.

Legend Plate dimensions	21 dia. 1
Film dimensions	22.7° _{.0.2} dia. 22.8° _{.0.2} T=0.1 to 0.2 mm


Removing and Tightening the Cap

For all Switches except for Mushroom Switches, use the A22Z-3908 Cap Tightening Tool to loosen the cap. When you tighten the cap, make sure that the Legend Plate is in the correct position and then turn the cap in the direction opposite of the direction shown in the following figure. Tighten it to a torque of 0.5 to 1.0 N·m so that it will not become loose.



Attaching the LED Lamp to the Lighting Unit


 Insert the protrusions on the LED Lamp into the guides on the Lighting Unit and then turn the LED Lamp in direction (2) to lock it in place.



Attaching and Replacing LED Lamps Removing the LED Lamp from the Panel Surface

 Insert the LED Lamp Extractor as shown in the following figure and then rotate the Extractor in the direction shown at (2) while pressing it inward.







Attaching the LED Lamp from the Panel Surface

 Insert the LED Lamp into the LED Lamp Extractor as shown in the following figure. Align the projections on the LED Lamp with the LED Lamp insertion guides, insert the LED Lamp, and turn it in the direction indicted at (2).

<A22N>




<M22N>




Control Box

You can attach a Legend Plate Frame. Attach it in the direction shown in the following figure. Mount the Switch in the same way as for a standard panel. The tightening torque of the Box screws is 1.4 to 2.0 N·m.



Creating a Cable Hole


To open a cable hole, leave the cover attached, place the tip of a screwdriver in the grooves at four locations around the cable hole, strike the screwdriver with a hammer in order at the four locations to open the hole, and remove the part from the cable hole.



Attaching the Connector and Cable


- Insert the connector into the cable port hole in the Box and secure with the fixing nut inside the box.
- 2. Run the cable through the tightening cap, insert the cable into the connector, and then tighten the hexagonal nut to secure the cable.

Cable diameter (mm)	Connector
7 to 9 dia.	A22Z-3500-1
9 to 11 dia.	A22Z-3500-2



Attaching and Removing Legend Plates

- Press the Legend Plate into the depression in the Legend Plate Frame. The Legend Plate Frame can be separate or it can be mounted on the panel when you attach the Legend Plate.
- The direction of the characters will depend on the mounting direction of the Operation Unit if the Switch is a Selector Switch or Key Selector Switch.



- You can easily remove the Legend Plate by pressing it forwards from the back of the Legend Plate Frame.
- The acrylic plastic Legend Plate is easily damaged by shock.
 Handle it with care.




Attaching the Lock Ring


Attach the Lock Ring as shown in the following figure.

To ensure water resistance, attach the rubber washer in the specified location.


*1. Lock Ring is sold separately. (Model: A22NZ-A-403)



 Align the TOP mark on the Operation Unit, part A on the Legend Plate, and the notch in the panel, and insert the Operation Unit.




- *2. This is the panel thickness when using Lock Ring.
- If there is no notch in the panel, remove part A from the Legend Plate with pliers.



Attaching the Protective Cover

Attach the Protective Cover (A22NZ-A-303) to a panel that is 0.8 to 1.0 mm thick. To ensure water resistance, attach the rubber washer in the specified location.



Attaching the Sealing Cap


<A22N/M22N>

• Panel acceptable thickness is given below.

Panel hole dimension	Panel thickness
22.3 dia.	0.8 to 4.2 mm
25.5 dia.	0.8 to 5.2 mm


Panel Hole of 22.3-mm Diameter

Attach the Sealing cap as shown in the following figure. To ensure water resistance, attach the rubber washer in the specified location.




Panel Hole of 25.5-mm Diameter

Attach the Sealing cap as shown in the following figure. Do not use the Lock Ring, and tighten the Mounting Nut while confirming that the projecting part on the Mounting Nut is aligned with mounting hole. To ensure water resistance, attach the rubber washer in the specified location.




Mounting the 30-dia. Resin Attachments

- Acceptable panel thickness is between 1.8 and 2.2 mm.
- Mount the attachment as shown in the following figure.
- To ensure water resistance, attach the rubber washer in the specified location.



<M22N>

- Acceptable panel thickness is between 1.8 and 2.2 mm.
- Mount the attachment as shown in the following figure.
- Purchase and mount a separate lock ring (A22NZ-A-50501).
- To ensure water resistance, attach the rubber washer in the specified location.



-	
MEMO	

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability: Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2016-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_4_13

Cat. No. A254-E1-09 1125 (0916)