OMRON



» Fast programming with Function Blocks

» Flexible Ethernet connectivity

» Easy positioning functionality


Think big... start small!

Omron's vast experience in the field of industrial automation has resulted in the creation of the right products for your applications, ranging from simple to more complex automation solutions. The CP family of programmable controllers provides you with a complete product line-up to automate compact machines and perform any other simple automation tasks, quickly and easily. Programming and operation are consistent with Omron's other modular Programmable controllers. And you are guaranteed the same high quality and reliability that you expect from any Omron product, ensuring that your equipment keeps on giving continuous dependable performance.

Scalable solution

The CP family is scalable; this means that you can choose the products with the right level of sophistication to meet your automation needs in terms of functionality, flexibility and pricing. Each of the CP family models, the CP2E, CP1L and CP1H, offers the functionality required for complete machine control. Benefits include: easy expansion of I/O, fast and versatile communication, and full positioning capabilities via ready-to-use Function Blocks. The CP family uses the same instruction set and professional programming software found in Omron's other modular Programmable controllers.





Fast and versatile communication

Flexible, fast and yet cost-effective communication is essential in today's competitive market. This applies in particular to compact Programmable controllers, which not only need to connect with devices inside the machine, but also outside the machine for operating, data-logging and remote access. With this in mind, Omron has given the CP family excellent communication capabilities for both serial and Ethernet networking. In addition, Omron provides flexible and economical option boards for serial communication.

Flexible Ethernet connectivity

To meet communication needs over different protocols simultaneously and to easily connect for remote access, our CP2E-N-type, CP1L-EM, and CP1L-EL Programmable Controllers feature embedded Ethernet with socket services functionality. This offers, among other things, programmable connectivity to third-party devices and makes this outstanding product the best-in-class machine controller on the market.

Easy positioning functions

The CP family is designed to fulfill position control tasks. Up to four axes of servo-drives can be controlled with high-speed pulse outputs, while high-speed pulse inputs can allow the connection of up to four encoders. Control is easily achieved with Function Block or standard functions without the need of specialist motion boards or expansion units. Furthermore, thanks to its fast serial ports, the CP family is also capable of performing simple positioning tasks. With the use of Modbus Function Blocks, up to 31 inverters can be controlled and monitored in real-time.

Easy positioning, quick results


The CP family is the perfect choice for any application that requires positioning. Whether for conveyor control, point-to-point position control, or non-interpolated pick-and-place systems, the combination of high-speed pulse outputs, variable speed drive control and position feedback will provide all the functionality that you need for your application.

Ideal for position control

When simplicity and ease of use are essential, there is no better solution for your position applications than combining the CP family with servos and inverters from Omron's extensive range. The SmartStep 2 servo drive is a perfect partner and offers high performance while keeping things simple and cost effective. Omron provides standard functions and Function Blocks for SmartStep 2 and other servo drives to create your application with minimal effort.

Easy variable speed drive control

Variable speed drive control is made easy within the CP family by using the serial port(s) and the Easy Modbus Master feature for high-speed communication. Omron Function Blocks enable you to control and monitor up to 31 inverters in real-time simply by configuration of parameters. With the encoders connected to the high-speed counter inputs, the CP is able to calculate the exact position to perform accurate positioning easily and quickly. In addition, in the MX2 inverter series, all simple positioning is handled within the drive itself.



For many standard functions Omron provide ready-to-use and tested Function Blocks that allow you to reduce your programming and testing time. With Function Blocks you achieve faster, easier and more structured programming that can also increase machine functionality. Ladder programming still remains the easiest language for many people to use, but for more complex mathematical calculations 'Structured Text' (ST) offers greater flexibility. These languages are supported in the CP2E, CP1L and CP1H. Omron's software is renowned for its ease of use and intuitive style and CX-One is no exception.


Flexible Ethernet connectivity

As simple and quick- as USB!

Thanks to the CP2E-N-type's, CP1L-EM's, or CP1L-EL's Automatic-Connect function, programming over Ethernet is as simple as using USB on the other models in the CP family. This means that you don't need to waste time adjusting the Ethernet settings on the PC, but that you can simply plug and connect, just like USB. The Automatic-Connect function connects instantly over a default IP address to the CP1L, saving you valuable set-up time.

Versatile communication

CP2E-N-type's, CP1L-EM's, or CP1L-EL's are equipped as standard with Socket Services. This facilitates the easy exchange of data with other Ethernet devices supporting a dedicated protocol. The Socket Services reduce effort and simplify programming and allow Ethernet protocols to be used directly from your Programmable controller program. Ethernet can also be used for applications that require remote access functionality, such as a secure VPN connection with a standard router.



More options - greater possibilities!

More analog I/Os

In addition to the two standard embedded analog inputs, Omron's CP1L with embedded Ethernet also supports three new, optional analog I/O boards. These enable you to add extra analog inputs and outputs, and mixed inputs/outputs at minimum cost and without the need for more cabinet space. With its analog I/O modules, auto-tuning PID function, the CP is ideal for accurate process control.

Note: The optional analog I/O board can be mounted in CP1L-EM, CP1L-EL, or CP2E-N-type.

CP family features at a glance

- 10 to 60 I/O base models, expandable to 320 I/O points
- Digital, analog and temperature sensor I/O expansion units
- 4 to 6 High-speed encoder inputs and
 2 to 4 high-speed pulse outputs
- Modbus Master feature for easy inverter or temperature control
- Analog I/O option boards and auto-tuning PID for accurate process control
- Optional boards for RS-232/RS-422/485/Ethernet or LCD display
- Ladder diagram, Function Block or Structured Text programming
- Powerful instructions common within Omron's modular Programmable controller series
- USB or Ethernet port no special cables needed
- No-Battery mode operation retains the program and data



Expansion units for more flexibility

An analog unit with up to four embedded analog inputs and four outputs achieves a high resolution of 12,000. A wide variety of temperature sensor units are available including: multi-input (thermocouple and analog inputs), platinum-resistance thermometer input, and thermocouple input models. Units with up to 12 embedded thermocouple inputs can be used for multiple temperature input applications, e.g. molding machines.



Note: The functions that are supported depend on the model.

Maximize efficiency by selecting the optimum CPU unit for your applications

								annum.						
		CP2E												
		E-type					S-type			N-type				
			s 20 I/O Point	s 30 I/O Points	40 I/O Points	s 60 I/O Points		40 I/O Points	s 60 I/O Points		s 20 I/O Points	s 30 I/O Points	40 I/O Points	s 60 I/O Points
1/0	Digital Inputs	8	12	18	24	36	18	24	36	8	12	18	24	36
	Digital Outputs	6	8	12	16	24	12	16	24	6	8	12	16	24
	Removable Terminals	No	U	12	10		12	10		· ·	· ·	12	10	
	Total I/O Capacity	14	20	150	160	180	150	160	180	14	20	150	160	180
		No	20			100		100	100	No No	20			100
	CP1W Expansion Units	NO		Yes (3 max.)			Yes (3 max.)			IVO		Yes (3 max.)		
	CJ-Series Special I/O and CPU Bus Units	No												
	Interrupt/Quick/	6								6	8			
	Counter Inputs													
	High Speed Counter Inputs	2 (100 kHz max.) / 4 (10 kHz max.) 3 (100 kHz max.) / 3 (10 kHz max.) / 3 (10 kHz max.)											kHz max.)	
	Pulse Outputs (transistor outputs models only)	No					2 axes (100 kHz max.)					4 axes (100 kHz max.)		
	Analog I/O (embedded)	No												
	Analog Adjuster (0-255)) No												
	External Analog Settings Input (resolution 1/256)	No												
	Number of boards supported	0					1					2		
	(CP1W-CIF01/11/12-V1)	No								Yes				
	2-ports Serial Communications (CP1W-CIFD1/D2/D3)	No Yes Yes (1 unit only)												
	Ethernet (CP1W-CIF41)	No												
	1 7 (No												
	Analog I/O boards	No								Yes		Yes (1 unit only)		
4-4-11-	Built-in port	USB, RS-232	2C				USB, RS-232C, RS-485 Ethernet							
	Function Blocks support (Ladder diagrams or ST language)	Yes												
	Processing Speed (minimum)	0.23 μs / Basic instruction, 1.76 μs / Special instruction												
	Program Capacity	4K steps					8K steps			10K steps				
	Data Memory Capacity	4K words					8K words 16K words							
	Memory Cassette (CP1W-ME05M)	No												
	Real-Time Clock	No					Yes							
	Battery	Battery-free required for data memory backup					Battery-free required for data memory backup (CP2W-BAT02 is required to use the clock.)							
	7-Segment Display	No												
Outputs	AC Power Supply	CP2E -E14DR-A	CP2E -E20DR-A	CP2E -E30DR-A	CP2E -E40DR-A	CP2E -E60DR-A		CP2E -S40DR-A	CP2E -S60DR-A	CP2E -N14DR-A	CP2E -N20DR-A	CP2E -N30DR-A	CP2E -N40DR-A	CP2E -N60DR-A
	DC Power Supply								-	CP2E -N14DR-D	CP2E -N20DR-D	CP2E -N30DR-D	CP2E -N40DR-D	CP2E -N60DR-D
Transistor Outputs	Туре				-		- CDOE	CDOE	- CD2E	CP2E -N14DT-A	CP2E -N20DT-A	CP2E -N30DT-A	CP2E -N40DT-A	CP2E -N60DT-A
	DC Power Supply Source DC Power Supply						CP2E -S30DT-D CP2E	CP2E -S40DT-D CP2E	CP2E -S60DT-D CP2E	CP2E -N14DT-D CP2E	CP2E -N20DT-D CP2E	CP2E -N30DT-D CP2E	CP2E -N40DT-D CP2E	CP2E -N60DT-D CP2E
	Type table is a general overview		dataila rafar	to the CDOF	dataahaat (C	ot No. D145	-S30DT1-D	-S40DT1-D	-S60DT1-D	-N14DT1-D	-N20DT1-D	-N30DT1-D	-N40DT1-D	-N60DT1-D





			CP1L									CP1H			
			L-type			M-type			EL-type	EM-type		Y-type	X-type	XA-type	
			10 I/O Points	14 I/O Points	20 I/O Points	30 I/O Points	40 I/O Points	60 I/O Points	20 I/O Points	30 I/O Points	40 I/O Points	20 I/O Points	40 I/O Points	40 I/O Points	
1/0	Digital	Inputs	6	8	12	18	24	36	12	18	24	12	24	24	
	Digital	Outputs	4	6	8	12	16	24	8	12	16	8	16	16	
	Remov	able Terminals	No			Yes			No	Yes		Yes			
	Total I/	O Capacity	10	54	60	150	160	180	60	150	160	300	320	320	
	CP1W	Expansion Units	No	Yes (1 max.)		Yes (3 max.)			Yes (1 max.) Yes (3 max.)			Yes (7 units or 15 input words / 15 output words max.)			
	CJ-Seri and CP	ies Special I/O 'U Bus Units	No						No			Yes (2 max.)			
		pt/Quick/ r Inputs	2	4 6					6			6	8		
	High S _i Inputs	peed Counter	4 (100 kHz max.)						4 (100 kHz max.)			2 (100 kHz max.) and 2 Line-driver (1 MHz)	4 (100 kHz m	ax.)	
		Outputs stor outputs s only)	2 axes (100 kHz max.) 2 axes							axes (100 kHz max.)			4 axes (100 k	Hz max.)	
	Analog (embed		No						2 inputs			No 4 inputs, 2 outputs			
	Analog	Adjuster (0-255)	Yes (1)						No			Yes (1)			
	Setting	al Analog s Input tion 1/256)	Yes (0-10V)						No			Yes (0-10V)			
Optional boards	Numbe suppor	er of boards ted	0 1			2			1	2		2			
		Communications '-CIF01/11/12-V1)	No Yes						Yes			Yes			
		s Serial unications '-CIFD1/D2/D3)	No												
	Etherne (CP1W	et V-CIF41)	No Yes						No			Yes			
	LCD Dis	play (CP1W-DAM01)	No Yes						Yes			Yes			
	Analog	I/O boards	No						Yes			No			
CPU	Built-in	port	USB						Ethernet			USB			
details		on Blocks support r diagrams or ST ge)	Yes						Yes			Yes			
	Proces (minim	sing Speed ium)	0.55 μs / Basic instruction, 4.1 μs / Specia			I instruction			$0.55~\mu s$ / Basic instruction, 4.1 μs / Special instruction			0.10 μs / Basic instruction, 0.15 μs / Special instruction			
	Program Capacity		5K steps 10K steps					5K steps			20K steps				
			10K words	OK words 32K words					10K words			32K words			
		ry Cassette '-ME05M)	Yes						Yes			Yes			
	Real-Ti	me Clock	Yes							Yes			Yes		
	Battery		Yes (CJ1W-BAT01)					Yes (CJ1W-BAT01)			Yes (CJ1W-BAT01)				
	7-Segment Display		No					No			Yes				
Relay Outputs	AC Power Supply		CP1L -L10DR-A	CP1L -L14DR-A	CP1L -L20DR-A	CP1L -M30DR-A	CP1L -M40DR-A	CP1L -M60DR-A	-	-	-	-	CP1H -X40DR-A	CP1H -XA40DR-A	
	DC Power Supply		CP1L -L10DR-D	CP1L -L14DR-D	CP1L -L20DR-D	CP1L -M30DR-D	CP1L -M40DR-D	CP1L -M60DR-D	CP1L -EL20DR-D	CP1L -EM30DR-D	CP1L -EM40DR-D	-	-	-	
Transistor Outputs	Sink Type	AC Power Supply	-L10DT-A	CP1L -L14DT-A	CP1L -L20DT-A	CP1L -M30DT-A	CP1L -M40DT-A	CP1L -M60DT-A		-	-	-	-	-	
		DC Power Supply	-L10DT-D	CP1L -L14DT-D	CP1L -L20DT-D	CP1L -M30DT-D	CP1L -M40DT-D	CP1L -M60DT-D	CP1L -EL20DT-D	CP1L -EM30DT-D		CP1H -Y20DT-D	CP1H -X40DT-D	CP1H -XA40DT-D	
	Source Type	DC Power Supply	CP1L -L10DT1-D	CP1L -L14DT1-D	CP1L -L20DT1-D	CP1L -M30DT1-D	CP1L -M40DT1-D	CP1L -M60DT1-D	CP1L -EL20DT1-D	CP1L -EM30DT1-D	CP1L -EM40DT1-D	-	CP1H -X40DT1-D	CP1H -XA40DT1-D	

Expansion units

Expansion I/O Units



CP1W-8ED

DC inputs: 8

CP1W-8ER

Relay outputs: 8

CP1W-8ET

Transistor outputs (sinking): 8

CP1W-8ET1

Transistor outputs (sourcing): 8



CP1W-16ER

Relay outputs: 16

CP1W-16ET

Transistor outputs (sinking): 16

CP1W-16ET1

Transistor outputs (sourcing): 16

CP1W-20EDR1

DC inputs: 12 Relay outputs: 8



CP1W-20EDT

DC inputs: 12

Transistor outputs (sinking): 8

CP1W-20EDT1

DC inputs: 12

Transistor outputs (sourcing): 8

CP1W-32ER

Relay outputs: 32

CP1W-32ET

Transistor outputs (sinking): 32

CP1W-32ET1

Transistor outputs (sourcing): 32

CP1W-40EDR

DC inputs: 24 Relay outputs: 16

CP1W-40EDT

DC inputs: 24

Transistor outputs (sinking): 16

CP1W-40EDT1

DC inputs: 24

Transistor outputs (sourcing): 16

Analog I/O Units



Analog Input Unit CP1W-AD041

Analog inputs: 4 (resolution: 6,000)

CP1W-AD042

Analog inputs: 4 (resolution: 12,000)

Analog Output Unit

CP1W-DA021

Analog outputs: 2 (resolution: 6,000)

CP1W-DA041

Analog outputs: 4 (resolution: 6,000)

CP1W-DA042

Analog outputs: 4 (resolution: 12,000)



Analog I/O Unit CP1W-MAD11

Analog inputs: 2 (resolution: 6,000) Analog outputs: 1 (resolution: 6,000)

Analog inputs: 4 (resolution: 12,000) Analog outputs: 2 (resolution: 12,000)

CP1W-MAD44

Analog inputs: 4 (resolution: 12,000) Analog outputs: 4 (resolution: 12,000)

Temperature Sensor Unit





CP1W-TS001

Thermocouple inputs: 2

CP1W-TS002

Thermocouple inputs: 4

CP1W-TS003

Thermocouple inputs: 4 Analog inputs: 2

(instead of 2 thermocouple inputs) 12,000 resolution

CP1W-TS004

Thermocouple inputs: 12

CP1W-TS101

Platinum-resistance thermometer inputs: 2

CP1W-TS102

Platinum-resistance thermometer inputs: 4

Optional Boards



CP1W-CIF01 RS-232C



CP1W-CIF41 Ethernet *2



CP1W-CIF11 RS-422A/485 (50 m max.)



CP1W-DAM01 Display 4 rows, 12 characters *2



CP1W-CIF12-V1 RS-422A/485 (Isolated-type) (500 m max.)



CP1W-ADB21 2 analog inputs, 0-10 V, 0-20 mA



CP2W-CIFD1 2 x RS-232C *1



CP1W-DAB21V 2 analog outputs, 0-10 V



CP2W-CIFD2 RS-232C, RS-485 (Isolated-type) *1



CP2W-CIFD3 2 x RS-485 (Isolated-type) *1



CP1W-MAB221

2 analog inputs 0-10 V, 0-20 mA & 2 outputs 0-10 V

Memory Cassette



CP1W-ME05M *2

512K words

Battery Set



CP2W-BAT02 (for CP2E)



C.I1W-BAT01 (for maintenance of CP1L/CP1H)

CJ Unit Adapter



CP1W-FXT01 CJ Unit adapter for use with CP1H. Includes CJ endplate.

I/O Connecting Cable



CP1W-CN811 Length: 80 cm

CP1W Expansion Units include I/O Connection Cables (in lengths of approx. 6 cm) for side-by-side connection.

Note: This table is a general overview only. For details, refer to the CP2E datasheet (Cat. No. P145), CP1L datasheet (Cat. No. P081) or CP1H datasheet (Cat. No. P080).

- *1. Can be used with CP2E.
- *2. Cannot be used with CP2E.

Software

The CX-One is a comprehensive software package that integrates Support Software for OMRON PLCs and components. CX-One Ver. 4.□ includes CX-Programmer Ver. 9.□. CX-One Lite is a subset of the complete CX-One package that provides only the Support Software required for micro PLC applications. CX-One Lite Ver. 4.□ includes Micro PLC (the CP family) Edition CX-Programmer Ver. 9.□.

- Note 1: The CX-One and CX-One Lite cannot be simultaneously installed on the same computer.
- Note 2: This section is a general overview only. For details, refer to the CX-One Catalog (No. R134).
- Note 3: For corresponding version of CX-One and CX- Programmer, Refer to CPU Unit Hardware User's Manual.


		Media	Order code
FA Integrated Tool Package CX-One Ver.4.□	Single user licence *	DVD	CXONE-AL01D-V4
FA Integrated Tool Package CX-One Lite Ver.4.□	Single user licence	DVD	CXONE-LT01D-V4

^{*} Multi licenses are available for the CX-One (3, 10, 30, or 50 licenses).

CX-One and CX-One Lite supported OS:

Windows 7 (32-bit/64-bit version) / Windows 8 (32-bit/64-bit version) / Windows 8.1 (32-bit/64-bit version)/ Windows 10 (32-bit/64-bit version)

Using CJ-series units and CP1W units with the CP1H



Up to 7 CP1W Expansion Units and Expansion I/O Units can be connected. (Up to 3 units for CP1L and CP2E)

CP1W Expansion Units and Expansion I/O Units and CJ Units can be used simultaneously. CP1W-CN811 I/O Connecting Cable is required.

CJ-Series Units for use with CP1H

Description	Unit Name	Model	Description	Unit Name	Model
Analog I/O and	Analog Input Unit	CJ1W-AD041-V1	Motion/Position	Position Control Units	CJ1W-NC113
Control Units		CJ1W-AD042	Control Units		CJ1W-NC133
		CJ1W-AD081-V1			CJ1W-NC213
	Analog Output Unit	CJ1W-DA021			CJ1W-NC233
		CJ1W-DA041			CJ1W-NC413
		CJ1W-DA042V			CJ1W-NC433
		CJ1W-DA08V		MECHATROLINK-II Position Control Unit	CJ1W-NCF71
		CJ1W-DA08C			CJ1W-NCF71-MA
	Analog Input/Output Unit	CJ1W-MAD42			CJ1W-NC271
	Isolated- type Units with Universal Inputs	CJ1W-AD04U			CJ1W-NC471
		CJ1W-PH41U	Communication	Serial Communication Units	CJ1W-SCU21-V1
	Isolated-type DC Input Units	CJ1W-PDC15	Units		CJ1W-SCU22
	Thermocouple Input Unit	CJ1W-PTS15			CJ1W-SCU31-V1
		CJ1W-PTS51			CJ1W-SCU32
	Resistance Thermometer Input Unit	CJ1W-PTS52			CJ1W-SCU41-V1
	Temperature Control Loops,	CJ1W-TC001			CJ1W-SCU42
	Thermocouple Unit	CJ1W-TC002		Ethernet Unit	CJ1W-ETN21
		CJ1W-TC003		EtherNet/IP Unit	CJ1W-EIP21
		CJ1W-TC004		FL-net Ethernet Unit	CJ1W-FLN22
	Temperature Control Loops, RTD	CJ1W-TC101		DeviceNet Master Unit	CJ1W-DRM21
		CJ1W-TC102		CompoNet Master Unit	CJ1W-CRM21
		CJ1W-TC103		CompoBus/S Master Unit	CJ1W-SRM21
		CJ1W-TC104		Controller Link Unit	CJ1W-CLK23
Motion/Position Control Units	High Speed Counter Unit	CJ1W-CT021	High-speed Data Storage Unit	High-speed Data Storage Unit	CJ1W-SPU01-V2
Note: Including m	odels no longer available to order.		CJ Series ID Sensor	CJ Series ID Sensor Unit	CJ1W-V680C11
			Unit		CJ1W-V680C12
					CJ1W-V600C11
					CJ1W-V600C12

Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this catalog may vary somewhat from the actual products.



Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-2711

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222 Fax: (86) 21-5037-2200

Authorized Distributor:

©OMRON Corporation 2009-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_6_8

Cat. No. P082-E1-08 1122 (0405)