Safety-door Switch D4NS/D4NS-SK

CSM_D4NS_D4NS-SK_DS_E_9_8

Multi-contact, Labor-saving, Environment-friendly, Nextgeneration Safety-door Switch

- Lineup includes three contact models with 2NC/1NO and 3NC contact forms and MBB models in addition to the previous contact forms 1NC/1NO, and 2NC.
- M12-connector models are available, saving on labor and simplifying replacement.
- Applicable to both standard loads and microloads.
- Variety of metallic heads available.

Be sure to read the "Safety Precautions" on page 12.



Safety Door Switchs



Slide Keys

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Structure

Model Number Legend

Switch (Standard type)



1. Conduit Outlet/Connector

- 1:Pg13.5 (1-conduit type) 2:G1/2 (1-conduit type) 4:M20 (1-conduit type) 6:G1/2 (2-conduit type)
- 8:M20 (2-conduit type) 9:M12 connector (1-conduit type)
- 2. Built-in Switch
 - A:1NC/1NO (slow-action) B:2NC (slow-action) C:2NC/1NO (slow-action) D:3NC (slow-action) E:1NC/1NO (MBB contact) F:2NC/1NO (MBB contact)
- 3. Head Mounting Direction

F:Four mounting directions possible (Front-side mounting at shipping)/plastic

- D:Four mounting directions possible (Front-side mounting at shipping)/metal
- **Note:** An order for the head part or the switch part alone cannot be accepted. (The Operation Key is sold separately.)

Switch (High pull-force type)



- 1. Conduit Outlet 2:G1/2 (1-conduit type) 4:M20 (1-conduit type)
- 2. Built-in Switch A:1NC/1NO (slow-action) B:2NC (slow-action) C:2NC/1NO (slow-action) D:3NC (slow-action)

1. Operation Key Type

- 1:Horizontal mounting 2:Vertical mounting
- 3:Adjustable mounting (Horizontal)
- 5:Adjustable mounting (Horizontal/Vertical)

Ordering Information

Switches (Operation Keys are sold separately.)

Consult with your OMRON representative when ordering any models that are not listed in this table.

Туре	Contact con	figuration	Conduit outlet/Connector	Model
			Pg13.5	D4NS-1AF *
		1NC/1NO	G1/2	D4NS-2AF *
			M20	D4NS-4AF
			Pg13.5	D4NS-1BF *
		2NC	G1/2	D4NS-2BF *
	Olaw astian		M20	D4NS-4BF
	Slow-action		Pg13.5	D4NS-1CF *
		2NC/1NO	G1/2	D4NS-2CF *
Conduit to a			M20	D4NS-4CF
1-Conduit type			Pg13.5	D4NS-1DF *
		3NC	G1/2	D4NS-2DF *
			M20	D4NS-4DF
			Pg13.5	D4NS-1EF
		1NC/1NO	G1/2	D4NS-2EF
	Class action MDD		M20	D4NS-4EF
	Slow-action MBB contact		Pg13.5	D4NS-1FF
		2NC/1NO	G1/2	D4NS-2FF
			M20	D4NS-4FF
		1NC/1NO	G1/2	D4NS-6AF
			M20	D4NS-8AF
		010	G1/2	D4NS-6BF
		ZNC	M20	D4NS-8BF
	Slow-action	2NC/1NO	G1/2	D4NS-6CF
			M20	D4NS-8CF
2-Conduit type			G1/2	D4NS-6DF
	Slow-action 2NC/1NO	M20	D4NS-8DF	
			G1/2	D4NS-6EF
	Olever a them MDD	1NC/1NO	M20	D4NS-8EF
	Slow-action MBB contact	010/41/0	G1/2	D4NS-6FF
		2NC/1NO	M20	D4NS-8FF
	Olaur antian	1NC/1NO		D4NS-9AF
-Conduit type, vith connector	Slow-action	2NC	M12 connector	D4NS-9BF
	Slow-action MBB contact	1NC/1NO		D4NS-9EF
			G1/2	D4NS-2AF-SJ *
		1NC/1NO	M20	D4NS-4AF-SJ *
			G1/2	D4NS-2BF-SJ *
I-Conduit type		2NC	M20	D4NS-4BF-SJ *
(High pull-force type)	Slow-action		G1/2	D4NS-2CF-SJ *
		2NC/1NO	M20	D4NS-4CF-SJ *
			G1/2	D4NS-2DF-SJ *
		3NC	M20	D4NS-2DF-SJ *

* Models with Korean S-mark certification.

Operation	Keys
-----------	------

Туре	Model
Horizontal mounting	D4DS-K1
Vertical mounting	D4DS-K2
Adjustable mounting (Horizontal)	D4DS-K3
Adjustable mounting (Horizontal/Vertical)	D4DS-K5

Slide Keys

Appearance	Specifications	Contents	Model	Applicable Door Switch
	Weight: 422 g Mechanical durability: 20,000 operations min.	Slide Key (Operation Key included.): 1 Auxiliary mounting bracket: 1 Receptacle bracket: 1	D4NS-SK01	D4NS 1-conduit type
	Weight: 2,800 g Mechanical durability: 20,000 operations min.	Slide Key: 1 (Disable-prevention cover and Operation Key D4DS-K2 are already mounted on Slide Key) D4NS mounting tool: 1 Inner lever: 1 Inner lever mounting screws: 2 Door Switch mounting one-way screws: 2 Switch protective cover: 1 Switch protective cover screws: 4	D4NS-SK30	D4NS 1-conduit type

Slide Keys D4NS-SK01 Configration





D4NS 1-conduit type



D4NS-SK30 Configration





D4NS-SK30

D4NS 1-conduit type

+







The handle-shaped fixture makes it easy to use the Door Switch.

Specifications

Standards and EC Directives Conforms to the following EC Directives:

Machinery Directive

- Low Voltage Directive
- EN50047
- ENS0047
 EN60047
- EN60947-5-1EN ISO 14119
- GS-ET-15

Certified Standards

Certification body Standard		File No.
TÜV SÜD	EN60947-5-1 (certified direct opening)	Consult your OMRON representative for details.
UL *1	UL508, CSA C22.2 No.14	E76675
CQC (CCC)	GB/T 14048.5	Consult your OMRON representative for details.
KOSHA *2	EN60947-5-1	Consult your OMRON representative for details.

***1.** Certification for CSA C22.2 No. 14 is authorized by the UL mark. ***2.** Only certain models have been certified.

Certified Standard Ratings

TÜV (EN60947-5-1), CCC (GB/T 14048.5)

Item	Utilization category	AC-15	DC-13
Rated operating curr	ent (le)	3 A	0.27 A
Rated operating volta	age (U₀)	240 V	250 V

Note: Use a 10 A fuse type gI or gG that conforms to IEC60269 as a short-circuit protection device. This fuse is not built into the Switch.

UL/CSA (UL508, CSA C22.2 No. 14)

A300

Rated	Correct	Current (A)		Volt-amp	eres (VA)
voltage	Carry current	Make	Break	Make	Break
120 VAC	10 A	60	6	7.200	720
240 VAC	10 A	30	3	7,200	720

Q300

Rated Carry current		Current (A)		Volt-amperes (VA)	
voltage	Carry current	Make	Break	Make	Break
125 VDC	2.5 A	0.55	0.55	69	69
250 VDC	2.5 A	0.27	0.27	69	69

Characteristics

		-
Interlock type		Type 2 (EN ISO 14119)
Coding level		Low level coded (EN ISO 14119)
Degree of pro	tection *1	IP67 (EN60947-5-1)
Durability *2 Mechanical		<standard type=""> 1,000,000 operations min. <high pull-force="" type=""> 100,000 operations min.</high></standard>
		<standard type=""> 500,000 operations min. (3 A resistive load at 250 VAC) *3 300,000 operations min. (10 A resistive load at 250 VAC)</standard>
		<high pull-force="" type=""> 100,000 operations min. (10 A resistive load at 250 VAC)</high>
Operating speed		0.05 to 0.5 m/s

Direct opening force * 4		<standard type=""> 60 N min. <high pull-force="" type=""> 80 N min.</high></standard>	
Direct opening	g travel * 4	10 mm min.	
Contact resist	-	25 mΩ max.	
Minimum applicable load *5		1 mA resistive load at 5 VDC (N- level reference value)	
Rated insulati	on voltage (Ui)	300 V	
Rated frequen	су	50/60 Hz	
Protection aga shock	ainst electric	Class II (double insulation)	
Pollution degr environment)	ee (operating	3 (EN60947-5-1)	
Impulse withstand voltage (Uimp)	Between terminals of same polarity	2.5 kV	
(EN60947-5-1)	Between terminals of different polarity	4 kV	
	Between each terminal and non-current carrying metallic parts	6 kV	
Insulation res	istance	100 MΩ min.	
Contact gap		2×2 mm min.	
Vibration resistance	Malfunction	10 to 55 Hz, 0.75 mm single amplitude	
Shock	Destruction	1,000 m/s² min.	
resistance	Malfunction	300 m/s ² min.	
Conditional st current	nort-circuit	100 A (EN60947-5-1)	
Conventional current (Ith)	free air thermal	10 A (EN60947-5-1)	
Ambient operature	ating	–30 to 70°C (with no icing)	
Ambient opera	ating humidity	95% max.	
Weight		Approx. 96 g (D4NS-1CF)	
Note: 1 The of	oovo valuos aro i	nitial values	

Note: 1. The above values are initial values.


- *1. The degree of protection is tested using the method specified by the standard (EN60947-5-1). Confirm that sealing properties are sufficient for the operating conditions and environment beforehand. Although the switch box is protected from dust or water penetration, do not use the D4NS in places where foreign material may enter through the key hole on the head, otherwise Switch damage or malfunctioning may occur.
- *2. The durability is for an ambient temperature of 5 to 35°C and an ambient humidity of 40% to 70%. For more details, consult your OMRON representative.
- ***3.** Do not pass the 3 A, 250 VAC load through more than 2 circuits.
- ***4.** These figures are minimum requirements for safe operation.
- *5. This value will vary with the switching frequency, environment, and reliability level. Confirm that correct operation is possible with the actual load beforehand.

^{2.} The Switch contacts can be used with either standard loads or microloads. Once the contacts have been used to switch a load, however, they cannot be used to switch smaller loads. The contact surfaces will become rough once they have been used and contact reliability for smaller loads may be reduced.


Structure and Nomenclature

Structure

D4NS-□A□, D4NS-□B□, D4NS-□E□, D4NS-□AF-SJ, D4NS-□BF-SJ



D4NS-CC, D4NS-DC, D4NS-FC, D4NS-CF-SJ, D4NS-CF-SJ



Note: The 2-conduit types have the same terminal arrangement.

Model and Contact Configuration

Diagrams Show State with Key Inserted.


Model	Contact	Contact form	Operating pattern	Remarks
D4NS-□A□ D4NS-□AF-SJ	1NC/1NO		11-12 33-34 Stroke ON	Only NC contacts 11-12 have a certified direct opening mechanism.
		33 - 34	Key insertion completion completion position position	The terminals 11-12 and 33-34 can be used as unlike poles.
D4NS-⊡B⊡ D4NS-⊡BF-SJ	2NC		11-12 31-32 Operation Key insertion completion Stroke Operation Key insertion Completion	NC contacts 11-12 and 31-32 have a certified direct opening mechanism. The terminals 11-12 and 31-32
			position	can be used as unlike poles.
D4NS-□C□	2NC/1NO		11-12 21-22 33-34	NC contacts 11-12 and 21-22 have a certified direct opening mechanism.
D4NS-⊡CF-SJ		21 22 22 33 34	Stroke Stroke Extraction Operation Extraction Key insertion completion completion position	The terminals 11-12, 21-22, and 33-34 can be used as unlike poles.
D4NS-□D□			11-12 ON 21-22 ON 31-32 ON	NC contacts 11-12, 21-22, and 31-32 have a certified direct opening mechanism.
D4NS-⊡DF-SJ	3NC	$21 \xrightarrow{1} \bigoplus_{1 \to 0} 22$ $31 \xrightarrow{1} \bigoplus_{2 \to 0} 32$	Stroke	The terminals 11-12, 21-22, and 31-32 can be used as unlike poles.
D4NS-□E□	1NC/1NO MBB *		11-12 33-34 □ ON Stroke →	Only NC contacts 11-12 have a certified direct opening mechanism.
		33 - 34	Operation Extraction Key insertion completion completion position	The terminals 11-12 and 33-34 can be used as unlike poles.
D4NS-□F□	2NC/1NO MBB *	$\begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ 11 \end{array} \end{array} \end{array} \begin{array}{c} \begin{array}{c} \end{array} \\ 12 \end{array} \\ 21 \end{array} \end{array} \begin{array}{c} \begin{array}{c} \end{array} \end{array} \begin{array}{c} \begin{array}{c} \end{array} \\ 12 \end{array} \\ \end{array} \end{array} \begin{array}{c} \end{array} \\ 22 \end{array}$	11-12 21-22 33-34 ON	NC contacts 11-12 and 21-22 have a certified direct opening mechanism.
		33 - 34	Operation Extraction Key insertion completion completion position	The terminals 11-12, 21-22 and 33-34 can be used as unlike poles.

* MBB (Make Before Break) contacts have an overlapping structure, so that before the normally closed contact (NC) opens, the normally open contact (NO) closes.

Dimensions


Dimensions and Operating Characteristics

1-Conduit Types




Model Operating characteristics	D4NS-1□F D4NS-2□F D4NS-4□F	D4NS-2□F-SJ D4NS-4□F-SJ
Key insertion force Key extraction force	15 N max. 30 N max.	15N max. (50N max.)
Pretravel (PT)	6±3 mm	6±3 mm
Total travel (TT)	(28 mm)	(28 mm)

2-Conduit Types




1-Conduit Connector Types



Operating Model characteristics	D4NS-9□F
Key insertion force Key extraction force	15 N max. 30 N max.
Pretravel (PT)	6±3 mm
Total travel (TT)	(28 mm)

Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

2. There are fluctuations in the contact ON/OFF timing for Switches with multiple poles (2NC, 2NC/1NO, or 3NC). Confirm performance before application.



Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Slide Keys D4NS-SK01

40 (Stroke)

ŧ

Auxiliary Mounting Bracket and Main Body Receptacle Bracket -40 +20.5+ jpb 12 Auxiliary mounting bracket 36.5 55 19.5 + 5.5 dia. 65 58 0 0 Ц 0 0 -39.5-7.5 -17 2 3 -3 13 Receptacle bracket 45.5 Two, M4 × 6 Four, M5 tap screws P=0.8 Stroke 40 1 (Φ) þ ÷ 40 70 45.5 60 65 ۲ - 30 --45 **Switch Mounting Pattern 2 Switch Mounting Pattern 1** 42.5 Assembled with D4NS Auxiliary mounting bracket (included with product) 55 max 3-**⊷**39.5 85 - 42 65 55 Γ 39.5 -28--40 20 ÷ 74 max. l ż 45.5 Receptacle bracket (included with product) ଚି®୍ଡିବି 26 Ħ N З Assembled with D4NS Two, M4 × 6 58 28 ļ ٢ Ē 40 ⋬ 42 (included with product) Stroke 70 60 • 65 ۲ ۲ Ē

-30→

45

60

۲

51

19.5


-30-

45


۲


D4NS-SK30

Open Door




Closed Door






With Operation Key Inserted (Relationship between Insertion Radius, Operation Key and Key Hole)



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

* Insertion radii apply when the rotational center of the Operation Key is in line with a line extending from the front or top Head surface.



Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

* Insertion radii apply when the rotational center of the Operation Key is in line with a line extending from the front or top Head surface.

Safety Precautions

Be sure to read the precautions for All Safety Door Switches in the website at:http://www.ia.omron.com/.

Indication and Meaning for Safe Use

	Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, or undesirable effect on product performance.

<Safety-door Switch D4NS>




Electric shock may occasionally occur. Do not use metal cable glands or metal conduits.

Precautions for Safe Use

- · Do not use the Switch submersed in oil or water or in locations continuously subject to splashes of oil or water. Doing so may result in oil or water entering the Switch. (The IP67 degree of protection of the Switch specifies the amount of water penetration after the Switch is submerged in water for a certain period of time.)
- · Always attach the cover after completing wiring and before using the Switch. Also, do not turn ON the Switch with the cover open. Doing so may result in electric shock.
- Do not switch circuits for two or more standard loads (250 VAC, 3 A). Doing so may adversely affect insulation performance.

Stopper Installation

Do not use a Switch as a stopper. Be sure to install a stopper as shown in the following illustration to ensure that the base of the Operation Key does not strike the Head, and adjust the stopper to be within the setting zone (0.5 to 3 mm) of the base of the Operation Key. Do not subject the Switch to a shock that exceeds the Switch's shock resistance of 1,000 m/s².



Precautions for Correct Use

The Switch contacts can be used with either standard loads or microloads. Once the contacts have been used to switch a load. however, they cannot be used to switch smaller loads. The contact surfaces will become rough once they have been used and contact reliability for smaller loads may be reduced.

Mounting Method

Appropriate Tightening Torque


· Loose screws may result in malfunction. Be sure to tighten each screw of the Switch properly

be sure to agricell each serew of the ownen property.	
Terminal screw	0.6 to 0.8 N⋅m
Cover mounting screw	0.5 to 0.7 N·m
Head mounting screw	0.5 to 0.6 N⋅m
Operation Key mounting screw	2.4 to 2.8 N⋅m
Body mounting screw	0.5 to 0.7 N·m
Cable gland	1.8 to 2.2 N⋅m
Cap screw	1.3 to 1.7 N⋅m


• When loosening a screw with an electrical screwdriver or similar tool while pressing down on the screw head, do not continue turning the screw past the point where the threads disengage. Doing so may strip the end of the threads.

Mounting Holes

- Use M4 screws and washers to mount the Switch and Operation Key, and tighten the screws to a suitable torque. To ensure safety, use screws that cannot be easily removed or another means to prevent the Switch and Operation Key from easily being removed.
- As shown below, two studs with a maximum height of 4.8 mm and a diameter of 4^{-0.05}_{-0.15} mm can be provided, the studs inserted into the holes on the bottom of the Switch, and the Switch secured at four locations to increase the mounting strength.




Horizontal/Vertical Adjustable



42+0

Two, M4



4.0.15 dia

· Observe the specified insertion radius for the Operation Key and insert it in a direction perpendicular to the key hole.

Operation Key


- Use only the designated Operation Key. The Head has been designed so that operation is not possible with a screwdriver or other tools. Using anything other than the designated Operation Key may damage the Switch or affect machine safety.
- Do not operate the Switch with anything other than the special OMRON Operation Key, otherwise the Switch may break or the safety of the system may not be maintained.
- Do not impose excessive force on the Operation Key while the Key is inserted into the Switch or drop the Switch with the Operation Key inserted. Doing either of these may deform the Key or break the Switch.

Head Direction

- The rotation of the Switch head may be adjusted to any of the four directions by loosening the head mounting screws at the four corners of the head. Make sure that no foreign materials enter through the head.
- Do not insert or remove the Operation Key with the Switch head removed. Doing so may make it impossible to insert the Operation Key.

Securing the Door

When the door is closed (with the Operation Key inserted), the Operation Key may exceed the set zone because of, for example, the door's own weight, machine vibration, or the door cushion rubber. Secure the door with a stopper so that the Operation Key remains within the set zone.




Wiring


Wiring

• When connecting with insulation tubes and M3.5 crimp terminals, connect the terminals as shown in the following figure and wire without overriding to the case and the cover. Adequate conductor size is AWG 20 to AWG18 (0.5 to 0.75 mm²).

Prepare lead wires using the lengths given in the following diagrams. If lead wires are too long, they will press against the cover causing the cover to not close properly.




2-Conduit Types with 3 Poles



- Do not push the crimp terminal and the likes into the opening between the parts to prevent the case from being broken and deformed.
- Use terminals having the thickness of 0.5 mm or less to avoid the contact between the terminal and the Switch case inside.


<Reference>

The crimp terminals listed below have a thickness of 0.5 mm or less.



Pin arrangement of connector type





- Suitable socket is XS2F-D421 series (OMRON).
- Refer to the Connector Catalog for corresponding Socket pin numbers and lead wire colors.

Socket Tightening (Models with Connectors)

- Turn the tightening screws on the Socket by hand and tighten them until the gap between the Socket and Plug essentially disappears.
- Make sure that the Socket's connector is tightened securely, otherwise the rated degree of protection (IP67) of the D4NS may not be maintained, or the Socket connector may be loosened by vibration.

Conduit Outlet


- Use a cable conforming to the diameter of the cable gland to be used.
- When wiring, place the enclosed cap screw on unused conduit outlets (for 2-Conduit Types) and tighten them to the suitable tightening torque.

Cable Gland

- Use a commercially available cable gland.
- Use the cable gland with thread section of 9 mm long or less.

<Slide Keys D4NS-SK01/SK30>

Incorrect operation may cause injury. Also, the product is designed to be mounted so that it slides horizontally. Do not mount the product in a vertically sliding configuration. (excluding the D4NS-SK01)



- Do not drop the Switch. Doing so may prevent the Switch from functioning to full capacity.
- Mount the Switch securely to prevent it from falling. Otherwise, injuries may occur.
- Do not attempt to disassemble or modify the Switch. Doing so may cause the Switch to malfunction.
- Make sure that the gap between the short bolt and guide is (±3 mm. Otherwise, excessive wear or damage may cause malfunction.
- To ensure safety, do not operate the Switch with anything other than a Slide Key.
- Be careful to avoid pinching your hand when operating the Switch.
- Be sure to mount the Switch protective cover. Otherwise, your hand may be injured by being pinched between the shot bolt and Switch when closing the door with your hand on the Switch.
- When opening the door, be sure to lower the disable-prevention cover into position, attach a padlock, or take other steps to prevent other people from operating the Switch.
- The durability of the Switch is greatly influenced by the switching conditions. Always test the Switch under actual working conditions before application and use it in a switching circuit for which there are no problems with performance.
- The user must not maintain or repair equipment incorporating the Switch. Contact the manufacturer of the equipment for any maintenance or repairs required.
- Do not shut the door while the shot bolt is extended. The Switch may be damaged, preventing proper operation.
- Do not apply excessive force in the direction of the slide. This may damage the product and cause it to malfunction.

Precautions for Correct Use

 Insert the slide handle until the red operation indicator is completely displayed in the operation display window.




Operation display window

• Loose screws may result in malfunction. Use washers and tighten the screws to the specified torques. Also, when mounting the Switch to a door for disable-prevention purposes, purchase and use tamper-resistant screws.

Tightening Torque

Slide Key mounting screw (M6)	6.0 to 7.0 N⋅m
Switch mounting screw (included with product)	0.5 to 0.7 N·m
Switch protective cover mounting screw (included with product)	1.2 to 1.4 N·m
Lever mounting screw (included with product)	1.2 to 1.4 N⋅m

• Use the D4NS-SK30 only with the D4NS Safety-door Switch head in the direction shown below.




Technical Specifications


	D4NS-SK30
Ambient operating temperature	–10 to 55°C (with no icing)
Ambient operating humidity	95% max.
Mechanical durability	20,000 operations min.
Weight	Approx. 2.8 kg (not including D4NS Safety-door Switch)

- Do not store the Switch where corrosive gases (e.g., H₂S, SO₂, NH₃, HNO₃, or CL₂) or dust are present, or in locations subject to high temperature or humidity.
- · Perform maintenance inspections periodically.
- This product is for use only with OMRON Safety-door Switches. Do not use it with door switches made by other manufacturers.


Mounting Holes (Unit: mm) D4NS-SK30



Assembly Switch part D4NS-SK30



Handle part D4NS-SK30



- Use the supplied special screws to mount the operation key and D4NS Guard Lock Safety-door Switch.
- To tighten the screws, use the tip of a flat-head screwdriver on the screw heads as shown in the following figure.



O Note: The special screws are designed so that they cannot be turned counter-clockwise using a flat-head screwdriver.

• The special screws cannot be removed once they are tightened.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company