

Enables easier and standardized previously not possible



Easy design

Standardized design

Exceptional sensing range



The PREMIUM Model, which has a longer detection range compared to previous models, allows for more spacious designs with less risk of contact. It also enables you to standardize your designs by letting you adopt a single one-size model instead of multiple models of different sizes.

Quadruple distance model
9 mm [M12]

*1. Quadruple distance models of M12 sized

P.4-7

Triple distance model
6 mm [M12]

BASIC Model

In addition to our HIGH SPEC Models, we also offer mid/short-distance BASIC Models, to meet various facility design requirement specifications.

Double distance model
4 mm [M12]

Single distance model
2 mm [M12]

designs



New standards for usability

Early error detection

location, all new E2E Sensors can be monitored with IO-Link

P.8

Quick recovery

second replaceable with e-jig (adaptor)

P.10

with high visibility LED indicator

P.10

Less unexpected facility stoppages

Strong resistance to cutting oil

-year oil resistance *2

P.12


*2. Pre-wired models and pre-wired connector models.

Easy design

Equipped with exceptional sensing range

to enable collision-free sensor installation

Enables designs with more distance between the sensor and the sensing object, thereby reducing unexpected facility stoppages due to collision and false detection, which occurred with previous proximity sensors.




Allows for more spacious design with less risk of contact

With previous models, to avoid false detections, you were forced to adopt sensor installation designs that risked contact. The E2E NEXT PREMIUM Proximity Sensor can detect accurately from a greater distance, which means you can adopt designs with more space and less risk of contact.




■Approximately double the sensing distance of previous models

Sensing distance comparisons (Quadruple distance models)



Less false detection even when a stationary gets away from the sensor due to equipment vibration



PROX3 hybrid circuitry with Thermal Distance Control 2 eliminates ambient temperature influence to enable extended sensing ranges. Proximity sensors with longer sensing distance require increased sensitivity. However, with the increased sensitivity, temperature changes will have bigger influence in sensing distance, and differences between

individual sensors will be bigger. E2E NEXT Proximity Sensors (3-wire models) solve these issues by newly implementing Thermal Distance Control 2, a technology to enable extended sensing ranges. It enables in-line measurements of each sensor's temperature characteristics, using multiple temperature points, in loT-enabled production processes. The optimal correction values are then calculated based on our unique

algorithm. The values are written into the analog digital hybrid IC (PROX3) for shipping to minimize differences between sensors and the influence of temperature changes that may occur in the customer's environments.



PATENTED Thermal Distance Control 2 technology reduces the extent of error

Sensing distance fluctuation due to ambient temperature Before correction Error using measurement data from -25 °C +25 °C +70 °C Ambient temperature

^{*2. &}quot;Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of October 2025)

Standardized design


Exceptional sensing range

allows you to standardize your design with a single one-size model

Ensures equivalent sensing distance while being one size smaller than previous models. Equipment and facilities formerly designed to use sensors of multiple sizes can now be designed to use sensors that are all the same size, allowing you to standardize your designs.

Case where either M12 or M18 is used depending on sensing distance

Two different types of hole designs were required for the sensing distance of 4 mm and 8 mm.



Four types of M12 size sensors are available to meet the need for variable sensing distances for different installation sites.

Quadruple distance model 9 mm








Easy to install, even where space is limited

E2E NEXT PREMIUM Model Proximity Sensors ensure equivalent sensing distance while being one size smaller than previous models, allowing you to install them in spaces where conventional sensors were too big to fit.



Previous models

Proximity sensors could not be installed due to limited space.





They can be installed due to limited space.

One size smaller to allow you to install proximity sensors where space is limited.




Note: When installing proximity sensors, make sure to factor the influence of surrounding metal into your designs. (Refer to Influence of Surrounding Metal upon Design on page 51, page 70, page 84 and page 105 for details.)

■One size smaller than previous models

Size comparisons between models with equivalent sensing distance ("E2E NEXT" refers to quadruple distance models)






New standards for usability

Early error detection


Enables facility designs that allow for early discovery of the site and



Detects sensor failures through two output types, NO and NC


Enables failure discovery by wiring two outputs, NO and NC.

When NO cable is disconnected



Enables real-time identification of the site and substance of sensor failure from a single location


By using the IO-Link Master to connect proximity sensors to your controller, you can use your monitor (HMI) for early discovery of the site and substance of proximity sensor failures.



Enables predictive maintenance through condition monitoring

Connecting sensors with controllers using IO-Link Master enables to send information necessary for stable operation to host devices. This enables condition monitoring and failure detection of sensors, which in turn contribute to predictive maintenance of equipment and facilities. You can also increase the productivity of your facility by accumulating information in databases and feeding analysis results back to equipment on the site.





Applies only to the description of the high-brightness LED indicator

Enables facility designs that allow for quick recovery in case of failure



All around visible high-brightness **LED** indicator

Adopts high-brightness LED that is more luminous and visible than those in previous models. The indicator is visible from all angles, reducing the time required for operation checks after sensor replacement.



Visible even in areas deep inside the equipment, allowing for quicker replacement


PATENTED

and "Patented" means that we obtained a patent in Japan.

(As of September 2022)

Replacements in as little as 10 seconds*1 using e-jig

Using e-jig eliminates the need for adjustment so that anyone can install in the same position.



3. Loosen the nut and adjust the distance.

E2E NEXT


Replacement time reduced significantly to approx. 10 sec.*1

Eliminating the need for adjustment allows for installation in the same position by any worker.



Easily upgrade existing facilities to enable "10-second" proximity sensor replacements"

The HIGH SPEC Model's sensing distance is approximately twice that of previous models. For example, the sensing distance of the quadruple distance model of M12 sized is 9 mm, which is about the same as conventional M18 models. Using these sensors together with the e-jig allows you to easily upgrade your existing facilities so that you can replace their sensors in just 10 seconds.*1



Excellent environmental resistance enables robust facility design

Reduces sudden facility stoppages by reducing the number of failures, even in severe environments. Unexpected component failures: are caused by cutting oil. Approx. 3 Other causes Voltage or **Cutting** o noise Dust, dirt, or spatter ■ Environmental Causes of Component Failures (Based on June 2016 OMRON investigation.)

Cables with enhanced oil resistance shut out cutting oil for 2 years*1

Our new PVC compound protects against damage caused by swelling, deterioration or cracking, preventing oil from seeping into and destroying internal circuits. Designed to resist oil ingress for up to two years.

■Two years*1 of stable operation verified by OMRON's unique evaluation technology



■ Two years*1 of stable operation verified for pre-wired connector models as well, using similar oil resistance tests

• Delivers 2-year oil resistance*1 by adopting technologies unique to OMRON and PVC cables with enhanced oil resistance. PATENTED *2

• Smartclick connector cables block the ingress of cutting oil, and with the same torque, no matter who connects them.



(Illustration)

For machining processes where the amount of splashing cutting oil is large, oil-resistant Proximity Sensors E2ER/E2ERZ



- *1. Applicable oil types: specified in JIS K 2241:2000
 - "2-year oil resistance" refers to median values (=Typical values) of the product designs and the oil-resistance performance evaluation results. Products to be shipped will have around 2 years of oil resistance; actual oil resistance will vary depending on the product.
 - The pre-wired connector model has a verified oil resistance of 2 years when mated with XS5 NEXT series round oil-resistant connectors. This value has not been verified for connector models(M1/M3/M5).
- *2. "Patent Pending" means that we applied for a patent in Japan, and "Patented" means that we obtained a patent in Japan. (As of September 2022)

IP69K compliant for water resistance and wash resistance

IEC 60529 compliant. Ensures water resistance during hot pressure washing, where equipment is washed intensively with high-pressure water or steam. (8,000 to 10,000 kPa pressure, 80°C hot water, 30 seconds for each angle)

E2E NEXT Series Functions and Specifications

						DC 3	-wire			
				Shie	lded			Unsh	elded	
			W. Comments		A Park		Marie		A THE PARTY OF THE	
Main functi	ons and spe	Model	Quadruple distance	Triple distance	Double distance	Single distance	Quadruple distance	Triple distance	Double distance	Single distance
Wallitaliotion	Sensing distance	M8	4mm	3mm	2mm	1.5mm	8mm	6mm	4mm	2mm
		M12	9mm	6mm	4mm	2mm	16mm	10mm	8mm	5mm
		M18	14mm	12mm	8mm	5mm	30mm	20mm	16mm	10mm
Detection performance		M30	23mm	22mm	15mm	10mm	50mm	40mm	30mm	18mm
performance	Installation	Flush with surface	_	_	• *2	•	_	_	_	_
		Flush with surface using nut	_	• *1	•	•	_	_	_	_
	360° visib	le indicator	•	•	•	•	•	•	•	•
Usability	e	-jig	• *3	• *3	_	_	_	_	_	_
Industrial		evel and temp. n with IO-Link	•	•	•	•	•	•	•	•
loT enabled	2-outp	2-output model		•	•	•	_	•	•	•
Environmental resistance	Oil resistance	2 years	•	•	•	•	•	•	•	•
	Datasheet		P.18 ~	P.21 ~	P.25 ~	P.29 ~	P.20 ~	P.23 ~	P.27 ~	P.31 ~

			DC 2-wire			
	Shie	lded			Unshielded	
W. C.		A Park		William .		
Triple distance	Double distance	Standard	Single distance	Triple distance	Double distance	Standard
3mm	_	2mm	1.5mm	6mm	_	4mm
7mm	4mm	3mm	2.5mm	10mm	_	8mm
11mm	8mm	7mm	5mm	20mm	16mm	14mm
20mm	15mm	10mm	_	40mm	30mm	20mm
_	_	•	•	_	_	_
• *1	•	•	•	_	-	_
•	•	•	•	•	•	•
● *3	_	_	_	_	_	_
_	_	_	_	_	_	_
_	_	_	_	_	_	_
•	•	•	•	•	•	•
P.64 ~	P.75 ~	P.74 ~	P.75 ~	P.64 ~	P.75 ~	P.74 ~

^{*1.} The nuts are longer than other models. Please refer to the datasheet for details.

^{*2.} Applicable to some models. Please refer to datasheet for details. *3. Pre-wired models only.

E2EQ NEXT Series Functions and Specifications

				DC 3-wire		DC 2	2-wire	
			I	Fluororesin hea	d	Fluorore	esin head	
				Name of the last o		W. Comments		
	Model			BASIC	Model	PREMIUM Model	BASIC Model	
Main functions and specifications			Triple distance	Double distance	Single distance	Triple distance	Double distance	
		M8	3mm	2mm	1.5mm	3mm	_	
	Sensing	M12	6mm	4mm	2mm	7mm	4mm	
	distance	M18	12mm	8mm	5mm	11mm	8mm	
Detection		M30	22mm	15mm	10mm	20mm	15mm	
performance	Installation	Flush with surface	_	_	•	_	_	
		Flush with surface using nut	•	•	•	•	•	
Environmental resistance	Spatter resistance	Standard fluororesin coating	•	•	•	•	•	
Industrial IoT Detection level and temp. visualization with IO-Link			•	•	•	_	_	
	360° visible indi		(Orange)	(Orange)	(Orange)	(Green)	(Green)	
Usability	Laser prii nur	nted model mber	•	•	•	•	•	
	2-output (N	O+NC) model	• *1	• *1	• *1	_	_	
	Datasheet			P.89 ~		P.8	P.89 ~	

Proximity Sensor E2E NEXT Series

DC 3-Wire

Enables easier and standardized designs previously not possible

- Nearly double the sensing distance*1 of previous
- With high-brightness LED, the indicator is visible anywhere from 360°.
- Only 10 Seconds*2 to Replace a Proximity Sensor with the "e-jig" (Mounting Sleeve).
- Cables with enhanced oil resistance enabled 2-year oil resistance*3.
- IP69K compliant for water resistance and wash resistance
- Comes in a wide variation to make sensor selection easy
- UL certification (UL60947-5-2)*4 and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. Comparison with our previous model E2E.
- *2. Time required to adjust the distance when installing a Sensor. Based on OMRON investigation.
- *3. Refer to Ratings and Specifications for details. However, E2E Connector Models is excluded.
- *4. M8 (4-pin) Connector Models are not UL certified.



Be sure to read Safety Precautions on page 50.

Model Number Legend

E2E - X (1) (2) (3) (4) (5) (6) (7) (8) - (9) - (10) (11)

No.	Туре	Code	Meaning
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)
(2)	Shielding	Blank	Shielded
(2)	Sillelaing	М	Unshielded
(3)	Output configuration	В	PNP open collector
(3)	Odiput configuration	С	NPN open collector
		1	Normally open (NO)
(4)	Operation mode	2	Normally closed (NC)
		3	Normally open, Normally closed (NO+NC)
(5)	Oscillation frequency type	Blank	Standard frequency
(3)	Oscillation frequency type	5	Different frequency
		Blank	Non IO-Link compliant
(6)	IO-Link baud rate	D	COM2 (38.4 kbps)
		Т	COM3 (230.4 kbps)
(7)	Body size	Blank	Standard
(1)	Body Size	L	Long Body
		8	M8
(8)	Size	12	M12
(6)	Size	18	M18
		30	M30
		Blank	Pre-wired Models
		M1	M12 Connector Models
		M3	M8 (4-pin) Connector Models
(9)	Connection method	M5	M8 (3-pin) Connector Models
		M1TJ	M12 Pre-wired Smartclick Connector Models
		M1TJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable
	Cable specifications	Blank	Standard PVC cable
(10)	(Only shown in the model number of Pre-wired Models.)	R	Robot (bending-resistant) cable
(11)	Cable length	Number M	Cable length

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.







For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

PREMIUM Model

E2E NEXT Series (Quadruple distance model)

DC 3-wire [Refer to *Dimensions* on page 53.]

Shielded *1

Size	Connection	Ded.	Operation		Model	
(Sensing	Connection method	Body size	Operation mode	PN	NPN	
distance)		0.20		IO-Link (COM3)	IO-Link (COM2) *5	*5
		38 mm	NO	E2E-X4B1T8 2M	E2E-X4B1D8 2M	E2E-X4C18 2M
	Pre-wired (2 m) *2	*3	NC	-	E2E-X4B28 2M	E2E-X4C28 2M
	Fie-wired (2 iii) 2	40	NO	E2E-X4B1TL8 2M	E2E-X4B1DL8 2M	E2E-X4C1L8 2M
		48 mm	NC	-	E2E-X4B2L8 2M	E2E-X4C2L8 2M
		38 mm	NO	E2E-X4B1T8-M1TJ 0.3M	E2E-X4B1D8-M1TJ 0.3M	E2E-X4C18-M1TJ 0.3M
	M12 Pre-wired	*4	NC	-	E2E-X4B28-M1TJ 0.3M	E2E-X4C28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X4B1TL8-M1TJ 0.3M	E2E-X4B1DL8-M1TJ 0.3M	E2E-X4C1L8-M1TJ 0.3M
	,	48 mm	NC	-	E2E-X4B2L8-M1TJ 0.3M	E2E-X4C2L8-M1TJ 0.3M
		40	NO	E2E-X4B1T8-M1	E2E-X4B1D8-M1	E2E-X4C18-M1
M8		43 mm	NC	-	E2E-X4B28-M1	E2E-X4C28-M1
(4 mm)	M12 Connector		NO	E2E-X4B1TL8-M1	E2E-X4B1DL8-M1	E2E-X4C1L8-M1
		53 mm	NC	-	E2E-X4B2L8-M1	E2E-X4C2L8-M1
	M8 Connector (4-pin)	00	NO	E2E-X4B1T8-M3	E2E-X4B1D8-M3	E2E-X4C18-M3
		39 mm	NC	-	E2E-X4B28-M3	E2E-X4C28-M3
			NO	E2E-X4B1TL8-M3	E2E-X4B1DL8-M3	E2E-X4C1L8-M3
		49 mm	NC	-	E2E-X4B2L8-M3	E2E-X4C2L8-M3
			NO	E2E-X4B1T8-M5	E2E-X4B1D8-M5	E2E-X4C18-M5
	M8 Connector (3-pin)	39 mm	NC	-	E2E-X4B28-M5	E2E-X4C28-M5
			NO	E2E-X4B1TL8-M5	E2E-X4B1DL8-M5	E2E-X4C1L8-M5
		49 mm	NC	-	E2E-X4B2L8-M5	E2E-X4C2L8-M5
		47 mm	NO	E2E-X9B1T12 2M	E2E-X9B1D12 2M	E2E-X9C112 2M
	Pre-wired (2 m) *2	*3	NC	-	E2E-X9B212 2M	E2E-X9C212 2M
		69 mm	NO	E2E-X9B1TL12 2M	E2E-X9B1DL12 2M	E2E-X9C1L12 2M
			NC	-	E2E-X9B2L12 2M	E2E-X9C2L12 2M
		47 mm	NO	E2E-X9B1T12-M1TJ 0.3M	E2E-X9B1D12-M1TJ 0.3M	E2E-X9C112-M1TJ 0.3M
M12	M12 Pre-wired	*4	NC	-	E2E-X9B212-M1TJ 0.3M	E2E-X9C212-M1TJ 0.3M
(9 mm)	Smartclick		NO	E2E-X9B1TL12-M1TJ 0.3M	E2E-X9B1DL12-M1TJ 0.3M	E2E-X9C1L12-M1TJ 0.3M
(- /	Connector (0.3 m)	69 mm	NC	-	E2E-X9B2L12-M1TJ 0.3M	E2E-X9C2L12-M1TJ 0.3M
			NO	E2E-X9B1T12-M1	E2E-X9B1D12-M1	E2E-X9C112-M1
		48 mm	NC	-	E2E-X9B212-M1	E2E-X9C212-M1
	M12 Connector		NO	E2E-X9B1TL12-M1	E2E-X9B1DL12-M1	E2E-X9C1L12-M1
		70 mm	NC	-	E2E-X9B2L12-M1	E2E-X9C2L12-M1
		EE	NO	E2E-X14B1T18 2M	E2E-X14B1D18 2M	E2E-X14C118 2M
		55 mm *3	NC NC	-	E2E-X14B1D18 2M	E2E-X14C218 2M
	Pre-wired (2 m) *2	-	NO	E2E-X14B1TL18 2M	E2E-X14B1DL18 2M	E2E-X14C1L18 2M
		77 mm	NC	X 14B 11L 10 ZW	E2E-X14B2L18 2M	E2E-X14C1L18 2M
			NO	E2E-X14B1T18-M1TJ 0.3M	E2E-X14B1D18-M1TJ 0.3M	E2E-X14C2118-M1TJ 0.3M
1440	M12 Pre-wired	55 mm *4		E2E-X14B1110-W1113 U.SW		
M18 14 mm)	Smartclick	7	NC NC	- EDE VAADATI 40 MAT I 0 000	E2E-X14B218-M1TJ 0.3M	E2E-X14C218-M1TJ 0.3M
14 111111)	Connector (0.3 m)	77 mm	NO	E2E-X14B1TL18-M1TJ 0.3M	E2E-X14B1DL18-M1TJ 0.3M	E2E-X14C1L18-M1TJ 0.3N
			NC	-	E2E-X14B2L18-M1TJ 0.3M	E2E-X14C2L18-M1TJ 0.3N
		53 mm	NO	E2E-X14B1T18-M1	E2E-X14B1D18-M1	E2E-X14C118-M1
	M12 Connector		NC	-	E2E-X14B218-M1	E2E-X14C218-M1
		75 mm	NO	E2E-X14B1TL18-M1	E2E-X14B1DL18-M1	E2E-X14C1L18-M1
			NC	-	E2E-X14B2L18-M1	E2E-X14C2L18-M1

Size		Body size	Operation mode	Model				
(Sensing	Connection method			PN	IP	NPN		
distance)				IO-Link (COM3)	IO-Link (COM2) *5	*5		
		60 mm	NO	E2E-X23B1T30 2M	E2E-X23B1D30 2M	E2E-X23C130 2M		
	Pre-wired (2 m) *2	*4	NC	-	E2E-X23B230 2M	E2E-X23C230 2M		
	Pre-wired (2 iii) 2	82 mm	NO	E2E-X23B1TL30 2M	E2E-X23B1DL30 2M	E2E-X23C1L30 2M		
			NC	-	E2E-X23B2L30 2M	E2E-X23C2L30 2M		
		60 mm *4	NO	E2E-X23B1T30-M1TJ 0.3M	E2E-X23B1D30-M1TJ 0.3M	E2E-X23C130-M1TJ 0.3M		
M30	M12 Pre-wired Smartclick		NC	-	E2E-X23B230-M1TJ 0.3M	E2E-X23C230-M1TJ 0.3M		
(23 mm)	Connector (0.3 m)	82 mm	NO	E2E-X23B1TL30-M1TJ 0.3M	E2E-X23B1DL30-M1TJ 0.3M	E2E-X23C1L30-M1TJ 0.3M		
			NC	-	E2E-X23B2L30-M1TJ 0.3M	E2E-X23C2L30-M1TJ 0.3M		
		58 mm	NO	E2E-X23B1T30-M1	E2E-X23B1D30-M1	E2E-X23C130-M1		
	M12 Connector	30 11111	NC	-	E2E-X23B230-M1	E2E-X23C230-M1		
	M12 Connector	00	NO	E2E-X23B1TL30-M1	E2E-X23B1DL30-M1	E2E-X23C1L30-M1		
		80 mm		-	E2E-X23B2L30-M1	E2E-X23C2L30-M1		

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 51.

^{*2.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X9B1D12 5M)

^{*3.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X9B1D12-R 2M/ E2E-X9B1D12-R 5M)

^{*4.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X9B1D12-M1TJR 0.3M)

^{*5.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

E2E NEXT Series (Quadruple distance model)

DC 3-wire [Refer to Dimensions on page 54.]

Unshielded

Size		Body	Operation	Model				
(Sensing	Connection method	Body size	Operation mode	PN	P	NPN		
distance)		0.20		IO-Link (COM3)	IO-Link (COM2) *4	*4		
		38 mm	NO	E2E-X8MB1T8 2M	E2E-X8MB1D8 2M	E2E-X8MC18 2M		
	Pre-wired (2 m) *1	*2	NC	-	E2E-X8MB28 2M	E2E-X8MC28 2M		
	Pie-wiied (2 iii) T	10 mm	NO	E2E-X8MB1TL8 2M	E2E-X8MB1DL8 2M	E2E-X8MC1L8 2M		
		48 mm	NC	-	E2E-X8MB2L8 2M	E2E-X8MC2L8 2M		
		38 mm	NO	E2E-X8MB1T8-M1TJ 0.3M	E2E-X8MB1D8-M1TJ 0.3M	E2E-X8MC18-M1TJ 0.3M		
	M12 Pre-wired Smartclick	*3	NC	-	E2E-X8MB28-M1TJ 0.3M	E2E-X8MC28-M1TJ 0.3M		
	Connector (0.3 m)	48 mm	NO	E2E-X8MB1TL8-M1TJ 0.3M	E2E-X8MB1DL8-M1TJ 0.3M	E2E-X8MC1L8-M1TJ 0.3M		
		40 111111	NC	-	E2E-X8MB2L8-M1TJ 0.3M	E2E-X8MC2L8-M1TJ 0.3M		
	M12 Connector	12 mm	NO	E2E-X8MB1T8-M1	E2E-X8MB1D8-M1	E2E-X8MC18-M1		
M8		43 mm	NC	-	E2E-X8MB28-M1	E2E-X8MC28-M1		
(8 mm)		53 mm	NO	E2E-X8MB1TL8-M1	E2E-X8MB1DL8-M1	E2E-X8MC1L8-M1		
		33 11111	NC	-	E2E-X8MB2L8-M1	E2E-X8MC2L8-M1		
		20	NO	E2E-X8MB1T8-M3	E2E-X8MB1D8-M3	E2E-X8MC18-M3		
	M8 Connector	39 mm	NC	-	E2E-X8MB28-M3	E2E-X8MC28-M3		
	(4-pin)	40	NO	E2E-X8MB1TL8-M3	E2E-X8MB1DL8-M3	E2E-X8MC1L8-M3		
		49 mm	NC	-	E2E-X8MB2L8-M3	E2E-X8MC2L8-M3		
		39 mm	NO	E2E-X8MB1T8-M5	E2E-X8MB1D8-M5	E2E-X8MC18-M5		
	M8 Connector	39 111111	NC	-	E2E-X8MB28-M5	E2E-X8MC28-M5		
	(3-pin)	40	NO	E2E-X8MB1TL8-M5	E2E-X8MB1DL8-M5	E2E-X8MC1L8-M5		
		49 mm	NC	-	E2E-X8MB2L8-M5	E2E-X8MC2L8-M5		
		47 mm	NO	E2E-X16MB1T12 2M	E2E-X16MB1D12 2M	E2E-X16MC112 2M		
	Dro winod (2 m) *1	*2	NC	-	E2E-X16MB212 2M	E2E-X16MC212 2M		
	Pre-wired (2 m) *1	69 mm	NO	E2E-X16MB1TL12 2M	E2E-X16MB1DL12 2M	E2E-X16MC1L12 2M		
			NC	-	E2E-X16MB2L12 2M	E2E-X16MC2L12 2M		
		47 mm	NO	E2E-X16MB1T12-M1TJ 0.3M	E2E-X16MB1D12-M1TJ 0.3M	E2E-X16MC112-M1TJ 0.3M		
M12	M12 Pre-wired Smartclick	*3	NC	-	E2E-X16MB212-M1TJ 0.3M	E2E-X16MC212-M1TJ 0.3M		
(16 mm)	Connector (0.3 m)	69 mm	NO	E2E-X16MB1TL12-M1TJ 0.3M	E2E-X16MB1DL12-M1TJ 0.3M	E2E-X16MC1L12-M1TJ 0.3M		
		09 111111	NC	-	E2E-X16MB2L12-M1TJ 0.3M	E2E-X16MC2L12-M1TJ 0.3M		
		48 mm	NO	E2E-X16MB1T12-M1	E2E-X16MB1D12-M1	E2E-X16MC112-M1		
	M12 Connector	40 111111	NC	-	E2E-X16MB212-M1	E2E-X16MC212-M1		
	WITZ CONNECTOR	70 mm	NO	E2E-X16MB1TL12-M1	E2E-X16MB1DL12-M1	E2E-X16MC1L12-M1		
		70 111111	NC	-	E2E-X16MB2L12-M1	E2E-X16MC2L12-M1		
	Pre-wired (2 m) *1	77 mm	NO	E2E-X30MB1TL18 2M	E2E-X30MB1DL18 2M	E2E-X30MC1L18 2M		
	Tie-wired (2 iii) T	*2	NC	-	E2E-X30MB2L18 2M	E2E-X30MC2L18 2M		
M18	M12 Pre-wired	77 mm	NO	E2E-X30MB1TL18-M1TJ 0.3M	E2E-X30MB1DL18-M1TJ 0.3M	E2E-X30MC1L18-M1TJ 0.3M		
(30 mm)	Smartclick Connector (0.3 m)	*3	NC	-	E2E-X30MB2L18-M1TJ 0.3M	E2E-X30MC2L18-M1TJ 0.3M		
			NO	E2E-X30MB1TL18-M1	E2E-X30MB1DL18-M1	E2E-X30MC1L18-M1		
	M12 Connector	75 mm	NC	-	E2E-X30MB2L18-M1	E2E-X30MC2L18-M1		
	D	97 mm	NO	E2E-X50MB1TL30 2M	E2E-X50MB1DL30 2M	E2E-X50MC1L30 2M		
	Pre-wired (2 m) *1	*2	NC	-	E2E-X50MB2L30 2M	E2E-X50MC2L30 2M		
M30	M12 Pre-wired	97 mm	NO	E2E-X50MB1TL30-M1TJ 0.3M	E2E-X50MB1DL30-M1TJ 0.3M	E2E-X50MC1L30-M1TJ 0.3M		
(50 mm)	Smartclick Connector (0.3 m)	*3	NC	-	E2E-X50MB2L30-M1TJ 0.3M	E2E-X50MC2L30-M1TJ 0.3M		
	M40.0	0.5	NO	E2E-X50MB1TL30-M1	E2E-X50MB1DL30-M1	E2E-X50MC1L30-M1		
	M12 Connector 95 mm	NC	-	E2E-X50MB2L30-M1	E2E-X50MC2L30-M1			

^{*1.} Models with 5-m cable length are also available (Example: E2E-X16MB1D12 5M)

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X16MB1D12-R 2M/E2E-X16MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X16MB1D12-M1TJR 0.3M)

 $^{^{\}star}4$. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

E2E NEXT Series (Triple distance model)

DC 3-wire [Refer to *Dimensions* on page 53.]

Shielded *1

Size				Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN		
distance)	method	3120	mode	IO-Link (COM3)	IO-Link (COM2) *5	*5		
		38 mm	NO	E2E-X3B1T8 2M	E2E-X3B1D8 2M	E2E-X3C18 2M		
	Di d (0) *0	*3	NC	-	E2E-X3B28 2M	E2E-X3C28 2M		
	Pre-wired (2 m) *2	40	NO	E2E-X3B1TL8 2M	E2E-X3B1DL8 2M	E2E-X3C1L8 2M		
		48 mm	NC	-	E2E-X3B2L8 2M	E2E-X3C2L8 2M		
		38 mm	NO	E2E-X3B1T8-M1TJ 0.3M	E2E-X3B1D8-M1TJ 0.3M	E2E-X3C18-M1TJ 0.3M		
	M12 Pre-wired	*4	NC	-	E2E-X3B28-M1TJ 0.3M	E2E-X3C28-M1TJ 0.3M		
	Smartclick Connector (0.3 m)	40	NO	E2E-X3B1TL8-M1TJ 0.3M	E2E-X3B1DL8-M1TJ 0.3M	E2E-X3C1L8-M1TJ 0.3M		
	,	48 mm	NC	-	E2E-X3B2L8-M1TJ 0.3M	E2E-X3C2L8-M1TJ 0.3M		
		43 mm	NO	E2E-X3B1T8-M1	E2E-X3B1D8-M1	E2E-X3C18-M1		
M8			NC	-	E2E-X3B28-M1	E2E-X3C28-M1		
(3 mm)	M12 Connector	53 mm	NO	E2E-X3B1TL8-M1	E2E-X3B1DL8-M1	E2E-X3C1L8-M1		
		JJ IIIII	NC	-	E2E-X3B2L8-M1	E2E-X3C2L8-M1		
		00	NO	E2E-X3B1T8-M3	E2E-X3B1D8-M3	E2E-X3C18-M3		
	M8 Connector (4-pin)	39 mm	NC	-	E2E-X3B28-M3	E2E-X3C28-M3		
		40 mm	NO	E2E-X3B1TL8-M3	E2E-X3B1DL8-M3	E2E-X3C1L8-M3		
		49 mm	NC	-	E2E-X3B2L8-M3	E2E-X3C2L8-M3		
	M8 Connector (3-pin)	20	NO	E2E-X3B1T8-M5	E2E-X3B1D8-M5	E2E-X3C18-M5		
		39 mm	NC	-	E2E-X3B28-M5	E2E-X3C28-M5		
		49 mm	NO	E2E-X3B1TL8-M5	E2E-X3B1DL8-M5	E2E-X3C1L8-M5		
			NC	-	E2E-X3B2L8-M5	E2E-X3C2L8-M5		
		47 mm *3	NO	E2E-X6B1T12 2M	E2E-X6B1D12 2M	E2E-X6C112 2M		
			NC	-	E2E-X6B212 2M	E2E-X6C212 2M		
	Dro wined (2 m) *2		NO+NC	-	E2E-X6B3D12 2M	E2E-X6C312 2M		
	Pre-wired (2 m) *2		NO	E2E-X6B1TL12 2M	E2E-X6B1DL12 2M	E2E-X6C1L12 2M		
		69 mm	NC	-	E2E-X6B2L12 2M	E2E-X6C2L12 2M		
			NO+NC	-	E2E-X6B3DL12 2M	E2E-X6C3L12 2M		
			NO	E2E-X6B1T12-M1TJ 0.3M	E2E-X6B1D12-M1TJ 0.3M	E2E-X6C112-M1TJ 0.3M		
		47 mm *4	NC	-	E2E-X6B212-M1TJ 0.3M	E2E-X6C212-M1TJ 0.3M		
M12	M12 Pre-wired	7	NO+NC	-	E2E-X6B3D12-M1TJ 0.3M	E2E-X6C312-M1TJ 0.3M		
(6 mm)	Smartclick Connector (0.3 m)		NO	E2E-X6B1TL12-M1TJ 0.3M	E2E-X6B1DL12-M1TJ 0.3M	E2E-X6C1L12-M1TJ 0.3M		
	(2.2.1)	69 mm	NC	-	E2E-X6B2L12-M1TJ 0.3M	E2E-X6C2L12-M1TJ 0.3M		
			NO+NC	-	E2E-X6B3DL12-M1TJ 0.3M	E2E-X6C3L12-M1TJ 0.3M		
			NO	E2E-X6B1T12-M1	E2E-X6B1D12-M1	E2E-X6C112-M1		
		48 mm	NC	-	E2E-X6B212-M1	E2E-X6C212-M1		
	M12 Connector		NO+NC	-	E2E-X6B3D12-M1	E2E-X6C312-M1		
	M12 Connector		NO	E2E-X6B1TL12-M1	E2E-X6B1DL12-M1	E2E-X6C1L12-M1		
		70 mm	NC	-	E2E-X6B2L12-M1	E2E-X6C2L12-M1		
			NO+NC	-	E2E-X6B3DL12-M1	E2E-X6C3L12-M1		

PREMIUM Model

Size	_		0		Model	
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN
distance)	motilod	0.20	mode	IO-Link (COM3)	IO-Link (COM2) *5	*5
			NO	E2E-X12B1T18 2M	E2E-X12B1D18 2M	E2E-X12C118 2M
		55 mm *3	NC	-	E2E-X12B218 2M	E2E-X12C218 2M
	Dro winod (2 m) *2		NO+NC	-	E2E-X12B3D18 2M	E2E-X12C318 2M
	Pre-wired (2 m) *2	77 mm	NO	E2E-X12B1TL18 2M	E2E-X12B1DL18 2M	E2E-X12C1L18 2M
			NC	-	E2E-X12B2L18 2M	E2E-X12C2L18 2M
			NO+NC	-	E2E-X12B3DL18 2M	E2E-X12C3L18 2M
			NO	E2E-X12B1T18-M1TJ 0.3M	E2E-X12B1D18-M1TJ 0.3M	E2E-X12C118-M1TJ 0.3M
		55 mm *4	NC	-	E2E-X12B218-M1TJ 0.3M	E2E-X12C218-M1TJ 0.3M
M18	M12 Pre-wired	7	NO+NC	-	E2E-X12B3D18-M1TJ 0.3M	E2E-X12C318-M1TJ 0.3M
(12 mm)	Smartclick Connector (0.3 m)		NO	E2E-X12B1TL18-M1TJ 0.3M	E2E-X12B1DL18-M1TJ 0.3M	E2E-X12C1L18-M1TJ 0.3M
	,	77 mm	NC	-	E2E-X12B2L18-M1TJ 0.3M	E2E-X12C2L18-M1TJ 0.3M
			NO+NC	-	E2E-X12B3DL18-M1TJ 0.3M	E2E-X12C3L18-M1TJ 0.3M
		53 mm	NO	E2E-X12B1T18-M1	E2E-X12B1D18-M1	E2E-X12C118-M1
			NC	-	E2E-X12B218-M1	E2E-X12C218-M1
			NO+NC	-	E2E-X12B3D18-M1	E2E-X12C318-M1
	M12 Connector		NO	E2E-X12B1TL18-M1	E2E-X12B1DL18-M1	E2E-X12C1L18-M1
		75 mm	NC	-	E2E-X12B2L18-M1	E2E-X12C2L18-M1
			NO+NC	-	E2E-X12B3DL18-M1	E2E-X12C3L18-M1
		60 mm *3	NO	E2E-X22B1T30 2M	E2E-X22B1D30 2M	E2E-X22C130 2M
			NC	-	E2E-X22B230 2M	E2E-X22C230 2M
	Di d (0) *0		NO+NC	-	E2E-X22B3D30 2M	E2E-X22C330 2M
	Pre-wired (2 m) *2		NO	E2E-X22B1TL30 2M	E2E-X22B1DL30 2M	E2E-X22C1L30 2M
		82 mm	NC	-	E2E-X22B2L30 2M	E2E-X22C2L30 2M
			NO+NC	-	E2E-X22B3DL30 2M	E2E-X22C3L30 2M
			NO	E2E-X22B1T30-M1TJ 0.3M	E2E-X22B1D30-M1TJ 0.3M	E2E-X22C130-M1TJ 0.3M
		60 mm *4	NC	-	E2E-X22B230-M1TJ 0.3M	E2E-X22C230-M1TJ 0.3M
M30	M12 Pre-wired	7	NO+NC	-	E2E-X22B3D30-M1TJ 0.3M	E2E-X22C330-M1TJ 0.3M
(22 mm)	Smartclick Connector (0.3 m)		NO	E2E-X22B1TL30-M1TJ 0.3M	E2E-X22B1DL30-M1TJ 0.3M	E2E-X22C1L30-M1TJ 0.3M
	,	82 mm	NC	-	E2E-X22B2L30-M1TJ 0.3M	E2E-X22C2L30-M1TJ 0.3M
			NO+NC	-	E2E-X22B3DL30-M1TJ 0.3M	E2E-X22C3L30-M1TJ 0.3M
			NO	E2E-X22B1T30-M1	E2E-X22B1D30-M1	E2E-X22C130-M1
		58 mm	NC	-	E2E-X22B230-M1	E2E-X22C230-M1
			NO+NC	-	E2E-X22B3D30-M1	E2E-X22C330-M1
	M12 Connector		NO	E2E-X22B1TL30-M1	E2E-X22B1DL30-M1	E2E-X22C1L30-M1
		80 mm	NC	-	E2E-X22B2L30-M1	E2E-X22C2L30-M1
			NO+NC	-	E2E-X22B3DL30-M1	E2E-X22C3L30-M1
*4 \\/\	anala andelina en Ala a Dura			al rafar to Influence of Curroun	dian Matalan nana 54	

^{*1.} When embedding the Proximity Sensor in metal, refer to *Influence of Surrounding Metal* on page 51. *2. Models with 5-m cable length are also available (Example: E2E-X6B1D12 5M)

^{*3.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X6B1D12-R 2M/ E2E-X6B1D12-R 5M)

^{*4.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X6B1D12-M1TJR 0.3M)

^{*5.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

E2E NEXT Series (Triple distance model)

DC 3-wire [Refer to *Dimensions* on page 54.] Unshielded

Size	0	D- 1	0		Model	
(Sensing	Connection method	Body size	Operation mode	PN	IP .	NPN
distance)		0.20		IO-Link (COM3)	IO-Link (COM2) *4	*4
		38 mm	NO	E2E-X6MB1T8 2M	E2E-X6MB1D8 2M	E2E-X6MC18 2M
	Dro wired (2 m) *1	*2	NC	-	E2E-X6MB28 2M	E2E-X6MC28 2M
	Pre-wired (2 m) *1	40	NO	E2E-X6MB1TL8 2M	E2E-X6MB1DL8 2M	E2E-X6MC1L8 2M
		48 mm	NC	-	E2E-X6MB2L8 2M	E2E-X6MC2L8 2M
		38 mm	NO	E2E-X6MB1T8-M1TJ 0.3M	E2E-X6MB1D8-M1TJ 0.3M	E2E-X6MC18-M1TJ 0.3M
	M12 Pre-wired	*3	NC	-	E2E-X6MB28-M1TJ 0.3M	E2E-X6MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X6MB1TL8-M1TJ 0.3M	E2E-X6MB1DL8-M1TJ 0.3M	E2E-X6MC1L8-M1TJ 0.3M
	Commoder (d.c m)	48 mm	NC	-	E2E-X6MB2L8-M1TJ 0.3M	E2E-X6MC2L8-M1TJ 0.3M
		42	NO	E2E-X6MB1T8-M1	E2E-X6MB1D8-M1	E2E-X6MC18-M1
M8	M40 Commonton	43 mm	NC	-	E2E-X6MB28-M1	E2E-X6MC28-M1
(6 mm)	M12 Connector		NO	E2E-X6MB1TL8-M1	E2E-X6MB1DL8-M1	E2E-X6MC1L8-M1
		53 mm	NC	-	E2E-X6MB2L8-M1	E2E-X6MC2L8-M1
	M8 Connector	30 mm	NO	E2E-X6MB1T8-M3	E2E-X6MB1D8-M3	E2E-X6MC18-M3
		39 mm	NC	-	E2E-X6MB28-M3	E2E-X6MC28-M3
	(4-pin)	40	NO	E2E-X6MB1TL8-M3	E2E-X6MB1DL8-M3	E2E-X6MC1L8-M3
		49 mm	NC	-	E2E-X6MB2L8-M3	E2E-X6MC2L8-M3
			NO	E2E-X6MB1T8-M5	E2E-X6MB1D8-M5	E2E-X6MC18-M5
	M8 Connector	39 mm	NC	-	E2E-X6MB28-M5	E2E-X6MC28-M5
	(3-pin))	NO	E2E-X6MB1TL8-M5	E2E-X6MB1DL8-M5	E2E-X6MC1L8-M5
	49 mm	NC	-	E2E-X6MB2L8-M5	E2E-X6MC2L8-M5	
			NO	E2E-X10MB1T12 2M	E2E-X10MB1D12 2M	E2E-X10MC112 2M
		47 mm *2	NC	-	E2E-X10MB212 2M	E2E-X10MC212 2M
		2	NO+NC	-	E2E-X10MB3D12 2M	E2E-X10MC312 2M
	Pre-wired (2 m) *1		NO	E2E-X10MB1TL12 2M	E2E-X10MB1DL12 2M	E2E-X10MC1L12 2M
		69 mm	NC	-	E2E-X10MB2L12 2M	E2E-X10MC2L12 2M
			NO+NC	-	E2E-X10MB3DL12 2M	E2E-X10MC3L12 2M
			NO	E2E-X10MB1T12-M1TJ 0.3M	E2E-X10MB1D12-M1TJ 0.3M	E2E-X10MC112-M1TJ 0.3M
		47 mm	NC	-	E2E-X10MB212-M1TJ 0.3M	E2E-X10MC212-M1TJ 0.3M
M12	M12 Pre-wired	*3	NO+NC	-	E2E-X10MB3D12-M1TJ 0.3M	E2E-X10MC312-M1TJ 0.3M
(10 mm)	Smartclick Connector (0.3 m)		NO	E2E-X10MB1TL12-M1TJ 0.3M	E2E-X10MB1DL12-M1TJ 0.3M	E2E-X10MC1L12-M1TJ 0.3M
	Connector (0.5 m)	69 mm	NC	-	E2E-X10MB2L12-M1TJ 0.3M	E2E-X10MC2L12-M1TJ 0.3M
			NO+NC	-	E2E-X10MB3DL12-M1TJ 0.3M	E2E-X10MC3L12-M1TJ 0.3M
			NO	E2E-X10MB1T12-M1	E2E-X10MB1D12-M1	E2E-X10MC112-M1
		48 mm	NC	-	E2E-X10MB212-M1	E2E-X10MC212-M1
			NO+NC	-	E2E-X10MB3D12-M1	E2E-X10MC312-M1
	M12 Connector		NO	E2E-X10MB1TL12-M1	E2E-X10MB1DL12-M1	E2E-X10MC1L12-M1
		70 mm	NC	-	E2E-X10MB2L12-M1	E2E-X10MC2L12-M1
			NO+NC	-	E2E-X10MB3DL12-M1	E2E-X10MC3L12-M1
			NO	E2E-X20MB1TL18 2M	E2E-X20MB1DL18 2M	E2E-X20MC1L18 2M
	Pre-wired (2 m) *1	77 mm	NC	-	E2E-X20MB2L18 2M	E2E-X20MC2L18 2M
	(=,	*2	NO+NC	-	E2E-X20MB3DL18 2M	E2E-X20MC3L18 2M
			NO	E2E-X20MB1TL18-M1TJ	E2E-X20MB1DL18-M1TJ	E2E-X20MC1L18-M1TJ 0.3M
M18	M12 Pre-wired Smartclick	77 mm	NC		E2E-X20MB2L18-M1TJ 0.3M	E2E-X20MC2L18-M1TJ 0.3M
(20 mm)	Connector (0.3 m)	*3		-		
			NO+NC		E2E-X20MB3DL18-M1TJ 0.3M	E2E-X20MC3L18-M1TJ 0.3M
	M12 Consector	75	NO	E2E-X20MB1TL18-M1	E2E-X20MB1DL18-M1	E2E-X20MC1L18-M1
	M12 Connector	75 mm	NC	-	E2E-X20MB2L18-M1	E2E-X20MC2L18-M1
			NO+NC	-	E2E-X20MB3DL18-M1	E2E-X20MC3L18-M1

PREMIUM Model

Size				Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN		
distance)	motriou		liiouo -	IO-Link (COM3)	IO-Link (COM2) *4	*4		
			NO	E2E-X40MB1TL30 2M	E2E-X40MB1DL30 2M	E2E-X40MC1L30 2M		
	Pre-wired (2 m) *1	82 mm *2	NC	-	E2E-X40MB2L30 2M	E2E-X40MC2L30 2M		
		_	NO+NC	-	E2E-X40MB3DL30 2M	E2E-X40MC3L30 2M		
	M12 Pre-wired	82 mm *3	NO	E2E-X40MB1TL30-M1TJ 0.3M	E2E-X40MB1DL30-M1TJ 0.3M	E2E-X40MC1L30-M1TJ 0.3M		
M30 (40 mm)	Smartclick		NC	-	E2E-X40MB2L30-M1TJ 0.3M	E2E-X40MC2L30-M1TJ 0.3M		
(40 11111)	Connector (0.3 m)	3	NO+NC	-	E2E-X40MB3DL30-M1TJ 0.3M	E2E-X40MC3L30-M1TJ 0.3M		
			NO	E2E-X40MB1TL30-M1	E2E-X40MB1DL30-M1	E2E-X40MC1L30-M1		
	M12 Connector	80 mm	NC	-	E2E-X40MB2L30-M1	E2E-X40MC2L30-M1		
			NO+NC	-	E2E-X40MB3DL30-M1	E2E-X40MC3L30-M1		

^{*1.} Models with 5-m cable length are also available (Example: E2E-X10MB1D12 5M)

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X10MB1D12-R 2M/E2E-X10MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X10MB1D12-M1TJR 0.3M)

^{*4.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

BASIC Model

E2E NEXT Series (Double distance model)

DC 3-wire [Refer to *Dimensions* on page 57.]

Shielded

Size				Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP .	NPN		
distance)	metriou	3120	lilouc .	IO-Link (COM3)	IO-Link (COM2) *4	*4		
		38 mm	NO	E2E-X2B1T8 2M	E2E-X2B1D8 2M	E2E-X2C18 2M		
	D	*2	NC	-	E2E-X2B28 2M	E2E-X2C28 2M		
	Pre-wired (2 m) *1	40	NO	E2E-X2B1TL8 2M	E2E-X2B1DL8 2M	E2E-X2C1L8 2M		
		48 mm	NC	-	E2E-X2B2L8 2M	E2E-X2C2L8 2M		
		38 mm	NO	E2E-X2B1T8-M1TJ 0.3M	E2E-X2B1D8-M1TJ 0.3M	E2E-X2C18-M1TJ 0.3M		
	M12 Pre-wired	*3	NC	-	E2E-X2B28-M1TJ 0.3M	E2E-X2C28-M1TJ 0.3M		
	Smartclick Connector (0.3 m)	40	NO	E2E-X2B1TL8-M1TJ 0.3M	E2E-X2B1DL8-M1TJ 0.3M	E2E-X2C1L8-M1TJ 0.3M		
	,	48 mm	NC	-	E2E-X2B2L8-M1TJ 0.3M	E2E-X2C2L8-M1TJ 0.3M		
		40	NO	E2E-X2B1T8-M1	E2E-X2B1D8-M1	E2E-X2C18-M1		
		43 mm	NC	-	E2E-X2B28-M1	E2E-X2C28-M1		
M8 (2 mm)	M12 Connector		NO	E2E-X2B1TL8-M1	E2E-X2B1DL8-M1	E2E-X2C1L8-M1		
		53 mm	NC	-	E2E-X2B2L8-M1	E2E-X2C2L8-M1		
			NO+NC	•	E2E-X2B3DL8-M1	E2E-X2C3L8-M1		
		39 mm	NO	E2E-X2B1T8-M3	E2E-X2B1D8-M3	E2E-X2C18-M3		
	M8 Connector (4-pin)	39 111111	NC	-	E2E-X2B28-M3	E2E-X2C28-M3		
		49 mm	NO	E2E-X2B1TL8-M3	E2E-X2B1DL8-M3	E2E-X2C1L8-M3		
		49 11111	NC	-	E2E-X2B2L8-M3	E2E-X2C2L8-M3		
		39 mm	NO	E2E-X2B1T8-M5	E2E-X2B1D8-M5	E2E-X2C18-M5		
	M8 Connector (3-pin)	33 11111	NC	-	E2E-X2B28-M5	E2E-X2C28-M5		
		49 mm	NO	E2E-X2B1TL8-M5	E2E-X2B1DL8-M5	E2E-X2C1L8-M5		
			NC	-	E2E-X2B2L8-M5	E2E-X2C2L8-M5		
			NO	E2E-X4B1T12 2M	E2E-X4B1D12 2M	E2E-X4C112 2M		
		47 mm *2	NC	-	E2E-X4B212 2M	E2E-X4C212 2M		
	Dro wired (2 m) *4	-	NO+NC	-	E2E-X4B3D12 2M	E2E-X4C312 2M		
	Pre-wired (2 m) *1		NO	E2E-X4B1TL12 2M	E2E-X4B1DL12 2M	E2E-X4C1L12 2M		
		69 mm	NC	-	E2E-X4B2L12 2M	E2E-X4C2L12 2M		
			NO+NC	-	E2E-X4B3DL12 2M	E2E-X4C3L12 2M		
			NO	E2E-X4B1T12-M1TJ 0.3M	E2E-X4B1D12-M1TJ 0.3M	E2E-X4C112-M1TJ 0.3M		
		47 mm *3	NC	-	E2E-X4B212-M1TJ 0.3M	E2E-X4C212-M1TJ 0.3M		
M12	M12 Pre-wired	Ü	NO+NC	-	E2E-X4B3D12-M1TJ 0.3M	E2E-X4C312-M1TJ 0.3M		
(4 mm)	Smartclick Connector (0.3 m)		NO	E2E-X4B1TL12-M1TJ 0.3M	E2E-X4B1DL12-M1TJ 0.3M	E2E-X4C1L12-M1TJ 0.3M		
	, ,	69 mm	NC	-	E2E-X4B2L12-M1TJ 0.3M	E2E-X4C2L12-M1TJ 0.3M		
			NO+NC	-	E2E-X4B3DL12-M1TJ 0.3M	E2E-X4C3L12-M1TJ 0.3M		
			NO	E2E-X4B1T12-M1	E2E-X4B1D12-M1	E2E-X4C112-M1		
		48 mm	NC	•	E2E-X4B212-M1	E2E-X4C212-M1		
	M12 Connector		NO+NC	•	E2E-X4B3D12-M1	E2E-X4C312-M1		
	WITZ Connector		NO	E2E-X4B1TL12-M1	E2E-X4B1DL12-M1	E2E-X4C1L12-M1		
		70 mm	NC	-	E2E-X4B2L12-M1	E2E-X4C2L12-M1		
			NO+NC	-	E2E-X4B3DL12-M1	E2E-X4C3L12-M1		

BASIC Model

Size				Model				
(Sensing	Connection method	Body size	Operation mode	PN	P	NPN		
distance)	metriou	3126	illoue	IO-Link (COM3)	IO-Link (COM2) *4	*4		
			NO	E2E-X8B1T18 2M	E2E-X8B1D18 2M	E2E-X8C118 2M		
		55 mm *2	NC	-	E2E-X8B218 2M	E2E-X8C218 2M		
	D : 1/0)*4	2	NO+NC	-	E2E-X8B3D18 2M	E2E-X8C318 2M		
	Pre-wired (2 m) *1		NO	E2E-X8B1TL18 2M	E2E-X8B1DL18 2M	E2E-X8C1L18 2M		
		77 mm	NC	-	E2E-X8B2L18 2M	E2E-X8C2L18 2M		
			NO+NC	-	E2E-X8B3DL18 2M	E2E-X8C3L18 2M		
			NO	E2E-X8B1T18-M1TJ 0.3M	E2E-X8B1D18-M1TJ 0.3M	E2E-X8C118-M1TJ 0.3M		
		55 mm *3	NC	-	E2E-X8B218-M1TJ 0.3M	E2E-X8C218-M1TJ 0.3M		
M18	M12 Pre-wired	3	NO+NC	-	E2E-X8B3D18-M1TJ 0.3M	E2E-X8C318-M1TJ 0.3M		
(8 mm)	Smartclick Connector (0.3 m)		NO	E2E-X8B1TL18-M1TJ 0.3M	E2E-X8B1DL18-M1TJ 0.3M	E2E-X8C1L18-M1TJ 0.3M		
	,	77 mm	NC	-	E2E-X8B2L18-M1TJ 0.3M	E2E-X8C2L18-M1TJ 0.3M		
			NO+NC	-	E2E-X8B3DL18-M1TJ 0.3M	E2E-X8C3L18-M1TJ 0.3M		
			NO	E2E-X8B1T18-M1	E2E-X8B1D18-M1	E2E-X8C118-M1		
		53 mm	NC	-	E2E-X8B218-M1	E2E-X8C218-M1		
	M42 Connector		NO+NC	-	E2E-X8B3D18-M1	E2E-X8C318-M1		
	M12 Connector		NO	E2E-X8B1TL18-M1	E2E-X8B1DL18-M1	E2E-X8C1L18-M1		
		75 mm	NC	-	E2E-X8B2L18-M1	E2E-X8C2L18-M1		
			NO+NC	-	E2E-X8B3DL18-M1	E2E-X8C3L18-M1		
		60 mm *2	NO	E2E-X15B1T30 2M	E2E-X15B1D30 2M	E2E-X15C130 2M		
			NC	-	E2E-X15B230 2M	E2E-X15C230 2M		
	D : 1/0)*4		NO+NC	-	E2E-X15B3D30 2M	E2E-X15C330 2M		
	Pre-wired (2 m) *1		NO	E2E-X15B1TL30 2M	E2E-X15B1DL30 2M	E2E-X15C1L30 2M		
		82 mm	NC	-	E2E-X15B2L30 2M	E2E-X15C2L30 2M		
			NO+NC	-	E2E-X15B3DL30 2M	E2E-X15C3L30 2M		
			NO	E2E-X15B1T30-M1TJ 0.3M	E2E-X15B1D30-M1TJ 0.3M	E2E-X15C130-M1TJ 0.3M		
		60 mm *3	NC	-	E2E-X15B230-M1TJ 0.3M	E2E-X15C230-M1TJ 0.3M		
M30	M12 Pre-wired	3	NO+NC	-	E2E-X15B3D30-M1TJ 0.3M	E2E-X15C330-M1TJ 0.3M		
(15 mm)	Smartclick Connector (0.3 m)		NO	E2E-X15B1TL30-M1TJ 0.3M	E2E-X15B1DL30-M1TJ 0.3M	E2E-X15C1L30-M1TJ 0.3M		
	Commenter (ord m)	82 mm	NC	-	E2E-X15B2L30-M1TJ 0.3M	E2E-X15C2L30-M1TJ 0.3M		
			NO+NC	-	E2E-X15B3DL30-M1TJ 0.3M	E2E-X15C3L30-M1TJ 0.3M		
			NO	E2E-X15B1T30-M1	E2E-X15B1D30-M1	E2E-X15C130-M1		
		58 mm	NC	-	E2E-X15B230-M1	E2E-X15C230-M1		
			NO+NC	-	E2E-X15B3D30-M1	E2E-X15C330-M1		
	M12 Connector		NO	E2E-X15B1TL30-M1	E2E-X15B1DL30-M1	E2E-X15C1L30-M1		
		80 mm	NC	-	E2E-X15B2L30-M1	E2E-X15C2L30-M1		
			NO+NC	-	E2E-X15B3DL30-M1	E2E-X15C3L30-M1		

^{*1.} Models with 5-m cable length are also available (Example: E2E-X2B1D8 5M)

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2B1D8-R 2M/ E2E-X2B1D8-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X4B1T12-M1TJR 0.3M)

^{*4.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

BASIC Model

E2E NEXT Series (Double distance model)

DC 3-wire [Refer to *Dimensions* on page 58.] Unshielded

Size				Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN		
distance)	memod	3120	mode	IO-Link (COM3)	IO-Link (COM2) *4	*4		
		38 mm	NO	E2E-X4MB1T8 2M	E2E-X4MB1D8 2M	E2E-X4MC18 2M		
	D	*2	NC	-	E2E-X4MB28 2M	E2E-X4MC28 2M		
	Pre-wired (2 m) *1	40	NO	E2E-X4MB1TL8 2M	E2E-X4MB1DL8 2M	E2E-X4MC1L8 2M		
		48 mm	NC	-	E2E-X4MB2L8 2M	E2E-X4MC2L8 2M		
		38 mm	NO	E2E-X4MB1T8-M1TJ 0.3M	E2E-X4MB1D8-M1TJ 0.3M	E2E-X4MC18-M1TJ 0.3M		
	M12 Pre-wired	*3	NC	-	E2E-X4MB28-M1TJ 0.3M	E2E-X4MC28-M1TJ 0.3M		
	Smartclick Connector (0.3 m)	40	NO	E2E-X4MB1TL8-M1TJ 0.3M	E2E-X4MB1DL8-M1TJ 0.3M	E2E-X4MC1L8-M1TJ 0.3M		
	,	48 mm	NC	-	E2E-X4MB2L8-M1TJ 0.3M	E2E-X4MC2L8-M1TJ 0.3M		
		40	NO	E2E-X4MB1T8-M1	E2E-X4MB1D8-M1	E2E-X4MC18-M1		
		43 mm	NC	-	E2E-X4MB28-M1	E2E-X4MC28-M1		
M8 (4 mm)	M12 Connector		NO	E2E-X4MB1TL8-M1	E2E-X4MB1DL8-M1	E2E-X4MC1L8-M1		
(4 111111)		53 mm	NC	-	E2E-X4MB2L8-M1	E2E-X4MC2L8-M1		
			NO+NC	-	E2E-X4MB3DL8-M1	E2E-X4MC3L8-M1		
		20	NO	E2E-X4MB1T8-M3	E2E-X4MB1D8-M3	E2E-X4MC18-M3		
	M8 Connector	39 mm	NC	-	E2E-X4MB28-M3	E2E-X4MC28-M3		
	(4-pin)	40	NO	E2E-X4MB1TL8-M3	E2E-X4MB1DL8-M3	E2E-X4MC1L8-M3		
		49 mm	NC	-	E2E-X4MB2L8-M3	E2E-X4MC2L8-M3		
		20	NO	E2E-X4MB1T8-M5	E2E-X4MB1D8-M5	E2E-X4MC18-M5		
	M8 Connector (3-pin)	39 mm	NC	-	E2E-X4MB28-M5	E2E-X4MC28-M5		
		40	NO	E2E-X4MB1TL8-M5	E2E-X4MB1DL8-M5	E2E-X4MC1L8-M5		
		49 mm	NC	-	E2E-X4MB2L8-M5	E2E-X4MC2L8-M5		
		47 mm *2	NO	E2E-X8MB1T12 2M	E2E-X8MB1D12 2M	E2E-X8MC112 2M		
			NC	-	E2E-X8MB212 2M	E2E-X8MC212 2M		
	D		NO+NC	-	E2E-X8MB3D12 2M	E2E-X8MC312 2M		
	Pre-wired (2 m) *1		NO	E2E-X8MB1TL12 2M	E2E-X8MB1DL12 2M	E2E-X8MC1L12 2M		
		69 mm	NC	-	E2E-X8MB2L12 2M	E2E-X8MC2L12 2M		
			NO+NC	-	E2E-X8MB3DL12 2M	E2E-X8MC3L12 2M		
			NO	E2E-X8MB1T12-M1TJ 0.3M	E2E-X8MB1D12-M1TJ 0.3M	E2E-X8MC112-M1TJ 0.3M		
		47 mm *3	NC	-	E2E-X8MB212-M1TJ 0.3M	E2E-X8MC212-M1TJ 0.3M		
M12	M12 Pre-wired		NO+NC	-	E2E-X8MB3D12-M1TJ 0.3M	E2E-X8MC312-M1TJ 0.3M		
(8 mm)	Smartclick Connector (0.3 m)		NO	E2E-X8MB1TL12-M1TJ 0.3M	E2E-X8MB1DL12-M1TJ 0.3M	E2E-X8MC1L12-M1TJ 0.3M		
		69 mm	NC	-	E2E-X8MB2L12-M1TJ 0.3M	E2E-X8MC2L12-M1TJ 0.3M		
			NO+NC	-	E2E-X8MB3DL12-M1TJ 0.3M	E2E-X8MC3L12-M1TJ 0.3M		
			NO	E2E-X8MB1T12-M1	E2E-X8MB1D12-M1	E2E-X8MC112-M1		
		48 mm	NC	-	E2E-X8MB212-M1	E2E-X8MC212-M1		
	M42 Connected		NO+NC	-	E2E-X8MB3D12-M1	E2E-X8MC312-M1		
	M12 Connector		NO	E2E-X8MB1TL12-M1	E2E-X8MB1DL12-M1	E2E-X8MC1L12-M1		
		70 mm	NC	-	E2E-X8MB2L12-M1	E2E-X8MC2L12-M1		
		÷ ······	NO+NC	-	E2E-X8MB3DL12-M1	E2E-X8MC3L12-M1		

BASIC Model

Size					Model	
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN
distance)	method	3120	mode	IO-Link (COM3)	IO-Link (COM2) *4	*4
			NO	E2E-X16MB1T18 2M	E2E-X16MB1D18 2M	E2E-X16MC118 2M
		55 mm *2	NC	-	E2E-X16MB218 2M	E2E-X16MC218 2M
	Di d (0) *4	_	NO+NC	-	E2E-X16MB3D18 2M	E2E-X16MC318 2M
	Pre-wired (2 m) *1		NO	E2E-X16MB1TL18 2M	E2E-X16MB1DL18 2M	E2E-X16MC1L18 2M
		77 mm	NC	-	E2E-X16MB2L18 2M	E2E-X16MC2L18 2M
			NO+NC	-	E2E-X16MB3DL18 2M	E2E-X16MC3L18 2M
			NO	E2E-X16MB1T18-M1TJ 0.3M	E2E-X16MB1D18-M1TJ 0.3M	E2E-X16MC118-M1TJ 0.3M
	M12 Pre-wired Smartclick Connector (0.3 m)	55 mm *3	NC	-	E2E-X16MB218-M1TJ 0.3M	E2E-X16MC218-M1TJ 0.3M
M18		3	NO+NC	-	E2E-X16MB3D18-M1TJ 0.3M	E2E-X16MC318-M1TJ 0.3M
(16 mm)			NO	E2E-X16MB1TL18-M1TJ 0.3M	E2E-X16MB1DL18-M1TJ 0.3M	E2E-X16MC1L18-M1TJ 0.3M
		77 mm	NC	-	E2E-X16MB2L18-M1TJ 0.3M	E2E-X16MC2L18-M1TJ 0.3M
			NO+NC	-	E2E-X16MB3DL18-M1TJ 0.3M	E2E-X16MC3L18-M1TJ 0.3M
			NO	E2E-X16MB1T18-M1	E2E-X16MB1D18-M1	E2E-X16MC118-M1
		53 mm	NC	-	E2E-X16MB218-M1	E2E-X16MC218-M1
	M12 Connector		NO+NC	-	E2E-X16MB3D18-M1	E2E-X16MC318-M1
	W12 Connector	75 mm	NO	E2E-X16MB1TL18-M1	E2E-X16MB1DL18-M1	E2E-X16MC1L18-M1
			NC	-	E2E-X16MB2L18-M1	E2E-X16MC2L18-M1
			NO+NC	-	E2E-X16MB3DL18-M1	E2E-X16MC3L18-M1
			NO	E2E-X30MB1TL30 2M	E2E-X30MB1DL30 2M	E2E-X30MC1L30 2M
	Pre-wired (2 m) *1	82 mm *2	NC	-	E2E-X30MB2L30 2M	E2E-X30MC2L30 2M
		_	NO+NC	-	E2E-X30MB3DL30 2M	E2E-X30MC3L30 2M
1400	M12 Pre-wired		NO	E2E-X30MB1TL30-M1TJ 0.3M	E2E-X30MB1DL30-M1TJ 0.3M	E2E-X30MC1L30-M1TJ 0.3M
M30 (30 mm)	Smartclick	82 mm *3	NC	-	E2E-X30MB2L30-M1TJ 0.3M	E2E-X30MC2L30-M1TJ 0.3M
(00 111111)	Connector (0.3 m)		NO+NC	-	E2E-X30MB3DL30-M1TJ 0.3M	E2E-X30MC3L30-M1TJ 0.3M
			NO	E2E-X30MB1TL30-M1	E2E-X30MB1DL30-M1	E2E-X30MC1L30-M1
	M12 Connector	80 mm	NC	-	E2E-X30MB2L30-M1	E2E-X30MC2L30-M1
			NO+NC		E2E-X30MB3DL30-M1	E2E-X30MC3L30-M1

^{*1.} Models with 5-m cable length are also available (Example: E2E-X8MB1D12 5M)
*2. Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X8MB1D12-R 2M/ E2E-X8MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X8MB1D12-M1TJR 0.3M)

^{*4.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

BASIC Model

E2E NEXT Series (Single distance model)

DC 3-wire [Refer to *Dimensions* on page 57.] Shielded

Size Connection		Body	Operation	Model					
(Sensing	Connection method	Body size	Operation mode	PN	P	NPN			
distance)	motriou	0.20	mode	IO-Link (COM3)	IO-Link (COM2) *4	*4			
		38 mm	NO	E2E-X1R5B1T8 2M	E2E-X1R5B1D8 2M	E2E-X1R5C18 2M			
	Dro wined (2 m) *4	*2	NC	-	E2E-X1R5B28 2M	E2E-X1R5C28 2M			
	Pre-wired (2 m) *1	40	NO	E2E-X1R5B1TL8 2M	E2E-X1R5B1DL8 2M	E2E-X1R5C1L8 2M			
		48 mm	NC	-	E2E-X1R5B2L8 2M	E2E-X1R5C2L8 2M			
		38 mm	NO	E2E-X1R5B1T8-M1TJ 0.3M	E2E-X1R5B1D8-M1TJ 0.3M	E2E-X1R5C18-M1TJ 0.3M			
	M12 Pre-wired	*3	NC	-	E2E-X1R5B28-M1TJ 0.3M	E2E-X1R5C28-M1TJ 0.3M			
	Smartclick Connector (0.3 m)	40	NO	E2E-X1R5B1TL8-M1TJ 0.3M	E2E-X1R5B1DL8-M1TJ 0.3M	E2E-X1R5C1L8-M1TJ 0.3M			
	,	48 mm	NC	-	E2E-X1R5B2L8-M1TJ 0.3M	E2E-X1R5C2L8-M1TJ 0.3M			
		40	NO	E2E-X1R5B1T8-M1	E2E-X1R5B1D8-M1	E2E-X1R5C18-M1			
140		43 mm	NC	-	E2E-X1R5B28-M1	E2E-X1R5C28-M1			
M8 (1.5 mm)	M12 Connector		NO	E2E-X1R5B1TL8-M1	E2E-X1R5B1DL8-M1	E2E-X1R5C1L8-M1			
(1.0 11111)		53 mm	NC	-	E2E-X1R5B2L8-M1	E2E-X1R5C2L8-M1			
			NO+NC	-	E2E-X1R5B3DL8-M1	E2E-X1R5C3L8-M1			
		39 mm	NO	E2E-X1R5B1T8-M3	E2E-X1R5B1D8-M3	E2E-X1R5C18-M3			
	M8 Connector	39 111111	NC	-	E2E-X1R5B28-M3	E2E-X1R5C28-M3			
	(4-pin)	40	NO	E2E-X1R5B1TL8-M3	E2E-X1R5B1DL8-M3	E2E-X1R5C1L8-M3			
		49 mm	NC	-	E2E-X1R5B2L8-M3	E2E-X1R5C2L8-M3			
		20	NO	E2E-X1R5B1T8-M5	E2E-X1R5B1D8-M5	E2E-X1R5C18-M5			
	M8 Connector	39 mm	NC	-	E2E-X1R5B28-M5	E2E-X1R5C28-M5			
	(3-pin)	49 mm	NO	E2E-X1R5B1TL8-M5	E2E-X1R5B1DL8-M5	E2E-X1R5C1L8-M5			
			NC	-	E2E-X1R5B2L8-M5	E2E-X1R5C2L8-M5			
			NO	E2E-X2B1T12 2M	E2E-X2B1D12 2M	E2E-X2C112 2M			
		47 mm *2	NC	-	E2E-X2B212 2M	E2E-X2C212 2M			
	Dro wined (2 m) *4	2	NO+NC	-	E2E-X2B3D12 2M	E2E-X2C312 2M			
	Pre-wired (2 m) *1		NO	E2E-X2B1TL12 2M	E2E-X2B1DL12 2M	E2E-X2C1L12 2M			
		69 mm	NC	-	E2E-X2B2L12 2M	E2E-X2C2L12 2M			
			NO+NC	-	E2E-X2B3DL12 2M	E2E-X2C3L12 2M			
			NO	E2E-X2B1T12-M1TJ 0.3M	E2E-X2B1D12-M1TJ 0.3M	E2E-X2C112-M1TJ 0.3M			
		47 mm *3	NC	-	E2E-X2B212-M1TJ 0.3M	E2E-X2C212-M1TJ 0.3M			
M12	M12 Pre-wired Smartclick	Ü	NO+NC	-	E2E-X2B3D12-M1TJ 0.3M	E2E-X2C312-M1TJ 0.3M			
(2 mm)	Connector (0.3 m)		NO	E2E-X2B1TL12-M1TJ 0.3M	E2E-X2B1DL12-M1TJ 0.3M	E2E-X2C1L12-M1TJ 0.3M			
		69 mm	NC	-	E2E-X2B2L12-M1TJ 0.3M	E2E-X2C2L12-M1TJ 0.3M			
			NO+NC	-	E2E-X2B3DL12-M1TJ 0.3M	E2E-X2C3L12-M1TJ 0.3M			
			NO	E2E-X2B1T12-M1	E2E-X2B1D12-M1	E2E-X2C112-M1			
		48 mm	NC	-	E2E-X2B212-M1	E2E-X2C212-M1			
	M12 Connector		NO+NC	-	E2E-X2B3D12-M1	E2E-X2C312-M1			
	WIZ CONNECTOR		NO	E2E-X2B1TL12-M1	E2E-X2B1DL12-M1	E2E-X2C1L12-M1			
		70 mm	NC	-	E2E-X2B2L12-M1	E2E-X2C2L12-M1			
			NO+NC	-	E2E-X2B3DL12-M1	E2E-X2C3L12-M1			

BASIC Model

Size	Connection			Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN		
distance)	memou	3120	lilouc	IO-Link (COM3)	IO-Link (COM2) *4	*4		
			NO	E2E-X5B1T18 2M	E2E-X5B1D18 2M	E2E-X5C118 2M		
		55 mm *2	NC	-	E2E-X5B218 2M	E2E-X5C218 2M		
	Daninn d (0) *4	_	NO+NC	-	E2E-X5B3D18 2M	E2E-X5C318 2M		
	Pre-wired (2 m) *1		NO	E2E-X5B1TL18 2M	E2E-X5B1DL18 2M	E2E-X5C1L18 2M		
		77 mm	NC	-	E2E-X5B2L18 2M	E2E-X5C2L18 2M		
			NO+NC	-	E2E-X5B3DL18 2M	E2E-X5C3L18 2M		
		55	NO	E2E-X5B1T18-M1TJ 0.3M	E2E-X5B1D18-M1TJ 0.3M	E2E-X5C118-M1TJ 0.3M		
		55 mm *3	NC	-	E2E-X5B218-M1TJ 0.3M	E2E-X5C218-M1TJ 0.3M		
M18	M12 Pre-wired	3	NO+NC	-	E2E-X5B3D18-M1TJ 0.3M	E2E-X5C318-M1TJ 0.3M		
(5 mm)	Smartclick Connector (0.3 m)		NO	E2E-X5B1TL18-M1TJ 0.3M	E2E-X5B1DL18-M1TJ 0.3M	E2E-X5C1L18-M1TJ 0.3M		
	, ,	77 mm	NC	-	E2E-X5B2L18-M1TJ 0.3M	E2E-X5C2L18-M1TJ 0.3M		
			NO+NC	-	E2E-X5B3DL18-M1TJ 0.3M	E2E-X5C3L18-M1TJ 0.3M		
			NO	E2E-X5B1T18-M1	E2E-X5B1D18-M1	E2E-X5C118-M1		
		53 mm	NC	-	E2E-X5B218-M1	E2E-X5C218-M1		
			NO+NC	-	E2E-X5B3D18-M1	E2E-X5C318-M1		
	M12 Connector		NO	E2E-X5B1TL18-M1	E2E-X5B1DL18-M1	E2E-X5C1L18-M1		
		75 mm	NC	-	E2E-X5B2L18-M1	E2E-X5C2L18-M1		
			NO+NC	-	E2E-X5B3DL18-M1	E2E-X5C3L18-M1		
		60 mm *2	NO	E2E-X10B1T30 2M	E2E-X10B1D30 2M	E2E-X10C130 2M		
			NC	-	E2E-X10B230 2M	E2E-X10C230 2M		
	Dro wired (2 m) *4		NO+NC	-	E2E-X10B3D30 2M	E2E-X10C330 2M		
	Pre-wired (2 m) *1	82 mm	NO	E2E-X10B1TL30 2M	E2E-X10B1DL30 2M	E2E-X10C1L30 2M		
			NC	-	E2E-X10B2L30 2M	E2E-X10C2L30 2M		
			NO+NC	-	E2E-X10B3DL30 2M	E2E-X10C3L30 2M		
			NO	E2E-X10B1T30-M1TJ 0.3M	E2E-X10B1D30-M1TJ 0.3M	E2E-X10C130-M1TJ 0.3M		
		60 mm *3	NC	-	E2E-X10B230-M1TJ 0.3M	E2E-X10C230-M1TJ 0.3M		
M30	M12 Pre-wired	3	NO+NC	-	E2E-X10B3D30-M1TJ 0.3M	E2E-X10C330-M1TJ 0.3M		
(10 mm)	Smartclick Connector (0.3 m)		NO	E2E-X10B1TL30-M1TJ 0.3M	E2E-X10B1DL30-M1TJ 0.3M	E2E-X10C1L30-M1TJ 0.3M		
	, ,	82 mm	NC	-	E2E-X10B2L30-M1TJ 0.3M	E2E-X10C2L30-M1TJ 0.3M		
			NO+NC	-	E2E-X10B3DL30-M1TJ 0.3M	E2E-X10C3L30-M1TJ 0.3M		
			NO	E2E-X10B1T30-M1	E2E-X10B1D30-M1	E2E-X10C130-M1		
		58 mm	NC	-	E2E-X10B230-M1	E2E-X10C230-M1		
			NO+NC	-	E2E-X10B3D30-M1	E2E-X10C330-M1		
	M12 Connector		NO	E2E-X10B1TL30-M1	E2E-X10B1DL30-M1	E2E-X10C1L30-M1		
		80 mm	NC	-	E2E-X10B2L30-M1	E2E-X10C2L30-M1		
			NO+NC	-	E2E-X10B3DL30-M1	E2E-X10C3L30-M1		

^{*1.} Models with 5-m cable length are also available (Example: E2E-X2B1D12 5M)

^{*2.} Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2B1D12-R 2M/ E2E-X2B1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X2B1D12-M1TJR 0.3M)

^{*4.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

BASIC Model

E2E NEXT Series (Single distance model)

DC 3-wire [Refer to *Dimensions* on page 58.] Unshielded

Size	Connection Body Operation Model					
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN
distance)	motriod	0.20	mode	IO-Link (COM3)	IO-Link (COM2) *4	*4
		38 mm	NO	E2E-X2MB1T8 2M	E2E-X2MB1D8 2M	E2E-X2MC18 2M
	Dro wired (2 m) *4	*2	NC	-	E2E-X2MB28 2M	E2E-X2MC28 2M
	Pre-wired (2 m) *1	40	NO	E2E-X2MB1TL8 2M	E2E-X2MB1DL8 2M	E2E-X2MC1L8 2M
		48 mm	NC	-	E2E-X2MB2L8 2M	E2E-X2MC2L8 2M
		38 mm	NO	E2E-X2MB1T8-M1TJ 0.3M	E2E-X2MB1D8-M1TJ 0.3M	E2E-X2MC18-M1TJ 0.3M
	M12 Pre-wired	*3	NC	-	E2E-X2MB28-M1TJ 0.3M	E2E-X2MC28-M1TJ 0.3M
	Smartclick Connector (0.3 m)	40	NO	E2E-X2MB1TL8-M1TJ 0.3M	E2E-X2MB1DL8-M1TJ 0.3M	E2E-X2MC1L8-M1TJ 0.3M
	, ,	48 mm	NC	-	E2E-X2MB2L8-M1TJ 0.3M	E2E-X2MC2L8-M1TJ 0.3M
		42	NO	E2E-X2MB1T8-M1	E2E-X2MB1D8-M1	E2E-X2MC18-M1
		43 mm	NC	-	E2E-X2MB28-M1	E2E-X2MC28-M1
M8 (2mm)	M12 Connector		NO	E2E-X2MB1TL8-M1	E2E-X2MB1DL8-M1	E2E-X2MC1L8-M1
(211111)		53 mm	NC	-	E2E-X2MB2L8-M1	E2E-X2MC2L8-M1
			NO+NC	-	E2E-X2MB3DL8-M1	E2E-X2MC3L8-M1
		20	NO	E2E-X2MB1T8-M3	E2E-X2MB1D8-M3	E2E-X2MC18-M3
	M8 Connector	39 mm	NC	-	E2E-X2MB28-M3	E2E-X2MC28-M3
	(4-pin)	40	NO	E2E-X2MB1TL8-M3	E2E-X2MB1DL8-M3	E2E-X2MC1L8-M3
		49 mm	NC	-	E2E-X2MB2L8-M3	E2E-X2MC2L8-M3
		39 mm	NO	E2E-X2MB1T8-M5	E2E-X2MB1D8-M5	E2E-X2MC18-M5
	M8 Connector	39 111111	NC	-	E2E-X2MB28-M5	E2E-X2MC28-M5
	(3-pin)	49 mm	NO	E2E-X2MB1TL8-M5	E2E-X2MB1DL8-M5	E2E-X2MC1L8-M5
		45 111111	NC	-	E2E-X2MB2L8-M5	E2E-X2MC2L8-M5
			NO	E2E-X5MB1T12 2M	E2E-X5MB1D12 2M	E2E-X5MC112 2M
		47 mm *2	NC	-	E2E-X5MB212 2M	E2E-X5MC212 2M
	Pre-wired (2 m) *1		NO+NC	-	E2E-X5MB3D12 2M	E2E-X5MC312 2M
	Fie-wiled (2 iii)		NO	E2E-X5MB1TL12 2M	E2E-X5MB1DL12 2M	E2E-X5MC1L12 2M
		69 mm	NC	-	E2E-X5MB2L12 2M	E2E-X5MC2L12 2M
			NO+NC	-	E2E-X5MB3DL12 2M	E2E-X5MC3L12 2M
		47	NO	E2E-X5MB1T12-M1TJ 0.3M	E2E-X5MB1D12-M1TJ 0.3M	E2E-X5MC112-M1TJ 0.3M
		47 mm *3	NC	-	E2E-X5MB212-M1TJ 0.3M	E2E-X5MC212-M1TJ 0.3M
M12	M12 Pre-wired Smartclick		NO+NC	-	E2E-X5MB3D12-M1TJ 0.3M	E2E-X5MC312-M1TJ 0.3M
(5mm)	Connector (0.3 m)		NO	E2E-X5MB1TL12-M1TJ 0.3M	E2E-X5MB1DL12-M1TJ 0.3M	E2E-X5MC1L12-M1TJ 0.3M
		69 mm	NC	-	E2E-X5MB2L12-M1TJ 0.3M	E2E-X5MC2L12-M1TJ 0.3M
			NO+NC	-	E2E-X5MB3DL12-M1TJ 0.3M	E2E-X5MC3L12-M1TJ 0.3M
			NO	E2E-X5MB1T12-M1	E2E-X5MB1D12-M1	E2E-X5MC112-M1
		48 mm	NC	-	E2E-X5MB212-M1	E2E-X5MC212-M1
	M12 Connector		NO+NC	-	E2E-X5MB3D12-M1	E2E-X5MC312-M1
	WIZ COINECIO		NO	E2E-X5MB1TL12-M1	E2E-X5MB1DL12-M1	E2E-X5MC1L12-M1
		70 mm	NC	-	E2E-X5MB2L12-M1	E2E-X5MC2L12-M1
			NO+NC	-	E2E-X5MB3DL12-M1	E2E-X5MC3L12-M1

BASIC Model

Size	Connection			Model				
(Sensing	Connection method	Body size	Operation mode	PN	IP	NPN		
distance)	memou	3120	mouc	IO-Link (COM3)	IO-Link (COM2) *4	*4		
			NO	E2E-X10MB1T18 2M	E2E-X10MB1D18 2M	E2E-X10MC118 2M		
		55 mm *2	NC	-	E2E-X10MB218 2M	E2E-X10MC218 2M		
	Daninn d (0) *4	_	NO+NC	-	E2E-X10MB3D18 2M	E2E-X10MC318 2M		
	Pre-wired (2 m) *1		NO	E2E-X10MB1TL18 2M	E2E-X10MB1DL18 2M	E2E-X10MC1L18 2M		
		77 mm	NC	-	E2E-X10MB2L18 2M	E2E-X10MC2L18 2M		
			NO+NC	-	E2E-X10MB3DL18 2M	E2E-X10MC3L18 2M		
			NO	E2E-X10MB1T18-M1TJ 0.3M	E2E-X10MB1D18-M1TJ 0.3M	E2E-X10MC118-M1TJ 0.3M		
		55 mm *3	NC	-	E2E-X10MB218-M1TJ 0.3M	E2E-X10MC218-M1TJ 0.3M		
M18	M12 Pre-wired	3	NO+NC	-	E2E-X10MB3D18-M1TJ 0.3M	E2E-X10MC318-M1TJ 0.3M		
(10mm)	Smartclick Connector (0.3 m)		NO	E2E-X10MB1TL18-M1TJ 0.3M	E2E-X10MB1DL18-M1TJ 0.3M	E2E-X10MC1L18-M1TJ 0.3M		
	,	77 mm	NC	-	E2E-X10MB2L18-M1TJ 0.3M	E2E-X10MC2L18-M1TJ 0.3M		
			NO+NC	-	E2E-X10MB3DL18-M1TJ 0.3M	E2E-X10MC3L18-M1TJ 0.3M		
			NO	E2E-X10MB1T18-M1	E2E-X10MB1D18-M1	E2E-X10MC118-M1		
		53 mm	NC	-	E2E-X10MB218-M1	E2E-X10MC218-M1		
			NO+NC	-	E2E-X10MB3D18-M1	E2E-X10MC318-M1		
	M12 Connector		NO	E2E-X10MB1TL18-M1	E2E-X10MB1DL18-M1	E2E-X10MC1L18-M1		
		75 mm	NC	-	E2E-X10MB2L18-M1	E2E-X10MC2L18-M1		
			NO+NC	-	E2E-X10MB3DL18-M1	E2E-X10MC3L18-M1		
		60 mm *2	NO	E2E-X18MB1T30 2M	E2E-X18MB1D30 2M	E2E-X18MC130 2M		
			NC	-	E2E-X18MB230 2M	E2E-X18MC230 2M		
	Daninn d (0) *4		NO+NC	-	E2E-X18MB3D30 2M	E2E-X18MC330 2M		
	Pre-wired (2 m) *1		NO	E2E-X18MB1TL30 2M	E2E-X18MB1DL30 2M	E2E-X18MC1L30 2M		
		82 mm	NC	-	E2E-X18MB2L30 2M	E2E-X18MC2L30 2M		
			NO+NC	-	E2E-X18MB3DL30 2M	E2E-X18MC3L30 2M		
			NO	E2E-X18MB1T30-M1TJ 0.3M	E2E-X18MB1D30-M1TJ 0.3M	E2E-X18MC130-M1TJ 0.3M		
		60 mm *3	NC	-	E2E-X18MB230-M1TJ 0.3M	E2E-X18MC230-M1TJ 0.3M		
M30	M12 Pre-wired	3	NO+NC	-	E2E-X18MB3D30-M1TJ 0.3M	E2E-X18MC330-M1TJ 0.3M		
(18mm)	Smartclick Connector (0.3 m)		NO	E2E-X18MB1TL30-M1TJ 0.3M	E2E-X18MB1DL30-M1TJ 0.3M	E2E-X18MC1L30-M1TJ 0.3M		
	,	82 mm	NC	-	E2E-X18MB2L30-M1TJ 0.3M	E2E-X18MC2L30-M1TJ 0.3M		
			NO+NC	-	E2E-X18MB3DL30-M1TJ 0.3M	E2E-X18MC3L30-M1TJ 0.3M		
			NO	E2E-X18MB1T30-M1	E2E-X18MB1D30-M1	E2E-X18MC130-M1		
		58 mm	NC	-	E2E-X18MB230-M1	E2E-X18MC230-M1		
	M40 0		NO+NC	-	E2E-X18MB3D30-M1	E2E-X18MC330-M1		
	M12 Connector		NO	E2E-X18MB1TL30-M1	E2E-X18MB1DL30-M1	E2E-X18MC1L30-M1		
		80 mm	NC	-	E2E-X18MB2L30-M1	E2E-X18MC2L30-M1		
			NO+NC	-	E2E-X18MB3DL30-M1	E2E-X18MC3L30-M1		

^{*1.} Models with 5-m cable length are also available (Example: E2E-X5MB1D12 5M)

*2. Models with 2-m and 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X5MB1D12-R 2M/ E2E-X5MB1D12-R 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with R" in the model number. (Example: E2E-X5MB1D12-M1TJR 2M)

^{*4.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

Accessories (Sold Separately)

e-jig (Mounting Sleeves) [Refer to Dimensions on page 61.]

A Mounting Bracket is not provided with the Sensor. It must be ordered separately as required.

Appearance	Model	Applicable Sensor size	Applicable Sensor type
The same of the sa	Y92E-J8S12	M8	Triple distance model
	Y92E-J12S18	M12	Shielded models Pre-wired models
	Y92E-J18S30	M18	Standard body-sized

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents		
Y92E-NWM08-E2EN		M8	Clamping nuts (bronze with nickel plating): 2		
Y92E-NWM12-E2EN	E2E NEXT Series Quadruple distance/Triple distance model	M12	Toothed washer (iron with zinc plating): 2		
Y92E-NWM18-E2EN	(Shielded models)	M18			
Y92E-NWM30-E2EN		M30			
Y92E-NWM08-E2E	E2E NEXT Series	M8	Clamping nuts (bronze with nickel plating): 2		
Y92E-NWM12-E2E	Quadruple distance/Triple distance model (Unshielded models)	M12	Toothed washer (iron with zinc plating): 1		
Y92E-NWM18-E2E	Double distance/Single distance model (Shielded/Unshielded models)	M18			
Y92E-NWM30-E2E	, ,	M30			

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 108. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 111. For details of the connector, refer to XS3 Series Round Water-resistant Connectors (M8) on page 115.

Ratings and Specifications

PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Shielded

	Types		Quadruple di	stance model			Triple dista	ance model			
	Size	M8	M12	M18	M30	M8	M12	M18	M30		
Item	Model	E2E-X4□8	E2E-X9□12	E2E-X14□18	E2E-X23□30	E2E-X3□8	E2E-X6□12	E2E-X12□18	E2E-X22□30		
Sensing d	istance	4 mm±10%	9 mm±10%	14 mm±10%	23 mm±10%	3 mm±10%	6 mm±10%	12 mm±10%	22 mm±10%		
Setting dis	stance	0 to 3 mm	0 to 6.8 mm	0 to 10.6 mm	0 to 17.6 mm	0 to 2.4 mm	0 to 4.8 mm	0 to 9.6 mm	0 to 16.8 mm		
Differentia	al travel	15% max. of ser	nsing distance								
Detectable	e object	Ferrous metals ((For non-ferrous n	netals, refer to the	Engineering Dat	a on page 42.)					
Standard s	sensing	Iron, 12 × 12 × 1 mm	Iron, 27 × 27 × 1 mm	Iron, 42 × 42 × 1 mm	Iron, 69 × 69 × 1 mm	Iron, 9 × 9 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 36 × 36 × 1 mm	Iron, 66 × 66 × 1 mn		
Response	frequency	700 Hz	700 Hz	350 Hz	200 Hz	1,000 Hz	800 Hz	500 Hz	200 Hz		
Power sup	oply voltage	10 to 30 VDC (including 10% ripple (p-p)), Class 2									
Current co	onsumption	1-output models:16 mA max. 1-output models: 16 mA max., 2-output models: 20 mA max.									
Output co	nfiguration	B□ Models: PNF	open collector, 0	C□ Models: NPN	open collector						
Operation (with sens approachi	ing object		(B1, C1): NO (No (B2, C2): NC (No				1-output models	(B1, C1): NO (No (B2, C2): NC (No (B3, C3): NO+NC)	rmally closed),		
Control	Load current	1-output models 10 to 30 VDC, C	: lass 2, 50 mA ma	x.		1-output models: 10 to 30 VDC, Class 2, 100 mA max.	2-output models	lass 2, 100 mA m	,		
output	Residual voltage	1-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m) 1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m) 1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m) 2 v max. (Load current: 50 mA, Cable length: 2 m)							,		
Indicator *	2						ation indicator (grommunication indication		ng at 1 s intervals		
Protection	circuits	Power supply re	verse polarity pro	tection, Surge sur	opressor, Output	short-circuit prote	ction, Output reve	rse polarity protec	ction		
Ambient te range	emperature	Operating: -25 to 60°C Storage: -25 to 70°C (with no icing or condensation) Operating/Storage: -25 to 70°C (with no icing or condensation)									
Ambient h range	umidity	Operating/Stora	ge: 35% to 95% (v	with no condensa	tion)						
Temperatu influence	ure	-15% to 25% max. of sensing distance at 23°C in the temperature range of -25 to 60°C	x. of sing ance at ±15% max. of sensing distance at 23°C in the temperature range of -25 to 70°C ±10% max. of sensing distance at 23°C in the temperature -25 to 70°C -25 to 70°C						erature range of		
Voltage in	fluence		sing distance at r	ated voltage in th	e rated voltage +	15% range					
	resistance		500 VDC) between			/0					
Dielectric :		,	60 Hz for 1 minute	, ,		d case					
	resistance		-mm double ampli								
Shock resident	istance	500 m/s² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 tir	mes each in X, Y,	and Z directions	500 m/s² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 tir	mes each in X, Y,	and Z directions		
Degree of	protection	1: IP67G, Passe 35°C max.)		sistant Compone	nt Evaluation Star	dards *3 (Cutting	dard: DIN 40050 F oil type: specified				
Connectio	n method	Pre-wired Model		e length: 2 m), Pre	e-wired Connector	•	d cable length: 0.	3 m) and Connec	tor Models (M12		
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g		
Weight*4 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g		
,	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 95 g	Approx. 180 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 95 g	Approx. 180 g		

	Types		Quadruple di	stance model		Triple distance model							
	Size	M8	M12	M18	M30	M8	M12	M18	M30				
Item	Model	E2E-X4□8	E2E-X9□12	E2E-X14□18	E2E-X23□30	E2E-X3□8	E2E-X6□12	E2E-X12□18	E2E-X22□30				
	Case	Nickel-plated bra	Nickel-plated brass										
	Sensing surface	Polybutylene terephthalat (PBT)											
Materials	Clamping nuts	Nickel-plated bra	ass										
	Toothed washers	Zinc-plated iron											
	Cable	Vinyl chloride (PVC) Note: Material of Pre-wired Models and Pre-wired Connector Models.											
Main IO-Li functions*		Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function, monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset											
IO-Link	IO-Link specificati on	Ver 1.1											
Commun	Baud rate	COM2 (38.4 kbp	os), COM3 (230.4	kbps)									
ication specifica tions *2	Data length	PD size: 2 bytes	, OD size: 1 byte	(M-sequence type	e: TYPE_2_2)								
	Minimum cycle time	COM2: 2.3 ms, COM3: 0.4 ms											
Accessori	es	Instruction manual, Clamping nuts, Toothed washer											

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

*2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.
*3. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

²⁻year oil resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).

The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly.

The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

^{*4.} Weight of the standard body-sized model.

PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Unshielded

	Types		Quadruple di	stance model			Triple dista	ance model		
	Size	M8	M12	M18	M30	M8	M12	M18	M30	
Item	Model	E2E-X8M□8	E2E-X16M□12	E2E-X30M□18	E2E-X50M□30	E2E-X6M□8	E2E-X10M□12	E2E-X20M□18	E2E-X40M□30	
Sensing d	istance	8 mm±10%	16 mm±10%	30 mm±10%	50 mm±10%	6 mm±10%	10 mm±10%	20 mm±10%	40 mm±10%	
Setting dis	stance	0 to 6 mm	0 to 12.2 mm	0 to 23 mm	0 to 38.2 mm	0 to 4.8 mm	0 to 8 mm	0 to 16 mm	0 to 32 mm	
Differentia	al travel	15% max. of ser	nsing distance							
Detectable	e object	Ferrous metals	(For non-ferrous n	netals, refer to the	e Engineering Dat	a on page 42.)				
Standard sobject	sensing	Iron, 24 × 24 × 1 mm	Iron, 48 × 48 × 1 mm	Iron, 90 × 90 × 1 mm	Iron, 150 x 150 x 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 60 × 60 × 1 mm	Iron, 120 x 120 x 1 mm	
Response *1	frequency	500 Hz	400 Hz	200 Hz	100 Hz	800 Hz	400 Hz	200 Hz	100 Hz	
Power sup	oply voltage	10 to 30 VDC (ir	ncluding 10% ripp	le (p-p)), Class 2						
Current co	onsumption	1-output models	: 16 mA max.				1-output models 2-output models			
Output co	nfiguration	B□ Models: PNI C□ Models: NPI	P open collector N open collector							
Operation (with sens approachi	ing object		(B1, C1): NO (No (B2, C2): NC (No				1-output models 2-output models	s (B1, C1): NO (No s (B2, C2): NC (No s (B3, C3): illy open, Normally	ormally closed),	
Control	Load current 1-output models: 1-output models: 10 to 30 VDC, Class 2, 50 mA max.					Class 2, 100 mA m ::				
output	Residual voltage	1-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m) 1-output models: 2 V max. (Load current: 100 m 2-output models: 2 V max. (Load current: 100 m 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)						current: 100 mA, Ca	,	
Indicator *	2		I/O mode (SIO mode						ng at 1 s intervals)	
Protection	circuits	Power supply re	verse polarity pro	tection, Surge su	opressor, Output	short-circuit prote	ction, Output reve	rse polarity protec	ction	
Ambient to range	emperature	Operating/Storage: -25 to 70°C (with no icing or condensation)								
Ambient h range	umidity	Operating/Storage: 35% to 95% (with no condensation)								
Temperatu influence	ure	±15% max. of sensing distance at 23°C in the temperature range of -25 to 70°C ±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C								
Voltage in	fluence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range								
Insulation	resistance	50 M $Ω$ min. (at 500 VDC) between current-carrying parts and case								
Dielectric	strength	1,000 VAC, 50/6	60 Hz for 1 minute	between current	-carrying parts an	d case				
Vibration r		10 to 55 Hz, 1.5	-mm double ampl	itude for 2 hours	each in X, Y, and	Z directions				
Shock resident		500 m/s² 10 times each in X, Y, and Z directions 500 m/s² 10 times each in X, Y, and Z directions 500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions						and Z directions		
Degree of	protection	1: IP67G, Passe 35°C max.)	ls, Pre-wired Conr d OMRON's Oil-re els: IEC 60529: IP	esistant Compone	nt Evaluation Star	dards *3 (Cutting	oil type: specified			
Connectio	n method		ls (Standard cable 4-pin) Connector			Models (Standar	d cable length: 0.	3 m) and Connec	tor Models (M12	
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 190 g	Approx. 310 g	Approx. 85 g	Approx. 95 g	Approx. 190 g	Approx. 280 g	
Weight*4 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 125 g	Approx. 250 g	Approx. 55 g	Approx. 70 g	Approx. 125 g	Approx. 220 g	
	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 105 g	Approx. 230 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 105 g	Approx. 200 g	

	Types		Quadruple di	stance model		Triple distance model							
	Size	M8	M12	M18	M30	M8	M12	M18	M30				
Item	Model	E2E-X8M□8	E2E-X16M□12	E2E-X30M□18	E2E-X50M□30	E2E-X6M□8	E2E-X10M□12	E2E-X20M□18	E2E-X40M□30				
	Case	Stainless (SUS303)	Nickal-plated brace										
	Sensing surface	Polybutylene ter	Polybutylene terephthalat (PBT)										
Materials	Clamping nuts	Nickel-plated bra	Nickel-plated brass										
	Toothed washers	Zinc-plated iron											
	Cable	Vinyl chloride (P	VC) Note: Mate	rial of Pre-wired I	Models and Pre-w	ired Connector M	odels.						
Main IO-Li		the control outpu		electing, instability	output (IO-Link m	ode) ON delay tin	ximity judgment di ner time selecting t						
IO-Link	IO-Link specificati on	Ver1.1											
Commun	Baud rate	COM2 (38.4 kbp	os), COM3 (230.4	kbps)									
ication specifica tions *2	Data length	PD size: 2 bytes	s, OD size: 1 byte	(M-sequence type	e: TYPE_2_2)								
	Minimum cycle time	COM2: 2.3 ms,	COM3: 0.4 ms										
Accessories Instruction manual, Clamping nuts, Toothed washer													

 ^{*2.} ID-Link is not supported for NC-type PNP outputs or all types of NPN outputs.
 *3. The Oil-resistant Component Evaluation Standards are OMPONIO over direct.

The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from shipment. The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

^{*4.} Weight of the standard body-sized model.

BASIC Model

DC 3-wire (Double/Single distance model) Shielded

	Types		Double dista	nce model			Single distar	nce model	
	Size	M8	M12	M18	M30	М8	M12	M18	M30
Item	Model	E2E-X2□8	E2E-X4□12	E2E-X8□18	E2E-X15□30	E2E-X1R5□8	E2E-X2□12	E2E-X5□18	E2E-X10□30
Sensing d	istance	2 mm±10%	4 mm±10%	8 mm±10%	15 mm±10%	1.5 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%
Setting dis	stance	0 to 1.6 mm	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm	0 to 1.2 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm
Differentia	ıl travel	15% max. of sensi	ng distance			10% max. of sensi	ng distance		
Detectable	e object	Ferrous metals (Fo	r non-ferrous me	etals, refer to the	Engineering Dat	a on page 42.)	T.		
Standard s	sensing	Iron,	Iron,	Iron,	Iron,	Iron,	Iron,	Iron, 18 × 18 × 1 mm	Iron,
object	frequency	8 × 8 × 1 mm	12 × 12 × 1 mm	24 × 24 × 1 mm	45 × 45 × 1 mm	8 × 8 × 1 mm	12 × 12 × 1 mm	10 × 10 × 1 IIIII	30 × 30 × 1 mm
*1	rrequericy	1,500 Hz	1,000 Hz	500 Hz	250 Hz	2,000 Hz	1,500 Hz	600 Hz	400 Hz
Power sup	ply voltage	10 to 30 VDC (inclu	uding 10% ripple	(p-p)), Class 2	1	II.	11		Į.
Current co	onsumption	1-output models: 1- 2-output models: 2-							
Output co	nfiguration	B□ Models: PNP o C□ Models: NPN o							
Operation (with sens approachi	ing object	1-output models (B 1-output models (B 2-output models (B	2, C2): NC (Norr	mally closed),	Normally closed)	*3			
Control	Load current	1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA		1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA	,
	Residual voltage	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	m), 2-output model	current: 200 mA,	· ·	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m)		
Indicator *	2					it) and communication			g at 1 s intervals)
Protection	circuits	Power supply reve	rse polarity prote	ction, Surge sup	pressor, Output	short-circuit protection	on, Output revers	se polarity protect	ion
Ambient to	emperature	Operating/Storage: Note: The UL tem				lels is -25 to 70°C.			
Ambient h range	umidity	Operating/Storage:	35% to 95% (wi	th no condensati	on)				
Temperatu influence	ıre	±15% max. of sens ±10% max. of sens							
Voltage in		±1% max. of sensing	ng distance at ra	ted voltage in the	rated voltage ±	15% range			
	resistance	50 MΩ min. (at 500							
Dielectric		1,000 VAC, 50/60 I	Hz for 1 minute b	etween current-o	carrying parts an	d case			
Vibration r		10 to 55 Hz, 1.5-mi	m double amplitu	ude for 2 hours ea	ach in X, Y, and	1	1		
Shock resident (destruction		500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 t directions	imes each in X, \	Y, and Z	500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 t directions	imes each in X, \	∕, and Z
Degree of protection		1: IP67G, Passed C 35°C max.)	Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K, JIS C 0920 Anne 1: IP67G, Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000; Temperature						
Connectio	n method	Pre-wired Models (Models (M12 Conn				Models (Standard o	cable length: 0.3	m) and Connecto	or
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g
Weight *5 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g
,	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g

	Types		Double distar	nce model		Single distance model							
	Size	M8	M12	M18	M30	M8	M12	M18	M30				
Item	Model	E2E-X2□8	E2E-X4□12	E2E-X8□18	E2E-X15□30	E2E-X1R5□8	E2E-X2□12	E2E-X5□18	E2E-X10□30				
	Case	Stainless (SUS303)	Nickel-plated brass										
	Sensing surface	Polybutylene terep	Polybutylene terephthalat (PBT)										
Materials	Clamping nuts	Nickel-plated brass	Jickel-plated brass										
	Toothed washers	Zinc-plated iron											
	Cable	Vinyl chloride (PVC) Note: Material of Pre-wired Models and Pre-wired Connector Models.											
Main IO-Li			nd timer time sele	ecting, instability	output (IO-Link m	ng, excessive proxin lode) ON delay time I reset							
IO-Link	IO-Link specification	Ver1.1	Ver1.1										
Commun	Baud rate	COM2 (38.4 kbps),	COM3 (230.4 kl	bps)									
ication specifica	Data length	PD size: 2 bytes, C	D size: 1 byte (N	Л-sequence type	: TYPE_2_2)								
tions *2	Minimum cycle time	COM2: 2.3 ms, CO	M3: 0.4 ms										
Accessories Instruction manual, Clamping nuts, Toothed washer			Clamping nuts,	Toothed washer									

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

*2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

*3. Dual-output specification for the M8-size models is only applicable to long-size M12 Connector models.

*5. Weight of the standard body-sized model.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from shipment. The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

BASIC Model

DC 3-wire (Double/Single distance model)

Unshielded

	Types		Double dista	nce model			Single distar	nce model	
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2E-X4M□8	E2E-X8M□12	E2E-X16M□18	E2E-X30M□30	E2E-X2M□8	E2E-X5M□12	E2E-X10M□18	E2E-X18M□30
Sensing d	istance	4 mm±10%	8 mm±10%	16 mm±10%	30 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%	18 mm±10%
Setting dis	stance	0 to 3.2 mm	0 to 6.4 mm	0 to 12.8 mm	0 to 24 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm	0 to 14.4 mm
Differentia	ıl travel	15% max. of sensi	ng distance			10% max. of sensi	ng distance		
Detectable	e object	Ferrous metals (Fo	r non-ferrous me	tals, refer to the	Engineering Dat	a on page 42.)			,
Standard sobject	sensing	Iron, 12 x 12 x 1 mm	Iron, 24 × 24 × 1 mm	Iron, 48 × 48 × 1 mm	Iron, 90 × 90 × 1 mm	Iron, 8 × 8 × 1 mm	Iron, 15 x 15 x 1 mm	Iron, 30 x 30 x 1 mm	Iron, 54 × 54 × 1 mm
Response *1	frequency	1,000 Hz	800 Hz	400 Hz	100 Hz	1,000 Hz	800 Hz	400 Hz	100 Hz
Power sup	ply voltage	10 to 30 VDC (incli	uding 10% ripple	(p-p)), Class 2					
Current co	onsumption	1-output models: 1 2-output models: 2							
Output co	nfiguration	B□ Models: PNP o C□ Models: NPN o							
Operation (with sens approachi	ing object	1-output models (B 1-output models (B 2-output models (B	2, C3): NC (Norr	nally closed)	Normally closed)	*3			
Control output	Load current	1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA		1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max.	2-output model	Class 2, 200 mA	ŕ
	Residual voltage	1-output models: 2 V max. (Load current: 200 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)	m), 2-output model	current: 200 mA,	cable length of 2-output model	(under load current of 200 mA with gth of 2 m), nodels: (under load current of 100 mA with			
Indicator *	2					it) and communication			g at 1 s intervals)
Protection	circuits	Power supply reve	rse polarity prote	ction, Surge sup	pressor, Output	short-circuit protection	n, Output revers	e polarity protec	tion
Ambient to	emperature	Operating/Storage: Note: The UL terr				els is -25 to 70°C.			
Ambient h range	umidity	Operating/Storage:	: 35% to 95% (wi	th no condensati	on)				
Temperatu influence	ıre	±15% max. of sens							
Voltage in	fluence	±1% max. of sensi	ng distance at ra	ted voltage in the	rated voltage ±	15% range			
	resistance	50 MΩ min. (at 500		, ,					
Dielectric		1,000 VAC, 50/60	Hz for 1 minute b	etween current-	carrying parts an	d case			
Vibration r (destruction		10 to 55 Hz, 1.5-m	m double amplitu	ide for 2 hours e	ach in X, Y, and	Z directions			
Shock resident (destruction		500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 t directions	imes each in X, `	Υ, and Z	500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 times each in X, Y, and Z directions		
Degree of protection		1: IP67G, Passed C 35°C max.)	Pre-wired Models, Pre-wired Connector Models: IEC 60529:IP67, ISO 20653 (old standard: DIN 40050 PART9): IP69K, JIS C 0920 Anne 1: IP67G, Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000; Temperature						
Connectio	n method	Pre-wired Models (M8 (4-pin) Connec			wired Connector	Models (Standard c	able length: 0.3 r	m) and Models (N	M12 Connector,
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 280 g	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g
Weight *5 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 220 g	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g
	Connector	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 200 g	Approx. 40 g (M8/M12 Connector)	Approx. 55 g	Approx. 85 g	Approx. 160 g

	Types		Double distar	nce model		_	Single distar	ice model	_			
Size		M8	M12 M18 M30		M30	M8	M12	M18	M30			
Item	Model	E2E-X4M□8	E2E-X8M□12	E2E-X16M□18	E2E-X30M□30	E2E-X2M□8	E2E-X5M□12	E2E-X10M□18	E2E-X18M□30			
	Case	Stainless (SUS303)	Nickal-plated brace									
	Sensing surface	Polybutylene terephthalat (PBT)										
Materials	Clamping nuts	Nickel-plated brass										
	Toothed washers	Zinc-plated iron										
	Cable	Vinyl chloride (PVC) Note: Materia	al of Pre-wired M	odels and Pre-w	ired Connector Mod	els.					
Main IO-Li			nd timer time sele	ecting, instability	output (IO-Link m	ng, excessive proxin ode) ON delay timer I reset						
IO-Link	IO-Link specificati on	Ver 1.1										
Commun	Baud rate	COM2 (38.4 kbps),	COM3 (230.4 kb	ops)								
ication specifica tions *2	Data length	PD size: 2 bytes, C	D size: 1 byte (M	1-sequence type:	TYPE_2_2)							
	Minimum cycle time	COM2: 2.3 ms, CC	M3: 0.4 ms									
Accessories Instruction manual, Clamping nuts, Toothed washer			Clamping nuts,	Toothed washer								

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

*3. Dual-output specification for the M8-size models is only applicable to long-size M12 Connector models.

*4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the

*5. Weight of the standard body-sized model.


median value of the product design and the oil-resistance performance criterion result (=Typical value). Actual performance can be expected to decline after two years on average from shipment. The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

Engineering Data (Reference Value)

Sensing Area


PREMIUM Model

Quadruple distance model **Shielded**




Triple distance model


Shielded



Unshielded




Unshielded




BASIC Model

Double distance model Shielded




Single distance model


Shielded



Unshielded



Unshielded




Influence of Sensing Object Size and Material


PREMIUM Model

Shielded


Quadruple distance model Size: M8 E2E-X4□8




Triple distance model Size: M8 E2E-X3□8




Unshielded Quadruple distance model Size: M8 E2E-X8M□8




Triple distance model Size: M8 E2E-X6M□8




Size: M12 E2E-X9□12




Size: M12 E2E-X6□12




Size: M12 E2E-X16M□12




Size: M12 E2E-X10M□12




Size: M18 E2E-X14□18




Size: M18 E2E-X12□18




Size: M18 E2E-X30M□18




Size: M18 E2E-X20M□18




Size: M30 E2E-X23□30




Size: M30 E2E-X22□30



Size: M30 E2E-X50M□30




Size: M30 E2E-X40M□30




BASIC Model

Shielded

Double distance model Size: M8 E2E-X2□8




Single distance model Size: M8 E2E-X1R5□8




Unshielded


Double distance model Size: M8 E2E-X4M□8




Single distance model Size: M8 E2E-X2M□8




Size: M12 E2E-X4□12




Size: M12 E2E-X2□12




Size: M12 E2E-X8M□12




Size: M12 E2E-X5M□12




Size: M18 E2E-X8□18




Size: M18 E2E-X5□18




Size: M18 E2E-X16M□18




Size: M18 E2E-X10M□18




Size: M30 E2E-X15□30




Size: M30 E2E-X10□30



Size: M30 E2E-X30M□30



Size: M30 E2E-X18M□30




Monitor Output vs. Sensing Distance

PREMIUM Model

Shielded


Quadruple distance model

Size: M8 E2E-X4□8



Triple model


Size: M8 E2E-X3□8




Unshielded


Quadruple distance model

Size: M8 E2E-X8M□8




Triple distance model







Size: M12 E2E-X9□12




Size: M12 E2E-X6□12




Size: M12 E2E-X16M□12




Size: M12 E2E-X10M□12




Size: M18 E2E-X14□18




Size: M18 E2E-X12□18




Size: M18 E2E-X30M□18




Size: M18 E2E-X20M□18




Size: M30 E2E-X23□30




Size: M30 E2E-X22□30



Size: M30 E2E-X50M□30







BASIC Model

Shielded

Double distance model Size: M8 E2E-X2□8




Single distance model Size: M8 E2E-X1R5□8




Unshielded


Double distance model




Single distance model Size: M8 E2E-X2M□8




Size: M12 E2E-X4□12




Size: M12 E2E-X2□12




Size: M12 E2E-X8M□12




Size: M12 E2E-X5M□12




Size: M18 E2E-X8□18




Size: M18 E2E-X5□18




Size: M18 E2E-X16M□18




Size: M18 E2E-X10M□18




Size: M30 E2E-X15□30




Size: M30 E2E-X10□30



Size: M30 E2E-X30M□30



Size: M30 E2E-X18M□30



I/O Circuit Diagrams/Timing charts

DC 3-wire

PNP output


		Output	circuit
Operation mode	Model	Standard I/O mode (SIO mode) When using as a general	IO-Link Communication mode (COM mode) When using the Sensor connected to IO- Link Master Unit *1
NO	E2E-□B1	Proximity sensor main circuit Load Blue (3) 0V	Brown (1) L+ (1) Proximity sensor main circuit Black (4) C/Q (4) C- (3) IO-Link master
NC	E2E-□B2	Proximity sensor main circuit Load Note: M8 (3-pin) Connector: (1)(4)(3)	
NO+NC	E2E-□B3	Brown (1) +V Proximity Black (4)(NO) *2 OUT1 White (2) Load (NC) *2 OUT2 Load Blue (3) OV	Brown (1) L+ (1) Black (4) C/Q (4) sensor main circuit White (2) N(C) *2 DI (2) Blue (3) L- (3) IO-Link master

- *1. In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.
 *2. This is the factory setting. For models with IO-Link, the operation mode can be changed by the IO-Link communications.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2) (4) (3)	(24 (1) 3)	(1 ⁴ 3)

PNP output



Please contact your OMRON sales representative regarding assignment of data.


- *1. This is the factory setting. For models with IO-Link, the operation mode can be changed by the IO-Link communications.
- *2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).

NPN output

Operation mode	Model	Output circuit
NO	E2E-□C1	DC10 to 30V Brown (1) +V Load OUT main circuit Blue (3) OV
NC	E2E-□C2	DC10 to 30V Brown (1) +V Load Droximity Sensor Main Circuit Black (2) Note: M8 (3-pin) Connector: (1)(4)(3)
NO+NC	E2E-□C3	Brown (1) DC10 to 30V Proximity Sensor main circuit White (2)(NC) Blue (3) 0V

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2 (4) (3)		(T) ⁴ (3)



Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

№ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Otherwise, explosion may result. Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- 3. Do not use a voltage that exceeds the rated operating voltage range
 - Applying a voltage that is higher than the operating voltage range may result in explosion or fire.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- If the power supply is connected directly without a load, the internal elements may explode or burn.



Dispose of the product according to applicable regulations (laws).

Precautions for Correct Use

Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment


- 1. Do not install the Sensor in the following locations.
 - Outdoor locations directly subject to sunlight, rain, snow, waterdroplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited
 - Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.
- 6. When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state.
- 7. The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change.
- Operation check is performed using an OMRON's IO-Link master. If using an IO-Link master from another company, perform the operation check in advance.

Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Shielded


Туре	Model	L	d	D	m	n
	E2E-X4□8	3	30	3	12	20
Quadruple distance	E2E-X9□12	2	40	2	27	30
model	E2E-X14□18	2	60	2	42	70
	E2E-X23□30	2	100	2	12 27	100
	E2E-X3□8	0	20	0	9	18
Triple distance	E2E-X6□12	0	20	0	18	20
model	E2E-X12□18	0	50	0	36	54
	E2E-X22□30	0	70	0	66	90
	E2E-X2□8	0	8	0	4.5	12
Double distance	E2E-X4□12	0	18	0	12	18
model	E2E-X8□18	0	27	0	24	27
	E2E-X15□30	0	45	0	45	45
	E2E-X1R5□8	0	8	0	4.5	12
Single distance	E2E-X2□12	0	12	0	8	18
model	E2E-X5□18	0	18	0	20	27
	E2E-X10□30	0	30	0	40	45

Unshielded

Models	Model	L	d	D	m	n
	E2E-X8M□8	12	40	12	24	40
Quadruple distance	E2E-X16M□12	21	70	21	48	80
model	E2E-X30M□18	46	130	46	90	110
	E2E-X50M□30	60	200	60	150	180
	E2E-X6M□8	10	30	10	18	30
Triple distance	E2E-X10M□12	16	50	16	30	50
model	E2E-X20M□18	31	90	31	60	80
	E2E-X40M□30 *	50	170	50	120	140
Double distance	E2E-X4M□8	9	24	9	8	24
	E2E-X8M□12	11	40	11	20	40
model	E2E-X16M□18	21	70	21	48	70
	E2E-X30M□30	40	120	40	90	120
Single distance model	E2E-X2M□8	6	24	6	8	24
	E2E-X5M□12	11	40	11	20	36
	E2E-X10M□18	18	55	18	40	54
	E2E-X18M□30	25	90	25	70	90

^{*} If you use the model E2E-X40M□30, the panel thickness (t) is 4 mm or less.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

Models	Model	ı	d	D	m	n
	E2E-X4□8	4	30	4	12	20
Quadruple distance	E2E-X9□12	6	40	6	27	30
model	E2E-X14□18	7	60	7	42	70
	E2E-X23□30	9	100	9	69	100
	E2E-X3□8	2	20	2	9	18
Triple distance	E2E-X6□12	4	20	4	18	20
model	E2E-X12□18	4	50	4	36	54
	E2E-X22□30	8	70	8	66	90
	E2E-X2□8	0	8	0	4.5	12
Double distance	E2E-X4□12	2.4	18	2.4	12	18
model	E2E-X8□18	3.6	27	3.6	24	27
	E2E-X15□30	6	45	6	45	45
Single distance	E2E-X1R5□8	0	8	0	4.5	12
	E2E-X2□12	0	12	0	8	18
model	E2E-X5□18	0	18	0	20	27
	E2E-X10□30	0	30	0	40	45


Unshielded

Models	Model	ı	d	D	m	n
	E2E-X8M□8	15	40	15	24	40
Quadruple distance	E2E-X16M□12	25	70	25	48	80
model	E2E-X30M□18	50	130	50	90	110
	E2E-X50M□30	65	200	65	150	180
	E2E-X6M□8	13	30	13	18	30
Triple distance	E2E-X10M□12	20	50	20	30	50
model	E2E-X20M□18	35	90	35	60	80
	E2E-X40M□30 *	55	170	55	120	140
	E2E-X4M□8	12	24	12	8	24
Double distance	E2E-X8M□12	15	40	15	20	40
model	E2E-X16M□18	25	70	25	48	70
	E2E-X30M□30	45	120	45	90	120
	E2E-X2M□8	6	24	6	8	24
Single distance	E2E-X5M□12	15	40	15	20	36
model	E2E-X10M□18	22	55	22	40	54
	E2E-X18M□30	30	90	30	70	90

^{*} If you use the model E2E-X40M□30, the panel thickness (t) is 4 mm or less.

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

		Item		
Models	Model	Α	В	
	E2E-X4□8	40	20	
Quadruple distance	E2E-X9□12	60	35	
model	E2E-X14□18	90	50	
	E2E-X23□30	150	90	
	E2E-X3□8	25	20	
Triple distance model	E2E-X6□12	40	30	
Triple distance model	E2E-X12□18	70	45	
	E2E-X22□30	150	90	
	E2E-X2□8	20	15	
Double distance model	E2E-X4□12	30	20	
Double distance model	E2E-X8□18	60	35	
	E2E-X15□30	110	90	
Circula distance medal	E2E-X1R5□8	20	15	
	E2E-X2□12	30	20	
Single distance model	E2E-X5□18	50	35	
	E2E-X10□30	100	70	


Unshielded

Models	Model	Ite	em
Wodels	Woder	Α	В
	E2E-X8M□8	80	60
Quadruple distance	E2E-X16M□12	160	120
model	E2E-X30M□18	360	300
	E2E-X50M□30	700	480
	E2E-X6M□8	80	60
Triple distance model	E2E-X10M□12	120	100
Triple distance model	E2E-X20M□18	200	120
	E2E-X40M□30	380	300
	E2E-X4M□8	80	60
Double distance model	E2E-X8M□12	120	100
Double distance model	E2E-X16M□18	200	120
	E2E-X30M□30	350	300
Single distance model	E2E-X2M□8	80	60
	E2E-X5M□12	120	100
Single distance model	E2E-X10M□18	200	110
	E2E-X18M□30	300	200

Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.



Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table.

(A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

Quadruple distance model, Triple distance model, Spatter-resistant Triple distance model

		Part A		Part B	
Size	Shielded	Dimension (mm)	Torque	Torque	
M8	Shielded	9	4 N⋅m	10 N⋅m	
IVIO	Unshielded	3	4 11.111	IO N-III	
M12	Shielded	16	8 N⋅m	15 N⋅m	
IVI I Z	Unshielded	9	6 N⋅m		
M18	Shielded	16	15 N⋅m	60 N⋅m	
IVI I O	Unshielded	3	19 10-111	00 IN-III	
Mao	Shielded	23	40 N⋅m	80 N⋅m	
M30	Unshielded	8	40 N·M	90 IV-III	

Double distance model, Single distance model, Spatter-resistant Triple distance model, Spatter-resistant Single distance model

		Р	Part A	
Size	Shielded	Dimension (mm)	Torque	Torque
M8	Shielded	9	9 N⋅m	12 N⋅m
IVIO	Unshielded	3	9 111-1111	12 N-III
M12			30 N⋅m	
M18			70 N⋅m	
M30			180 N⋅m	

Dimensions

Sensor PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)

DEM


Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.


DC 3-wire (Long-body Quadruple/Triple distance model)


Pre-wired Models Pre-wired Connector Models (Shielded)


A) Francisco


Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.





















*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)
IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)




Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

_		
$\stackrel{\sim}{}$	Dimensions	F (mm)
$\downarrow \downarrow$	M8	8.5 dia. +0.5
- F :	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



M30

Wire pull	out posit
→ -Sc	
	Dimension

Sc		
	Dimensions	Sc (mm)
	M8	(0)
	M12	- (0)
	M18	2.5
	M30	2.5


Sensors PREMIUM Model


DC 3-wire (Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Unshielded)



Refer to the figure below the table for the connections of the Pre-wired Connector Model







DC 3-wire (Long-body Quadruple/Triple distance model)

Pre-wired Models Pre-wired Connector Models (Unshielded)





Refer to the figure below the table for the connections of the Pre-wired Connector Model.















*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

_		_
$\angle ! \Delta$	Dimensions	F (mm)
	M8	8.5 dia. +0.5
; F-+;	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)	
M8 M12	12	
M18	18	
M30	10	

Wire pull	out positio	n
	Dimensions	
	M8	

•	
Dimensions	Sc (mm)
M8	- (0)
M12	- (0)
M18	2.5
M30	2.5

Sensors PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)


Connector Models (Shielded)




DC 3-wire (Long-body Quadruple/Triple distance model)


Connector Models (Shielded)









E2E-X L8-M3/M5



E2E-X□8-M1




E2E-X□L8-M1




E2E-X□12-M1


⊢21 dia




E2E-X L12-M1




E2E-X□18-M1




E2E-X L18-M1



E2E-X□30-M1



E2E-X□L30-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)
IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Mounting Hole Dimensions



Dimensions	F (mm)
М8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Sensors PREMIUM Model

DC 3-wire (Quadruple/Triple distance model)

Connector Models (Unshielded)




DC 3-wire (Long-body Quadruple/Triple distance model)


Connector Models (Unshielded)




E2E-X M 8-M3/M5




E2E-X M L8-M3/M5




E2E-X□M□8-M1




E2E-X M L8-M1



E2E-X M 12-M1



E2E-X M L12-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator

(orange/ON), communication indicator (green/Flashing (1sec cycle))


Mounting Hole Dimensions





Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E-X M L18-M1







E2E-X□8

15 dia

--13 -

 \oplus

DC 3-wire (Double/Single distance model)

37.8

10

44

Operation mode: NO, NC Type 4-dia. vinyl-insulated round cable with 3 conductors

Insulator diameter: 1.05 mm), Standard length: 2 m

(Conductor cross section: 0.2 mm² (AWG24),

Pre-wired Models Pre-wired Connector Models (Shielded)



Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.


Two clamping nuts


DC 3-wire (Long-body Double/Single distance model) **Pre-wired Models**


Pre-wired Connector Models (Shielded)


Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model


Two clamping nuts


















*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

_		
$\angle ! $	Dimensions	F (mm)
\bigvee	M8	8.5 dia. +0.5
← F →;	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)
M8	12
M12	12
M18	18
M30	10

Wire pullout position

Sc		
	Dimensions	(
	M8	
	M12	
	M18	
	M30	

Sc

DC 3-wire (Double/Single distance model)

Pre-wired Models Pre-wired Connector Models (Unshielded)


Refer to the figure below the table for the connections of the Pre-wired

Connector Model


DC 3-wire (Long-body Double/Single distance model)


Pre-wired Models Pre-wired Connector Models (Unshielded)

Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.





Operation mode: NO, NC Type 4-dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm² (AWG24). Insulator diameter: 1.05 mm). Standard length: 2 m








Operation mode: NO, NC Type 4-dia. vinyl-insulated round cable with 3 conductors (Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.05 mm), Standard length: 2 m Note: Operation mode: NO+NC Type 4.3-dia. vinylinsulated round cable with 4 conductors













*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF) IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))



Pre-wired Connector Models (-M1TJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

_		
\angle ! Δ	Dimensions	F (mm)
\square	M8	8.5 dia. +0.5
+- F →	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Angle R of the Bending Wire

Dimensions	R (mm)
M8	12
M12	12
M18	18
M30	10



Wire pullout position

Dimensions	Sc (mm)
M8	- (0)
M12	- (0)
M18	2.5
M30	2.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

DC 3-wire (Double/Single distance model)

Connector Models (Shielded)




DC 3-wire (Long-body Double/Single distance model)

Connector Models (Shielded)




E2E-X□8-M3/M5






E2E-X□L8-M3/M5






E2E-X□8-M1






E2E-X□L8-M1






E2E-X□12-M1







E2E-X L12-M1







E2E-X□18-M1






E2E-X□L18-M1






E2E-X□30-M1





E2E-X□L30-M1



*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)
IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

DC 3-wire (Double/Single distance model)

Connector Models (Unshielded)



Note: The sensing surface of size M30 is light gray.

DC 3-wire (Long-body Double/Single distance model)


Connector Models (Unshielded)



Note: The sensing surface of size M30 is light gray.


E2E-X M 8-M3/M5






E2E-X M L8-M3/M5






E2E-X M 8-M1






E2E-X□M□L8-M1






E2E-X□M□12-M1






E2E-X M L12-M1







E2E-X M 18-M1







E2E-X M L18-M1







E2E-X18M□30-M1





E2E-X18M□L30-M1





*1. Standard I/O mode (SIO mode): Operation indicator (orange/ON), communication indicator (green/OFF)

IO-Link Communication mode (COM mode): Operation indicator (orange/ON), communication indicator (green/Flashing (1sec cycle))


Mounting Hole Dimensions




Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E-X30M L30-M1







Accessories (Sold Separately)

e-jig (Mounting Sleeves)


Y92E-J8S12



Y92E-J12S18



Y92E-J18S30



Material

Mounting Sleeve	Polyetheretherketone (PEEK) / Polybutylene terephthalate (PBT)			
Mounting Sleeve clamping nut	Polybutylene terephthalate (PBT)			
Sensor lock nut	Polybutylene terephthalate (PBT)			
Sensor lock O-ring	Material combining HNBR and fluororubber			

Tightening Force

	Torque				
Model	Mounting Sleeve clamping nut	Sensor lock nut			
Y92E-J8S12	0.6 N°m	0.6 N°m			
Y92E-J12S18	1.2 N°m	1.2 N°m			
Y92E-J18S30	5 N°m	3.5 N°m			

Note: The dimensional control of the threaded part is based on the fit with the accompanying nut.

MEMO

Proximity Sensor

E2E NEXT Series

DC 2-wire (Triple distance model)

Long-distance Detection Prevents Unexpected Facility Stoppages

- The world's longest sensing distance*1
 Nearly double the sensing distance of previous
- With high-brightness LED, the indicator is visible anywhere from 360°.
- Only 10 Seconds*2 to Replace a Proximity Sensor with the "e-jig" (Mounting Sleeve).
- Cables with enhanced oil resistance enabled 2-year oil resistance*3.
- IP69K compliant for water resistance and wash resistance.
- UL certification (UL60947-5-2) and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. Based on October 2025 OMRON investigation.
- *2. Time required to adjust the distance when installing a Sensor. Based on OMRON investigation.
- *3. Refer to page 66 for details.



Be sure to read Safety Precautions on page 69.







For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Legend

E2E - X (1) (2) D (3) (4) (5) - (6) - (7) (8) (9)

No.	Classification	Code	Meaning
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)
(2)	Chiclding	Blank	Shielded Models
(2)	Shielding	М	Unshielded Models
(2)	Operation mode	1	Normally open (NO)
(3)	Operation mode	2	Normally closed (NC)
(4)	Body size	Blank	Standard
(4)	Body Size	L	Long Body
		8	M8
(E)	Size	12	M12
(5)		18	M18
		30	M30
		Blank	Pre-wired Models
(6)	Connecting method	M1TGJ	M12 Pre-wired Smartclick Connector Models
		M1TGJR	M12 Pre-wired Smartclick Connector Models (Robot (bending-resistant) PVC cable)
(7)	Delegite	Blank	Polarity
(7)	Polarity	Т	No polarity
(8)	Cable specifications (Only shown in the model	Blank	Standard PVC cable
(0)	number of Pre-wired Models.)	R	Robot (bending-resistant) PVC cable
(9)	Cable length	Number M	Cable length

Note: 1. The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

2. Pin arrangements vary depending on the model. Refer to I/O Circuit Diagrams on page 68 for details.

Ordering Information

Sensors

DC 2-wire (Triple distance model) [Refer to Dimensions on page 71.] Shielded Models *1

Size	Connection method	Dolovity	Model		
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: No	
	Deci.e.d (0 ex) +0 +0	Yes	E2E-X3D18 2M	E2E-X3D28 2M	
M8	Pre-wired (2 m) *2 *3	No	E2E-X3D18-T 2M	E2E-X3D28-T 2M	
(3 mm)	M12 Pre-wired	Yes	E2E-X3D18-M1TGJ 0.3M	E2E-X3D28-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X3D18-M1TGJ-T 0.3M	E2E-X3D28-M1TGJ-T 0.3M	
	Pre-wired (2 m) *2 *3	Yes	E2E-X7D112 2M	E2E-X7D212 2M	
M12	Fie-wiled (2 iii) 2 3	No	E2E-X7D112-T 2M	E2E-X7D212-T 2M	
(7 mm)	M12 Pre-wired	Yes	E2E-X7D112-M1TGJ 0.3M	E2E-X7D212-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X7D112-M1TGJ-T 0.3M	E2E-X7D212-M1TGJ-T 0.3M	
	Dro wired (2 m) *2 *2	Yes	E2E-X11D118 2M	E2E-X11D218 2M	
M18	Pre-wired (2 m) *2 *3	No	E2E-X11D118-T 2M	E2E-X11D218-T 2M	
(11 mm)	M12 Pre-wired	Yes	E2E-X11D118-M1TGJ 0.3M	E2E-X11D218-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X11D118-M1TGJ-T 0.3M	E2E-X11D218-M1TGJ-T 0.3M	
	Pro wired (2 m) *2 *2	Yes	E2E-X20D130 2M	E2E-X20D230 2M	
M30	Pre-wired (2 m) *2 *3	No	E2E-X20D130-T 2M	E2E-X20D230-T 2M	
(20 mm)	M12 Pre-wired	Yes	E2E-X20D130-M1TGJ 0.3M	E2E-X20D230-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X20D130-M1TGJ-T 0.3M	E2E-X20D230-M1TGJ-T 0.3M	

Unshielded Models

Size	Connection method	Polority	Model		
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC	
	Pre-wired (2 m) *2 *3	Yes	E2E-X6MD18 2M	E2E-X6MD28 2M	
M8	Fre-wired (2 III) 2 3	No	E2E-X6MD18-T 2M	E2E-X6MD28-T 2M	
(6 mm)	M12 Pre-wired	Yes	E2E-X6MD18-M1TGJ 0.3M	E2E-X6MD28-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X6MD18-M1TGJ-T 0.3M	E2E-X6MD28-M1TGJ-T 0.3M	
	Dro wired (2 m) *2 *2	Yes	E2E-X10MD112 2M	E2E-X10MD212 2M	
M12	Pre-wired (2 m) *2 *3	No	E2E-X10MD112-T 2M	E2E-X10MD212-T 2M	
(10 mm)	M12 Pre-wired	Yes	E2E-X10MD112-M1TGJ 0.3M	E2E-X10MD212-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X10MD112-M1TGJ-T 0.3M	E2E-X10MD212-M1TGJ-T 0.3M	
	Dro wired (2 m) *2 *2	Yes	E2E-X20MD1L18 2M	E2E-X20MD2L18 2M	
M18	Pre-wired (2 m) *2 *3	No	E2E-X20MD1L18-T 2M	E2E-X20MD2L18-T 2M	
(20 mm)	M12 Pre-wired	Yes	E2E-X20MD1L18-M1TGJ 0.3M	E2E-X20MD2L18-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X20MD1L18-M1TGJ-T 0.3M	E2E-X20MD2L18-M1TGJ-T 0.3M	
	Dro wired (2 m) *2 *2	Yes	E2E-X40MD1L30 2M	E2E-X40MD2L30 2M	
M30	Pre-wired (2 m) *2 *3	No	E2E-X40MD1L30-T 2M	E2E-X40MD2L30-T 2M	
(40 mm)	M12 Pre-wired	Yes	E2E-X40MD1L30-M1TGJ 0.3M	E2E-X40MD2L30-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X40MD1L30-M1TGJ-T 0.3M	E2E-X40MD2L30-M1TGJ-T 0.3M	

^{*1.} When embedding the Proximity Sensor in metal, refer to *Influence of Surrounding Metal* on page 70.
*2. Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X3D18 5M)
*3. Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X3D18-R 2M/E2E-X3D18-R 5M)

^{*4.} Models with M12 Pre-wired Smartclick Connectors and robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X3D18-M1TGJR 0.3M/E2E-X3D18-M1TGJR-T 0.3M)

Accessories (Sold Separately)

e-jig (Mounting Sleeves) [Refer to Dimensions on page 72.]

A Mounting Bracket is not provided with the Sensor. It must be ordered separately as required.

Appearance	Model	Applicable Sensor size	Applicable Sensor type
and the same	Y92E-J8S12	M8	Triple distance model
	Y92E-J12S18	M12	Shielded models Pre-wired models
	Y92E-J18S30	M18	Standard body-sized

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents
Y92E-NWM08-E2EN		M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2EN	E2E NEXT Series	M12	Toothed washer (iron with zinc plating): 2
Y92E-NWM18-E2EN	Triple distance model (Shielded models)	M18	
Y92E-NWM30-E2EN		M30	
Y92E-NWM08-E2E		M8	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM12-E2E	E2E NEXT Series	M12	Toothed washer (iron with zinc plating): 1
Y92E-NWM18-E2E	Triple distance model (Unshielded models)	M18	
Y92E-NWM30-E2E		M30	

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 108. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 111.

Ratings and Specifications

DC 2-wire (Triple distance model)

	Size	Size M8 M12 M18		M30					
	Shielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded
Item	Model	E2E-X3D□	E2E-X6MD□	E2E-X7D□	E2E-X10MD□	E2E-X11D□	E2E-X20MD□	E2E-X20D□	E2E-X40MD□
Sensing o	distance	3 mm ±10%	6 mm ±10%	7 mm ±10%	10 mm ±10%	11 mm ±10%	20 mm ±10%	20 mm ±10%	40 mm ±10%
Setting di	istance *1	0 to 2.4 mm	0 to 4.8 mm	0 to 5.6 mm	0 to 8 mm	0 to 8.8 mm	0 to 16 mm	0 to 16 mm	0 to 32 mm
Differentia	al travel	15% max. of se	nsing distance						
Detectabl	le object	Ferrous metal (The sensing dista	ance decreases v	vith non-ferrous r	metal. Refer to E	ngineering Data	on page 67.)	
Standard	sensing object	Iron, Iron, <th< th=""><th>Iron, 120 x 120 x 1 mm</th></th<>						Iron, 120 x 120 x 1 mm	
Response frequency *2 350 Hz 250 Hz 350 Hz 200 Hz 250 Hz 200 Hz 200 Hz						200 Hz	50 Hz		
Power su	pply voltage	10 to 30 VDC, (10 to 30 VDC, (including 10% ripple (p-p))						
Leakage o	current	0.8 mA max.							
0	Load current	3 to 100 mA							
Control output	Residual voltage		x. (Load current: max. (Load curre						
Indicator			eration indicator (eration indicator (indicator (green)				
Operation	n mode	D1 Models: NO D2 Models: NC	Refer to the t	iming charts und	er I/O Circuit Dia	grams on page 6	8 for details.		
Protection	n circuits	Surge suppress	or, Load short-ci	rcuit protection					
Ambient t	temperature	Operating: -25 t	o 70°C, Storage:	-40 to 85°C (wit	n no icing or cond	densation)			
Ambient I	humidity range	Operating and S	Storage: 35% to 9	95% (with no con	densation)				
Temperature influence		±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C			±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C	±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C		
Voltage in	nfluence	±1% max. of se	nsing distance at	rated voltage in	the rated voltage	±15% range			
Insulation	n resistance	50 M Ω min. (at	500 VDC) betwe	en current-carryi	ng parts and case	Э			
Dielectric	strength	1,000 VAC, 50/	60 Hz for 1 minut	e between curre	nt-carrying parts	and case			
Vibration (destructi	resistance ion)	10 to 55 Hz, 1.5	i-mm double amp	olitude for 2 hours	s each in X, Y, ar	nd Z directions			
Shock res (destructi		500 m/s ² 10 tim and Z directions	es each in X, Y,	1,000 m/s ² 10 t	mes each in X, Y	, and Z direction	s		
Degree of	f protection	Component Eva	els/Pre-wired Cor aluation Standard 0050 PART9) IP	ls *4 (Cutting oil	P67 (IEC 60529) type: specified in	, IP67G *3 (JIS C JIS K 2241:2000	0920 Annex 1) , Temperature: 3	Passed OMRON' 35 °C max.) and I	s Oil-resistant SO 20653 (old
Connectir	ng method	Pre-wired Mode	els (Standard cab	le length: 2 m) a	nd Pre-wired Cor	nector Models (S	Standard cable le	ength: 0.3 m)	
Weight	Pre-wired Models	Approx. 60 g		Approx. 70 g		Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g
(packed state)	Pre-wired Connector Models	Approx. 30 g		Approx. 40 g		Approx. 70 g	Approx. 90 g	Approx.110 g	Approx. 140 g
	Case	Nickel-plated brass	Stainless steel (SUS303)	Nickel-plated b	ass				
	Sensing surface	Polybutylene terephthalate (PBT)							
Materials	Clamping nuts	Nickel-plated br	ass						
	Toothed washer	Zinc-plated iron							
	Cable	Vinyl chloride (PVC)							
Accessor	ies	Instruction man	ual, Clamping nu	ts, Toothed wash	ner				
*4. Use the Concer within the range in which the potting indicator (green LED) is ON (except D2 Models)									

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).


The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.
2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).
The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly.
The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

Engineering Data (Reference Value)

Sensing Area


Triple distance model **Shielded Models**



Influence of Sensing Object Size and Materials


Triple distance model **Shielded Models**

Size: M8 E2E-X3D□8




Unshielded Models

Size: M8 E2E-X6MD□8




Leakage Current


Triple distance model **Shielded / Unshielded Models** E2E-X□(M)D□(-T)




Unshielded Models



Size: M12 E2E-X7D□12




Size: M12 E2E-X10MD□12




Residual Output Voltage


Triple distance model **Shielded / Unshielded Models** $E2E-X\square(M)D\square(-T)$




Size: M18 E2E-X11D□18




Size: M18 E2E-X20MD□L18



Size: M30 E2E-X20D□30




Size: M30 E2E-X40MD□L30



67


I/O Circuit Diagrams

DC 2-wire Models (Triple distance model)



Note: For the Pre-wired Connector Models, the core wire color and pin number are different.

Connector Pin Arrangement



Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

⚠WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.			
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.			
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.			

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion.

Do not connect sensor to AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in an environment where flammable or explosive gas is present.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range. Applying a voltage that is higher than the operating voltage range may result in damage or burnout.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or burnout.
- 5. If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.



Dispose of the product according to applicable regulations (laws).

Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.


Operating Environment

- Do not install the product in the following locations.
 Doing so may result in product failure or malfunction.
 - Outdoor locations directly subject to sunlight, rain, snow, water droplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, in particular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - · Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.


AND Connection of Proximity Sensors

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Shielded

Туре	Size Model		L	d	D	m	n
	M8	E2E-X3D□8	0	20	2	9	18
Triple distance model	M12	E2E-X7D□12	0	20	4	18	20
	M18	E2E-X11D□18	0	50	4	33	54
	M30	E2E-X20D□30	0	70	8	60	90


Unshielded

Туре	Size	Model	L	d	D	m	n
	M8	E2E-X6MD□8	10	30	13	18	30
Triple distance	M12	E2E-X10MD□12	16	50	20	30	50
model	M18	E2E-X20MD□18	31	90	35	60	80
	M30	E2E-X40MD□30	50 *1	170	55 *2	120	140

^{*1.} If you use the M30 Triple distance model of Unshielded Model, the panel thickness (t) is 4 mm or less.

*2. Cannot be mounted if countersunk holes are used.

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Shielded


Туре	Size	Model	ı	d	D	m	n
	M8	E2E-X3D□8	2	20	2	9	18
Triple distance	M12	E2E-X7D□12	4	20	4	18	20
model	M18	E2E-X11D□18	4	50	4	33	54
	M30	E2E-X20D□30	8	70	8	60	90

Unshielded

Туре	Size Model		ı	d	D	m	n
	М8	E2E-X6MD□8	13	30	13	18	30
Triple distance	M12	E2E-X10MD□12	20	50	20	30	50
model	M18	E2E-X20MD□18	35	90	35	60	80
	M30	E2E-X40MD□30	55	170	55	120	140

Mutual Interference

When the Proximity Sensor is embedded in metal, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Shielded

Туре	Size	Model	Α	В
Triple distance model	М8	E2E-X3D□8	25	20
	M12	E2E-X7D□12	40	30
	M18	E2E-X11D□18	70	45
	M30	E2E-X20D□30	140	70

Unshielded

Туре	Size	Model	Α	В
Triple distance	М8	E2E-X6MD□8	80	60
	M12	E2E-X10MD□12	120	100
model	M18	E2E-X20MD□18	200	120
	M30	E2E-X40MD□30	380	280


Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.







Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

Triple distance model

Model		Part A		Part B	
		Dimension (mm)	Torque	Torque	
MO	Shielded	9	4 N⋅m	10 N⋅m	
M8	Unshielded	3	4 IN-III		
MAO	Shielded	16	8 N⋅m	15 N⋅m	
M12	Unshielded	9	6 N⋅m	19 14-111	
M18	Shielded	16	15 N⋅m	60 N·m	
IVI I O	Unshielded	3	13 11.111	60 N-III	
M30	Shielded	23	40 N⋅m	80 N⋅m	
	Unshielded	8	40 N·M	80 N·M	

Dimensions

Sensor

DC 2-wire (Triple distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)




Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.

Pre-wired Models Pre-wired Connector Models (Unshielded)



Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.

E2E-X3D₈




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m

E2E-X6MD₈ 37.8 33.4 15 dia 20 -Indicators *1 M8 × P1 Two clamping nuts Toothed washer

4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m


E2E-X7D□12




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23),

Insulator diameter: 1.15 mm), Standard length: 2 m


E2E-X10MD□12




E2E-X11D 18




E2E-X20MD L18



E2E-X20D □30




E2E-X40MD L30



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green) / D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

\rightarrow		
	Dimensions	F (mm)
4	M8	8.5 dia. +0.5
	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



a)	Dimensions	R (mm)
	M8	12
	M12	12
	M18	18
	M30	10

Wire pullout position




Dimensions	Sc (mm)
M8	- (0)
M12	- (0)
M18	2.5
M30	2.5


Accessories (Sold Separately)

e-jig (Mounting Sleeves)


Y92E-J8S12



Y92E-J12S18



Y92E-J18S30



Material

Mounting Sleeve	Polyetheretherketone (PEEK) / Polybutylene terephthalate (PBT)
Mounting Sleeve clamping nut	Polybutylene terephthalate (PBT)
Sensor lock nut	Polybutylene terephthalate (PBT)
Sensor lock O-ring	Material combining HNBR and fluororubber

Tightening Force

	Torque			
Model	Mounting Sleeve clamping nut	Sensor lock nut		
Y92E-J8S12	0.6 N°m	0.6 N*m		
Y92E-J12S18	1.2 N°m	1.2 N°m		
Y92E-J18S30	5 N * m	3.5 N°m		

Note: The dimensional control of the threaded part is based on the fit with the accompanying nut.

Proximity Sensor E2E NEXT Series

DC 2-wire (Standard/Double/Single distance model)

Enhanced Usability Enables Installation without Special Skills and Shortens Commissioning and Recovery Time

- With high-brightness LED, the indicator is visible anywhere from 360°.
- Cables with enhanced oil resistance enabled 2-year oil resistance*1.
- IP69K compliant for water resistance and wash resistance.
- UL certification (UL60947-5-2) and CSA certification (CSA C22.2 UL60947-5-2-14)
- *1. Refer to page 77 to 79 for details.



Be sure to read *Safety Precautions* on page 83.







Note: Some models are not certified.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Model Number Legend

E2E - X (1) (2) D (3) (4) (5) - (6) - (7) (8) - (9) (10)

No.	Туре	Code	Meaning
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)
(2)	Chielding	Blank	Shielded
(2)	Shielding	M	Unshielded
(2)	B) Operation mode	1	Normally open (NO)
(3)		2	Normally closed (NC)
(4)	Oscillation frequency type	Blank	Standard frequency
(4)	Oscillation nequency type	5	Different frequency
(5)	Body size	Blank	Standard
(5)	Douy SIZE	L	Long-body
		Blank	Pre-wired Models
		M1	M12 Connector Models (Old pin arrangement)
		M1G	M12 Connector Models (IEC pin arrangement)
		M1J	M12 Pre-wired Standard Connector Models (Old pin arrangement)
(6)	Connection method	M1GJ	M12 Pre-wired Standard Connector Models (IEC pin arrangement)
(0)	Cocodon modiod	M1TJ	M12 Pre-wired Smartclick Connector Models (Old pin arrangement)
		M1TGJ	M12 Pre-wired Smartclick Connector Models (IEC pin arrangement)
		M1TGJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable (IEC pin arrangement)
		M3G	M8 (4-pin) Connector Models (IEC pin arrangement)
(7)	Polarity	Blank	Polarity
(7)	Polarity	Т	No polarity
(8)	Cable specifications (Only shown in the model	Blank	Standard PVC cable
(0)	number of Pre-wired Models.)	R	Robot (bending-resistant) PVC cable
(9)	New model	N	New model This is blank if the cable specification in number (8) is R.
(10)	Cable length	Number M	Cable length (Applicable to Pre-wired Models and Prewired Connector Models.)

Note: 1. The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

2. Pin arrangements vary depending on the model. Refer to I/O Circuit Diagrams on page 82 for details.

E2E NEXT Series

Ordering Information

Sensors

DC 2-wire (Standard model) [Refer to *Dimensions* on page 85.] Shielded Models

Size	Connection method	Body size	Polarity	Model		
(Sensing distance)	Connection metriod	Body Size	Polarity	Operation mode: NO	Operation mode: NC	
	Pre-wired (2 m)	38 mm	Yes	E2E-X2D1-N 2M *1 *2	E2E-X2D2-N 2M *1 *2	
M8 (2mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	Yes	E2E-X2D1-M1TGJ 0.3M *4 *5		
(2111111)	M12 Connector	43 mm	Yes	E2E-X2D1-M1G *5	E2E-X2D2-M1G *5	
	M8 (4-pin) Connector	39 mm	Yes	E2E-X2D1-M3G	E2E-X2D2-M3G	
	Dro wined (2 m)	47 mm	Vee	E2E-X3D1-N 2M *1 *2 *3	E2E-X3D2-N 2M *1 *2 *3	
	Pre-wired (2 m)	69 mm	Yes	E2E-X3D1L 2M *1 *3	E2E-X3D2L 2M *1	
M12	M12 Pre-wired	47 mm	Yes	E2E-X3D1-M1TGJ 0.3M *4 *5		
(3 mm)	Smartclick Connector (0.3 m)	47 mm	No	E2E-X3D1-M1TJ-T 0.3M		
,	M12 Pre-wired Standard Connector (0.3 m)	47 mm	No		E2E-X3D2-M1GJ-T 0.3M	
	M12 Connector	48 mm	Yes	E2E-X3D1-M1G *3 *5	E2E-X3D2-M1G *5	
	Pre-wired (2 m)	55 mm	Yes	E2E-X7D1-N 2M *1 *2 *3	E2E-X7D2-N 2M *1 *2 *3	
	Pre-wired (2 m)	77 mm	res	E2E-X7D1L 2M *1 *3	E2E-X7D2L 2M *1	
M18	M12 Pre-wired	FF	Yes	E2E-X7D1-M1TGJ 0.3M *4 *5		
(7 mm)	Smartclick Connector (0.3 m)	55 mm	No	E2E-X7D1-M1TJ-T 0.3M		
,	M12 Pre-wired Standard Connector (0.3 m)	55 mm	No		E2E-X7D2-M1GJ-T 0.3M	
	M12 Connector	53 mm	Yes	E2E-X7D1-M1G *3 *5	E2E-X7D2-M1G *5	
	Dro wined (2 m)	60 mm	Yes	E2E-X10D1-N 2M *1 *2	E2E-X10D2-N 2M *1 *3	
• • • •	Pre-wired (2 m)	82 mm	res	E2E-X10D1L 2M *1 *3	E2E-X10D2L 2M *1	
M30 (10 mm)	M12 Pre-wired	60	Yes	E2E-X10D1-M1TGJ 0.3M *3 *4 *5		
(10 1/111)	Smartclick Connector (0.3 m)	60 mm	No	E2E-X10D1-M1TJ-T 0.3M		
	M12 Connector	58 mm	Yes	E2E-X10D1-M1G *3 *5	E2E-X10D2-M1G *5	

Unshielded Models

Size	Connection method	Dody size	Delevite	Model	
(Sensing distance)	Connection method	Body size	Polarity	Operation mode: NO	Operation mode: NC
	Pre-wired (2 m)	38 mm	Yes	E2E-X4MD1 2M *1 *2	E2E-X4MD2 2M *1 *2
M8 (4 mm)	M12 Connector	43 mm	Yes	E2E-X4MD1-M1G *5	E2E-X4MD2-M1G *5
(4 11111)	M8 (4-pin) Connector	39 mm	Yes	E2E-X4MD1-M3G	E2E-X4MD2-M3G
	5 (5 .)	47 mm	V	E2E-X8MD1 2M *1 *2	E2E-X8MD2 2M *1 *3
M12	Pre-wired (2 m)	69 mm	Yes	E2E-X8MD1L 2M *1 *3	E2E-X8MD2L 2M *1
(8 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	47 mm	Yes	E2E-X8MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	48 mm	Yes	E2E-X8MD1-M1G *3 *5	E2E-X8MD2-M1G *5
		55 mm		E2E-X14MD1 2M *1 *2 *3	E2E-X14MD2 2M *1 *2 *3
M18	Pre-wired (2 m)	77 mm	Yes	E2E-X14MD1L 2M *1 *3	E2E-X14MD2L 2M
(14 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	55 mm	Yes	E2E-X14MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	53 mm	Yes	E2E-X14MD1-M1G *3 *5	E2E-X14MD2-M1G *5
		60 mm	V	E2E-X20MD1 2M *1 *2 *3	E2E-X20MD2 2M *1 *3
M30	Pre-wired (2 m)	82 mm	Yes	E2E-X20MD1L 2M *1 *3	E2E-X20MD2L 2M *1
(20 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	60 mm	Yes	E2E-X20MD1-M1TGJ 0.3M *4 *5	
	M12 Connector	58 mm	Yes	E2E-X20MD1-M1G *3 *5	E2E-X20MD2-M1G *5

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X2D1-N 5M)

^{*2.} Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X2D1-R 2M/E2E-X2D1-R 5M)

^{*3.} Models with different frequencies are also available. The model number is E2E-X□D□5. (Example: E2E-X3D15-N 2M/E2E-X3D15L 2M)

^{*4.} M12 Pre-wired Standard Connector Models with a 0.3-m cable are also available. The model numbers of models with IEC pin arrangement include "-M1GJ". (Example: E2E-X2D1-M1GJ 0.3M)

The model numbers of models with old pin arrangement include "-M1J". (Example: E2E-X2D1-M1J 0.3M)

Models with old pin arrangement of M12 Pre-wired Smartclick Connector Models are also available. The model numbers include "-M1TJ". (Example: E2E-X3D1-M1TJ 0.3M)

^{*5.} Models with old pin arrangement are also available. The model number is E2E-X□D□-M1. (Example: E2E-X2D1-M1)

Sensors

DC 2-wire (Double distance model) [Refer to *Dimensions* on page 85.] Shielded Models

Size	Connection method	Body size	Polarity	Model		
(Sensing distance)	Connection method	Bouy Size	Folality	Operation mode: NO	Operation mode: NC	
M12 (4 mm)	Pre-wired (2 m)	47 mm	No	E2E-X4D1-T 2M *1	E2E-X4D2-T 2M *1	
M18 (8 mm)	Pre-wired (2 m)	55 mm	No	E2E-X8D1-T 2M *1	E2E-X8D2-T 2M *1	
M30 (15 mm)	Pre-wired (2 m)	60 mm	No	E2E-X15D1-T 2M *1	E2E-X15D2-T 2M *1	

Unshielded Models

Size	Connection method	Body size	Polarity	Model		
(Sensing distance)	Connection method	Bouy Size	lolanty	Operation mode: NO	Operation mode: NC	
M18 (16 mm)	Pre-wired (2 m)	77 mm	No	E2E-X16MD1L-T 2M *1	E2E-X16MD2L-T 2M	
M30 (30 mm)	Pre-wired (2 m)	82 mm	No	E2E-X30MD1L-T 2M *1	E2E-X30MD2L-T 2M *1	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X4D1-T 5M)

DC 2-wire (Single distance model) [Refer to *Dimensions* on page 88.] Shielded Models

Size	Connection method	Dolority	Model		
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC	
	Dec. (1) 10 10 10 10 10	Yes	E2E-X1R5D1-N 2M	E2E-X1R5D2-N 2M	
M8	Pre-wired (2 m) *2 *3	No	E2E-X1R5D1-T-N 2M	E2E-X1R5D2-T-N 2M	
(1.5 mm)	M12 Pre-wired	Yes	E2E-X1R5D1-M1TGJ 0.3M	E2E-X1R5D2-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X1R5D1-M1TGJ-T 0.3M	E2E-X1R5D2-M1TGJ-T 0.3M	
	Dro wind (2 m) *2 *2	Yes	E2E-X2R5D1-N 2M	E2E-X2R5D2-N 2M	
M12	Pre-wired (2 m) *2 *3	No	E2E-X2R5D1-T-N 2M	E2E-X2R5D2-T-N 2M	
(2.5 mm)	M12 Pre-wired	Yes	E2E-X2R5D1-M1TGJ 0.3M	E2E-X2R5D2-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X2R5D1-M1TGJ-T 0.3M	E2E-X2R5D2-M1TGJ-T 0.3M	
	Dro wind (2 m) *2 *2	Yes	E2E-X5D1-N 2M	E2E-X5D2-N 2M	
M18	Pre-wired (2 m) *2 *3	No	E2E-X5D1-T-N 2M	E2E-X5D2-T-N 2M	
(5 mm)	M12 Pre-wired	Yes	E2E-X5D1-M1TGJ 0.3M	E2E-X5D2-M1TGJ 0.3M	
	Smartclick Connector (0.3 m) *4	No	E2E-X5D1-M1TGJ-T 0.3M	E2E-X5D2-M1TGJ-T 0.3M	

^{*1.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2E-X1R5D1-N 5M)

^{*2.} Models with a 2-m or 5-m robot (bending-resistant) cables are also available with "-R" in the model number. (Example: E2E-X1R5D1-R-N 2M/ E2E-X1R5D1-R-N 5M)

^{*3.} Models with M12 Smartclick connector model robot (bending-resistant) cables are also available with "R" in the model number. (Example: E2E-X1R5D1-M1TGJR 0.3M/E2E-X1R5D1-M1TGJR-T 0.3M)

E2E NEXT Series

Accessories (Sold Separately)

Nut Sets

A Nut Set is included with the Sensor. Order a Nut Set when required, e.g., if you lose the nuts.

Model	Applicable Sensors	Applicable Sensor diameter	Set contents
Y92E-NWM08-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Single distance model (Shielded Models)	M8	
Y92E-NWM12-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded Models) Single distance model (Shielded Models)	M12	Clamping nuts (bronze with nickel plating): 2
Y92E-NWM18-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded/Unshielded Models) Single distance model (Shielded Models)	M18	Toothed washer (iron with zinc plating): 1
Y92E-NWM30-E2E	E2E NEXT Series Standard model (Shielded/Unshielded Models) Double distance model (Shielded/Unshielded Models)	M30	

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 NEXT Series Round Oil-resistant Connectors (M12 Smartclick) on page 108. For details of the connector, refer to XS5 Series Round Water-resistant Connectors (M12 Smartclick) on page 111. For details of the connector, refer to XS3 Series Round Water-resistant Connectors (M8) on page 115.

Ratings and Specifications

DC 2-wire (Standard model)

Size		M8		M12		M18		M30		
	Shielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	Shielded	Unshielded	
Item	Model	E2E-X2D□	E2E-X4MD□	E2E-X3D□	E2E-X8MD□	E2E-X7D□	E2E-X14MD□	E2E-X10D□	E2E-X20MD□	
Sensing di	stance	2 mm ±10%	4 mm ±10%	3 mm ±10%	8 mm ±10%	7 mm ±10%	14 mm ±10%	10 mm ±10%	20 mm ±10%	
Setting dis	tance *1	0 to 1.6 mm	0 to 3.2 mm	0 to 2.4 mm	0 to 6.4 mm	0 to 5.6 mm	0 to 11.2 mm	0 to 8 mm	0 to 16 mm	
Differential	travel	15% max. of se	nsing distance	10% max. of se	nsing distance		1			
Detectable	object			ance decreases v		metal. Refer to E	ngineering Data o	on page 80.)		
Standard s	ensing object	Iron, 8 × 8 × 1 mm	Iron, 20 × 20 × 1 mm	Iron, 12 × 12 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 18 x 18 x 1 mm	Iron, 30 × 30 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 54 × 54 × 1 mm	
Response	frequency *2	1.5 kHz	1 kHz	1 kHz	0.8 kHz	0.5 kHz	0.4 kHz	0.4 kHz	0.1 kHz	
Power sup	ply voltage	12 to 24 VDC (i	ncluding 10% rip	ple (p-p)), Class	2					
Leakage cı	urrent	0.8 mA max.								
	Load current	3 to 100 mA								
Control output	Residual voltage		larity: 3 V max. (Load current: 100 mA, Cable length: 2 m) polarity: 5 V max. (Load current: 100 mA, Cable length: 2 m)							
Indicator			D1 Models: Operation indicator (orange), Setting indicator (green) D2 Models: Operation indicator (orange)							
Operation	mode	D1 Models: NO D2 Models: NC	Refer to the t	timing charts und	er I/O Circuit Dia	grams on page 8	2 for details.			
Protection circuits Surge suppressor, Load short-circuit protection										
Ambient temperature range Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)										
Ambient hu	umidity range	Operating and Storage: 35% to 95% (with no condensation)								
Temperatu	re influence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C								
Voltage inf	luence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range								
Insulation resistance		$50~\text{M}\Omega$ min. (at $500~\text{VDC}$) between current-carrying parts and case								
Dielectric s	strength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case								
Vibration re (destructio		10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions								
Shock resident (destruction)		500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions								
Degree of p	orotection	Pre-wired Models/Pre-wired Connector Models: IP67 (IEC 60529), IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35°C max.) and ISO 20653 (old standard: DIN 40050 PART9) IP69K								
Connecting	g method			le length: 2 m), F Connector Mode		tor Models (Stan	dard cable length	n: 0.3 m),		
	Pre-wired Models	Approx. 60 g		Approx. 70 g		Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g	
Weight *5 (packed state)	Pre-wired Connector Models	Approx. 30 g		Approx. 40 g		Approx. 70 g	Approx. 90 g	Approx. 110 g	Approx. 140 g	
	Connector Models	Approx. 40 g (M8/M12 Connector) Approx. 55 g Approx. 85 g Approx. 80 g Approx. 160 g						Approx. 150 g		
	Case	M8 Size: Stainle	ess steel (SUS30	3), M12/M18/M3	0 Size: Nickel-pla	ated brass				
	Sensing surface	Polybutylene terephthalate (PBT)								
Materials	Clamping nuts	Nickel-plated bi	ass							
	Toothed washer	Zinc-plated iron								
	Cable	Vinyl chloride (f	PVC) Note: Ma	terial of Pre-wire	d Models and Pre	e-wired Connecto	r Models.			
Accessorie	es	Instruction man	ual, Clamping nu	ts, Toothed wash	ner					

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).

The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

^{*5.} Weight of the standard body-sized model.

E2E NEXT Series

DC 2-wire (Double distance model)

Size		M12	M	M30				
	Shielded	Shielded	Unshielded	Shielded	Shielded	Unshielded		
Item	Model	E2E-X4D□	E2E-X8D□	E2E-X16MD□	E2E-X15D□	E2E-X30MD□		
Sensing distance	e	4 mm ±10%	8 mm ±10%	16 mm ±10%	15 mm ±10%	30 mm ±10%		
Setting distance	e *1	0 to 3.2 mm	0 to 6.4 mm	0 to 12.8 mm	0 to 12 mm	0 to 24 mm		
Differential trave	el	15% max. of sensing d	istance	ı	1	•		
Detectable obje	ct	Ferrous metal (The ser	nsing distance decrease	s with non-ferrous metal	. Refer to Engineering D	Pata on page 80.)		
Standard sensir	ng object	Iron, 12 x 12 x 1 mm	Iron, 18 x 18 x 1 mm	Iron, 45 × 45 × 1 mm	Iron, 30 × 30 × 1 mm	Iron, 70 × 70 × 1 mm		
Response frequ	ency *2	1 kHz	0.5 kHz	0.4 kHz	0.25 kHz	0.1 kHz		
Power supply ve	oltage	12 to 24 VDC (including	g 10% ripple (p-p)), Clas	ss 2				
Leakage curren	t	0.8 mA max.						
Control output	Load current	3 to 100 mA						
Control output	Residual voltage	5 V max. (Load current	:: 100 mA, Cable length:	2 m)				
Indicator		D1 Models: Operation D2 Models: Operation	indicator (orange), Settir indicator (orange)	ng indicator (green)				
Operation mode	•	D1 Models: NO Ref	er to the timing charts u	nder I/O Circuit Diagram	s on page 82 for details			
Protection circu	its	Surge suppressor, Load short-circuit protection						
Ambient temper	ature range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)						
Ambient humidi	ty range	Operating and Storage: 35% to 95% (with no condensation)						
Temperature inf	luence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C						
Voltage influence	e	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resist	tance	$50~\text{M}\Omega$ min. (at $500~\text{VDC}$) between current-carrying parts and case						
Dielectric streng	gth	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case						
Vibration resista	ance (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistance	ce (destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions						
Degree of prote	ction	Pre-wired Models/Pre-wired Connector Models: IP67 (IEC 60529), IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35°C max.) and ISO 20653 (old standard: DIN 40050 PART9) IP69K						
Connecting met	hod	Pre-wired Models (Star	ndard cable length: 2 m)	, Pre-wired Connector M	lodels (Standard cable le	ength: 0.3 m)		
Weight	Pre-wired Models	Approx. 70 g	Approx. 130 g	Approx. 150 g	Approx. 180 g	Approx. 210 g		
(packed state)	Pre-wired Connector Models	Approx. 40 g	Approx. 70 g	Approx. 90 g	Approx. 110 g	Approx. 140 g		
	Case	Nickel-plated brass						
	Sensing surface	Polybutylene terephthalate (PBT)						
Materials	Clamping nuts	Nickel-plated brass						
	Toothed washer	Zinc-plated iron						
	Cable	Vinyl chloride (PVC)						
Accessories		Instruction manual, Cla	imping nuts, Toothed wa	sher				

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. 2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

DC 2-wire (Single distance model)

	Size	M8	M12	M18			
	Shielded		Shielded				
Item	Model	E2E-X1R5D□	E2E-X2R5D□	E2E-X5D□			
Sensing distance)	1.5 mm ±10%	2.5 mm ±10%	5 mm ±10%			
Setting distance	*1	0 to 1.2 mm	0 to 2 mm	0 to 4 mm			
Differential trave	l	10% max. of sensing distance		-			
Detectable objec	t	Ferrous metal (The sensing distance of	decreases with non-ferrous metal. Refe	r to Engineering Data on page 80.)			
Standard sensing	g object	Iron, 10 × 10 × 1 mm	Iron, 12 x 12 x 1 mm	Iron, 18 × 18 × 1 mm			
Response freque	ency *2	250 Hz	250 Hz	250 Hz			
Power supply vo	Itage	10 to 30 VDC, (including 10% ripple (p	p-p))				
Leakage current		0.8 mA max.					
	Load current	3 to 100 mA					
Control output	Residual voltage	Polarity: 3 V max. (Load current: 100 n No polarity: 5 V max. (Load current: 10					
Indicator		D1 Models: Operation indicator (orang D2 Models: Operation indicator (orang					
Operation mode		D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 82 for details.					
Protection circui	ts	Surge suppressor, Load short-circuit protection					
Ambient tempera	ture range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)					
Ambient humidit	y range	Operating and Storage: 35% to 95% (with no condensation)					
Temperature infl	uence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C					
Voltage influence	•	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range					
Insulation resista	ance	$50~\text{M}\Omega$ min. (at $500~\text{VDC}$) between current-carrying parts and case					
Dielectric streng	th	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case					
Vibration resista	nce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions					
Shock resistance	e (destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions					
Degree of protec	tion	Pre-wired Models/Pre-wired Connector Models: IP67 (IEC 60529), IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000 Temperature: 35°C max.) and ISO 20653 (old standard: DIN 40050 PART9) IP69K					
Connecting meth	od	Pre-wired Models (Standard cable len	gth: 2 m) and Pre-wired Connector Mod	dels (Standard cable length: 0.3 m)			
Waight	Pre-wired Models	Approx. 60 g	Approx. 70 g	Approx. 130 g			
Weight (packed state)	Pre-wired Connector Models	Approx. 30 g	Approx. 40 g	Approx. 70 g			
	Case	Stainless steel (SUS303)	Nickel-plated brass				
	Sensing surface	Polybutylene terephthalate (PBT)	•				
Materials	Clamping nuts	Nickel-plated brass					
	Toothed washer	Zinc-plated iron					
	Cable	Vinyl chloride (PVC)					
Accessories		Instruction manual, Clamping nuts, To	othed washer				

*1. Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

3. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).
The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard.

^{*4.} The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

2-year oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value).


The Pre-wired Connector Model verifies 2 years of oil resistance when mating with Round Oil-resistant Connectors XS5 NEXT series correctly. The degree of protection is not satisfied with the part where cable wires are uncovered for the Pre-wired Models.

E2E NEXT Series


Engineering Data (Reference Value)

Sensing Area

Standard model Shielded



Double distance model Shielded




Influence of Sensing Object Size and Materials

Standard model


Shielded

Size: M8 E2E-X2D□




Unshielded


Size: M8 E2E-X4MD□




Unshielded




Unshielded




Size: M12 E2E-X3D□




Size: M12 E2E-X8MD□




Single distance model Shielded




Size: M18 E2E-X7D□




Size: M18 E2E-X14MD□



Size: M30 E2E-X10D□



Size: M30 E2E-X20MD□




Influence of Sensing Object Size and Materials

Double distance model


Shielded

Size: M12 E2E-X4D□




Unshielded

Size: M18 E2E-X16MD□




Single distance model Shielded

Size: M8 E2E-X1R5D□




Standard/Double distance/ Single distance model Shielded/Unshielded E2E-X□(M)D□(-T)


Leakage Current




Size: M18 E2E-X8D□



Size: M30 E2E-X30MD□




Size: M12 E2E-X2R5D□




Residual Output Voltage


Standard/Double distance/ Single distance model Shielded/Unshielded E2E-X□(M)D□(-T)



Size: M30 E2E-X15D□



Size: M18 E2E-X5D□




81

E2E NEXT Series

I/O Circuit Diagrams

DC 2-wire (Standard/Double distance/Single distance model)



Note: For the Pre-wired Connector Models, the core wire color and pin number are different.

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector
-M1/M1G -M1T□□ (2 4) 3	-M3G

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

♠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion.


Do not connect sensor to AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in an environment where flammable or explosive gas is present.
- 2. Do not attempt to disassemble, repair, or modify the product.
- Do not use a voltage that exceeds the rated operating voltage range. Applying a voltage that is higher than the operating voltage range may result in damage or burnout.
- **4.** Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or burnout.
- If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.



Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.


Operating Environment

- Do not install the product in the following locations.
 Doing so may result in product failure or malfunction.
 - Outdoor locations directly subject to sunlight, rain, snow, water droplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, in particular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.


AND Connection of Proximity Sensors

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.

When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



Shielded


(Unit: mm)

Туре	Size	Model	L	d	D	m	n
	M8	E2E-X2D□	0	8	0	4.5	12
Standard	M12	E2E-X3D□	0	12	0	8	18
model	M18	E2E-X7D□	0	18	0	20	27
	M30	E2E-X10D□	0	30	0	40	45
	M12	E2E-X4D□	0	18	0	12	18
Double distance model	M18	E2E-X8D□	0	27	0	24	27
alotarioo moaor	M30	E2E-X15D□	0	45	0	45	45
Circula diatana	M8	E2E-X1R5D□	0	8	0	4.5	12
Single distance model	M12	E2E-X2R5D□	0	12	0	8	18
	M18	E2E-X5D□	0	18	0	20	27

Unshielded

Туре	Size	Model	L	d	D	m	n
	M8	E2E-X4MD□	9	24	9	8	24
Standard	M12	E2E-X8MD□	11	40	11	20	40
model	M18	E2E-X14MD□	18	55	18	40	54
	M30	E2E-X20MD□	25	90	25	70	90
Double	M18	E2E-X16MD□	21	70	21	48	70
distance model	M30	E2E-X30MD□	40	120	40	90	120

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)


Silielueu							
Туре	Size	Model	I	d	D	m	n
	M8	E2E-X2D□	0	8	0	4.5	12
Standard	M12	E2E-X3D□	0	12	0	8	18
model	M18	E2E-X7D□	0	18	0	20	27
	M30	E2E-X10D□	0	30	0	40	45
	M12	E2E-X4D□	2.4	18	2.4	12	18
Double distance model	M18	E2E-X8D□	3.6	27	3.6	24	27
4.0.4	M30	E2E-X15D□	6	45	6	45	45
0'	M8	E2E-X1R5D□	0	8	0	4.5	12
Single distance model	M12	E2E-X2R5D□	0	12	0	8	18
	M18	E2E-X5D□	0	18	0	20	27

Unshielded

ooo.aoa							
Туре	Size	Model	ı	d	D	m	n
	M8	E2E-X4MD□	12	24	12	8	24
Standard	M12	E2E-X8MD□	15	40	15	20	40
model	M18	E2E-X14MD□	22	55	22	40	54
	M30	E2E-X20MD□	30	90	30	70	90
Double	M18	E2E-X16MD□	25	70	25	48	70
distance model	M30	E2E-X30MD□	45	120	45	90	120

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.



Shielded

(Unit: mm)

Type	Size	Model	Α	В
	M8	E2E-X2D□	20	15
Standard model	M12	E2E-X3D□	30(20)	20(12)
Standard model	M18	E2E-X7D□	50(30)	35(18)
	M30	E2E-X10D□	100(50)	70(35)
	M12	E2E-X4D□	30	20
Double distance model	M18	E2E-X8D□	60	35
	M30	E2E-X15D□	110	90
Single distance model	M8	E2E-X1R5D□	20	15
	M12	E2E-X2R5D□	30	20
mouoi	M18	E2E-X5D□	50	35

Unshielded

Туре	Size	Model	Α	В
	M8	E2E-X4MD□	80	60
Standard model	M12	E2E-X8MD□	120(60)	100(50)
Standard model	M18	E2E-X14MD□	200(100)	110(60)
	M30	E2E-X20MD□	300(100)	200(100)
Double distance	M18	E2E-X16MD□	200	120
model	M30	E2E-X30MD□	350	300

Note: 1. Values in parentheses apply to Sensors operating at different frequencies.

The values of mutual interference are provided for reference. Test the sensors on the actual machine or contact your OMRON sales representative to validate that there is no interference.

Mounting

Tightening Force

Do not tighten the sensor mounting nuts with excessive force. Secure the mounting nuts to the corresponding torque values in the following table.







Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table.

(A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

Standard/Double distance model

	Model	Part A		Part B
	Wiodei	Dimension (mm)	Torque	Torque
M8	Shielded	9	9 N·m	12 N⋅m
IVIO	Unshielded	3	3 11.111	12 11.111
M12			30 N·m	
M18		70 N⋅m		V-m
M30		180 N⋅m		N∙m

Single distance model

Onigio diotarios moder				
Model	Par	rt A	Part B	
Wodel	Dimension (mm)	Torque	Torque	
M8	9	9 N⋅m	12 N⋅m	
M12			V-m	
M18	70 N		V·m	

Dimensions

Tolerance class 11 to applies to dimensions in this data sheet diffess otherwise specific

Sensor

DC 2-wire (Standard/Double distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)





Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.


Pre-wired Models Pre-wired Connector Models (Unshielded)





Note: Refer to the figure below the table for the connections of the Pre-wired Connector Model.





















*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

\rightarrow		
\rightarrow	Dimensions	F (mm)
4	M8	8.5 dia. +0.5
- F - - -1	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	18	


Wire pullout position



	-	
- N	Dimensions	Sc (mm)
"	M8	(0)
	M12	- (0)
	M18	2.5
	M30	2.5


Sensor

DC 2-wire (Long-body Standard/Double distance model)



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Mounting Hole Dimensions



Angle R of the Bending Wire

10 mm	
	-

Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	

Wire pullout position



;		
-	Dimensions	Sc (mm)
7	M8	(0)
•	M12	- (0)
	M18	2.5
	M30	2.5

Toothed washe

Two clamping nuts

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Sensor

DC 2-wire (Standard model)


M12 Connector Models (Shielded)




M12 Connector Models (Unshielded)




E2E-X2D -M1/-M1G




E2E-X4MD -M1/-M1G




E2E-X3D□-M1/-M1G




E2E-X8MD -M1/-M1G




E2E-X7D -M1/-M1G




E2E-X14MD -M1/-M1G



E2E-X10D .- M1/-M1G




E2E-X20MD□-M1/-M1G



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Mounting Hole Dimensions



Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

E2E NEXT Series

Sensor

DC 2-wire (Standard model)


M8 Connector Models (Shielded)




M8 Connector Models (Unshielded)










DC 2-wire (Single distance model)

Pre-wired Models Pre-wired Connector Models (Shielded)




Note: 1. Refer to the figure below the table for the connections of the Pre-wired Connector Model.


E2E-X1R5D



4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m




4-dia. vinyl-insulated round cable with 2 conductors (Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm), Standard length: 2 m



*1. D1 Models: Operation indicator (Orange), Setting indicator (Green)/ D2 Models: Operation indicator (Orange)

Pre-wired Connector Models (-M1TGJ)



Note: Refer to the Pre-wired Model for the cable specifications of the Pre-wired Connector Model.

Mounting Hole Dimensions

(Dimensions	F (mm)
<u> </u>	M8	8.5 dia. +0.5
- F -	M12	12.5 dia. +0.5
	M18	18.5 dia. +0.5
	M30	30.5 dia. +0.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Angle R of the Bending Wire



Dimensions	R (mm)	
M8	12	
M12	12	
M18	18	
M30	10	

Wire pullout position



١	Dimensions	Sc (mm)
1	M8	(0)
	M12	- (0)
	M18	2.5
	M30	2.5

Proximity Sensor E2EQ NEXT Series

DC 3-wire/DC 2-wire

Enables easier and standardized designs previously not possible with fluororesin coating models

- Nearly double*1 the sensing distance of previous
- With high-brightness LED, the indicator is visible anywhere from 360°
- Comes in a wide variation to make sensor selection easy
- UL certification (UL60947-5-2)*2 and CSA certification (CSA C22.2 UL60947-5-2-14)
- Comparison with E2EQ products. Based on September 2021 OMRON investigation.
- *2. M8 (4-pin) Connector Models are not UL certified.



Be sure to read Safety Precautions on page 104.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

E2EQ NEXT Series Model Number Legend

E2EQ - X (1) (2) (3) (4) (5) (6) - (7) - (8) (9)

No.	Туре	Code	Meaning	Remarks
(1)	Sensing distance	Number	Sensing distance (Unit: mm) (R: Indication of decimal point)	
		В	PNP open collector	Whether the D mode
(2)	Output configuration	С	NPN open collector	has polarity is defined
		D	DC 2-wire polarity/no polarity	by number (7).
		1	Normally open (NO)	
(3)	Operation mode	2	Normally closed (NC)	
		3	Normally open, Normally closed (NO+NC)	
		Blank	Non IO-Link compliant	
(4)	IO-Link baud rate	D	COM2 (38.4 kbps)	
		Т	COM3 (230.4 kbps)	
		8	M8	
(5)	Size	12	M12	
(5)	Size	18	M18	
		30	M30	
		Blank	Pre-wired Models	
		M1	M12 Connector Models	
		M3	M8 (4-pin) Connector Models	
		M5	M8 (3-pin) Connector Models	
		M1GJ	M12 Pre-wired Standard Connector Models DC 2-wire	
(6)	Connection method	M1TGJ	M12 Pre-wired Smartclick Connector Models DC 2-wire	
		M1TGJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable DC 2-wire	
		M1TJ	M12 Pre-wired Smartclick Connector Models DC 3-wire	
	M1TJR	M12 Pre-wired Smartclick Connector Models Robot (bending-resistant) cable DC 3-wire		
(7) DC 2-wire polarity	DC 0ina nalanitu	Blank	Polarity	
	Т	No polarity		
(0)	Coble enseification - *4	Blank	Standard PVC cable	
(8)	Cable specifications *1	R	Robot (bending-resistant) cable	
(9)	Cable length	Number M	Cable length	

^{*1. (8)} is only shown in the model number of Pre-wired Models.

Note: The purpose of this model number legend is to provide understanding of the meaning of specifications from the model number.

E2EQ NEXT Series

Ordering Information

Sensors

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 3-wire Shielded [Refer to Ratings and Specification on page 93, Dimension on page 106.]

Size (Sensing	Connection method *2	Dody size	Operation	Mo	del	
distance)	Connection method 2	Body size	mode *3	PNP	NPN	
M8	Pre-wired (2 m) *1	38 mm	NO	E2EQ-X2B1D8 2M	E2EQ-X2C18 2M	
(2 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X2B1D8-M1TJ 0.3M	E2EQ-X2C18-M1TJ 0.3M	
	Pre-wired (2 m) *1	47 mm	NO	E2EQ-X4B1D12 2M	E2EQ-X4C112 2M	
M12	Fre-wired (2 iii)	47 111111	NO+NC	E2EQ-X4B3D12 2M	E2EQ-X4C312 2M	
(4 mm)	M12 Pre-wired	47	NO	E2EQ-X4B1D12-M1TJ 0.3M	E2EQ-X4C112-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	47 mm	NO+NC	E2EQ-X4B3D12-M1TJ 0.3M	E2EQ-X4C312-M1TJ 0.3M	
	Dro wired (2 m) *4	FF	NO	E2EQ-X8B1D18 2M	E2EQ-X8C118 2M	
M18	Pre-wired (2 m) *1		55 mm	NO+NC	E2EQ-X8B3D18 2M	E2EQ-X8C318 2M
(8 mm)	M12 Pre-wired	55 mm	NO	E2EQ-X8B1D18-M1TJ 0.3M	E2EQ-X8C118-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	55 111111	NO+NC	E2EQ-X8B3D18-M1TJ 0.3M	E2EQ-X8C318-M1TJ 0.3M	
		e-wired (2 m) *1 60 mm	NO	E2EQ-X15B1D30 2M	E2EQ-X15C130 2M	
M30	Pre-wired (2 III) "T		NO+NC	E2EQ-X15B3D30 2M	E2EQ-X15C330 2M	
(15 mm)	M12 Pre-wired	60	NO	E2EQ-X15B1D30-M1TJ 0.3M	E2EQ-X15C130-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	60 mm	NO+NC	E2EQ-X15B3D30-M1TJ 0.3M	E2EQ-X15C330-M1TJ 0.3M	

BASIC Model

E2EQ NEXT Series (Spatter-resistant Single distance model)

DC 3-wire Shielded [Refer to Ratings and Specification on page 93, Dimension on page 106.]

Size (Sensing	Connection method *2	Pody size	Operation	Мо	del	
distance)	Connection method 2	Body size	mode *3	PNP	NPN	
M8	Pre-wired (2 m) *1	38 mm	NO	E2EQ-X1R5B1D8 2M	E2EQ-X1R5C18 2M	
(1.5 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X1R5B1D8-M1TJ 0.3M	E2EQ-X1R5C18-M1TJ 0.3M	
	Dro wired (2 m) *4	47 mm	NO	E2EQ-X2B1D12 2M	E2EQ-X2C112 2M	
M12	Pre-wired (2 m) *1	47 11111	NO+NC	E2EQ-X2B3D12 2M	E2EQ-X2C312 2M	
(2 mm)	M12 Pre-wired	47	NO	E2EQ-X2B1D12-M1TJ 0.3M	E2EQ-X2C112-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	47 mm	NO+NC	E2EQ-X2B3D12-M1TJ 0.3M	E2EQ-X2C312-M1TJ 0.3M	
	Dro wired (2 m) *4	FF	NO	E2EQ-X5B1D18 2M	E2EQ-X5C118 2M	
M18	Pre-wired (2 m) *1	55 mm	NO+NC	E2EQ-X5B3D18 2M	E2EQ-X5C318 2M	
(5 mm)	M12 Pre-wired	<i></i>	NO	E2EQ-X5B1D18-M1TJ 0.3M	E2EQ-X5C118-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	55 mm	NO+NC	E2EQ-X5B3D18-M1TJ 0.3M	E2EQ-X5C318-M1TJ 0.3M	
		CO	NO	E2EQ-X10B1D30 2M	E2EQ-X10C130 2M	
M30	Pre-wired (2 m) *1	-wired (2 m) *1 60 mm	NO+NC	E2EQ-X10B3D30 2M	E2EQ-X10C330 2M	
(10 mm)	M12 Pre-wired	CO	NO	E2EQ-X10B1D30-M1TJ 0.3M	E2EQ-X10C130-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	60 mm	NO+NC	E2EQ-X10B3D30-M1TJ 0.3M	E2EQ-X10C330-M1TJ 0.3M	

^{*1.} Models with 5-m cable length are also available (Example: E2EQ-X6B1D12 5M)

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□T□" (Example: E2EQ-X6B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

^{*2.} M12 Connector Models are also available with "M1" suffix. (Example: E2EQ-X2B1D8-M1)

^{*3.} NC models are also available. The model number is E2EQ-X\(\to\)\(\to\)\(\to\)\(\to\)\(\text{(Example: E2EQ-X3\text{B28 2M})}.

^{2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

Sensors

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 2-wire Shielded [Refer to Ratings and Specification on page 94, Dimension on page 106.]

Size	size Connection method Polarity		Model	
(Sensing distance)	Connection method	Polarity	Operation mode: NO	
M12	Pre-wired (2 m) *1		E2EQ-X4D112-T 2M	
(4 mm)	M12 Pre-wired Smartclick Connector (0.3 m)		E2EQ-X4D112-M1TGJ-T 0.3M	
M18	M18 Pre-wired (2 m) *1	NO	E2EQ-X8D118-T 2M	
(8 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	NO	E2EQ-X8D118-M1TGJ-T 0.3M	
M30	Pre-wired (2 m) *1		E2EQ-X15D130-T 2M	
(15 mm)	M12 Pre-wired Smartclick Connector (0.3 m)		E2EQ-X15D130-M1TGJ-T 0.3M	

^{*1.} Models with 5-m cable length are also available (Example: E2EQ-X4D112-T 5M).

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 3-wire Shielded *1 [Refer to Ratings and Specification on page 95, Dimension on page 107.]

Size (Sensing	Connection method *3	Dady size	Operation	Model		
distance)	Connection method 3	Body size	mode *4	PNP	NPN	
M8	Pre-wired (2 m) *2	38 mm	NO	E2EQ-X3B1D8 2M	E2EQ-X3C18 2M	
(3 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	38 mm	NO	E2EQ-X3B1D8-M1TJ 0.3M	E2EQ-X3C18-M1TJ 0.3M	
	Dre wired (2 m) *2	47	NO	E2EQ-X6B1D12 2M	E2EQ-X6C112 2M	
M12	Pre-wired (2 m) *2	47 mm	NO+NC	E2EQ-X6B3D12 2M	E2EQ-X6C312 2M	
(6 mm) M12 Pre-wired Smartclick Connector (0.3 m)	M12 Pre-wired	47	NO	E2EQ-X6B1D12-M1TJ 0.3M	E2EQ-X6C112-M1TJ 0.3M	
	47 mm	NO+NC	E2EQ-X6B3D12-M1TJ 0.3M	E2EQ-X6C312-M1TJ 0.3M		
	Dec	FF	NO	E2EQ-X12B1D18 2M	E2EQ-X12C118 2M	
M18	Pre-wired (2 m) *2	2 m) *2 55 mm	NO+NC	E2EQ-X12B3D18 2M	E2EQ-X12C318 2M	
(12 mm)	M12 Pre-wired	55	NO	E2EQ-X12B1D18-M1TJ 0.3M	E2EQ-X12C118-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	55 mm	NO+NC	E2EQ-X12B3D18-M1TJ 0.3M	E2EQ-X12C318-M1TJ 0.3M	
	Dec		NO	E2EQ-X22B1D30 2M	E2EQ-X22C130 2M	
M30 Pre-wired (2 m) *2	60 mm	NO+NC	E2EQ-X22B3D30 2M	E2EQ-X22C330 2M		
(22 mm)	M12 Pre-wired	00	NO	E2EQ-X22B1D30-M1TJ 0.3M	E2EQ-X22C130-M1TJ 0.3M	
	Smartclick Connector (0.3 m)	60 m	60 mm	NO+NC	E2EQ-X22B3D30-M1TJ 0.3M	E2EQ-X22C330-M1TJ 0.3M

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 105.

Note: 1. Models in _____ are equipped with IO-Link (COM2). For IO-Link (COM3), select a model number with the format of "E2E-X□□□T□" (Example: E2EQ-X6B1T12 2M).

Operation mode NO can be changed to NC via IO-Link communications.

2. IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 2-wire Shielded *1 [Refer to Ratings and Specification on page 96, Dimension on page 107.]

Size	0	Dalasita	N	lodel
(Sensing distance)	Connection method	Polarity	Operation mode: NO	Operation mode: NC
	Deci d (0) *0	Yes	E2EQ-X3D18 2M	E2EQ-X3D28 2M
M8	Pre-wired (2 m) *2	No	E2EQ-X3D18-T 2M	E2EQ-X3D28-T 2M
(3 mm)	M12 Pre-wired	Yes	E2EQ-X3D18-M1TGJ 0.3M	E2EQ-X3D28-M1TGJ 0.3M
	Smartclick Connector (0.3 m)	No	E2EQ-X3D18-M1TGJ-T 0.3M	E2EQ-X3D28-M1TGJ-T 0.3M
Pre-wired (2 m) *2	Dro wired (2 m) *2	Yes	E2EQ-X7D112 2M	E2EQ-X7D212 2M
	Pre-wired (2 m) *2	No	E2EQ-X7D112-T 2M	E2EQ-X7D212-T 2M
(7 mm)	M12 Pre-wired Smartclick Connector (0.3 m)	Yes	E2EQ-X7D112-M1TGJ 0.3M	E2EQ-X7D212-M1TGJ 0.3M
		No	E2EQ-X7D112-M1TGJ-T 0.3M	E2EQ-X7D212-M1TGJ-T 0.3M
	D : 1/0) to	Yes	E2EQ-X11D118 2M	E2EQ-X11D218 2M
M18	Pre-wired (2 m) *2	No	E2EQ-X11D118-T 2M	E2EQ-X11D218-T 2M
(11 mm)	M12 Pre-wired	Yes	E2EQ-X11D118-M1TGJ 0.3M	E2EQ-X11D218-M1TGJ 0.3M
	Smartclick Connector (0.3 m)	No	E2EQ-X11D118-M1TGJ-T 0.3M	E2EQ-X11D218-M1TGJ-T 0.3M
	Dec. wire d (0 m) *0	Yes	E2EQ-X20D130 2M	E2EQ-X20D230 2M
M30	Pre-wired (2 m) *2	No	E2EQ-X20D130-T 2M	E2EQ-X20D230-T 2M
(20 mm)	M12 Pre-wired	Yes	E2EQ-X20D130-M1TGJ 0.3M	E2EQ-X20D230-M1TGJ 0.3M
	Smartclick Connector (0.3 m)	No	E2EQ-X20D130-M1TGJ-T 0.3M	E2EQ-X20D230-M1TGJ-T 0.3M

^{*1.} When embedding the Proximity Sensor in metal, refer to Influence of Surrounding Metal on page 105.

Sensor I/O Connectors (Sold Separately)

For details of the connector, refer to XS5 Series on page 111.

^{*2.} Models with 5-m cable length are also available (Example: E2EQ-X6B1D12 5M)

^{*3.} M12 Connector Models are also available with "M1" suffix. (Example: E2EQ-X3B1D8-M1).

^{*4.} NC models are also available. The model number is E2EQ-□□2□ (Example: E2EQ-X3B28 2M).

^{*2.} Models with 5-m cable length are also available with "5M" suffix. (Example: E2EQ-X3D18 5M)

Ratings and Specifications

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance/Single distance model)

DC 3-wire Shielded

	Types Double distance Models Single distance Models								
	Size	M8	M12	M18	M30	M8	M12	M18	M30
Item	Model	E2EQ-X2□8	E2EQ-X4□12	E2EQ-X8□18	E2EQ-X15□30	E2EQ-X1R5□8	E2EQ-X2□12	E2EQ-X5□18	E2EQ-X10□30
Sensing di	istance	2 mm±10%	4 mm±10%	8 mm±10%	15 mm±10%	1.5 mm±10%	2 mm±10%	5 mm±10%	10 mm±10%
Setting dis	stance	0 to 1.6 mm	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm	0 to 1.2 mm	0 to 1.6 mm	0 to 4 mm	0 to 8 mm
Differentia	l travel	15% max. of sensing distance 10% max. of sensing distance							
Detectable	object	Ferrous metals	(For non-ferrous	metals, refer to	the Engineering	Data on page 97	.)		
Standard so	ensing object (Iron)	8 × 8 × 1 mm	12 x 12 x 1 mm	24 × 24 × 1 mm	45 × 45 × 1 mm	8 × 8 × 1 mm	12 x 12 x 1 mm	18 x 18 x 1 mm	30 × 30 × 1 mm
Response	frequency *1	1,500 Hz	1,000 Hz	500 Hz	250 Hz	2,000 Hz	1,500 Hz	600 Hz	400 Hz
Power sup	ply voltage	10 to 30 VDC (i	ncluding 10% rip	ple (p-p)), Class	2				
Current co	nsumption	1-output models	s: 16 mA max., 2	-output models:	20 mA max.				
Output cor	nfiguration	B□ Models: PN	P open collector	, C□ Models: NF	PN open collector	r			
	mode (with oject approaching)				1-output models en, Normally clos		ormally closed)		
M8 size 1-output models: 10 to 30 VDC, Class 2, 200 mA max., (-40 to 70°C), 100 mA max., (70 to 85°C) 2-output models: 10 to 30 VDC, Class 2, 50 mA max. M12, M18, M30 size 1-output models: 10 to 30 VDC, Class 2, 200 mA max., 2-output models: 10 to 30 VDC, Class 2, 100 mA max.									
output	Residual voltage	M12, M18, M30	size	ŕ	Cable length: 2 m)		,	•	,
In the Standard I/O mode (SIO mode): Operation indicator (orange, lit) and communication indicator (green, not In the IO-Link communication mode (COM mode): Operation indicator (orange, lit) and communication indicator (1 s intervals)									
Protection	circuits	Power supply reverse polarity protection, Surge suppressor, Output short-circuit protection, Output reverse polarity protection							
Ambient te	emperature range	Operating/Storage: -40 to 85°C (with no icing or condensation) Note: The UL temperature rating for M12 Pre-wired Connector Models is -25 to 70°C.							
Ambient h	umidity range	Operating/Storage: 35% to 95% (with no condensation)							
Temperatu	re influence	±15% max. of sensing distance at 23°C in the temperature range of -40 to 85°C ±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C							
Voltage inf	fluence	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range							
Insulation	resistance	50 MΩ min. (at 500 VDC) between current-carrying parts and case							
Dielectric s	strength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case							
Vibration re (destruction)		10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions							
Shock resi (destructio		M8 size: 500 m/s² 10 times each in X, Y, and Z directions/M12, M18, M30 size: 1,000 m/s² 10 times each in X, Y, and Z directions							
Degree of	protection	Pre-wired Mode	ls, Pre-wired Co	nnector Models:	IEC 60529:IP67,	JIS C 0920 Anne	x 1: IP67G *4/Cc	onnector Models:	IEC 60529 IP67
Connection	n method	Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 0.3 m), M12 Connector Models							
	Pre-wired	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g	Approx. 85 g	Approx. 95 g	Approx. 170 g	Approx. 240 g
Weight *3 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g	Approx. 55 g	Approx. 70 g	Approx. 105 g	Approx. 170 g
	Connector	Approx. 40 g	Approx. 55 g	Approx. 85 g	Approx. 160 g	Approx. 40 g	Approx. 55 g	Approx. 85 g	Approx. 160 g
	Case	M8 size: Fluoro	resin coating (Ba	ase material: SU	S303)/M12, M18	, M30 size: Fluor	oresin coating (E	Base material: br	ass)
	Sensing surface	Fluorine resin							
Materials	Clamping nuts	Fluororesin coa	ting (Base mater	ial: brass)					
	Toothed washers	Zinc-plated iron							
	Cable	Vinyl chloride (F	PVC) Note: Ma	terial of Pre-wire	ed Models and Pr	e-wired Connect	or Models.		
Main IO-Lii	nk functions *2	Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function, monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset							
IO-Link	IO-Link specification	Ver1.1							
Commun	Baud rate	COM2 (38.4 kb	ps), COM3 (230.	4 kbps)					
ication specifica	Data length	PD size: 2 byte	s, OD size: 1 byt	e (M-sequence t	ype: TYPE_2_2)				
tions *2	Minimum cycle time	COM2: 2.3 ms,	COM3: 0.4 ms						
Accessorie	es	Instruction man	ual, Clamping nu	ıts, Toothed was	her				
1. The res	sponse frequency i	s an average v	alue. Measure	ment condition	s are as follows	s: standard sen	sing object, a	distance of twic	e the standard

The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*3.} Weight of the standard body-sized model.

^{*4.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

E2EQ NEXT Series

BASIC Model

E2EQ NEXT Series (Spatter-resistant Double distance model)

DC 2-wire Shielded

	Size	M12	M18	M30				
Item	Model	E2EQ-X4D□12	E2EQ-X8D□18	E2EQ-X15D□30				
Sensing distant	ce	4 mm ±10%	8 mm ±10%	15 mm ±10%				
Setting distance	e *1	0 to 3.2 mm	0 to 6.4 mm	0 to 12 mm				
Differential trav	el	15% max. of sensing distance	15% max. of sensing distance					
Detectable obje	ct	Ferrous metals (For non-ferrous meta	ls, refer to Engineering Data on page 9	7.)				
Standard sensi	ng object (Iron)	12 × 12 × 1 mm	18 × 18 × 1 mm	30 × 30 × 1 mm				
Response frequ	ency *2	1,000 Hz	500 Hz	250 Hz				
Power supply v	oltage	10 to 30 VDC (including 10% ripple (p	-p)), Class 2					
Current consun	nption	0.8 mA max.						
Cantral autment	Load current	3 to 100 mA						
Control output	Residual voltage	5 V max. (Load current: 100 mA, Cabl	e length: 2 m)					
Indicator		Operation indicator (orange), Setting i	ndicator (green)					
Operation mode)	NO Refer to the timing charts under I/O Circuit Diagrams/Timing charts on page 103 for details.						
Protection circu	iits	Surge suppressor, Load short-circuit protection						
Ambient tempe	rature range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)						
Ambient humid	ity range	Operating and Storage: 35% to 95% (with no condensation)						
Temperature in	fluence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C						
Voltage influend	ce	±1% max. of sensing distance at rated voltage in the rated voltage ±15% range						
Insulation resis	tance	50 M Ω min. (at 500 VDC) between cu	rrent-carrying parts and case	nt-carrying parts and case				
Dielectric stren	gth	1,000 VAC, 50/60 Hz for 1 minute bet	ween current-carrying parts and case					
Vibration resist	ance (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions						
Shock resistand	ce (destruction)	1,000 m/s² 10 times each in X, Y, and Z directions						
Degree of prote	ction	Pre-wired Models, Pre-wired Connected	or Models: IEC 60529:IP67, JIS C 0920	Annex 1: IP67G				
Connection me	thod	Pre-wired Models (Standard cable length: 2 m) and M12 Pre-wired Smartclick Connector Models (Standard cable length: 0.3 m)						
Weight	Pre-wired	Approx. 100 g	Approx. 180 g	Approx. 250 g				
(packed state)	M12 Pre-wired Smartclick Connector	Approx. 75 g	Approx. 110 g	Approx. 180 g				
	Materials	Fluororesin coating (Base material: br	ass)					
	Sensing surface	Fluororesin						
Materials	Clamping nuts	Fluororesin coating (Base material: brass)						
	Toothed washer	Zinc-plated iron						
	Cable	Vinyl chloride (PVC)						
Accessories		Instruction manual, Clamping nuts, To	othed washer					

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON.

^{*2.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 3-wire Shielded

	Size	M8	M12	M18	M30		
Item	Model	E2EQ-X3□8	E2EQ-X6□12	E2EQ-X12□18	E2EQ-X22□30		
Sensing dis	tance	3 mm±10%	6 mm±10%	12 mm±10%	22 mm±10%		
Setting dista	ance	0 to 2.4 mm					
Differential t		15% max. of sensing distance					
Detectable of	object	Ferrous metals (For non-ferrou	s metals, refer to the Engineering	ng Data on page 97.)			
Standard se	ensing object (Iron)	9 x 9 x 1 mm	18 × 18 × 1 mm	36 × 36 × 1 mm	66 x 66 x 1 mm		
Response fr	requency *1	1,000 Hz	800 Hz	500 Hz	200 Hz		
Power supp	ly voltage	10 to 30 VDC (including 10% ri	pple (p-p)), Class 2				
Current con	sumption	1-output models: 16 mA max.	1-output models: 16 mA max.,	2-output models: 20 mA max.			
Output conf	iguration	B□ Models: PNP open collecto	r, C Models: NPN open collect	tor			
(with sensing object 1 output models (R2 C2):			1-output models (B1, C1): NO 1-output models (B2, C2): NC 2-output models (B3, C3): NO-		closed)		
Control	Load current	1-output models: 10 to 30 VDC, Class 2, 100 mA max.	1-output models: 10 to 30 VDC 2-output models: 10 to 30 VDC				
output	Residual voltage	1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m), 1-output models: 2 V max. (Load current: 100 mA, Cable length: 2 m), 2-output models: 2 V max. (Load current: 50 mA, Cable length: 2 m)					
Indicator *2			mode): Operation indicator (ora node (COM mode): Operation ind				
Protection c	circuits	Power supply reverse polarity p	protection, Surge suppressor, Ou	utput short-circuit protection, Ou	tput reverse polarity protection		
Ambient ten	nperature range	Operating/Storage: -25 to 70°C (with no icing or condensation)					
Ambient humidity range		Operating/Storage: 35% to 95% (with no condensation)					
Temperature influence		±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C					
Voltage influence		±1% max. of sensing distance at rated voltage in the rated voltage ±15% range					
nsulation re	esistance	50 MΩ min. (at 500 VDC) between current-carrying parts and case					
Dielectric st	rength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case					
Vibration res	sistance (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions					
Shock resis	tance (destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions					
Degree of p	rotection	Pre-wired Models, Pre-wired Connector Models: IEC 60529: IP67, JIS C 0920 Annex 1: IP67G *4 Connector Models: IEC 60529: IP67					
Connection	method	Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 0.3 m), M12 Connector Models					
	Pre-wired Models	Approx. 85 g	Approx. 95 g	Approx. 180 g	Approx. 260 g		
Weight *3 (packed state)	M12 Pre-wired Smartclick Connector	Approx. 55 g	Approx. 70 g	Approx. 115 g	Approx. 200 g		
	Connector	Approx. 40 g	Approx. 55 g	Approx. 95 g	Approx. 180 g		
	Case	Fluororesin coating (Base mate	erial: brass)				
	Sensing surface	Fluorine resin					
Materials	Clamping nuts	Fluororesin coating (Base mate	erial: brass)				
	Toothed washers	Zinc-plated iron					
	Cable	Vinyl chloride (PVC) Note: Material of Pre-wired Models and Pre-wired Connector Models.					
Main IO-Lini	k functions *2	Operation mode switching between NO and NC, self diagnosis enabling, excessive proximity judgment distance selecting, timer function of the control output and timer time selecting, instability output (IO-Link mode) ON delay timer time selecting function, monitor output, operating hours read-out, readout of the sensor internal temperature, and initial reset					
IO-Link	IO-Link specification	Ver 1.1					
Communic	Baud rate	COM2 (38.4 kbps), COM3 (230	0.4 kbps)				
ation specificati	Data length	PD size: 2 bytes, OD size: 1 by	rte (M-sequence type: TYPE_2_	2)			
ons *2	Minimum cycle time	COM2: 2.3 ms, COM3: 0.4 ms					
Accessories	3	Instruction manual, Clamping n	uts, Toothed washer				
1. The resp	onse frequency is a	n average value. Measureme	ent conditions are as follows:	standard sensing object, a c	distance of twice the standa		

^{*1.} The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*2.} IO-Link is not supported for NC-type PNP outputs or all types of NPN outputs.

^{*3.} Weight of the standard body-sized model.

^{*4.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

E2EQ NEXT Series

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant Triple distance model)

DC 2-wire Shielded

	Size	M8	M12	M18	M30		
Item	Model	E2EQ-X3D□	E2EQ-X7D□	E2EQ-X11D□	E2EQ-X20D□		
Sensing distance		3 mm ±10%	7 mm ±10%	11 mm ±10%	20 mm ±10%		
Setting distance *	1	0 to 2.4 mm	0 to 4.9 mm	0 to 8.8 mm	0 to 16 mm		
Differential travel		15% max. of sensing distan	ce				
Detectable object		Ferrous metal (The sensing	distance decreases with nor	-ferrous metal. Refer to Eng	gineering Data on page 97.		
Standard sensing	object (Iron)	9 × 9 × 1 mm	21 × 21 × 1 mm	33 × 33 × 1 mm	60 × 60 × 1 mm		
Response frequer	ncy *2	250 Hz	250 Hz	250 Hz	200 Hz		
Power supply volt	age	10 to 30 VDC, (including 10	% ripple (p-p))				
Leakage current		0.8 mA max.					
	Load current	3 to 100 mA					
Control output	Residual voltage		rrent: 100 mA, Cable length: current: 100 mA, Cable leng				
Indicator		D1 Models: Operation indica D2 Models: Operation indica	ator (orange), Setting indicato ator (orange)	or (green)			
Operation mode		D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams/Timing charts on page 103 for details.					
Protection circuits	5	Surge suppressor, Load short-circuit protection					
Ambient temperat	ure range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)					
Ambient humidity	range	Operating and Storage: 35% to 95% (with no condensation)					
Temperature influ	ence	±10% max. of sensing distance at 23°C in the temperature range of -25 to 70°C ±20% max. of sensing distance at 23°C in the temperature range of -25 to 70°C					
Voltage influence		±1% max. of sensing distance at rated voltage in the rated voltage ±15% range					
Insulation resistar	nce	50 M Ω min. (at 500 VDC) be	etween current-carrying parts	and case			
Dielectric strength	ı	1,000 VAC, 50/60 Hz for 1 r	000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case				
Vibration resistan	ce (destruction)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions					
Shock resistance	(destruction)	500 m/s² 10 times each in X, Y, and Z directions 1,000 m/s² 10 times each in X, Y, and Z directions					
Degree of protecti	on	Pre-wired/Pre-wired M12 Connector: IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1)					
Connecting metho	od	Pre-wired (Standard cable le	ength: 2 m) and Pre-wired M	12 Connector (Standard cab	le length: 0.3 m)		
Weight	Pre-wired	Approx. 60 g	Approx. 70 g	Approx. 150 g	Approx. 210 g		
(packed state)	Pre-wired M12 Connector	Approx. 30 g	Approx. 40 g	Approx. 90 g	Approx. 140 g		
	Case	Fluororesin coating (Base m	naterial: brass)				
	Sensing surface	Fluororesin					
Materials	Clamping nuts	Fluororesin coating (Base m	naterial: brass)				
	Toothed washer	Zinc-plated iron					
	Cable	Vinyl chloride (PVC)					
		Instruction manual Clampin	ng nuts, Toothed washer				

^{*1.} Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).
*2. The response frequency is an average value. Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

^{*3.} The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

.


X X X

Engineering Data (Reference Value)


Sensing Area

BASIC Model


DC 3-wire Spatter-resistant Double distance model



DC 3-wire Spatter-resistant Single distance model




DC 2-wire Spatter-resistant Double distance model




PREMIUM Model

DC 3-wire Spatter-resistant Triple distance model




DC 2-wire Spatter-resistant Triple distance model



Leakage Current


DC 2-wire Spatter-resistant Triple distance/ Double distance model

$E2EQ-X\square D\square (-T)$



Residual Output Voltage

DC 2-wire Spatter-resistant Triple distance/ Double distance model E2EQ-X□D□(-T)




E2EQ NEXT Series

Influence of Sensing Object Size and Material


BASIC Model

DC 3-wire/2-wire Spatter-resistant Double distance model


Size: M8 E2EQ-X2□8




Size: M12 E2EQ-X4□12



Size: M18 E2EQ-X8□18




Size: M30 E2EQ-X15□30




BASIC Model

DC 3-wire Spatter-resistant Single distance model


Size: M8 E2EQ-X1R5□8




Size: M12 E2EQ-X2□12



Size: M18 E2EQ-X5□18




Size: M30 E2EQ-X10□30




PREMIUM Model

DC 3-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3□8




Size: M12 E2EQ-X6□12



Size: M18 E2EQ-X12□18




Size: M30 E2EQ-X22□30




PREMIUM Model

DC 2-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3D□8




Size: M12 E2EQ-X7D□12



Size: M18 E2EQ-X11D□18



Size: M30 E2EQ-X20D□30




Monitor Output vs. Sensing Distance


BASIC Model

DC 3-wire Spatter-resistant Double distance model


Size: M8 E2EQ-X2□8




Size: M12 E2EQ-X4□12



Size: M18 E2EQ-X8□18




Size: M30 E2EQ-X15□30




BASIC Model

DC 3-wire Spatter-resistant Single distance model


Size: M8 E2EQ-X1R5□8




Size: M12 E2EQ-X2□12



Size: M18 E2EQ-X5□18




Size: M30 E2EQ-X10□30




PREMIUM Model

DC 3-wire Spatter-resistant Triple distance model


Size: M8 E2EQ-X3□8




Size: M12 E2EQ-X6□12



Size: M18 E2EQ-X12□18



Size: M30 E2EQ-X22□30




E2EQ NEXT Series

I/O Circuit Diagrams/Timing charts

DC 3-wire

PNP output




^{*} In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less.

Connector Pin Arrangement


M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2) (4) (3)		(1 ⁽⁴⁾ (3)

DC 3-wire

PNP output



*3. The timer function of the control output can be set up by the IO-Link communications. (It is able to select ON delay, OFF delay, or one-shot function and select a timer time of 1 to 16,383ms (T).)



- *4. The excessive proximity diagnosis function can be selected by the IO-
- Link communications.
 *5. The instability detection diagnosis can be selected by the IO-Link communications.
- *6. The judgment time for the instability detection diagnosis can be selected by the IO-Link communications. (For the ON delay timer function, the setting can be selected from 0 (invalid), 10, 50, 100, 300, 500, or 1000 ms.)
- *7. The judgment distance of the excessive proximity diagnosis function can be selected by the IO-Link communications.

 (The distance can be selected as a combination of the material of the object detected, such as iron, aluminum, or SUS and the judgment distance of approximately 10, 20, or 30%. However, it is not allowed to select a combination of aluminum and 30%.)

Please contact your OMRON sales representative regarding the IO-Link setup file (IODD file).

Please contact your OMRON sales representative regarding assignment of data.

- *1. For models with IO-Link, the operation mode can be changed by the IO-Link communications.
- *2. If using a model with IO-Link as a general sensor or using a model without IO-Link, it operates in the standard I/O mode (SIO mode).

E2EQ NEXT Series


DC 3-wire

NPN output

Operation mode	Model	Output circuit
NO	E2EQ-□C1	DC10 to 30V Brown (1) +V Load Proximity sensor main circuit Black (4) OUT
NC	E2EQ-□C2	DC10 to 30V Brown (1) +V Load DUT Black (2) Blue (3) OV Note: M8 (3-pin) Connector: (1)(4)(3)
NO+NC	E2EQ-□C3	Brown (1) DC10 to 30V +V Load Black (4) White (3) Blue (3) OV

Connector Pin Arrangement

M12 Connector M12 Smartclick Connector	M8 (4-pin) Connector	M8 (3-pin) Connector
(2) (4) (3)		(1 ⁴ 3)



DC 2-wire

Operation mode	Model	Timing Chart	Output circuit
	E2EQ-X□D1□	Non- sensing area unstable sensing area sensing area Sensing object (%) 100 80 0	Brown Connector Pin Arrangement Proximity sensor main circuit Blue 0 V Note: Pins 2 and 3 are not used.
NO	E2EQ-X□D1□-T	Rated sensing distance ON Setting indicator OFF (green) ON Operation indicator OFF (orange) ON Control OFF output	Brown Arrangement 10 to 30 VDC (0V) Note: Pins 1 and 2 are not used. Note1. The load can be connected to either the +V or 0 V side. 2. The E2E□-X□D1□(-M1TGJ)-T has no polarity. There is no need to be concerned about the polarity of brown and blue wires, or pins 3 and 4.
	E2EQ-X□D2□	Non-sensing area Sensing area Sensing object (%) 100 0	Brown Connector Pin Arrangement 10 to 30 VDC 10 to 30 VD
NC	E2EQ-X□D2□-T	Rated sensing distance ON Operation indicator (orange) ON Control OFF output	Brown Connector Pin Arrangement 10 to 30 VDC (0V) Proximity Sensor Main Circuit OV (10 to 30 VDC) Note: Pins 3 and 4 are not used. Note1. The load can be connected to either the +V or 0 V side. 2. The E2E□-X□D1□(-M1TGJ)-T has no polarity. There is no need to be

E2EQ NEXT Series

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

∆WARNING	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

General prohibition Indicates the instructions of unspecified prohibited action.
Caution, explosion Indicates the possibility of explosion under specific conditions.

M WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Otherwise, explosion may result. Never use the product with an AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation.

- Do not use the product in environments subject to flammable or explosive gases.
- 2. Do not attempt to disassemble, repair, or modify the product.
- 3. Do not use a voltage that exceeds the rated operating voltage range
 - Applying a voltage that is higher than the operating voltage range may result in explosion or fire.
- Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or fire.
- If the power supply is connected directly without a load, the internal elements may explode or burn.
- 6. Be sure to insert a load when connecting the power supply.

Precautions for Correct Use


Do not use the product in any atmosphere or environment that exceeds the ratings.

Operating Environment

- 1. Do not install the Sensor in the following locations.
 - Outdoor locations directly subject to sunlight, rain, snow, waterdroplets, or oil.
 - (2) Locations subject to atmospheres with chemical vapors, inparticular solvents and acids.
 - (3) Locations subject to corrosive gases.
- 2. The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- 3. Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- 5. The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited
 - Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.
- 6. When turning on the power by influence of temperature environment, an outputmis-pulse sometimes occurs. After the sensor has passed for 300 msec after turning on, please use in the stable state. (DC 3-wire only.)
- The sensor is adjusted with a high degree of accuracy, so do not use in the environment with sudden temperature change. (DC 3wire only.)
- Operation check is performed using an OMRON's IO-Link master. If using an IO-Link master from another company, perform the operation check in advance. (Models with IO-Link only.)
- In the IO-Link mode, the cord between the IO-Link master and sensor must have a length of 20 m or less. (Models with IO-Link only.)


AND Connection of Proximity Sensors (DC 2-wire)

Two or more sensors cannot be connected in series on the AND circuit. Use them via a relay as shown on the figure.



OR Wiring of Proximity Sensors (DC 2-wire)

As a general principle, two or more sensors cannot be used in parallel on the OR circuit. It is possible only when sensors do not operate simultaneously and loads do not need to be maintained. When loads need to be maintained, use the sensors via a relay as shown on the figure.




Design

Influence of Surrounding Metal

When mounting the Proximity Sensor using a nut, only use the provided nut. And ensure that the minimum distances given in the following table are maintained.


When mounting the Proximity Sensor using a nut, only use the provided nut. Nuts that are supplied along with each Sensor are different. Refer to Dimensions for details on shapes.



(Unit: mm)

Туре	Model	L	d	D	m	n
DC 3-wire	E2EQ-X3□8	0	20	0	9	18
Spatter-resistant	E2EQ-X6□12	0	20	0	18	20
Triple distance	E2EQ-X12□18	0	50	0	36	54
model	E2EQ-X22□30	0	70	0	66	90
DC 2-wire	E2EQ-X3D□8	0	20	2	9	18
Spatter-resistant	E2EQ-X7D□12	0	20	4	18	20
Triple distance	E2EQ-X11D□18	0	50	4	33	54
model	E2EQ-X20D□30	0	70	8	60	90
DC 3-wire/DC 2-wire	E2EQ-X2□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X4□12	0	18	0	12	18
Double distance	E2EQ-X8□18	0	27	0	24	27
model	E2EQ-X15□30	0	45	0	45	45
DC 3-wire	E2EQ-X1R5□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X2□12	0	12	0	8	18
Single distance	E2EQ-X5□18	0	18	0	20	27
model	E2EQ-X10□30	0	30	0	40	45

When the Proximity Sensor is mounted in metal, ensure that the minimum distances given in the following table are maintained.




(Unit: mm)

					,	,
Models	Model	I	d	D	m	n
DC 3-wire	E2EQ-X3□8	2	20	2	9	18
Spatter-resistant	E2EQ-X6□12	4	20	4	18	20
Triple distance	E2EQ-X12□18	4	50	4	36	54
model	E2EQ-X22□30	8	70	8	66	90
DC 2-wire	E2EQ-X3D□8	2	20	2	9	18
Spatter-resistant	E2EQ-X7D□12	4	20	4	18	20
Triple distance	E2EQ-X11D□18	4	50	4	33	54
model	E2EQ-X20D□30	8	70	8	60	90
DC 3-wire/DC 2-wire	E2EQ-X2□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X4□12	2.4	18	2.4	12	18
Double distance		3.6	27	3.6	24	27
model	E2EQ-X15□30	6	45	6	45	45
DC 3-wire	E2EQ-X1R5□8	0	8	0	4.5	12
Spatter-resistant	E2EQ-X2□12	0	12	0	8	18
Single distance	E2EQ-X5□18	0	18	0	20	27
model	E2EQ-X10□30	0	30	0	40	45

Mutual Interference

When installing two or more Proximity Sensors face-to-face or sideby-side, ensure that the minimum distances given in the following table are maintained.



(Unit: mm)

Models	Model	Ite	em
Wodels	wodei	Α	В
DC 3-wire	E2EQ-X3□8	25	20
	E2EQ-X6□12	40	30
Spatter-resistant Triple distance model	E2EQ-X12□18	70	45
·	E2EQ-X22□30	150	90
	E2EQ-X3D□8	25	20
DC 2-wire Spatter-resistant Triple distance model	E2EQ-X7D□12	40	30
	E2EQ-X11D□18	70	45
	E2EQ-X20D□30	140	70
	E2EQ-X2□8	20	15
DC 3-wire/DC 2-wire	E2EQ-X4□12	30	20
Spatter-resistant Double distance model	E2EQ-X8□18	60	35
	E2EQ-X15□30	110	90
	E2EQ-X1R5□8	20	15
DC 3-wire Spatter-resistant Single distance model	E2EQ-X2□12	30	20
	E2EQ-X5□18	50	35
	E2EQ-X10□30	100	70


Mounting

Tightening Force

Do not tighten the nut with excessive force. A washer must be used with the nut.







Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)

2. The following strengths assume washers are being used.

DC 3-wire/DC 2-wire Spatter-resistant Triple distance model

Size	Par	Part B		
Size	Dimension (mm)	Torque	Torque	
M8	9	4 N⋅m	10 N⋅m	
M12	16	8 N⋅m	15 N⋅m	
M18	16	15 N⋅m	30 N⋅m	
M30	23	40 N⋅m	80 N⋅m	

DC 3-wire/DC 2-wire Spatter-resistant Double distance model, Spatter-resistant Single distance model

Size	Pai	Part A			
Size	Dimension (mm)	Torque	Torque		
M8	9	9 N⋅m	12 N⋅m		
M12		30 N·m			
M18		70 N·m			
M30		100 N⋅m			

Sensors

BASIC Model

E2EQ NEXT Series (Spatter-resistant, Double distance/Single distance model) DC 3-wire/DC 2-wire


Pre-wired Model/Pre-wired Connector Model





Connector Models (M12 Connector, M8 (4-pin) Connector and M8 (3-pin) Connector)





Indicators DC 2-wire D1 Models


Operation indicator (orange), Setting indicator (green)

Operation indicator (orange) DC 3-wire

Standard I/O mode (SIO mode): Operation indicator (orange/ON), Comunication indicator

(green/OFF) IO-Link Communication mode (COM mode):

Operation indicator (orange/ON). Comunication indicator (green/Flashing (1sec cycle))



Indicators

Standard I/O mode (SIO mode) Operation indicator (orange/ON), Comunication indicator (green/OFF)

IO-Link Communication mode (COM mode):

Operation indicator (orange/ON), Comunication indicator (green/Flashing (1sec cycle)

Model E2EQ-X□8-M1;

Pre-wired Models

Pre-wired Connector Models (M1TJ/M1TGJ) M12xP1





Operation mode, Output configuration (D1: NO, D2: NC) Vinyl-insulated round cable with 2 conductors

M8 M12 size: 4-dia

(Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm),

M18, M30 size: 6-dia.

(Conductor cross section: 0.5 mm² (AWG20), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B1/C1: NO, B2/C2: NC)

Vinyl-insulated round cable with 3 conductors M8, M12 size: 4-dia.

M18, M30 size: 6-dia

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B3/C3: NO+NC Type)

Vinvl-insulated round cable with 4 conductors

M8, M12 size: 4.3-dia

M18. M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm) Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Model	Α	В	С	D	F	Н	ı	J
E2EQ-X□8	M8XP1	37.8	4.4	26	8	3	15	13
E2EQ-X□12	M12XP1	47.1	3.7	33	10	4	21	17
E2EQ-X□18	M18XP1	55.3	8.5	38	10	4	29	24
E2EQ-X□30	M30XP1.5	60.3	8.3	43	10	5	42	36

Model Α В С D Н J E2EQ-X□8-M3/M5 M8XP1 M8XP1 26 8 3 15 13 E2EQ-X□8-M1 M8XP1 M12XP1 26 13 43 8 3 15 E2EQ-X□12-M1 M12XP1 48 M12XP1 33 10 4 21 17 E2EQ-X□18-M1 M18XP1 M12XP1 38 53 10 29 24 4 E2EQ-X□30-M1 M30XP1.5 58 M12XP1 43 10 5 42 36

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Angle R of the **Bending Wire**



Dimensions	R (mm)
M8	12
M12	12
M18	18
M30	10

Wire pullout position



Dimensions	Sc (mm)
M8	- (0)
M12	- (0)
M18	2.5
M30	2.5

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

PREMIUM Model

E2EQ NEXT Series (Spatter-resistant, Triple distance model)

DC 3-wire/DC 2-wire

Pre-wired Model/Pre-wired Connector Model






Connector Models (M12 Connector, M8 (4-pin) Connector and M8 (3-pin) Connector)



Note: DC 3-wire only



Indicators

Operation indicator (orange), Setting indicator (green) D2 Models:

Operation indicator (orange)

DC 3-wire Standard I/O mode (SIO mode): Operation indicator (orange/ON), Comunication indicator (green/OFF)

IO-Link Communication mode (COM mode):

Operation indicator (orange/ON), Comunication indicator (green/Flashing (1sec cycle))

Two clamping nuts

Indicators

Standard I/O mode (SIO mode): Operation indicator (orange/ON), Comunication indicator (green/OFF)

IO-Link Communication mode (COM mode):

Operation indicator (orange/ON), Comunication indicator (green/Flashing (1sec cycle))

Model E2EQ-X□8-M1; Shape of connection.

Model	Α	В	С	D	Е	F	Н	-	7
E2EQ-X□8-M3/M5	M8XP1	39	M8XP1	26	1	10	4	15	13
E2EQ-X□8-M1	M8XP1	43	M12XP1	26	1	10	4	15	13
E2EQ-X□12-M1	M12XP1	48	M12XP1	33	1	12	5.5	21	17
E2EQ-X□18-M1	M18XP1	53	M12XP1	38	1	12	6	29	24
E2EQ-X□30-M1	M30XP1.5	58	M12XP1	43	1	12	7	42	36

Pre-wired Models

Pre-wired Connector Models (M1TJ/M1TGJ) M12×P1



Operation mode,Output configuration (D1: NO, D2: NC)

Vinyl-insulated round cable with 2 conductors

(Conductor cross section: 0.3 mm² (AWG23), Insulator diameter: 1.15 mm),

(Conductor cross section: 0.5 mm² (AWG20), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B1/C1: NO, B2/C2: NC)

Vinyl-insulated round cable with 3 conductors M8, M12 size: 4-dia.

M18, M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm), Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Operation mode, Output configuration (B3/C3: NO+NC Type)

Vinyl-insulated round cable with 4 conductors

M8, M12 size: 4.3-dia.

M18. M30 size: 6-dia.

(Conductor cross section: 0.2 mm² (AWG24), Insulator diameter: 1.5 mm),

Standard length: 2 m (Pre-wired Models), 0.3 m (Pre-wired Connector Models)

Model	Α	В	С	D	E	F	Н	I	J
E2EQ-X□□8	M8XP1	37.8	4.4	26	1	10 (8 *)	4	15	13
E2EQ-X□□12	M12XP1	47.1	3.7	33	1	12 (10*)	5.5	21	17
E2EQ-X□□18	M18XP1	55.3	8.5	38	1	12	6	29	24
E2EQ-X□□30	M30XP1.5	60.3	8.3	43	1	12	7	42	36

^{*} If using the E2EQ-X\(\subseteq\text{D}\subseteq\text{8, E2EQ-X\(\subseteq\text{D}\subseteq\text{12, refer to () dimensions.}}

Mounting Hole Dimensions



Dimensions	F (mm)
M8	8.5 dia. +0.5
M12	12.5 dia. +0.5
M18	18.5 dia. +0.5
M30	30.5 dia. +0.5

Angle R of the **Bending Wire**



Dimensions	R (mm)
M8	12
M12	12
M18	18
M30	10

Wire pullout position



Dimensions	Sc (mm)
M8	(0)
M12	- (0)
M18	2.5
M30	2.3

Note: When installed with a long hole, there is a possibility that the nut may be damaged due to the force applied during tightening, and therefore it cannot be used.

Round Oil-resistant Connectors (M12 Smartclick)

XS5 NEXT Series

Round Oil-resistive Smartclick Connectors for E2E NEXT Series proximity sensors, that are Resistant to Oil, and that Reduce Installation Work

- Uses unique OMRON technology*1 and the same PVC cable with increased oil resistance as the E2E NEXT Series proximity sensors.
 Oil-resistance performance values of 2 years*2 when used in combination with E2E NEXT Series proximity sensors.
- Oil-resistant robot cables for use with moving parts such as loaders and cableveyors
- OMRON's unique lock mechanism (Smartclick) that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approximately 1/8 of a turn to lock.
- A positive click indicates locking.
- IP67, IP69K degree of protection.
- UL approved products.
- *1. Patented (as of March, 2022)
- ***2.** Covered types of oil: Cutting oil specified in JIS K 2241:2000

The oil-resistance performance value (2 years) indicates the median value (=Typ) at product design, and in evaluation testing results of oil-resistance performance. Shipped products will show some variance around this 2 year value in actual usage.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
M12 Smartclick Connector Straight type	Oil-resistant PVC cable	Sockets on One Cable End	6 dia.	Straight	1	XS5F-D421-C80-X	E2E-X\ \text{D}\ \text{-M1(T)(G)J(R)(-T)}\ \text{E2E-X}\ \text{D}\ \text{-M1(G)(-T)}\ \text{E2E-X}\ \text{D}\ \text{-M1TJ(R)}\ \text{E2E-X}\ \text{D}\ \text{-M1}\ \text{M1}\ \text{M2}\ \text{M1}\ \text{M2}\ \text{M3}\ \text{M2}\ \text{M3}\ \text{M2}\ \text{M3}\ \t
					2	XS5F-D421-D80-X	
					3	XS5F-D421-E80-X	
					5	XS5F-D421-G80-X	
					10	XS5F-D421-J80-X	
	Oil-resistant PVC robot cable	Sockets on One Cable End	6 dia.	Straight	1	XS5F-D421-C80-XR	
					2	XS5F-D421-D80-XR	
					3	XS5F-D421-E80-XR	
					5	XS5F-D421-G80-XR	
					10	XS5F-D421-J80-XR	
	Oil-resistant PVC cable	Socket and Plug on Cable Ends	6 dia.	Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-X	
					2	XS5W-D421-D81-X	
					3	XS5W-D421-E81-X	
					5	XS5W-D421-G81-X	
					10	XS5W-D421-J81-X	
	Oil-resistant PVC robot cable	Socket and Plug on Cable Ends	6 dia.	Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-XR	
					2	XS5W-D421-D81-XR	
					3	XS5W-D421-E81-XR	
					5	XS5W-D421-G81-XR	
					10	XS5W-D421-J81-XR	

Connections for Sensor I/O Connectors

DC 2-wire

	Pro	ximity Senso	or	Sensor I/O Connector	
Туре	Polarity	Operation mode	Model	Model	Connections
		NO	E2E-X□D1□-M1(T)G(J)		E2E NEXT Series XS5 NEXT Brown (+) White (not connected) Black (-)
	V		E2E-X□D1□-M1(T)(J)		E2E NEXT Series XS5 NEXT Brown (not connected) White (not connected) White (not connected) Black (-)
	Yes	NC NC	E2E-X□D2□-M1(T)G(J)	XS5F-D421-□80-X□ XS5W-D421-□81-X□	XS5 NEXT O Brown (+) O White (-) O Black (not connected)
M12 Connector/			E2E-X□D2□-M1(T)(J)		E2E NEXT Series XS5 NEXT O Brown (not connected) O White (+) O Blue (-) O Black (not connected)
M12 Smartclick Connector	No —	NO -	E2E-X□D1-M1(T)G(J)-T (Standard/Double distance model)		STATE OF THE STATE
			E2E-X□D1-M1(T)(J)-T E2E-X□D1-M1TGJ-T (Triple distance/Single distance model)		XS5 NEXT OBrown (not connected) O White (not connected) O Blue (+) (-) O Black (-) (+)
			E2E-X□D2-M1(T)G(J)-T (Standard/Double distance model)		XSS NEXT Brown (+)(-) White (-)(+) Blue (not connected) Black (not connected)
			E2E-X□D2-M1(T)(J)-T E2E-X□D2-M1TGJ-T (Triple distance/Single distance model)		EZE NEXT Series XS5 NEXT Brown (+)(-) O White (-)(+) EXECUTE: The series of the se

Note: Different from Proximity Sensor wire colors.

^{*} If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

XS5 NEXT Series

DC 3-wire

	Pr	oximity Sens	sor	Sensor I/O Connectors		
Types	Output	Operation mode	Model	Model	Connections	
		NO	E2E-X□B1□-M1TJ/ M1		EZE NEXT Series XS5 NEXT Brown (+) White (not connected) Black (Output)	
	PNP	NC	E2E-X□B2□-M1TJ/M1		E2E NEXT Series XS5 NEXT D D D Brown (+) O White (Output) O Blue (-) O Black (not connected)	
M12 Connector/ M12 Smartclick		NO+NC	E2E-X□B3□-M1TJ/M1	XS5F-D421-□80-X□	EZE NEXT Series XSS NEXT Brown (+) White (Output 2) Black (Output 1)	
Connector	NPN	NO	E2E-X□C1□-M1TJ/M1	XS5W-D421-□81-X□	EZE NEXT Series XS5 NEXT O Brown (+) O White (not connected) O Blue (-) O Black (Output)	
		NC	E2E-X□C2□-M1TJ/M1		EZE NEXT Series XS5 NEXT Brown (+) O White (Output) O Blue (-) O Black (not connected)	
		NO+NC	E2E-X□C3□-M1TJ/M1		E2E NEXT Series XS5 NEXT Brown (+) White (Output 2) Blue (-) Black (Output 1)	

Note: Different from Proximity Sensor wire colors.


Sensor I/O Connectors Oil resistance performance of mating combination

E2E NEX	Applicable connector Model	
Connecting method Model		XS5 NEXT Series
Pre-wired Connector Models	E2E-X□D□-M1T(G)J(R)	Oil resistant (2 years)*
Fre-wired Confrector Models	E2E-X - M1TJ(R)	Oli resistant (2 years)
M12 Connector Models	E2E-X□D□-M1(G)	Water-resistant (IP67)
W12 Connector Woders	E2E-X□□-M1	Water-resistant (IPO7)


^{*} Applicable cutting oil type: specified in JIS K 2241:2000

Dimensions (Unit: mm)


Both end connector type XS5W Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS5W-D421-□81-X/XS5W-D421-□81-XR



One end connector type XS5F Wiring Diagram for 4 Cores



Straight XS5F-D421-□80-X/XS5F-D421-□80-XR



^{*} If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

² years of oil resistance indicates the median value of the product design and the oil-resistance performance criterion result (=Typical value). Products to be shipped will have around 2 years of oil resistance, but will very depending on the product.

Round Water-resistant Connectors (M12 Smartclick)

XS5

Round Water-resistive Smartclick Connectors for E2E NEXT Series proximity sensors that Reduce Installation Work

- A newly developed lock mechanism that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approximately 1/8 of a turn to lock.
- · A positive click indicates locking.
- IP67 degree of protection.
- UL approved products.

Note: For details, refer to XS5 on your OMRON website.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable Specification	Туре	Cable diameter (mm)	Cable Connection Direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
					1	XS5F-D421-C80-F	-
					2	XS5F-D421-D80-F	
				Straight	3	XS5F-D421-E80-F	
					5	XS5F-D421-G80-F	
Л12		Sockets on One	6 dia.		10	XS5F-D421-J80-F	
Smartclick		Cable End	o uia.		1	XS5F-D422-C80-F	
Connector					2	XS5F-D422-D80-F	
Straight type	PVC robot cable			Right-angle	3	XS5F-D422-E80-F	E2E(Q)-X\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\
					5	XS5F-D422-G80-F	
					10	XS5F-D422-J80-F	
O. E. III		Socket and Plug on Cable Ends	6 dia.	Straight (Socket)/ Straight (Plug)	1	XS5W-D421-C81-F	
					2	XS5W-D421-D81-F	
					3	XS5W-D421-E81-F	
Right-angle type					5	XS5W-D421-G81-F	
0 0 71					10	XS5W-D421-J81-F	
T				Right-angle (Socket)/	2	XS5W-D422-D81-F	
6			o uia.	Right-angle (Plug)	5	XS5W-D422-G81-F	
				Straight (Socket)/	2	XS5W-D423-D81-F	
				Right-angle (Plug)	5	XS5W-D423-G81-F	
				Right-angle (Socket)/ Straight (Plug)	2	XS5W-D424-D81-F	
					5	XS5W-D424-G81-F	

Connections for Sensor I/O Connectors

DC 2-wire

	Pr	oximity Sens	sor	Sensor I/O Connector			
Туре	Polarity	Operation mode	Model	model number	Connections		
		NO	E2E-X□D1□-M1(T)G(J) E2EQ-X□D1□-M1TGJ		E2E(Q) NEXT Series XS5 Brown (+) White (not connected) Blue (not connected) Black (-)		
	Vec		E2E-X□D1□-M1(T)(J)		E2E NEXT Series XS5 OBrown (not connected) OWhite (not connected) OBlue (+) OBlue (+)		
	Yes	NC	E2E-X□D2□-M1(T)G(J) E2EQ-X□D2□-M1TGJ	XS5F-D42□-□80-F XS5W-D42□-□81-F	E2E(Q) NEXT Series XS5 OBrown (+) OBrown (+) OBlue (not connected) OBlack (not connected)		
M12 Connector/			E2E-X□D2□-M1(T)(J)		E2E NEXT Series XS5 Brown (not connected) O White (+) O Blue (-) O Black (not connected)		
M12 Smartclick Connector		NO	E2E-X□D1-M1(T)G(J)-T (Standard/Double distance model)		E2E NEXT Series XS5 O Brown (+) (-) O White (not connected) O Blue (not connected) O Black (-) (+)		
	No	NO	E2E-X□D1-M1(T)(J)-T E2E-X□D1-M1TGJ-T (Triple distance/Single distance model) E2EQ-X□D1□-M1TGJ-T		E2E(Q) NEXT Series XS5 O Brown (not connected) O Blue (+) (-) O Black (-) (+)		
	No	NC	E2E-X□D2-M1(T)G(J)-T (Standard/Double distance model)		E2E(Q) NEXT Series XS5 Description of Brown (+)(-) O Brown (+)(-) O White (-)(+) O Blue (not connected) O Black (not connected)		
			E2E-X\(\to\)D2-M1(T)(J)-T E2E-X\(\to\)D2-M1TGJ-T (Triple distance/Single distance model) E2EQ-X\(\to\)D2\(\to\)-M1TGJ-T		E2E(Q) NEXT Series XS5 Brown (+)(-) White (-)(+) Blue (not connected) Black (not connected)		

Note: Different from Proximity Sensor wire colors.

* If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.

DC 3-wire

	Pr	oximity Sen	sor		Sensor I/O Connectors		
Types	Output	Operation mode	Model	Model	Connections		
		NO	E2E(Q)-X□B1□- M1TJ/ M1		EZE(Q) NEXT Series XS5 Brown (+) With the (not connected) Bilue (-) Black (Output)		
	PNP	NC	E2E(Q)-X□B2□-M1TJ/M1		EZE(Q) NEXT Series XS5 Brown (+) White (Output) Blue (-) Black (not connected)		
M12 Connector/ M12 Smartclick		NO+NC	E2E(Q)-X□B3□-M1TJ/M1	XS5F-D421-□80-X□	EZE(Q) NEXT Series XS5 Brown (+) White (Output 2) Blue (-) Black (Output 1)		
Connector	NPN	NO	E2E(Q)-X□C1□-M1TJ/M1	XS5W-D421-□81-X□	EZE(Q) NEXT Series XSS Brown (+) White (not connected) Black (Output)		
		NC	E2E(Q)-X□C2□-M1TJ/M1		EZE(Q) NEXT Series XS5 Brown (+) White (Output) Blue (-) Black (not connected)		
Note Different		NO+NC	E2E(Q)-X□C3□-M1TJ/M1		E2E(Q) NEXT Series Some of the series of th		

Sensor I/O Connectors mating combination

E2E(Q) N	Applicable connector Model	
Connecting method	Model	XS5 Series
Pre-wired Connector Models	E2E(Q)-X□D□-M1T(G)J(R)	
Fre-wired Connector Models	E2E(Q)-X□□-M1TJ(R)	Motor registant (IDC7)
M42 Connector Modele	E2E-X□D□-M1(G)	Water-resistant (IP67)
M12 Connector Models	E2E(Q)-X -M1	


Note: Different from Proximity Sensor wire colors.

* If the XS5W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.


Dimensions (Unit: mm)

Socket and Plug on Cable Ends XS5W


Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS5W-D421-□81-F




Right-angle (Socket)/right-angle (Plug) XS5W-D422-□81-F




Straight (Socket)/right-angle (Plug) XS5W-D423-□81-F




Right-angle (Socket)/Straight (Plug) XS5W-D424-□81-F




Sockets on One Cable End XS5F Wiring Diagram for 4 Cores



Straight XS5F-D421-□80-F



Right-angle XS5F-D422-□80-F



Round Water-resistant Connectors (M8/S8)

XS3

Small Round Water-resistive Connectors

- Water-resistive, compact connector meets IP67 requirements.
- XS3-R Series; connectors with cables are available.
 M8 models are UL certified.
- Oil-resistant Polyurethane Robot Cables added.

Note: For details, refer to XS3 on your OMRON website.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Ordering Information

Sensor I/O Connectors

A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.


Appearance	Cable specification	Туре	Cable diameter (mm)	No. of cable cores (Poles)	Cable connection direction	Cable length (m)	Sensor I/O Connector model number	Applicable Proximity Sensor model number
						2	XS3F-M321-302-R	
					Straight	5	XS3F-M321-305-R	
						10	XS3F-M321-310-R	FOE VODE ME
M8 Connector				3		2	XS3F-M322-302-R	E2E-X□□□-M5
Straight type					Right-angle	5	XS3F-M322-305-R	
	PVC robot cable	Sockets on One Cable End				10	XS3F-M322-310-R	
			4 dia.	4	Straight	2	XS3F-M421-402-R	E2E-X□□□-M3
						5	XS3F-M421-405-R	
						10	XS3F-M421-410-R	
					Right-angle	2	XS3F-M422-402-R	
Right-angle type						5	XS3F-M422-405-R	
						10	XS3F-M422-410-R	
		Socket and Plug		3	Straight (Plug)/ Straight (Socket)	2	XS3W-M321-302-R	E2E-X□□-M5
						5	XS3W-M321-305-R	
95					Graight (Gooker)	10	XS3W-M321-310-R	
		on Cable Ends				2	XS3W-M421-402-R	E2E-X□□-M3
				4	Straight (Plug)/	5	XS3W-M421-405-R	
					Straight (Socket)	10	XS3W-M421-410-R	

Connections for Sensor I/O Connectors

DC 2-wire

		Proximity Se	nsor	Sensor I/O Connector	Connections	
Туре	Polarity	Operation mode	Model	model number		
M8 (4-pin) Connector	Vac	NO	E2E-X□D1-M3G	XS3W-M42□-4□-R	E2E NEXT Series XS3 Brown (+) White (not connected) Blue (not connected) Blue (not connected) Black (-)	
Models	Yes	Yes XS3F-M42□-4□-R	XS3F-M42□-4□-R	E2E NEXT Series XS3 OBrown (+) OBrown (+) OBrown (-) OBlue (not connected) OBlack (not connected)		

DC 3-wire



Note: Different from Proximity Sensor wire colors.

Sensor I/O Connectors mating combination


E2E NEX	Applicable connector Model	
Connecting method	Model	XS3 Series
M8 (4-pin) Connector Models	E2E-X□D□-M3G	
wio (4-pin) Connector Models	E2E-X□□-M3	Water-resistant (IP67)
M8 (3-pin) Connector Models	E2E-X□□-M5	

^{*} If the XS3W Series Connector which has a socket and plug on the cable ends is connected to the Sensor, this part will be a plug.


Dimensions (Unit: mm)

Socket and Plug on Cable Ends XS3W

Wiring Diagram for 3 Cores




Straight (Socket)/Straight (Plug) XS3W-M321-3□□-R




Socket and Plug on Cable Ends XS3W

Wiring Diagram for 4 Cores




Straight (Socket)/Straight (Plug) XS3W-M421-4□□-R




Sockets on One Cable End XS3F


Wiring Diagram for 3 Cores



Straight XS3F-M321-3□□-R




Right-angle XS3F-M322-3□□-R




Sockets on One Cable End XS3F


Wiring Diagram for 4 Cores



Straight XS3F-M421-4□□-R



Right-angle XS3F-M422-4□□-R



MEMO

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Smartclick is a registered trademark of OMRON Corporation.

Company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2018-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_3_5

Cat. No. D121-E1-13 1025 (1218)