# Small Spot/Mark (Separate Amplifier)

### CSM\_E3C-VS/VM\_DS\_E\_6\_2

# Extremely thin beam ideal for detection of minute objects and marks

- Ideal for detection of small objects and slight color differences
- Bad mark detection
- Detection of thin wire of 200  $\mu$
- Detection of slight level differences.



Be sure to read *Safety Precautions* on page 4.

# **Ordering Information**

# Sensors

**Sensor Heads** 

Red light Green light

				5
Sensing method	Appearance	Connection method	Sensing distance	Model
Reflective model (for mark detection)		Pre-wired (2 m)	10±2 mm	E3C-VS1G 2M
			<b>3</b> 0±5 mm	E3C-VS3R 2M
	₫		<b>35±5 mm</b>	E3C-VM35R 2M
			<b>7</b> 0±10 mm	E3C-VS7R 2M

# **Amplifier Units**

Power supply	Application	Appearance	Function	Model
DC	Slim body		Self-diagnosis	E3C-JC4P 2M

# Accessories (Order Separately)

# **Mounting Brackets**

Appearance	Model	Quantity	Remarks
	E39-L42	2	Can be used with the E3C-VS1G, or E3C-VS3R.

Refer to Mounting Brackets on E39-L/E39-S/E39-R for details.

# **Ratings and Specifications**

# **Sensor Head**

	Sensing method	Reflective model (for mark detection)				
Item	Model E3C-VS1G		E3C-VS3R	E3C-VM35R	E3C-VS7R	
Sensing distance		10±2 mm	30±5 mm	35±5 mm	7±10 mm	
Minimum detectable object (black mark on white)		0.7 mm at central sensing distance	2 mm at central sensing distance	0.2 mm at central sensing distance 0.6 mm at central se distance		
Light sou (waveleng	rce gth)	Green LED (565 nm)	Red LED (680 nm)	Red LED (660 nm)		
Ambient i	illumination	Incandescent lamp: 1,000 lx max. (on light-receiving side) Sunlight: 3,000 lx max. (on light-receiving side)				
Ambient temperate	ure range	Operating:-10 to 70°C (with no icing or condensation)Storage:-25 to 70°C (with no icing or condensation)		Operating/storage: -25 to 70°C (with no icing or condensation)		
Ambient humidity	range	Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)				
Insulation	n resistance	20 MΩ min. (at 500 VDC)				
Dielectric	strength	500 VAC, 50/60 Hz for 1 min				
Vibration (destruction	resistance ion)	10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions				
Shock res (destruction	sistance ion)	500 m/s <sup>2</sup> 3 times each in X, Y, and Z directions				
Degree of	f protection	IEC IP64 (indoors only)		IEC IP50 (indoors only)		
Connectio	on method	Pre-wired cable (standard length: 2 m)				
Weight (packed s	state)	Approx. 50 g		Approx. 60 g		
	Case	<sup>2</sup> olycarbonate		Heat-resistant ABS		
Material	Lens	Polycarbonate		Glass		
	Mounting Bracket			Steel		
Accessories		Instruction manual		Mounting Bracket, Slotted/ Phillips screws $M3 \times 16$ , Spring washer, Flat washer, M3 nuts	Mounting Bracket, Slotted/ Phillips screws M3 × 16, Spring washer, Flat washer, M3 nuts. Instruction manual	

# **Amplifier Units**

Refer to E3C. I/O Circuit Diagrams Refer to E3C. Connection Refer to E3C. Connectors Refer to E3C.

# Engineering Data (Reference Value)

# **Operating Range**

# E3C-VS1G



# E3C-VS7R



# E3C-VM35R



E3C-VS3R



# E3C-VS7R









## E3C-VS3R



# E3C-VM35R



# E3C-VS3R



# E3C-VS7R



# **Safety Precautions**

# Refer to Warranty and Limitations of Liability.

# <u> WARNING</u>

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



# **Precautions for Correct Use**

Do not use the product in atmospheres or environments that exceed product ratings.

# Wiring

For details on Extension Cables, refer to E3C.

# Dimensions

(Unit: mm) Tolerance class IT16 applies to dimensions in this datasheet unless otherwise specified.

# Sensors Sensor Heads



# **Amplifier Unit**

Refer to E3C for details.

# Accessories (Order Separately)

Mounting Brackets

Refer to E39-L/F39-L/E39-S/E39-R for details.

# Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

## Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

**OMRON** Corporation Industrial Automation Company