# E3S-C


CSM\_E3S-C\_DS\_E\_9\_3

## Water- and Oil-resistant Photoelectric Sensor with Metal Housing Used for Longrange Sensing

- Excellent resistance against the water and oil. Easy application in locations with oil mist.
- Long-range sensing up to 30 m with Through-beam models.
- Shock resistance rated at 1,000m/s<sup>2</sup>.
- Product lineup includes metal M12 pre-wired connector models.
- NPN/PNP selector switch output.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



## **Ordering Information**

Sensing method	Appearance	Connection method	Sen	sing di	stance	Model
	Horizontal	Pre-wired				E3S-CT11 2M Emitter E3S-CT11-L 2M Receiver E3S-CT11-D 2M
Through-beam		Pre-wired Connector (M12)			30 m	E3S-CT11-M1J 0.3M Emitter E3S-CT11-L-M1J 0.3M Receiver E3S-CT11-D-M1J 0.3M
Emitter + Receiver) *	Vertical	Pre-wired				E3S-CT61 2M Emitter E3S-CT61-L 2M Receiver E3S-CT61-D 2M
		Pre-wired Connector (M12)				E3S-CT61-M1J 0.3M Emitter E3S-CT61-L-M1J 0.3M Receiver E3S-CT61-D-M1J 0.3M
	Horizontal	Pre-wired				E3S-CR11 2M
Data and action		Pre-wired Connector (M12)				E3S-CR11-M1J 0.3M
Retro-reflective	Vertical	Pre-wired		3 n	1	E3S-CR61 2M
		Pre-wired Connector (M12)				E3S-CR61-M1J 0.3M
		Des voins d	700	mm		E3S-CD11 2M
Diffuse-reflective	Horizontal	Pre-wired		2 m		E3S-CD12 2M
	चः िं ← − −	Pre-wired Connector (M12)	700	mm		E3S-CD11-M1J 0.3M
		1 16-wiled Collifector (W12)		2 m		E3S-CD12-M1J 0.3M
	I	Pre-wired	700	mm		E3S-CD61 2M
	Vertical	Fie-wileu		2 m		E3S-CD62 2M
		Dre wined Connector (MAC)	700	mm		E3S-CD61-M1J 0.3M
		Pre-wired Connector (M12)		2 m		E3S-CD62-M1J 0.3M

<sup>\*</sup> Through-beam Sensors are normally sold in sets that include both the Emitter and Receiver.

#### Accessories (Order Separately)

Slits (A Slit is not provided with Through-beam Sensors. Order a Slit separately if required.) (Refer to Dimensions on page 10.)

Slit width	Sensing distance	Minimum detect- able object (reference value)	Model	Quantity	Remarks
0.5 mm × 11 mm	1.8 m	0.5-mm dia.		1 set each for	(0 1 1 0 0 0 0
1 mm × 11 mm	3.5 m	1-mm dia.	E39-S61	Emitter and Re-	(Snap-in Long Slit) Can be used with the E3S-CT□1(-M1J) Through-beam Sensor. Refer to page 10.
2 mm × 11 mm	7 m	2-mm dia.		ceiver	
4 mm × 11 mm	15 m	2.6-mm dia.		(8 Slits total)	

#### Reflectors (A Reflector is required for each Retro-reflective Sensor.)

The E39-R1 Reflector is provided with the Sensor. Order other Reflectors separately if required. (Refer to Dimensions on E39-L/E39-S/E39-R.)

Name	Sensing distance		Model	Quantity	Remarks	
Name	Rated value	Reference value	Wiodei	Quantity	Remarks	
Reflectors	3 m		E39-R1	1	Provided with the E3S-CR□1 (-M1J) Retro-reflective Sensor.	
		4 m	E39-R2	1	_	
Small Reflectors		1.5 m	E39-R3	1		
Small Reflectors		750 mm	E39-R4	1		
Tape Reflectors		700 mm (50 mm)*	E39-RS1	1		
		1,100 mm (100 mm)*	E39-RS2	1	Enables MSR function.	
		1,400 mm (100 mm)*	E39-RS3	1		

Note: 1. If you use any Reflector other than the enclosed Reflector, make sure that the stability indicator lights properly when you set the Sensor.

#### **Mounting Brackets**

Some Mounting Brackets are provided with the Sensor. Order other Mounting Brackets separately if required. (Refer to Dimensions on E39-L/E39-S/E39-R.)

Appearance	Model	Quantity	Remarks
	E39-L102	1	Provided with Horizontal Models.
	E39-L103	1	Provided with Vertical Models.
	E39-L85	1	Mounting bracket for changing from E3S-
	E39-L86	1	Mounting bracket for changing from E3S-
	E39-L87	1	

Note: 1. When using a Through-beam Sensor, order one Connector for the Receiver and one for the Emitter. 2. Refer to *Mounting Brackets* on *E39-L/F39-L/E39-S/E39-R* for details.

### Sensor I/O Connectors (Sockets on One Cable End)

(Models with Pre-wired Connectors: A Connector is not provided with the Sensor. Be sure to order a Connector separately.) (Refer to Dimensions on XS2.)

Cable	Appearance	Cable	e type	Model
	Straight	2 m		XS2F-D421-DC0-F
Fire-retardant, robot cable		5 m	- 3-wire	XS2F-D421-GC0-F
	L-chane	2 m		XS2F-D422-DC0-F
	L-shape	5 m		XS2F-D422-GC0-F

Note: 1. When using a Through-beam Sensor, order one Connector for the Receiver and one for the Emitter.

<sup>2.</sup> Refer to Reflectors on E39-L/E39-S/E39-R for details.

<sup>\*</sup> Values in parentheses indicate the minimum distance required between the Sensor and Reflector.

<sup>2.</sup> For details on Sensor I/O Connectors and cables such as vibration-proof robot cables, refer to Introduction to Sensor I/O Connectors/Sensor Controllers.

## **Ratings and Specifications**

	Sensing method	Through-beam	Retro-reflective (with M.S.R. function) *1	Diffuse	reflective	
	Model	Horizontal E3S-CT11(-M1J)	Horizontal E3S-CR11(-M1J)	Horizontal E3S-CD11(-M1J)	Horizontal E3S-CD12(-M1J)	
Item	Woder	Vertical E3S-CT61(-M1J)	Vertical E3S-CR61(-M1J)	Vertical E3S-CD61(-M1J)	Vertical E3S-CD62(-M1J)	
Sensing d	listance	30 m	3 m (when using E39-R1)	700 mm ( $300 \times 300$ mm white paper)	2 m (300 × 300 mm white paper)	
Standard object	sensing	Opaque, 15-mm dia. min.	Opaque, 75-mm dia. min.			
Differentia	al travel	-	-	20% max. of sensing dista	nce	
Directiona	al angle	Emitter and Receiver: 3° to15°	3° to 10°			
Light sour		Infrared LED (880 nm)	Red LED (660 nm)	Infrared LED (880 nm)		
Power sup	pply voltage	10 to 30 VDC including 10% (	p.p) ripple			
Current co	onsumption	50 mA max. (Emitter 25 mA max. Receiver 25 mA max.)	40 mA max.			
Control o	utput	Load power supply voltage: 30 VDC max. Load current: 100 mA max. (Residual voltage: NPN output: 1.2 V max., PNP output: 2.0 V max.) Open controller output (NPN/PNP selectable) Light-ON/Dark-ON selectable				
Protection	n circuits	Power supply reverse polarity circuit protection, Output short-circuit protection  Power supply reverse polarity protection, Output short-circuit protection, Mutual interference prevention				
Response	time	Operate or reset: 1 ms max.	1		Operate or reset 2 ms max	
Sensitivity adjustmer		One-turn adjuster		Two-turn endless adjuster	with an indicator	
Ambient il (Receiver	llumination side)	Incandescent lamp: 5,000 lx max. Sunlight: 10,000 lx max.				
Ambient t	emperature	Operating: -25°C to 55°C, Sto	orage: –40°C to 70°C (with no i	cing or condensation)		
Ambient h	numidity	Operating: 35% to 85%, Stora	age: 35% to 95% (with no cond	ensation)		
Insulation	resistance	20 $\text{M}\Omega$ min. (at 500 VDC)				
Dielectric	strength	1,000 VAC, 50/60 Hz for 1 mi	n			
Vibration	resistance	Destruction: 10 to 2,000 Hz, 1	.5-mm double amplitude or 30	0 m/s <sup>2</sup> for 0.5 hours each in	X, Y, and Z directions	
Shock res	sistance	Destruction: 1,000 m/s <sup>2</sup> 3 time	es each in X, Y, and Z direction	IS		
Degree of	protection	IEC 60529: IP67 (in-house sta	andards: oil-resistant), NEMA: (	6P (indoors only) *2		
Connection	on method	Pre-wired (standard cable len	gth: 2 m) or Pre-wired M12 Co	nnector (standard cable len	gth: 0.3 m)	
Weight (packed state)  Approx. 270 g (Pre-wired cable) Approx. 230 g (Pre-wired Connector (M12))  Approx. 130 g (Pre-wired Connector (M12))  Approx. 130 g (Pre-wired Connector (M12))  (Pre-wired Connector (M12))			2))			
	Case	Zinc die-cast				
Material	Operation panel cover	PES (polyether sulfone)				
materiai	Lens	Methacrylic resin				
	Mounting	Stainless steel (SUS304)				
	Bracket					


<sup>\*1.</sup> Refer to MSR function of Technical Guide (Technical version).
\*2. NEMA: National Electrical Manufactures Association

## **Engineering Data (Reference value)**


#### **Parallel Operating Range**

#### Through-beam

E3S-CT□ (-M1J)




#### Through-beam E3S-CT□ (-M1J) + E39-S61 Slit (Order Separately)



#### Retro-reflective


E3S-CR□1 (-M1J) + E39-R1 Reflector (Provided)



#### **Operating Range**

#### Diffuse-reflective


E3S-CD (-M1J)



#### **Excess Gain vs. Set Distance**


#### Through-beam

E3S-CT 1 (-M1J)




#### Retro-reflective

E3S-CR□1 (-M1J) + E39-R1 Reflector (Provided)



### Diffuse-reflective

E3S-CD□□ (-M1J)




### I/O Circuit Diagrams

#### **NPN Output**

Model	Operation mode	Timing charts	Operation selector	Output circuits
E3S-CT11(-M1J) *	Light-ON	Incident light No incident light Light indicator ON (Red) OFF Output ON transistor OFF Load Operate (e.g. relay) Reset (Between brown ① and black ④ leads)	L side (LIGHT ON)	Through-beam Model Receivers: Retro-reflective Models, Reflective Models    Control output   Control output
E3S-CT61(-M1J) * E3S-CR11(-M1J) E3S-CR61(-M1J) E3S-CD11(-M1J) E3S-CD12(-M1J) E3S-CD61(-M1J) E3S-CD62(-M1J)	Dark-ON	Incident light No incident light Light indicator ON (Red) OFF Output ON transistor OFF Load Operate (e.g. relay) Reset (Between brown ① and black ④ leads)	D side (DARK ON)	* Set the NPN or PNP selector to NPN.  Connector Pin Arrangement  (3) (3) (3) (4) (5) (5) (6) (7) (7) (8) (9) (9) (9) (9) (10) (10) (10) (10) (10) (10) (10) (10
	Through-beam Model Emitters  Power Indicator I			


#### **PNP Output**



<sup>\*</sup> Models numbers for Through-beam Sensors (E3S-CT11(-M1J)) are for sets that include both the Emitter and Receiver.

The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3S-CT11-L 2M), the model number of the Receiver, by adding "-D" (example: E3S-CT11-D 2M.) Refer to Ordering Information to confirm model numbers for Emitter and Receivers.

#### Plug (Sensor I/O Connector)



Clas- sifica- tion	Conductor	Connector pin No.	Application
	Brown	1	Power supply (+V)
DC		2	
ьс	Blue	3	Power supply (0 V)
	Black	4	Output

Refer to Introduction to Sensor I/O Connectors/Sensor Controllers for details.

Note: Pin 2 is not used.

#### **Nomenclature**

## **Horizontal Model** Operation panel cover Stability indicator (green) Light indicator (red) Sensitivity adjuster Operation selector \*2 Output selector \*1 Model number

## **Vertical Model** Operation panel Light indicator (red) Stability indicator (green) Output selector \*1 Sensitivity adjuster Operation selector \*2

Note: The sensitivity adjuster on Through-beam and Retro-reflective Models is different.

- \*1. Use the output selector to select the type of output transistor, NPN or PNP. \*2. Use the operation selector to select the operation mode.

#### **Safety Precautions**

#### Refer to Warranty and Limitations of Liability.



This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



#### **Precautions for Correct Use**

Do not use the product in atmospheres or environments that exceed product ratings.

#### Wiring

#### Cable

- The E3S-C uses an oil-resistive cable to ensure oil resistivity.
- Do not allow the cable to be bent to a radius of less than 25 mm.

#### Mounting

#### **Mounting**


- When mounting the E3S-C, do not hit the E3S-C with a hammer, or the E3S-C will loose watertightness.
- Use M4 screws to mount the E3S-C. The tightening torque of each screw must be 1.18 N·m maximum.

#### **Mounting Bracket**


- When mounting the E3S-C with the mounting bracket so that sensing objects will be in the direction of the mechanical axis, use the optical axis lock holes.
- If it is not possible to mount the E3S-C so that the sensing objects will be in the direction the mechanical axis, move the E3S-C upwards, downwards, to the left, or to the right and secure the E3S-C in the center of the range where the light indicator will be lit, at which time make sure that the stability indicator is lit.

#### **Direct Mounting**

Mount the E3S-C as shown in the following illustration.



By inserting screws into the optical axis lock holes, the Mounting Bracket will be in the direction of the optical axis of the E3S-C.



Mounting axis

axis loc


holes (M4)

#### Adjusting

#### **Optical Axis of Through-beam Sensor**

The E3S-C Through-beam Models incorporates two lenses, one of which will be used as shown in the following illustration. When using a Slit, the Slit must be on the side where the lens to be used is located.

#### **Horizontal Model Vertical Model**



#### **Water Resistance**

To ensure the water resistance of the E3S-C, tighten the screws of the operation panel cover to a torque of 0.34 N·m to 0.54 N·m.

#### Others

#### **Oil and Chemical Resistance**

- Although the E3S-C is oil-resistance, refer to the following table before using the E3S-C in places where oil may be sprayed on the E3S-C.
- Tests were carried out with the following oils and it was certified that the E3S-C resists these oils.

Oil	Product name	Kinematic viscosity (mm²/s (cst)) at 40°C	PH
Lubricating oil	Velocite No.3 (manufactured by Exxon Mobil)	2.02	
Water insoluble machining oil	Yushiron Oil No. 2 ac (manufactured by Yushi- ro Chemical Industry Co., Ltd.)	Less than 10	
Water soluble machining oil	Yushiroken EC50T-3 (manufactured by Yushi- ro Chemical Industry Co., Ltd.)		7 to 9.5
	Yushiron Lubic HWC68 (manufactured by Yushi- ro Chemical Industry Co., Ltd.)		7 to 9.9
	Griton 1700D (manufactured by Toho Chemical Industry Co., Ltd.)		7 to 9.2
	Yushiroken S50N (manufactured by Yushi- ro Chemical Industry Co., Ltd.)		7 to 9.8

- Note: 1. The E3S-C maintained a minimum insulation resistance of 100  $\mbox{M}\Omega$ after the E3S-C was dipped in all the above oils at a temperature of 50°C for 240 hours.
  - 2. When using the E3S-C in a place where an oil other than the ones listed above is sprayed on the E3S-C, refer to the above kinematic viscosity and ph values. The location may be suitable for the E3S-C if the kinematic viscosity and pH values of the oil are close to the above kinematic viscosity and pH values, but make sure that the oil does not contain any additive that may have a negative influence on the E3S-C.


#### **Dimensions**

### **Sensors**

#### **Through-beam (Horizontal)**

#### E3S-CT11(-M1J)

#### Pre-wired Connector (-M1J)



- \*1. The Mounting Bracket can be attached to side A.
  \*2. The Emitters for Through-beam Sensors only have the power indicator (red).
  \*3. The Emitter cable is 4-dia.vinyl-insulated round cable with 2 conductors (conductor cross section: 0.3 mm², insulator diameter: 1.3 mm) and a standard length of 2 m.


Note: Models numbers for Through-beam Sensors (E3S-CT11(-M1J)) are for sets that include both the Emitter and Receiver.

The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3S-CT11-L 2M), the model number of the Receiver, by adding "-D" (example: E3S-CT11-D 2M.) Refer to Ordering Information to confirm model numbers for Emitter and Receivers.

#### **Through-beam (Vertical)**

#### E3S-CT61(-MJ)

#### Pre-wired Connector (-M1J)




- \*1. The Mounting Bracket can be attached to side A.
  \*2. The Emitters for Through-beam Sensors only have the power indicator (red).
- \*3. The Emitter cable is 4-dia vinyl-insulated round cable with 2 conductors (conductor cross section: 0.3 mm<sup>2</sup>, insulator diameter: 1.3 mm) and a standard length of 2 m.

#### **Retro-/Diffuse-reflective (Horizontal)**


# E3S-CD11(-M1J)

#### Pre-wired Connector (-M1J)



Note: Models numbers for Through-beam Sensors (E3S-CT61(-M1J)) are for sets that include both the Emitter and Receiver.


The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3S-CT61-L 2M), the model number of the Receiver, by adding "-D" (example: E3S-CT61-D 2M.) Refer to Ordering Information to confirm model numbers for Emitter and Receivers.



#### **Accessories (Order Separately)**

Snap-in Long Slit (For Through-beam Models) E39-S61





Dimension A (mm)	Material	Quantity	
0.5		4 1 6	
1	Stainless	1 set each for Emitter/Receiver (8 Slits total)	
2	steel		
4		(o omo total)	

#### Reflectors

Refer to E39-L/E39-S/E39-R for details.

**Mounting Brackets** 

Refer to E39-L/E39-S/E39-R for details.

#### Terms and Conditions Agreement

#### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

#### Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <a href="http://www.omron.com/global/">http://www.omron.com/global/</a> or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2023.1

In the interest of product improvement, specifications are subject to change without notice.

#### OMRON Corporation **Industrial Automation Company**