

OMRON



Contact-Type Smart Sensor (Communications Type) E9NC-T



Durable Space-saving Advanced

Handles Diverse Measurement Applications





Handles Diverse Measurement Applications



Handles Measurement Applications in Harsh Environments

Durable

Tough under Vibration and Shock

Ball Spline Mechanism

Resists Water and Oil

IP67 Degree of Protection and Magnetic Sensing Method



Angle Inspections for Camshafts

Withstands Bending

Robot Cables

Handles Measurement Applications with Limited Space

Space-saving

Slim, Short Sensor Heads

8-mm outside diameter

Slim Amplifier Units

Slim Body Only 10 mm Wide



Height Measurement for Assembled Watch Gears

Handles Advanced Measurement Applications *1

Advanced

Data Communications via Field Networks

High-precision Data Transmission (0.1-µm Resolution)

Connect Many Sensors

Connect Up to 30 Sensors with Reduced Wiring *2

Measurement of Machined Part Precision

Eight Calculation Functions *3

Maximum Value, Minimum Value, Flatness, Average, Step, Twist, Warp, and Thickness

^{*1.} E9NC-TA0 only

^{*2.} You can connect up to 30 Sensors to an E3NW Sensor Communications Unit with EtherCAT (when using an OMRON NJ-series Controller) or up to 16 Sensors with CC-Link.

^{*3.} Calculations are performed on the host controller. Special function blocks are available separately. For details, please contact your OMRON sales representative.

Durable

Tough under Vibration and Shock

Ball Spline Mechanism

A ball spline mechanism is used to hold the balls in grooves (on the right in the following diagram). This helps prevent the balls from damaging internal parts due to vibration or shock to reduce the chance of malfunction. In comparison with the previous method (on the left in the following diagram), load capacity is increased and an exceptionally smooth sliding operation is achieved for long-term stable operation.



Resists Water and Oil

IP67 protection is combined with a magnetic sensing method.

the sensing section, this sensor is not affected by problems

such as light scattering, which can occur with optical sensors.

You therefore get stable detection even in harsh environments.

elhow

Even in the unlikely event that water, oil, or condensation enters

IP67 Degree of Protection *1 and

Detection is possible even with adhesion of oil.

Magnetic Sensing Method

Space-saving


107.8 mm* even including the bending radius Save more space and design more freely with the right-angle air type.

Slim, Short Sensor Heads

8-mm outside diameter




Measuring Dimensions of Electronic Components



Slim Amplifier Units


Slim Body Only 10 mm Wide



* For the above connection example.



Actual Size * ★ E9NC-TH5S (on the left) and E9NC-TH5L (on the right)




Advanced

Data Communications via Field Networks

High-precision Data Transmission (0.1-µm Resolution)

With a standard type with an analog output, accuracy is reduced when the data is sent. With the communications type, however, the high-precision data measured at a resolution of 0.1 µm is transmitted as digital data without loosing any precision or accuracy.




Connect Many Sensors

Connect Up to 30 Sensors with Reduced Wiring

You can quickly and easily connect E9NC-TA0 Units to the E3NW-ECT Sensor Communications Unit. You can easily achieve simultaneous measurements or measurements for multiple processes. You can reduce wiring work in comparison with the analog output type.


- *1. When using EtherCAT with an OMRON NJ-series Controller. With CC-Link, you can connect up to 16 Sensors.
- Comparison of Wiring When Connecting Five Sensors



Eight Calculation Functions

From Maximum/Minimum Values to Warp and Thickness

Just add function blocks to the host controller to easily perform various calculations.



or details, please contact your OMRON sales representative

ON/OFF Output Type for Determinations E9NC-TA21/TA51

Easy Setup with One Button!

Smart Tuning

Just press the **STUNE Button** to easily set up various types of determinations.



Check Component Heights or Assembly Conditions

Height Determination Set a threshold value for the standard height.



Set the Head against the reference workpiece and press the S-TUNE Button.

Determine the Heights of Two Workpieces Model Determine the Difference in Heights

Model Determine the Difference in Heights between Two Workpieces



Set the Head against each of the two workpieces and press the S-TUNE Button once for each.

Determine If the Dimension of a Components is within a Specified Range Determination within Range Set upper and lower threshold values. High threshold value Low threshold value Low threshold value workpiece

Set the Head against each of the upper-limit and lower-limit workpieces and press the S-TUNE Button once for each.

Determine If a Workpiece is within Tolerances Set thresholds for the upper and lower limits of the plus-minus tolerance for the height of a reference workpiece. HIGH (NG) GO (OK) +Tolerance -Tolerance Low threshold value

Set the Head against the workpiece and press the S-TUNE Button.

Reference workpiece

Hybrid Output

You can use the hybrid output with the two outputs from the Amplifier Unit to determine if the high threshold value is exceeded or if the low threshold value is exceeded.

Outputs (Set for NO Operation) in Hybrid Output Mode

	LOW judgement	GO judgement	HIGH judgement	Error judgement or undetermined
Control output 1	OFF	ON	ON	OFF
Control output 2	ON	ON	OFF	OFF

Ordering Information

Sensor Heads (Connection Cable between Preamplifier and Amplifier Unit is not provided with the Sensor Head. Be sure to have the Connection Cable ready when using the Sensor.)

*	· · · · · · · · · · · · · · · · · · ·				, ,
Туре	Appearance (Head size)	Measuring range (Moving range)	Resolution	Precision	Model
Straight Type	8 dia. 82.8				E9NC-TH5S 2M
Right-angle Air Type	8 dia. 82.7	F 100 100			E9NC-TH5L 2M
Flanged Type/ Straight Type	M9 82.8	- 5 mm			E9NC-TH5SF 2M
Flanged Type/ Right-angle Air Type	M9 82.7			4	E9NC-TH5LF 2M
Straight Type	8 dia. 109.7		0.1 μm	1 μm	E9NC-TH12S 2M
Right-angle Air Type	8 dia. 109.6				E9NC-TH12L 2M
Flanged Type/ Straight Type	M9 109.7	12 mm			E9NC-TH12SF 2M
Flanged Type/ Right-angle Air Type	M9 109.6				E9NC-TH12LF 2M

Amplifier Units

Туре		Inputs/outputs	Model		
Communications Type *1		Data communication	E9NC-TA0		
011/055	A CONTRACTOR OF THE PARTY OF TH	1 input	NPN output	PNP output	
ON/OFF Output Type	+ 2 outputs	E9NC-TA21 2M	E9NC-TA51 2M		

^{*1.} A Sensor Communications Unit is required if you want to use the Amplifier Unit on a network.

Connection Cable between Preamplifier and Amplifier Unit

Model	Quantity
E9NC-TXC05	1
E9NC-TXC5	1
E9NC-TXC10	1
E9NC-TXC20	1
	E9NC-TXC05 E9NC-TXC5 E9NC-TXC10

Accessories (Sold Separately)

Sensor Head Accessories

Probe

The E9NC-TB1 is provided with the Sensor Head. Order replacements as required.

Type	Appearance	Model	Quantity
3-dia. probe	6	E9NC-TB1	1
Nylon probe	8	E9NC-TB2	1
Probe for flat surfaces		E9NC-TB3	1

Amplifier Unit Accessories

Mounting bracket

A Mounting Bracket is not provided with the Amplifier Unit. It must be ordered separately as required.

Appearance	Model	Quantity
63	E39-L143	1

We also supply other accessories, such as Rubber Boots for Sensor Heads and DIN Track and End Plates and Covers for Amplifier Units. For details, refer to the E9NC-T Compact-Type Smart Sensor datasheet (Cat. No. E434-E1).

Related Products

Sensor Communications Units

Type	Appearance	Model
Sensor Communications Unit for EtherCAT		E3NW-ECT
Sensor Communications Unit for CC-Link		E3NW-CCL
Distributed Sensor Unit*2		E3NW-DS

Authorized Distributor:

EtherCAT® is a registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany. CC-Link is a registered trademark of Mitsubishi Electric Corporation. The trademark is managed by the CC-Link Partner Association.

OMRON Corporation Industrial Automation Company Tokyo, JAPAN

Contact: www.ia.omron.com

Regional Headquarters **OMRON EUROPE B.V.**

Sensor Business Unit Carl-Benz-Str. 4, D-71154 Nufringen, Germany Tel: (49) 7032-811-0/Fax: (49) 7032-811-199

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2), Alexandra Technopark, Singapore 119967 Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON ELECTRONICS LLC One Commerce Drive Schaumburg, IL 60173-5302 U.S.A Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200 © OMRON Corporation 2014 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_2_4_0716 Printed in Japan Cat. No. E433-E1-02

0614 (0614)

Refer to your OMRON website for details. *2. The Distributed Sensor Unit can be connected to any of the Sensor Communications Units.