OMRON



» ADVANCED type supports finger protection, and complex blanking and muting functions

» EASY type simple and affordable hand protection » BASIC type simple hand protection and simple muting functions





Offering the best selection of safety light curtains for your guarding needs.

Three F3SJ types allow easy selection for your application.


Omron's new F₃SJ series of safety light curtains offers a tailored approach for a variety of production environments. Conventional safety light curtains offer full-featured models, even when only simple intrusion detection is needed. The F₃SJ series offers a product range that allows you to choose the best product according to your application needs.

The EASY type has been added for simple hand detection, while the BASIC type adds the potential for series connection and simple muting functions.

The F₃SJ series now allows you to select the best safety light curtain for your application environment without paying for unused functions.

- For simple and affordable hand protection: The EASY type (F3SJ-E)
- and muting functions:
- For finger protection, series connection, complex blanking and muting functions:





Easy to install EASY type (F3SJ-E)

Can be used for simple hand intrusion detection. Mounting now takes less than half the man-hours that conventional models take.

Despite its simplicity, the EASY type is a highly reliable safety light curtain.

Easy to maintain BASIC type (F3SJ-B)

The muting function allows use of the safety light curtain in a variety of manufacturing environments. The flexible mounting supports up to three sets of series-connected sensors.

High functionality ADVANCED type (F3SJ-A)

The detection capability supports finger protection through use of 14mm resolution. The ADVANCED type has a a wide variety of muting and blanking functions to increase productivity.

[·] STI is a trademark or registered trademark of OMRON Corporation in Japan and other countries.

Microsoft product screen shot(s) reprinted with permission from Microsoft Corporation.

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

^{*} As the beams are infrared, they are invisible to the naked eye.


Implementation cost reduction with 1/2* the mounting time: Start with the "EASY type"

The EASY type safety light curtain well is suited for straight forward on/off detection applications.

* Comparison with existing OMRON products.

By carefully selecting the available functions, we have reduced man hours necessary for installation by approximately 1/2 when compared with existing OMRON models.


Reduced installation time means added savings to your project's budget, start with the EASY type.





Machine safety first, narrowed down to the simplest functions:

Upon detection of personnel, the machine stops. Simple yet very optimal.



1/2 the mounting time Fixed response time makes calculation of the safety distance is easier.

Reduced wiring, one-touch brackets and easy-to-view alignment beams all add up to cost savings.

Additionally, with one fixed response time, it is know easier to calculate the safety distance.





Global Support OMRON will support you through the our global network





Easy-to-view Diagnostics


These indicators enable you to intuitively know the status and cause of any error.
Allowing you faster installation while reducing machine down time.

Fits any site, equipped with muting functions and series connection: Use the "BASIC type"

In addition to the simple functions inherited from the EASY type, such as global support, easy-to-view indicators, the BASIC type includes series connection and simple muting functions . This enables the BASIC type to satisfy installations that require multiple safety light curtains.







Up to three sets-connected in series It is possible to connect up to three sets of safety light curtains in series.

These sensors can be placed in a U-shaped or L-shaped pattern with a single power line, thus requiring less wiring.



Instant visibility of process trouble during muting

The BASIC type includes a muting function which temporarily disables the safety light curtain when a workpiece passes through. In the event of any trouble occurring, the error can be instantly recognized from the pattern of the LED indicators, allowing for a fast solution.



Functions inherited from the EASY type

Simple functions such as universal power voltage specification, easy-to-view diagnostics, a fixed response time have been inherited from the EASY type, As a result, expect reduced work-hours at each stage of use, from design and installation to operation.

Multi-functional for special applications such as finger protection: the "ADVANCED" type

The detection capability supports finger protection through use of 9 mm resolution. The ADVANCED type is equipped with various functions such as blanking, muting and the programing of warning zones. All settings can be done via an easy to use software tool. This Tool simplifies installations that were previously complicated, again our way of reducing cost and increasing productivity.






Beam alignment is easier.

 The state of the stat


Tool for setting parameters and checking the system status

With the ADVANCED type (F3SJ-A) "SD Manager", all parameters can be set and the system status can be checked with a personal computer. Complex settings are now simple to configure



Detection capability supports fingerprotection

Even if the distance from the hazard is short, we have prepared a lineup that includes safety light curtains with a detection capability of 14 mm.



Versatile muting function possible


Equipped with partial muting that disables only the beams where a workpiece passes through, and position detection muting that disables the beams while detecting the position of a machine or robot.

The blanking function disables specific beams of the Safety Light Curtain

If a part of the mechanical equipment is within the detection zone of the Safety Light Curtain, the relevant beams can be disabled. This is possible not only with non-moving parts but also with moving parts.

Setting up a warning zone to prevent unnecessary stoppage


Under normal use, if an intrusion occurs in the safety zone, the machine will stop immediately. However, use of a warning zone will only notify the operator that an intrusion has occurred. This can be used to prevent carelessness resulting in machine stoppage on the part of the operator.




Partial muting



Position detection muting




Fixed blanking



Floating blanking



Dividing the zone between seriesconnected sensors



A single sensor zone can also be divided

Easy and fast mounting with one-touch brackets*


EASY

Patented



OMRON has developed "one-touch" brackets which speed mounting to aluminum framing and reduce mounting time in half, when compared with existing models. This unique design allows for smooth horizontal movement, beam alignment is easy.

* Sold separately




Top and bottom blue LEDs enabling beam alignment





Simple positional alignment can be done using the blue LEDs at the top (TOP) and bottom (BTM) of the emitter and receiver. With the blue LEDs ON, you can see at a glance that the beams' positions are correctly aligned.




Laser pointer used to easily align the beams*




Use of the laser pointer allows simple alignment of the beams especially across long distances. This saves approximately 60% of installation time.



ADVANCED







Easy-to-understand diagnostics




Light curtain status can be immediately determined as the LED will light to indicate the status or possible error.










Industry First! Error indication while muting is in progress.



The days of searching through user manuals to find the cause of certain muting errors are long gone. Now these errors and their causes can be well understood.



|"Simple wiring connector" used to reduce wiring work by more than 50%*






The connector can be used to easily connect between an emitter and a receiver, reducing the required wiring time by more than 50%.

Less wiring also reduces the width of the terminal block, saving valuable space in the control panel.


Note: The simple wiring connector can be used for F3SJ-A/B in auto reset mode only, not for F3SJ-E.


*Comparison with existing OMRON products.



Tool for setting parameters and checking the system status








The "SD Manager" PC Setting Support Software helps reduce the time required for installing and troubleshooting the Safety Light Curtain.

Beam alignment is easier.



The incident light level can be displayed in a bar graph for each beam.

 The ambient incident light intensity can be checked.



The incident light level when the light emission of the Safety Light Curtain is stopped is displayed in a bar graph.

•The error log can be displayed.



The cause of the errors and countermeasures are both displayed.

Added the ENVIRONMENT RESISTANT type (F3SJ-B | P25-02TS) to the E3SJ series.

The coolant-resistant structure supports use in a severe work environment

ENVIRONMENT RESISTANT

Protects the sensor unit from direct exposure to the coolant.

The aluminum frame and transparent plate protect the sensor unit from direct exposure to the coolant. The cover protects the sensor's detection surface from collision with a workpiece, etc.



Protects the sensor from entry of the coolant that runs around the sensor.

The coolant-resistant sponge used inside the cover protects the sensor from entry of the coolant that runs around the sensor.



Note: The sensor may be affected depending on the type of the cutting oil. Check the oil type before use.

Achieving muting function without a controller




The muting function temporarily disables the light curtain when an object must pass through the detection zone, such as when supplying a workpiece to your equipment. In the past, this function required a dedicated muting controller, but now it is built into the F3SJ. To use the muting function, purchase the Muting Key Cap (for F3SJ-B: F39-CN10 and for F3SJ-A: F39-CN6) (sold separately). The muting function is enabled simply by replacing the Unit's cap with this Key Cap. In addition, a muting sensor that determines the muting timing, as well as a muting lamp that notices the muting status to other operators, should be connected to the F3SJ.

The muting time for the F3SJ-A can be set via the software tool.

Use example of a muting key cap for F3SJ-A

Built-in muting function

No controller required. Simply attach the Key Cap (sold separately) to the sensor.




Equipped with two muting functions



With F3SJ-A, the muting function temporarily disables the Safety Light Curtain when an object must pass through the detection zone, such as when supplying a workpiece to your equipment. "Partial muting," which further heightens the level of safety, and "position detection muting," which allows muting when the safety status can be determined by the position of a machine (such as a robot), have been newly added to the muting function.


Partial muting

Partial muting raises safety by muting only the beams of the Safety Light Curtain in the area where the workpiece passes through, while preventing muting in all other areas.



Position detection muting


This is used in applications where the workpiece is set in position each time by an operator, and then a turntable or positioning robot moves the workpiece to the area where the work is done. A limit switch or other means is used to detect when the robot is in a safe position, and muting is then applied.




		EASY type		BASIC type			ADVANCED type
		F3SJ-E	F3SJ-B	F3SJ-B-01TS	F3SJ-B-02TS		F3SJ-A
		For simple hand protection	A combina performan function	nce and		F(saf	or complex fety solutions
Application	Finger protection					•	
	Hand and arm protection	•	•	•	•		•
	Body protection						
Specification	Detection capability	25-mm dia.		25-mm dia.		14-mm dia.	20-mm dia.
	Beam gap	20 mm		20 mm		9 mm	15 mm
	Operating range	0.2 to 7 m	0.2 t	to 7 m	0.2 to 6 m		0.2 to 9 m *1
	Protective height	185 to 1,105 mm	185 to 2	2,065 mm	225 to 1,985 mm	245 to 1,271 mm	245 to 1,505 mm
	Number of beams	8 to 54	8 to 102 10 to 98		26 to 140	16 to 100	
Feature	PNP/NPN Selection	-		_			_
	External Test			-			
	Interlock	_			_		₽ -
	Pre-Reset	-		_			
	External Device Monitoring (EDM)	_					₽ -
	Auxiliary Output	-		_			
	Muting	_	П	_	П		П/П+⊒
	Blanking	-		_			
	Reduced Resolution						
	Warning Zone	_					
	Scan Code Selection		(Not re	equired for wired sy	nchronization)		
	Operating Range Selection	-		-			
	Response Time Adjustment	-		_			_
	Designated Beam Output	-		-			
Connection/ wiring	Cascade Connection	_		-		-	
-	Simple wiring connector	-		-			
Environmental resistance	Degree of protection	IP65		IP65			IP65
Accessory	Lamp	_		-			•
	Bluetooth communication unit	_		-			-
	SD Manager	_		-			•
	Laser pointer	•		•	-		•
More inform	nation	Page 18		Page 30	+		Page 66

Setting by DIP Switch Setting by Configuration Tool Setting by Wiring Setting by End Cap/Key Cap

		М	ore rugged – F3SG-R Seri	ies		
		F3SG-RA	F3SG-RR	F3SG-RE		
		OHROH		HOMIO		
		•	•	•	Finger protection	Application
•		•	•	•	Hand and arm protection	
	•				Body protection	
30-mm dia.	55-mm dia.	14-mm dia./30-mm dia.	14-mm dia./25-mm dia.	14-mm dia./30-mm dia.	Detection capability	Specification
25 mm	50 mm	10 mm/20 mm	10 mm/20 mm	10 mm/20 mm	Beam gap	
		0.3 to 10 m/0.3 to 20 m	0.3 to 10 m/0.3 to 17 m	0.3 to 10 m/0.3 to 20 m	Operating range	
245 to 2,495 mm	270 to 2,470 mm	160 to 2,080 mm/190 to 2,510 mm	240 to 1,920 mm	160 to 2,080 mm/190 to 2,510 mm	Protective height	
10 to 100	6 to 50	15 to 207/8 to 124	23 to 191/12 to 96	15 to 207/8 to 124	Number of beams	
				_	PNP/NPN Selection	Feature
		*2	*2	_	External Test	
		■ 🖳		_	Interlock	
		■ 📮		_	Pre-Reset	
		∞ 및 -	□ -	_	External Device Monitoring (EDM)	
		■ 🖳		_	Auxiliary Output	
		■ 📮		-	Muting	
		■ 🖳		-	Blanking	
				_	Reduced Resolution	
				_	Warning Zone	
				_	Scan Code Selection	
			-		Operating Range Selection	
				_	Response Time Adjustment	
				-	Designated Beam Output	
		-	-	_	Cascade Connection	Connection/ wiring
		-			Simple wiring connector	· ·······
		IP67	IP67, IP67G	IP67	Degree of protection	Environmental resistance
		•	•	_	Lamp	Accessory
		•	•	_	Bluetooth communication unit	
		SD Manager2	SD Manager2	_	SD Manager	
		•	•	•	Laser pointer	
		Refer to	o the F3SG-R Catalog (Cat. No	p. F094).	More information	





Safety Light Curtain

F3SJ-E

EASY type reduces implementation costs with 1/2 the mounting time.

- In pursuit of simple functions: Upon detection of personnel, the machine stops.
- Can be used for simple hand intrusion detection.
- Implementation costs can be significantly reduced.

Related information

Dimensions : Page 56 to 65 Function List : Page 103 to 100

Safety Precautions : Page 105 Precautions on Safety : Page 106 to 107

Ordering Information

Main Units

Safety Light Curtain

Application	Detection	etection Beam gap Opera		Protective height	Model	
Аррисации	capability	Bealli gap	Operating range	(mm)	PNP output	NPN output
Hand protection	Dia. 25 mm	20 mm	0.2 to 7 m	185 to 1,105	F3SJ-E□□□□P25 *1	F3SJ-E□□□□N25

Note: F3SJ-E uses a 3 m prewired discrete cable.

*1. For S-mark compatible model, the suffix "-S" is added to the model name.

(Example) F3SJ-E0185P25-S

Safety Light Curtain Model List

Please contact our sales representative.

F3SJ-E Series (20 mm pitch)

M	odel	Number of beams	Protective height [mm] *2	
PNP output *1	NPN output	Number of beams	Protective neight [mm] *2	
F3SJ-E0185P25	F3SJ-E0185N25	8	185	
F3SJ-E0225P25	F3SJ-E0225N25	10	225	
F3SJ-E0305P25	F3SJ-E0305N25	14	305	
F3SJ-E0385P25	F3SJ-E0385N25	18	385	
F3SJ-E0465P25	F3SJ-E0465N25	22	465	
F3SJ-E0545P25	F3SJ-E0545N25	26	545	
F3SJ-E0625P25	F3SJ-E0625N25	30	625	
F3SJ-E0705P25	F3SJ-E0705N25	34	705	
F3SJ-E0785P25	F3SJ-E0785N25	38	785	
F3SJ-E0865P25	F3SJ-E0865N25	42	865	
F3SJ-E0945P25	F3SJ-E0945N25	46	945	
F3SJ-E1025P25	F3SJ-E1025N25	50	1,025	
F3SJ-E1105P25	F3SJ-E1105N25	54	1,105	

^{*1.} For S-mark compatible model, the suffix "-S" is added to the model name. (Example) F3SJ-E0185P25-S

^{*2.} Protective height (mm) = Total sensor length

Accessories (Sold separately)

Relays with Forcibly Guided Contacts

Туре	Appearance	Specifications	Model	Remarks
G7SA Relays with		Nodes: 4 Contact type: 2A2B Rated switch load: 250 VAC 6A, 30 VDC 6A	G7SA-2A2B	For details on other models or socket models, refer to the
Forcibly Guided Contacts	9	Nodes: 4 Contact type: 3NO+1NC Rated switch load: 250 VAC 6A, 30 VDC 6A	G7SA-3A1B	OMRON's website.
G7S-□-E Relays with Forcibly Guided Contacts		Nodes: 6 Contact type: 4NO+2NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	G7S-4A2B-E	For details on other models or socket models, refer to the
		Nodes: 6 Contact type: 3NO+3NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	G7S-3A3B-E	OMRON's website.

Laser Pointer

Appearance	Output	Model	
0.00	Laser Pointer for F3SJ	F39-PTJ	

Spatter Protection Cover (2 covers per set, one for emitter and one for receiver) (10% Operating Range Attenuation)

Appearance	Model
	F39-HB□□□□ *

Protective Bar

Appearance	Model Remarks			
	F39-PB□□□□ *1	 2 Light Curtain brackets 4 mounting brackets 0 to 4 intermediate brackets for backside mounting (quantity required for the sensing width) 0 to 4 intermediate brackets for mounting to the sides (quantity required for the sensing width) 		
	F39-PB□□□□-S *1 *2	 1 Light Curtain bracket 2 mounting brackets 0 to 2 intermediate brackets for backside mounting (quantity required for the sensing width) 0 to 2 intermediate brackets for mounting to the sides (quantity required for the sensing width) 		

Note: The following are not provided with the Protective Bars.

- Safety Light Curtain
- Safety Light Curtain Top/Bottom Brackets
- Wall Mounting Screw Unit
- *1. The same four digits indicating protective height that are used in the Sensor model number ($\square\square\square\square$) are used in the part of the Protector model number.
- *2. Purchase the F39-PB (which contains two sets of brackets) to use Protective Bars for both the Emitter and Receiver.

Test rod (Sold separately)

77	
Diameter	Model
14mm dia.	F39-TRD14
20mm dia.	F39-TRD20
25mm dia.	F39-TRD25
30mm dia.	F39-TRD30

Mirror Column

Appearance	Applicable light curtain F3SJ Series Safety Light Curtain	Column height	Model
ı	Protective height up to 0880	990 mm	F39-SML0990
- 1	Protective height up to 1200	1,310 mm	F39-SML1310
	Protective height up to 1520	1,630 mm	F39-SML1630
(Operating range becomes 15% shorter than the rating)	Protective height up to 1840	1,950 mm	F39-SML1950

Sensor Mounting Bracket (Sold separately)

Appearance	Specifications	Model	Application	Remarks
	Top/bottom bracket	F39-LJB1	Top/bottom bracket for F3SJ-E/B	2 for an emitter, 2 for a receiver, total of 4 per set
	Intermediate bracket	F39-LJB2 *1 *2	In combination use with top/bottom bracket for F3SJ-E/B Can be used as free-location bracket.	1 set with 2 pieces
	One-touch bracket	F39-LJB3-M6 *1	One-touch bracket for F3SJ-E/B Supports M6 slide nut for aluminum frame.	
		One-touch bracket	F39-LJB3-M8 *2	One-touch bracket for F3SJ-E/B Supports M8 slide nut for aluminum frame.
9		F39-LJB3-M6K *1	Bracket to mount an intermediate	Hexagon socket head cap screws (M6 x 10) are included.
	One-touch M6 bracket One-touch M8 bracket	F39-LJB3-M8K *2	bracket to the aluminum frame with a single touch.	Hexagon socket head cap screws (M8 x 14) are included.
	Compatible mounting bracket	F39-LJB4	Mounting bracket used when replacing existing area sensors (F3SJ-A or F3SN) with the F3SJ-E/B.	2 for an emitter, 2 for a receiver, total of 4 per set
	Contact mount bracket	F39-LJB5	Bracket to closely contact the back side of the Sensor.	2 for an emitter, 2 for a receiver, total of 4 per set

Note: All the sensor mounting brackets for F3SJ-E are sold separately. ***1.** Combining F39-LJB2 and F39-LJB3-M6K makes F39-LJB3-M6. ***2.** Combining F39-LJB2 and F39-LJB3-M8K makes F39-LJB3-M8.

Specifications (For details, refer to the instruction manual or User's manual.)

Main Units

F3SJ-E□□□□**P25/N25**

	PNP output	F3SJ-E□□□□P25				
Model	NPN output	F3SJ-E□□□□N25				
Sensor type		Type 4 safety light curtain				
Setting tool con	nection *1	Parameter settings: Not available				
Safety category		Safety purpose of category 4, 3, 2, 1, or B				
Detection capa	bility	Opaque objects 25 mm in diameter				
Beam gap (P)		20 mm				
Number of bea	ms (n)	8 to 54				
Protective heig	ht (PH)	185 to 1,105 mm				
Lens diameter		Diameter 5 mm				
Operating rang	je *2	0.2 to 7 m				
Response time	ON to OFF	15 ms max.				
(under stable light incident condition)	OFF to ON	70 ms max.				
Startup waiting	time	2 s max.				
Power supply v	oltage (Vs)	SELV/PELV 24 VDC±20% (ripple p-p 10% max.)				
Consumption	PNP output	Emitter: Up to 22 beams: 41 mA max., 26 to 42 beams: 57 mA max., 46 to 54 beams: 63 mA max. Receiver: Up to 22 beams: 42 mA max., 26 to 42 beams: 47 mA max., 46 to 54 beams: 51 mA max.				
current (no load)	NPN output	Emitter: Up to 22 beams: 41 mA max., 26 to 42 beams: 57 mA max., 46 to 54 beams: 63 mA max. Receiver: Up to 22 beams: 40 mA max., 26 to 42 beams: 45 mA max., 46 to 54 beams: 48 mA max.				
Light source (emitte	nd wayolongth)	Infrared LED (870 nm)				
Effective aperture	• ,	Based on IEC 61496-2. Within ±2.5° for both emitter and receiver when the detection distance is 3 m or over				
Ellective aperture						
Safety outputs	PNP output	Two PNP transistor outputs, load current 200 mA max., residual voltage 2 V max. (except for voltage drop due to cable extension), Leakage current 1 mA max., load inductance 2.2 H max. *3, Maximum capacity load 1 μF *4				
(OSSĎ)	NPN output	Two NPN transistor outputs, load current 200 mA max., residual voltage 2 V max. (except for voltage drop due to cable extension), Leakage current 1 mA max., load inductance 2.2 H max. $*3$, Maximum capacity load 1 μ F $*4$				
Output operation	on mode	Safety output: On when receiving light				
Input voltage	PNP output	Test input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 3.0 mA) *5 OFF voltage: 0 V to 1/2 Vs or open (short circuit current: approx. 4.0 mA) *5				
input voitage	NPN output	Test input: ON voltage: 0 to 3 V (short circuit current: approx. 4.0 mA) OFF voltage: 1/2 Vs to Vs or open (short circuit current: approx. 3.0 mA) *5				
Mutual interfer prevention fun		Mutual interference prevention algorithm prevents interference in up to 3 sets.				
Test function		Self test (at power-ON and at power distribution) External test (emission stop function by test input)				
Protection circ	uit	Output short-circuit protection, and power supply reverse polarity protection				
Ambient tempe	erature	Operating: -10 to 55°C (non-freezing), Storage: -25 to 70°C				
Ambient humic	lity	Operating: 35% to 85% (no condensation), Storage: 35% to 95% RH				
Operating ambient I	ight intensity	Incandescent lamp: 3,000 lx max., Sunlight: 10,000 lx max.				
Insulation resis		$20~\mathrm{M}\Omega$ min. (at 500 VDC)				
Dielectric stren	igth	1,000 VAC 50/60 Hz, 1 min				
Degree of prote	ection	IP65 (IEC 60529)				
Vibration resis		Malfunction: 10 to 55 Hz, Multiple amplitude of 0.7 mm, 20 sweeps in X, Y, and Z directions				
Shock resistan		Malfunction: 100 m/s², 1,000 times each in X, Y, and Z directions				
Pollution degre	e	Pollution degree 3 (IEC 60664-1)				
Power cable		Connection method: Pull-out type, cable length 3 m Number of wires: Emitter: 5 wires, receiver: 6 wires Cable diameter: Dia. 6 mm Allowable bending radius: R5 mm				
Extension cabl	е	30 m max. * 6				
Material		Case: Aluminum Cap: ABS resin, PBT Optical cover: PMMA resin (acrylic) Cable: Oil resistant PVC				
Net Weight *7		Weight (g) = (protective height) x 1.59 + 330				
Gross Weight	* 8	Weight (g) = (protective height) x 2.6 + 800				
Accessories		Instruction Manual, Quick Installation Manual (QIM) *9				
Applicable star	ndards *10	IEC 61496-1, EN 61496-1, UL 61496-1, Type 4 ESPE (Electro-Sensitive Protective Equipment) IEC 61496-2, EN 61496-2, UL 61496-2, Type 4 AOPD (Active Opto-electronic Protective Devices) IEC 61508-1 to -3, EN 61508-1 to -3 SIL3 ISO 13849-1: 2015, EN ISO 13849-1: 2015 (PLe/Safety Category 4) UL 508, UL 1998, CAN/CSA C22.2 No.14, CAN/CSA C22.2 No.0.8				
		01 000, 01 1000, ONIVOON 022.2 110.11, ONIVOON 022.2 110.0.0				

- *1. Do not use the Support Software and Setting Console for F3SJ-A. Operation cannot be guaranteed.
 *2. Use of the Spatter Protection Cover causes a 10% maximum sensing distance attenuation.
 *3. The load inductance is the maximum value when the safety output frequently repeats ON and OFF. When you use the safety output at 4 Hz or less, the usable load inductance becomes larger.
- inductance becomes larger.

 44. These values must be taken into consideration when connecting elements including a capacitive load such as capacitor.

 55. The Vs indicates a voltage value in your environment.

 66. To extend a cable of the F3SJ-E, refer to the User's Manual (SCHG-733/732).

 77. The net weight is the weight of an emitter and a receiver.

 88. The gross weight is the weight of an emitter, a receiver, included accessories and a package.

 99. Mounting brackets and test rod are sold separately.

 10. Refer to Safety Precautions for information about Legislation and Standards.

Indicator

Emitter

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light.	
Stable-state indicator	STB	Turns ON when incidence level is more than 170% of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns OFF when safety output is OFF.	Red: Blinks when the F3SJ-E enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-E enters a lockout on the receiver.	Blinks when the F3SJ-E enters a lockout on the emitter.
Power indicator	POWER	Turns ON while the power of the emitter is ON.	Blinks when the F3SJ-E enters a lockout due to power voltage/noise.
Test indicator	TEST		Blinks when external test is being performed.
Bottom-beam-state indicator	втм	Turns ON when the bottom beam is receiving light.	

Receiver

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light.	
Stable-state indicator	STB	Turns ON when incidence level is more than 170% of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns OFF when safety output is OFF.	Red: Blinks when the F3SJ-E enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-E enters a lockout on the emitter.	Blinks when the F3SJ-E enters a lockout on the receiver.
Communication indicator	СОМ	Turns ON when communication between emitter and receiver is established.	Blinks when the F3SJ-E enters lockout due to a communication error between receiver and emitter.
Configuration indicator	CFG		Blinks when the F3SJ-E enters lockout due to a model type error between receiver and emitter.
Internal error indicator	INTERNAL		Blinks when the F3SJ-E enters a lockout due to an internal error.
Bottom-beam-state indicator	втм	Turns ON when the bottom beam is receiving light.	

Accessories

Laser Pointer

Item Model	F39-PTJ
Applicable sensor	F3SJ Series
Power supply voltage	4.65 or 4.5 VDC
Battery	Three button batteries (SR44 or LR44)
Battery life *	SR44: 10 hours of continuous operation, LR44: 6 hours of continuous operation
Light source	Red semiconductor laser (wavelength: 650 nm, 1 mW max. JIS class 2, EN/IEC class 2, FDA class II)
Spot diameter (typical value)	6.5 mm at 10 m
Ambient temperature	Operating: 0 to 40°C Storage: -15 to 60°C (with no icing or condensation)
Ambient humidity	Operating and storage: 35% to 85% (with no condensation)
Material	Laser module case: aluminum Mounting bracket: aluminum and stainless
Weight	Approx. 220 g (packed)
Accessories	Laser safety standard labels (EN: 1, FDA: 3) Button batteries (SR44: 3), instruction manual


^{*} Battery life varies depending on a battery used.

Connections

Emitter


Basic Wiring Diagram

Minimum wiring required to check the operation of the F3SJ-E [PNP Output]



Minimum wiring required to check the operation of the F3SJ-E [NPN Output]

Receiver




F3SJ-E


Input/Output Circuit Diagram

[PNP Output]

Entire Circuit Diagram




Input circuit diagram by function




[NPN Output]

Entire Circuit Diagram



Input circuit diagram by function




Connection Circuit Examples

Wiring for single F3SJ-E application [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-E P25 Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring for single F3SJ-E application [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-E□□□□N25 Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring to connect a F3SJ-E with a controller G9SP [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-E□□□□□P25 Safety Controller G9SP Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.





Wiring to connect a F3SJ-E with a controller G9SA-301 [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-E□□□□□P25 Safety Relay Unit G9SA-301 24V AC/DC Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual


Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.





- * If an emergency stop switch is not used, connect safety output 1 to T12 terminal and safety output 2 to T23 directly.
- S1: External test/lockout reset switch (connect to 0 V if a switch is not required)
- S2: Interlock reset switch
 S3: Emergency stop switch (force-opening contact) (A165E, A22E)
 KM1,KM2: Safety relay with force-guided contact (G7SA) or magnetic contactor




Wiring to connect a F3SJ-E with a controller G9SA-301-P [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-E□□□□N25 Safety Relay Unit G9SA-301-P 24V DC Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.



Note: 1. As the G9SP Safety Controller is a PNP output type, it cannot be connected to the F3SJ-E□□□□N25. Also, a Safety Controller with PNP output cannot be connected to the F3SJ-E□□□□N25.

2. The G9SA-301-P is a safety relay unit only for NPN output.

Safety Light Curtain

F3SJ-B

Basic Type with a combination of performance and functionality

- Up to three sets of series-connected sensors.
- The muting function is enabled simply with Muting Key Cap.
- Comes standard with interlock and auxiliary output functions.

Related information

: Page 56 to 65 Dimensions **Function List** : Page 103 to 100

Safety Precautions : Page 105 Precautions on Safety: Page 106 to 107

Ordering Information

Main Units

Safety Light Curtain

Application	Detection	Detection Beam gap Or		Operating range Protective height	Model	
Application	capability	Bealli gap	Operating range	(mm)	PNP output	NPN output
Hand protection	Dia. 25 mm	20 mm	0.2 to 7 m	185 to 2,065	F3SJ-B□□□□P25 *1	F3SJ-B□□□□N25
Hand protection	Dia. 25 mm	20 mm	0.2 to 7 m	185 to 2,065	F3SJ-B□□□□P25-01TS *2	
Environmental resistance	Dia. 25 mm	20 mm	0.2 to 6 m	225 to 1,985	F3SJ-B□□□□P25-02TS *2	

^{*1.} For S-mark compatible model, the suffix "-S" is added to the model name. (except for models with the suffix "-01TS" or "-02TS".) (Example) F3SJ-E0185P25-S

Safety Light Curtain Model List

Please contact our sales representative.

F3SJ-B Series (20 mm pitch)

F3SJ-B-01TS Series (20 mm pitch) F3SJ-B-02TS Series (20 mm pitch)

	Model				Protective height [mm] *
PNP output	NPN output	PNP output	PNP output	Number of beams	Frotective neight [mm] *
F3SJ-B0185P25	F3SJ-B0185N25	F3SJ-B0185P25-01TS	-	8	185
F3SJ-B0225P25	F3SJ-B0225N25	F3SJ-B0225P25-01TS	F3SJ-B0225P25-02TS	10	225
F3SJ-B0305P25	F3SJ-B0305N25	F3SJ-B0305P25-01TS	F3SJ-B0305P25-02TS	14	305
F3SJ-B0385P25	F3SJ-B0385N25	F3SJ-B0385P25-01TS	F3SJ-B0385P25-02TS	18	385
F3SJ-B0465P25	F3SJ-B0465N25	F3SJ-B0465P25-01TS	F3SJ-B0465P25-02TS	22	465
F3SJ-B0545P25	F3SJ-B0545N25	F3SJ-B0545P25-01TS	F3SJ-B0545P25-02TS	26	545
F3SJ-B0625P25	F3SJ-B0625N25	F3SJ-B0625P25-01TS	F3SJ-B0625P25-02TS	30	625
F3SJ-B0705P25	F3SJ-B0705N25	F3SJ-B0705P25-01TS	F3SJ-B0705P25-02TS	34	705
F3SJ-B0785P25	F3SJ-B0785N25	F3SJ-B0785P25-01TS	F3SJ-B0785P25-02TS	38	785
F3SJ-B0865P25	F3SJ-B0865N25	F3SJ-B0865P25-01TS	F3SJ-B0865P25-02TS	42	865
F3SJ-B0945P25	F3SJ-B0945N25	F3SJ-B0945P25-01TS	F3SJ-B0945P25-02TS	46	945
F3SJ-B1025P25	F3SJ-B1025N25	F3SJ-B1025P25-01TS	F3SJ-B1025P25-02TS	50	1,025
F3SJ-B1105P25	F3SJ-B1105N25	F3SJ-B1105P25-01TS	F3SJ-B1105P25-02TS	54	1,105
F3SJ-B1185P25	F3SJ-B1185N25	F3SJ-B1185P25-01TS	F3SJ-B1185P25-02TS	58	1,185
F3SJ-B1265P25	F3SJ-B1265N25	F3SJ-B1265P25-01TS	F3SJ-B1265P25-02TS	62	1,265
F3SJ-B1345P25	F3SJ-B1345N25	F3SJ-B1345P25-01TS	F3SJ-B1345P25-02TS	66	1,345
F3SJ-B1425P25	F3SJ-B1425N25	F3SJ-B1425P25-01TS	F3SJ-B1425P25-02TS	70	1,425
F3SJ-B1505P25	F3SJ-B1505N25	F3SJ-B1505P25-01TS	F3SJ-B1505P25-02TS	74	1,505
F3SJ-B1585P25	F3SJ-B1585N25	F3SJ-B1585P25-01TS	F3SJ-B1585P25-02TS	78	1,585
F3SJ-B1665P25	F3SJ-B1665N25	F3SJ-B1665P25-01TS	F3SJ-B1665P25-02TS	82	1,665
F3SJ-B1745P25	F3SJ-B1745N25	F3SJ-B1745P25-01TS	F3SJ-B1745P25-02TS	86	1,745
F3SJ-B1825P25	F3SJ-B1825N25	F3SJ-B1825P25-01TS	F3SJ-B1825P25-02TS	90	1,825
F3SJ-B1905P25	F3SJ-B1905N25	F3SJ-B1905P25-01TS	F3SJ-B1905P25-02TS	94	1,905
F3SJ-B1985P25	F3SJ-B1985N25	F3SJ-B1985P25-01TS	F3SJ-B1985P25-02TS	98	1,985
F3SJ-B2065P25	F3SJ-B2065N25	F3SJ-B2065P25-01TS	-	102	2,065

^{*} Protective height (mm) = Total sensor length

^{*2.} The F3SJ-B series with the suffix "-01TS" or "02TS" have different functions. Refer to page 37 for details.

Note: 1. The models with the suffix "-01TS" or "-02TS are the PNP type only.

^{2.} The test input logic is inverted for the models with the suffix "-01TS"

^{3.} Reset mode is fixed with auto reset mode for the models with the suffix "-01TS" or "-02TS".

Accessories (Sold separately)

Single-Ended Cable (2 covers per set, one for emitter and one for receiver) *

For wiring with safety circuit such as single safety relay, safety relay unit, and safety controller

Appearance	Cable length	Specifications	Model
	3 m		F39-JD3A
	7 m	M12 connector (8-pin)	F39-JD7A
	10 m		F39-JD10A
	15 m		F39-JD15A
	20 m		F39-JD20A

^{*}The cable for emitter and the cable for receiver are available separately. Add '-L' for emitter or '-D' for receiver to the end of the model number when you order.

Single-Ended Cable for Emitter: F39-JD A-L, Single-Ended Cable for Receiver: F39-JD A-D

Note: To extend the cable length to 20 m or more, add the F39-JD□B Double-Ended Cable.

Example: When using a cable of 30 m, connect the F39-JD10A Single-Ended Cable with the F39-JD20B Double-Ended Cable.

Double-Ended Cable (2 covers per set, one for emitter and one for receiver) *

Control unit for connection with F3SP-B1P, to extend the length under series connection


Appearance	Cable length	Specifications	Model
	0.5 m		F39-JDR5B
	1 m 3 m		F39-JD1B
		M12 connector (8-pin)	F39-JD3B
	5 m		F39-JD5B
	7 m		F39-JD7B
	10 m		F39-JD10B
•	15 m		F39-JD15B
	20 m		F39-JD20B

^{*}The cable for emitter and the cable for receiver are available separately. Add '-L' for emitter or '-D' for receiver to the end of the model number when you order.

Double-Ended Cable for Emitter: F39-JD B-L, Double-Ended Cable for Receiver: F39-JD B-D

Note: To extend the cable length to 20 m or more, use the Double-Ended Cables in combination.

Example: When using a cable of 30 m, connect the F39-JD10B Double-Ended Cable with the F39-JD20B Double-Ended Cable.




Series-connection Cable (2 covers per set, one for emitter and one for receiver)

Type	Appearance	Cable length	Model	Application
Series connection cable for extension	*	0.2 m	F39-JBR2W *	For series connection

^{*} This product is for F3SJ-B only.

Note: The Double-Ended Cable (up to 7 m: F39-JD7B) can be added to extend the cable length between the series-connected sensors. Cable length between sensors: 7 m max. (not including series connection cable (F39-JBR2W) and power cable)


<Connection example>



Simple wiring connector system (Order the F39-CN5 and Cables for Simple Wiring.)

Simple wiring connector

Appearance	Model	Application
	F39-CN5	To reduce wiring



Cable for simple wiring * (2 cables per set, one double-ended cable and one single-ended cable)

Appearance	Con	tents	Cable length	Model	
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0303BA	
	Single-Ended Cable	F39-JD3A-D	3 m	F39-3D0303BA	
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0307BA	
	Single-Ended Cable	F39-JD7A-D	7 m	F39-3D0307BA	
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0310BA	
	Single-Ended Cable	F39-JD10A-D	10 m	F39-JD0310DA	
	Double-Ended Cable	F39-JD5B-L	5 m	E20 ID0E02BA	
(F)	Single-Ended Cable	F39-JD3A-D	3 m	F39-JD0503BA	
	Double-Ended Cable	F39-JD5B-L	5 m	F39-JD0507BA	
	Single-Ended Cable	F39-JD7A-D	7 m		
	Double-Ended Cable	F39-JD5B-L	5 m	F20 ID0540D4	
	Single-Ended Cable	F39-JD10A-D	10 m	F39-JD0510BA	
	Double-Ended Cable	F39-JD10B-L	10 m	F20 ID4002DA	
	Single-Ended Cable	F39-JD3A-D	3 m	F39-JD1003BA	
	Double-Ended Cable	F39-JD10B-L	10 m	F20 ID4007D4	
	Single-Ended Cable	F39-JD7A-D	7 m	F39-JD1007BA	
	Double-Ended Cable	F39-JD10B-L	10 m	F20 ID4040BA	
	Single-Ended Cable	F39-JD10A-D	10 m	F39-JD1010BA	

Note: A double-ended cable and single-ended cable with other cable lengths than those listed above can also be used in combination. Please contact your OMRON sales representative for details.

* Although the double-ended cable for the emitter is used for the emitter in the above figure, it can also be used for the receiver.

Relays with Forcibly Guided Contacts

Type	Appearance	Specifications	Model	Remarks
G7SA Relays with Forcibly Guided Contacts		Nodes: 4 Contact type: 2NO+2NC Rated switch load: 250 VAC 6A, 30 VDC 6A	G7SA-2A2B	For details on other models or socket
	2	Nodes: 4 Contact type: 3NO+1NC Rated switch load: 250 VAC 6A, 30 VDC 6A	G7SA-3A1B	 models, refer to the OMRON's website.
G7S-□-E Relays with Forcibly Guided Contacts		Nodes: 6 Contact type: 4NO+2NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	For details on other models or socket	
		Nodes: 6 Contact type: 3NO+3NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	G7S-3A3B-E	models, refer to the OMRON's website.

Test rod (Sold separately)

Diameter	Model
14mm dia.	F39-TRD14
20mm dia.	F39-TRD20
25mm dia.	F39-TRD25
30mm dia.	F39-TRD30

Control Unit (Can not be used as a muting system)

(Dedicated PNP output type)

Appearance	Output	Model	Remarks
The state of the s	Relay, 3NO+1NC	F3SP-B1P *	For connection with F3SJ-B, use a double-ended cable F39-JD□B.

^{*} F3SJ for NPN output type cannot be connected.

Wire-saving Devices

Туре	Appearance	Specifications	Model	Remarks
		Model with PNP Muting Sensor Output	F39-TC5P01	
Connector Terminal Box/		Model with PNP Override Input	F39-TC5P02 Safety Light Curtains and Muting Se	Significantly reduces amount of wiring between Safety Light Curtains and Muting Sensors. IP67 model for mounting at Sensor installation
Muting Terminals *2		Model with NPN Muting Sensor Output	F39-TC5N01	site. For details, refer to the OMRON's website.
		Model with NPN Override Input	F39-TC5N02	of details, roler to the district website.
Safety Terminal Relays *2		PNP output relay, SPDT-NO	F3SP-T01 *1	Significantly reduces amount of wiring between Safety Light Curtains and Muting Sensors. For details, refer to the OMRON's website.

*1. F3SJ for NPN output type cannot be connected.
*2. The models with the suffix "-01TS" cannot be connected.
Note: Orders for F39-TC5 Series and F3SP-T01 have been discontinued at the end of May 2020.

Laser Pointer

Appearance	Output	Model	
8.	Laser Pointer for F3SJ	F39-PTJ *	

* It cannot be mounted to the models with the suffix "-02TS".

Spatter Protection Cover (2 covers per set, one for emitter and one for receiver) (10% Operating Range Attenuation)

Appearance	Model
	F39-HB□□□□ *1 *2

^{*1.} The same 4-digit numbers as the protective heights (□□□□ in the light curtain model names) are substituted by in the model names.

*2. It cannot be mounted to the models with the suffix "-02TS".

Protective Bar

Appearance	Model	Remarks
	F39-PB□□□□ *1	 2 Light Curtain brackets 4 mounting brackets 0 to 4 intermediate brackets for backside mounting (quantity required for the sensing width) 0 to 4 intermediate brackets for mounting to the sides (quantity required for the sensing width)
	F39-PB□□□□-S *1 *2	 1 Light Curtain bracket 2 mounting brackets 0 to 2 intermediate brackets for backside mounting (quantity required for the sensing width) 0 to 2 intermediate brackets for mounting to the sides (quantity required for the sensing width)

Note: The following are not provided with the Protective Bars.

- ·Safety Light Curtain
- Safety Light Curtain Top/Bottom Brackets
 Wall Mounting Screw Unit
- *1. The same four digits indicating protective height that are used in the Sensor model number ($\Box\Box\Box\Box$) are used in the part of the Protector model number. *2. Purchase the F39-PB $\Box\Box\Box\Box$ (which contains two sets of brackets) to use Protective Bars for both the Emitter and Receiver.

Mirror Column

Appearance	Applicable light curtain F3SJ Series Safety Light Curtain	Column height	Model
1	Protective height up to 0880	990 mm	F39-SML0990
- 1	Protective height up to 1200	1,310 mm	F39-SML1310
1	Protective height up to 1520	1,630 mm	F39-SML1630
(Operating range becomes 15% shorter than the rating)	Protective height up to 1840	1,950 mm	F39-SML1950

Sensor mounting bracket (Sold separately)

Appearance	Specifications	Model	Application	Remarks
	Top/bottom bracket	F39-LJB1	Top/bottom bracket for F3SJ-E/B	2 for an emitter, 2 for a receiver, total of 4 per set
	Intermediate bracket	F39-LJB2 *1 *2	In combination use with top/bottom bracket for F3SJ-E/B Can be used as free-location bracket.	1 set with 2 pieces
3-	One-touch bracket	F39-LJB3-M6 *1	One-touch bracket for F3SJ-E/B Supports M6 slide nut for aluminum frame.	1 set with 2 pieces
		F39-LJB3-M8 *2	One-touch bracket for F3SJ-E/B Supports M8 slide nut for aluminum frame.	
	One-touch M6 bracket	F39-LJB3-M6K *1	Bracket to mount an intermediate bracket to the aluminum frame with	Hexagon socket head cap screws (M6 x 10) are included.
	One-touch M8 bracket	F39-LJB3-M8K *2	a single touch.	Hexagon socket head cap screws (M8 x 14) are included.
	Compatible mounting bracket	F39-LJB4	Mounting bracket used when replacing existing area sensors (F3SJ-A or F3SN) with the F3SJ-E/B.	2 for an emitter, 2 for a receiver, total of 4 per set
	Contact mount bracket	F39-LJB5	Bracket to closely contact the back side of the Sensor.	2 for an emitter, 2 for a receiver, total of 4 per set

^{*1.} Combining F39-LJB2 and F39-LJB3-M6K makes F39-LJB3-M6.

End Cap

Appearance	Model	Remarks
	F39-CN11 *	For both emitter and receiver. The End Cap can be purchased if lost. (Case: Black)

^{*} This product is for F3SJ-B only.

Key Cap for Muting

Appearance	Model	Remarks
	F39-CN10 *1 *2	A cap to be attached to the main unit to enable muting function. Attach it to either an emitter or a receiver. (Case: orange)

^{*1.} This product is for F3SJ-B only.

^{*2.} Combining F39-LJB2 and F39-LJB3-M8K makes F39-LJB3-M8.

^{*2.} The models with the suffix "-01TS" cannot be connected.

Specifications (For details, refer to the instruction manual or User's manual.)

Main Units

F3SJ-B□□□□P25/N25

Model PNP output		F3SJ-B□□□□P25			
	NPN output	F3SJ-B□□□N25			
Sensor type		Type 4 safety light curtain			
		Parameter settings: Not available			
Safety category		Safety purpose of category 4, 3, 2, 1, or B			
Detection capability		Opaque objects 25mm in diameter			
Beam gap (P)		20 mm			
		8 to 102			
Protective height (PH) Lens diameter		185 to 2,065 mm Diameter 5 mm			
Operating range *2		0.2 to 7 m			
Response time		15 ms max. (response time at 1 set connection, series connection of 2 sets or 3 sets)			
(under stable light					
incident condition)		70 ms max. (response time at 1 set connection, series connection of 2 sets or 3 sets)			
Startup waiting		2 s max.			
Power supply v	oltage (Vs)	SELV/PELV 24 VDC±20% (ripple p-p 10% max.)			
Consumption current (no load)	PNP output	Emitter: Up to 22 beams: 52 mA max., 26 to 42 beams: 68 mA max., 46 to 62 beams: 75 mA max., 66 to 82 beams: 88 mA max., 86 to 102 beams: 101 mA max. Receiver: Up to 22 beams: 45 mA max., 26 to 42 beams: 50 mA max., 46 to 62 beams: 56 mA max., 66 to 82 beams: 61 mA max., 86 to 102 beams: 67 mA max.			
	NPN output	Emitter: Up to 22 beams: 52 mA max., 26 to 42 beams: 68 mA max., 46 to 62 beams: 75 mA max., 66 to 82 beams: 88 mA max., 86 to 102 beams: 101 mA max. Receiver: Up to 22 beams: 47 mA max., 26 to 42 beams: 52 mA max., 46 to 62 beams: 58 mA max., 66 to 82 beams: 63 mA max., 86 to 102 beams: 69 mA max.			
Light source (emitte		Infrared LED (870 nm)			
Effective aperture	angle (EAA)	Based on IEC 61496-2. Within +/-2.5° for both emitter and receiver when the detection distance is 3 m or over			
Safety outputs	PNP output	Two PNP transistor outputs, load current 200 mA max., residual voltage 2 V max. (except for voltage drop due to cable extension), Leakage current 1 mA max., load inductance 2.2 H max. *3, Maximum capacity load 1 µF *4			
(OSSD)	NPN output	Two NPN transistor outputs, load current 200 mA max., residual voltage 2 V max. (except for voltage drop due t cable extension), Leakage current 1 mA max., load inductance 2.2 H max. $*3$, Maximum capacity load 1 μ F $*4$			
Auxiliary	PNP output	One PNP transistor outputs, load current 100 mA max., residual voltage 2 V max. (except for voltage drop due to cable extension), leak current 1 mA max.			
NPN output		One NPN transistor outputs, load current 100 mA max., residual voltage 2 V max. (except for voltage drop due to cable extension), leak current 1 mA max.			
Output operation mode		Safety output: On when receiving light Auxiliary output: - Reverse output of safety output for a basic system - ON when muting/override for a muting system			
Input voltage	PNP output	Test input, Interlock select input, Reset input, Muting input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 3.0 mA) *5, OFF voltage: 0 V to 1/2 Vs or open (short circuit current: approx. 4.0 mA) * External device monitoring input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 6.0 mA) *5, OFF voltage: open			
	NPN output	Test input, Interlock select input, Reset input, Muting input: ON voltage: 0 to 3 V (short circuit current: approx. 4.0 mA), OFF voltage:1/2 Vs to Vs or open (short circuit current: approx. 3.0 mA) *5 External device monitoring input: ON voltage: 0 to 3 V (short circuit current: approx. 5.5 mA) *5, OFF voltage: open			
Mutual interfer		Mutual interference prevention algorithm prevents interference in up to 3 sets.			
Series connect		Time division emission by series connection Number of connections: up to 3 sets (between F3SJ-Bs only)Other models cannot be connected. Total number of beams: up to 192 beams Cable length between sensors: 7 m max. (not including series connection cable (F39-JBR2W) and power cable)			
Test function		Self test (at power-ON and at power distribution) External test (emission stop function by test input)			
Safety-related functions		Interlock (basic system) External device monitoring (basic system) Muting (muting system) Override (muting system)			
Connection type		Connector method (M12, 8-pin)			
Protection circuit		Output short-circuit protection, and power supply reverse polarity protection			
		Operating: -10 to 55°C (non-freezing), Storage: -25 to 70°C			
_		Operating: 35% to 85% (no condensation), Storage: 35% to 95% RH			
		Incandescent lamp: 3,000 lx max., Sunlight: 10,000 lx max.			
Insulation resistance		20 M $Ω$ min. (at 500 VDC)			
Dielectric strength		1,000 VAC 50/60 Hz, 1 min			
Degree of protection		IP65 (IEC 60529)			
Vibration resistance		Malfunction: 10 to 55 Hz, Multiple amplitude of 0.7 mm, 20 sweeps in X, Y, and Z directions			
Shock resistance		Malfunction: 100 m/s², 1,000 times each in X, Y, and Z directions			
Pollution degre	e	Pollution degree 3 (IEC 60664-1)			

Power cable	Connection method: Prewired connector cable, cable length 0.3 m, connector type (M12, 8-pin), connector: IP67 rated (when mated) Number of wires: 8 wires Cable diameter: Dia. 6 mm Allowable bending radius: R5 mm
Extension cable	30 m max.
Material	Case: Aluminum Cap: ABS resin, PBT Optical cover: PMMA resin (acrylic) Cable: Oil resistant PVC
Net Weight *6	Weight (g) = (protective height) x 1.62 + 110
Gross Weight *7	Weight (g) = (protective height) x 2.7 + 500
Accessories	Instruction Manual, Quick Installation Manual (QIM) *8
Applicable standards *9	IEC 61496-1, EN 61496-1, UL 61496-1, Type 4 ESPE (Electro-Sensitive Protective Equipment) IEC 61496-2, EN 61496-2, UL 61496-2, Type 4 AOPD (Active Opto-electronic Protective Devices) IEC 61508-1 to -3, EN 61508-1 to -3 SIL3 ISO 13849-1: 2015, EN ISO 13849-1: 2015 (PLe/Safety Category 4) UL 508, UL 1998, CAN/CSA C22.2 No.14, CAN/CSA C22.2 No.0.8

- *1. Do not use the Support Software and Setting Console for F3SJ-A. Operation cannot be guaranteed.
- *2. Use of the Spatter Protection Cover causes a 10% maximum sensing distance attenuation.
- *3. The load inductance is the maximum value when the safety output frequently repeats ON and OFF. When you use the safety output at 4 Hz or less, the usable load inductance becomes larger.
- ***4.** These values must be taken into consideration when connecting elements including a capacitive load such as capacitor. ***5.** The Vs indicates a voltage value in your environment.
- ***6.** The net weight is the weight of an emitter and a receiver.
- *7. The gross weight is the weight of an emitter, a receiver, included accessories and a package.
- *8. Mounting brackets are sold separately.
- *9. Refer to Safety Precautions for information about Legislation and Standards.

Indicator (F3SJ-B□□□□P25/N25)

Emitter

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light.	Blinks during muting/override, or when cap error or connection error occurs.
Stable-state indicator	STB	Turns ON when incidence level is more than 170% of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns OFF when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the receiver.	Blinks when the F3SJ-B enters a lockout on the emitter.
Power indicator	POWER	Turns ON while the power of the emitter is ON.	Blinks when the F3SJ-B enters a lockout due to power voltage/noise.
Test indicator	TEST		Blinks when external test is being performed.
Muting error indicator	MUTING ERROR		Blinks during a muting error.
Muting input 1 indicator	MUTE1	Turns ON when muting input 1 is ON under the muting system.	
Muting input 2 indicator	MUTE2	Turns ON when muting input 2 is ON under the muting system.	
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.	Blinks during muting/override.

Receiver

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	TOP	Turns ON when the top beam is receiving light.	Blinks during muting/override, or when cap error or connection error occurs.
Stable-state indicator	STB	Turns ON when incidence level is more than 170% of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns OFF when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the emitter.	Blinks when the F3SJ-B enters a lockout on the receiver.
Communication indicator	СОМ	Turns ON when communication between emitter and receiver is established.	Blinks when the F3SJ-B enters lockout due to a communication error between receiver and emitter.
Configuration indicator	CFG		Blinks when the F3SJ-B enters lockout due to a model type error between receiver and emitter.
Internal error indicator	INTERNAL		Blinks when the F3SJ-B enters a lockout due to an internal error.
Interlock indicator	INT -LK	Turns ON when the F3SJ-B is in interlock state.	Blinks when the F3SJ-B enters a lockout due to a wiring error.
External device monitoring indicator	EDM	Turns ON when an input is given to external device monitoring input. *1 *2	Blinks when the F3SJ-B enters a lockout due to an external device monitoring error.
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.	Blinks during muting/override.

- 734) or the specifications of the models with the suffix "-01TS".

Main Units

F3SJ-B□□□□P25-01TS/-02TS

Model		F3SJ-B□□□□P25-01TS	F3SJ-B□□□□P25-02TS		
Sensor type		Type 4 safety light curtain			
Setting tool connection *1		Parameter settings: Not available			
Safety category		Safety purpose of category 4, 3, 2, 1, or B			
Detection capability		Opaque objects 25mm in diameter			
Beam gap (P)		20 mm			
Number of bear	ms (n)	8 to 102	10 to 98		
Protective heig	ht (PH)	185 to 2,065 mm	225 to 1,985 mm		
Lens diameter		Diameter 5 mm			
Operating rang	е	0.2 to 7 m *2	0.2 to 6 m		
Response time	ON to OFF	15 ms max. (response time at 1 set connection, series co	onnection of 2 sets or 3 sets)		
(under stable light	OFF to ON	70 ms max. (response time at 1 set connection, series co	unportion of 2 sats or 3 sats)		
incident condition)		, ·	inflection of 2 sets of 3 sets)		
Startup waiting		2 s max.			
Power supply ve	oitage (vs)	SELV/PELV 24 VDC±20% (ripple p-p 10% max.)			
	Emitter	Up to 22 beams: 52 mA max., 26 to 42 beams: 68 mA max., 46 to 62 beams: 75 mA max.,	Up to 22 beams: 52 mA max., 26 to 42 beams: 68 mA max., 46 to 62 beams: 75 mA max.,		
Consumption	Lillittei	66 to 82 beams: 88 mA max., 86 to 102 beams: 101 mA max.			
current		Up to 22 beams: 45 mA max., 26 to 42 beams: 50 mA	Up to 22 beams: 45 mA max., 26 to 42 beams: 50 mA		
(no load)	Receiver	max., 46 to 62 beams: 56 mA max.,	max., 46 to 62 beams: 56 mA max.,		
		66 to 82 beams: 61 mA max., 86 to 102 beams: 67 mA max.	66 to 82 beams: 61 mA max., 86 to 98 beams: 66 mA max.		
Light source (e	mitted	Infrared LED (870 nm)			
wavelength)					
Effective aperture	angle (EAA)	Based on IEC 61496-2. Within +/-2.5° for both emitter and			
Safety outputs	(OSSD)	Two PNP transistor outputs, load current 200 mA max., r			
•	. ,	cable extension), Leakage current 1 mA max., load induc	, , ,		
Auxiliary output	ıt	One PNP transistor outputs, load current 100 mA max., r cable extension), leak current 1 mA max.	esiduai voltage z v max. (except for voltage grop que to		
Output operation mode		Safety output: On when receiving light Auxiliary output: Reverse output of safety output	Safety output: On when receiving light Auxiliary output: • Basic system Reverse output of safety output • Muting system On during muting/override		
Input voltage		Test input ON voltage: 0 V to 1/2 Vs or open (short circuit current: approx. 4.0 mA) \$5 OFF voltage: Vs-3 V to Vs (short circuit current: approx. 3.0 mA) \$5 Reset input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 3.0 mA) \$5 OFF voltage: 0 V to 1/2 Vs or open (short circuit current: approx. 4.0 mA) \$5 External device monitoring input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 6.0 mA) \$5 OFF voltage: open	Test input, Interlock select input, Reset input, Muting input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 3.0 mA) *5 OFF voltage: 0 V to 1/2 Vs or open (short circuit current: approx. 4.0 mA) *5 External device monitoring input: ON voltage: Vs-3 V to Vs (short circuit current: approx. 6.0 mA) *5 OFF voltage: open		
Mutual interfere		Mutual interference prevention algorithm prevents interference in up to 3 sets.			
prevention function Series connection		Time division emission by series connection Number of connections: up to 3 sets (between F3SJ-BP25-01TSs only) Other models cannot be connected. Total number of beams: up to 192 beams Cable length between sensors: 7 m max. (not including series connection cable (F39-JBR2W) and power cable)	Time division emission by series connection Number of connections: up to 3 sets (between F3SJ-BDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDDD		
Test function		Self test (at power-ON and at power distribution) External test (emission stop function by test input)			
Safety-related functions		External device monitoring	External device monitoring (basic system) Muting (muting system) Override (muting system)		
Connection type		Connector method (M12, 8-pin)			
Protection circuit		Output short-circuit protection, and power supply reverse polarity protection			
Ambient temperature		Operating: -10 to 55°C (non-freezing), Storage: -25 to 70°C			
Ambient humid	lity	Operating: 35% to 85% (no condensation), Storage: 35% to 95% RH			
Operating ambient	light intensity	, , ,			
Insulation resis	stance				
Dielectric strength		1,000 VAC 50/60 Hz, 1 min			
Degree of protection		IP65 (IEC 60529)			
Vibration resist		Malfunction: 10 to 55 Hz, Multiple amplitude of 0.7 mm, 2	0 sweeps in X, Y, and Z directions		
Shock resistan		Malfunction: 100 m/s ² , 1,000 times each in X, Y, and Z di			
uni			· · · · · ·		

Pollution degree	Pollution degree 3 (IEC 60664-1)		
Power cable	Connection method: Prewired connector cable, cable len rated (when mated) Number of wires: 8 wires Cable diameter: Dia. 6 mm Allowable bending radius: R5 mm	gth 0.3 m, connector type (M12, 8-pin), connector: IP67	
Extension cable	30 m max.		
Material	Case: Aluminum Cap: ABS resin, PBT Optical cover: PMMA resin (acrylic) Cable: Oil resistant PVC		
Net Weight *6	Weight (g) = (protective height) x 1.62 + 110	Weight (g) = (protective height) x 1.83 + 122	
Gross Weight *7	Weight (g) = (protective height) x 2.7 + 500	Weight (g) = (protective height) x 2.9 + 550	
Accessories	Quick Installation Manual (QIM), Instruction Manual *8		
Applicable standards *9	IEC 61496-1, EN 61496-1, UL 61496-1, Type 4 ESPE (Electro-Sensitive Protective Equipment) IEC 61496-2, EN 61496-2, UL 61496-2, Type 4 AOPD (Active Opto-electronic Protective Devices) IEC 61508-1 to -3, EN 61508-1 to -3 SIL3 ISO 13849-1: 2015, EN ISO 13849-1: 2015 (PLe/Safety Category 4) UL 508, UL 1998, CAN/CSA C22.2 No.14, CAN/CSA C22.2 No.0.8		

- Manual (SCHG-734) for details.
 - 2. Reset mode is fixed with auto reset mode.
- *1. Do not use the Support Software and Setting Console for F3SJ-A. Operation cannot be guaranteed.
- *2. Use of the Spatter Protection Cover causes a 10% maximum sensing distance attenuation.
- *3. The load inductance is the maximum value when the safety output frequently repeats ON and OFF. When you use the safety output at 4 Hz or less, the usable load inductance becomes larger.

 *4. These values must be taken into consideration when connecting elements including a capacitive load such as capacitor.
- ***5.** The Vs indicates a voltage value in your environment.
- ***6.** The net weight is the weight of an emitter and a receiver.
- *7. The gross weight is the weight of an emitter, a receiver, included accessories and a package.
- ***8.** Mounting brackets and test rod are sold separately.
- *9. Refer to Safety Precautions for information about Legislation and Standards.

Indicator (F3SJ-B□□□□P25-01TS)

Emitter

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light.	Blinks when cap error or connection error occurs.
Stable-state indicator	STB	Turns ON when incidence level is 170% or more of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns ON when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the receiver.	Blinks when the F3SJ-B enters a lockout on the emitter.
Power indicator	POWER	Turns ON while the power of the emitter is ON.	Blinks when the F3SJ-B enters a lockout due to power voltage/noise.
Test indicator	TEST		Blinks when external test is being performed.
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.	

Receiver

Name of indicator	Label	ON	Blinking	
Top-beam-state indicator TOP		Turns ON when the top beam is receiving light.	Blinks when cap error or connection error occurs.	
Stable-state indicator STB		Turns ON when incidence level is 170% or more of the output ON threshold. Blinks when the safety output is turn due to disturbance light or vibration.		
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns ON when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.	
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the emitter.	Blinks when the F3SJ-B enters a lockout on the receiver.	
Communication indicator	СОМ	Turns ON when communication between emitter and receiver is established.	Blinks when the F3SJ-B enters lockout due to a communication error between receiver and emitter.	
Configuration indicator	CFG		Blinks when the F3SJ-B enters lockout due to a model type error between receiver and emitter.	
Internal error indicator	INTERNAL		Blinks when the F3SJ-B enters a lockout due to an internal error.	
Interlock indicator	INT -LK	Not used	Not used	
External device monitoring indicator	EDM	Turns ON when an input is given to external device monitoring input. *	Blinks when the F3SJ-B enters a lockout due to an external device monitoring error.	
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.		

^{*} It turns ON when there is an external device monitoring input regardless of the availability of the external device monitoring.

Indicator (F3SJ-B□□□□P25-02TS)

Emitter

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light. Blinks during muting/override, or who or connection error occurs.	
Stable-state indicator	STB	Turns ON when incidence level is 170% or more of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns ON when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the receiver.	Blinks when the F3SJ-B enters a lockout on the emitter.
Power indicator	POWER	Turns ON while the power of the emitter is ON.	Blinks when the F3SJ-B enters a lockout due to power voltage/noise.
Test indicator	TEST		Blinks when external test is being performed.
Muting error indicator	MUTING ERROR		Blinks during a muting error.
Muting input 1 indicator	MUTE1	Turns ON when muting input 1 is ON under the muting system.	
Muting input 2 indicator	MUTE2	Turns ON when muting input 2 is ON under the muting system.	
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.	Blinks during muting/override.

Receiver

Name of indicator	Label	ON	Blinking
Top-beam-state indicator	ТОР	Turns ON when the top beam is receiving light.	Blinks during muting/override, or when cap error or connection error occurs.
Stable-state indicator	STB	Turns ON when incidence level is 170% or more of the output ON threshold.	Blinks when the safety output is turned OFF due to disturbance light or vibration.
ON/OFF-state indicator	ON OFF	Green: Turns ON when safety output is ON. Red: Turns ON when safety output is OFF.	Red: Blinks when the F3SJ-B enters a lockout due to a safety output error.
Lockout indicator	LOCKOUT	Turns ON when the F3SJ-B enters a lockout on the emitter.	Blinks when the F3SJ-B enters a lockout on the receiver.
Communication indicator	СОМ	Turns ON when communication between emitter and receiver is established.	Blinks when the F3SJ-B enters lockout due to a communication error between receiver and emitter.
Configuration indicator	CFG		Blinks when the F3SJ-B enters lockout due to a model type error between receiver and emitter.
Internal error indicator	INTERNAL		Blinks when the F3SJ-B enters a lockout due to an internal error.
Interlock indicator	INT -LK	Not used	Not used
External device monitoring indicator	EDM	Turns ON when an input is given to external device monitoring input. *	Blinks when the F3SJ-B enters a lockout due to an external device monitoring error.
Bottom-beam-state indicator	BTM	Turns ON when the bottom beam is receiving light.	Blinks during muting/override.

^{*} It turns ON when there is an external device monitoring input regardless of the availability of the external device monitoring.

Accessories

Control Unit

Item	Model	F3SP-B1P
Applicable sen	sor	F3SJ-B/A (Only for PNP output type) *
Power supply	voltage	24 VDC±10%
Power consum	ption	DC1.7 W max. (not including sensor's current consumption)
Operation time	•	100 ms max. (not including sensor's response time)
Response time)	100 ms max. (not including sensor's response time)
	Number of contacts	3NO+1NC
Relay output	Rated load	25 VAC 5 A (cos φ = 1), 30 VDC 5 A L/R = 0 ms
	Rated current	5 A
Connection type	Between sensors	M12 connector (8-pin)
туре	Others	Terminal block
Weight (packed state)		Approx. 280 g
Accessories		Instruction manual

^{*} NPN output type cannot be connected. Also, the system cannot be used as a muting system.

Laser Pointer


Item Model	F39-PTJ
Applicable sensor	F3SJ Series *1
Power supply voltage	4.65 or 4.5 VDC
Battery	Three button batteries (SR44 or LR44)
Battery life *2	SR44: 10 hours of continuous operation, LR44: 6 hours of continuous operation
Light source	Red semiconductor laser (wavelength: 650 nm, 1 mW max. JIS class 2, EN/IEC class 2, FDA class II)
Spot diameter (typical value)	6.5 mm at 10 m
Ambient temperature	Operating: 0 to 40°C Storage: -15 to 60°C (with no icing or condensation)
Ambient humidity	Operating and storage: 35% to 85% (with no condensation)
Material	Laser module case: aluminum Mounting bracket: aluminum and stainless
Weight	Approx. 220 g (packed)
Accessories	Laser safety standard labels (EN: 1, FDA: 3) Button batteries (SR44: 3), instruction manual

^{*1.} It cannot be mounted to the models with the suffix "-02TS".

^{*2.} Battery life varies depending on a battery used.

Connections

Basic Wiring Diagram



S1 : External test switch (connect to 0 V if a switch is not required)

S2 : Interlock/lockout reset switch


KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

K1 : Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

***2.** F3SJ operates even when K1 is not connected.

Wiring when using manual reset mode, external device monitoring (F3SJ-B DD N25) [NPN Output]



S1 : External test switch (connect to 24 V if a switch is not required)


S2 : Interlock/lockout reset switch

KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

K1 : Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

Wiring for manual reset mode and deactivated external device monitoring function (F3SJ-B□□□□P25) [PNP Output]



S1 : External test switch (connect to 0 V if a switch is not required)

: Interlock/lockout reset switch


S2 KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

: Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

*2. F3SJ operates even when K1 is not connected.

Wiring for manual reset mode and deactivated external device monitoring function (F3SJ-B DDDDN25) [NPN Output]



S1 S2 : External test switch (connect to 24 V if a switch is not required)


: Interlock/lockout reset switch

KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

: Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

Wiring for auto reset mode and external device monitoring function (F3SJ-B DDDDD25) [PNP Output]




S1 : External test switch (connect to 0 V if a switch is not required)
S2 : Lockout reset switch (connect to 24 V if a switch is not required)
KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor
C1 : Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

*2. F3SJ operates even when K1 is not connected.


Wiring for auto reset mode and external device monitoring function (F3SJ-B□□□□N25) [NPN Output]



S1 : External test switch (connect to 24 V if a switch is not required)
S2 : Lockout reset switch (connect to 0 V if a switch is not required)
KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor
C1 : Load or PLC, etc. (for monitoring)

***1.** Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

Wiring for auto reset mode and deactivated external device monitoring (F3SJ-B P25) [PNP Output]




S1 : External test switch (connect to 0 V if a switch is not required)
S2 : Lockout reset switch (connect to 24 V if a switch is not required)
KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor
Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

*2. F3SJ operates even when K1 is not connected.


Wiring for auto reset mode and deactivated external device monitoring (F3SJ-B□□□□N25) [NPN Output]




S1 : External test switch (connect to 24 V if a switch is not required)
S2 : Lockout reset switch (connect to 0 V if a switch is not required)
KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor
C1 : Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).


Minimum wiring required to check the operation of the F3SJ-B (Wiring for deactivated external device monitoring) (F3SJ-B CCC P25-01TS) [PNP Output]



Minimum wiring required to check the operation of the F3SJ-B (Wiring for deactivated external device monitoring) (F3SJ-B CCC P25-02TS) [PNP Output]



Wiring for external device monitoring function (F3SJ-B P25-01TS) [PNP Output]



S2 : Lockout reset switch (connect to 24 V if a switch is not required)


KM1, KM2: Safety relay with force-guided contact (G7SA) or magnetic contactor

: Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

*2. F3SJ operates even when K1 is not connected.

Wiring for external device monitoring function (F3SJ-B P25-02TS) [PNP Output]




KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

: Load or PLC, etc. (for monitoring)

*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

Wiring for deactivated external device monitoring function (F3SJ-BDDDDP25-01TS) [PNP Output]




S2 : Lockout reset switch (connect to 24 V if a switch is not required) KM1, KM2 : Safety relay with force-guided contact (G7SA) or magnetic contactor

: Load or PLC, etc. (for monitoring)

***1.** Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

*2. F3SJ operates even when K1 is not connected.

Wiring for deactivated external device monitoring function (F3SJ-B□□□□P25-02TS) [PNP Output]




: Lockout reset switch (connect to 24 V if a switch is not required)

KM1, KM2: Safety relay with force-guided contact (G7SA) or magnetic contactor : Load or PLC, etc. (for monitoring)


*1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).

Basic Wiring Diagram for Muting System

Wiring for muting function (F3SJ-B□□□□P25) [PNP Output]




Wiring for muting function (F3SJ-B□□□□N25) [NPN Output]



Wiring Diagram When Using Simple Wiring System

F39-CN5 simple wiring connector

Internal wiring of F39-CN5 simple wiring connector




2 3

PIN No



6




- S1: External test switch (connect 0 V if a switch is not required)
- ***1.** Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).
- *2. When the lockout reset function is used, connect to 24 V via a lockout reset switch (N.C. contact).
- ***3.** Make sure the Communication lines are insulated. If the lines are shorted, the F3SJ-B enters the lockout state.

Controllers connectable with PNP output F3SJ series

Safety controller	Model
Safety Network Controller	NE1A series
Safety Controller	G9SP series
Flexible Safety Unit	G9SX series
Safety Relay Unit	G9SA series

[NPN Output]



- S1: External test switch (connect 24 V if a switch is not required)
- *1. Use a switch for small loads
- (input specifications: 24 V, 1.0 mA max.).
- *2. When the lockout reset function is used, connect to 0 V via a lockout reset switch (N.C. contact).
- *3. Make sure the Communication lines are insulated. If the lines are shorted, the F3SJ-B enters the lockout state.

Controller connectable with NPN output F3SJ series

Safety controller	Model
Safety Relay Unit	G9SA-301-P

Note: When using the Simple Wiring Connector (F39-CN5), the following functions are not available.

- Manual Reset
- · External Device Monitoring
- Auxiliary Output
- Muting/Override


Input/Output Circuit Diagram

F3SJ-B P25 [PNP Output]


Entire Circuit Diagram


The numbers in circles indicate the connectors' pin numbers.

The words in brackets ([]) indicate the signal name for muting system.



Input circuit diagram by function






F3SJ-B | N25 [NPN Output]


Entire Circuit Diagram


The numbers in circles indicate the connectors' pin numbers.

The words in brackets ([]) indicate the signal name for muting system.



Input circuit diagram by function







F3SJ-B P25-01TS [PNP Output]


Entire Circuit Diagram

The numbers in circles indicate the connectors' pin numbers.



Input circuit diagram by function






* The light emission stops when opening the test input line or applying voltage of 0 V to 1/2 Vs to the test input line.

F3SJ-B DDDDP25-02TS [PNP Output]


Entire Circuit Diagram


The numbers in circles indicate the connectors' pin numbers.

The words in brackets ([]) indicate the signal name for muting system.



Input circuit diagram by function





Connection Circuit Examples


Wiring for single F3SJ-B application (F3SJ-B□□□□P25) [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-B□□□□P25 Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring for single F3SJ-B application (F3SJ-B□□□□N25) [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-B□□□□N25 Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring to connect a F3SJ-B with a controller G9SP (F3SJ-B DDDP25) [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-B□□□□P25 Safety Controller G9SP Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.




Wiring to connect a F3SJ-B with a controller F3SP-B1P (F3SJ-B□□□□P25) [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-B□□□□P25 Control Unit F3SP-B1P Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.



Note: It cannot be used as a muting system when F3SP-B1P is used.


Wiring to connect a F3SJ-B with a controller G9SA-301-P (F3SJ-B□□□□N25) [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-B□□□□N25 Safety Relay Unit G9SA-301-P 24V DC Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.



Note: 1. As the G9SP Safety Controller is a PNP output type, it cannot be connected to the F3SJ-B□□□□N25. Also, a Safety Controller with PNP output cannot be connected to the F3SJ-B□□□□N25.


2. The G9SA-301-P is a safety relay unit only for NPN output.

Dimensions (Unit: mm)

The dimensions of the F3SJ-E and F3SJ-B are the same except for connector cables and cable leads.

Main Units


Mounting Top/Bottom and Intermediate Brackets



C (protective height): 4-digit number in the table A = C + 69, B = C + 42.2 D = C - 45, E = See table below, P = 20

Protective height	Number of intermediate brackets	E
185 to 1,105	0	
1,185 to 1,345	1	C/2 max.
1,425 to 2,065	2	C/3 max.

Side mounting




C (protective height): 4-digit number in the table A = C + 69, B = C + 42.2

D = C - 45, E = See table below, P = 20


-	Protective height	Number of intermediate brackets	E
	185 to 1,105	0	
	1,185 to 1,345	1	C/2 max.
	1,425 to 2,065	2	C/3 max.

Dimensions of top/bottom bracket for F39-LJB1



Mounting Intermediate Brackets only (location-free mounting)


Backside mounting



C (protective height): 4-digit number in the table F = See the table below.

Protective height	Number of intermediate brackets	F
185 to 225	1	
305 to 1,105	2	555 mm max.
1,185 to 1,585	3	555 mm max.
1,665 to 2,065	4	555 mm max.

Side mounting




4 2

C (protective height): 4-digit number in the table F = See the table below.


Protective height	Number of intermediate brackets	F
185 to 225	1	
305 to 1,105	2	555 mm max.
1,185 to 1,585	3	555 mm max.
1,665 to 2,065	4	555 mm max.


Dimensions of intermediate bracket for F39-LJB2



When Using One-touch Brackets

Backside mounting






C (protective height): 4-digit number in the table F = See the table below.

	Protective height	Number of intermediate brackets	F
	185 to 1,105	2	555 mm max.
>	1,185 to 1,585	3	555 mm max.
	1,665 to 2,065	4	555 mm max.

Side mounting




C (protective height): 4-digit number in the table F = See the table below


= See the table below.

	Protective height	Number of intermediate brackets	F
-	185 to 1,105	2	555 mm max.
•	1,185 to 1,585	3	555 mm max.
	1,665 to 2,065	4	555 mm max.

Dimensions of one-touch bracket for F39-LJB3




Dimensions of one-touch M6 bracket dia.6.2 22 Material : Stainless



Side mounting dia.22 Material : Zinc die-cast

Precautions on mounting the sensor using One-touch Brackets


When using two One-touch Brackets to mount a sensor, the combination of One-touch M6 Bracket (or One-touch M8 Bracket) and Intermediate Bracket at the both ends of the sensor must be positioned opposite each other. When using three or more Brackets, One-touch M6 Brackets (or One-touch M8 Brackets) and Intermediate Brackets at other positions than the both ends must be in the same orientation.




Mount One-touch M6 Brackets (or One-touch M8 Brackets) according to the mounting positions of the emitter and receiver. The positions of Intermediate Brackets mounted to the emitter and receiver must be aligned with each other.

Side view of the aluminum profile to be mounted


Position of the brackets to be mounted to the sensor






When Using Compatible Brackets


Backside mounting



Side mounting



Dimensions of compatible bracket for F39-LJB4




Material: Stainless

When Using Contact Mount Brackets

Backside mounting

Mounting screw holes




C (protective height): 4-digit number in the Model name


A = C + 69 B = C + 47.5 D = C - 45

Side mounting

Mounting screw holes




Dimensions of F39-LJB5 contact mount bracket



Material: Stainless

- Note: 1. The protective height of the F3SJ-E/B series that supports the contact mount bracket is limited. Protective height allowed for mounting: 185 mm to 1,105 mm (225 mm to 545 mm for the model with the suffix "-02TS")
 - 2. Brackets of other models such as F39-LJB1 cannot be used simultaneously.

F3SJ-B P25-02TS



Note: For information on dimensions with brackets mounted, refer to the User's Manual of the F3SJ-B□□□□P25-02TS (SCHG-736). Brackets used are common to other F3SJ-E/B series.

Required number of intermediate brackets

The number of the brackets needed for the F3SJ-B _ _ _ \P25-02TS differs from the other F3SJ-E/B series. The table below shows the number of brackets corresponding to the protective heights.

When using top/bottom bracket/compatible bracket + intermediate bracket

Protective height	Number of top/ bottom brackets /compatible brackets	Number of intermediate brackets
0225 to 0545	2	0
0625 to 1105	2	1
1185 to 1585	2	2
1665 to 1985	2	3

Using only the intermediate bracket (free-location mounting)

Protective height	Number of intermediate brackets
0225 to 0385	2
0465 to 0785	3
0865 to 1105	4
1185 to 1425	5
1505 to 1825	6
1905 to 1985	7

When using the one-touch bracket

Protective height	Number of one-touch bracket
0225 to 0385	2
0465 to 0785	3
0865 to 1105	4
1185 to 1425	5
1505 to 1825	6
1905 to 1985	7


Accessories

Single-Ended Cable F3SJ-B

F39-JD3A (L = 3 m) F39-JD15A (L = 15 m) F39-JD7A (L = 7 m) F39-JD20A (L = 20 m)

F39-JD10A (L = 10 m)


Cable color: Gray for emitter and Black for receiver



Double-Ended Cable F3SJ-B

F39-JDR5B (L = 0.5 m) F39-JD7B (L = 7 m) F39-JD1B (L = 1 m) F39-JD10B (L = 10 m) F39-JD3 (L = 3 m) F39-JD15B (L = 15 m) F39-JD20B (L = 20 m)

Cable color: Gray for emitter and Black for receiver



Simple Wiring Connector F39-CN5 (52) 24.7 13.6 8 dia. (SPOT FACING 2) 12 4.5 dia. **Control Unit F3SJ-B** Emitter F3SP-B1P Receiver Mounting screw holes 2-4.2 dia. or M4 76 max. 63 ← 35±0.3 -Laser Pointer F3SJ-E F3SJ-B **Spatter Protection Cover (F3SJ-E) (F3SJ-B)** F39-HB□□□□ F39-PTJ 35.5 101±5 _ - 76 Optical axis

L = 🗆 🗆 - 21 mm


15.9 dia.


Material: PC (protective cover)

F3SJ-E/F3SJ-B


Mirror Column

F39-SML





73.9




Material: Aluminum alloy (Housing) Hot rolled steel (Base) PBT resin (Cap) Glass mirror (Mirror)


Model	Dimension L
F39-SML0990	990
F39-SML1310	1310
F39-SML1630	1630
F39-SML1950	1950

Protective Bar (F3SJ-E) (F3SJ-B)

F39-PB□□□□

Backside mounting (using M5 screws)







Protective height Number of protective brackets (3) used D1 0185 to 0945 0 -- 1025 to 1985 1 B1/2 2065 2 B1/3

Note: For reference, D1 is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

Backside mounting (using M8 screws)






2-Mounting holes


C (protective height): 4-digit number in the Model name A2: A2 = C + 69 B2: B2 = C + 54

	Protective height	Number of protective brackets (3) used	D2
•	0185 to 0945	0	
٠	1025 to 1985	1	B2/2
٠	2065	2	B2/3

Note: For reference, D2 is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

F39-PB□□□□ Side mounting (using M5 screws)





 Protective height
 Number of protective brackets (4) used
 D1


 0185 to 0945
 0
 --


 1025 to 1985
 1
 B1/2

 2065
 2
 B1/3

Note: For reference, D1 is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

Side mounting (using M8 screws)





2-Mounting holes

C (protective height): 4-digit number in the Model name A2: A2 = C + 69 B2: B2 = C + 54

Protective height	Number of protective brackets (4) used	D2
0185 to 0945	0	
1025 to 1985	1	B2/2
2065	2	B2/3

Note: For reference, D2 is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

MEMO

Safety Light Curtain

F3SJ-A

High-functional ADVANCED type supports finger protection and special applications.

• Detection capability supports finger protection.

• Equipped with wide variety of functions such as partial muting and blanking functions.

• The system status can be checked with PC tool.

Ordering Information

Main Units

Safety Light Curtain

Application	Detection	Beam gap	Operating	Protective	Model		del	
Application	capability	Bealli gap	range	height (mm)	PNP output		NPN output	
Finger protection	Dia. 14 mm	9 mm	0.2 to 9 m	245 to 1,271	F3SJ-A□□□□P14	*2	F3SJ-A□□□□N14	
Hand protection	Dia. 20 mm	15 mm	0.2 to 9 m	245 to 1,505	F3SJ-A□□□□P20	*2	F3SJ-A□□□□N20	
Hand/arm protection	Dia. 30 mm	25 mm	0.2 to 9 m	245 to 1,620	F3SJ-A□□□□P30		F3SJ-A□□□□N30	
manu/ami protection	Dia. 30 mm	25 111111	0.2 to 7 m	1,745 to 2,495	•	*1	F333-ALLLLINGU	
Leg/body protection,	Dia 55 mm	50 mm	0.2 to 9 m	270 to 1,570	F3SJ-A□□□□P55		F3SJ-A□□□□N55	
presence detection	Dia. 55 mm	50 mm 0.2 to 7	50 mm -	0.2 to 7 m	1,670 to 2,470	*	*1	

Note: Connection cables are not included in the products. You must purchase optional connector cable.

Example: F3SJ-A0245P30-S

(Models with ditection capability 25 mm dia. are also available.)

^{*1.} Models with S-mark certification have an "-S" at the end of the model number.

^{*2.} The F3SJ-A-\(\subseteq \subseteq \subseteq

Safety Light Curtain Model List

F3SJ-A14 Series (9 mm gap)

Мо	del	Number of	Protective
PNP Output	NPN Output	Beams	Height (mm) *
F3SJ-A0245P14	F3SJ-A0245N14	26	245
F3SJ-A0263P14	F3SJ-A0263N14	28	263
F3SJ-A0299P14	F3SJ-A0299N14	32	299
F3SJ-A0317P14	F3SJ-A0317N14	34	317
F3SJ-A0389P14	F3SJ-A0389N14	42	389
F3SJ-A0461P14	F3SJ-A0461N14	50	461
F3SJ-A0551P14	F3SJ-A0551N14	60	551
F3SJ-A0623P14	F3SJ-A0623N14	68	623
F3SJ-A0695P14	F3SJ-A0695N14	76	695
F3SJ-A0731P14	F3SJ-A0731N14	80	731
F3SJ-A0803P14	F3SJ-A0803N14	88	803
F3SJ-A0875P14	F3SJ-A0875N14	96	875
F3SJ-A0983P14	F3SJ-A0983N14	108	983
F3SJ-A1055P14	F3SJ-A1055N14	116	1,055
F3SJ-A1127P14	F3SJ-A1127N14	124	1,127
F3SJ-A1199P14	F3SJ-A1199N14	132	1,199
F3SJ-A1271P14	F3SJ-A1271N14	140	1,271

^{*}Protective Height (mm) = Total sensor length

F3SJ-A30 Series (25 mm gap)

Мо	Number of	Protective	
PNP Output	NPN Output	Beams	Height (mm) *
F3SJ-A0245P30	F3SJ-A0245N30	10	245
F3SJ-A0295P30	F3SJ-A0295N30	12	295
F3SJ-A0395P30	F3SJ-A0395N30	16	395
F3SJ-A0470P30	F3SJ-A0470N30	19	470
F3SJ-A0520P30	F3SJ-A0520N30	21	520
F3SJ-A0545P30	F3SJ-A0545N30	22	545
F3SJ-A0570P30	F3SJ-A0570N30	23	570
F3SJ-A0620P30	F3SJ-A0620N30	25	620
F3SJ-A0720P30	F3SJ-A0720N30	29	720
F3SJ-A0795P30	F3SJ-A0795N30	32	795
F3SJ-A0870P30	F3SJ-A0870N30	35	870
F3SJ-A0920P30	F3SJ-A0920N30	37	920
F3SJ-A0945P30	F3SJ-A0945N30	38	945
F3SJ-A0995P30	F3SJ-A0995N30	40	995
F3SJ-A1020P30	F3SJ-A1020N30	41	1,020
F3SJ-A1095P30	F3SJ-A1095N30	44	1,095
F3SJ-A1120P30	F3SJ-A1120N30	45	1,120
F3SJ-A1195P30	F3SJ-A1195N30	48	1,195
F3SJ-A1270P30	F3SJ-A1270N30	51	1,270
F3SJ-A1395P30	F3SJ-A1395N30	56	1,395
F3SJ-A1620P30	F3SJ-A1620N30	65	1,620
F3SJ-A1745P30	F3SJ-A1745N30	70	1,745
F3SJ-A1870P30	F3SJ-A1870N30	75	1,870
F3SJ-A1995P30	F3SJ-A1995N30	80	1,995
F3SJ-A2245P30	F3SJ-A2245N30	90	2,245
F3SJ-A2370P30	F3SJ-A2370N30	95	2,370
F3SJ-A2495P30	F3SJ-A2495N30	100	2,495

^{*}Protective Height (mm) = Total sensor length

F3SJ-A20 Series (15 mm gap)

Mo	Model		Protective	
PNP Output	NPN Output	Beams	Height (mm) *	
F3SJ-A0245P20	F3SJ-A0245N20	16	245	
F3SJ-A0275P20	F3SJ-A0275N20	18	275	
F3SJ-A0305P20	F3SJ-A0305N20	20	305	
F3SJ-A0395P20	F3SJ-A0395N20	26	395	
F3SJ-A0455P20	F3SJ-A0455N20	30	455	
F3SJ-A0545P20	F3SJ-A0545N20	36	545	
F3SJ-A0605P20	F3SJ-A0605N20	40	605	
F3SJ-A0635P20	F3SJ-A0635N20	42	635	
F3SJ-A0695P20	F3SJ-A0695N20	46	695	
F3SJ-A0785P20	F3SJ-A0785N20	52	785	
F3SJ-A0815P20	F3SJ-A0815N20	54	815	
F3SJ-A0875P20	F3SJ-A0875N20	58	875	
F3SJ-A0935P20	F3SJ-A0935N20	62	935	
F3SJ-A1025P20	F3SJ-A1025N20	68	1,025	
F3SJ-A1115P20	F3SJ-A1115N20	74	1,115	
F3SJ-A1205P20	F3SJ-A1205N20	80	1,205	
F3SJ-A1265P20	F3SJ-A1265N20	84	1,265	
F3SJ-A1445P20	F3SJ-A1445N20	96	1,445	
F3SJ-A1505P20	F3SJ-A1505N20	100	1,505	

*Protective Height (mm) = Total sensor length

F3SJ-A55 Series (50 mm gap)

Mo	Model				
PNP Output	NPN Output	Number of Beams	Height (mm) *		
F3SJ-A0270P55	F3SJ-A0270N55	6	270		
F3SJ-A0320P55	F3SJ-A0320N55	7	320		
F3SJ-A0370P55	F3SJ-A0370N55	8	370		
F3SJ-A0470P55	F3SJ-A0470N55	10	470		
F3SJ-A0570P55	F3SJ-A0570N55	12	570		
F3SJ-A0620P55	F3SJ-A0620N55	13	620		
F3SJ-A0720P55	F3SJ-A0720N55	15	720		
F3SJ-A0770P55	F3SJ-A0770N55	16	770		
F3SJ-A0870P55	F3SJ-A0870N55	18	870		
F3SJ-A0920P55	F3SJ-A0920N55	19	920		
F3SJ-A0970P55	F3SJ-A0970N55	20	970		
F3SJ-A1020P55	F3SJ-A1020N55	21	1,020		
F3SJ-A1120P55	F3SJ-A1120N55	23	1,120		
F3SJ-A1170P55	F3SJ-A1170N55	24	1,170		
F3SJ-A1270P55	F3SJ-A1270N55	26	1,270		
F3SJ-A1320P55	F3SJ-A1320N55	27	1,320		
F3SJ-A1420P55	F3SJ-A1420N55	29	1,420		
F3SJ-A1570P55	F3SJ-A1570N55	32	1,570		
F3SJ-A1770P55	F3SJ-A1770N55	36	1,770		
F3SJ-A1920P55	F3SJ-A1920N55	39	1,920		
F3SJ-A2070P55	F3SJ-A2070N55	42	2,070		
F3SJ-A2220P55	F3SJ-A2220N55	45	2,220		
F3SJ-A2370P55	F3SJ-A2370N55	48	2,370		
F3SJ-A2470P55	F3SJ-A2470N55	50	2,470		

*Protective Height (mm) = Total sensor length

Accessories (Sold separately)

Single-Ended Cable (2 cables per set, one for emitter and one for receiver) *

For wiring with safety circuit such as single safety relay, safety relay unit, and safety controller

Appearance	Cable length	Specifications	Model
	3 m		F39-JD3A
	7 m		F39-JD7A
	10 m	M12 connector (8-pin)	F39-JD10A
	15 m		F39-JD15A
	20 m		F39-JD20A

^{*} The cable for emitter and the cable for receiver are available separately. Add '-L' for emitter or '-D' for receiver to the end of the model number when you order. Single-Ended Cable for Emitter: F39-JD

A-L, Single-Ended Cable for Receiver: F39-JD

A-D

Note: To extend the cable length to 20 m or more, add the F39-JD□B Double-Ended Cable.

Example: When using a cable of 30 m, connect the F39-JD10A Single-Ended Cable with the F39-JD20B Double-Ended Cable.

Double-Ended Cable (2 cables per set, one for emitter and one for receiver) *


Control unit for connection with F3SP-B1P, to extend the length under series connection (*)

Appearance	Cable length	Specifications	Model	
	0.5 m		F39-JDR5B	
		1 m		F39-JD1B
	3 m	M12 connector (8-pin)	F39-JD3B	
	5 m		F39-JD5B	
	7 m		F39-JD7B	
	10 m		F39-JD10B	
	6 Y	15 m	1	F39-JD15B
	20 m		F39-JD20B	

^{*} The cable for emitter and the cable for receiver are available separately. Add '-L' for emitter or '-D' for receiver to the end of the model number when you order. Double-Ended Cable for Emitter: F39-JD□B-L, Double-Ended Cable for Receiver: F39-JD□B-D

Note: To extend the cable length to 20 m or more, use the Double-Ended Cables in combination.

Example: When using a cable of 30 m, connect the F39-JD10B Double-Ended Cable with the F39-JD20B Double-Ended Cable.



Power cable (included in the main unit. 2 cables per set, one for emitter and one for receiver)

Appearance	Cable Length	Model
*	0.3 m	F39-JJR3K


Note: This product is for F3SJ-A only.

Series-connection Cable (2 cables per set, for emitter and receiver)

Type	Appearance	Cable Length	Model	Application
Series connection cable		0.3 m	F39-JJR3W *1	For series connection *2 When using the Water-resistant Case. *3
Side-by-side Series connection cable	*	0.06 m	F39-JJR06L *1	Dedicated cable to materialize series connection with minimum length without
		0.15 m	F39-JJR15L *1	connector cable of the main sensor unit

^{*1.} This product is for F3SJ-A only.

Note: The Double-Ended Cable (up to 15 m: F39-JD15B) can be added to extend the cable length between the series-connected sensors. Cable length between sensors: 15 m max. (not including series connection cable (F39-JJR3W or F39-JJR□L) and power cable)




^{*2.} For series connection with minimum length, use F39-JJR06L or F39-JJR15L.

^{*3.} When using the F39-EJ \(\text{-}\text{-}\text{L/D}\) Water-resistant Case in series connection configurations, use the special series connection cables for the Water-resistant Case. Refer to page 75 for details.

Simple wiring connector system (Order the F39-CN5 and Cables for Simple Wiring.)

Simple wiring connector

Appearance	Model	Application
	F39-CN5	To reduce wiring



Cable for simple wiring * (2 cables per set, one double-ended cable and one single-ended cable)

Appearance	Contents		Cable length	Model
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0303BA
	Single-Ended Cable	F39-JD3A-D	3 m	F39-3D0303DA
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0307BA
	Single-Ended Cable	F39-JD7A-D	7 m	L22-2D0201.DV
	Double-Ended Cable	F39-JD3B-L	3 m	F39-JD0310BA
	Single-Ended Cable	F39-JD10A-D	10 m	L99-JD09J0DA
	Double-Ended Cable	F39-JD5B-L	5 m	E20 ID0E02BA
	Single-Ended Cable	F39-JD3A-D	3 m	F39-JD0503BA
	Double-Ended Cable	F39-JD5B-L	5 m	E20 ID0E07DA
	Single-Ended Cable	F39-JD7A-D	7 m	F39-JD0507BA
	Double-Ended Cable	F39-JD5B-L	5 m	E20 ID0E40BA
	Single-Ended Cable	F39-JD10A-D	10 m	F39-JD0510BA
	Double-Ended Cable	F39-JD10B-L	10 m	F39-JD1003BA
•	Single-Ended Cable	F39-JD3A-D	3 m	L99-201009DA
	Double-Ended Cable	F39-JD10B-L	10 m	E20 ID4007BA
	Single-Ended Cable	F39-JD7A-D	7 m	F39-JD1007BA
	Double-Ended Cable	F39-JD10B-L	10 m	F20 ID4040DA
	Single-Ended Cable	F39-JD10A-D	10 m	F39-JD1010BA

Note: A double-ended cable and single-ended cable with other cable lengths than those listed above can also be used in combination. Please contact your OMRON sales representative for details.

^{*}Although the double-ended cable for the emitter is used for the emitter in the above figure, it can also be used for the receiver.

Relays with Forcibly Guided Contacts

Туре	Appearance	Specifications	Model	Remarks	
G7SA Relays with Forcibly Guided Contacts		Nodes: 4 Contact type: 2A2B Rated switch load: 250 VAC 6 A, 30 VDC 6 A	G7SA-2A2B	For details on other models or socket	
		Nodes: 4 Contact type: 3NO+1NC Rated switch load: 250 VAC 6 A, 30 VDC 6 A	G7SA-3A1B	- models, refer to the OMRON's website.	
G7S-□-E Relays with Forcibly Guided Contacts		Nodes: 6 Contact type: 4NO+2NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	G7S-4A2B-E	For details on other models or socket models, refer to the OMRON's	
		Nodes: 6 Contact type: 3NO+3NC Rated switch load: 250 VAC 10 A, 30 VDC 10 A	G7S-3A3B-E	website.	

Control Unit (Can not be used as a muting system) (Dedicated PNP output type) *

Appearance	Output	Model	Remarks
300000	Relay, 3NO+1NC	F3SP-B1P *	For connection with F3SJ-A, use a double-ended cable F39-JD□B.

^{*}F3SJ for NPN output type cannot be connected.

Wire-saving Devices

Type	Appearance	Specifications	Model	Remarks	
		Model with PNP Muting Sensor Output	F39-TC5P01	Significantly reduces amount of wiring between Safety Light Curtains and Muting Sensors. IP67 model for mounting at Sensor installation site. For details, refer to the OMRON's website.	
Connector Terminal Box/ Muting Terminals		Model with PNP Override Input	F39-TC5P02		
		Model with NPN Muting Sensor Output	F39-TC5N01		
		Model with NPN Override Input	F39-TC5N02		
Safety Terminal Relays		PNP output relay, SPDT-NO	F3SP-T01 *	Significantly reduces amount of wiring between Safety Light Curtains and Muting Sensors. For details, refer to the OMRON's website.	

*F3SJ for NPN output type cannot be connected.

Note: Orders for F39-TC5 Series and F3SP-T01 have been discontinued at the end of May 2020.

Laser Pointer

Appearance	Output	Model
3.0	Laser Pointer for F3SJ	F39-PTJ

Dedicated External Indicator Set (can be connected to either an emitter or a receiver)

Appearance	Color	Model	Remarks
Red	Red	F39-A01PR-PAC	Indicator (red), mounting bracket 1 set, and dedicated connection cable (0.1 m)
	Green	F39-A01PG-PAC	Indicator (green), mounting bracket 1 set, and dedicated connection cable (0.1 m)
	Yellow	F39-A01PY-PAC	Indicator (yellow), mounting bracket 1 set, and dedicated connection cable (0.1 m)

Note: 1. For indication timing (operation mode), see "Specifications" on page 76.

2. This product is for F3SJ-A only.

General External Indicator Cable

Appearance	Cable Length	Specifications	Model
	3 m	Cable to connect top of the main unit and an off-the-shelf external indicator (2-wire)	F39-JJ3N *

*This product is for F3SJ-A only.

Spatter Protection Cover (2 cables per set, one for emitter and one for receiver) (10% Operating Range Attenuation)

Appearance	Model	
	F39-HJ□□□□	*1 *2

*1. This product is for F3SJ-A only.

*2. The same 4-digit numbers as the protective heights (

Mirror Column

Appearance	Applicable light curtain F3SJ Series Safety Light Curtain	Column height	Model
	Protective height up to 0880	990 mm	F39-SML0990
	Protective height up to 1200	1,310 mm	F39-SML1310
I.	Protective height up to 1520	1,630 mm	F39-SML1630
(Operating range becomes 15% shorter than the rating)	Protective height up to 1840	1,950 mm	F39-SML1950

Test rod (Sold separately)

Diameter	Model
14mm dia.	F39-TRD14
20mm dia.	F39-TRD20
25mm dia.	F39-TRD25
30mm dia.	F39-TRD30

Sensor Mounting Brackets (Sold separately)

Appearance	Specifications	Model	Application	Remarks
	Standard mounting bracket (for top/bottom)	F39-LJ1	(provided with the F3SJ)	2 for an emitter, 2 for a receiver, total of 4 per set
	Flat side mounting bracket	F39-LJ2	Use these small-sized brackets when performing side mounting with standard mounting brackets, so that they do not protrude from the detection surface.	2 for an emitter, 2 for a receiver, total of 4 per set
	Free-location mounting bracket (also used as standard intermediate bracket)	F39-LJ3	Use these brackets for mounting on any place without using standard bracket.	Two brackets per set (For details about the number of required brackets, refer to page 91.)
	F3SN Intermediate Bracket Replacement Spacers	F39-LJ3-SN	When replacing the F3SN with the F3SJ, the mounting hole pitches in the Intermediate Brackets are not the same. This Spacer is placed between the mounting holes to mount the F3SJ.	1 set with 2 pieces
	Top/bottom bracket B (Mounting hole pitch 19 mm)	F39-LJ4	Mounting bracket used when replacing existing area sensors (other than F3SN or F3WN) with the F3SJ. For front mounting. Suitable for mounting hole pitch of 18 to 20 mm.	2 for an emitter, 2 for a receiver, total of 4 per set
	Bracket for replacing short-length F3SN	F39-LJ5	Mounting bracket used when an F3SN with protective height of 300 mm or less is replaced by an F3SJ.	2 for an emitter, 2 for a receiver, total of 4 per set
Service of the servic	Space-saving mounting bracket	F39-LJ8	Use these brackets to mount facing inward. Length is 12 mm shorter than the standard F39-LJ1 bracket.	2 for an emitter, 2 for a receiver, total of 4 per set
	Mounting bracket used when replacing an F3W-C.	F39-LJ9	Mounting bracket used when replacing existing F3W-C series area sensors with the F3SJ. For front mounting or side mounting. Mounting hole pitch 16 mm.	2 for an emitter, 2 for a receiver, total of 4 per set
	Top/bottom bracket C (mounting hole pitch 13 mm)	F39-LJ11	Mounting bracket used when replacing existing area sensors having a mounting pitch of 13 mm with the F3SJ.	2 for an emitter, 2 for a receiver, total of 4 per set

End Cap

Appearance	Model	Remarks	
	F39-CN9 *	For both emitter and receiver. The End Cap can be purchased if lost. (Case: Black)	

^{*}This product is for F3SJ-A only.

Key Cap for Muting

Appearance	Model	Remarks
	F39-CN6	A cap to be attached to the main unit to enable muting function. Attach it to either an emitter or a receiver.(Case: orange)

^{*}This product is for F3SJ-A only.

Setting Tools *1

Type	Appearance	Model	Remarks
"SD Manager" Setting Support Software for the F3SJ	Suncy Company of the	F39-GWUM *2	Accessories: SD Manager CD-ROM (1), F39-CN1 Branch Connector (1), Connector Cap (1), 2-m Dedicated Cable (1), 0.3-m Dedicated Cable with Plug (1), Instruction Manual
Setting Console		F39-MC21 *3	Accessories: F39-CN1 Branch Connector (1), Connector Cap (1), 2-m Dedicated Cable (1), 0.3-m Dedicated Cable with Plug (1), Instruction Manual

^{*1.} The setting tools described above can be connected only to F3SJ-A models with built-in software of Ver. 2 or later.

Protective Bar *1 *2

Type	Appearance	Model	Remarks
Protective Bar		F39-PJ□□□□-S *3	Main unit bracket (1), rear mounting brackets (2), including intermediate brackets to match protective height (0 to 2).
Intermediate brackets for side mounting		F39-PJ-MS	For side mounting, order to suit the desired protective height Protective height of up to 1,000 mm: 0 intermediate brackets Protective height of 1,001 to 2,000 mm: 1 intermediate bracket Protective height of 2,001 mm or more: 2 intermediate brackets

Water-resistant Case (Set of 1 tube, packing, and dedicated connector cable) *1 *2 *3

Appearance	Specifications	Model	Remarks
	For emitter	F39-EJ□□□□-L *4	Includes gray cable for emitter.
For	For receiver	F39-EJ□□□□-D *4	Includes black cable for receiver.
The Common of th	Rear Mounting Brackets	F39-EJ-R *5	Top/bottom 1 each, total of 2
	Side Mounting Brackets	F39-EJ-S *5	Top/bottom 1 each, total of 2
	Series connection cable (for emitter)	F39-JJR3WE-L	Purchase additionally for series connection when using
	Series connection cable (for receiver)	F39-JJR3WE-D	the Water-resistant Case.

^{*1.} This product is for F3SJ-A only.

Note that the setting tools cannot be used with products shipped prior to December 2005. The setting tools cannot be used for setting parameters on the F3SJ-A \square -TS series, but the monitoring function can be used.

^{*2.} The PC tool supports Windows XP/7.

^{*3.} This product is for use only with the F3SJ-A.It cannot be connected to conventional models of the F3SJ-E/B or F3SN-A series.

^{*1.} This product is for F3SJ-A only. ***2.** When using for both emitter and receiver, order two sets.

^{*3.} The same four digits indicating protective height that are used in the Sensor model number (

^{*2.} When using for both emitter and receiver, order two sets.

^{*3.} There are restrictions to the application conditions depending on the protective height of the Curtain. Refer to the Water-resistant Case on page 79.

^{*5.} Be sure to purchase brackets with the Case to match the mounting direction (rear or side).

F3SJ-A

Specifications (For details, refer to the instruction manual or User's manual.)

F3SJ-A P14/P20/P30/P55/N14/N20/N30/N55

Model	PNP Output	F3SJ-A□□□□□P14	F3SJ-A□□□□P20	F3SJ-A□□□□P30	F3SJ-A□□□□P55	
Wiodei	NPN Output	F3SJ-A□□□□N14	F3SJ-A□□□□N20	F3SJ-A□□□□N30	F3SJ-A□□□□N55	
Sensor type		Type 4 safety light curtain				
Version		Ver. 2				
Setting tool co	nnection	Connectable				
Safety categor	у	Safety purpose of category	4, 3, 2, 1, or B			
Detection capability		Opaque objects 14 mm in diameter	Opaque objects 20 mm in diameter	Opaque objects 30 mm in diameter	Opaque objects 55 mm in diameter	
Beam gap (P)		9 mm	15 mm	25 mm	50 mm	
Number of beams (n)		26 to 140	16 to 100	10 to 100	6 to 50	
Protective heig	<u> </u>	245 to 1,271 mm	245 to 1,505 mm	245 to 2,495 mm	270 to 2,470 mm	
Lens diameter		Diameter 5 mm				
Operating rang	je *	0.2 to 9 m (protective height 0.2 to 7 m (protective height (Depending on the setting to		n be shortened to 0.5 m.)		
Response time (under stable light incident condition)	ON to OFF	1 set, 0245 to 983: 11 ms to 17.5 ms max. 1,055 or higher: 20 ms to 25 ms max.	1 set, 0245 to 1205: 10 ms to 15 ms max. 1235 or higher: 17.5 ms to 22.5 ms max.	1 set: 10 ms to 17.5 ms max.	1 set: 10 ms to 13 ms ma.	
(For details, see "Response Time" on page 78.)	OFF to ON	1 set, 0245 to 983: 44 ms to 70 ms max. 1,055 or higher: 80 ms to 100 ms max.	1 set, 0245 to 1205: 40 ms to 60 ms max. 1235 or higher: 70 ms to 90 ms max.	1 set: 40 ms to 70 ms max.	1 set: 40 ms to 52 ms ma	
Startup waiting	•	2 s max. (2.2 s max. for seri				
Power supply v	oltage (Vs)	24 VDC ±20% (ripple p-p10)	,			
Current consumption	Emitter	To 50 beams: 76 mA max., 51 to 100 beams: 106 mA max., 101 to 150 beams: 130 mA max., 151 to 180 beams: 153 mA max., 201 to 234 beams: 165 mA max.				
(no load)	Receiver	To 50 beams: 68 mA max., 51 to 100 beams: 90 mA max., 101 to 150 beams: 111 mA max., 151 to 180 beams: 128 mA max., 201 to 234 beams: 142 mA max.				
Light source (emitte	ed wavelength)	Infrared LED (870 nm)				
Effective aperture	angle (EAA)	Based on IEC 61496-2.With	in ±2.5° for both emitter and	receiver when the detection of	distance is 3 m or over	
Safety	PNP outputs	cable extension), allowable capacity load 2.2	load current 300 mA max., r μF, leak current 1 mA max. raditional logic (ON/OFF) bec	· ·	cept for voltage drop due to	
outputs (OSSD)	NPN Output	cable extension), allowable capacity load 2.2	, load current 300 mA max., r μF, leak current 2mA max. raditional logic (ON/OFF) bec	·	cept for voltage drop due to	
Auxiliary output 1	PNP outputs	One PNP transistor output, cable extension), leak current 1 mA max.	oad current 300 mA max., re	sidual voltage 2 V max. (exc	ept for voltage drop due to	
(Non-safety output)	NPN output	One NPN transistor output, cable extension), leak curre	load current 300 mA max., re nt 1 mA max.	esidual voltage 2 V max. (exc	ept for voltage drop due to	
Auxiliary output 2 (Non-safety	PNP outputs	One PNP transistor output, le extension), leak current 1 mA max.	oad current 50 mA max., resid	lual voltage 2 V max. (except	for voltage drop due to cabl	
output. Function for Basic System.)	NPN output	One NPN transistor output, le extension), leak current 1 m	oad current 50 mA max., resid A max.	lual voltage 2 V max. (except	for voltage drop due to cabl	
External indica (Non-safety ou		Available indicators Incandescent lamp: 24 VDC, 3 to 7 W LED lamp: Load current 10 mA to 300 mA max., leak current 1 mA max. (To use an external indicator, an F39-JJ3N universal indicator cable or an F39-A01P-PAC dedicated external indicator kit is required.)			ternal indicator kit is required.)	
Output operation	Receiver	Auxiliary output 1: Inverse o External indicator output 1:	Safety output 1, 2: ON when receiving light Auxiliary output 1: Inverse of safety output signals (Operation mode can be changed with the setting tool.) External indicator output 1: Inverse of safety output signals for a basic system (Operation mode can be changed with the setting tool.), ON when muting/override for a muting system (Operation mode can be changed with the setting tool.)			
mode	Emitter	with the se External indicator output 2:	when the point of 30,000 ope etting tool.) ON when lock-out for a basic sys ON when muting/override for the setting tool.)	stem (Operation mode can be cl	nanged with the setting tool.)	

^{*} Use of the Spatter Protection Cover causes a 10% maximum sensing distance attenuation.

Madal	PNP output	F3SJ-A□□□□P14	F3SJ-A□□□□P20	F3SJ-A□□□□P30	F3SJ-A□□□□P55	
Model	NPN output	F3SJ-A□□□□N14	F3SJ-A□□□□N20	F3SJ-A□□□□N30	F3SJ-A□□□□N55	
	PNP output	ON voltage: 9 V to Vs (short External device monitoring i ON voltage: 9 V to Vs (short	nput, Reset input, Muting inpu circuit current: approx. 2.0 n nput: circuit current: approx. 3.5 n Itage value in your environme	nA), OFF voltage: 0 to 1.5 V, nA), OFF voltage:open	or open	
Input voltage	NPN output	ON voltage: 0 to 1.5 V (shor External device monitoring i ON voltage: 0 to 1.5 V (shor	t-circuit current: approx. 4.0 ι	nA), OFF voltage: 9 V to Vs, nA), OFF voltage:open	or open	
Indicator	Emitter	Light intensity level indicator Error mode indicators (red L Power indicator (green LED Interlock indicator (yellow LE External device monitoring i	Note: The Vs indicates a voltage value in your environment. Light intensity level indicators (green LED x 2, orange LED x 3): ON based on the light intensity Error mode indicators (red LED x 3): Blink to indicate error details Power indicator (green LED x 1): ON while power is on Interlock indicator (yellow LED x 1): ON while under interlock, blinks at lockout. External device monitoring indicator (muting input 1 indicator), Blanking/test indicator (muting input 2 indicator) (green LED x 2): ON/flash according to function Light intensity level indicators (green LED x 2, orange LED x 3): ON based on the light intensity Error mode indicators (red LED x 3): Blink to indicate error details OFF output indicator (red LED x 1): ON when safety output is OFF, blinks at lockout. ON output indicator (green LED x 1): ON while safety output is ON Muting error indicator, Blanking /test indicator (green LED x 2): ON/flash according to function			
	Receiver	Error mode indicators (red L OFF output indicator (red LE ON output indicator (green L				
Mutual interfer prevention fun		Interference light prevention	algorithm, sensing distance	change function		
Series connec	tion	Time division emission by series connection • Number of connections: up to 4 sets (F3SJ-A only) F3SJ-E, F3SJ-B and F3SJ-TS cannot be connected. • Total number of beams: up to 400 beams • Cable length between sensors: 15 m max. (not including series connection cable (F39-JJR3W or F39-JJR□L) and power cable) • Response time under connection: Refer to page 78				
Test function		Self test (at power-ON and at power distribution) External test (emission stop function by test input)				
Safety-related	functions	Start interlock, restart interlock (Must be set with a setting tool when the muting function is used.) External device monitor Muting (Lamp burnout detection, override function included. F39-CN6 key cap for muting is required.) Fixed blanking (must be set by a setting tool) Floating blanking (must be set by a setting tool)				
Connection me	ethod	Connector method (M12, 8-pin)				
Protection circ	uit	Output short-circuit protection, and power supply reverse polarity protection				
Ambient tempe	erature	Operating: -10 to 55°C (no icing), Storage: -30 to 70°C				
Ambient humi	dity	Operating: 35% to 85% (no condensation), Storage: 35% to 95%				
Operating amb	•	Incandescent lamp: receiving-surface light intensity of 3,000 lx max., Sunlight: receiving-surface light intensity of 10,000 lx max.				
nsulation resi	stance	20 MΩ min. (at 500 VDC)				
Withstand volt	age	1,000 VAC 50/60 Hz, 1 min				
Degree of prot	ection	IP65 (IEC 60529)				
Vibration resis			ultiple amplitude of 0.7 mm, 2	· · · · · · · · · · · · · · · · · · ·	ctions	
Shock resistar	nce		times each in X, Y, and Z d			
Material Casing (including metal parts on both ends): Aluminum, zinc die-cast Cap: ABS resin, Optical cover: PMMA resin (acrylic), Cable: Oil resistant PVC						
Calculate using the following expressions: (1) For F3SJ-A						
Gross Weight *1		 (2) For F3SJ-A = 20/F (3) For F3SJ-A = 55, The values for α are as for Protected height 245 to 5 	weight (g) = (protective height 3SJ-A 30, weight (g) weight (g) = (protective height) of mm: = 1,100 protected 130 mm: = 1,500 protected) = (protective height) x 1.5 + t) x 1.4 + α neight 1,660 to 2,180 mm: =	2,400	

^{*1.} The net weight is the weight of an emitter and a receiver.

*2. The gross weight is the weight of an emitter, a receiver, included accessories and a package.

Model	PNP output	F3SJ-A□□□□P14	F3SJ-A□□□□P20	F3SJ-A□□□□P30	F3SJ-A□□□□P55
Wodei	NPN output	F3SJ-A□□□□N14	F3SJ-A□□□□N20	F3SJ-A□□□□N30	F3SJ-A□□□□N55
Accessories		(intermediate) (*), error mode label, Quick Insta * Number of intermediate b • For protective height from	brackets depends on protective height of F3SJ. n 600 to 1,130 mm : 1 set for each of the emitter and receiver is included n 1,136 to 1,658 mm: 2 sets for each of the emitter and receiver are included n 1,660 to 2,180 mm: 3 sets for each of the emitter and receiver are included n 2,195 to 2,500 mm: 4 sets for each of the emitter and receiver are included		
Applicable standards * IEC 61496-1, EN 61496-1, UL 61496-1, Type 4 ESPE (Electro-Sensitive Protective Equipment) IEC 61496-2, EN 61496-2, UL 61496-2, Type 4 AOPD (Active Opto-electronic Protective Devices) IEC 61508-1 to -3, EN 61508-1 to -3 SIL3 ISO 13849-1: 2015, EN ISO 13849-1: 2015 (PLe/Safety Category 4) UL 508, UL 1998, CAN/CSA C22.2 No.14, CAN/CSA C22.2 No.0.8					

^{*} Refer to Safety Precautions for information about Legislation and Standards.

Response Time

Model	Protected Height (mm)	Number of Beams	Response time ms (ON to OFF)	Response time ms (OFF to ON)
	245 to 263	26 to 28	11	44
	281 to 389	30 to 42	12	48
	407 to 497	44 to 54	13	52
F3SJ-A□14 Series	515 to 605	56 to 66	14	56
	623 to 731	68 to 80	15	60
	767 to 983	84 to 108	17.5	70
	1,055 to 1,271	116 to 140	20	80
	245	16	10	40
	275 to 425	18 to 28	11	44
	455 to 635	30 to 42	12	48
F3SJ-A□20 Series	665 to 815	44 to 54	13	52
	845 to 995	56 to 66	14	56
	1,025 to 1,205	68 to 80	15	60
	1,235 to 1,505	82 to 100	17.5	70
	245 to 395	10 to 16	10	40
	420 to 720	17 to 29	11	44
	745 to 1,045	30 to 42	12	48
F3SJ-A□30 Series	1,070 to 1,295	43 to 52	13	52
	1,395 to 1,620	56 to 65	14	56
	1,745 to 1,995	70 to 80	15	60
	2,120 to 2,495	85 to 100	17.5	70
	270 to 770	6 to 16	10	40
F3SJ-A□55 Series	820 to 1,420	17 to 29	11	44
rooj-A∟joo Series	1,470 to 2,070	30 to 42	12	48
	2,120 to 2,470	43 to 50	13	52

Note: Use the following expressions for series connection.

For 2-set series connection:

Response time (ON to OFF): Response time of the 1st unit + Response time of the 2nd unit - 1 (ms), Response time (OFF to ON): Response time calculated by the above x 4 (ms) For 3-set series connection:

Response time (ON to OFF):

Response time of the 1st unit + Response time of the 2nd unit + Response time of 3rd unit - 5 (ms), Response time (OFF to ON): Response time calculated by the above x 5 (ms) (For models with the "-TS" suffix, multiply the response time obtained by the above x 5 (ms), or use 200 ms, whichever is less.)

For 4-set series connection:

Response time (ON to OFF): Response time of the 1st unit + Response time of the 2nd unit + Response time of the 3rd unit + Response time of the 4th unit - 8 (ms) Response time (OFF to ON): Response time calculated by the above x 5 (ms)

Cable Extension Length

Total cable extension length must be no greater than the lengths described below.

When the F3SJ and an external power supply are directly connected, or when the F3SJ is connected to a G9SA-300-SC.

Condition	1 set	2 sets	3 sets	4 sets
Using incandescent lamp for auxiliary output and external indicator output	45 m	40 m	30 m	20 m
Not using incandescent lamp *	100 m	60 m	45 m	30 m

When connected to the F3SP-B1P

Condition	1 set	2 sets	3 sets	4 sets
Using incandescent lamp for external indicator output 2	40 m	30 m	25 m	20 m
Using incandescent lamp for external indicator output 1	60 m	45 m	30 m	20 m
Using incandescent lamp for auxiliary output 1	00 111	40 111	30 111	20 111
Not using incandescent lamp *	100 m	60 m	45 m	30 m

Note: Keep the cable length within the rated length. Failure to do so is dangerous as it may prevent safety functions from operating normally.
★ The F39-A01P□-PAC Dedicated External Indicator Set uses LEDs. Refer to the cable extension lengths for "Not using incandescent lamp".

Accessories

Control Unit

Item	Model	F3SP-B1P
Applicable sen	sor	F3SJ-B/A (Only for PNP output type) *
Power supply	voltage	24 VDC±10%
Power consum	ption	DC1.7 W max. (not including sensor's current consumption)
Operation time)	100 ms max. (not including sensor's response time)
Response time)	10 ms max. (not including sensor's response time)
	Number of contacts	3NO+1NC
Relay output	Rated load	25 VAC 5 A (cos φ = 1), 30 VDC 5 A L/R = 0 ms
	Rated current	5 A
Connection	Between sensors	M12 connector (8-pin)
type	Others	Terminal block
Weight (packed	d state)	Approx. 280 g
Accessories		Instruction manual

*NPN output type cannot be connected. Also, the system cannot be used as a muting system.

Laser Pointer

Item Model	F39-PTJ
Applicable sensor	F3SJ Series
Power supply voltage	4.65 or 4.5 VDC
Battery	Three button batteries (SR44 or LR44)
Battery life *	SR44: 10 hours of continuous operation, LR44: 6 hours of continuous operation
Light source	Red semiconductor laser (wavelength: 650 nm, 1 mW max. JIS class 2, EN/IEC class 2, FDA class II)
Spot diameter (typical value)	6.5 mm at 10 m
Ambient temperature	Operating: 0 to 40°C Storage: -15 to 60°C (with no icing or condensation)
Ambient humidity	Operating and storage: 35% to 85% (with no condensation)
Material	Laser module case: aluminum Mounting bracket: aluminum and stainless
Weight	Approx. 220 g (packed)
Accessories	Laser safety standard labels (EN: 1, FDA: 3) Button batteries (SR44: 3), instruction manual

^{*} Battery life varies depending on a battery used.

Dedicated External Indicator Set

Item Model	F39-A01PR-PAC	F39-A01PG-PAC	F39-A01PY-PAC	
Applicable sensor	pplicable sensor F3SJ-A (Common for PNP/NPN output type. Can be attached to emitters and/or receivers)			
Light source Red LED Green LED		Green LED	Yellow LED	
Power supply voltage 24 VDC±10% (supplied by sensor)				
Consumption current	50 mA max. (supplied by sensor)			
Connection type	Dedicated accessory connector cable (Sensor side: Dedicated 10-pin connector, Indicator side: M12 8-pin connector)			
Set details	Indicator (red), Dedicated connector cable (0.1 m), Dedicated mounting bracket (1 for each)	Indicator (green), Dedicated connector cable (0.1 m), Dedicated mounting bracket (1 for each)	Indicator (yellow), Dedicated connector cable (0.1 m), Dedicated mounting bracket (1 for each)	

Water-resistant Case

Item Model	F39-EJ□□□-L,	F39-EJ□□□-D	
Applicable sensor	F3SJ-A Series Curtains with a protective height of 600 mm or shorter.	F3SJ-A Series Curtains with a protective height of 605 mm or longer.	
Ambient temperature	-10 to 55°C (operation and storage)	13 to 33°C (operation and storage)	
Mounting direction	No restrictions	Vertical direction only (see following diagram)	
Operating range	0.2 to 7 m (for a protective height of 1,631 mm max.), 0.2 to 5 m (for a protective height of 1,655 mm min.)		
Degree of protection	IP67 (IEC 60529) (When assembled according to the application precautions)		
Material	Case: Acrylic resin, Rubber: Nitrile rubber, M5 bolt: SUSXM7, M4 bolt: SUS316L, Cable: Oil-resistant PVC, Plate: SUS304, Mounting Bracket (optional): SUS304		
Weight (packed state)	Calculation formula: Weight (g) = 1.5 x		

Note: 1. Vibration

When using Curtains with a protective height of 605 mm or more, the vibration performance of the applicable sensor is reduced. Do not use these Curtains in locations that are subject to vibration.

2. Operating range

When using these cases, the operating range of the applicable sensor is reduced. Check the specifications prior to use.

3. Mounting direction

When using Curtains with a protective height of 605 mm or more, some slackness occurs due to the weight of the Curtain.


For this reason, mount these Curtains only in the vertical direction.

Horizontal direction

Terminating end

Cable end

Mounting direction (the cable end and terminating end can be positioned in either direction)






Connections

Basic Wiring Diagram

[PNP Output]

Wiring when using manual reset mode, external device monitoring



(Gray) Communication line (+)

(Pink) Communication line (-)


+24 VDC Power 0 V

Wiring for auto reset mode

- The auto reset mode will be enabled when the emitter is wired as shown below.
- S1 : External test switch (connect to 0 V if a switch is not required) S3 : Lockout reset switch
- (connect to 24 V if a switch is not required)
- K2 : Load or PLC, etc. (for monitoring)
- *1. Use a switch for small loads

Wiring when the external device monitoring function will not be used

- · Use a setting tool to set the external device monitoring function to "Disabled."
- When using an auxiliary output 1 that has not been changed (output operation mode is "Safety Output Information," and reverse output mode is "Enabled), the external device monitoring function will be disabled when auxiliary output 1 and the external device monitoring input are connected as shown below.




[NPN Output]

Wiring when using manual reset mode, external device monitoring


0 V (Blue)

input (White) Test input (Black)

select




Wiring for auto reset mode



Wiring when the external device monitoring function will not be used

- Use a setting tool to set the external device monitoring function to "Disabled."
- When using an auxiliary output 1 that has not been changed (output operation mode is "Safety Output Information," and reverse output mode is "Enabled), the external device monitoring function will be disabled when auxiliary output 1 and the external device monitoring input are connected as shown below.



Basic Wiring Diagram for Muting System

[PNP Output]

Wiring when using muting and external device monitoring functions

Emitter Communication line (+) Muting input 2 (Red) (Blue) Muting input 1 (White) Reset input (Yellow) Communication (Blow) V 42+ Safety output 1 (Black) 0 V (Blue) Test input (Black) MAuxiliary output 1 (Yellow) Brown External device monitoring input +24 V (KM1) (K1) *****5 KM2 +24 VDC 0 V supply

S1 S2 : External test switch (connect to 0 V if a switch is not required)

: Lockout reset switch (connect to 24 V if a switch is not required)

Α1 : Contact by muting sensor A1 B1 Contact by muting sensor B1

: Safety relay with force-guided contact (G7SA) or magnetic contactor KM1, KM2


: Load or PLC, etc. (for monitoring)

M1 : Muting lamp

- *1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).
- *2. When using the interlock function, this also functions as an interlock reset switch. (Must be set with a setting tool.)
- *3. F3SJ operates even when K1 is not connected.
- *4. Connect the muting lamp to either the external indicator output or auxiliary output 1 for the emitter or the receiver. When connecting the muting lamp to auxiliary output 1, the parameter must be changed with a setting tool.
- *5. Two-wire type muting sensor cannot be used.

[NPN Output]

Wiring when using muting and external device monitoring functions



S1 : External test switch (connect to 24 V if a switch is not required)

S2 : Lockout reset switch (connect to 0 V if a switch is not required) Α1 : Contact by muting sensor A1

Contact by muting sensor B1

: Safety relay with force-guided contact (G7SA) or magnetic contactor KM1, KM2

K1 Load or PLC, etc. (for monitoring)

M1 : Muting lamp

- *1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).
- *2. When using the interlock function, this also functions as an interlock reset switch. (Must be set with a setting tool.)
- *3. F3SJ operates even when K1 is not connected.
- *4. Connect the muting lamp to either the external indicator output or auxiliary output 1 for the emitter or the receiver. When connecting the muting lamp to auxiliary output 1, the parameter must be changed with a setting tool.
- ★5. Two-wire type muting sensor cannot be used

When external device monitoring function is not required

- Use a setting tool to set the external device monitoring function to
- When using an auxiliary output 1 that has not been changed (output operation mode is "Safety Output Information," and reverse output mode is "Enabled), the external device monitoring function will be disabled when auxiliary output 1 and the external device monitoring input are connected.


When external device monitoring function is not required

- Use a setting tool to set the external device monitoring function to "Disabled '
- When using an auxiliary output 1 that has not been changed (output operation mode is "Safety Output Information," and reverse output mode is "Enabled), the external device monitoring function will be disabled when auxiliary output 1 and the external device monitoring input are connected.

Wiring Diagram When Using Simple Wiring System

F39-CN5 simple wiring connector

Internal wiring of F39-CN5 simple wiring connector








6

2

PIN No




- S1 : External test switch (connect 0 V if a switch is not required)
- *1. Use a switch for small loads (input specifications: 24 V, 1.0 mA max.).
- ***2.** When the lockout reset function is used, connect to 24 V via a lockout reset switch (N.C. contact).
- *3. Make sure the Communication lines are insulated.

 If the lines are shorted, the F3SJ-A enters the lockout state.

Controllers connectable with PNP output F3SJ series

Safety controller	Model
Safety Network Controller	NE1A series
Safety Controller	G9SP series
Flexible Safety Unit	G9SX series
Safety Relay Unit	G9SA series

[NPN Output]



- S1: External test switch (connect 24 V if a switch is not required)
- *1. Use a switch for small loads
- (input specifications: 24 V, 1.0 mA max.).
- *2. When the lockout reset function is used, connect to 0 V via a lockout reset switch (N.C. contact).
- *3. Make sure the Communication lines are insulated. If the lines are shorted, the F3SJ-A enters the lockout state.

Controller connectable with NPN output F3SJ series

Safety controller	Model
Safety Relay Unit	G9SA-301-P

Note: When using the Simple Wiring Connector (F39-CN5), the following functions are not available.

- Manual Reset
- External Device Monitoring
- · Auxiliary Outputs 1, 2
- Muting/Override

When using the setting tools, make sure to keep the settings in the factory default.

Input/Output Circuit Diagram


Entire Circuit Diagram

[PNP Output]

The numbers in circles indicate the connectors' pin numbers.

The black circles indicate connectors for series connection.

The words in brackets ([]) indicate the signal name for muting system.




- *1. Open or muting input 1 for models with the "-TS" suffix. *2. Open or muting input 2 for models with the "-TS" suffix.

[NPN Output]

The numbers in circles indicate the connectors' pin numbers.

The black circles indicate connectors for series connection.

The words in brackets ([]) indicate the signal name for muting system.



F3SJ-A


Connection Circuit Examples

Wiring for single F3SJ-A application [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-A□□□□□□□□ Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring for connection with a controller F3SP-B1P [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-A□□□□□□□ Control Unit F3SP-B1P Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

Application Overview

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Note: It cannot be used as a muting system when F3SP-B1P is used.

Wiring for connection with a controller G9SX-AD322-T15 [PNP Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-A□□□□□□□ Flexible Safety Unit G9SX-AD322-T15 Safety Relay G7SA	M1: 0 M2: 1	Auto

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M1 is turned OFF immediately when the beam is blocked, and stop command is sent to the motor controller for the motor M2.
- The power supply to the motor M2 is turned OFF after OFF-delay time.
- The power supply to the motor M1 and M2 is kept OFF until the beams are unblocked.




Wiring for single F3SJ-A application [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-A□□□□N□□ Safety Relay G7SA	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.

- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed.




Wiring for connection with a controller G9SA-301-P [NPN Output]

Highest achievable PL/ safety category	Model	Stop category	Reset
PLe/4 equivalent	Safety Light Curtain F3SJ-A□□□□N□□ Safety Relay Unit G9SA-301-P 24V DC Safety Relay G7SA Emergency Stop Switch A165E/A22E	0	Manual

Note: The above PL is only the evaluation result of the example. The PL must be evaluated in an actual application by the customer after confirming the usage conditions.


- The power supply to the motor M is turned OFF when the beam is blocked.
- The power supply to the motor M is turned OFF when the emergency stop switch is pressed.
- The power supply to the motor M is kept OFF until the beams are unblocked and the reset switch S2 is pressed while the emergency stop switch is released.



Dimensions (Unit: mm)

Main Units

When Using Standard Mounting Brackets




C (protective height): 4-digit number in the table A = C + 74, B = C + 46.5

D = C - 20	E = Se	ee table	below
------------	--------	----------	-------


Protective height	Number of intermediate brackets	E*
245 to 596	0	
600 to 1,130	1	E = B/2
1,136 to 1,658	2	E = B/3
1,660 to 2,180	3	E = B/4
2,195 to 2,500	4	E = B/5

*Use E = 530 or less when none of the E values shown above are used.

Side mounting



Mounting screw holes




C (protective height): 4-digit number in the table A = C + 74, B = C + 46.5


D = C - 20, E = See table below.


Protective height	Number of intermediate brackets	E*
245 to 596	0	
600 to 1,130	1	E = B/2
1,136 to 1,658	2	E = B/3
1,660 to 2,180	3	E = B/4
2,195 to 2,500	4	E = B/5

★ Use E = 530 or less when none of the E values shown above are used.


F39-LJ1 Detailed Dimensions of Bracket








Using Side Flat Mounting Bracket (F39-LJ2)






Dimensions A to C

Α	C + 74
В	C + 39.5
С	4-digit number of the model name (protective height)


Using Free Location Mounting Bracket (F39-LJ3)

Backside mounting

F39-LJ3 Material: Zinc die-cast Horizontal angle: ±10°










Side mounting

F39-LJ3 Material:Zinc die-cast/ stainless Horizontal angle: ±10°







Dimensions B, C, and F

В	C - 90
С	4-digit number of the model name (protective height)
F	Depends on the protective height. See the table on the right.

Dimensions F

Protective height	Number of intermediate brackets	F*
245 to 440	2	
443 to 785	3	B/2
794 to 1,140	4	B/3
1,145 to 1,490	5	B/4
1,495 to 1,840	6	B/5
1,845 to 2,180	7	B/6
2,195 to 2,500	8	B/7

*Use F = 350 or less when none of the F values shown above are used.

When only F39-LJ3 free-location mounting brackets are used without standard brackets, allow a space of at least 350 mm between the brackets. The number of brackets required varies according to the protective height. For details about the number of required brackets, refer to the table below

The standard included intermediate brackets are the same as the F39-LJ3 free-location mounting brackets. Purchase brackets as necessary if there are fewer intermediate brackets than required. When intermediate brackets are included, they can be used as free-location mounting brackets.


Required number of F39-LJ3 free-location mounting brackets for 1 F3SJ set (emitter/receiver) (2 pieces are included with F39-LJ3)

Protective height	Number of included free location brackets as intermediate brackets	Number of free location brackets to mount F3SJ	Number of free location bracket sets to be purchased (pcs)
245 to 440	0	4	2 sets (4)
443 to 596	0	6	3 sets (6)
600 to 785	2	6	2 sets (4)
794 to 1,130	2	8	3 sets (6)
1,136 to 1,140	4	8	2 sets (4)
1,145 to 1,490	4	10	3 sets (6)
1,495 to 1,658	4	12	4 sets (8)
1,660 to 1,840	6	12	3 sets (6)
1,845 to 2,180	6	14	4 sets (8)
2,195 to 2,500	8	16	4 sets (8)

Using Top/Bottom Bracket B (F39-LJ4)

Backside mounting


С




Note: Refer to the User's Manual for the dimensions for side mounting.

4-digit number of the model

name (protective height)



Using Top/Bottom Bracket C (F39-LJ11)






Α	C + 109
В	C + 69
С	4-digit number of the model name (protective height)

Mounting screw holes (54.5)C (Protective height) 4-Mounting holes


Using Space-saving Mounting Bracket (F39-LJ8)

Backside mounting




Dimensions A to C C + 23 Α В C - 10.3 4-digit number of the model

name (protective height)



C (Protective height)



Note: Because the F39-LJ8 cannot be mounted together with an intermediate bracket, keep the protective height at 600 mm max.

С

Guide to Replacing F3SJ-A with F3SJ-E/B (Including models whose production will be discontinued)

F3SJ-A to F3SJ-E/B replacement correspondence table (F3SJ-A mounting holes can be used without modification)

To check available brackets for replacement, refer to the table below.

To check dimensions when mounting brackets, refer to page 95.

The values in the table correspond to in the model name, meaning the protective height (mm) of a sensor.

□□□□P(N)20	F3SJ-A □□□□P(N)25	□□□□P(N)30	Replacement F3SJ-E/B	Top/bottom bracket (F39-LJB1)	t for replacement Compatible brack (F39-LJB4)
0245 0260 0275 0290	0260 0280	0245 0270 0295	0225		√ ×
	0300			✓	√
0305 0320 0335 0350 0365	0320 0340 0360	0320 0345 0370	0305		√
0380	0380			✓	✓
0395 0410 0425 0440 0455	0400 0420 0440	0395 0420 0445	0385		~
	0460			✓	✓
0470 0485 0500 0515 0530	0480 0500 0520	0470 0495 0520	0465		✓
	0540			✓	✓
0545 0560 0575 0590 0605	0560 0580 0600	0545 0570 0595	0545		✓
0620	0620	0620		✓	✓
0635 0650 0665 0680 0695	0640 0660 0680	0645 0670 0695	0625		✓
	0700			✓	✓
0710 0725 0740 0755 0770	0720 0740 0760	0720 0745 0770	0705		~
0705	0780	0705		✓	✓
0785 0800 0815 0830 0845	0800 0820 0840	0795 0820 0845	0785	·	*
0860 0875 0890 0905 0920	0880 0900 0920	0870 0895 0920	0865	· ·	· ·
0935	0940			✓	✓
0950 0965 0980 0995 01010	0960 0980 01000	0945 0970 0995	0945		√
0.010	1020	1020		✓	✓
1025 1040 1055 1070 1085 1100	1040 1060 1080	1045 1070 1095	1025		√
	1100			✓	√
1115 1130 1145 1160 1175	1120 1140 1160	1120 1145 1170	1105		✓

F3SJ-A

	F3SJ-A		Replacement F3SJ-B		t for replacement
□□□□P(N)20	□□□□P(N)25	□□□□P(N)30	□□□□P(N)25	Top/bottom bracket (F39-LJB1)	Compatible bracke
	1180	. ,	, ,	(F39-LJB1) √	(F39-LJB4)
1190	1200	1195	-	<u> </u>	•
	1220				
1205 1220	1240	1220 1245	1185		✓
1235	1240	1245			· ·
1250					
1250	1260			√	√
1265	1280	1270	-	•	*
1280	1300	1295	1265		
1295	1320	1320	1205		✓
1310					
1325					
1340	1340			✓	✓
1355	1360	1345			
1370	1380	1370	1345		
1385	1400	1395	1343		✓
1400					
1415					
	1420	1420		✓	√
1430	1440	1445	 		
1445	1460	1470	4.405		
1460	1480	1495	1425		✓
1475	1700	1700			
1490					
	1500			✓	✓
1505	1520	1520	 		
1520	1540	1545	1505		
1535	1560	1570	1505		✓
1550					
1565					
1580	1580			✓	✓
1595	1600	1595	<u> </u>		
1610	1620	1620	1585		
1625	1640	1645	1505		✓
1640					
1655					
	1660			✓	✓
1670	1680	1670	-		
1685	1700	1695	1665		
1700	1720	1720	1005		✓
1715					
1730					
	1740			✓	✓
1745	1760	1745			
1760	1780	1770	1745		
1775	1800	1795			✓
1790 1805					
1820	1820	1820		,	
			_	✓	✓
1835	1840	1845			
1850	1860	1870	1825		
1865 1880	1880	1895			√
1895					
	1900				,
10/2			_	✓	✓
1910	1920	1920			
1925	1940	1945	1905		
1940	1960	1970			✓
1955 1970					
1910	4000				
	1980		_	✓	✓
1985	2000	1995			
2000	2020	2020	1985		
2015	2040	2045			✓
2030					
2045					
2060	2060			✓	✓
2075	2080	2070			
0000	2100	2095	2065		
2090			ń l		1
2090 2105 2120	2120	2120			✓


<sup>Note: 1. Protective height and detection capability vary according to replacement. Check the safe design of your device before use.
2. The maximum protective height of F3SJ-E is 1,105 mm. Only the F3SJ-B can be replaced for the protective height of 1,185 or more.</sup>


Change of Dimensions due to Replacement

(1) Replacement by backside mounting

	F3SJ-A (Using standard bracket)	F3SJ-E/B (Top/bottom bracket used)	F3SJ-E/B (Compatible bracket used)
Dimensions (mm) from mounting wall surface to optical surface (mm)	26	43	43
Total length including bracket (mm)	Protective height + 74	Protective height + 69	Protective height + 159

Dimensional drawing from mounting wall surface to optical surface





(2) Replacement by side mounting

	F3SJ-A (Using standard bracket)	F3SJ-E/B (Top/bottom bracket used)	F3SJ-E/B (Compatible bracket used)
Dimensions of a protrusion from mounting wall (mm)	51	46	46
Total length including bracket (mm)	Protective height +74	Protective height +69	Protective height +159

Dimensional drawing of a protrusion from mounting wall





F3SJ-E/B


Replacement using intermediate brackets

For backside mounting, the F3SJ-A and F3SJ-E/B can be used without modification due to compatibility in mounting hole pitch. For side mounting, a new hole needs to be made due to the different mounting hole pitch.

Mounting hole pitch for side mounting using intermediate bracket

	F3SJ-A (Free-location bracket used)	F3SJ-E/B (Intermediate bracket used)	
Mounting hole pitch (mm)	15	42	


Dimensional drawing of mounting hole for side mounting using intermediate bracket




Change of Dimensions due to Replacement

	F3SJ-A (Free-location bracket used)	F3SJ-E/B (Intermediate bracket used)
Dimensions (mm) from mounting wall surface to optical surface (mm)	26	43

Using mounting bracket for short-length F3SN (F39-LJ5)



Inward + outward-facing mounting



Dimensions A to C Α

В

С

C + 65

C + 34

4-digit number of the model


name (protective height)

Accessories

Single-Ended Cable

F39-JD3A (L = 3 m) F39-JD7A (L = 7 m) F39-JD10A (L = 10 m)

Cable color: Gray for emitter Black for receiver F39-JD15A (L = 15 m) F39-JD20A (L = 20 m)



Double-Ended Cable

F39-JDR5B (L = 0.5 m) F39-JD1B (L = 1 m) F39-JD3B (L = 3 m) F39-JD5B (L = 5 m)

Cable color: Gray for emitter Black for receiver


F39-JD7B (L = 7 m) F39-JD10B (L = 10 m) F39-JD15B (L = 15 m) F39-JD20B (L = 20 m)

Waterproof connector

Insulated vinyl round cable 6.6 dia. with braided shield
8-wire (4-pair) (Cross section of conductor: 0.3 mm²/insulator diameter: 1.15 mm)
Standard length L


Simple Wiring Connector

F39-CN5




Control Unit

F3SP-B1P




Laser Pointer

F39-PTJ



Dedicated External Indicator Set


F39-A01□-PAC



Material: Stainless steel

Spatter Protection Cover F39-HJ






Material: PC (transparent area) ABS (non-transparent area)

Assembled dimensions



Mirror Column

F39-SML




Material: Aluminum alloy (Housing) Hot rolled steel (Base) PBT resin (Cap) Glass mirror (Mirror)

3-M10

Model	Dimension L
F39-SML0990	990
F39-SML1310	1310
F39-SML1630	1630
F39-SML1950	1950


Setting Support Software for the F3SJ

F39-GWUM



Protective Bar

F39-PJ□□□□-S **Backside mounting**







C (protective height): 4-digit number in the table A = C + 74, B = C + 46.5

Protective height	Number of intermediate brackets used (3)	D
245 to 995	0	
1,001 to 2,000	1	B/2
2,009 to 2,500	2	B/3


Note: For reference, D is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

Side mounting





*The four intermediate brackets (F39-PJ-MS) for side mounting are not provided.




C (protective height): 4-digit number in the table


Protective height	Intermediate brackets for side mounting Number of intermediate brackets used (4)	D
245 to 995	0	
1,001 to 2,000	1	B/2
2,009 to 2,500	2	B/3

Note: For reference, D is the dimension that will not interfere with the intermediate bracket on the Safety Light Curtain body.

Water-resistant Case



Side mounting



	_
MEMO	

Function List

Functions that can be used on F3SJ are shown as follows: Refer to the F3SJ User's Manual for details. For manual number, check the "Related Manuals" at the end of the catalog.

Basic functions

Function	F3SJ-E (EASY)	F3SJ-B (BASIC)	F3SJ-A (ADVANCED)
Self-test function	✓	✓	✓
External test function	✓	✓	✓
External device monitoring function	X	√ * 1	✓
Interlock function	X	√ * 1	✓
Auxiliary output function	X	✓	✓
Muting function *2	X	✓	✓

^{*1.} Cannot be used at muting.

Functions for individual applications

Override function	X	✓	✓
Partial muting function	Х	X	✓
Position detection muting function	Х	X	✓
Fixed blanking function	Х	X	√
Floating blanking function	Х	X	√
Warning zone function	Х	X	✓
Use of setting tools	Х	X	✓

Wiring/mounting related function

Series connection function	X	✓	✓
Dead space less (single connection)	✓	✓	✓
Dead space less (series connection)	X	X	✓
Response time integration (15 ms) *3	✓	✓	Х
Simple wiring	✓	X	Х
Connector cable	X	✓	✓
Quick mounting	✓	✓	X
TOP/BOTTOM indicator for beam adjustment	√	√	X
Laser Pointer	✓	✓	✓

^{*3.} Convenient to calculate safety distance.

Indicator related functions

External indicator output	X	√ * 4	√ * 5	
Muting error display	X	✓	X	

Note: The specifications of the models with the suffixes "-01TS", "-02TS" or "-TS" are different. Refer to the Specifications.

^{√:} Can be used.

X: Cannot be used.

^{*2.} The muting time for the F3SJ-A can be set via the software tool. The muting time for the F3SJ-B cannot be changed.

^{*4.} An external Indicator can be connected to the F3SJ-B auxiliary output .

^{*5.} An external Indicator can be connected to the F3SJ-A auxiliary output 1 and 2, external Indicator 1 and 2.

F3SJ-E/F3SJ-B/F3SJ-A

Self-test Function

A self-test is performed to check for errors when the power is turned ON. Also, the self-test is regularly performed (within the response time) while operating.

External Test Function

This function stops the emission using an external signal. It can be used to verify that a safety system should properly stop when F3SJ is interrupted.

External Device Monitoring Function

This function detects malfunctions, such as welding, in external relays (or contactors) that control the hazardous part of a machine. This function constantly monitors that a specified voltage is applied to the receiver's external device monitoring input line, and the system enters lockout state when an error occurs. The relay's operational delay can be up to 300 ms without being evaluated as an error. For example, if the normally closed N.C. contact does not close within 0.3 s after the safety outputs turn from ON to OFF, and a specified voltage is not applied to the external device monitoring line, it is evaluated as an error and the system enters a lockout state. To utilize this function properly, use safety relays and contactors that have force guided or mechanically linked contact structure.

Interlock Function

The F3SJ turns the safety outputs OFF when its power is turned on or its beam is interrupted and holds this state until reset input is applied. This state is called "interlock".

Two methods can be used to reset the interlock state: "auto reset that automatically turns safety outputs ON when the interrupting object is removed" and "manual reset mode that keeps safety outputs OFF until a reset signal is provided, if the interrupting object is removed".

Auto Reset

When the interrupting object is removed from the detection zone, the safety outputs automatically turn ON. Auto reset is used on machines where a worker is not able to enter the area between the detection zone and the hazardous part of the machine.

Manual Reset

When a reset input is given while no interrupting object exists in a detection zone, the safety outputs turn ON. This allows the machine to be manually reset using a reset switch after ensuring safety, preventing unexpected startup.

Auxiliary Output Function

The auxiliary output is used to monitor the status of the F3SJ. This output can be connected to a device such as programmable controller.

Muting Function

Muting function temporarily disables safety function of the F3SJ, keeping safety output ON even if beams are interrupted. This makes it possible to install safety light curtains for AGV passage, enabling both safety and productivity.

Override Function

The override function turns the safety outputs ON when the muting start condition is not satisfied. If a workpiece stops while passing through the F3SJ, as shown below, causing a muting error, the normal state cannot be recovered unless the workpiece is removed from the muting sensors and the detection field of the F3SJ. However, the override function will mute the safety outputs of the F3SJ so that the conveyor can be restarted to move the workpiece out of the muting sensors and detection zone.

Partial Muting Function

Partial muting function secures safety without enabling muting except for beams when a workpiece passes.

Position Detection Muting

A limit switch or other means is used to detect when the robot is in a safe position, and muting is then applied.

Fixed Blanking Function

Fixed blanking function disables a specific beam of the F3SJ. This function keeps safety output ON even when part of machinery equipment exists within a detection zone.

Floating Blanking Function

Floating blanking function increases the diameter of the F3SJ's detection capability and turns OFF the safety output when multiple objects are detected. When there is a moving object with a fixed width in the detection area that we do not want to detect, the detection function can be disabled.

Warning Zone Function

When an individual enters, a warning lamp lights or buzzer sounds without stopping the equipment by dividing the detection zone into the detection zone and a warning zone.

Setting Tool

The following setting tools (sold separately) can be purchased in order to change or confirm various F3SJ-A parameters.

- F39-MC21 Setting Console
- F39-GWUM SD Manager Setting Support Software for the F3SJ

Series Connection Function

Up to 3 sets of the F3SJ-Bs or up to 4 sets of F3SJ-As can be seriesconnected. Series connection allows them to be used as a safety light curtain, requiring only one set to be wired to a controller and preventing mutual interference.

Safety Precautions

Description shown below is only a guideline to choose a safety sensor. To use the product properly, you must read its instruction manual that comes with the product.

Legislation and Standards

- Application of a sensor alone cannot receive type approval provided by Article 44-2 of the Industrial Safety and Health Act of Japan. It is necessary to apply it in a system.
 Therefore, when using the F3SJ in Japan as a "safety system for
 - pressing or shearing machines" prescribed in Article 42 of that law, the system must receive type approval.
- The F3SJ is electro-sensitive protective equipment (ESPE) in accordance with European Union (EU) Machinery Directive Index Annex V, Item 2.
- 3. The F3SJ-E/B is in conformity with the following standards:
 - (1) EC legislation Machinery Directive 2006/42/EC EMC Directive 2014/30/EU
 - (2) European standards
 EN 61496-1 (type 4 ESPE),
 EN 61496-2 (type 4 AOPD),
 EN 61508-1 through -3 (SIL3),

EN 61000-6-4, EN ISO 13849-1:2015 (PLe/Safety Category 4)

- (3) International standards
 IEC 61496-1 (type 4 ESPE),
 IEC 61496-2 (type 4 AOPD),
 IEC 61508-1 through -3 (SIL3),
 ISO 13849-1:2015 (PLe/Safety Category 4)
- JIS standards
 JIS B 9704-1 (type 4 ESPE),
 JIS B 9704-2 (type 4 AOPD)
 North American standards:
- (5) North American standards: UL 61496-1 (type 4 ESPE), UL 61496-2 (type 4 AOPD), UL 508, UL 1998, CAN/CSA C22.2 No.14, CAN/CSA C22.2 No.0.8
- 4. The F3SJ-A is in conformity with the following standards:
 - (1) EC legislation
 Machinery Directive 2006/42/EC
 EMC Directive 2014/30/EU
 - (2) European standards
 EN 61496-1 (type 4 ESPE),
 EN 61496-2 (type 4 AOPD),
 EN61508-1 through -3 (SIL3)
 EN ISO 13849-1:2015 (PLe/Safety Category 4)
 - (3) International standardsI EC 61496-1 (type 4 ESPE), IEC 61496-2 (type 4 AOPD), IEC 61508-1 through -3 (SIL3) ISO13849-1: 2015 (PLe/Safety Category 4)

- JIS standards
 JIS B 9704-1 (type 4 ESPE),
 JIS B 9704-2 (type 4 AOPD)
- (5) North American standards:
 UL 61496-1 (type 4 ESPE),
 UL 61496-2 (type 4 AOPD),
 UL 508, UL 1998, CAN/CSA C22.2 No.14,
 CAN/CSA C22.2 No.0.8
- The F3SJ received the following certification from the EUaccredited body, TÜV SÜD Product Service GmbH:
 - EC type test based on machinery directive Type 4 ESPE (EN 61496-1),
 Type 4 AOPD (EN 61496-2)
- The F3SJ is scheduled to received certificates of UL listing for US and Canadian safety standards from the Third Party Assessment Body UL.
 - Type 4 ESPE (UL 61496-1),
 Type 4 AOPD (UL 61496-2)
- 7. The F3SJ is designed according to the standards listed below. To make sure that the final system complies with the following standards and regulations, you are asked to design and use it in accordance with all other related standards, laws, and regulations. If you have any questions, consult with specialized organizations such as the body responsible for prescribing and/or enforcing machinery safety regulations in the location where the equipment is to be used
 - European standards: EN 415-4, EN 692, EN 693
 - US Occupational Safety and Health Standards: OSHA 29 CFR 1910.212
 - US Occupational Safety and Health Standards: OSHA 29 CFR 1910.217
 - American National Standards: ANSI B11.1 to B11.19
 - American National Standards: ANSI/RIA 15.06
 - Canadian Standards Association CSA Z142, Z432, Z434
 - SEMI Standards SEMI S2
 - Japan Ministry of Health, Labour and Welfare "Guidelines for Comprehensive Safety Standards of Machinery"

8.	We have obtained S-Mark Certification from Legislation and
	Standards Korea Occupational Safety & Health Agency (KOSHA).
	(F3SJ-E P25-S/F3SJ-B P25-S/
	F3SJ-A□□□P□□-S)

F3SJ-E/F3SJ-B/F3SJ-A

Precautions on Safety

Indication and meaning for safe use

This instruction manual describes notification and/or waning with indication and symbols as shown below for safe use of F3SJ. This notification describes very important details for safety. You must follow the description. Shown below are indication and symbols.



Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.



If you fail to use a product properly, it may result in injuries or damage on property.

Meanings of Alert Symbols



Inhibited Indicates general inhibition.

Alert Statements in this Manual

F3SJ-B Description applied to F3SJ-B models.

F3SJ-B Description applied to F3SJ-B models.

F3SJ-A Description applied to F3SJ-A models.

For users

⚠ WARNING

F3SJ-E F3SJ-B F3SJ-A

The FS3J must be installed, set, and integrated into the mechanical control system by a qualified technician who has received the appropriate training. Failure to make correct settings may prevent detection of people and result in serious injury.

F3SJ-A

When changing parameters with a setting tool (F39-GWUM or F39-MC21), the change must be made and the contents of the change must be managed by the person in charge of the system. Unintentional or mistaken parameter changes may prevent detection of people and result in serious injury.

For machines

⚠ WARNING

F3SJ-E F3SJ-B F3SJ-A

Do not use this sensor for machines that cannot be stopped by electrical control. For example, do not use it for a pressing machine that uses full-rotation clutch. Otherwise, the machine may not stop before a person reaches the hazardous part, resulting in serious injury.

F3SJ-B F3SJ-A

Do not use the auxiliary output or external indicator output for safety applications. Human body may not be detected when F3SJ fails, resulting in serious injury.

For installation

⚠ WARNING

F3SJ-E F3SJ-B F3SJ-A

Make sure to test the operation of the F3SJ after installation to verify that the F3SJ operates as intended. Make sure to stop the machine until the test is complete.

Unintended function settings may cause a person to go undetected, resulting in serious injury.

F3SJ-E F3SJ-B F3SJ-A

Make sure to install the F3SJ at the safe distance from the hazardous part of the equipment. Otherwise, the machine may not stop before a person reaches the hazardous part, resulting in serious injury.

F3SJ-E F3SJ-B F3SJ-A

Install a protective structure so that the hazardous part of a machine can only be reached by passing through the sensor's detection zone. Install the sensors so that part of the person is always present in the detection zone when working in a machine's hazardous zones. If a person is able to step into the hazardous zone of a machine and remain behind the 's detection zone, configure the system with an interlock function that prevents the machine from being restarted. Otherwise it may result in heavy injury.

F3SJ-B F3SJ-A

Install the interlock reset switch in a location that provides a clear view of the entire hazardous area and where it cannot be activated from within the hazardous area.

F3SJ-E F3SJ-B F3SJ-A

The F3SJ cannot protect a person from a projectile exiting the hazardous zone. Install protective cover(s) or fence(s).

F3S.I-A

When detection of an area has been disabled by the fixed blanking function, provide a protective structure around the entire area that will prevent a person from passing through it and reaching the hazardous part of the machinery. Failure to do so may prevent detection of people and result in serious injury.

F3SJ-A

After setting the fixed blanking function, be sure to confirm that a test rod is detected within all areas that require detection. Failure to do so may prevent detection of people and result in serious injury.

F3SJ-A

When the fixed blanking function or the floating blanking function is used, the diameter for the smallest detectable object becomes larger. Be sure to use the diameter for the smallest detectable object for the fixed blanking function or the floating blanking function when calculating the safety distance. Failure to do so may prevent the machinery from stopping before a person reaches the hazardous part of the machinery, and result in serious injury.

F3SJ-B F3SJ-A

The muting and override functions disable the safety functions of the device. Additional safety measures must be taken to ensure safety while these functions are working.

F3SJ-B F3SJ-A

Install muting sensors so that they can distinguish between the object that is being allowed to be pass through the detection zone and a person. If the muting function is activated by the detection of a person, it may result in serious injury.

F3SJ-B F3SJ-A

Muting lamps (external indicators) that indicate the state of the muting and override functions must be installed where they are clearly visible to workers from all the operating positions.

F3SJ-A

Muting times must be precisely set according to the application by qualified personnel who have received appropriate training. In particular, if the muting time limit is to be set to infinity, the person who makes the setting must bear responsibility.

F3SJ-B F3SJ-A

Use two independent input devices for the muting inputs.

F3SJ-B F3SJ-A

Install the F3SJ, Muting Sensors, or a protective wall so that workers cannot enter hazardous areas while muting is in effect, and set muting times.

F3SJ-B F3SJ-A

Position the switch that is used to activate the override function in a location where the entire hazardous area can be seen, and where the switch cannot be operated from inside the hazardous area. Make sure that nobody is in the hazardous area before activating the override function.

F3SJ-E F3SJ-B F3SJ-A

Install the sensor system so that it is not affected by reflective surfaces. Failure to do so may hinder detection, resulting in serious injury.

F3SJ-E F3SJ-B F3SJ-A

When using more than 1 set of F3SJ, install them so that mutual interference does not occur, such as by configuring series connections or using physical barriers between adjacent sets.

F3SJ-E F3SJ-B F3SJ-A


Make sure that the F3SJ is securely mounted and its cables and connectors are properly secured.

F3SJ-E F3SJ-B F3SJ-A

Make sure that no foreign material, such as water, oil or dust, enters the inside of the F3SJ while the cap is removed.

F3SJ-E F3SJ-B F3SJ-A

Do not use the sensor system with mirrors in a regressive reflective configuration. Doing so may hinder detection. It is possible to use mirrors to "bend" the detection zone to a 90-degree angle.



F3SJ-E F3SJ-B F3SJ-A

When using series connections, perform inspection of all connected F3SJs as instructed in the User's Manual.

For wiring

⚠ WARNING

F3SJ-E F3SJ-B F3SJ-A

[For PNP output]

Connect the load between the output and 0V line.

[For NPN output]

Connect the load between the output and $\pm 24V$ line. If $\pm 24V$ and 0 V are connected, it is dangerous because operation mode is inversed to "ON when interrupted".

F3SJ-E F3SJ-B F3SJ-A

[For PNP output]

Do not short-circuit an output line to +24 V line. Otherwise, the output is always ON. Also, 0 V of the power supply must be grounded so that output should not turn ON due to grounding of the output line.

[For NPN output]

Do not short-circuit an output line to 0 V line. Otherwise, the output is always ON. Also, +24 V of the power supply must be grounded so that output should not turn ON due to grounding of the output line.

F3SJ-E F3SJ-B F3SJ-A

Configure the system by using the optimal number of safety outputs that satisfy the requirements of the necessary safety category.

F3SJ-E F3SJ-B F3SJ-A

Do not connect each line of F3SJ to a DC power supply higher than 24 V+20%. Also, do not connect to an AC power supply. Failure to do so may result in electric shock.

F3SJ-E F3SJ-B F3SJ-A

For F3SJ to comply with IEC 61496-1 and UL 508, the DC power supply unit must satisfy all of the following conditions:

- Must be within rated power voltage (24 VDC±20%).
- Must have tolerance against the total rated current of devices if it is connected to multiple devices.
- Must comply with EMC directives (industrial environment)
- Double or enhanced insulation must be applied between the primary and secondary circuits
- Automatic recovery of overcurrent protection characteristics (reversed L sagging)
- · Output holding time must be 20 ms or longer
- Must satisfy output characteristic requirements for class 2 circuit or limited voltage current circuit defined by UL 508
- Must comply with EMC, laws, and regulations of a country or a region where F3SJ is used. (Ex: In EU, the power supply must comply to the EMC Low Voltage Directive)

F3SJ-E F3SJ-B F3SJ-A

Double or enhanced insulation from hazardous voltage must be applied to all input and output lines. Failure to do so may result in electric shock.

F3SJ-E F3SJ-B F3SJ-A

Note: Keep the cable length within the rated length. Failure to do so is dangerous as it may prevent safety functions from operating normally.

F3SJ-E F3SJ-B F3SJ-A

Make sure to perform wiring while the power supply is OFF.

Others (F3SJ-B) (F3SJ-A)

WARNING

To use the F3SJ in PSDI mode (Reinitiation of cyclic operation by the protective equipment), you must configure an appropriate circuit between the F3SJ and the machine. For details about PSDI, refer to OSHA1910.217, IEC 61496-1, and other relevant standards and regulations.

Do not try to disassemble, repair, or modify this product. Doing so may cause the safety functions to stop working properly.

Do not use the F3SJ in environments where flammable or explosive gases are present. Doing so may result in explosion.

Perform daily and 6-month inspections for the F3SJ. Otherwise, the system may fail to work properly, resulting in serious injury.

Do not use radio equipment such as cellular phones, walkietalkies, or transceivers near the F3SJ.

Note: For customers using the F3SJ-B□□□□P25-01TS: The functions available are external test, lockout reset, auxiliary output and series connection.

Installation Conditions

Detection Zone and Approach F3SJ-B F3SJ-B F3SJ-A

⚠ WARNING

Install a protective structure so that the hazardous part of a machine can only be reached by passing through the sensor's detection zone. Install the sensors so that part of the person is always present in the detection zone when working in a machine's hazardous zones.

If a person is able to step into the hazardous zone of a machine and remain behind the F3SJ's detection zone, configure the system with an interlock function that prevents the machine from being restarted. Failure to do so may result in serious injury.

Install the interlock reset switch in a location that provides a clear view of the entire hazardous zone and where it cannot be activated from within the hazardous zone.

The F3SJ cannot protect a person from a projectile exiting the hazardous zone. Install protective cover(s) or fence(s).

Right positions

The hazardous zone of a machine can be reached only by passing through the sensor's detection zone.



While working, a person is inside the sensor's detection zone.



Incorrect installation

It is possible to reach the hazardous zone of a machine without passing through the sensor's detection zone.




A person is between the sensor's detection zone and the hazardous zone of a machine.



Safety Safety Distance F3SJ-E F3SJ-B F3SJ-A

The safety distance is the distance that must be set between the F3SJ and a machine's hazardous part to stop the hazardous part before a person or object reaches it. The safety distance varies according to the standards of each country and the individual specifications of each machine. In addition, the calculation of the safety distance differs if the direction of approach is not vertical to the detection zone of the F3SJ. Always refer to relevant standards.



⚠ WARNING

Make sure to secure the safety distance (S) between the F3SJ and the hazardous part. Failure to do so may prevent the machinery from stopping before a person reaches the hazardous part of the machinery, and result in serious injury.

Note: The response time of a machine is the time period from when the machine receives a stop signal to when the machine's hazardous part stops. Measure the response time on the actual system. Also, periodically check that the response time of the machine has not changed.

How to calculate the safety distance specified by International Standard ISO 13855 (European Standard EN ISO 13855) (Reference)

Detection Zone Orthogonal to Direction of Approach

 $S = K \times T + C \dots Formula (1)$

- S: Safety distance
- · K: Approach speed to the detection zone
- T: Total response time of the machine and F3SJ
- C: Additional distance calculated by the detection capability of the F3SJ

<System with a detection capability of 40 mm max.>
Use K = 2,000 mm/s and $C = 8 \times (d - 14 \text{ mm})$ in equation (1) for the calculation

S = 2,000 mm/s x (Tm + Ts) + 8 x (d - 14 mm)

- S = Safety distance (mm)
- Tm = Machine's response time (s)
- Ts = Response time of the F3SJ from ON to OFF (s)
- d = Size of F3SJ's detection capability (mm)

[Calculation example]

When Tm = 0.05 s, Ts = 0.01 s, and d = 14 mm:

S = 2,000 mm/s x (0.05 s + 0.01 s) + 8 x (14 mm - 14 mm)

= 120 mm . . . Formula (2)

If the result is less than 100 mm, use S = 100 mm.

If the result exceeds 500 mm, use the following formula where K = 1.600 mm/s.

 $S = 1,600 \text{ mm/s } x \text{ (Tm + Ts)} + 8 x \text{ (d - 14 mm)} \dots \text{ Formula (3)}$

If the result of this Formula (3) is less than 500 mm,

S = 500 mm

<System with a detection capability larger than 40 mm> Use K = 1,600 mm/s and C = 8 x (d - 850 mm) in equation (1) for the calculation.

 $S = 1,600 \text{ mm/s x (Tm + Ts) + } 850 \text{ x (d - } 14 \text{ mm)} \dots \text{Formula (4)}$

- S = Safety distance (mm)
- Tm = Machine's response time (s)
- Ts = Response time of the F3SJ from ON to OFF (s)

[Calculation example]

When Tm = 0.05 s, Ts = 0.01 s:


S = 1,600 mm/s x (0.05 s + 0.01 s) + 850 mm

= 946 mm

F3SJ-E/F3SJ-B/F3SJ-A

Possible Circumventing by Reaching Over the Detection Zone

If access to the hazardous zone by reaching over the detection zone of vertically mounted F3SJ cannot be excluded, the height and the safety distance, S, of the F3SJ shall be determined. S shall be determined by comparison of the calculated values in *Detection Zone Orthogonal to Direction of Approach*. The greater value resulting from this comparison shall be applied.



 $S=(K \times T) + Cro \dots Formula (5)$

- · S: Safety distance
- · K: Approach speed to the detection zone
- T: Total response time of the machine and F3SJ
- Cro: Approach distance based on the distance which personnel
 can move towards the hazardous zone of a machine by reaching
 over the detection zone. The distance is determined in the table
 below based on the height of the hazardous zone, a, and the
 height of the upper edge of the detection zone, b.

Note: Lower edge of the detection zone above 300 mm in relation to the reference plane does not offer sufficient protection against crawling below.

First, use K = 2,000 mm/s in formula (5) for the calculation. If the result of this calculation is less than 100 mm, use S = 100 mm. If the result exceeds 500 mm, use K = 1,600 mm/s to recalculate it. If the result of the recalculation is less than 500 mm, use S = 500 mm

Height of	Height of upper edge of detection zone, b											
hazardous	900	1000	1100	1200	1300	1400	1600	1800	2000	2200	2400	2600
zone, a		Additional distance to hazardous zone, Cro						1				
2600	0	0	0	0	0	0	0	0	0	0	0	0
2500	400	400	350	300	300	300	300	300	250	150	100	0
2400	550	550	550	500	450	450	400	400	300	250	100	0
2200	800	750	750	700	650	650	600	550	400	250	0	0
2000	950	950	850	850	800	750	700	550	400	0	0	0
1800	1100	1100	950	950	850	800	750	550	0	0	0	0
1600	1150	1150	1100	1000	900	850	750	450	0	0	0	0
1400	1200	1200	1100	1000	900	850	650	0	0	0	0	0
1200	1200	1200	1100	1000	850	800	0	0	0	0	0	0
1000	1200	1150	1050	950	750	700	0	0	0	0	0	0
800	1150	1050	950	800	500	450	0	0	0	0	0	0
600	1050	950	750	550	0	0	0	0	0	0	0	0
400	900	700	0	0	0	0	0	0	0	0	0	0
200	600	0	0	0	0	0	0	0	0	0	0	0
0	0	0	0	0	0	0	0	0	0	0	0	0

Note: 1. Upper edge of the detection zone below 900 mm is not included since they do not offer sufficient protection against circumventing or stepping over.

2. When determining the values of this table, it shall not be interpolated. If the known values a, b or Cro are between two values of this table, the greater safety distance shall be used.

[Calculation example]

- T: Tm + Ts (s)
- Tm: Machine's response time (s)
- Ts: Response time of the F3SJ from ON to OFF (s)
- a: Height of machine hazardous zone (mm)
- b: Height of upper edge of detection zone (mm)

When Tm = 0.05 s, Ts = 0.01 s, a = 1,400 mm, b = 1,500 m: From the table above, Cro = 850 mm. Since b is between 1,400 mm and 1,600 mm, b = 1,400 mm which has the greater Cro value, shall be used

 $S = 2,000 \text{ mm/s} \times (0.05 \text{ s} + 0.01 \text{ s}) + 850 \text{ mm}$

= 970 mm

Since 970 mm is greater than 500 mm, use K = 1,600 mm/s and recalculate it

 $S = 1,600 \text{ m/s} \times (0.05 \text{ s} + 0.01 \text{ s}) + 850 \text{ mm}$

= 946 mm

Compare S = 946 mm with the calculation in Detection Zone Orthogonal to Direction of Approach, and choose the larger value as the safety distance.

For the system with a detection capability of 40 mm max., the safety distance S is 946 mm since this is larger than S = 120 mm calculated in the calculation example of Detection Zone Orthogonal to Direction of Approach.

For the system with a detection capability larger than 40 mm, the safety distance S is 946 mm since this is the same value as S = 946 mm calculated in the calculation example of Detection Zone Orthogonal to Direction of Approach.

Detection Zone Parallel to Direction of Approach


Use K = 1,600 mm/s and C = (1200 - 0.4 x H) in formula (1) for calculation. Note that C must not be less than 850 mm.

S = 1,600 mm/s x (Tm + Ts) + 1200 - 0.4 x H

- S = Safety distance (mm)
- Tm = Machine's response time (s)
- Ts = Response time of F3SJ from ON to OFF (s)
- H = Installation height (mm)

Note that H must satisfy:

 $1000 \ge H \ge 15 (d - 50 \text{ mm}) \ge 0 \text{ mm}$



Also, you must include a hazardous condition under which a person may go through under a detection zone if H exceeds 300 mm (200 mm for other purpose than industrial use) into risk assessment.

[Calculation example]


When Tm = 0.05 s, Ts = 0.01 s, and d = 14 mm: S = 1,600 mm/s x (0.05 s + 0.01 s) + 1200 - 0.4 x 500 mm

= 1096 mm

When a warning zone is configured as in the figure, you must calculate L, a distance from an end of casing to a detection zone, using a formula below:

L = (Total number of F3SJ beams - number of warning zone beams

- 1) x P + 10
- P: Beam Gap (mm)
- F3SJ-A P14/N14 . . . 9 mm
- F3SJ-A DD P20/N20 . . . 15 mm
- F3SJ-A DDDDP25/N25 . . . 20 mm
- F3SJ-A DDDDP55/N55 . . . 50 mm



Distance L from casing end to detection zone

Refer to the F3SJ User's Manual for details. For manual number, check the "*Related Manuals*" at the end of the catalog.

How to calculate the safety distance specified by American standard ANSI B11.19 (Ref.)

If a person approaches the detection zone of the F3SJ orthogonally, calculate the safety distance as shown below. S = K x (Ts + Tc + Tr + Tbm) + Dpf

- · S: Safety distance
- K: Approach speed to the detection zone (the value recommended by OSHA standard is 1,600 mm/s)

Approach speed K is not specified in the ANSI B.11.19 standard. To determine the value of K to apply, consider all factors, including the operator's physical ability.

- Ts = Machine's stop time (s)
- Ts = Response time of the F3SJ from ON to OFF (s)
- Tc = Machine control circuit's maximum response time required to activate its brake (s)
- Tbm = Additional time (s)

If a machine has a brake monitor, "Tbm = Brake monitor setting time - (Ts + Tc)". If it has no brake monitor, we recommend using 20% or more of (Ts + Tc) as additional time.

• Dpf = Additional distance

According to ANSI's formula, Dpf is calculated as shown below: $Dpf = 3.4 \times (d - 7.0)$: Where d is the detection capability of the F3SJ (unit: mm)

[Calculation example]

When K = 1,600 mm/s, Ts + Tc = 0.06 s, brake monitor setting time = 0.1 s, Tr = 0.01 s, and d = 14 mm:

Tbm = 0.1 - 0.06 = 0.04 s

 $Dpf = 3.4 \times (14 - 7.0) = 23.8 \text{ mm}$


 $S = 1,600 \text{ mm/s} \times (0.06 \text{ s} + 0.01 \text{ s} + 0.04 \text{ s}) + 23.8 \text{ mm} = 199.8 \text{ mm}$


Distance from Reflective Surface F3SJ-E F3SJ-B F3SJ-A

⚠ WARNING

Install the sensor system so that it is not affected by reflection from a reflective surface. Failure to do so may hinder detection, resulting in serious injury.

Install the sensor system at distance D or further from highly reflective surfaces such as metallic walls, floors, ceilings, or workpieces, as shown below.





Distance between emitter and receiver (operating range L)	Allowable installation distance D		
For 0.2 to 3 m	0.13 m		
For 3 m or more	L/2 x tan5° = L x 0.044 (m)		

Mutual Interference Prevention F3SJ-B F3SJ-A

⚠ WARNING


Do not use the sensor system with mirrors in a regressive reflective configuration. Doing so may hinder detection. It is possible to use mirrors to "bend" the detection zone to a 90-degree angle.

When using more than 1 set of F3SJ, install them so that mutual interference does not occur, such as by configuring series connections or using physical barriers between adjacent sets.

Mutual interference from other F3SJ is prevented in up to 3 sets without series connection.

For series connection F3SJ-B F3SJ-A

Series connection can prevent mutual interference when multiple sensors are used. Up to 3 sets with 192 beam for F3SJ-B series, or up to 4 sets with 400 beams for F3SJ-A series can be series-connected. Emission of series-connected F3SJ is time-divided, ensuring safety without occurring mutual interference.




No series connections F3SJ-B F3SJ-A


Mutual interference is prevented in up to three sets, using interference light detection and cycle shift algorithm.

If 4 or more sets of F3SJs are installed and are not connected to each other, arrange them so that mutual interference does not occur. If two sets are installed near each other, reflection from the surface of the F3SJ may cause mutual interference. When mutual interference occurs, the safety outputs are turned OFF momentarily or the F3SJ enters lockout state. Combining countermeasures 1 to 3 shown below is effective.


1. Install a physical barrier



2. Alternate the direction of emission (alternation)




Keep sufficient distance between the F3SJs so that mutual interference does not occur



Distance between emitter and receiver (operating range L)	Allowable installation distance D		
For 0.2 to 3 m	0.26 m		
For 3 m or more	L x tan5° = L x 0.088 (m)		


Installation shown below may cause mutual interference. When mutual interference occurs, the safety outputs are turned OFF momentarily or the F3SJ enters lockout state.






F3SJ-A

If two sets are installed near each other, reflection from the surface of the F3SJ may cause mutual interference. Use of F3SJ-A can improve the condition by shortening operating range with the setting tool.





F3SJ-E/F3SJ-B/F3SJ-A

Related Manuals

Man. No.	Model	Manual name
SCHG-718	F3SJ-A□□□□□□□	F3SJ-A□□□□P□□ (Ver.2) Safety Light Curtain User's Manual
SCHG-720	F3SJ-A□□□□P□□-TS	F3SJ-A□□□□P□□-TS Safety Light Curtain User's Manual
SCHG-722	F3SJ-A□□□□P□□-01TS	F3SJ-A□□□□P□□-01TS Safety Light Curtain User's Manual
SCHG-719	F3SJ-A□□□□□□□	F3SJ-A□□□□N□□(Ver.2) Safety Light Curtain User's Manual
SCHG-726	F3SJ-A□□□□N□□-01T	F3SJ-A□□□□N□□-01T(Ver.2) Safety Light Curtain User's Manual
SCHG-716	F3SJ-AM□P□□□	F3SJ-AM□P□□□(Ver.2) Multi-beam Safety Sensor User's Manual
SCHG-734	F3SJ-B□□□□P25-01TS	F3SJ-B□□□□P25-01TS Safety Light Curtain User's Manual
SCHG-733	F3SJ-E□□□□N25/B□□□□N25	F3SJ-E□□□□N25/B□□□□N25 Safety Light Curtain User's Manual
SCHG-732	F3SJ-E□□□□P25/B□□□□P25	F3SJ-E□□□□□P25/B□□□□P25 Safety Light Curtain User's Manual
SCHG-712	F39-MC21	F39-MC21 F39-MC21 Setting Console Instruction Sheet
SCHG-736	F3SJ-B□□□□P25-02TS	F3SJ-B□□□□P25-02TS Safety Light Curtain User's Manual

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact: www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-2711

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222 Fax: (86) 21-5037-2200

Authorized Distributor:

©OMRON Corporation 2005-2023 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_27_9

Cat. No. F074-E1-15 0123 (0505)