


A compact smart camera that simplifies inspections



Simplify multiple-device inspection systems by using a single camera

Traditional image inspections require one or more dedicated cameras to be paired with a code reader. Omron's F430-F Series Smart Camera bundles all this functionality into a single device, dramatically simplifying application design. The single-camera solution also reduces the initial investment, cuts down on wiring work and keeps maintenance costs to a minimum.

Inspections | 01


Multiple cameras in one to enhance precision

Inspections | 02

A single camera performing powerful inspection tasks and code reading


Inspections | 03

A single camera designed for long operational lifetime



Inspections | 01

Multiple cameras in one to enhance precision



Mechanical design is required for multiple cameras. Positioning of the mechanism and fine-tuning of software are time consuming.

Only a single camera is required, simplifying design and fine-tuning.

When using low-resolution cameras, multiple cameras are needed to divide a view in several sections and achieve the resolution required for inspections. The 5-megapixel color camera of the F430-F Series delivers high-resolution imaging of multiple points with a single device.

Inspection scope examples

0.3 Megapixel color camera: 1 PCB




5 Megapixel color camera: 8 PCBs




Positioning of a single camera only

A single camera can capture a wide view, eliminating the need to combine multiple cameras that require time-consuming positioning design and fine-tuning.



Presence, color and shape detection and reading at the same time


The F430-F Series can simultaneously perform detection tasks (presence, color, and shape) and code reading within the field of view. You can easily increase inspection points for quality enhancement.



Inspections | 02

A single camera performing powerful inspection tasks and code reading

FROM



Installation space and communication design are required for both the sensor and code reader.

TO



Installation space and communication design are required for a single smart camera only.

To perform a simple inspection task - such as presence/absence detection, color detection, etc. - along with a code or character reading, a highly-functional sensor or a sensor combined with a code reader for each purpose would be required. The F430-F Series successfully performs both functions, simplifying inspection tasks overall.

Code reading




Cap presence/absence inspection

Cap present **OK** Cap absent **NG**



Wiring and installation space reduced by half

A single camera with smart camera and code reader functionalities halves the number of cables to the host device and the installation space.



Text and verification result output


The F430-F Series can output character strings and code quality verification results, which is difficult with standard smart cameras. The output information can be used for traceability.

Example of output data


1. Result of inspection: OK/NG
2. Result of code reading: Character string
3. Result of verification: Quality grade of code

The long-life autofocus lens provides long operational lifetime without the need for replacement

How long until the camera is replaced due to failure caused by focus changes?




The F430-F Series with a long-life liquid lens provides unlimited autofocus, easily focusing on different items just by switching the focus. The liquid lens greatly reduces the replacement frequency that is once every several months to several years with the mechanical autofocus lens.




Difference between mechanical autofocus and liquid lens autofocus

Mechanical autofocus uses a small motor as a major component. Metal fatigue and wear shorten the life of the camera, which requires replacement every year. The liquid autofocus lens can flexibly change its focal length without mechanical wear by applying voltage to change the internal oil and water shape.

Mechanical autofocus



Autofocus with liquid lens



* Calculated using Omron's condition below.

Limit of standard mechanical autofocus : 50,000 operations

Usage condition: Focus is changed 200 times a day for 20 days a month. 200 operations x 20 days x 12 months = 48,000 operations » approximately 1 year.


Tools

12 tools are provided.

The provided tools vary depending on the model. Refer to the datasheet for details.




Count



Counts objects detected within the inspection area.
(Method: Select from Blob Count and Shape Count)




Measure



Measures width or height between two edges.
(Method: Select from Width Measure, Height Measure, Circle Measure, Point to Point Measure, Point to Line Measure, and Angle Measure)



Presence/Absence



Inspects the presence of objects.
(Method: Select from Count Gray Pixels and Count Edge Pixels)



Color (5 Mpix camera)



Judges whether the color matches the registered one.
The degree of match can be adjusted in percent. Speed can be increased by setting the precision parameter.



Decode



Reads a bar code or 2D code. The Match String function allows this smart camera to perform verification that is usually done by a PC or PLC.




Symbol Quality Verification

Parameter Grades:			Calibration Data:	
	Grade	Score	Units	
Symbol Contrast	A	100	%	State: Not Calibrated
Modulation	A			Target Symbol 1 Width: 0.24
Reflectance Margin	A			Target Symbol 2 Width: 0.48
Fixed Pattern Dmg	A			Maximum Exposure: 32000
Axial NonUniformity	A	0	%	Target Rmin: 4
Grid NonUniformity	A	8	%	Target Rmax: 82
Unused Err Correction	A	100	%	

Enables simple print quality verification of codes to application standards such as ISO 15415, AIM DPM/ISO 29158, and ISO 15416. Also automatically generates reports.
Note: QR codes cannot be verified. The Calibration Card is required.



OCR



Just draw a square around characters to read them using its built-in dictionary. Reads capital alphabets, numbers, and multi-row text and compares them with the character string received from the host device.



Locate



Outputs the position and angle of the registered image. The inspection area of this tool can automatically be used for the processing following this tool.




Match Strings Tool



Compares a human-readable character string read by OCR with data contained in the code read by CR, which is mostly done by a PC or PLC.



OCV




Detects defects from measured character strings using the registered reference character string. Automatically focuses on a target character string even if its position differs.

* Up to ±15°




String Format



Outputs extracted character strings and combined two character strings, which is usually done by a PC or PLC.



Logic Tool




Performs logical operation and compares sizes of tool results. Logical operation of "status" of each tool can be used to create individual judgment conditions instead of the overall condition.

Simple setup on a single screen AutoVISION Software


3-step easy setting

Follow the guide on the screen to start inspection in three steps: Image, Edit, and Run.




STEP 1. Image One click to optimize image

Place an object within a focal length and press the Autofocus button to optimize the focus and brightness of the inspection image.



STEP 2. Edit Just select tools and specify inspection areas

Setup can be done by simply selecting tools and specifying the inspection areas. You can check the test measurement results on this screen and adjust the inspection range and the threshold by viewing the screen.



STEP 2. Edit Allocate outputs

Select values and memory areas for each tool to allocate outputs, reducing PLC connection design time. In addition to OK/NG results, measured values, code reading results, and OCR results can be output, which is useful for data collection.

Example: Output of OCR results

Data that can be output is displayed as selections. Example: OCR

The screenshot shows the 'Inspection Outputs' configuration window. It lists several tools: 'Camera' (752 x 480 Pixels, 8 bit Grayscale), 'Decode' (123456), 'PresenceAbsence' (Pixel Count = 4179), and 'OCR' (123456). Each tool has a green checkmark and a 'GO' button. Below the tool list is an 'Output String' configuration window with a dropdown menu set to 'string' and four output string slots (string1 to string4), each with a 'GO' button. Blue arrows point from the OCR tool's 'GO' button to the 'Output String' window, and from the 'Output String' window to the labels 'Judgment result', 'Output character string', 'Number of detected characters', and 'Memory to allocate'.

STEP 3. Run One click to start inspection

Just press the Run button to start the inspection. Inspection results are displayed on the screen in real time.

Utilization

Free software and materials available to support your learning

AutoVISION software is available for free. Visit your local omron website or ask to your omron representatives.

The quick start guide and sample image/job data attached with the software will help you use the software. The software includes the help file, allowing you to refer to help without connecting to a network.

Examples of materials and data to support your learning

Quick start guide



A quick guide showing how to start inspection is attached.

Help file



The help file can be easily opened from the help menu in AutoVISION. Offline help can be used without connecting to a network.

Sample image/job data



It contains sample images and job data that will be helpful for learning how to operate.

Easy-to-see display of inspection status

WebMonitor Software

Improve usability with large display

Your tablet or PC with a web browser can be used as the display, providing much better visibility than small displays of standard smart cameras. Choose a device size to suit the installation environment and inspection images. Refer to the datasheet for browser requirements.

Standard smart cameras


The small dedicated display provides limited visibility.



Up to 6 inches

F430-F Series

A large, high-resolution display can be used.



Selectable size

Customizable user interface to maximize usability of large screens

The WebMonitor software facilitates customization of the user interface. Simply select from various pre-installed widgets and place the widget. No programming is required.

Example of widget layout

Inspection Counters
Shows measurement, pass, and fail counts.

Read Value
Shows a parameter and the measured value.

Write Value
Allows you to modify a parameter.

Image Filmstrip
Shows a history of measurement images. Pass or fail inspection images can be displayed.




Chart
Shows a chart of measured values.


Log of Values
Shows measured values as a historical list.

Device Control
Allows you to start and stop measurements, and to change and save job data.

Note: The ability to display 100% of inspection images depends on the number of inspection tasks, line speed, and the number of connected cameras.


Example: Displaying decoded code

STEP 1 Link a parameter




Assign the position and angle data of the Locate tool to memory in the AutoVISION software.

STEP 2 Place a widget



Place a widget in the WebMonitor.

STEP 3 Select the parameter



Select the parameter to display in the WebMonitor.

Decoded Text
3930034


The selected parameter is displayed.

Reduce equipment costs by integrating monitoring of multiple cameras

Inspection status of multiple cameras can be monitored using a single device. Unlike standard smart cameras which require a display for each camera, the F430-F Series requires only one display for all cameras, reducing not only initial and installation costs but also time to view each display.


Standard smart cameras

One display per camera



F430-F Series

One display for all cameras




Note: The maximum number of cameras that can be simultaneously monitored on the WebMonitor varies depending on the inspection cycle time and system environment.

Web browser interface for easy integration of monitoring

The WebMonitor software pre-installed in the smart camera allows you to view inspection status simply by connecting your tablet or PC that has a web browser. When multiple smart cameras are monitored, the smart camera to display can be easily changed by entering its IP address in your web browser.

Configuration example




Attachments to capture clear images


Eliminate uneven lighting and halation

Polarizer and Diffuser


Attaching a polarizer or diffuser reduces halation and reflection without the need to install the camera at an angle.



Polarizer



Diffuser



Protect against laser radiation

YAG Filter

When the smart camera is installed near YAG laser equipment (e.g., laser marker, laser engraver, and laser cutter), the YAG filter is used to protect image elements against laser light.



Protect against static

ESD Safe Window*

To prevent line or object problems caused by electrostatic discharge (ESD) of the smart camera, the ESD safe window is used.




* This model is coming soon.

Install in a confined space

Right Angle Mirror

The right angle mirror is used to install the smart camera in a space where the camera cannot face the object.



Right Angle Connector

This connector can be used when there is no wiring space behind the smart camera.




(Right angle down (photo above) and right angle up connectors are available.)

Use under insufficient light

Ring Light Model

This model can provide reliable inspection even under insufficient light conditions and maintain the shutter speed to focus on high-speed lines, which both are difficult with a standard light.



The ring light model is available with F430 1.2 Mpix Cameras.

Enhance contrast

Color Filters

The color filter is used with a monochrome camera with white light when you want to emphasize the area where the intensity of the red or blue component is high.




Inspection area

With Red Filter

With Blue Filter

Additional Lighting Options

This option is used with a monochrome camera when you want to emphasize a specific color component or infrared ink. White, red, blue, and IR LEDs are available.



Color Camera White LEDs

Mono Camera Red LEDs


Mono Camera Blue LEDs

Mono Camera IR LEDs


Applications

Automotive industry



Incorrect gear inspection



Orientation inspection of attached rubber





Reading lot numbers and codes on automotive body parts





Digital industry



Presence inspection and code reading of electronic components



Presence inspection of PCB mounted components




Identification of electronic components




Food, beverage, and pharmaceutical industry


Label presence inspection



Inspection for absence of medicines in blister packs



Capping and label presence inspection of beverage bottles





Logistics industry



Label orientation inspection, and code and expiration date inspection



Product quantity inspection



Code print quality verification of packing boxes



- Intel and Intel Core are trademarks of Intel Corporation in the U.S. and/or other countries.
- Windows is a registered trademark of Microsoft Corporation in the USA and other countries.
- Firefox is a trademark of the Mozilla Foundation in the US and other countries.
- iPhone, iPad and Safari are trademarks of Apple Inc., registered in the U.S. and other countries and regions.
- Google Chrome, Android™, Google Play, and the Google Play logo are trademarks of Google LLC.
- Microsoft product screen shot(s) used with permission from Microsoft Corporation.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp
The Netherlands
Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200
Hoffman Estates, IL 60169 U.S.A.
Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

438B Alexandra Road, #08-01/02 Alexandra
Technopark, Singapore 119968
Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

Authorized Distributor:

©OMRON Corporation 2020-2026 All Rights Reserved.
In the interest of product improvement,
specifications are subject to change without notice.

CSM_4_1

Cat. No. Q272-E1-05 0326 (1219)