# OMRON

# Slim I/O Relay/Slim I/O Solid State Relay

# Slim I/O relay realizes space saving thanks to high-density mounting and ultra-slim body

- 60% space saving from G2R series with 6.2 mm width.
- 60%\* reduction in wiring time and user-friendly with a low insertion force thanks to Push-In Plus Technology.
- Larger hole and angled structure contribute to efficient wiring and standardization of wires up to AWG14, 2.5 mm<sup>2</sup>.
- Easy maintenance with improved LED visibility and color stopper voltage line identification.
- Low cutting force of short bars contribute to reducing health issues such as Tenosynovitis.

\* According to OMRON actual measurement data for both push-in plus terminal blocks and screw terminal blocks.

# Slim I/O Relay Types

G2RV-ST series mounted relay: electromagnetic relay...... from page 2 G3RV-ST series mounted relay: solid state relay...... from page 12

# Common matter

Common precautions	from page 22 .
Common accessories (order separately)	from page 29

# Common features of G2RV-ST/G3RV-ST

#### Wiring standardization is also

supported by 2.5 mm<sup>2</sup> compatibility DC common wiring also provides support for 2.5 mm<sup>2</sup> dia./AWG14 (2.0 mm<sup>2</sup>) needs

# Wiring work efficiency improvement

Easy to see and easy insertion thanks to large-diameter wiring holes and tilted structure.



# Work judgment support is provided through mounting feeling enhancement.

Work efficiency is enhanced by DIN rail sliding performance and short bar improvements.




DIN rail tolerance is also supported through elasticity.



Insertion feeling to let you know when mounting is complete.

#### Easy and safe

Short bar cutting force has been decreased to reduce the burden during assembly. Electrification of the short bar fracture plane is prevented by an isolation plate.



Note. Cutting force of 25 kg, so easily cut by needle-nose pliers

# Maintainability is enhanced by color stoppers



website

Both easy replacement and detachment prevention of relays are achieved by locking and unlocking of stopper.

Designed so that wires are hard come out even if release levers are touched unintentionally.

For the recent information on models that have been

certified for safety standards, refer to your OMRON

Refer to Safety Precautions on page 22.



Coil voltage line identification Red: AC Blue: DC White: Multi (e.g. 24 VAC/VDC)

#### Visibility is enhanced by release lever LED



Visibility from the front is improved by a structure where the actual release lever lights and by expanding the light emission area.

Note. The third relay from the right is equipped with a label.

G2RV-S1

# OMRON

# Slim I/O Relay V-ST

# Slim I/O relay realizes space saving thanks to high-density mounting and ultra-slim body

- 60% space saving from G2R series with 6.2 mm width technology.
- 60%\*1 reduction in wiring time and user-friendly with a low insertion force thanks to Push-In Plus Technology.
- Max. 6 A realized even with close-contact mounting.
- Au-plated contacts suitable for micro loads with a failure rate P value<sup>\*2</sup> of 1 mA at 100 mVDC.
- A transparent case that allows for easy on-site visual checks of contact state abnormalities.
- Easy relay replacement with a terminal structure that does not bend easily.
- Operation check using a test switch reduces inspection time.
- A coil surge absorption circuit equipped as standard.
- \*1. According to OMRON actual measurement data for both push-in plus terminal blocks and screw terminal blocks. \*2. Reference value



For the recent information on models that have been certified for safety standards, refer to your OMRON website.

Refer to Safety Precautions on page 22.


# **Features**

Operation

verification which is linked to the contact

#### **Common Precautions** Standard model/Micro load Terminal x 5 Push-in Screw Operation display LED (Socket section) Release lever Mechanical indicator

#### With latching lever (Test switch)





Confirmation, reducing the inspection effort


#### **Push-In Plus technology**



Terminal (insertion) hole Release hole

Short bar insertion holes

Common Accessories



Release lever Relay easily fixed/removed

Transparent case Relay contact Easy confirmation of the situation



**Plug-in terminal** Peace of mind as the terminal does not bend when replacing

G3RV-S

G2RV-S

2

OMRON

# **Model Number Structure**

#### **Model Number Legend**

G2RV	-ST		-	•		
(1)	(2)	(3)	(4)	(5)	(6)	

(1) Basic model name

G2RV: Slim I/O Relay

(2) Sub type

ST: Slim relay + integrated low profile socket

(3) Terminal (wire connection) 50: Push-In Plus Terminal 70: Screw terminal

(4) Latching lever (test switch)0: Without latching lever1: With latching lever

(5) Contact structure Blank: Standard AP: Microloads

(6) Rated input voltage 12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC

# **Ordering Information**

Terminal (Wire connection)	Classification	Latching lever (Test switch)	Rated input	t voltage (V)	Model
			DC	12	G2RV-ST500 12 VDC
			DC	24	G2RV-ST500 24 VDC
			AC/DC	24	G2RV-ST500 24 VAC/VDC
		No	AC/DC	48	G2RV-ST500 48 VAC/VDC
	Standard	NO		100	G2RV-ST500 100 VAC
	Stanuaru		AC	110	G2RV-ST500 110 VAC
			AC	200	G2RV-ST500 200 VAC
				230	G2RV-ST500 230 VAC
Push-In Plus Terminal		Yes	DC	24	G2RV-ST501 24 VDC
Push-in Plus Terminal		res	AC/DC	24	G2RV-ST501 24 VAC/VDC
			50	12	G2RV-ST500-AP 12 VDC
			DC	24	G2RV-ST500-AP 24 VDC
			40/00	24	G2RV-ST500-AP 24 VAC/VDC
	NA:	No	AC/DC	48	G2RV-ST500-AP 48 VAC/VDC
	Microloads			100	G2RV-ST500-AP 100 VAC
				110	G2RV-ST500-AP 110 VAC
			AC	200	G2RV-ST500-AP 200 VAC
				230	G2RV-ST500-AP 230 VAC
			50	12	G2RV-ST700 12 VDC
			DC	24	G2RV-ST700 24 VDC
			A.C./D.C	24	G2RV-ST700 24 VAC/VDC
			AC/DC	48	G2RV-ST700 48 VAC/VDC
		No		100	G2RV-ST700 100 VAC
	Standard			110	G2RV-ST700 110 VAC
			AC	200	G2RV-ST700 200 VAC
				230	G2RV-ST700 230 VAC
		X	DC	24	G2RV-ST701 24 VDC
Screw terminal		Yes	AC/DC	24	G2RV-ST701 24 VAC/VDC
			<b>D</b> 0	12	G2RV-ST700-AP 12 VDC
			DC	24	G2RV-ST700-AP 24 VDC
			10/20	24	G2RV-ST700-AP 24 VAC/VDC
			AC/DC	48	G2RV-ST700-AP 48 VAC/VDC
	Microloads	No		100	G2RV-ST700-AP 100 VAC
				110	G2RV-ST700-AP 110 VAC
			AC	200	G2RV-ST700-AP 200 VAC
				230	G2RV-ST700-AP 230 VAC

Note: Sockets are not sold individually.

# **G2RV-ST**

#### **Relay for Maintenance**

#### **Model Number Legend**

G2RV-1 - S □ - □ - G (1) (2)(3) (4) (5) (6)

(1) No. of poles 1: 1 pole

(2) Terminal S: plug-in

(3) Latching lever (Test switch) Blank: Without latching lever I: With latching lever

#### List of Models

(4) Contact material Blank: Ag alloy AP: Ag alloy + Au plating

(5) Types of relay for exchange G: G2RV-ST series equipped Relay

(6) Rated coil voltage Number: 11, 21, 48 VDC



#### G2RV-1-S(-AP)-G





Туре	Latching Lever (Test switch)	Rated coil voltage (V)		Model	Applicable model	
			11	G2RV-1-S-G DC11	G2RV-ST700/500 12 VDC	
		21	G2RV-1-S-G DC21	G2RV-ST700/500 24 VDC		
			21	G2RV-1-3-G DC21	G2RV-ST700/500 24 VAC/VDC	
	No	DC			G2RV-ST700/500 48 VAC/VDC	
Standard	INO	DC			G2RV-ST700/500 100 VAC	
Standard			48	G2RV-1-S-G DC48	G2RV-ST700/500 110 VAC	
					G2RV-ST700/500 200 VAC	
					G2RV-ST700/500 230 VAC	
	Yes		21	G2RV-1-SI-G DC21	G2RV-ST701/501 24 VDC	
	res	DC	21	G2RV-1-31-G DC21	G2RV-ST701/501 24 VAC/VDC	
			11	G2RV-1-S-AP-G DC11	G2RV-ST700/500-AP 12 VDC	
			21		G2RV-ST700/500-AP 24 VDC	
			21	G2RV-1-S-AP-G DC21	G2RV-ST700/500-AP 24 VAC/VDC	
Mierolood	No				G2RV-ST700/500-AP 48 VAC/VDC	
IVIICIOIOAU	Microload No	DC			G2RV-ST700/500-AP 100 VAC	
			48	G2RV-1-S-AP-G DC48	G2RV-ST700/500-AP 110 VAC	
					G2RV-ST700/500-AP 200 VAC	
					G2RV-ST700/500-AP 230 VAC	

Note: Voltage is reduced within the socket for the slim I/O relay, so the rated input voltage and rated coil voltage of replacement relays are different.

#### Accessories (order separately)

Refer to page 29 for G2RV-ST/G3RV-ST Common Accessories.

**Common Precautions** 

G3RV-ST

# G2RV-ST

# **Specifications**

# Ratings

#### Coil ratings

Rated input	Rated current		Must operate voltage	Must release voltage	Power consumption		Maximum allowable voltage	
voltage	A	C	DC	Percentage of t	he rated voltage	AC (VA)	DC (mW)	Percentage of the
	50 Hz	60 Hz		r ercentage of t	Percentage of the rated voltage		50 (IIIV)	rated voltage
12 VDC	-	-	27.9 mA			-	Approx. 300 mW	
24 VDC	-	-	13.5 mA			-	Approx. 300 mW	
24 VAC/VDC	13.7 mA	14.9 mA	12.6 mA			Approx. 0.4 VA	Approx. 300 mW	
48 VAC/VDC	5.9 mA	6.4 mA	5.4 mA		10% min.	Approx. 0.3 VA	Approx. 250 mW	110%
100 VAC	6.8 mA	7.1 mA	-	- 00 % IIIdX.	1070 11111.	Approx. 0.7 VA	-	11070
110 VAC	6.1 mA	6.4 mA	-			Approx. 0.7 VA	-	
200 VAC	6.1 mA	7.3 mA	-			Approx. 1.5 VA	-	
230 VAC	6.8 mA	8.2 mA	-			Approx. 1.9 VA	-	

Note: The operating characteristics are measured at ambient temperature of 23°C.

The rated current tolerances are as follows. AC rating: +15%/-20%, DC rating: ±10%

\* Operating voltage will be, for mounting in the upside down direction, 85% max.

(Upside down: Direction in which the mechanical indicator faces down)

#### **Contact ratings**

Item	Standard (G2F	RV-ST700, 500, 701, 501)	For microloads (G2RV-ST700-AP, 500-AP) *2		
Contact configuration	SPDT				
Load	Resistive load (coso=1)	Inductive load (cosφ=0.4, L/R=7ms)	Resistive load (cos∳=1)		
Rated load	6 A at 250 VAC 6 A at 30 VDC	2.5 A at 250 VAC 2 A at 30 VDC	50 mA at 30 VAC 50 mA at 36 VDC		
Rated carry current *3	6 A		50 mA		
Maximum switching voltage	440 VAC, 125 VDC		30 VAC, 36 VDC		
Maximum switching current	6 A		50 mA		
Maximum switching power	1,500 VA 180 W	500 VA 60 W	-		
Failure rate P value (reference value) *1	10 mA at 5 VDC		1 mA at 100 mVDC		

**\*1.** P level: λ<sub>60</sub>=0.1×10<sup>-6</sup>/times

This value is the value in switching frequency 120 operations/min.

\*2. If the Au plating layer is destroyed, the number will be the same as the standard type.

**\*3.** Please energize under 32A total when use short bar connection.

# Characteristics

G	Item		Standard (G2RV-ST700, 500, 701, 501)	For microloads (G2RV-ST700-AP, 500-AP)		
32RV-	Contact resistance *		100 m Ω max.			
U	Polosso timo *		20 ms max.			
- - - -			AC, AC/DC: 40 ms max. DC: 20 ms max.			
-	Maximum operating fre	equency	Mechanical: 18,000 operations/h Electrical: 1,800 operations/h (rated load)			
	Insulation resistance		1,000 MΩ min. (at 500 VDC)			
	Dielectric strength		Between coil and contacts: 4,000VAC 50/60 Hz Contact between the same polarity: 1,000 VAC			
	Vibration resistance			Destruction: 10 to 55 to 10 Hz, single amplitude 0.50 mm (double amplitude 1.0 mm) Malfunction: 10 to 55 to 10 Hz, single amplitude 0.50 mm (double amplitude 1.0 mm)		
	Shock resistance		Destruction: 1,000 m/s <sup>2</sup> Malfunction: Energized 200m/s <sup>2</sup> , Non-energized 100m/s <sup>2</sup>			
		Mechanical	5,000,000 operations min.			
۔ د	Endurance *	Electrical	NO contact: 70,000 operations min. NC contact: 50,000 operations min.	5,000,000 operations min.		
C3BV-	Ambient operating tem	perature	Operating: -40 to +55°C (with no icing or condensation)			
	Ambient operating hun	nidity	Operating: 5 to 85% RH			
	Weight		Approx. 30 g			
ΉI	Type of interruption		Micro-disconnection			
	Type of insulation		Basic isolation: Coil-Contact, Live parts-Ground			
	Pollution degree		2			
	Impulse withstand volt	age	4.0 kV			
	Test procedure		A (Group mounting)			
	Categories of environm	nental protection	RT 1			
Comm	Degree of protection by according to IEC 60529		IP20			
	Contact material		Ag alloy	Ag allov + Au plating		

## Approved standards


#### UL (File No.E41515)

Model	Contact form	Operation coil ratings	Contact ratings	Operations
G2RV-ST series	SPDT	12 to 48 VDC 24 to 230 VAC	6 A at 250 VAC (Resistive load) 6 A at 30 VDC (Resistive load) 2 A at 400 VAC (Resistive load)*	6,000
	eeds 250 VAC, please a a separate plate (XW52 P3.1T).		12 mm 12 mm +++ 	

#### TÜV (File No.R50559210, EN61810-1)

Model	Contact form	Operation coil ratings	Contact ratings	Operations
G2RV-ST series S	SPDT	,	6 A at 250 VAC (Resistive load) 6 A at 30 VDC (Resistive load) 2 A at 400 VAC (Resistive load)*	50,000 50,000 6,000

\* If the load voltage exceeds 250 VAC, please attach with a spacing of 12 mm min., or use a separate plate (XW5Z-EP12) or 4psc of isolation plate (P2RV-P3.1T).




#### Lloyd's (File No.LR23158192TA)


Model	No. of poles	Operation coil ratings	Contact ratings	
G2RV-ST500 G2RV-ST700	1c	12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC	6 A at 250 VAC (Resistive load) 2.5 A at 250 VAC (PF0.4) 6 A at 30 VDC (Resistive load) 2 A at 30 VDC (L/R=7 ms)	
G2RV-ST501 G2RV-ST701	1c	12, 24 VDC 24 VAC/VDC	6 A at 250 VAC (Resistive load) 2.5 A at 250 VAC (PF0.4) 6 A at 30 VDC (Resistive load) 2 A at 30 VDC (L/R=7 ms)	
G2RV-ST500-AP G2RV-ST700-AP	1c	12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC	0.05 A at 30 VAC (Resistive load) 0.05 A at 36 VDC (Resistive load)	

# **Reference Data**

#### Endurance curve (N.O. side)



Switching capacity of DC resistive load





# **G2RV-ST**

# **Dimensions**


Slim I/O Relay + socket **Push-In Plus Terminal Block** 

Models without latching lever (without test switch) **G2RV-ST500** G2RV-ST500-AP






88




Note: For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. Recommended Ferrules and Crimp Tools on page 26.


#### Models with latching lever (with test switch) G2RV-ST501





Terminal Arrangement/Internal Connection Diagram (TOP VIEW)





Equipped with a coil surge absorption circuit as standard. AC input and AC/DC input models: 🔛 Diode bridge DC input models: ✤ Diode


Note: For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. Recommended Ferrules and Crimp Tools on page 26.


G2RV-S

8

#### Screw terminal Models without latching lever (without test switch) G2RV-ST700 G2RV-ST700-AP








G2RV-ST

G3RV-ST


**Common Precautions** 


**Note:** For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. *Recommended Ferrules and Crimp Tools* on page 26.

Models with latching lever (with test switch) G2RV-ST701



Terminal Arrangement/Internal Connection Diagram (TOP VIEW)






G2RV-ST700(-AP) 24 VAC/VDC

Equipped with a coil surge absorption circuit as standard. AC input and AC/DC input models: 🔝 Diode bridge DC input models: 🕂 Diode

Note: For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. Recommended Ferrules and Crimp Tools on page 26.

# **G2RV-ST**

#### **Relay for maintenance**



0.5

5.04

2.4

\_3

5.04

22

3.5

1.8

МЕМО

# OMRON

# Slim I/O Solid State Relay

# Slim I/O SSR realizes space saving thanks to high-density mounting and ultra-slim body


- 60% space saving from G3R-I/O series with 6.2 mm width technology.
- 60%\* reduction in wiring time and user-friendly with a low insertion force thanks to Push-In Plus Technology.
- Maximum applicable load of 3 A (DC) and 2 A (AC) realized thanks to slim technology.
- The output DC type has a minimum applicable load of 100 µA and a leaked current of 10 µA or less.
- High-speed switching type (operation time of 0.2 ms or less, release time of 0.4 ms or less) added.
- \* According to OMRON actual measurement data for both push-in plus terminal blocks and screw terminal blocks.

Refer to Safety Precautions on page 22. /!\

# **Features**

G2RV-S


G3RV-S







For the recent information on models that have been certified for safety standards, refer to your OMRON website.



# **Model Number Structure**

#### **Model Number Legend**

G3RV	-ST		- 🗌 -	•	
(1)	(2)	(3)	(4)	(5)	(6)

(1) Basic model name

G3RV: Slim I/O Solid State Relay

#### (2) Sub type

ST: Slim solid relay + integrated low profile socket

#### (3) Terminal (wire connection) 500: Push-In Plus Terminal

700: Screw terminal

#### (4) Output voltage specification

- A : AC output (triac) zero cross function available AL : AC output (triac) zero cross function not available
- D : DC output (MOS FET)

#### (5) Operation and release time

H : High speed type

#### (6) Rated voltage input

12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC

# G3RV-ST

# **Ordering Information**

Terminal (wire connection)	Applicable output load	Zero cross function	Rated inp	ut voltage (V)	Model	
(wire connection)		runction		12	G3RV-ST500-D 12 VDC	
			DC	24	G3RV-ST500-D 12 VDC	
				24	G3RV-ST500-D 24 VAC/VDC	
			AC/DC	48	G3RV-ST500-D 24 VAC/VDC	
	DC load	—		100	G3RV-ST500-D 48 VAC/VDC	
				110	G3RV-ST500-D 100 VAC	
			AC	200	G3RV-ST500-D 110 VAC	
				200	G3RV-ST500-D 200 VAC	
	DC load		DC	230	G3RV-ST500-D-H 24 VDC	
	(high-speed	_	-			
	opening and closing)		AC/DC	24	G3RV-ST500-D-H 24 VAC/VDC	
			DC	12	G3RV-ST500-A 12 VDC	
			20	24	G3RV-ST500-A 24 VDC	
Push-In Plus Terminal			AC/DC	24	G3RV-ST500-A 24 VAC/VDC	
		Yes		48	G3RV-ST500-A 48 VAC/VDC	
		103		100	G3RV-ST500-A 100 VAC	
			AC	110	G3RV-ST500-A 110 VAC	
				200	G3RV-ST500-A 200 VAC	
	AC load			230	G3RV-ST500-A 230 VAC	
	ACIDAU		DC	12	G3RV-ST500-AL 12 VDC	
			DC	24	G3RV-ST500-AL 24 VDC	
			AC/DC	24	G3RV-ST500-AL 24 VAC/VDC	
		No	AC/DC	48	G3RV-ST500-AL 48 VAC/VDC	
•			AC DC AC/DC	100	G3RV-ST500-AL 100 VAC	
				110	G3RV-ST500-AL 110 VAC	
1				200	G3RV-ST500-AL 200 VAC	
				230	G3RV-ST500-AL 230 VAC	
				12	G3RV-ST700-D 12 VDC	
				24	G3RV-ST700-D 24 VDC	
				24	G3RV-ST700-D 24 VAC/VDC	
	DC load			48	G3RV-ST700-D 48 VAC/VDC	
			AC	100	G3RV-ST700-D 100 VAC	
				110	G3RV-ST700-D 110 VAC	
				200	G3RV-ST700-D 200 VAC	
				230	G3RV-ST700-D 230 VAC	
	DC load		DC	24	G3RV-ST700-D-H 24 VDC	
	(high-speed	—	AC/DC	24	G3RV-ST700-D-H 24 VAC/VDC	
]	opening and closing)					
			DC	12	G3RV-ST700-A 12 VDC	
1				24	G3RV-ST700-A 24 VDC	
Screw terminal			AC/DC	24	G3RV-ST700-A 24 VAC/VDC	
		Yes		48	G3RV-ST700-A 48 VAC/VDC	
				100	G3RV-ST700-A 100 VAC	
			AC	110	G3RV-ST700-A 110 VAC	
				200	G3RV-ST700-A 200 VAC	
	AC load			230	G3RV-ST700-A 230 VAC	
			DC	12	G3RV-ST700-AL 12 VDC	
				24	G3RV-ST700-AL 24 VDC	
			AC/DC	24	G3RV-ST700-AL 24 VAC/VDC	
		No		48	G3RV-ST700-AL 48 VAC/VDC	
				100	G3RV-ST700-AL 100 VAC	
]			AC	110	G3RV-ST700-AL 110 VAC	
				200	G3RV-ST700-AL 200 VAC	
				230	G3RV-ST700-AL 230 VAC	

Note: Sockets are not sold individually.

#### Solid state relay for maintenance

#### **Model Number Legend**

G3RV-(1) (2) (3) (4) (5) (6)

(1) Output voltage specification D: DC output 2: AC output

Operation

Display

Output

(SSR)

AC

Zero cross

Function

Yes

No

(2) Rated current

02: AC output 2 A 03: DC output 3 A

(3) Terminal S: Plug-in type

List of Models

Insulation

method

Photo-triac

Photo-

voltage

coupler

Yes (green) (4) Zero cross functions Blank: Zero cross function available L: Zero cross function not available

(5) Operation and release time H : High speed type

(6) Rated voltage input Number: 12, 24, 48 VDC

Rated

output

Load \*

2 A

3 A

VDC)

(at 5 to 24

(at 100 to

240 VAC)

Rated input

voltage

(socket) 12 VDC

24 VAC/VDC

48 VAC/VDC

24 VDC

100 VAC

110 VAC

200 VAC

230 VAC

12 VDC

24 VDC 24 VAC/VDC 48 VAC/VDC

100 VAC

110 VAC 200 VAC 230 VAC 12 VDC 24 VDC 24 VAC/VDC 48 VAC/VDC

100 VAC

110 VAC

200 VAC 230 VAC

24 VDC



Model

G3RV-202S DC12

G3RV-202S DC24

G3RV-202S DC48

G2RV-S1

G3RV-ST

G3RV-202SL DC12	G3RV-ST700/500-AL 12 VDC		
G3RV-202SL DC24	G3RV-ST700/500-AL 24 VDC	B	
G3R V-2023L DC24	G3RV-ST700/500-AL 24 VAC/VDC	B	
	G3RV-ST700/500-AL 48 VAC/VDC	ommon	
	G3RV-ST700/500-AL 100 VAC	Precautions	
G3RV-202SL DC48	G3RV-ST700/500-AL 110 VAC		
	G3RV-ST700/500-AL 200 VAC		
	G3RV-ST700/500-AL 230 VAC	Ĩ	
G3RV-D03SL DC12	G3RV-ST700/500-D 12 VDC	lio	
	G3RV-ST700/500-D 24 VDC	ŝŭ	
G3RV-D03SL DC24	G3RV-ST700/500-D 24 VAC/VDC	07	
	G3RV-ST700/500-D 48 VAC/VDC		
	G3RV-ST700/500-D 100 VAC		
G3RV-D03SL DC48	G3RV-ST700/500-D 110 VAC	C C	
	G3RV-ST700/500-D 200 VAC	H	
	G3RV-ST700/500-D 230 VAC	m l	
	G3RV-ST700/500-D-H 24 VDC	ō	
G3RV-D03SL-H DC24	G3RV-ST700/500-D-H 24 VAC/VDC	Common Acces	
		6	
18.		Ce	
		SS	
		ő	
		sories	
		S.	

Applicable model

G3RV-ST700/500-A 12 VDC

G3RV-ST700/500-A 24 VDC

G3RV-ST700/500-A 100 VAC

G3RV-ST700/500-A 110 VAC

G3RV-ST700/500-A 200 VAC

G3RV-ST700/500-A 230 VAC

G3RV-ST700/500-A 24 VAC/VDC

G3RV-ST700/500-A 48 VAC/VDC

\* Different depending on the ambient temperature.

DC

For more details, refer to Load current vs. ambient rated temperature on page 18.

#### Accessories (order separately)

Refer to page 29 for G2RV-ST/G3RV-ST Common Accessories.

15

# G3RV-ST

# **Specifications**

## Rating (ambient temperature 25°C)

G2RV-ST

#### Input G3RV-ST700/500-A series

	i	Rated curre	ent			Input voltage	
Rated input voltage	A	AC		Must operate voltage	Must release voltage	Percentage of the	
voltage	50 Hz	60 Hz	DC	voltage	Voltage	rated voltage	
12 VDC	-	-	15.0 mA	10.8 V max.			
24 VDC	-	-	12.0 mA	21.6 V max.	_		
24 VAC/VDC	11.3 mA	11.4 mA	11.0 mA	21.6 V max.		±10%	
48 VAC/VDC	6.8 mA	6.9 mA	6.0 mA	43.2 V max.			
100 VAC	6.2 mA	6.2 mA	-	90 V max.	– 1 V min.	±10%	
110 VAC	6.2 mA	6.2 mA	-	99 V max.	-		
200 VAC	6.7 mA	7.9 mA	-	180 V max.	_		
230 VAC	7.5 mA	8.8 mA	-	207 V max.			

#### G3RV-ST700/500-AL series

	Rated current						Input voltage
Rated input voltage	A	AC		Must operate voltage	Must release voltage	Percentage of the	
Tonago	50 Hz	60 Hz	DC	Vollago	Venage	rated voltage	
12 VDC	-	-	15.0 mA	10.8 V max.			
24 VDC	-	-	12.0 mA	21.6 V max.			
24 VAC/VDC	11.4 mA	11.5 mA	11.0 mA	21.6 V max.			
48 VAC/VDC	7.7 mA	7.7 mA	6.9 mA	43.2 V max.	1 V min.	. 100/	
100 VAC	7.3 mA	7.3 mA	-	90 V max.	- i v min.	±10%	
110 VAC	7.3 mA	7.3 mA	-	99 V max.			
200 VAC	7.0 mA	8.1 mA	-	180 V max.			
230 VAC	7.7 mA	8.9 mA	-	207 V max.	_		

#### G3RV-ST700/500-D series

<b>B</b> ( 11) (	Rated current					Input voltage	
Rated input voltage	AC		DC	Must operate voltage	Must release voltage	Percentage of the	
ronago	50 Hz	60 Hz		Tenage	Voltago	rated voltage	
12 VDC	-	-	8.0 mA	10.8 V max.			
24 VDC	-	-	4.6 mA	21.6 V max.	_		
24 VAC/VDC	5.0 mA	5.1 mA	4.3 mA	21.6 V max.	_		
48 VAC/VDC	6.8 mA	6.9 mA	6.0 mA	43.2 V max.	1 V min.	±10%	
100 VAC	6.8 mA	6.8 mA	-	90 V max.		±10%	
110 VAC	6.7 mA	6.7 mA	-	99 V max.	_		
200 VAC	6.7 mA	7.9 mA	-	180 V max.			
230 VAC	7.5 mA	8.8 mA	-	207 V max.	1		

#### High-speed type G3RV-ST700/500-D-H series

Deted in mut	Rated current			Mustereste	Must valages	Input voltage	
Rated input voltage	AC		DC	Must operate voltage	Must release voltage	Percentage of the	
	50 Hz	60 Hz				rated voltage	
24 VDC	-	-	9.0 mA	21.6 V max.	1 V min.	±10%	
24 VAC/VDC	9.0 mA	9.5 mA	8.4 mA	21.6 V max.	1 V IIIII.	1070	

#### Output

Item	G3RV-ST700/500-A(L)	G3RV-ST700/500-D(-H)
Rated load voltage	100 to 240 VAC (50/60 Hz)	5 to 24 VDC
Load voltage range	75 to 264 VAC (50/60 Hz)	3 to 26.4 VDC
Load current	0.1 to 2 A (Ambient temperature=25°C)	100 μA to 3 A (Ambient temperature=25°C)
Inrush current resistance	30 A (60 Hz, 1 cycle)	30 A (10 ms)
Permissible l <sup>2</sup> t; Joule integral value (reference value)	15A <sup>2</sup> s	9 A <sup>2</sup> s
Applied load capacity	400 W (Output voltage: 200 VAC)	72 W (Output voltage: 24 VDC)

16

**Common Precautions** 

#### **Characteristics**

ltem	G3RV- ST700/500-A	G3RV- ST700/500-AL	G3RV- ST700/500-D-H 24 VDC	G3RV- ST700/500-D-H 24 VAC/VDC	G3RV- ST700/500-D
Operate time	11 ms max. *1	3 ms max.	0.2 ms max.	3 ms max.	6 ms max.
Release time	31 ms max. *2	31 ms max. *2	0.4 ms max.	21 ms max. *3	21 ms max. *3
Output ON voltage drop	1.6 V (RMS) max.			_	
Output ON resistance		_	0.3 Ω max. (at 24 \	/DC)	
Leaked current	5 mA max. (at 200	VAC, 50/60 Hz)	10 µA max. (at 24	VDC)	
Insulation resistance	100 MΩ min. (at 50	00 VDC)	,		
Dielectric strength	Between input and	output 2,500 VAC 5	50/60 Hz 1 min		
Vibration resistance	10 to 55 to 10 Hz c	ouble amplitude 0.7	'0 mm		
Shock resistance	300m/s <sup>2</sup>				
Ambient operating temperature	Storage: –30 to +100°C (with no icing or no condensation) Operating: –30 to +55°C (with no icing or no condensation)				
Ambient operating humidity	45 to 85% RH				
Weight	Approx. 30 g				
Pollution degree	2				
The degree of protection by IEC60529	IP20				
Rated impulse dielectric strength	4.0 kV/III				
Load category	LC-A		DC-12		
Overload current profile	1.5le 1.1Ue 5s ON, 10s OFF, 10 cycles				
Rated insulation voltage	240 V				
MTTFd (Reference value)	1,000 years min.				

\*1. 1/2 cycle of load power supply frequency + 1 ms max.
\*2. 1/2 cycle of load power supply frequency + 1 ms + 1 cycle of input power supply frequency (AC input model)
\*3. 1 cycle of input power supply frequency + 1 ms

#### **Approved standards**

#### UL (File No.E41515)

Model	Input ratings	Contact ratings
G3RV-ST700/500-D(-H) series	12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC	24 VDC 3 A (resistive load) at 25°C
G3RV-ST700/500-A(L) series	12, 24 VDC 24, 48 VAC/DC 100, 110, 200, 230 VAC	240 VAC 2 A (resistive load) at 25°C

#### TÜV (File No.R50559231, EN62314)

Model	Input ratings	Contact ratings
G3RV-ST700/500-D(-H) series	12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC	24 VDC 3 A (resistive load)
G3RV-ST700/500-A(L) series	12, 24 VDC 24, 48 VAC/VDC 100, 110, 200, 230 VAC	240 VAC 2 A (resistive load)


# G3RV-ST

# **Engineering Data**

#### Load current vs. ambient rated temperature

#### G3RV-ST700/500-A(L) series


Product mounting spacing 10 mm (Separate Mounting)



#### Load current (A) During close mounting with 8 units 5 2 0.6 0.2 0 -30 10 20 55 60 100 40 80 Ambient temperature (°C)


Close mounting (up to 8 units \*)

Close mounting (up to 5 units)




G3RV-ST700/500-D(-H) series

Product mounting spacing 10 mm (Separate Mounting)





Close mounting (up to 8 units \*)




\*When eight or more are installed, install with 10 mm space between each. For details, please refer to Mounting on page 28.


#### **Inrush Current Resistance: Non-repetitive**

Keep the inrush current to below the inrush current resistance value (i.e., below the broken line) if it occurs repetitively.

#### G3RV-ST700/500-A(L) series




#### G3RV-ST700/500-D(-H) series





## **Dimensions**


Solid state relay + socket **Push-In Plus Terminal Block** G3RV-ST500











G3RV-ST 24 VAC/VDC G3RV-ST 48 VAC/VDC G3RV-ST 100 VAC G3RV-ST 110 VAC G3RV-ST 200 VAC G3RV-ST 230 VAC

Input circuit

(A1) (A2)

(12)

(14)

(13)

7  $\overline{\mathbb{A}}^{2}$ Ø

G3RV

A2-INPUT A1+ 13 (+) OUTPUT

14 (-)

The information in parentheses in for

a DC output.



19

Note: For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. Recommended Ferrules and Crimp Tools on page 26.

# G3RV-ST

(unit: mm)

G2RV-ST

G3RV-ST

**Terminal Arrangement/** Internal Connection Diagram (TOP VIEW)


G3RV-ST 12 VDC


OMRON

# G3RV-ST

#### Screw terminal G3RV-ST700







Note: For recommended ferrules, crimp tools, and types and gauges of wires, refer to 3. Recommended Ferrules and Crimp Tools on page 26.

G3RV-S1

# G3RV-ST

#### Solid state relay for maintenance

20509E6

DC-12

óc ≡

13+

E TÜV

G3RV-D03SL(-H) G3RV-202S(L)


> OMRON G3RV-D03SL

c 91 us (

INPUT 24VDC =

INPUT A2-A1+


11



Terminal Arrangement/ Internal Connection Diagram (TOP VIEW) G3RV-D03SL(-H)

**Note:** The load can be connected to either the positive or negative terminals.

G3RV-202S(L)



G3RV-ST

G2RV-ST

omron 21

# **Safety Precautions**

Be sure to read the *Safety Precautions for All Relays* in the website at the following URL: http://www.ia.omron.com/.

#### Format of Warning Indications

	Format of Wa	Format of Warning Indications					
	WARNING		Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally, there may be significant property damage.				
			Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.				
7	Precautions for Safe Use		Indicates supplementary comments on what to do or avoid doing, to use the product safety.				
	Precaution for Correc Use		Includes operating precautions to ensure that the product will operate properly and that performance and functions will not be adversely affected.				
	Meaning of G	rapł	hic Symbols for Ensuring Product Safety				
			icates the possibility of electric shock under ecific conditions.				
		DA	sed for general CAUTION, WARNING, or ANGER precautions for which there is no				

DANGER precautions for which there is no specified symbol. (This symbol is also used as the alerting symbol, but shall not be used in this meaning on the product.)

Indicates the possibility of explosion or rupture under specific conditions.

Indicates the possibility of injuries by high temperature under specific conditions.

#### 🕂 WARNING


Ensure that the socket is not charged during wiring and maintenance. Not doing so may result in electric shock.

Do not touch the terminal section of the G2RV-ST or the surrounding area while the power is being supplied. Doing so may result in electric shock.



#### 

Minor electrical shock may occasionally occur. Do not touch the G3RV terminal section (i.e., current carrying parts) while the power is being supplied.



The G3RV may rupture if short-circuit current flows. As protection against accidents due to short-circuiting, be sure to install protective devices, such as fuses and no-fuse breakers, on the power supply side.

Minor electrical shock may occasionally occur. Do not touch the main circuit terminals on the G3RV immediately after the power supply has been turned OFF.



Shock may result due to the electrical charge stored in the built-in snubber circuit. Note: G3RV-202S(L), G3RV-ST500/700-A(L) series models only

Minor burns may occasionally occur. Do not touch the G3RV or the heat sink while the power is being supplied or immediately after the power supply has been turned OFF. The G3RV becomes extremely hot.

Provide a space of at least 3 mm or place an insulating plate (P2RV-P3.1ST) between the G2RV-ST or G3RV-ST and ground and other adjacent components. Not doing so may result in an electric shock.

When mounting the G2RV-ST or G3RV-ST with its input and output opposite to the input and output of an adjacent product, provide a space of at least 3 mm or place an insulating plate (P2RV-P3.1ST) between them.



G3RV-S

G2RV-

#### **Precautions for Safe Use**

#### Transport

- Do not use the product if it has been dropped on the ground. Dropping the product may adversely affect performance.
- Do not drop the product or subject it to abnormal vibration or shock during transportation or mounting. Doing so may result in deterioration of performance, malfunction, or failure.
- Do not transport the product without it being packaged. Doing so may result in damage, malfunction, or failure.
- Do not transport the G3RV under the following conditions. Doing so may result in damage, malfunction, or deterioration of performance characteristics.
  - · High temperature, high humidity conditions
  - Conditions such as temperature change that causes rapid condensation
  - Condition where it is not packaged

#### **Operating and Storage Environments**

- Do not use or store the product in the following locations. Doing so may result in damage, malfunction, or deterioration of performance characteristics.
  - Storage in locations subject to ambient temperature outside the range -40 to 70°C (for G2RV) and -30 to 100°C (for G3RV), and usage in locations subject to ambient temperature outside the range -40 to 55°C (for G2RV) and -30 to 55°C (for G3RV).
  - Locations subject to relative humidity outside the range 5% to 85% (for G2RV) and outside the range 45% to 85% (for G3RV).
  - Locations subject to high temperature or high humidity.
  - Conditions such as temperature change that causes rapid condensation
  - · Locations where corrosive gases or flammable gases are present
  - · Location where rainwater or water droplets gets splashed
  - · Location with splashes of water, oil, and chemicals, etc.
  - Locations with much dust, salt, and iron powder
  - Location with blockers
  - Where static electricity or noise occurs
  - · Where strong electromagnetic field is generated
  - · Where there is a risk of exposure to radioactivity
  - Storage in a state with a load applied to the product
  - · Locations subject to ultraviolet rays from direct sunlight
- Do not use or store Sockets in environments that contain silicone gas, sulfidizing gas (e.g., SO<sub>2</sub> or H<sub>2</sub>S), or organic gas, or near materials that contain silicone. Doing so may cause the contacts to be unstable or to fail.

#### Handling <G3RV>

Keep the G3RV well ventilated.
 There is a risk of short-circuiting or burning due to G3RV overheating.

#### Mounting

- Before you start wiring, please make sure that the socket is securely attached to the mounting rail. If the socket is unstable, it may come loose and risk of injury towards the workers.
- Please insert the flat-blade screwdriver to the bottom of the hole. If you do not insert the flat-blade screwdriver correctly, the cable will not be connected correctly.
- When lubricant such as oil is attached to the tip of the driver, the driver will fall off, with a risk of injury towards the workers.

 When replacing a relay, set the stopper to the unlocked state and then eject the relay with the ejector lever. In addition, press the stopper after replacement to change the state from unlocked to locked.





Locked state

Unlocked state

- To operate the stopper, you can change the state from locked to unlocked by gripping the stopper protruding part with the recommended needle-nose pliers. (Needle-nose pliers with a tip shape that is 4 mm wide or less and 3 mm thick or less.)
- Do not use cutting nippers to operate the stopper. Doing so may damage the stopper.



 If the stopper is operated with an exceedingly strong force, the stopper protruding part may be damaged and the stopper may drop out. Since the function of the stopper is to fix the ejector lever, use as a product is possible even in the event that the stopper is damaged or drops out because the functionality is satisfied even without a stopper in respect to vibrations and impacts.

#### Usage

- Please select the load within the rated range. Doing so may result in damage, malfunction, or failure.
- Please use the power of the rated frequency. It may cause malfunction, failure, or risk of burnout.

#### <G3RV>

- Install G3RV according to instructions *Mounting* on page 28. If you
  install in the wrong direction, abnormal heat is generated, and may
  lead to short-circuiting or burning the output element.
- G3RV is an SSR that generates heat. Please observe the ambient temperature setting range of G3RV. If installing in an enclosed space, set a fan, and ventilate.
- When mounting G3RV to DIN rail, firmly fits into the groove. If it is not properly installed, there is a risk of it falling.

G2RV-S

G3RV-S

#### Wiring

G2RV-S

- For the current to be applied, make sure a wire size with margin is used. Otherwise, excessive heat generated by the wires may cause burning.
- Do not attempt to use the wire if the coat is torn. Not doing so may result in electric shock.
- Always turn OFF the power supply before performing wiring. Not doing so may cause electrical shock.

#### <G3RV>

 The wires of the socket for G3RV socket should not be passed through the same duct as that being connected to the high-voltage power supply. Otherwise, inductive noise may damage the G3RV or cause it to malfunction.

#### **Push-In Plus Terminal Block**

- Do not wire anything to the release holes.
- Do not tilt or twist a flat-blade screwdriver while it is inserted into a release hole on the terminal block. The terminal block may be damaged.
- Insert a flat-blade screwdriver into the release holes at an angle. The terminal block may be damaged if you insert the screwdriver straight in.
- Do not allow the flat-blade screwdriver to fall out while it is inserted into a release hole.
- Do not bend the wire past its natural bending radius or pull on it with excessive force. Doing so may cause the wire disconnection.
- Do not insert more than one wire into each terminal (insertion) hole.
- To prevent wiring materials from smoking or ignition, confirm wire ratings and use the wiring materials given in the following table. \*

Recommended Wire (UL and EN standard certification)	Stripping length
0.5 to 2.5 mm <sup>2</sup> / AWG20 to AWG14 stranded wire, 0.5 to 2.5 mm <sup>2</sup> /	8 to 10 mm
AVAIC20 to AVAIC14 polid wire	

AWG20 to AWG14 solid wire


\* The recommended wire gauge and stripping length values are for stranded wire or solid wire. When using ferrules, refer to the table of recommended ferrules in Precautions for Correct Use.


#### Disposal


• When disposing of the product, do not put into the fire.

**Precautions for Correct Use** 


- Do not use or store the product in the following locations. Doing so may result in damage, malfunction, or deterioration of performance characteristics.
  - Where vibration or shock is directly transmitted to the body
  - Where the socket could come into contact with a solvent or alkaline agent
- When installing the short bar, insert it into the insertion hole, and insert until all terminals are all the way in.








Incomplete insertion All terminals are not inserted all the way in. Incorrect installation Some terminals not inserted completely.





• To remove the short bar, insert a screwdirver beneath the hole on top of the short bar and lift up.

Start lifting up from either end, lift up all screwdriver in order, and then remove the short bar.

- When removing the short bar while the product is mounted in a control panel or on equipment, make sure there is enough space to use the screwdriver.
- · Remove the short bar with the wiring disconnected.



Common Accessories

24

G3RV-S

- If using a short bar, install the short bar before performing wiring work.
- A push-in Plus terminal block type and a screw terminal type have different insertion positions, so a mixed installation using the same short bar is not possible.
- Do not insert short bar in the hole for wire or screw driver, it may cause the result of failure of pull out.
   If insert short bar in the hole for wire or screw driver and try to pull out, it may cause damage for short bar or socket and failure in
- electric conductivity.
  Please insert P2RVC terminal into the short bar insertion hole of G2RV-ST/G3RV-ST. If insert P2RVC into the release hole or terminal (insertion) hole wrongly, P2RVC may stuck and can not remove and it may cause result of damage on P2RVC and G2RV-ST/G3RV-ST.

Please turn off the power of input and output side and remove PLC interface unit when replacing mounting relays and SSRs for maintenance.

- When replacing relays, there is a possibility the relay will pop out and fall. Take care to prevent the relay from falling during replacement.
- When replacing a relay, remove it by tilting it to the left as shown in the figure below because the protrusion to prevent pop-out relay will get in the way.



 Dedicated accessories for G2RV-SR/G3RV-SR are not compatible and cannot be used.

#### Short Bars


- PYDN-6.2-020
- PYDN-6.2-030
- PYDN-6.2-040
- PYDN-6.2-100
- PYDN-6.2-200

#### PLC interface unit

- P2RVC-8-I-5-1
- P2RVC-8-I-5
- P2RVC-8-I-7-1
- P2RVC-8-O-5-1
- P2RVC-8-O-5
- P2RVC-8-O-7-1


#### **Push-In Plus Terminal Block**

1. Connecting Wires to the Push-In Plus Terminal Block Part Names of the Terminal Block



#### **Connecting Wires with Ferrules and Solid Wires**


Insert the solid wire or ferrule straight into the terminal block until the end strikes the terminal block.




• If a wire is difficult to connect because it is too thin, use a flat-blade screwdriver in the same way as when connecting stranded wire.

#### **Connecting Stranded Wires**

- Use the following procedure to connect the wires to the terminal block. (1) Hold a flat-blade screwdriver at an angle and insert it into the
  - release hole. The angle should be between 10°and15°. If the flat-blade screwdriver is inserted correctly, you will feel the spring in the release hole.
- (2) With the flat-blade screwdriver still inserted into the release hole, insert the wire into the terminal hole until it strikes the terminal block.
- (3) Remove the flat-blade screwdriver from the release hole.





#### **Checking Connections**


- After the insertion, pull gently on the wire to make sure that it will not come off and the wire is securely fastened to the terminal block.
- If you use a ferrule with a conductor length of 10 mm, part of the conductor may be visible after the ferrule is inserted into the terminal block, but the product insulation distance will still be satisfied.


#### 2. Removing Wires from the Push-In Plus Terminal Block

Use the following procedure to remove wires from the terminal block. The same method is used to remove stranded wires, solid wires, and ferrules.

- (1) Hold a flat-blade screwdriver at an angle and insert it into the release hole.
- (2) With the flat-blade screwdriver still inserted into the release hole, remove the wire from the terminal insertion hole.

(3) Remove the flat-blade screwdriver from the release hole.





OMRON

Common Accessories

G2RV-S


G3RV-ST

#### 3. Recommended ferrules and Crimp Tools **Recommended ferrules**

Applicable wire		Ferrules Conduct	Stripping length	Recommended ferrules		
(mm²)	(AWG) (mm) (Ferr		(mm) (Ferrules used)	Phoenix Contact product	Weidmuller product	Wago product
0.25	24	8	10	AI 0,25-8	H0.25/12	216-301
0.25	24	10	12	AI 0,25-10		
0.24	22	8	10	AI 0,34-8	H0.34/12	216-302
0.34 22	22	10	12	AI 0,34-10		
0.5 20	8	10	AI 0,5-8	H0.5/14	216-201	
0.5 20	20	10	12	AI 0,5-10	H0.5/16	216-241
0.75 18	10	8	10	AI 0,75-8	H0.75/14	216-202
	10	10	12	AI 0,75-10	H0.75/16	216-242
4/4.05 4.0/4	18/17	8	10	AI 1-8	H1.0/14	216-203
1/1.25	10/17	10	12	AI 1-10	H1.0/16	216-243
1.25/1.5	17/16	8	10	AI 1,5-8	H1.5/14	216-204
1.20/1.5	17/16	10	12	AI 1,5-10	H1.5/16	216-244
2.0/2.5	14	10	12	AI 2,5-10	H2.5/16DS	
Recom	mended	crimp tool	1	CRIMPFOX6 CRIMPFOX6T-F CRIMPFOX10S	PZ6 roto	Variocrimp

Note: 1. Make sure that the outer diameter of the wire is smaller than the inner diameter of the insulating sleeve of the recommended ferrule.

2. Make sure that the ferrule processing dimensions conform to the following figure.




3. If you use AWG24 to AWG22 (0.25 to 0.34 mm<sup>2</sup>) wires, UL and TÜV certification will not apply.

#### **Recommended Flat-blade Screwdriver**

Use a flat-blade screwdriver to connect and remove wires. Use the following flat-blade screwdriver.

The following table shows manufacturers and models as of 2015/ Dec



Model	Manufacturer
ESD 0,40×2,5	Wera
SZS 0,4×2,5 SZF 0-0,4×2,5 <b>*</b>	Phoenix Contact
0.4×2.5×75 302	Wiha
AEF.2,5×75	Facom
210-719	Wago
SDI 0.4×2.5×75	Weidmuller
*OMRON's exclusive purchase m	odel XW4Z-00B is avail

vailable to order as SZF 0-0,4×2,5 (manufactured by Phoenix Contact).

#### **Screw Terminal** Screw terminal


#### Applicable wire Stripping Wired type length size Stranded wires, without ferrule Stranded wires, with ferrule and plastic collar 0.5 to 2.5 mm<sup>2</sup> 8 to 10 mm Stranded wires with ferrule, without plastic collar Single wire

#### Tightening Torque

0.36 to 0.46 N • m

#### Electric wiring

Use the electric wire of specified size as shown above. The length of the that is not covered is 8 to 10 mm.



#### **Recommended Flat-blade Screwdriver/ Phillips Screwdriver**


Use a Phillips screwdriver or flat-blade screwdriver to remove the product from a DIN rail and connect and remove the electric wires. Use a Phillips screwdriver with the shape specified below and a flatblade screwdriver in the table below.

The following table shows manufacturers and models as of 2015/Dec.

Side



Recommended Flat-blade Screwdriver



Model	Manufacturer
ESD 0,40×2,5	Wera
SZS 0,4×2,5 SZF 0-0,4×2,5 <b>*</b>	Phoenix Contact
0.4×2.5×75 302	Wiha
AEF.2,5×75	Facom
210-719	Wago
SDI 0.4x2.5x75	Weidmuller


\*OMRON's exclusive purchase model XW4Z-00B is available to order as SZF 0-0,4×2,5 (manufactured by Phoenix Contact).

G2RV-

G3RV-ST

#### **Mounting Method**

To mount the product to a DIN rail, hook one side of the socket and then press the socket onto the DIN rail.



#### **Removal Method**

To remove the product from the DIN rail, catch the tip of a screwdriver in the hook and then move the screwdriver so that the tip moves in the directions indicated by the arrows.




#### <G2RV>

Operating latching lever (test switch) When operating the latching lever for G2RV-ST701/501 series, use a 2.5 mm width flat-blade screwdriver.

#### Applicable flat-blade screwdriver

Flat-blade screwdriver with parallel cutting edge: shaft diameter 2.5 mm (3.0 mm max.)



Driver with a thick shaft cannot be used.

- Always turn OFF the power supply before operating latching lever.
- Return to its original state after using the latching lever.
- Do not use the latching lever as a switch.
- Operation durability of the latching lever is 100 times or more. Do not keep the latching lever ON for a long period of time (24
- hours or more) in order to maintain the operation check function.

# Method of operation of the latching lever (test switch)

<Protective cover: locked>

omron

Close protective

<protective cover:="" disengage=""></protective>
Contact normal position
omron I Jee
Contact operating position (on-state)
Open protective cover

Keep the protective cover open when using the latching lever. Move until the latching lever clicks to the ON position (ON state). After use latching lever, in order to prevent malfunction, return the switch to contact normal position (OFF state), and make sure the protective cover is firmly closed.

#### Using the latching lever

Example: check the operation of the relay and the sequence circuit

#### Input ratings

Smoothing capacitors are used in the internal circuits of AC/DCtype G2RV-ST devices. AC/DC-type G2RV-ST devices driven by the sensor may not operate normally due to the characteristics of the smoothing capacitor. When driving such devices by the sensor, use the DC specification settings.

#### <G3RV>


G2RV-S

G3RV-S

- Since the G3RV uses electronic components, do not allow it to fall, vibrate, or apply shock that exceeds the criteria. Doing so may result in failure, malfunction, or deterioration of performance.
- Tighten screw terminal for G3RV at torque 0.36 to 0.46 N · m. It may cause short-circuit failure or burning.
- Please use the voltage and current suitable for the input and output terminal portion of G3RV. It may cause short-circuit failure or burning.

#### Mounting


#### <The SSR Mounting Pitch (Panel Mounting)>




- \* When over eight are installed, install with 10 mm space between each.
- \* Please ask distributor or sales when need assistance in detail of mounting pitch.

Countermeasure 1


#### <Relationship of SSR and duct (duct depth)>






#### Duct or other object blocking airflow

Use ducts that have a shallow depth, to provide a sufficient ventilation area.



blocking airflow If the ducts cannot be made lower, place the SSR on a metal base so that it is not surrounded by the ducts

#### <Ventilation Outside the Control Panel>



- If the air inlet or air outlet has a filter, clean the filter regularly to prevent it from clogging to ensure an efficient flow of air.
- Do not place objects that may obstruct the proper ventilation for outside or inside the inlet or exhaust port, and in the outside vicinity.
- A heat exchanger, if used, should be located in front of the G3RV to ensure the efficiency of the heat exchanger.
- Please observe the ambient temperature of G3RV. The rated current of the G3RV is measured at an ambient temperature of 25°C.
- The G3RV uses a semiconductor in the output element. This causes the temperature inside the control panel to increase due to heating resulting from the flow of electrical current through the load. The G3RV reliability can be increased by adding a ventilation fan to the control panel to dispel this heat, thus lowering the ambient temperature of the G3RV.

(It suggests that life expectancy is doubled by each 10°C reduction in ambient temperature.)

#### EMI

The G3RV is a Class A product (for industrial environments). When used in a residential environment, it may cause radio interference. In such case, the user may be required to take appropriate measures.

#### For G2RV-ST/G3RV-ST **Common Accessories (order separately)**

# **Ordering Information**

#### **Short Bars**

Appearance	Pitch	No. of poles	Colors	Model <b>*</b> 1	Minimum order (Quantity)	Maximum energizing current
	6.2 mm	20	Red (R), Blue (S), Yellow (Y)	PYDN-6.2ST-200□	10 *2	32 A

Note: Use for wiring to the adjacent socket.

\*1. Replace the box (
) in the model number with the code for the covering color. Color selection: R = red, S = blue, Y = yellow **\*2.** Short bars come in bags of 10.

#### Label

Appearance	Model	Minimum order (Sheet) (Pieces per sheet)
	XW5Z-P2.5LB1	5 (1 sheet/72 pieces)

#### **Separate Plate**

#### **Isolation plate**

Appearance	Model	Appearance	Model
	XW5Z-EP12		P2RV-P3.1ST

#### PLC interface unit

Appearance	I/O classification	Connection method	Common process	Applicable Models *1	Model
		Push-In	PNP	G2RV-ST500-AP *2	P2RVC-8ST-I-5-1
	For input	Push-in	NPN	G2RV-31500-AF +2	P2RVC-8ST-I-5
(TEB)		Screw	PNP	G2RV-ST700-AP *2	P2RVC-8ST-I-7-1
and the second s	Frankrik	Push-In	PNP	G3RV-ST500(-D)/(-D-H)/	P2RVC-8ST-O-5-1
Mohra.			NPN	- (-A)/(-AL) or G3RV-ST500 series <b>*</b> 3	P2RVC-8ST-O-5
	For output	Screw	PNP	G3RV-ST700(-D)/(-D-H)/ (-A)/(-AL) or G3RV-ST500 series <b>%</b> 3	P2RVC-8ST-0-7-1

\*1. Please make sure applicable models, P2RVC can not be used other combination than the above table.

\*2. The maximum contact voltage is 30 VAC/DC.
\*3. Operating coils are only available in 12 and 24 VDC and 24 VAC/DC.

#### Parts for DIN Track Mounting

Appearance	Туре		Model	Minimum order (Quantity)
	DIN Tracks	1 m	PFP-100N	1
		0.5 m	PFP-50N	
6	End Plate *	1	PFP-M	10
	Spacer		PFP-S	10

\*When mounting DIN Track, please use End Plate (PFP-M). Refer to your OMRON website for details on PFP-D.

#### **Applicable Cables** Cable G2RV-S Name Appearance length L **Connecting Cables Applicable Connectors** (mm) 1,000 End A End B P2RV-A100C Device PLC interface Cables with Loose end unit end 2,000 P2RV-A200C 8 I/O Wires Various devices 200 points P2RV-ACC 3,000 P2RV-A300C 70 5,000 P2RV-A500C 1,000 P2RV-4-100C OMRON PLC 2.000 P2RV-4-200C Connecting PLC I/O Units with MIL connectors (1:4) 32 output Cables with points CJ1W-OD232/OD262, etc. Connectors (1:4) 3,000 P2RV-4-300C P2RV-4-□C 5,000 P2RV-4-500C 300 G3RV-S 1,000 P2RV-4-100IMC OMRON PLC 2,000 P2RV-4-200IMC Connecting 32 input PLC I/O Units with MIL connectors (1:4) Cables with , points CJ1W-ID232/ID262, etc. \*1 Connectors (1:4) 3,000 P2RV-4-300IMC P2RV-4-DIMC 5,000 P2RV-4-500IMC 300 1,000 P2RV-4-100IFC **Common Precautions** OMRON PLC 2,000 P2RV-4-200IFC PLC I/O Units with Fujitsu/Otax Connecting 32 input Cables with connectors (1:4) points Connectors (1:4) CJ1W-ID231/ID261, etc. \*2 3,000 P2RV-4-300IFC P2RV-4-DIFC 5,000 P2RV-4-500IFC 300 Removable terminal block P2RV-A050C-OMR NX 500 OMRON PLC 8 output PLC I/O Units with screw-less clamp points Connecting 1,000 P2RV-A100C-OMR NX terminal block (1:1) Cables with For inputs: NX-ID4442 500 P2RV-A050IC-OMR NX Connectors (1:1) 8 input For outputs: NX-OD4256 P2RV-ACC-OMR NX points 1,000 P2RV-A100IC-OMR NX

\*1. Use the P2RVC-8ST-I---1(PNP) as the PLC interface unit when connecting to the CJ1W-ID232/ID262 (or a unit with an equivalent terminal arrangement).

\*2. Use the P2RVC-8ST-I--1(PNP) as the PLC interface unit when connecting to the CJ1W-ID231/ID261 (or a unit with an equivalent terminal arrangement).

Name		Appearance	Cable length L (mm)	Connecting Cables	Applicable Connectors	ດ
			500	P2RV-050C-SCH-A		G2RV-ST
	22 innut	End A End B Device PLC interface	1,000	P2RV-100C-SCH-A	_	₹
	32 input points	end unit end	2,000	P2RV-200C-SCH-A	_	S.
			3,000	P2RV-300C-SCH-A	- Schneider Electric PLCs with 32-point	
			5,000	P2RV-500C-SCH-A	connectors (1:4)	
			500	P2RV-050C-SCH-B	For inputs: 140 DDI 353 00 - For outputs: 140 DDO 353 00	
	32 output		1,000	P2RV-100C-SCH-B	- Fol outpuis. 140 DDO 355 00	
	points		2,000	P2RV-200C-SCH-B		
Schneider Electric		← L→ ← 300 →	3,000	P2RV-300C-SCH-B		
PLC Connecting			5,000	P2RV-500C-SCH-B		_
Cables P2RV-□C-SCH-□			500	P2RV-050C-SCH-C	_	
	16 input		1,000	P2RV-100C-SCH-C	_	
	points		2,000	P2RV-200C-SCH-C	_	
			3,000	P2RV-300C-SCH-C	Schneider Electric PLCs with	ι Ω
			5,000	P2RV-500C-SCH-C	16-point connectors (1:2)	G3RV-ST
			500	P2RV-050C-SCH-D	For inputs: BMX DDI 1602 For outputs: BMX DDO 1602	5
	16 output		1,000	P2RV-100C-SCH-D		Ϊ
	points		2,000	P2RV-200C-SCH-D		
			3,000	P2RV-300C-SCH-D		
			5,000	P2RV-500C-SCH-D		_
			500	P2RV-050C-SIM-A	_	
	32 input		1,000	P2RV-100C-SIM-A	_	
	points		2,000	P2RV-200C-SIM-A	Siemens PLCs with 32-point connectors (1:4) For inputs: 6ES7 321-1BL00-0AA0 For outputs: 6ES7 322-1BL00-0AA0	
			3,000	P2RV-300C-SIM-A		Common
			5,000	P2RV-500C-SIM-A		<b>B</b>
			500	P2RV-050C-SIM-B		B
	32 output		1,000	P2RV-100C-SIM-B		n o
	points		2,000	P2RV-200C-SIM-B		Ū
			3,000	P2RV-300C-SIM-B		Prec
			5,000	P2RV-500C-SIM-B		-   Ĉ
			500	P2RV-050C-SIM-C	_	autions
Siemens PLC			1,000	P2RV-100C-SIM-C	Sigmono DI Co with	<b>Q</b>
Connecting Cables	16 input points		2,000	P2RV-200C-SIM-C	Siemens PLCs with 16-point connectors (1:2) For inputs: 6ES7 321-1BH02-0AA0	SI
			3,000	P2RV-300C-SIM-C		
		L	5,000	P2RV-500C-SIM-C		S
			500	P2RV-050C-SIM-D	_	m
	32 input		1,000	P2RV-100C-SIM-D	_	<b>H</b>
	points		2,000	P2RV-200C-SIM-D	_	Q
			3,000	P2RV-300C-SIM-D	- Siemens PLCs with	7
			5,000	P2RV-500C-SIM-D	32-point connectors (1:4)	Ċ
			500	P2RV-050C-SIM-E	For inputs: 6ES7 421-1BL-0AA0 For outputs: 6ES7 422-1BL-0AA0	Common Accessories
	32 output		1,000	P2RV-100C-SIM-E		Se
	points	L→ 4 300 →	2,000	P2RV-200C-SIM-E	_	ő
			3,000	P2RV-300C-SIM-E	_	rie
			5,000	P2RV-500C-SIM-E		10

OMRON

#### PLC interface unit


# Ratings / characteristices

ratinge / onaraotoria		
Rated insulation voltage		30 VAC/DC *
Rated current		0.5 A/poles, 2 A/unit
Ambient operating tempe	rature	-40 to 55°C
Vibration resistance	Destruction	10 to 55 to 10 Hz, single amplitude 0.50 mm (double amplitude 1.0 mm)
VIDIALION TESISLANCE	Malfunction	10 to 55 to 10 Hz, single amplitude 0.50 mm (double amplitude 1.0 mm)
Shock resistance	Destruction	300 m/s <sup>2</sup>
SHOCK TESISLATICE	Malfunction	100 m/s <sup>2</sup>


\*DC voltage is limited to 30 V.

# Electrical schematic

#### P2RVC-8ST-I-D-1 (PNP)



#### P2RVC-8ST-I-5 (NPN)




\*1.Terminal numbers on G2RV-ST


# **Common Precautions**

Common Accessories

#### Output P2RVC-8ST-O-□-1 (PNP)




#### P2RVC-8ST-O-5 (NPN)



\*2.Terminal numbers on G2RV-ST/G3RV-ST

# Dimensions

(unit: mm)




#### (Except for PLC interface unit) **Common Accessories (order separately)**

# **Dimensions**


**Short Bars** PYDN-6.2ST-200

G2RV-ST



Pitch	No. of poles	L (Length)	Colors	Model *	Maximum carry current
6.2 mm	20	124	Red (R) Blue (S) Yellow (Y)	PYDN-6.2ST-200	32 A

Note: Use the Short Bars for crossover wiring within one Socket or between Sockets. \* Replace the box  $(\Box)$  in the model number with the code for the covering color.



#### Parts for DIN Track Mounting

Refer to your OMRON website for details on the PFP-D.


(unit: mm)

# **Safety Precautions**

#### **Precautions for Correct Use**

#### When mounting a short bar


· Intermediate pins can be bent by a tool and cut off for use.




• The short bar can be cut to as many poles as needed. Insert the tool from the plastic part side, and cut along the groove in the plastic part between the terminals. When cutting, take care not to break or deform the terminals.

However, since the metal on the cut surface will be exposed, human safety and insulation countermeasures between adjacent products must be ensured.

Such countermeasures include using insulating plate model P2RV-P3.1-ST or taking an equivalent insulation countermeasure.



- When cutting the short bar or its pins, do not touch the conductive part. If the conductive part is deformed, contact failure may result.
- When cutting the product, check that there is no person nearby and take care that a cut off piece does not fly off.



#### Using an isolation plate and short bar together


- Using two isolation plates makes it possible to configure the same 6.2 mm pitch used by slim relays and short bars.
- When using a short bar with two isolation plates, cutting the joining parts of the isolation plate make it possible to use the short bar without cutting the conductive part.
- The joining parts of the isolation plate can be easily cut using needle-nose pliers.
- Cut the joining parts for a single isolation plate at a time.
- Connecting two isolation plates with a short bar



Isolation plate



• After mounting to a DIN rail, check that the product is correctly held in place.



G2RV-ST

G3RV-ST

#### Removing the PLC interface

- To remove the PLC interface, place a finger at the location
  - indicated below and pull out the interface.



#### Mounting a separate plate

• Use a flat-blade screwdriver to tighten the center top screw and secure the plate. Loosen the screw to remove the plate from the DIN rail.





G3RV-ST

**Common Precautions** 

**Common Accessories** 

МЕМО

# **Terms and Conditions Agreement**

#### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

#### Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

#### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

#### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

#### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

#### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

#### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

#### Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

**OMRON Corporation** Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

#### **Regional Headquarters**

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2022-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM\_2\_9 Cat. No. J265-E1-11 0525 (0922)