OMRON

Solid-state Timer **H3Y Series**

Miniature Timer Compatible with the MY Relay

- The Push-In Plus Terminal Block Socket-compatible H3Y--B/H3YN--B Timers in a black design join the Single-mode H3Y and Multi-mode H3YN.
- The H3Y-----B and H3YN-----B are UL listed when they are used together with Push-In Plus Terminal Block Sockets.
- Large transparent time setting knob facilitates time setting.


A flat-blade and Phillips screwdriver can also be used for time setting.

- · Conforms to EMC standards.
- Conforms to EN 61812-1 and approved by UL and CSA.

Model Number Structure



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.



H3Y Series Model Number Structure

H3Y- [(1	$\frac{1}{1}$ - $\frac{1}{(2)}$ - $\frac{1}{(3)}$					
(1) Outpu	ıt		(2) Termi	nal Type	(3) Body	Color and Terminal Arrangement
Symbol	Meaning		Symbol	Meaning	Symbol	Meaning
2	DPDT		None	Plug-in terminals	None	Beige with output terminals on top and power supply terminals on bottom
4	4PDT		0	PCB terminals	 В	Black with power supply terminals on top and output terminals on bottom
Ex) H3Y	7-2 100 to 120VAC).5S	Rated	time		

Note: Specify both the model number, supply voltage, and rated time when ordering.

H3YN - \square \square \square \square \square - \square (4)

(1) Output		(2) Time	(2) Time Range		(3) Contact Type	
Symbol	Meaning	Symbol	Meaning	Symbol	Meaning	
2	DPDT	None	Short-time range	None	Single contact	
4	4PDT	0	Long-time range	Z	Twin contacts	

Symbol Meaning None Beige with output terminals on top and power supply terminals on bottom В Black with power supply terminals on top and output terminals on bottom

Ex) H3YN-2 100 to 120VAC Supply Voltage

Note: Specify both the model number, supply voltage when ordering.

Solid-state Timer

Miniature Timer Compatible with the MY Relay

• Semi-multi power supply voltage.

• Large transparent time setting knob facilitates time setting.

A flat-blade and Phillips screwdriver can also be used for time setting.

- Pin configuration compatible with MY Power Relay.
- LED indication for power and output statuses.
- Conforms to EMC standards.
- Conforms to EN 61812-1 and approved by UL and CSA.

Refer to Safety Precautions on page 37.

Ordering Information

Operation/resetting		Time ranges		Mounting	
system	Time-limit contact		Supply voltage	Surface/DIN-track mounting (with socket)	Surface mounting (with PCB terminals)
Time-limit operation/	DPDT (for power switching)	0.04 s to 3 h	24, 100 to 120, 200 to 230, 240 VAC (50/60 Hz);	НЗҮ-2	H3Y-2-0
self-resetting	4PDT		12, 24, 48, 125, 100 to 110 VDC	H3Y-4 *	H3Y-4-0 *

Note: Sockets and Hold-down Clips are not included with the H3Y. They must be ordered separately. * Use the H3Y-4 or H3Y-4-0 Series when switching micro loads.

Accessories (Order Separately) Adapter, Mounting Plate, Hold-down Clips,

I ei	mi	nai	CO/	/ers	

Name/specification			
Flush mounting adapter			
For 1 Socket	PYP-1		
For 18 Sockets	PYP-18		
For PYFZ- and PYF A	Y92H-3		
For PY and PYF M	Y92H-4		
For PYFZ-08	PYCZ-C08 (2 pcs/set)		
For PYFZ-14	PYCZ-C14 (1 pcs/set)		
	apter For 1 Socket For 18 Sockets For PYFZ- and PYFA For PYC and PYFM For PYFZ-08		

Note: For details, refer to *Precautions for H3Y-series Timers* on page 31.

Socket

Timer		Square Sockets			
Contact	Model	Pin	Connection	Terminal	Model
	H3Y-2		Front Connecting	DIN track mounting	PYFZ-08
DPDT		8-pin		DIN track mounting (Finger Protection Structure)	PYFZ-08-E
				Screw mounting	PYF08M
			Back	Solder terminal	PY08
			Connecting	PCB terminal	PY08-02
	H3Y-4 14-pin			DIN track mounting	PYFZ-14
4PDT		4-pin	DIN track mounting (Finger Protection Structure)	PYFZ-14-E	
			Back	Solder terminal	PY14
			Connecting	PCB terminal	PY14-02

Note: 1. Cannot be used with the H3Y- \Box -0 (PCB terminals).

 The PYFZ-D-E and PYFDA-E have a finger-protection structure. Round crimp terminals cannot be used. Use forked crimp terminals.

crimp terminals. 3. For details, refer to *Precautions for H3Y-series Timers* on page 31.

For the most recent information on models that have been certified for

Sec

H3

sec

(E 91 () LR ()

sec

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

H3Y

Specifications

Time Ranges

Rated time	Time setting range	Rated time	Time setting range
0.5 s	0.04 to 0.5 s	3 min	0.1 to 3 min
1 s	0.1 to 1 s	5 min	0.2 to 5 min
5 s	0.2 to 5 s	10 min	0.5 to 10 min
10 s	0.5 to 10 s	30 min	1 to 30 min
30 s	1.0 to 30 s	60 min	2 to 60 min
60 s	2.0 to 60 s	3 h	0.1 to 3 h
120 s	5.0 to 120 s		

Ratings

Item	H3Y-2(-0)/H3Y-4(-0)			
Rated supply voltage *6, *7	100 to 120 (50/60 Hz), 200 to 230 VAC (50/60 Hz), 24 VAC (50/60 Hz) * 1 12, 24, 48, 125, 100 to 110 VDC * 2, * 3			
Operating voltage rangeAll rated voltages except 12 VDC: 85% to 110% of rated supply voltage 12 VDC: 90% to 110% of rated supply voltage *4				
Reset voltage	10% min. of rated supply voltage *5			
Power consumption	100 to 120 VAC: 1.5 VA (at 120 VAC) 200 to 230 VAC: 1.8 VA (at 230 VAC) 24 VAC: 1.5 VA (at 24 VAC) 12 VDC: 0.9 W (at 12 VDC) 24 VDC: 0.9 W (at 24 VDC) 48 VDC: 1.0 W (at 48 VDC) 100 to 110 VDC: 1.3 W (at 110 VDC) 125 VDC: 1.3 W (at 125 VDC)			
Control outputs	H3Y-2(-0): 5 A at 250 VAC, resistive load ($\cos\phi = 1$) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag H3Y-4(-0): 2 A ct 250 VAC, resistive load ($acct = 1$)			
	3 A at 250 VAC, resistive load $(\cos\phi = 1)$ The minimum applicable load is 1 mA at 1 VDC (P reference value). Contact materials: Au-clad + Ag-alloy			
Ambient operating temperature	-10°C to 50°C (with no icing)			
Storage temperature	-25°C to 65°C			
Ambient operating humidity	35% to 85%			

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.

*2. With DC ratings, single-phase full-wave rectified power sources may be used.

***3.** Only the H3Y-2 and H3Y-2-0 Series include 12 VDC models.

*4. Use the Timer within 90% to 110% of the rated supply voltage (95% to 110% for 12 VDC) when using it continuously under an ambient operating temperature of 50°C.

*5. Set the reset voltage as follows to ensure proper resetting.

100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*6. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor.

*7. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Accuracy of operating time	±1% FS max. (0.5 s range: ±1%±10 ms max.) * 1				
Setting error	±10%±50 ms FS max.				
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)				
Influence of voltage	±2% FS max. * 1				
Influence of temperature	±2% FS max. * 1				
Insulation resistance	100 MΩ min. (at 500 VDC)				
Dielectric strength 2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) \$2 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) \$2 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts)					
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC				
Noise immunity	\pm 1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μ s, 1-ns rise)				
Static immunity	Destruction: 8 kV Malfunction: 4 kV				
Vibration resistance	Destruction: 10 to 55 Hz, 0.75-mm single amplitude Malfunction: 10 to 55 Hz, 0.5-mm single amplitude				
Shock resistance	Destruction: 1,000 m/s ² (approx. 100G) * 3 Malfunction: 100 m/s ² (approx. 10G)				
Life expectancy	Mechanical:10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: H3Y-2: 500,000 operations min. (5 A at 250 VAC, resistive load at 1800 operations/h) H3Y-4: 200,000 operations min. (3 A at 250 VAC, resistive load at 1800 operations/h) * 4				
Enclosure rating	IP40				
Weight	Approx. 50 g				
EMC	(EMI) EN 61812-1 Emission Enclosure: EN 55011 Group 1 class A Emission AC Mains: EN 55011 Group 1 class A (EMS) EN 61812-1 Immunity ESD: IEC 61000-4-2 Immunity RF-interference: IEC 61000-4-3 Immunity Surge: IEC 61000-4-5 Immunity Conducted Disturbance: IEC 61000-4-6 Immunity Voltage Dip/Interruption: IEC 61000-4-11				
Approved standards	UL 508, CSA C22.2 No. 14, Lloyds, CCC: GB/T 14048.5 * 6 Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3Y-2/-2-0, 2.5 kV/1 for H3Y-4/-4-0) * 5				

***1.** Add ±10 mS to the above value for the 0.5-S range model. ***2.** Terminal screw sections are excluded.

***3.** The destructive shock resistance test was performed on the Timer. ***4.** Check the electrical life curve.


***5.** Overvoltage category II. ***6.** CCC certification requirements

Model	H3Y-2 (-0)	H3Y-4 (-0)			
Recommended fuse	RT14-20/6A (380 VAC 6 A), manufactured by DELIXI	RT14-20/4A (380 VAC 4 A), manufactured by DELIXI			
Rated operating voltage Ue Rated operating current le	AC-15: Ue: 250 VAC, le: 3 A AC-13: Ue: 250 VAC, le: 5 A DC-13: Ue: 30 VDC, le: 0.5 A	AC-15: Ue: 250 VAC, Ie: 2 A AC-13: Ue: 250 VAC, Ie: 3 A DC-13: Ue: 30 VDC, Ie: 0.5 A			
Rated insulation voltage	250 V				
Rated impulse withstand voltage (altitude: 2,000 m max.)	2.5 kV (at 240 VAC)				
Conditional short-circuit current	1000 A				

H₃Y **Engineering Data**

H3Y-2, H3Y-2-0 H3Y-2, H3Y-2-0 250 VAC, $\cos\phi = 1$ 24 VDC, $\cos\phi = 1$ 250 VAC, $\cos\phi = 0.4$ 24 VDC, L/R = 7 ms Switching operations (×10⁴) Switching operations (×10⁴) 500 500 100 100 50 50 20 20 0 0 3 6 4 2 Load current (A) Load current (A)

Reference: A maximum current of 0.6 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 1 mA at 5 VDC (P reference value).



Reference: A maximum current of 0.5 A can be switched at 125 VDC ($\cos \phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 1 mA at 1 VDC (P reference value).

Connect the DC power supply to


terminals 13 and 14 according

to the polarity marks.

Connections

Connections


H3Y-2, H3Y-2-0






(DIN notation)

H3Y-4, H3Y-4-0




Connect the DC power supply to terminals 13 and 14 according to the polarity marks.




Operation

Timing Chart



Nomenclature




H3Y


Dimensions

Timers


H3Y-2











(Unit: mm)

Solid-state Timer

Miniature Timer with Multiple Time Ranges and Multiple Operating Modes

- Minimizes stock.
- Pin configuration compatible with MY Power Relay.
- Standard multiple operating modes and multiple time ranges.
- Conforms to EN 61812-1 and IEC 60664-1 for Low Voltage, and EMC Directives



Refer to *Safety Precautions* on page 37.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

H3YN

Ordering Information

List of Models

Supply voltage	Time-limit contact	Short-time range model (0.1 s to 10 min)	Long-time range model (0.1 min to 10 h)
24, 100 to 120, 200 to 230 VAC;	DPDT	H3YN-2	H3YN-21
12, 24, 48, 100 to 110, 125 VDC	4PDT	H3YN-4 * 1	H3YN-41 * 1
24 VDC	4PDT (Twin contacts)	H3YN-4-Z *1, *2	H3YN-41-Z *1, *2

Note: Sockets and Hold-down Clips are not included with the H3YN. They must be ordered separately.

*1. Use the H3YN-4 or H3YN-41 Series when switching micro loads, and use the H3YN-4-Z or H3YN-41-Z Series when switching even smaller loads. *2. Only models with 24 VDC power supply are available.

Accessories (Order Separately) Adapter, Mounting Plate, Hold-down Clips, Terminal covers

Name/specification	Model		
Flush mounting ada	Y92F-78		
Mounting Plate	For 1 Socket	PYP-1	
for Socket	For 18 Sockets	PYP-18	
Hold-down Clips	For PYFZ- and PYF A	Ү92Н-3	
	For PY and PYF M	Y92H-4	
Terminal covers	For PYFZ-08	PYCZ-C08 (2 pcs/set)	
reminal covers	For PYFZ-14	PYCZ-C14 (1 pcs/set)	

Note: For details, refer to *Precautions for H3Y-series Timers* on page 31.

Socket

Timer			Square Sockets			
Contact	Model	Pin	Connection	Terminal	Model	
				DIN track mounting	PYFZ-08	
DPDT	H3YN-2	8-pin	Front Connecting	DIN track mounting (Finger Protection Structure)	PYFZ-08-E	
	Screw mounting	Screw mounting	PYF08M			
			Back	Solder terminal	PY08	
			Connecting	PCB terminal	PY08-02	
				DIN track mounting	PYFZ-14	
4PDT	H3YN-4 14-pin	DIN track mounting (Finger Protection Structure)	PYFZ-14-E			
			Back	Solder terminal	PY14	
	Connecting	PCB terminal	PY14-02			

Note: 1. Cannot be used with the H3Y---0 (PCB terminals).
2. The PYFZ--E and PYF-A-E have a finger-protection structure. Round crimp terminals cannot be used. Use forked crimp terminals.

3. For details, refer to *Precautions for H3Y-series Timers* on page 31.

H₃YN

Specifications

Ratings

Item	H	3YN-2/-4/-4-Z		H3YN-21/-41/-41-Z		
Time ranges	0.1 s to 10 min (1 s selectable)			0.1 min to 10 h (1 min, 10 min, 1 h, or 10 h max selectable)		
Rated supply voltage *5, *6		24, 100 to 120, 200 to 230 VAC (50/60 Hz) * 1 12, 24, 48, 100 to 110, 125 VDC * 2				
Pin type	Plug-in					
Operating mode	ON-delay, interval,	flicker OFF sta	rt, or flicker ON	start (selectable with DIP switch)		
Operating voltage range	85% to 110% of ra	ted supply volta	ge (12 VDC: 90	0% to 110% of rated supply voltage) * 3		
Reset voltage	10% min. of rated	supply voltage	k 4			
	100 to 120 VAC: 200 to 230 VAC: 24 VAC:	Relay ON: Relay OFF:	Approx. 1 VA Approx. 2.2 V Approx. 1.5 V	A (1.6 W) at 120 VAC, 60 Hz (0.6 W) at 120 VAC, 60 Hz A (1.8 W) at 230 VAC, 60 Hz A (1.1 W) at 230 VAC, 60 Hz A (1.1 W) at 230 VAC, 60 Hz		
Power consumption	12 VDC:	Relay ON: Approx. 1.8 VA (1.4 W) at 24 VAC, 60 Hz Relay OFF: Approx. 0.3 VA (0.2 W) at 24 VAC, 60 Hz Relay ON: Approx. 1.1 W at 12 VDC Relay OFF: Approx. 0.1 W at 12 VDC				
	24 VDC: 48 VDC:	Relay ON:	Approx. 1.1 W Approx. 0.1 W Approx. 1.2 W Approx. 0.3 W	/ at 24 VDC / at 48 VDC		
	100 to 110 VDC: 125 VDC:	Relay ON:	Approx. 0.3 W Approx. 1.6 W Approx. 0.4 W Approx. 1.6 W	' at 110 VDC ' at 110 VDC		
Control outputs	Relay OFF: Approx. 0.4 W at 125 VDC DPDT: 5 A at 250 VAC, resistive load (cos\$\u03c6 = 1) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag 4PDT: 3 A at 250 VAC, resistive load (cos\$\u03c6 = 1) H3YN-4/-41 series: The minimum applicable load is 1 mA at 1 VDC (P reference value). H3YN-4/-2/-41-Z series: The minimum applicable load is 1 mA at 1 VDC (P reference value).					
A	Contact materials:	0	шоу			
Ambient operating temperature	-10°C to 50°C (with	n no icing)				
Storage temperature	-25°C to 65°C					
Ambient operating humidity	35% to 85%					

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.
*2. Single-phase, full-wave-rectified power supplies can be used.
*3. When using the H3YN continuously in any place where the ambient temperature is in a range of 45°C to 50°C, supply 90% to 110% of the provide the provided and rated supply voltages (supply 95% to 110% with 12 VDC type).

*4. Set the reset voltage as follows to ensure proper resetting. 100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*5. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *6. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Item	H3YN-2/-21/-4/-41			
Accuracy of operating time	±1% FS max. (1 s range: ±1%±10 ms max.)			
Setting error	±10%±50 ms FS max.			
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)			
Influence of voltage	±2% FS max.			
Influence of temperature	±2% FS max.			
Insulation resistance	100 MΩ min. (at 500 VDC)			
Dielectric strength	2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) * 1 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts)			
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitude for 1 h each in 3 directionsMalfunction:10 to 55 Hz, 0.5-mm single amplitude for 10 min each in 3 directions			
Shock resistance	Destruction: 1,000 m/s ² * 2 Malfunction: 100 m/s ²			
Life expectancy	Mechanical: 10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: DPDT: 500,000 operations min. (5 A at 250 VAC, resistive load at 1,800 operations/h) 4PDT: 200,000 operations min. (H3YN-4-Z/-41-Z: 100,000 operations min.) (3 A at 250 VAC, resistive load at 1,800 operations/h) * 3			
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC			
Noise immunity	±1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 µs, 1-ns rise)			
Static immunity	Destruction: 8 kV Malfunction: 4 kV			
Degree of protection	IP40			
Weight	Approx. 50 g			
EMC	(EMI) EN 61812-1 Emission Enclosure: EN 55011 Group 1 class A Emission AC Mains: EN 5CC: GB/T 14048.5 5011 Group 1 class A (EMS) EN 61812-1 Immunity ESD: IEC 61000-4-2 Immunity Burst: IEC 61000-4-3 Immunity Surge: IEC 61000-4-5 Immunity Voltage Dip/Interruption: IEC 61000-4-6			
Approved standards	UL 508, CSA C22.2 No. 14, Lloyds, CCC: GB/T 14048.5 * 5 Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3YN-2/-21, 2.5 kV/1 for H3YN-4/-41, H3YN-4-Z/-41-Z) * 4			


*1. Terminal screw sections are excluded.
*2. The destructive shock resistance test was performed on the Timer.
*3. Refer to the *Life-test Curve*.


***4.** Overvoltage category II. ***5.** CCC certification requirements

Model	H3YN-2/-21	H3YN-4/-41	
Recommended fuse	RT14-20/6A (380 VAC 6 A), manufactured by DELIXI	RT14-20/4A (380 VAC 4 A), manufactured by DELIXI	
Rated operating voltage Ue Rated operating current le	AC-13: Ue: 250 VAC, le: 5 A	AC-15: Ue: 250 VAC, le: 2 A AC-13: Ue: 250 VAC, le: 3 A DC-13: Ue: 30 VDC, le: 0.5 A	
Rated insulation voltage	250 V		
Rated impulse withstand voltage (altitude: 2,000 m max.)	2.5 kV (at 240 VAC)		
Conditional short-circuit current	1000 A		

Life-test Curve (Reference Value)


H3YN-2/-21







The minimum applicable load is 1 mA at 5 VDC (P reference value)















Load current (A)

 $\begin{array}{rl} \mbox{Reference:} & A \mbox{maximum current of } 0.5 \mbox{ A can be switched at } 125 \mbox{VDC } (\cos \phi = 1). \\ \mbox{Maximum current of } 0.2 \mbox{ A can be switched if } L/R \mbox{ is } 7 \mbox{ ms. In both cases, a } \\ \mbox{life of } 100,000 \mbox{ operations can be expected.} \\ \mbox{The minimum applicable load is } 0.1 \mbox{ mA at } 1 \mbox{ VDC } (P \mbox{ reference value}) \end{array}$

Connections

Connection

H3YN-2/-21



(Bottom View)

Pulse Operation

A pulse output for a certain period can be obtained with a random external input signal. Use the H3YN in interval mode as shown in the following timing charts.


12

5

Ŷ

H3YN-2/-21

H3YN-4/-41 H3YN-4-Z/-41-Z



Power (9-14) External short circuit (5-13) External input (9-13) Time limit contact NO (12-8) Time limit contact NC (12-4) Run/Power indicator (PW) Output indicator (UP)

- t	Rt	t Rt	t
		 	I
50 ms min.			

Note: t: Set time Rt: Reset time

H3YN-4/-41 H3YN-4-Z/-41-Z

> 10 1

Timer circuit

ᠮ᠊᠆᠇

VP PW

(Bottom View)

5

13

(~)

8

12

14

(+) (~)

8 6 10 12 11 Time 14 m circuit (+) (~) LI€ LI€ External input - \odot (++)

Power (9-14)
External short circuit (5-13)
External input (9-13)
Time limit contact NO (10-6, 11-7, 12-8)
Time limit contact NC (10-2, 11-3, 12-4)
Run/Power indicator (PW) Output indicator (UP)


 t	Rt	- t	 Rt	t	
50 ms min.					


Note: t: Set time Reset time Rt:

Caution -Be careful when connecting wires.

Mode	Terminals
Pulse operation	Power supply between 9 and 14 Short-circuit between 5 and 13 Input signal between 9 and 13
Operating mode; interval and all other modes	Power supply between 13 and 14

DIN Indication





H3YN Nomenclature

Output Indicator (Orange) (Lit: Output ON)

Main Dial



Run/Power Indicator (Green) (Lit: Power ON)


Set the desired time according to time range selectable by DIP switch.

Dimensions

Timers


(Unit: mm)

H3YN-2/-21 Front Mounting



H3YN-4/-41 Front Mounting H3YN-4-Z/-41-Z





Operation

DIP Switch Settings

The 1-s range and ON-delay mode for H3YN-2/-4/-4-Z, the 1-min range and ON-delay mode for H3YN-21/-41/-41-Z are factory-set before shipping.

Time Ranges

Model	Time range	Time setting range	Setting	Factory-set
	1 s	0.1 to 1 s		Yes
H3YN-2, H3YN-4	10 s	1 to 10 s		No
H3YN-4-Z	1 min	0.1 to 1 min		No
	10 min	1 to 10 min		No
	1 min	0.1 to 1 min		Yes
H3YN-21,	10 min	1 to 10 min		No
H3YN-41 H3YN-41-Z	1 h	0.1 to 1 h		No
	10 h	1 to 10 h		No

Note: The top two DIP switch pins are used to select the time ranges.

Operating Modes

Operating mode	Setting	Factory-set
ON-delay		Yes
Interval		No
Flicker OFF-start		No
Flicker ON-start		No

 PW
 Imin 10min

 Imin 10min
 Imin 10min

 Imin 1

Note: The bottom two DIP switch pins are used to select the operating mode.

H3YN

Operating mode	Timing chart						
Operating mode	H3YN-2/-21	H3YN-4/-41					
ON-delay Power	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)					
Interval Power	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator (UP)	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)					
Flicker OFF-start	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator (UP)	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)					
Flicker ON-start	Power (13-14) Time limit contact NC (9-1, 12-4) Time limit contact NO (9-5, 12-8) Run/Power indicator (PW) Output indicator (UP)	Power (13-14) Time limit contact NC (9-1, 10-2, 11-3, 12-4) Time limit contact NO (9-5, 10-6, 11-7, 12-8) Run/Power indicator (PW) Output indicator (UP)					

Note: t: Set time Rt: Reset time

Solid-state Timer

Miniature Timer Compatible with the MY Relay

- UL listed when used with a Push-In Plus Terminal Block Socket. ***** Conforms to CSA, CE Marking, CCC and LR.
- Black design with power supply terminals on top and contact output terminals on bottom.
- Large transparent time setting knob facilitates time setting. A flat-blade and Phillips screwdriver can also be used for time setting.
- Semi-multi power supply voltage.

*When used in combination with a Push-In Plus Terminal Block Socket (PYF-□-PU-L).



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Refer to *Safety Precautions* on page 37.

Ordering Information

Operation/resetting system	Time-limit contact	Time ranges	Supply voltage	Mounting Surface/DIN-track mounting (with socket)
Time-limit operation/ self-resetting	DPDT (for power switching)	0.04 s to 3 h	100 to 120, 200 to 230 VAC (50/60 Hz);	НЗҮ-2-В
	4PDT		12, 24, 48, 100 to 110 VDC	H3Y-4-B *

Note: Sockets and Hold-down Clips are not included with the H3Y-B. They must be ordered separately.

* Use the H3Y-4-B Series when switching micro loads.

Accessories (Order Separately)

Hold-down Clips

Name/specificatio	Model	
Hold-down Clips	For PYFPU-L	Y92H-3

Note: For details, refer to Precautions for H3Y-series Timers on page 31.

Socket

Timer		Square Sockets				
Contact	Model	Pin	Connection	Terminal	Model	Terminal Type
DPDT	H3Y-2-B	8-pin	Front Connecting	DIN track mounting	PYF-08-PU-L	Push-In Plus Terminal Block
4PDT	H3Y-4-B	14-pin	Front Connecting	DIN track mounting	PYF-14-PU-L	Push-In Plus Terminal Block

Note: 1. Cannot be used with the H3Y- \Box -0 (PCB terminals).

2. For details, refer to Precautions for H3Y-series Timers on page 31.

H3Y-□-B

Specifications

Time Ranges

Rated time	Time setting range	Rated time	Time setting range
0.5 s	0.04 to 0.5 s	3 min	0.1 to 3 min
1 s	0.1 to 1 s	5 min	0.2 to 5 min
5 s	0.2 to 5 s	10 min	0.5 to 10 min
10 s	0.5 to 10 s	30 min	1 to 30 min
30 s	1.0 to 30 s	60 min	2 to 60 min
60 s	2.0 to 60 s	3 h	0.1 to 3 h
120 s	5.0 to 120 s		

Ratings

Item	H3Y-2-B/H3Y-4-B		
Rated supply voltage *6, *7	100 to 120 (50/60 Hz), 200 to 230 VAC (50/60 Hz), 24 VAC (50/60 Hz) * 1 12, 24, 48, 125, 100 to 110 VDC * 2, * 3		
Operating voltage range	All rated voltages except 12 VDC: 85% to 110% of rated supply voltage 12 VDC: 90% to 110% of rated supply voltage *4		
Reset voltage	10% min. of rated supply voltage *5		
Power consumption	100 to 120 VAC: 1.5 VA (at 120 VAC) 200 to 230 VAC: 1.8 VA (at 230 VAC) 24 VAC: 1.5 VA (at 24 VAC) 12 VDC: 0.9 W (at 12 VDC) 24 VDC: 0.9 W (at 24 VDC) 48 VDC: 1.0 W (at 48 VDC) 100 to 110 VDC: 1.3 W (at 110 VDC) 125 VDC: 1.3 W (at 125 VDC)		
Control outputs	H3Y-2-B: 5 A at 250 VAC, resistive load ($\cos\phi = 1$) The minimum applicable load is 1 mA at 5 VDC (P reference value). Contact materials: Ag		
	H3Y-4-B: 3 A at 250 VAC, resistive load ($\cos\phi = 1$) The minimum applicable load is 1 mA at 1 VDC (P reference value). Contact materials: Au-clad + Ag-alloy		
Ambient operating temperature	-10°C to 55°C (with no icing)		
Storage temperature	-25°C to 65°C		
Ambient operating humidity	35% to 85%		

*1. Do not use the output from an inverter as the power supply. Refer to Safety Precautions for All Timers for details on your OMRON website.

*2. With DC ratings, single-phase full-wave rectified power sources may be used.

***3.** Only the H3Y-2-B Series include 12 VDC models.

*4. Use the Timer within 90% to 110% of the rated supply voltage (95% to 110% for 12 VDC) when using it continuously under an ambient operating temperature of 50°C.

*5. Set the reset voltage as follows to ensure proper resetting.

100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*6. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *7. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics

Accuracy of operating time	±1% FS max. (0.5 s range: ±1%±10 ms max.) * 1		
Setting error	±10%±50 ms FS max.		
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)		
Influence of voltage	±2% FS max. * 1		
Influence of temperature	±2% FS max. * 1		
Insulation resistance	100 MΩ min. (at 500 VDC)		
Dielectric strength	 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) *2 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) *2 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) *2 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts) 		
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC		
Noise immunity	±1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μs, 1-ns rise)		
Static immunity	Destruction: 8 kV Malfunction: 4 kV		
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitudeMalfunction:10 to 55 Hz, 0.5-mm single amplitude		
Shock resistance	Destruction:1,000 m/s² (approx. 100G) *3Malfunction:100 m/s² (approx. 10G)		
Life expectancy	Mechanical:10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: H3Y-2-B: 500,000 operations min. (5 A at 250 VAC, resistive load at 1800 operations/h) H3Y-4-B: 200,000 operations min. (3 A at 250 VAC, resistive load at 1800 operations/h) * 4		
Enclosure rating	IP40		
Weight	Approx. 50 g		
EMC	(EMI)EN 61812-1Emission Enclosure:EN 55011 Group 1 class AEmission AC Mains:EN 55011 Group 1 class A(EMS)EN 61812-1Immunity ESD:IEC 61000-4-2Immunity RF-interference:IEC 61000-4-3Immunity Burst:IEC 61000-4-4Immunity Surge:IEC 61000-4-5Immunity Conducted Disturbance:IEC 61000-4-6Immunity Voltage Dip/Interruption:IEC 61000-4-11		
Approved standards	UL 508/CSA C22.2 No.14 * 5, CSA C22.2 No.14, Lloyds, CCC: GB/T 14048.5 * 7 Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3Y-2-B * 6, 2.5 kV/1 for H3Y-4-B * 6)		

***1.** Add ±10 mS to the above value for the 0.5-S range model. ***2.** Terminal screw sections are excluded.

***3.** The destructive shock resistance test was performed on the Timer.

*4. Check the electrical life curve.


Solution of the electrical life curve.
*5. cULus listing applies when the OMRON PYF-PU-L is used. cURus recognition applies when any other socket is used.
*6. Overvoltage category II.

*7. CCC certification requirements


Model	H3Y-2-B	H3Y-4-B	
Recommended fuse	RT14-20/6A (380 VAC 6 A), manufactured by DELIXI	RT14-20/4A (380 VAC 4 A), manufactured by DELIXI	
Rated operating voltage Ue Rated operating current le	AC-15: Ue: 250 VAC, le: 3 A AC-13: Ue: 250 VAC, le: 5 A DC-13: Ue: 30 VDC, le: 0.5 A	AC-15: Ue: 250 VAC, Ie: 2 A AC-13: Ue: 250 VAC, Ie: 3 A DC-13: Ue: 30 VDC, Ie: 0.5 A	
Rated insulation voltage	250 V	·	
Rated impulse withstand voltage (altitude: 2,000 m max.)	2.5 kV (at 240 VAC)		
Conditional short-circuit current	1000 A		

H3Y-□-B

Engineering Data



Reference: A maximum current of 0.6 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 5 VDC (P reference value).




Reference: A maximum current of 0.5 A can be switched at 125 VDC ($\cos\phi = 1$). Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected.The minimum applicable load is 1 mA at 1 VDC (P reference value).


Connections

Connections

H3Y-2-B




(Bottom View)



H3Y-4-B


Connect the DC power supply to terminals A1(13) and A2(14) according to the polarity marks.




Connect the DC power supply to terminals A1(13) and A2(14) according to the polarity marks.

Operation

Timing Chart




Nomenclature



Н3Ү-□-В

Dimensions

Timers



Solid-state Timer

Miniature Timer with Multiple Time Ranges and Multiple Operating Modes

- UL listed when used with a Push-In Plus Terminal Block Socket. * Conforms to CSA, CE Marking, LR, and CCC.
- Black design with power supply terminals on top and contact output terminals on bottom.
- Standard multiple operating modes and multiple time ranges.
- Pin configuration compatible with MY Power Relay.
- Minimizes stock.
- *When used in combination with a Push-In Plus Terminal Block Socket (PYF---PU-L).

Refer to Safety Precautions on page 38.

Ordering Information

List of Models

Supply voltage	Time-limit contact	Short-time range model (0.1 s to 10 min)	Long-time range model (0.1 min to 10 h)
24, 100 to 120, 200 to 230 VAC;	DPDT	H3YN-2-B	H3YN-21-B
12, 24, 48, 100 to 110, 125 VDC	4PDT	H3YN-4-B * 1	H3YN-41-B * 1
24 VDC	4PDT (Twin contacts)	H3YN-4-Z-B * 1, * 2	H3YN-41-Z-B * 1, * 2

Note: 1. Sockets and Hold-down Clips are not included with the H3YN-B. They must be ordered separately.

*1. Use the H3YN-4-B or H3YN-41-B Series when switching micro loads, and use the H3YN-4-Z-B or H3YN-41-Z-B Series when switching even smaller loads.

*2. Only models with 24 VDC power supply are available.

Accessories (Order Separately)

Hold-down Clips

Name/specificatio	Model	
Hold-down Clips For PYFPU-L		Y92H-3

Note: For details, refer to Precautions for H3Y-series Timers on page 31.

Socket

Timer		Square Sockets				
Contact	Model	Pin	Connection	Terminal	Model	Terminal Type
DPDT	H3YN-2□-B	8-pin	Front Connecting	DIN track mounting	PYF-08-PU-L	Push-In Plus Terminal Block
4PDT	H3YN-4□-B	14-pin	Front Connecting	DIN track mounting	PYF-14-PU-L	Push-In Plus Terminal Block

2. For details, refer to Precautions for H3Y-series Timers on page 31.





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

H3YN-D-B

Specifications

Ratings

Item	H3YN	I-2-B/-4-B/-4-Z-	·B	H3YN-21-B/-41-B/-41-Z-B
Time ranges	0.1 s to 10 min (1 s selectable)	s, 10 s, 1 min, c	r 10 min max.	0.1 min to 10 h (1 min, 10 min, 1 h, or 10 h max selectable)
Rated supply voltage * 5, * 6		24, 100 to 120, 200 to 230 VAC (50/60 Hz) * 1 12, 24, 48, 100 to 110, 125 VDC * 2		
Pin type	Plug-in			
Operating mode	ON-delay, interval,	flicker OFF sta	rt, or flicker ON	start (selectable with DIP switch)
Operating voltage range	85% to 110% of ra	ted supply volta	ige (12 VDC: 90	0% to 110% of rated supply voltage) * 3
Reset voltage	10% min. of rated s	supply voltage	* 4	
	100 to 120 VAC: 200 to 230 VAC:	Relay ON:	Approx. 1 VA Approx. 2.2 V	A (1.6 W) at 120 VAC, 60 Hz (0.6 W) at 120 VAC, 60 Hz A (1.8 W) at 230 VAC, 60 Hz A (1.1 W) at 230 VAC, 60 Hz
	24 VAC:	Relay ON: Relay OFF:	Approx. 1.8 V Approx. 0.3 V	A (1.4 W) at 24 VAC, 60 Hz A (0.2 W) at 24 VAC, 60 Hz
ower consumption	12 VDC: 24 VDC:	Relay ON:	Approx. 1.1 W Approx. 0.1 W Approx. 1.1 W	/ at 12 VDC / at 24 VDC
	48 VDC:	Relay ON: Relay OFF:	Approx. 0.1 W Approx. 1.2 W Approx. 0.3 W	/ at 48 VDC / at 48 VDC
	100 to 110 VDC:	Relay ON: Relay OFF:	Approx. 1.6 W Approx. 0.4 W	
	125 VDC:	Relay ON: Relay OFF:	Approx. 1.6 W Approx. 0.4 W	
	DPDT: 5 A at 250 VAC, re The minimum appl Contact materials:	icable load is 1		P reference value).
Control outputs 4PDT: 3 A at 250 VAC, resistive load (cos\$\u03c6 = 1) H3YN-4-B/-41-B series: The minimum applicable load is 1 mA at 1 VD0 H3YN-4-B/-41-Z-B series: The minimum applicable load is 1 mA at 1 Contact materials: Au-clad + Ag-alloy				
Ambient operating temperature	-10°C to 55°C (with	n no icing)		
Storage temperature	-25°C to 65°C			
Ambient operating humidity	35% to 85%			

***1.** Do not use the output from an inverter as the power supply. Refer to *Safety Precautions for All Timers* for details on your OMRON website. ***2.** Single-phase, full-wave-rectified power supplies can be used.

*3. When using the H3YN-B continuously in any place where the ambient temperature is in a range of 45°C to 50°C, supply 90% to 110% of the rated supply voltages (supply 95% to 110% with 12 VDC type).

*4. Set the reset voltage as follows to ensure proper resetting. 100 to 120 VAC: 10 VAC max. 200 to 230 VAC: 20 VAC max.

100 to 110 VDC: 10 VDC max.

*5. Refer to Safety Precautions for All Timers on your OMRON website when combining the Timer with an AC 2-wire proximity sensor. *6. A diode to prevent reverse voltages is provided only on models with a DC power supply.

Characteristics


Item	H3YN-2-B/-21-B/-4-B/-41-B		
Accuracy of operating time	±1% FS max. (1 s range: ±1%±10 ms max.)		
Setting error	±10%±50 ms FS max.		
Reset time	Min. power-opening time: 0.1 s max. (including halfway reset)		
Influence of voltage	±2% FS max.		
Influence of temperature	±2% FS max.		
Insulation resistance	100 MΩ min. (at 500 VDC)		
Dielectric strength	2,000 VAC, 50/60 Hz for 1 min (between current-carrying terminals and exposed non-current-carrying metal parts) * 1 2,000 VAC, 50/60 Hz for 1 min (between operating power circuit and control output) 2,000 VAC, 50/60 Hz for 1 min (between different pole contacts; 2-pole model) 1,500 VAC, 50/60 Hz for 1 min (between different pole contacts; 4-pole model) 1,000 VAC, 50/60 Hz for 1 min (between non-continuous contacts)		
Vibration resistance	Destruction:10 to 55 Hz, 0.75-mm single amplitude for 1 h each in 3 directionsMalfunction:10 to 55 Hz, 0.5-mm single amplitude for 10 min each in 3 directions		
Shock resistance	Destruction: 1,000 m/s ² Malfunction: 100 m/s ²		
Life expectancy	Mechanical: 10,000,000 operations min. (under no load at 1,800 operations/h) Electrical: DPDT: 500,000 operations min. (5 A at 250 VAC, resistive load at 1,800 operations/h) 4PDT: 200,000 operations min. (H3YN-4-Z/-41-Z: 100,000 operations min.) (3 A at 250 VAC, resistive load at 1,800 operations/h) * 2		
Impulse withstand voltage	Between power terminals: 3 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC Between exposed non-current-carrying metal parts: 4.5 kV for 100 to 120 VAC, 200 to 230 VAC, 100 to 110 VDC, 125 VDC 1.5 kV for 12 VDC, 24 VDC, 48 VDC, 24 VAC		
Noise immunity	\pm 1.5 kV, square-wave noise by noise simulator (pulse width: 100 ns/1 μ s, 1-ns rise)		
Static immunity	Destruction: 8 kV Malfunction: 4 kV		
Degree of protection	IP40		
Weight	Approx. 50 g		
EMC	(EMI)EN 61812-1Emission Enclosure:EN 55011 Group 1 class AEmission AC Mains:EN 55011 Group 1 class A(EMS)EN 61812-1Immunity ESD:IEC 61000-4-2Immunity Burst:IEC 61000-4-3Immunity Surge:IEC 61000-4-4Immunity Surge:IEC 61000-4-5Immunity Voltage Dip/Interruption:IEC 61000-4-11		
Approved standards	cULus (or cURus): UL 508/CSA C22.2 No.14 * 3, CSA C22.2 No.14, Lloyds, CCC: GB/T 14048.5 * Conforms to EN 61812-1 and IEC 60664-1. (2.5 kV/2 for H3YN-2-B/-21-B * 4, 2.5 kV/1 for H3YN-4-B/-41-B, H3YN-4-Z-B/-41-Z-B * 4)		


*1. Terminal screw sections are excluded.
*2. Refer to the *Life-test Curve*.
*3. cULus listing applies when the OMRON PYF-□-PU-L is used. cURus recognition applies when any other socket is used.
*4. Overvoltage category II
*5. CCC certification requirements

Model	H3YN-2-B/21-B	H3YN-4-B/41-B	
Recommended fuse	RT14-20/6A (380 VAC 6 A), manufactured by DELIXI	RT14-20/4A (380 VAC 4 A), manufactured by DELIXI	
Rated operating voltage Ue Rated operating current le	AC-15: Ue: 250 VAC, le: 3 A AC-13: Ue: 250 VAC, le: 5 A DC-13: Ue: 30 VDC, le: 0.5 A	AC-15: Ue: 250 VAC, le: 2 A AC-13: Ue: 250 VAC, le: 3 A DC-13: Ue: 30 VDC, le: 0.5 A	
Rated insulation voltage	250 V		
Rated impulse withstand voltage (altitude: 2,000 m max.)	2.5 kV (at 240 VAC)		
Conditional short-circuit current	1000 A		

Life-test Curve (Reference Value)


H3YN-2-B/-21-B







The minimum applicable load is 1 mA at 5 VDC (P reference value)








The minimum applicable load is 1 mA at 1 VDC (P reference value)






Load current (A)

Reference: A maximum current of 0.5 A can be switched at 125 VDC $(\cos\phi = 1)$. Maximum current of 0.2 A can be switched if L/R is 7 ms. In both cases, a life of 100,000 operations can be expected. The minimum applicable load is 0.1 mA at 1 VDC (P reference value)

Connections

Connection

H3YN-2-B/-21-B



41 (12)

5 5 5 12 14 42 (1) (5) (4)

. 44 (8)

H3YN-4-B/-41-B H3YN-4-Z-B/-41-Z-B

A2 (14)

44 (8) 42 (4)

(12) (11)

34 (7)

32 (3)

PW ∕ U⊦ ſĦ

Time

24 (6) 14 (5)

22 (2)

(Bottom View)

A1 (13 circuit


12

(1)

21

(10) (9)

(DIN Indication)




(Bottom View)

Pulse Operation

A pulse output for a certain period can be obtained with a random external input signal. Use the H3YN-B in interval mode as shown in the following timing charts.

H3YN-2-B/-21-B




Caution

Be careful when connecting wires.

Mode	Terminals
Pulse operation	Power supply between 11(9) and A2(14) Short-circuit between 14(5) and A1(13) Input signal between 11(9) and A1(13)
Operating mode; interval and all other modes	Power supply between A1(13) and A2(14)

H3YN-□-B Nomenclature




Dimensions

Timers


H3YN-2-B/-21-B Front Mounting





H3YN-4-B/-41-B Front Mounting H3YN-4-Z-B/-41-Z-B





(Unit: mm)

Operation

DIP Switch Settings

The 1-s range and ON-delay mode for H3YN-2-B/-4-B/-4-Z-B, the 1-min range and ON-delay mode for H3YN-21-B/-41-B/-41-Z-B are factory-set before shipping.

Time Ranges

Model	Time range	Time setting range	Setting	Factory-set
H3YN-2-B, H3YN-4-B H3YN-4-Z-B	1 s	0.1 to 1 s		Yes
	10 s	1 to 10 s		No
	1 min	0.1 to 1 min		No
	10 min	1 to 10 min		No
H3YN-21-B, H3YN-41-B H3YN-41-Z-B	1 min	0.1 to 1 min		Yes
	10 min	1 to 10 min		No
	1 h	0.1 to 1 h		No
	10 h	1 to 10 h		No

 PW
 PZZZZZZZZ

 Imode
 Imode

 Imode</

Note: The top two DIP switch pins are used to select the time ranges.

Operating Modes

Operating mode	Setting	Factory-set
ON-delay		Yes
Interval		No
Flicker OFF-start		No
Flicker ON-start		No

Note: The bottom two DIP switch pins are used to select the operating mode.

H3YN-□-B

Timing Chart			
Operating mode	Timing chart		
	H3YN-2-B/-21-B	H3YN-4-B/-41-B	
ON-delay Power	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 41(12)-42(4)) Time initi contact NO (11(9)-14(5), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	Power Rt 1 Time limit contact NC 1 1 (119)-12(1), 21(10)-22(2), 31(11)-32(3), 41(12)-42(4)) 1 1 Time limit contact NO 1 1 1 (119)-14(5), 21(10)-24(6), 31(11)-34(7), 41(12)-44(8)) 1 1 1 Run/Power indicator (PW) 0 1 1 1 Output indicator (UP) 1 1 1 1	
Interval Power	Power (A1(13)-A2(14)) Rt Time limit contact NC (11(9)-12(1), 41(12)-42(4))	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 21(10)-22(2), 31(11)-32(3), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 21(10)-24(6), 31(11)-34(7), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	
Flicker OFF-start	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 21(10)-22(2), 31(11)-32(3), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 21(10)-24(6), 31(11)-34(7), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	
Flicker ON-start	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	Power (A1(13)-A2(14)) Time limit contact NC (11(9)-12(1), 21(10)-22(2), 31(11)-32(3), 41(12)-42(4)) Time limit contact NO (11(9)-14(5), 21(10)-24(6), 31(11)-34(7), 41(12)-44(8)) Run/Power indicator (PW) Output indicator (UP)	


Note: t: Set time Rt: Reset time

Precautions for H3Y-series Timers

Flush Mounting Adapter

Y92F-78


(Excluding the H3Y----B and H3YN-----B)



Note: 1. Push the H3Y in until the Adaptor (Y92F-78) hooks engage with its rear panel.
2. Do not round the corners of the cutout on the rear panel surface, otherwise the Adaptor (Y92F-78) tabs may not engage properly.

Mounting Height






59.3 H3YN Series 20 PY08 (PY14)


PY08 (PY14 *1)

PY08QN (PY14QN *1)



PYFZ-08(-E), PYF08A-N (PYFZ-14(-E), PYF14A-N)

PYF-08-PU-L (PYF-14-PU-L *2)



PYF-08-PU-L (PYF-14-PU-L)

Note: 1. The are no restrictions to the mounting direction.

2. Always use the PYF-□-PU-L with the H3Y-□-B or H3YN-□-B.

*1. Models in parentheses are Connecting Sockets to the H3Y-4, H3YN-4/-41, or H3YN-4-Z/-41-Z.

*2. Models in parentheses are Connecting Sockets to the H3Y-4-B, H3YN-4-B/-41-B, or H3YN-4-Z-B/-41-Z-B.

***3.** These values apply when the PFP- \Box N is used.

Add 9 mm if you use the PFP-DN2.

Connecting Sockets (Order Separately) H3Y/H3YN Series

Use one of the following Connecting Sockets: PYFZ-□(-E), PYF□A(-E), PYF□M, PY□, PY□-02, or PY□QN(2)(-Y3). (□: 08 or 14)

H3Y-D-B/H3YN-D-B Series

Use one of the following Connecting Sockets: PYF-□-PU-L. (□: 08 or 14)

Accessories (Order Separately)

Use the PYFZ-□(-E), PYF□A(-E), PYF□M, PY□, PY□-02, or PY□QN(2) to mount the H3Y/H3YN. Use the PYF-□-PU-L to mount the H3Y-□-B/H3YN-□-B. When ordering any one of these sockets, replace "□" with "08" or "14."

Socket Mounting Plates (t = 1.6)


(Excluding the H3Y-D-B and H3YN-D-B)


Use a Socket Mounting Plate to mount multiple Connecting Sockets in a row.

CC

Applicable socket	For mounting 1 socket	For mounting 18 sockets
PY08, PY14, PY08QN(2), PY14QN(2)	PYP-1	PYP-18
Note: PYP-18 may be cut to any desired length.		

PYP-1






Terminal covers PYCZ-C08 PYCZ-C14

Use these covers in a combination with PYFZ-08 and PYFZ-14.

H3Y/H3YN Series for PYFZ-08 PYCZ-C08







Dimensions with terminal cover

PYCZ-C08





H3Y/H3YN Series for PYFZ-14 PYCZ-C14




(Unit: mm)

12.6-



PYCZ-C14



32

Relay Hold-down Clips

The Hold-down Clip makes it possible to mount the H3YN securely and prevent the H3YN from falling out due to vibration or shock. **Note:** When you attach the Hold-down Clip to or remove it from the Socket, take sufficient precautions to not injury your fingers, such as wearing gloves.

3.5


53

4.5


Y92H-3 Y92H-4 H3Y/H3YN Series for PYFZ-□, PYF□A Socket Y92H-3 (Set of Two Clips)



H3Y-□-B/H3YN-□-B Series for PYF-□-PU-L Socket Y92H-3 (Set of Two Clips)




Y92H-4 for PY , PYF M Socket (Excluding the H3Y---B and H3YN---B)




H3Y/H3YN Series Track Mounting/Front Connecting Sockets


PYFZ-08



Terminal Arrangement/Internal Connection Diagram (Top View)




Mounting Hole Dimensions (Top View)




Note: Track mounting is also possible.

PYFZ-14



Terminal Arrangement/Internal Connection Diagram (Top View)



Terminal Arrangement/Internal

Connection Diagram

=


-0103

-(1) 8 (5)

9 12


(Top View)

Mounting Hole Dimensions (Top View)




Note: Track mounting is also possible.


PYFZ-08-E (Finger-protection structure)




PYFZ-14-E (Finger-protection structure)



Terminal Arrangement/Internal Connection Diagram (Top View)




Mounting Hole Dimensions (Top View)



Note: Track mounting is also possible.

Mounting Hole Dimensions (Top View)




Note: Track mounting is also possible.


34

H3Y Series


PYF08A-N




PYF14A-N




Terminal Arrangement




Terminal Arrangement



Mounting Holes (for Surface Mounting)




Mounting Holes (for Surface Mounting)




H3Y/H3YN Series Back Connecting Sockets

PY08, PY14




PY08QN, PY14QN PY08QN(2), PY14QN(2)



Note: With PY QN(2), dimension * should read 20 max. and dimension ** 36.5 max.


PY08-02, PY14-02



Terminal Arrangement (Bottom View) 0000 0 4 8 6678 6 9000 9 12 B 14 ß 14 PY08 PY14

21.4^{+0.2} 25.8^{+0.2}

Panel Cutout



PY□, PY□-02, PY□QN(2)


0	4	00	84
6	8	60	08
9	Ð	90	00
ß	Ø	ß	۵
PY08 PY08	QN QN(2)	PY140 PY140	


Terminal Arrangement (Bottom View)

		-	
0	4	00	84
6	8	60	08
9	Ð	90	10
ß	Ø	ß	Ø
PY08	-02	PY14-	02


H3Y-□-B/H3YN-□-B Series Front Connecting Sockets PYF-08-PU-L







Note: The numbers in parentheses are traditionally used terminal numbers.




Mounting Hole Dimensions

Note: Pull out the hooks to mount the Socket with screws.

PYF-14-PU-L







35 3


27.35

3.9






Note: The numbers in parentheses are traditionally used terminal numbers.



Note: Pull out the hooks to mount the Socket with screws.


Mounting Track PFP-100N/PFP-50N (see note 1)



- 1000 (500) (See note 2)
 7.3±0.15

 Note:
 1. Meets DIN EN50022

 2. This dimension applies to PFP-50N.
- Spacer PFP-S



End Plate PFP-M


24 27±0.15

1.5

35±0.3

·M

50



Safety Precautions

Be sure to read precautions for all models in the website at the following URL: http://www.ia.omron.com/.

Warning Indications

_	
	Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

0	Used for general mandatory action precautions for which there is no specified symbol.	
	Use to indicate prohibitions when there is a risk of minor injury from electrical shock or other source if the product is disassembled.	
\bigcirc	Used for general prohibitions for which there is no specific symbol.	

Risk of fire and explosion due to arcing and relay heat generation that accompanies switching. Do not use in an environment where flammable or explosive gas is present.



The service life of the output relay varies widely depending on switching capacity and switching conditions. Use only within the rated load and electrical life count, based on actual conditions of use. Risk of contact sticking and burning if used past the service

life. Always use a load current that does not exceed the rating, and if a heater is used, use a thermal switch in the load circuit.

Do not remove the outer casing.



In rare circumstances there is a risk of slight electrical shock, fire, or device damage. Do not disassemble, modify, repair, or otherwise touch the inside.



Tighten the screws for the lead wires to the Socket to the following torque.

PYF Socket: 0.78 to 1.18 N·m

OMRON

This is the recommended range when crimp terminals are used.

If the screws are not tightened sufficiently on Front-connecting Sockets, the lead wires may come off, connection failure may cause abnormal heating, or fires may occur.

If they are tightened excessively, the screw threads may be damaged.


Precautions for Safe Use

Confirm that the setting dial, indicators and plastic parts are operating normally. Depending on the operating environment, the setting dial, indicators and plastic parts may deteriorate faster than expected, causing the indicators to fail. Periodically perform inspections and replacements.

We recommend that you use a surge absorber if surge voltages may occur. When you dispose of the Timer, do so according to all local ordinances for processing industrial waste.


Precautions for Correct Use

- When selecting a control output, use the H3Y-2/H3YN-2/H3Y-2-B/ H3YN-2-B for switching ON and OFF the power and the H3Y-4/ H3YN-4/H3Y-4-B/H3YN-4-B for switching ON and OFF the minute load. Gold-plated relays are used in the H3Y-4, H3YN-4, H3Y-4-B, H3YN-4-B, H3YN-4-Z, H3YN-41-Z, H3YN-4-Z-B, and H3YN-41-Z-B Series.
- Connect the power supply between terminals A1 (13) and A2 (14). For a DC power supply, connect the negative side to A1 (13) and the positive side to A2 (14).
- The operating voltage will increase when using the H3Y/H3YN/ H3Y-B/H3YN-B in any place where the ambient temperature is more than 50°C. Supply 90% to 110% of the rated voltages (at 12 VDC: 95% to 110%) when operating at 45°C or higher.
- Do not leave the H3Y/H3YN/H3Y-B/H3YN-B in time-up condition for a long period of time (for example, more than one month in any place where the ambient temperature is high), otherwise the internal parts (aluminum electrolytic capacitor) may become damaged. Therefore, the use of the H3Y/H3YN/H3Y-B/H3YN-B with a relay as shown in the following circuit diagram is recommended to extend the service life of the H3Y/H3YN/H3Y-B/ H3YN-B.




 $\otimes\colon$ Auxiliary relay such as MY Relay

- The H3YN/H3YN-B must be disconnected from the Socket when setting the DIP switch, otherwise the user may touch a terminal imposed with a high voltage and get an electric shock.
- Do not connect the H3Y/H3YN/H3Y-B/H3YN-B as shown in the following circuit diagram on the right hand side, otherwise the H3Y's/H3YN's/H3Y-B's/H3YN-B's internal contacts different from each other in polarity may become short-circuited.



 Use the following safety circuit when building a self-holding or selfresetting circuit with the H3Y/H3YN/H3Y-B/H3YN-B and an auxiliary relay, such as an MY Relay, in combination.



- In the case of the above circuit, the H3YN will be in pulse operation. Therefore, if the circuit shown on page 13 is used, no auxiliary relay will be required.
- Do not set to the minimum setting in the flicker modes, otherwise the contact may become damaged.
- Be careful not to apply any voltage to the terminal screws on the back of the Timer. Mount the product so that the screws will not come in contact with the panel or metal parts.
- Do not use the H3Y/H3YN/H3Y-B/H3YN-B in places where there is excessive dust, corrosive gas, or direct sunlight.
- Do not mount more than one H3Y/H3YN/H3Y-B/H3YN-B closely together, otherwise the internal parts may become damaged. Make sure that there is a space of 5 mm or more between any H3Y/ H3YN/H3Y-B/H3YN-B Models next to each other to allow heat radiation.
- The internal parts may become damaged if a supply voltage other than the rated ones is imposed on the H3Y/H3YN/H3Y-B/H3YN-B. When more than 100 V is applied to 12 or 24 VDC models, the internal element (varistor) may break.

Precautions for EN 61812-1 Conformance

The H3Y/H3YN/H3Y-B/H3YN-B as a built-in timer conforms to EN 61812-1 provided that the following conditions are satisfied.

Handling

- Do not touch the DIP switch while power is supplied to the H3YN/ H3YN-B.
- Before dismounting the H3YN/H3YN-B from the Socket, make sure that no voltage is imposed on any terminal of the H3YN/ H3YN-B.
- The applicable Socket is the PYF□A (H3Y/H3YN) or PYF-□-PU-L (H3Y-B/H3YN-B).
- Only basic insulation is ensured between the Y92H-3 Hold-down Clips and H3Y/H3YN/H3Y-B/H3YN-B internal circuits.
- Do not allow the Y92H-3 Hold-down Clips to contact other parts.
- The insulation test voltage between different pole contacts for the 4-pole model is the impulse voltage of 2.95 kV.

Wiring

- The power supply for the H3Y/H3YN/H3Y-B/H3YN-B must be protected with equipment such as a breaker approved by VDE.
- Basic insulation is ensured between the H3Y's/H3YN's/H3Y-B's/
- H3YN-B's operating circuit and control output. • Insulation requirement:

Overvoltage category II,

pollution degree 1 (H3Y-4/-4-0/-4-B, H3YN-4/41/-4-B/-41-B, H3YN-4-Z/-41-Z/-4-Z-B/-41-Z-B),

(with a clearance of 1.5 mm and a creepage distance of 2.5 mm at 240 VAC)

• Output terminals next to each other on the H3Y-4 or H3Y-4-0 must have the same polarity.

- In order to conform to UL and CSA requirements when using the H3Y-4/-4-0/-4-B, H3YN-4/-41/-4-B/-41-B, or H3YN-4-Z/-41-Z/ -4-Z-B/-41-ZB, connect the Unit so that output contacts (contacts of different poles) have the same electric potential.
- In cases such as PLC input where the load is extremely small for the control output of a timer containing a power relay (using other than gold-plated contacts), reliability can be increased by using contacts of the same poles (e.g., the H3Y-2) in parallel.
- Always use the same type of wire.
- Installation
 - There are no restrictions on the installation orientation. Install the Timer securely.

Recommended Replacement Periods and Periodic Replacement as Preventive Maintenance

The recommended replacement period for preventive maintenance is greatly influenced by the application environment of the product. As a guideline for models that do not have a Maintenance Forecast Monitor, the recommended replacement period is 7 to 10 years.* To prevent failures that can be caused by using a product beyond its service live, we recommend that you replace the product as early as possible within the recommended replacement period. However, realize that the recommended replacement period is for reference only and does not guarantee the life of the product.

Many electronic components are used in the product and the product depends on the correct operation of these components to achieve product functions and performance. However, the influence of the ambient temperature on aluminum electrolytic capacitors is large, and the service life is reduced by half for each 10°C rise in temperature (Arrhenius law). When the capacity reduction life of the electrolytic capacitor is reached, the product may fail. We therefore recommend that you replace the product periodically to minimize product failures in advance.

* The following conditions apply: rated input voltage, load rate of 50% max., ambient temperature of 35°C max., and the standalone mounting method.

This product model is designed with a service life of 10 years minimum under the above conditions.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-2711 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222 Fax: (86) 21-5037-2200 Authorized Distributor:

©OMRON Corporation 2016-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_2_4 Cat. No. M092-E1-07 1122 (0316)