

# Timer Interval Indicator K3HB-P

CSM\_K3HB-P\_DS\_E\_16\_6

## Digital Time Interval Meter for Measuring Passing Speed, Time, or Cycle between Two Points.

- Visual confirmation of judgement results through display colors that switch between red and green. \*
- Measures Wide Range of Pulse Interval Times
- Measures, calculates, and displays pulse intervals between two points. Wide range for pulse interval measurements, from 10 ms to 3,200 s, max.
- Six Measurement Operations, Including Passing Speed, Time, and Cycle Measurement between Two Points
- One Digital Time Interval Meter has six measurement functions, to support a variety of pulse interval measurement applications. Select the best function for your application from the following: Passing speed, cycle, time difference, time band, measuring length, and interval.
- \* Visual confirmation of judgement results is not supported on models that do not have an output.
- You can change the display color by setting it, but you cannot switch it based on the judgement results.

 Refer to Safety Precautions for All Digital Panel Meters.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

## Model Number Structure

### ■ Model Number Legend

Base Units and Optional Boards can be ordered individually or as sets.

#### Base Units

K3HB-P    
1 5

#### 1. Input Sensor Code

NB: NPN input/voltage pulse input  
PB: PNP input

#### 5. Supply Voltage

100-240 VAC: 100 to 240 VAC  
24 VAC/VDC: 24 VAC/VDC

#### Optional Board

##### Sensor Power Supply/Output Boards

K33-  
2

##### Relay/Transistor Output Boards

K34-  
3

##### Event Input Boards

K35-  
4

#### Base Units with Optional Boards

K3HB-P -     
1 2 3 4 5

#### 2. Sensor Power Supply/Output Type Code

None:	None
CPA:	Relay output (PASS: SPDT) + Sensor power supply (12 VDC±10%, 80 mA) (See note 1.)
L1A:	Linear current output (0 to 20 or 4 to 20 mA DC) + Sensor power supply (12 VDC±10%, 80 mA) (See note 2.)
L2A:	Linear voltage output (0 to 5, 1 to 5, or 0 to 10 VDC) + Sensor power supply (12 VDC±10%, 80 mA) (See note 2.)
A:	Sensor power supply (12 VDC ±10%, 80 mA)
FLK1A:	Communications (RS-232C) + Sensor power supply (12 VDC±10%, 80 mA) (See note 2.)
FLK3A:	Communications (RS-485) + Sensor power supply (12 VDC±10%, 80 mA) (See note 2.)

**Note:** 1. CPA can be combined with relay outputs only.

2. Only one of the following can be used by each Digital Indicator: RS-232C/RS-485 communications, or a linear output.

#### 3. Relay/Transistor Output Type Code

None:	None
C1:	Relay contact (H/L: SPDT each)
C2:	Relay contact (HH/H/LL/L: SPST-NO each)
T1:	Transistor (NPN open collector: HH/H/PASS/L/LL)
T2:	Transistor (PNP open collector: HH/H/PASS/L/LL)
BCD	*BCD output + transistor output (NPN open collector: HH/H/PASS/L/LL)

\* A Special BCD Output Cable (sold separately) is required.

#### 4. Event Input Type Code

None:	None
1:	5 inputs (HOLD/RESET), NPN open collector
2 *:	8 inputs (HOLD/RESET/BANK1/BANK2/BANK4), NPN open collector
3:	5 inputs (HOLD/RESET), PNP open collector
4 *:	8 inputs (HOLD/RESET/BANK1/BANK2/BANK4), PNP open collector

\* There is no bank selection for "None" types of "Transistor Output Type Code".

**Note:** The following combinations are not possible.

- Communications (FLKA) + BCD output (BCD)

## Accessories (Sold Separately)

K32-DICN: Special Cable (for event inputs with 8-pin connector)

K32-BCD: Special BCD Output Cable

### Watertight Cover

Model
Y92A-49N

### Rubber Packing

Model
K32-P1

**Note:** Rubber packing is provided with the Controller.

## Specifications

### ■ Ratings

Supply voltage	100 to 240 VAC, 24 VAC/VDC						
Allowable power supply voltage range	85% to 110% of the rated power supply voltage						
Power consumption (See note 1.)	100 to 240 VAC: 18 VA max. (max. load) 24 VAC/DC: 11 VA/7 W max. (max. load)						
Input	No-voltage contact, voltage pulse, open collector						
External power supply	12 VDC 10%, 80 mA (for models with external power supplies only)						
Event inputs (See note 2.)	<table border="1"> <tr> <td>Hold input</td> <td>NPN open collector or no-voltage contact signal</td> </tr> <tr> <td>Reset input</td> <td>ON residual voltage: 2 V max. ON current at 0 Ω: 4 mA max.</td> </tr> <tr> <td>Bank input</td> <td>Max. applied voltage: 30 VDC max. OFF leakage current: 0.1 mA max.</td> </tr> </table>	Hold input	NPN open collector or no-voltage contact signal	Reset input	ON residual voltage: 2 V max. ON current at 0 Ω: 4 mA max.	Bank input	Max. applied voltage: 30 VDC max. OFF leakage current: 0.1 mA max.
Hold input	NPN open collector or no-voltage contact signal						
Reset input	ON residual voltage: 2 V max. ON current at 0 Ω: 4 mA max.						
Bank input	Max. applied voltage: 30 VDC max. OFF leakage current: 0.1 mA max.						
Output ratings (depends on the model)	<table border="1"> <tr> <td>Relay output</td> <td>250 VAC, 30 VDC, 5 A (resistive load) Mechanical life expectancy: 5,000,000 operations, Electrical life expectancy: 100,000 operations</td> </tr> <tr> <td>Transistor output</td> <td>Maximum load voltage: 24 VDC, Maximum load current: 50 mA, Leakage current: 100 μA max.</td> </tr> <tr> <td>Linear output</td> <td>Linear output 0 to 20 mA DC, 4 to 20 mA DC: Load: 500 Ω max, Resolution: Approx. 10,000, Output error: ±0.5% FS Linear output 0 to 5 VDC, 1 to 5 VDC, 0 to 10 VDC: Load: 5 kΩ max, Resolution: Approx. 10,000, Output error: ±0.5% FS (1 V or less: ±0.15 V; no output for 0 V or less)</td> </tr> </table>	Relay output	250 VAC, 30 VDC, 5 A (resistive load) Mechanical life expectancy: 5,000,000 operations, Electrical life expectancy: 100,000 operations	Transistor output	Maximum load voltage: 24 VDC, Maximum load current: 50 mA, Leakage current: 100 μA max.	Linear output	Linear output 0 to 20 mA DC, 4 to 20 mA DC: Load: 500 Ω max, Resolution: Approx. 10,000, Output error: ±0.5% FS Linear output 0 to 5 VDC, 1 to 5 VDC, 0 to 10 VDC: Load: 5 kΩ max, Resolution: Approx. 10,000, Output error: ±0.5% FS (1 V or less: ±0.15 V; no output for 0 V or less)
Relay output	250 VAC, 30 VDC, 5 A (resistive load) Mechanical life expectancy: 5,000,000 operations, Electrical life expectancy: 100,000 operations						
Transistor output	Maximum load voltage: 24 VDC, Maximum load current: 50 mA, Leakage current: 100 μA max.						
Linear output	Linear output 0 to 20 mA DC, 4 to 20 mA DC: Load: 500 Ω max, Resolution: Approx. 10,000, Output error: ±0.5% FS Linear output 0 to 5 VDC, 1 to 5 VDC, 0 to 10 VDC: Load: 5 kΩ max, Resolution: Approx. 10,000, Output error: ±0.5% FS (1 V or less: ±0.15 V; no output for 0 V or less)						
Display method	Negative LCD (backlit LED) display 7-segment digital display (Character height: PV: 14.2 mm (green/red); SV: 4.9 mm (green))						
Main functions	Scaling function, measurement operation selection, output hysteresis, output OFF delay, output test, teaching, display value selection, display color selection, key protection, bank selection, display refresh period, maximum/minimum hold, reset						
Ambient operating temperature	-10 to 55°C (with no icing or condensation)						
Ambient operating humidity	25% to 85%						
Storage temperature	-25 to 65°C (with no icing or condensation)						
Altitude	2,000 m max.						
Accessories	Watertight packing, 2 fixtures, terminal cover, unit stickers, instruction manual.						

**Note:** 1. DC power supply models require a control power supply capacity of approximately 1 A per Unit when power is turned ON. Particular attention is required when using two or more DC power supply models. The OMRON S8VS-series DC Power Supply Unit is recommended.

2. PNP input types are also available.

## ■ Characteristics

Display range	-19,999 to 99,999																																
Measurement accuracy (at 23±5°C)	±0.08% rgd ±1 digit (for voltage pulse/open collector sensors)																																
Measurement range	Functions F1, F3, and F4: (Interval between input pulses) 10 ms to 3,200 s Function F2: (Interval between input pulses) 20 ms to 3,200 s Functions F5, F6: (Number of input pulses) 0 to 4 gigacounts																																
Input signals	<ul style="list-style-type: none"> <li>• Contact input (dry contact input) (30 Hz max. with ON/OFF pulse width of 15 ms min.)</li> <li>• No contact voltage pulse</li> <li>• Open collector</li> </ul> <table border="1"> <thead> <tr> <th>Mode</th> <th>Input frequency range</th> <th>ON/OFF pulse width</th> <th>ON voltage</th> <th>OFF voltage</th> <th>Input impedance</th> </tr> </thead> <tbody> <tr> <td>F1 to F4</td> <td>0 to 50 kHz</td> <td>9 µs min.</td> <td>4.5 to 30 V</td> <td>-30 to 2 V</td> <td>10 kΩ</td> </tr> <tr> <td>F5, F6</td> <td>0 to 30 kHz</td> <td>16 µs min.</td> <td></td> <td></td> <td></td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th>Mode</th> <th>Input frequency range</th> <th>ON/OFF pulse width</th> </tr> </thead> <tbody> <tr> <td>F1 to F4</td> <td>0 to 50 kHz</td> <td>9 µs min.</td> </tr> <tr> <td>F5, F6</td> <td>0 to 30 kHz</td> <td>16 µs min.</td> </tr> </tbody> </table>						Mode	Input frequency range	ON/OFF pulse width	ON voltage	OFF voltage	Input impedance	F1 to F4	0 to 50 kHz	9 µs min.	4.5 to 30 V	-30 to 2 V	10 kΩ	F5, F6	0 to 30 kHz	16 µs min.				Mode	Input frequency range	ON/OFF pulse width	F1 to F4	0 to 50 kHz	9 µs min.	F5, F6	0 to 30 kHz	16 µs min.
Mode	Input frequency range	ON/OFF pulse width	ON voltage	OFF voltage	Input impedance																												
F1 to F4	0 to 50 kHz	9 µs min.	4.5 to 30 V	-30 to 2 V	10 kΩ																												
F5, F6	0 to 30 kHz	16 µs min.																															
Mode	Input frequency range	ON/OFF pulse width																															
F1 to F4	0 to 50 kHz	9 µs min.																															
F5, F6	0 to 30 kHz	16 µs min.																															
Connectable sensors	<p>ON residual voltage: 3 V max. OFF leakage current: 1.5 mA max. Load current: Must have a switching capacity of 20 mA or higher. Must be able to properly switch load currents of 5 mA or less.</p>																																
Comparative output response time (transistor output)	2 ms max. (time until the comparative output is made when there is a forced sudden change in the input signal from 15% to 95% or 95% to 15%)																																
Linear output response time	10 ms max. (time until the final analog output value is reached when there is a forced sudden change in the input signal from 15% to 95% or 95% to 15%)																																
Insulation resistance	20 MΩ min. (at 500 VDC)																																
Dielectric strength	2,300 VAC for 1 min between external terminals and case																																
Noise immunity	<p>100 to 240 VAC models: ±1,500 V at power supply terminals in normal or common mode (waveform with 1-ns rising edge and pulse width of 1 µs/100 ns)</p> <p>24 VAC/VDC models: ±1,500 V at power supply terminals in normal or common mode (waveform with 1-ns rising edge and pulse width of 1 µs/100 ns)</p>																																
Vibration resistance	Frequency: 10 to 55 Hz; Acceleration: 50 m/s <sup>2</sup> , 10 sweeps of 5 min each in X, Y, and Z directions																																
Shock resistance	150 m/s <sup>2</sup> (100 m/s <sup>2</sup> for relay outputs) 3 times each in 3 axes, 6 directions																																
Weight	Approx. 300 g (Base Unit only)																																
Degree of protection	Front panel	Conforms to NEMA 4X for indoor use (equivalent to IP66)																															
	Rear case	IP20																															
	Terminals	IP00 + finger protection (VDE0106/100)																															
Memory protection	EEPROM (non-volatile memory) Number of rewrites: 100,000																																
Applicable standards	UL61010-1, CSA C22.2 No. 61010-1-04 EN61010-1 (IEC61010-1): Pollution degree 2/Overvoltage category II EN61326-1																																
EMC	<p>EMI: EN61326-1 Industrial electromagnetic environment Electromagnetic radiation interference CISPR 11 Group 1, Class A</p> <p>Terminal interference voltage CISPR 11 Group 1, Class A</p> <p>EMS: EN61326-1 Industrial electromagnetic environment Electrostatic Discharge Immunity EN61000-4-2: 4 kV (contact), 8 kV (in air)</p> <p>Radiated Electromagnetic Field Immunity EN61000-4-3: 10 V/m sine wave amplitude modulation (80 MHz to 1 GHz, 1.4GHz to 2 GHz)</p> <p>Electrical Fast Transient/Burst Noise Immunity EN61000-4-4: 2 kV (power line), 1 kV (I/O signal line)</p> <p>Surge Immunity EN61000-4-5: 1 kV with line (power line), 2 kV with ground (power line)</p> <p>Conducted Disturbance Immunity EN61000-4-6: 3 V (0.15 to 80 MHz)</p> <p>Power Frequency Magnetic Immunity EN61000-4-8: 30 A/m (50 Hz) continuous time</p> <p>Voltage Dips and Interruptions Immunity EN61000-4-11: 0.5 cycle, 0°/180°, 100% (rated voltage)</p>																																

# Operation


## ■ Functions (Operating Modes)

### F1 to F6

These functions use the internal system clock to measure the time between pulses or the pulse ON time and then display time measurements or a variety of other calculations.

Function name	Function No.
Passing speed	F1
Cycle	F2
Time difference	F3
Time band	F4
Measuring length	F5
Interval	F6

#### Example: F1 Passing Speed



The time (T) between input A pulse and input B pulse is measured by the internal system clock. If, for example, the system clock measures 100,000 counts during time T, then









$$T = 1 \text{ system clock count (0.5 } \mu\text{s}) \times 100,000$$

$$T = 0.05 \text{ s}$$

F1 (the passing speed) is calculated internally using the formula  $\frac{1}{T} \times 60$  (m/min), and the

$$\text{display, in this example, would be } \frac{1}{0.05 \text{ s}} \times 60 = 1200 \text{ (m/min).}$$

Function	Operation	Operation image (application)
F1 Passing speed	<p>The reciprocal of the time (T) from input A ON to input B ON is multiplied by 60 and displayed. Display value <math>D = 1/T \times 60 \times \alpha</math>, <math>\alpha</math>: Prescaling value</p> <p>• Recovery time (<math>T^R</math>) of 20 ms is required before starting the next measurement. Display unit: mm/s, m/s m/min, km/h, etc.</p>	<p>Measuring workpiece passing speed between A and B</p>
F2 Cycle	<p>Measures and displays input A cycle (T). Display value <math>D = T \times \alpha</math>, <math>\alpha</math>: Prescaling value</p> <p>Measurement range: 20 ms to 3,200 s Display unit: ms, s, min., min.s.1/10 s</p>	<p>Measuring feed cycles for parts</p>
F3 Time dif- ference	<p>Displays the time (T) from input A ON to input B ON. Display value <math>D = T \times \alpha</math>, <math>\alpha</math>: Prescaling value</p> <p>Measurement range: 10 ms to 3,200 s • Recovery time (<math>T^R</math>) of 20 ms is required before starting the next measurement. Display unit: ms, s, min., min.s.1/10 s</p>	<p>Measuring workpiece passing time between A and B</p> <p>Measuring the length of a workpiece step by changing prescale values.</p>

Function	Operation	Operation image (application)
F4 Time band	<p>Displays input A ON time (T). Display value <math>D = T \times \alpha</math>, <math>\alpha</math>: Prescaling value</p>  <p>Measurement range: 10 ms to 3,200 s • Recovery time (<math>T^R</math>) of 20 ms is required before starting the next measurement. Display unit: ms, s, min., min.s.1/10 s</p>	<p>Monitoring the ON time of a printing press</p>  <p>Managing the valve release time</p> 
F5 Measuring length	<p>Displays the number of input A pulses while input B is ON. Display value <math>D = C \times \alpha</math>, C: Pulse value <math>\alpha</math>: Prescaling value</p>  <p>• Recovery time (<math>T^R</math>) of 20 ms is required before starting the next measurement. Display unit: mm, cm, m, etc.</p>	<p>Measuring workpiece length</p> 
F6 Interval	<p>Displays the number of input A pulses from when input B turns ON until input B turns ON again. Measurement is made every other time input B turns ON. Display value <math>D = C \times \alpha</math>, C: Pulse value <math>\alpha</math>: Prescaling value</p>  <p>• Recovery time (<math>T^R</math>) of 20 ms is required before starting the next measurement. Display unit: mm, cm, m, etc.</p>	<p>Measuring slit intervals</p>  

## ■ What Is Prescaling?

To make calculations using the input pulse to display the passing speed between two points, the distance between the two points and the display unit must be set and the internally measured time multiplied by a certain coefficient. This coefficient is called the prescale value. (For information on settings details, refer to the User's Manual.)

### Time Unit Settings

Setting	Meaning
OFF	Seconds display when prescaling = 1.0000
MIN	Minutes display when prescaling = 1.0000
H.MM.SS	h.mm.ss display
MM.SS.D	mm.ss.d display (d = tenths of a second)

### Input Type Setting

	NO: Voltage pulse high	NC: Voltage pulse low
No-contact or voltage pulse input	00	01
Contact	10	11

**Note:** Set to 10 or 11 when there is a large variation in the display.  
The largest measurement range is 30 Hz.

# Common Specifications

## ■ Event Input Ratings

K3HB-P/C	HOLD, RESET, BANK1, BANK2, BANK4
Contact	ON: 1 kΩ max., OFF: 100 kΩ min.
No-contact	ON residual voltage: 2 V max. OFF leakage current: 0.1 mA max. Load current: 4 mA max. Maximum applied voltage: 30 VDC max.

## ■ Output Ratings

### Contact Output

Item	Resistive loads (250 VAC, cosφ=1; 30 VDC, L/R=0 ms)	Inductive loads (250 VAC, closed circuit, cosφ=0.4; 30 VDC, L/R=7 ms)
Rated load	5 A at 250 VAC 5 A at 30 VDC	1 A at 250 VAC 1 A at 30 VDC
Mechanical life expectancy	5,000,000 operations	
Electrical life expectancy	100,000 operations	

### Linear Output

Item	Outputs	0 to 20 mA	4 to 20 mA	0 to 5 V	1 to 5 V	0 to 10 V
Allowable load impedance		500 Ω max.		5 kΩ min.		
Resolution		Approx. 10,000				
Output error		±0.5% FS		±0.5% FS (±0.15 V for 1 V or less and no output for 0 V)		

### Serial Communications Output

Item	Type	RS-232C, RS-485
Communications method	Half duplex	
Synchronization method	Start-stop synchronization (asynchronous)	
Baud rate	9600/19200/38400 bps	
Transmission code	ASCII	
Data length	7 bits or 8 bits	
Stop bit length	2 bits or 1 bit	
Error detection	Vertical parity and FCS	
Parity check	Odd, even	

### Transistor Outputs

Maximum load voltage	24 VDC
Maximum load current	50 mA
Leakage current	100 μA max.

### BCD Output I/O Ratings

#### (Input Signal Logic: Negative)

I/O signal name		Item	Rating
Inputs	REQUEST	Input signal	No-voltage contact input
	HOLD	Input current for no-voltage input	10 mA
	MAX	Signal level	ON voltage: 1.5 V max.
	MIN		OFF voltage: 3 V min.
Outputs	RESET	Leakage current	100 μA max.
	DATA	Maximum load voltage	24 VDC
	POLARITY	Maximum load current	10 mA
	OVER	Leakage current	100 μA max.
	DATA VALID	HH	Maximum load voltage
	RUN	H	24 VDC
		PASS	Maximum load current
		L	50 mA
		LL	Leakage current
			100 μA max.

Refer to the *K3HB Communications User's Manual* (Cat. No. N129) for details on serial communications.

# Connections


## External Connection Diagrams

### Terminal Arrangements


Note: Refer to *Internal Block Diagram* on page 9 for information on isolation.

#### A Operating Power Supply

100 to 240 VAC  
24 VAC/VDC




\*Check the required power supply type.




#### B Sensor Power Supply/Output


Sensor power supply + PASS output




Sensor power supply + linear output



Sensor power supply



Sensor power supply + communications




#### C Relays, Transistors, and BCD


Relay Outputs <C1>

Relay Outputs <C2>

Transistor Outputs <T1> <T2>




BCD (NPN Open Collector): <BCD>  
Special Cable (Sold separately)  
K32-BCD (OMRON)  
(HDR-E50MAG1 with 0.3-m cable)




The BCD COMMON is shared.  
The pins indicated in the above diagram as blank (white) boxes have been removed.

\*Only one of the following can be used for each Digital Indicator: communications, or BCD.

Contact Outputs






Transistor Outputs (NPN Open Collector)




#### Safety Standards Conformance



- The product must be used indoors for the above applicable standards to apply.

**E Pulse Inputs****NPN Input Model****PNP Input Model****Connectable Sensors**

ON residual voltage: 3 V  
OFF leakage current: 1.5 mA max.




Note: A 2-wire DC sensor can also be connected. Check the ratings and characteristics tables, however, for the connection conditions.

**D Event Inputs****Models with Terminal Blocks****Models with Connectors**

- Applicable Connector (Sold separately) XG4M-1030 (OMRON)
- Special Cable (Sold separately) K32-DICN (OMRON) (XG4M-1030 with 3-m cable)

- Use terminal pin D6 as the common terminal.
- Use NPN open collector or no-voltage contacts for event input.

PNP types are also available.

**BCD Output Cable**

Model	Shape	Pin arrangement
K32-BCD	<p>K3HB end</p> <p>Connected device end (PLC, display device, etc.)</p>	


Note: The BCD Output Cable has a D-sub plug.

**Special Cable (for Event Inputs with 8-pin Connector)**

Model	Appearance	Wiring																						
K32-DICN		<p>Cable marking</p> <table border="1"> <tr> <th>Pin No.</th> <th>Signal name</th> </tr> <tr> <td>1</td> <td>N/C</td> </tr> <tr> <td>2</td> <td>S-TMR</td> </tr> <tr> <td>3</td> <td>HOLD</td> </tr> <tr> <td>4</td> <td>RESET</td> </tr> <tr> <td>5</td> <td>N/C</td> </tr> <tr> <td>6</td> <td>COM</td> </tr> <tr> <td>7</td> <td>BANK4</td> </tr> <tr> <td>8</td> <td>BANK2</td> </tr> <tr> <td>9</td> <td>BANK1</td> </tr> <tr> <td>10</td> <td>COM</td> </tr> </table>	Pin No.	Signal name	1	N/C	2	S-TMR	3	HOLD	4	RESET	5	N/C	6	COM	7	BANK4	8	BANK2	9	BANK1	10	COM
Pin No.	Signal name																							
1	N/C																							
2	S-TMR																							
3	HOLD																							
4	RESET																							
5	N/C																							
6	COM																							
7	BANK4																							
8	BANK2																							
9	BANK1																							
10	COM																							


## ■Derating Curve for Sensor Power Supply (Reference Values)

For 12V



**Note:** 1. The above values were obtained under test conditions with the standard mounting conditions, so be sure to adjust accordingly.  
 2. Internal components may be deteriorated or damaged. Do not use the Digital Indicator outside of the derating range (i.e., do not use it in the area labeled (1), above).


## ■Internal Block Diagram



## ■BCD Output Timing Chart

A REQUEST signal from a Programmable Controller or other external device is required to read BCD data.

### Single Sampling Data Output





The data is set in approximately 30 ms from the rising edge of the REQUEST signal and the DATA VALID signal is output.

When reading the data from a Programmable Controller, start reading the data when the DATA VALID signal turns ON.


The DATA VALID signal will turn OFF 40 ms later, and the data will turn OFF 16 ms after that.

- The K3HB BCD output model has an open collector output, so wired OR connection is possible




Note: Leave 20 ms min. between DATA VALID turning OFF and the REQUEST signal.

### Programmable Controller Connection Example



### Display Unit Connection Example




Note: The BCD output connector pin number is the D-sub connector pin number when the BCD Output Cable (sold separately) is connected. This number differs from the pin number for the Digital Indicator narrow pitch connector (manufactured by Honda Tsushin Kogyo Co., Ltd.).

\*M7E series were discontinued at the end of March, 2020.


Refer to the following User's Manual for application precautions and other information required when using the Digital Indicator:  
K3HB-R/P/C Digital Indicator User's Manual (Cat. No. N136)

The manual can be downloaded from the following site in PDF format: OMRON Industrial Web <http://www.fa.omron.co.jp>

## ■ Component Names and Functions



## Dimensions




Note: Mounting Recommended Panel Thickness 1 to 8 mm.  
Mount the product horizontally.

## Wiring Precautions

- For terminal blocks, use the crimp terminals suitable for M3 screws.
- Tighten the terminal screws to the recommended tightening torque of approx. 0.5 N·m.
- To prevent inductive noise, separate the wiring for signal lines from that for power lines.


## Wiring

- Use the crimp terminals suitable for M3 screws shown below.



## Unit Stickers (included)


- No unit stickers are attached to the Digital Indicator.
- Select the appropriate units from the unit sticker sheets provided.



**Note:** For measurements for commercial purposes, be sure to use the unit required by any applicable laws or regulations.


## Watertight Cover

Y92A-49N




## Rubber Packing

K32-P1




## Mounting Method

- Insert the K3HB into the mounting cutout in the panel.
- Insert watertight packing around the Unit to make the mounting watertight.




- Insert the fixture into the grooves on the left and right sides of the rear case and push until it reaches the panel and is fixed in place.



## LCD Field of Vision

The K3HB is designed to have the best visibility at the angles shown in the following diagram.



If the rubber packing is lost or damaged, it can be ordered using the following model number: K32-P1.

(Depending on the operating environment, deterioration, contraction, or hardening of the rubber packing may occur and so, in order to ensure the level of waterproofing specified in NEMA4, periodic replacement is recommended.)

**Note:** Rubber packing is provided with the Controller.

# Main Functions

## ■ Main Functions and Features

### Measurement

#### Function **FUnC**

The K3HB-R has the following six functions for receiving and displaying input pulses.

- F1: Rotation (rpm)/circumferential speed
- F2: Absolute ratio
- F3: Error ratio
- F4: Rotational difference
- F5: Flow rate ratio
- F6: Passing time

The K3HB-P has the following six functions for receiving and displaying input pulses.

- F1: Passing speed
- F2: Cycle
- F3: Time difference
- F4: Time band
- F5: Measuring length
- F6: Interval

The K3HB-C has the following three functions for receiving and displaying input pulses.

- F1: Individual inputs
- F2: Phase differential inputs
- F3: Pulse counting input

### Filters

#### Input Types **In-A, In-B** **In-C**

Specify the types of sensor connected to input A and input B.

### Key Operations

#### Key Protection

Key protection restricts level or parameter changes using the keys to prevent unintentional key operations and malfunctions.

### Outputs

#### Comparative Output Pattern **oUt-P**

Standard, zone, and level comparative output patterns can be selected for comparative outputs.

#### Output Refresh Stop **o-StP**

Holds the output status when a comparative result output other than PASS turns ON.

#### PASS Output Change **PASS**

Comparative results other than PASS can be output from the PASS output terminal.

#### Output OFF Delay **oFF-d**

Delays turning OFF comparatives for a set period. This can be used to provide sufficient time to read the comparative output ON status when the comparative result changes at short intervals.

#### Shot Output **Shot**

Turns ON the comparative output for a specific time.

#### Output Logic **oUt-n**

Reverses the output logic of comparative results.

#### Output Test **tEst**

Output operation can be checked without using actual input signals by using the keys to set a test measurement value.

#### Linear Outputs **LSetL, LSetu, LSetH, LSetL**

A current or voltage proportional to the change in the measurement value can be output.

#### Standby Sequence **Stby**

The comparison outputs can be kept OFF until the measurement value enters the PASS range.

## Display

### Display Value Selection **dSP**

The display value can be set to the present value, the maximum value, or the minimum value.

### Display Color Selection **Color**

The present value display color can be set to green or red. The color of the present value can also be switched according to the comparative output.

### Display Refresh Period **drEF**

When the input changes rapidly, the display refresh period can be lengthened to control flickering and make the display easier to read.

### Position Meter **Pos-L, Pos-H, Pos-L**

The present measurement value can be displayed as a position in relation to the scaling width on a 20-gradation position meter.

### Prescale **PSAL, PSAY, PS.bu, PS.bY**

The input signal can be converted and displayed as any value.

### Comparative Set Value Display **SudSP**

Select whether or not to display the comparative value during operation.

### Display auto-return **reT**

Automatically returns the display to RUN level when there are no key operations (e.g., max./min. switching, bank settings using keys).

## Other

### Max./Min. Hold

Holds the maximum and minimum measurement values.

### Bank Selection **bnH-L**

Switch between 8 comparative value banks using the keys on the front panel or external inputs. A set of set comparative values can be selected as a group.

### Bank Copy **CoPY**

Any bank settings can be copied to all banks.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

In the interest of product improvement, specifications are subject to change without notice.

## Terms and Conditions Agreement

### Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

### Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See <http://www.omron.com/global/> or contact your Omron representative for published information.

### Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

### Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

### Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

### Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

### Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

2026.1

In the interest of product improvement, specifications are subject to change without notice.

**OMRON Corporation**  
Industrial Automation Company

<http://www.ia.omron.com/>

(c)Copyright OMRON Corporation 2026 All Right Reserved.