

Machine Automation Controller

NJ-Series


Controller that covers functions and high-speed processing required for machine control and safety, reliability and maintainability



Features

- Implemented OPC UA as standard feature. **EXECUTE** (NJ501-1□00)
- Integration of Logic and Motion in one CPU.
- Conforms to IEC 61131-3 (JIS B 3503) standard programming and PLCopen function blocks for Motion Control. Programming with variables allows users to create complex programs efficiently.
- Fast and accurate control by synchronizing all EtherCAT devices, such as vision sensors, servo drives, and field devices, with the PLC and Motion Engines.
- · Offers speed without compromising on reliability and robustness expected from PLCs.
- Complete RAS functions: Transmission frame error check, timeout, bus diagnosis, Watchdog (WDT), memory check, and topology check, etc.
- Ideal for small-scale control with up to 8 axes. (NJ301-□□□□)
- Ideal for simple machines. (NJ101-
- · Linear and circular interpolation.
- Electronic gear and cam synchronization.
- The Controller can be directly connected to a database. No special Unit, software, nor middleware is required. (NJ501-□□20/NJ101-□020)
- The NJ501 SECS/GEM CPU Unit has built-in the SECS/GEM communications functions which are the standards in the semiconductor industry. (NJ501-1340)
- Control function of parallel link robots, cartesian robots and serial link robots. (NJ501-4□□0)
- Integration of Logic, Motion, OMRON Robot and Kinematics in one CPU. (NJ501-R□□0)
- Realize high-accuracy synchronization motion control (MC) and numerical control (NC) functions by ONE controller. G-Code available. (NJ501-5300)

System Configuration



Ordering Information

Applicable standards

Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

CPU Units

		Specifications					
Product name	I/O capacity / maximum number of configuration Units (Expansion Racks)	of configuration Units		Number of motion axes	Model		
NJ501 OPC UA Support				64	NJ501-1500		
	2,560 points / 40 Units (3 Expansion Racks)	20 MB	MB: Retained during power interruption MB: Not retained during power interruption	32	NJ501-1400		
				16	NJ501-1300		
NJ301 CPU Units		5 MB	0.5 MB: Retained during power interruption 2 MB: Not retained during power interruption	8	NJ301-1200		
				4	NJ301-1100		
NJ101 CPU Units		3 MB		2	NJ101-1000		
				0	NJ101-9000		

	Specifications									
Product name	I/O capacity / maximum number of configuration Units (Expansion Racks)	Program capacity	Memory capacity for variables	Number of motion axes	Number of CNC axes	Database Connection function	SECS/GEM Communication function	Number of	Number of controlled OMRON robots	Model
Database			2 MB: Retained during	64						NJ501-1520
Connection CPU Units		20 MB	power interruption 4 MB: Not retained	32						NJ501-1420
	2,560 points / 40 Units		during power interruption	16		Yes	No			NJ501-1320
	(3 Expansion Racks)	3 MB	0.5 MB: Retained during power interruption	2						NJ101-1020
		02	2 MB: Not retained during power interruption	0						NJ101-9020
SECS/GEM CPU Unit				16		No	Yes			NJ501-1340
NJ Robotics				64	0			8 max. *1		NJ501-4500
CPU Units				32						NJ501-4400
										NJ501-4300
				16				1		NJ501-4310
	2,560 points /		2 MB: Retained during			Yes				NJ501-4320
Robot Integrated	40 Units	20 MB	power interruption 4 MB: Not retained			No				NJ501-R500
CPU Units	(3 Expansion Racks)		during power interruption	04		Yes				NJ501-R520
MI NAS				32		No	No	8 max. *1	8 max.	NJ501-R400
				32		Yes	110		8 max.	NJ501-R420
				16		No				NJ501-R300
				10		Yes				NJ501-R320
NC Integrated Controller				16	16 *2 *3	No				NJ501-5300

^{*1.} The number of controlled robots varies according to the number of axes used for the system.

^{*2.} With a combination of a CPU Unit with CNC version 1.03 or higher and Sysmac Studio version 1.60 or higher, up to 32 axes can be controlled. For a CPU Unit with CNC version 1.02 or lower, the maximum number of motion axes and CNC axes total is 16 axes.
*3. One CNC Operator License (SYSMAC-RTNC0001L) is attached with the CPU Unit.

Accessories

The following accessories come with the CPU Unit.

Product name	Model
Battery	CJ1W-BAT01
End Cover	CJ1W-TER01 (must be attached to the right end of the CPU Rack)
End Plate	PFP-M (2 required)
SD Memory Card (Flash Memory)	NJ501-□□20, NJ501-1340, NJ501-R□□□: HMC-SD492 NJ101-□□20: HMC-SD292

Power Supply Units

One Power Supply Unit is required for each Rack.

Product name	Bower cumply	Output current		Output capacity	Options				
	Power supply voltage	5-VDC output capacity	24-VDC output capacity	Total power consumption	24-VDC service power supply	RUN output	Maintenance forecast monitor	Model	
AC Power Supp	ly Unit	100 to 240 VAC	6.0 A	1.0 A	30 W	No	Yes	No	NJ-PA3001
DC Power Supp	ly Unit	24 VDC							NJ-PD3001

Note: Power supply units for the CJ-Series cannot be used as a power supply for a CPU rack of the NJ system or as a power supply for an expansion rack.

Expansion Racks

Select the I/O Control Unit, I/O Interface Unit, Expansion Connecting Cable, and Power Supply Unit.

CJ-Series I/O Control Unit (Mounted on CPU Rack when Connecting Expansion Racks)

Product name	Specifications		rent ption (A)	Model
			24 V	
	Mount one I/O Control Unit on the CJ-Series CPU Rack when connecting one NJ-Series Expansion Racks. Connecting Cable: CS1W-CN□□3 Expansion Connecting Cable Connected Unit: CJ1W-II101 I/O Interface Unit Mount to the right of the CPU Unit.	0.02		CJ1W-IC101

Note: Mounting the I/O Control Unit in any other location may cause faulty operation.

CJ-Series I/O Interface Unit (Mounted on Expansion Rack)

Product Name	Specifications		rent ption (A)	Model	
			24 V		
	One I/O Interface Unit is required on each Expansion Rack. Connecting Cable: CS1W-CN□□3 Expansion Connecting Cable Mount to the right of the Power Supply Unit.	0.13		CJ1W-II101	

Note: Mounting the I/O Interface Unit in any other location may cause faulty operation.

I/O Connecting Cables

Product name	Specifications	Model	
I/O Connecting Cable		Cable length: 0.3 m	CS1W-CN313
	Connects an I/O Control Unit on NJ-Series CPU Rack to an I/O Interface Unit on a NJ-Series Expansion Rack. or Connects an I/O Interface Unit on NJ-Series Expansion Rack to an I/O Interface Unit on another NJ-Series Expansion Rack.	Cable length: 0.7 m	CS1W-CN713
		Cable length: 2 m	CS1W-CN223
		Cable length: 3 m	CS1W-CN323
		Cable length: 5 m	CS1W-CN523
	an 1/0 interface officion another No-oeries Expansion Nack.	Cable length: 10 m	CS1W-CN133
		Cable length: 12 m	CS1W-CN133-B2

Automation Software Sysmac Studio

The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slave, and the HMI.

For details, refer to your local OMRON website and Sysmac Studio Catalog (Cat. No. P138).

Collection of software functional components Sysmac Library

Please download it from following URL and install to Sysmac Studio. https://www.ia.omron.com/sysmac_library/

Typical Models

Product	Features	Model
Vibration Suppression Library	The Vibration Suppression Library is used to suppress residual vibration caused by the operation of machines.	SYSMAC-XR006
Device Operation Monitor Library	The Device Operation Monitor Library is used to monitor the operation of devices such as air cylinders, sensors, motors, and other devices.	SYSMAC-XR008
Dimension Measurement Library	The Dimension Measurement Library is used to dimension measurement with ZW-8000/7000/5000 Confocal Fiber Displacement Sensor, or E9NC-TA0 Contact-Type Smart Sensor.	SYSMAC-XR014

SECS/GEM Configurator (For NJ-series SECS/GEM CPU Unit NJ501-1340)

Please purchase the required number of SECS/GEM Configurator licenses and a Sysmac Studio Standard Edition DVD the first time you purchase the SECS/GEM Configurator.

The Sysmac Studio Standard Edition DVD includes the SECS/GEM Configurator. The license does not include the DVD.

	Specifications			
Product Name		Number of licenses	Media	Model
SECS/GEM Configurator	The SECS/GEM Configurator is the software to make HSMS, SECSII and GEM settings for NJ501 SECS/GEM CPU Units.	1 license		WS02-GCTL1
VOI.1.	The software is included in the Sysmac Studio Standard Edition DVD.			

Operation Software CNC Operator (For NJ-series NC Integrated Controller NJ501-5300)

Please purchase a DVD or download it from following URL.

http://www.ia.omron.com/cnc-operator/

One CNC Operator License (SYSMAC-RTNC0001L) is attached with the CPU Unit.

	Specifications			
Product Name		Number of licenses	Media	Model
CNC Operator	The CNC Operator is the software that provides a operation interface for	(Installer only)	(Download)	SYSMAC-RTNC0000
	NC programming, debugging and maintenance of CNC machine.	 (Media only)	DVD	SYSMAC-RTNC0000D
CNC Operator License	The one license key (hardware key, USB dongle). The CNC Operator needs license key.	1 license		SYSMAC-RTNC0001L
CNC Operator Software Development Kit	The CNC Operator Software Development Kit provides a environment for customization of CNC Operator. Supported execution environment: NET Framework (4.6.1) Development environment: Visual Studio 2013/2015 Development languages: C#		DVD	SYSMAC-RTNC0101D

Recommended EtherCAT and EtherNet/IP Communications Cables

Use a straight STP (shielded twisted-pair) cable of category 5 or higher with double shielding (aluminum tape and braiding) for EtherCAT. For EtherNet/IP, required specification for the communications cables varies depending on the baud rate.

For 100BASE-TX/10BASE-T, use a straight or cross STP (shielded twisted-pair) cable of category 5 or higher.

For 1000BASE-T, use a straight or cross STP cable of category 5e or higher with double shielding (aluminum tape and braiding).

Cable with Connectors

	Recommended manufacturer	Cable length (m)	Model	
	Cable with Connectors on Both Ends (RJ45/RJ45)	OMRON	0.3	XS6W-6PUR8SS30CM-YF
	Standard RJ45 plug type *1 Cable color: Yellow *2		0.5	XS6W-6PUR8SS50CM-YF
Vire Gauge and Number of Pairs:	EtherCAT/		1	XS6W-6PUR8SS100CM-YF
WG26, 4-pair Cable Cable Sheath material: PUR	EtherNet/IP (10BASE/100BASE/1000BASE *4)		2	XS6W-6PUR8SS200CM-YF
			3	XS6W-6PUR8SS300CM-YF
	,		5	XS6W-6PUR8SS500CM-YF
	Cable with Connectors on Both Ends (RJ45/RJ45)	OMRON	0.3	XS5W-T421-AMD-K
	Rugged RJ45 plug type *1		0.5	XS5W-T421-BMD-K
	Cable color: Light blue EtherCAT/		1	XS5W-T421-CMD-K
	EtherNet/IP (10BASE/100BASE)		2	XS5W-T421-DMD-K
			5	XS5W-T421-GMD-K
			10	XS5W-T421-JMD-K
	Cable with Connectors on Both Ends (M12 Straight/M12 Straight) Shield Strengthening Connector cable *3 M12/Smartclick Connectors Cable color: Black EtherCAT/ EtherNet/IP (10BASE/100BASE)	OMRON	0.5	XS5W-T421-BM2-SS
			1	XS5W-T421-CM2-SS
			2	XS5W-T421-DM2-SS
Vire Gauge and Number of Pairs: .WG22, 2-pair cable			3	XS5W-T421-EM2-SS
WVOZZ, Z-paii dabio			5	XS5W-T421-GM2-SS
	-0		10	XS5W-T421-JM2-SS
	Cable with Connectors on Both Ends (M12 Straight/RJ45)	OMRON	0.5	XS5W-T421-BMC-SS
	Shield Strengthening Connector cable *3 M12/Smartclick Connectors		1	XS5W-T421-CMC-SS
	Rugged RJ45 plug type Cable color: Black		2	XS5W-T421-DMC-SS
	EtherCAT/ EtherNet/IP (10BASE/100BASE)		3	XS5W-T421-EMC-SS
	(105.102)1005.102)		5	XS5W-T421-GMC-SS
	0		10	XS5W-T421-JMC-SS

^{*1.} Cables with standard RJ45 plugs are available in the following lengths: 0.2 m, 0.3 m, 0.5 m, 1 m, 1.5 m, 2 m, 3 m, 5 m, 7.5 m, 10 m, 15 m, 20 m. Cables with rugged RJ45 plugs are available in the following lengths: 0.3 m, 0.5 m, 1 m, 2 m, 3 m, 5 m, 10 m, 15 m. For details, refer to the Industrial Ethernet Connectors Catalog (Cat. No. G019).

Cables / Connectors

	Item		Recommended manufacturer	Model
Products for EtherCAT or EtherNet/IP	Time Caage ama riamber or	Cables	Kuramo Electric Co.	KETH-SB *1
(1000BASE-T*2/100BASE- TX)	Pairs: AWG24, 4-pair Cable	RJ45 Connectors	Panduit Corporation	MPS588-C *1
Products for EtherCAT or	Wire Gauge and Number of Pairs: AWG22, 2-pair Cable	Cables	Kuramo Electric Co.	KETH-PSB-OMR *3
EtherNet/IP			JMACS Japan Co., Ltd.	PNET/B *3
(100BASE-TX/10BASE-T)		RJ45 Assembly Connector	OMRON	XS6G-T421-1 *3

^{*1.} We recommend you to use the above Cable and RJ45 Connector together.

^{*2.} Cable colors are available in yellow, green, and blue.
*3. For details, contact your OMRON representative.

^{*4.} The products can be used only with the NX701/NX502.

^{*2.} The products can be used only with the NX701/NX502.

^{*3.} We recommend you to use the above Cable and RJ45 Assembly Connector together.

Optional Products and Maintenance Products

Product name	Specifications	Model
	SD memory card, 2GB	HMC-SD292
Memory Cards *1	SDHC memory card, 4GB	HMC-SD492
	SDHC memory card, 16GB	HMC-SD1A2

^{*1.} There are restrictions on the combination of CPU Unit version and memory card. Refer to NJ/NX-series CPU Unit Software User's Manual (W501) 8-5-2 Specifications of Supported SD Memory Cards, Folders, and Files for details.

Product name		Model	
Battery Set	Battery for NX701-DDD/NJ501-DDD/NJ301-DDD/NJ101-DDDN/NJ/NX-Series CPU Unit maintenance	 Note: 1. The battery is included as a standard accessory with the CPU Unit. 2. The battery service life is 5 years at 25°C. (The service life depends on the ambient operating temperature and the power conditions.) 3. Use batteries within two years of manufacture. 	CJ1W-BAT01
End Cover	Mounted to the right-hand side of NJ-Series CPU Racks or Expansion Racks.	One End Cover is provided as a standard accessory with each CPU Unit and I/O Interface Unit.	CJ1W-TER01

DIN Track Accessories

Product name	Specifications	Model
DIN Track	Length: 0.5 m; Height: 7.3 mm	PFP-50N
	Length: 1 m; Height: 7.3 mm	PFP-100N
	Length: 1 m; Height: 16 mm	PFP-100N2
End Plate	There are 2 stoppers provided with CPU Units and I/O Interface Units as standard accessories to secure the Units on the DIN Track.	PFP-M

Basic I/O Units Input Units

Unit	Unit classification Product name		Specifi	cations		Number of bits	Respons	se time *1	consu	rent mption A)	Model
Classification		I/O points	Input voltage and current	Commons	External connection	allocated	ON	OFF	5 V	24 V	
		8 inputs	12 to 24 VDC, 10 mA	Independent contacts	Removable terminal block	16	20 μs max.	400 μs max.	0.08		CJ1W-ID201
	DC Input Units	16 inputs	24 VDC, 7 mA	16 points, 1 common	Removable terminal block	16	20 μs max.	400 μs max.	0.08		CJ1W-ID211
		16 inputs High-speed type	24 VDC, 7 mA	16 points, 1 common	Removable terminal block	16	15 µs max.	90 μs max.	0.13		CJ1W-ID212
		32 inputs	24 VDC, 4.1 mA	16 points, 1 common	Fujitsu/OTAX connector	32	20 µs max.	400 μs max.	0.09		CJ1W-ID231 *2
CJ1		32 inputs	24 VDC, 4.1 mA	16 points, 1 common	MIL connector	32	20 μs max.	400 μs max.	0.09		CJ1W-ID232 *2
Basic I/O Units		32 inputs High-speed type	24 VDC, 4.1 mA	16 points, 1 common	MIL connector	32	15 µs max.	90 μs max.	0.20		CJ1W-ID233 *2
		64 inputs	24 VDC, 4.1 mA	16 points, 1 common	Fujitsu/OTAX connector	64	120 µs max.	400 μs max.	0.09		CJ1W-ID261 *2
	AC Input Units	64 inputs	24 VDC, 4.1 mA	16 points, 1 common	MIL connector	64	120 μs max.	400 μs max.	0.09		CJ1W-ID262 *2
		8 inputs	200 to 24 VAC, 10 mA (200 V, 50 Hz)	8 points, 1 common	Removable Terminal Block	16	10 μs max.	40 μs max.	0.08		CJ1W-IA201
		16 inputs	100 to 120 VAC, 7 mA (100 V, 50 Hz)	16 points, 1 common	Removable Terminal Block	16	10 μs max.	40 μs max.	0.09		CJ1W-IA111

^{*1} This is the input response time when no filter (i.e., 0 ms) is set.

*2 The cable-side connector is not provided with Units equipped with cables. Purchase the 40-pin connector separately (Refer to page 11), or use an OMRON XW2K Series Datasheet (Cat. No. G152) and XW2R Datasheet or a G7□ I/O Relay Terminal.

Output Units

Unit classification Product name				Specifications			Number of bits	Current consumption (A)		Model
Classification		Output type	I/O points	Maximum switching capacity	Commons	External connection	allocated	5 V	24 V	
	Relay Contact Output Units	-	8 outputs	250 VAC/24 VDC, 2 A	Independent contacts	Removable terminal block	16	0.09	0.048 max.	CJ1W-OC201
	transcription (A)	-	16 outputs	250 VAC/24 VDC, 2 A	16 points, 1 common	Removable terminal block	16	0.11	0.096 max.	CJ1W-OC211
	Triac Output Unit	-	8 outputs	250 VAC, 0.6 A	8 points, 1 common	Removable terminal block	16	0.22	-	CJ1W-OA201*1 CJ1W-OA201-1
		Sinking	8 outputs	12 to 24 VDC, 2 A	4 points, 1 common	Removable terminal block	16	0.09	-	CJ1W-OD201
		Sinking	8 outputs	12 to 24 VDC, 0.5 A	8 points, 1 common	Removable terminal block	16	0.10	-	CJ1W-OD203
		Sinking	16 outputs	12 to 24 VDC, 0.5 A	16 points, 1 common	Removable terminal block	16	0.10	-	CJ1W-OD211 *2
CJ1 Basic	Transistor Output Units	Sinking	16 outputs High-speed type	24 VDC, 0.5 A	16 points, 1 common	Removable terminal block	16	0.15	-	CJ1W-OD213 *2
I/O Units		Sinking	32 outputs	12 to 24 VDC, 0.5 A	16 points, 1 common	Fujitsu/OTAX connector	32	0.14	_	CJ1W-OD231 *3
		Sinking	32 outputs	12 to 24 VDC, 0.5 A	16 points, 1 common	MIL connector	32	0.14	-	CJ1W-OD233 *2, *3
		Sinking	32 outputs High-speed type	24 VDC, 0.5 A	16 points, 1 common	MIL connector	32	0.22	_	CJ1W-OD234 *2, *3
		Sinking	64 outputs	12 to 24 VDC, 0.3 A	16 points, 1 common	Fujitsu/OTAX connector	64	0.17	-	CJ1W-OD261 *3
		Sinking	64 outputs	12 to 24 VDC, 0.3 A	16 points, 1 common	MIL connector	64	0.17	-	CJ1W-OD263 *3
		Sourcing	8 outputs	24 VDC, 2 A Short-circuit protection	4 points, 1 common	Removable terminal block	16 *1	0.11	-	CJ1W-OD202
		Sourcing	8 outputs	24 VDC, 0.5 A Short-circuit protection	8 points, 1 common	Removable terminal block	16 *1	0.10	-	CJ1W-OD204
		Sourcing	16 outputs	24 VDC, 0.5 A Short-circuit protection	16 points, 1 common	Removable terminal block	16	0.10	-	CJ1W-OD212
		Sourcing	32outputs	24 VDC, 0.5 A Short-circuit protection	16 points, 1 common	MIL connector	32	0.15	-	CJ1W-OD232 *3
		Sourcing	64 outputs	12 to 24 VDC, 0.3 A	16 points, 1 common	MIL connector	64	0.17	_	CJ1W-OD262 *3

^{*1} CJ1W-OA201 is not UC1 cULus (Class I Division 2 hazardous location certification). If cULus (Class I Div 2 hazardous location certification) is required, use CJ1W-OA201-1.
*2 The ON/OFF response time for the CJ1W-OD213/CJ1W-OD234 is shorter than for the CJ1W-OD211/CJ1WOD233, as shown below.

• ON response time: 0.1 ms improved to 0.015 ms

[·] OFF response time: 0.8 ms improved to 0.08 ms

^{*3} Connectors are not provided with these connector models. Either purchase one of the following 40-pin Connectors, or use an OMRON XW2K Series Datasheet (Cat. No. G152) and XW2R Datasheet or a G7□ I/O Relay Terminal.

I/O Units

				Specifications			N of the second	Current consumption (A)		
Unit classification	Product name	Output type	I/O points	Input voltage, Input current	Commons	External	Number of bits allocated	5 V	24 V	Model
		output typo	" o pomio	Maximum switching capacity		connection			24.	
		Sinking	16 inputs	24 VDC, 7 mA	16 points, 1 common	Fujitsu/OTAX	32	0.13		CJ1W-MD231
		Siriking	16 outputs	250 VAC/24 VDC, 0.5 A	16 points, 1 common	connector	32	0.13		*2
	DC Input/ Transis-	Cialda -	16 inputs	24 VDC, 7 mA	16 points, 1 common	NAU	64	0.13		CJ1W-MD233
	tor Out- put Units	Sinking	16 outputs	12 to 24 VDC, 0.5 A	16 points, 1 common	MIL connector	64	0.13		*2
		Sinking	32 inputs	24 VDC, 4.1 mA	16 points, 1 common	Fujitsu/OTAX connector	32	0.14		CJ1W-MD261
			32 outputs	12 to 24 VDC, 0.3 A	16 points, 1 common		32	3.11		*1
CJ1 Basic		0:1:	32 inputs	24 VDC, 4.1 mA	16 points, 1 common	- MIL connector	64	0.14		CJ1W-MD263
I/O Units		Sinking	32 outputs	12 to 24 VDC, 0.3 A	16 points, 1 common	- MIL Connector	04	0.14		*1
		0	16 inputs	24 VDC, 7 mA	16 points, 1 common	MIL connector	20	0.13		CJ1W-MD232
		Sourcing	16 outputs	24 VDC, 0.5 A Short-circuit protection	16 points, 1 common	- MIL Connector	32			*2
	TTL I/O Units		32 inputs	5 VDC, 35 mA	16 points, 1 common					CJ1W-MD563
			32 outputs	5 VDC, 35 mA	16 points, 1 common	- MIL connector	64	0.19		*1

^{*1} Connectors are not provided with these connector models. Either purchase one of the following 40-pin Connectors, or use an OMRON XW2K Series Datasheet (Cat. No. G152) and XW2R Datasheet or a G7 I/O Relay Terminal.

Applicable Connectors

Fujitsu/OTAX Connectors for 32-input, 32-output, 64-input, 64-output, 32-input/32-output, and 16-input/16-output Units

Name	Connection		Remarks	Applicable Units	Model
40-pin Connectors	Soldered	Connector Connector Cover	Fujitsu FCN-361J040-AU Fujitsu FCN-360C040-J2 OTAX N360C040J2	Fujitsu/OTAX Connectors: CJ1W-ID231(32 inputs): 1 per Unit CJ1W-ID261 (64 inputs) 2 per Unit	C500-CE404
	Crimped	Housing Contactor Connector Cover	Fujitsu FCN-363J040 OTAX N363J040 Fujitsu FCN-363J-AU OTAX N363JAU Fujitsu FCN-360C040-J2 OTAX N360C040J2	CJ1W-ID261 (64 Iniputs) 2 per Unit CJ1W-OD261 (64 outputs): 1 per Unit CJ1W-MD261 (64 outputs): 2 per Unit CJ1W-MD261 (32 inputs, 32 outputs): 2 per Unit	C500-CE405
	Pressure welded	Fujitsu FCN-367J	040-AU/F		C500-CE403
24-pin Connectors	Soldered	Connector Connector Cover	Fujitsu FCN-361J024-AU Fujitsu FCN-360C024-J2 OTAX N360C024J2	Fujitsu/OTAX Connectors: CJ1W-MD231 (16 inputs, 16 outputs): 2 per Unit	C500-CE241
	Pressure welded	Fujitsu FCN-367J OTAX N367J024A			C500-CE243

MIL Connectors for 32-input, 32-output, 64-input, 64-output, 32-input/32-output, and 16-input/16-output Units

Name	Connection	Remarks	Applicable Units	Model
40-pin Connectors	Pressure welded	FRC5-AO40-3TOS	MIL Connectors: CJ1W-ID232/233 (32 inputs): 1 per Unit CJ1W-OD232/233/234 (32 outputs):1 per Unit CJ1W-ID262 (64 inputs): 2 per Unit CJ1W-OD262/263 (64 outputs): 2 per Unit CJ1W-MD263/563 (32 inputs, 32 outputs): 2 per Unit	XG4M-4030-T
20-pin Connectors	Pressure welded	FRC5-AO20-3TOS	MIL Connectors: CJ1W-MD232/233 (16 inputs, 16 outputs): 2 per Unit	XG4M-2030-T

^{*2} Connectors are not provided with these connector models. Either purchase one of the following 20-pin or 24-pin Connectors, or use an OMRON XW2K Series Datasheet (Cat. No. G152) and XW2R Datasheet or a G7 l/O Relay Terminal.


Applicable Connector-terminal block conversion unit

Example: With OMRON Connector-terminal block conversion unit


Only main products are shown here.

More detail informations are shown in XW2K Series Datasheet (Cat. No. G152) and XW2R Datasheet.


32-point Input Unit or Output Unit CJ1W-ID231 32-point



64-point Input Unit or Output Unit CJ1W-ID261 64-point



64-point Output UnitCJ1W-MD563 IN 32 Points, OUT 32 Points



Choose the wiring method.

Choose $\square\square$ from a following combination table PLC type.

Wiring method	Model
Models with Push-In Plus	XW2K-40G-O32□
Models with Phillips screw	XW2R-J34GD-C□
Models with Slotted screw (rise up)	XW2R-E34GD-C□

Combination table

PLC Type (Connector-terminal block)			PLC		Connecting askins							
XW2K	XW2R	1/0	I/O Points	I/O unit model	Connecting cables							
		lanut	32	CJ1W-ID231	XW2Z-□□□B							
O32A	C1	Input	64	CJ1W-ID261	32-point Unit: 1 Cable							
		Input/Output	32	CJ1W-MD261 (inputs)	64-point Unit: 2 Cables							
			32	CJ1W-ID232								
		Input	32	CJ1W-ID233	XW2Z-□□□K							
O32C	C2		64	CJ1W-ID262	32-point Unit: 1 Cable							
		I +/O++	20	CJ1W-MD263 (inputs)	64-point Unit: 2 Cables							
		Input/Output	32	CJ1W-MD563 (inputs)								
		lancet	32	CJ1W-OD231	XW2Z-□□□B							
O32B	C3	C3	C3	C3	C3	C3	C3	C3	Input	64	CJ1W-OD261	32-point Unit: 1 Cable
		Input/Output	32	CJ1W-MD261 (outputs)	64-point Unit: 2 Cables							
				CJ1W-OD232								
				32	CJ1W-OD233							
		Output		CJ1W-OD234	XW2Z-□□□K							
O32C	C4		64	CJ1W-OD262	32-point Unit: 1 Cable							
			64	CJ1W-OD263	64-point Unit: 2 Cables							
		I +/O++	22	CJ1W-MD263 (outputs)								
		Input/Output	32	CJ1W-MD563 (outputs)								

Note: 1. $\square\square\square$ is replaced by the cable length.

2. There is one common for each 32 points.

Connector-terminal block conversion unit

Product name	Specifications	I/O Points (number of poles)	Model
	Push-In Plus	32 (36)	XW2K-40G-O32A
		32 (36)	XW2K-40G-O32B
		32 (36)	XW2K-40G-O32C
	Phillips screw	32 (34)	XW2R-J34GD-C1
0		32 (34)	XW2R-J34GD-C2
Connector-Terminal Block Conversion Unit		32 (34)	XW2R-J34GD-C3
	*	32 (34)	XW2R-J34GD-C4
	Slotted screw	32 (34)	XW2R-E34GD-C1
	(rise up)	32 (34)	XW2R-E34GD-C2
		32 (34)	XW2R-E34GD-C3
	₹/	32 (34)	XW2R-E34GD-C4

Connecting cables

Product name	Appearance	Connectors	Model	Cable length (m)
	XW2Z-□□B		XW2Z-050B	0.5
			XW2Z-100B	1
		One 40-pin FCN Connector to	XW2Z-150B	1.5
		One 40-pin MIL Connector	XW2Z-200B	2
			XW2Z-300B	3
or I/O Unit Connecting			XW2Z-500B	5
able	XW2Z-□□□K	One 40-pin MIL Connector to	XW2Z-C50K	0.5
			XW2Z-100K	1
			XW2Z-150K	1.5
		One 40-pin MIL Connector	XW2Z-200K	2
			XW2Z-300K	3
			XW2Z-500K	5

Quick-response Input Units

Unit clas-	Product		Specif	fications		Number of bits allo- cated	Response time		Current con- sumption (A)		
sification		I/O points	Input voltage, Input current	Commons	External connection		ON	OFF	5 V	24 V	Model
CJ1 Basic I/O Units	Quick- response Input Unit	16 inputs	24 VDC, 7 mA	16 points, 1 common	Removable terminal block	16	0.05 ms max.	0.5 ms max.	0.08		CJ1W-IDP01

Special I/O Units and CPU Bus Units

Process I/O Units

Isolated-type Units with Universal Inputs

Unit clas-	Product name	Input	Signal range	Signal range	Conversion speed	Accuracy (at ambient tempera-		No. of unit numbers		nt con- ion (A)	Model
Silication	name	points	selection		(resolution)	ture of 25°C)	tion	allocated	5 V	24 V	
CJ1 Special I/O Units	Process Input Units (Isolated- type Units with Uni- versal Inputs)	4 inputs	Set sepa- rately for each input	Universal inputs: Pt100 (3-wire), JPt100 (3-wire), Pt1000 (3-wire), Pt1000 (3-wire), Pt100 (4-wire), K, J, T, E, L, U, N, R, S, B, WRe5-26, PL II, 4 to 20 mA, 0 to 20 mA, 1 to 5 V, 0 to 1.25 V, 0 to 5 V, 0 to 10 V, ±100 mV selectable range -1.25 to 1.25 V, -5 to 5 V, -10 to 10 V, ±10 V selectable range, potentiometer	Resolution (conversion speed): 1/256,000 (conversion cycle: 60 ms/ 4 inputs) 1/64,000 (con- version cycle: 10 ms/ 4 inputs) 1/16,000 (con- version cycle: 5 ms/ 4 inputs)	Standard accuracy: ±0.05% of F.S.	Remov- able ter- minal block	1	0.30		CJ1W-PH41U *1
		4 inputs	Set sepa- rately for each input	Universal inputs: Pt100, JPt100, Pt1000, K, J, T, L, R, S, B, 4 to 20 mA, 0 to 20 mA, 1 to 5 V, 0 to 5 V, 0 to 10 V	Conversion speed: 250 ms/ 4 inputs	Accuracy: Platinum resistance thermometer input: (±0.3% of PV or ±0.8°C, whichever is larger) ±1 digit max. Thermocouple input: (±0.3% of PV or ±1.5°C, whichever is larger) ±1 digit max. *2 Voltage or current input: ±0.3% of F.S. ±1 digit max.			0.32		CJ1W-AD04U

^{*1} Do not connect a Relay Output Unit to the same CPU Rack or to the same Expansion Rack as the CJ1W-PH41U.

Isolated-type DC Input Units

Unit clas-		Input	Signal range selection	Conversion speed	Accuracy (at ambient tem-	connection	No. of unit numbers		nt con- ion (A)	Model
Silication	name	points	(resolution) perature of 25°C) connection alloc		allocated	5 V	24 V			
CJ1 Special I/O Units	Isolated- type DC Input Units	2 inputs	DC voltage: 0 to 1.25 V, -1.25 to 1.25 V, 0 to 5 V, 1 to 5 V, -5 to 5 V, 0 to 10 V, -10 to 10 V, ±10 V selectable range DC current: 0 to 20 mA, 4 to 20 mA	Conversion speed: 10 ms/ 2 inputs Resolution: 1/ 64,000	Standard accuracy: ±0.05% of F.S.	Removable terminal block	1	0.18	0.09 *	CJ1W-PDC15

^{*} This is for an external power supply, and not for internal current consumption.

^{*2} L and -100°C or less for K and T are ±2°C±1 digit max., and 200°C or less for R and S is ±3°C±1 digit max. No accuracy is specified for 400°C or less for B.

Analog I/O Units Analog Input Units

Unit clas-	Product name	Input points	Signal range selection	Signal range	Resolution	Conversion speed	Accuracy (at ambient temperature of	connec-	No. of unit	COHOUNE		Model
			Selection				25°C)	tion	anocateu	5 V	24 V	
CJ1 Special	Analog Input Units	4 inputs	Set sep- arately for each	1 to 5 V (1/10 0 to 10 V (1/2 -5 to 5 V (1/2 -10 to 10 V (1/2 4 to 20 mA (1	0,000), 0,000), 1/40,000), and	20 μs/1 point, 25 μs/2 points, 30 μs/3 points, 35 μs/4 points	Voltage: ±0.2% of F.S. Current: ±0.4% of F.S.	Remov- able terminal	1	0.52		CJ1W-AD042 *1
Units	Analog Input Units	8 inputs	input	1 to 5 V, 0 to 5 V, 0 to 10 V, –	1/4000, (Settable to	1 ms/point max. (Settable to	Voltage: ±0.2% of F.S.	block		0.42		CJ1W-AD081-V1
	Table and the second se	4 inputs		10 to 10 V, 4 to 20 mA	1/8000)	250 μs/point) *2	Current: ±0.4% of F.S. *3			0.42		CJ1W-AD041-V1

^{*1} The direct conversion function using the AIDC instruction cannot be used.

Analog Output Units

Unit clas-		Output	Signal range	Signal	Resolution	Conver-	Accuracy (at ambient	External connec-	External	No. of unit		ent con- etion (A)	Model
sification	name	points	selection	range		speed	temperature of 25°C)	tion	power supply	allocated	5 V	24 V	
	Analog Output Units	4 outputs		1 to 5 V (1/1/1) 0 to 10 V (1/2) and -10 to 10 V (20,000),	20 μs/ 1 point, 25 μs/ 2 points, 30 μs/ 3 points, 35 μs/ 4 points	±0.3% of F.S.				0.40		CJ1W-DA042V *1
CJ1 Special I/O Units	Analog	8 outputs	Set sep- arately for each input	1 to 5 V, 0 5 to 5 V, 0 to 10 V, -10 to 10 V	1/4,000 (Settable	1 ms/ point max. (Settable		Remov- able ter- minal block	24 VDC ⁺¹⁰ % 140 mA max.	1	0.14	0.14	CJ1W-DA08V
	Units Analog Output Units	nalog input input 8 outputs 4 outputs	4 to 20 mA	1/8,000)	to 250 μs/point)			24 VDC ^{+10%} , 170 mA max.		0.14	0.17 *2	CJ1W-DA08C	
				1 to 5 V, 0 to 5 V, 0 to 10 V,	1/4000	1 ms/	Voltage output: ±0.3% of F.S.		24 VDC ^{+10%} , 200 mA max.		0.12	0.2 *2	CJ1W-DA041
	2 outputs		-10 to 10 V, -10 to 10 V, 4 to 20 mA	1/4000	point max.	Current output: ±0.5% of F.S.		24 VDC ^{+10%} , 140 mA max.		0.12	0.14	CJ1W-DA021	

^{*1} The direct conversion function using the AODC instruction cannot be used.

Analog I/O Units

Unit clas-		No. of points	Signal range selection	- 3	Resolution (See note.)		(at ambient tem-	External connection	No. of unit numbers allocated		rent ump- ı (A)	Model
			Sciection			(See Hote.)	perature or 25 c)		anocateu	5 V	24 V	
CJ1 Special	Analog I/O Units	4 inputs	Set sepa-	1 to 5 V, 0 to 5 V,	1/4,000 (Settable	1 ms/point (Settable to	Voltage input: ±0.2% of F.S. Current input: ±0.2% of F.S.	Remov-	4	0.50		C IAW MADA2
Special I/O Units		rately for each input	0 to 10 V, -10 to 10 V, 4 to 20 mA	to 1/8,000)	Settable to 500 μs/ point max.)	Voltage output: ±0.3% of F.S. Current output: ±0.3% of F.S.	able termi- nal block	1	0.58		CJ1W-MAD42	

Note: The resolution and conversion speed cannot be set independently. If the resolution is set to 1/4,000, then the conversion speed will be 1 ms/point.

^{*2} The resolution and conversion speed cannot be set independently. If the resolution is set to 1/4,000, then the conversion speed will be 1 ms/ point. *3 At 23 ±2°C

^{*2} This is for an external power supply, and not for internal current consumption

Temperature Control Units

Unit classifi-	Product		Specifications			Current con- sumption (A)		Model
cation	name	No. of loops	Temperature sensor inputs	Control outputs	numbers allocated	5 V	24 V	Wodel
	Tempera-		Thermocouple input	Open collector NPN outputs (pulses)		0.25		CJ1W-TC003
CJ1 Spe-	ture Con- trol Units	2 loops, heater	(R, S, K, J, T, B, L)	Open collector PNP outputs (pulses)		0.25		CJ1W-TC004
cial I/O Units		burnout detection function	Platinum resistance thermometer input	Open collector NPN outputs (pulses)	2	0.25		CJ1W-TC103
			(JPt100, Pt100)	Open collector PNP outputs (pulses)		0.25		CJ1W-TC104

High-speed Counter Unit

Unit classifi-	Product		Specifications			Current con- sumption (A)		Model
cation	name	Countable channels	Encoder A and B inputs, pulse input Z signals	Max. counting rate	numbers allocated	5 V	24 V	Woder
CJ1 Spe-	High- speed Counter Unit		Open collector Input voltage: 5 VDC, 12 V, or 24 V (5 V and 12 V are each for one axis only.)	50 kHz				
cial I/O Units		2	RS-422 line driver	500 kHz	4	0.28		CJ1W-CT021

Note: The following functions become unavailable when it is used with the NJ-Series CPU unit.

- Counter value capture using allocation area(CIO)
- The capture, Stop/capture/continue, Stop/capture/reset/continue, and Capture/reset functions using External Control Input Function
- Pulse rate range control using Output Control Mode
- The pulse rate measurement function
- Because the NJ-Series has no power OFF interrupt task, operation cannot be restarted from the position at which the power was interrupted.
- Read or write the data using IORD/IOWR instruction
- Starting of External Interrupt Task by Output and External Control Input

Serial Communications Units

Unit clas-	Product name	s	Specifications	No. of unit numbers	Current con- sumption (A)		Model
sification		Communications Interface	Communications functions	allocated	5 V	24 V	
	Serial Com- munications Units High-speed type	2 RS-232C ports	The following functions can be calcuted		0.29 *2		CJ1W-SCU22
CJ1 CPU Bus Units		2 RS-422A/485 ports	The following functions can be selected for each port: Protocol macro *1 Host Link NT Links (1:N mode) Serial Gateway	1	0.46		CJ1W-SCU32
		1 RS-232C port and 1 RS-422A/485 port	No-protocol *3 Modbus-RTU Slave		0.38 *2		CJ1W-SCU42
RS-422A Converter		Converts RS-233C to RS-422				CJ1W-CIF11	

Note: Simple Backup Function and Interrupt notification function cannot be used.

- *1 You can activate protocol macro trace function when the CPU Unit is set to the RUN Mode. (MONITOR Mode is not available with the NJ-Series CPU Units.)
- *2 When an NT-AL'001 RS-232C/RS-422A Conversion Unit is used, this value increases by 0.15 A/Unit. Add 0.20A/Unit when using NV3W-M□20L Programmable Terminals. Add 0.04A/Unit when using CJ1W-CIF11 RS-422A Adapters.

^{*3} Supported only by the SerialRcvNoClear Instructions with Serial communication unit version 2.1 or later, CPU Units with unit version 1.03 or later and the Sysmac Studio version 1.04 or higher.

EtherNet/IP Unit

Unit classifi-			Specifications			Current con- sumption (A)			
cation	name	Communications cable	Communications functions	Max. Units mountable per CPU Unit	numbers r allocated	5 V	24 V	Model	
CJ1 CPU	EtherNet/IP Unit	Shielded twisted-pair (STP) cable	Tag Data Link Functions, Message Communications Functions, Socket Service Functions	4	1	0.65		CJ1W-EIP21S *1	
Bus Unit		Categories: 100 Ω at 5, 5e	Tag Data Link Functions, Message Communications Functions	4	'	0.41		CJ1W-EIP21 *1, *2	

^{*1} EtherNet/IP Unit with unit version 1.0 or later (Lot number 241001□ or later) is required to connect CJ1W-EIP21S to NJ-series CPU Unit. Use NJ-series CPU Unit with version 1.67 or later and Sysmac Studio with version 1.60 or later.

EtherNet/IP Unit with unit version 2.1 or later is required to connect CJ1W-EIP21 to NJ-series CPU Unit. Use NJ-series CPU Unit with version 1.01 or later and Sysmac Studio with version 1.02 or later.

EtherCAT Slave Unit

Unit classifi-	Product name	Specifications	Communications type	No. of unit numbers	Current con- sumption (A)		Model	
Cation				allocated	5 V	24 V		
CJ1 CPU Bus Units	EtherCAT Slave Unit	STP (shielded twisted-pair) cable of category 5 or higher with double shielding	Refreshing methods: Free-Run Mode PDO DATA SIZE: TxPDO 400byte or less/RxPDO: 400byte or less	1	0.34		CJ1W-ECT21 *	

^{*} When using with the Machine Automation Controller NJ /NXSeries, use CPU Units with unit version 1.10 or later and the Sysmac Studio version 1.13 or higher.

DeviceNet Unit

Unit classifi-	Product name	Specifications	Communications type	No. of unit numbers	Current con- sumption (A)		Model
Cation				allocated	5 V	24 V	
CJ1 CPU Bus Units	DeviceNet Unit	Functions as master and/or slave; allows control of 32,000 points max. per master.	Remote I/O communications master (fixed or user-set allocations) Remote I/O communications slave (fixed or user-set allocations) Message communications	1	0.29		CJ1W-DRM21

Note: 1. Simple backup function cannot be used.

CompoNet Master Unit

Unit classifi-	Product name		No. of unit	Current con- sumption (A)		Model		
cation	Froduct name	Communications functions	No. of I/O points per Master Unit	allocated	5 V	24 V	Wodel	
CJ1 Special I/O Units	CompoNet Master Unit	Remote I/O communications Message communications	Word Slaves: 2,048 max. (1.024 inputs and 1,024 outputs) Bit Slaves: 512 max. (256 inputs and 256 outputs)	1, 2, 4, or 8	0.4		CJ1W-CRM21 *	

Note: 1. Simple backup function cannot be used.

^{*2} Product no longer available to order.

^{2.} DeviceNet configurator cannot be used. Use CX-Integrator.

^{2.} The FINS command to the CompoNet Master Unit cannot be issued.

* Supported only by the CPU Units with unit version 1.01 or later and the Sysmac Studio version 1.02 or higher.

ID Sensor Units

Unit classifi-	Product name	Specifications			No. of unit	Current con- sumption (A)		Model	
cation	1 Toddet Hame	Connected ID Systems	No. of connected R/W heads	External power supply	allocated	5 V	24 V	inidud:	
CJ1 CPU	ID Sensor Units	V680-Series RFID System 2	1		1	0.26	0.13 *	CJ1W-V680C11	
Bus Units			Not required.	2	0.32	0.26	CJ1W-V680C12		

Peripheral Devices EtherCAT junction slaves

Product	name	No. of ports	Power supply voltage	Current consumption (A)	Model
EtherCAT	-therCAT	3	20.4 to 28.8 VDC	0.08	GX-JC03
junction slaves	33. 33. 34.	6	(24 VDC -15 to +20%)	0.17	GX-JC06

Note: 1. Please do not connect EtherCAT junction slaves with OMRON position control unit, Model CJ1W-NC 81/ 82.

2. EtherCAT junction slaves cannot be used for EtherNet/IP and Ethernet.

Industrial Switching Hubs for EtherNet/IP and Ethernet

Product name	Appearance	Functions	No. of ports	Accessories	Current consumption (A)	Model
Industrial Switching Hubs	000 000 000	Quality of Service (QoS): EtherNet/IP control data priority 10/100BASE-TX, Auto-Negotiation	5	Power supply connector	0.07	W4S1-05D

Note: Industrial switching hubs cannot be used for EtherCAT.

WE70 FA WIRELESS LAN UNITS (Final order entry date: The end of June, 2020)

Product name	Applicable region	Туре	Model
	Japan	Access Point (Master)	WE70-AP
	Јаран	Client (Slave)	WE70-CL
WET	Europo	Access Point (Master)	WE70-AP-EU
WE70 FA WIRELESS LAN UNITS	Europe	Client (Slave)	WE70-CL-EU
	U.S	Access Point (Master)	WE70-AP-US *1
	0.3	Client (Slave)	WE70-CL-US *1
	Canada	Access Point (Master)	WE70-AP-CA *2
3.5	Canada	Client (Slave)	WE70-CL-CA *2
	China	Access Point (Master)	WE70-AP-CN
	China	Client (Slave)	WE70-CL-CN

Note: 1. A Pencil Antenna, mounting magnet, and screw mounting bracket are included as accessories. 2. Always use a model that is applicable in your region. Refer to the WE70 Catalog (Cat. No. N154).

The Units will be sold in the USA until the end of May 2016.

Note: The data transfer function using intelligent I/O commands can not be used.

* To use a V680-H01 Antenna, refer to the V680 Series RFID System Catalog (Cat. No. Q151).

From December 2015, the WE70-AP-US and WE70-CL-US can be used in Mexico.

From January 2016, the WE70-AP-CA and WE70-CL-CA can be used in Singapore.

General Specifications

	Maria		Specification						
	Item	NJ501-□□□	NJ301	NJ101					
Enclosure		Mounted in a panel							
Grounding Me	thod	Ground to less than 100 Ω							
Dimensions (h	eight×depth×width)	90 mm × 90 mm × 90 mm							
Weight		550 g (including the End Cover)							
Current Consu	ımption	5 VDC, 1.90 A (including SD Memory 0	Card and End Cover)						
	Ambient Operating Temperature	0 to 55°C							
	Ambient Operating Humidity	10% to 90% (with no condensation)							
	Atmosphere	Must be free from corrosive gases.							
	Ambient Storage Temperature	-20 to 75°C (excluding battery)							
	Altitude	2,000 m or less							
Operation Environment	Pollution Degree	2 or less: Meets IEC 61010-2-201.							
	Noise Immunity	2 kV on power supply line (Conforms to IEC 61000-4-4.)							
	Overvoltage Category	Category II: Meets IEC 61010-2-201.							
	EMC Immunity Level	Zone B							
	Vibration Resistance		Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 to 150 Hz Acceleration of 9.8 m/s² for 100 min in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total)						
	Shock Resistance	Conforms to IEC 60068-2-27. 147 m/s², 3 times in X, Y, and Z direction	ons (100 m/s² for Relay Output Units)						
Pottory	Life *1	5 years at 25°C							
Battery	Model	CJ1W-BAT01							
Applicable Sta	ındards *2	cULus, EU, UKCA, RCM, KC, NK, LR	*3						

^{*1.} This is the value when the power ON time rate is 0% (power OFF).
*2. Refer to the OMRON website (http://www.ia.omron.com/) or consult your OMRON representative for the most recent applicable standards for

^{*3.} Supported only by the CPU Units with unit version 1.01 or later.

Performance Specifications

	Item				NJ501-		NJ3	01-	NJ1	01-	
	iten			□5□0	□4□0	□3□0	1200	1100	1□□0	9□□0	
Brassasina	Instruction	LD instruct	ion	1.1 ns (1.7 n	s or less)		1.6 ns (2.5 ns	or less) *2	3.0 ns (4.5 ns	or less) *2	
Processing Time	Execution Times	Math Instru (for Long R		24 ns or mor	re *1		35 ns or more	*2	63 ns or more	*2	
		Size		20 MB (400 KS)		5 MB (100 KS)		3 MB (60 KS)			
	Program capacity		POU definition	3,000			750		450		
	*3	Number	POU instance	Using Sysmac Studio Ver. 1.05 or lower : 6,000 Using Sysmac Studio Ver. 1.06 or higher : 9,000			Using Sysma Ver. 1.04 or lo Using Sysma Ver. 1.05 or h	ower : 1,500 c Studio	1,800		
		No Retain	Size	4 MB			2 MB				
		Attribute *4	Number	180,000 *5			90,000 *6		22,500		
_	Variables		Size	2 MB			0.5 MB				
Programming capacity	Retain Attribute *7	Number	10,000			Using Sysma 1.04 or lower Using Sysma 1.05 or higher	: 2,500 c Studio Ver.	5,000			
	Data type	Number		2,000			1,000		•		
	Mamagara	CIO Area		6,144 words	(CIO 0 to CIO	O 6143)					
	Memory for CJ-Series Units	Work Area		512 words (V	V0 to W511)						
	(Can be Specified	Holding Are	ea	1,536 words	(H0 to H153	5)					
with AT Specifications for			32,768 words (D0 to D32767)								
Variables.) EM Area					s × 25 banks o E18_32767		32,768 words	×4 banks (E	E0_00000 to E	3_32767) *8	
Mavimum	Maximum	Maximum r CJ unit per Expansion	CPU Rack or	10 Units							
	Number of Connectable	Maximum r		40 Units							
11	Units	Maximum number of NX unit on the system		4,096 (on NX serie	s EtherCAT s	slave terminal)			400 (on NX series		
Unit Configuration	Maximum number	of Expansio	n Racks	3 max.							
-	I/O Capacity		umber of I/O J-series Units	2,560 points max.							
	Danier C	Model		NJ-P□3001	NJ-P□3001						
	Power Supply Unit for CPU Rack and Expansion	Power OFF Detection	AC Power Supply	30 to 45 ms							
	Racks	Time	DC Power Supply	22 to 25 ms							
		Maximum N		Maximum nu	mber of axes	which can be	defined. 15 axes *9	15 axes *9	6 axes		
		Motio	on control axes				which can be		6 axes		
	Number of	Maximum r	umber of used	The Number	1	axes includes	following servo	axes and end	1		
	Controlled Axes			64 axes	32 axes	16 axes	8 axes	4 axes	2 axes		
			motion control axes			1	Il motion contro		1		
		Maximum r	number of axes terpolation axis	64 axes 4 axes per a	32 axes	16 axes	8 axes	4 axes	2 axes		
			axes for circular on axis control	2 axes per a	xes group						
	Maximum Number	·		32 groups							
	Motion Control Pe	Control Period			The same control period as that is used for the process data communications cycle for EtherCAT.						

^{*1.} When the hardware revision for the Unit is A or B.

^{*2.} When the hardware revision for the Unit is A.

^{*3.} This is the capacity for the execution objects and variable tables (including variable names).

^{*4.} Words for CJ-series Units in the Holding, DM, and EM Areas are not included.

^{*5.} The number of variables of the CPU Unit version 1.19 or earlier is 90,000.

^{*6.} The number of variables of the CPU Unit version 1.18 or earlier is 22,500.

^{*7.} Words for CJ-series Units in the CIO and Work Areas are not included.
*8. When the Spool function of the NJ501-□20 is enabled, the DB Connection Service uses E9_0 to E18_32767 (NJ501-1□20).
When the Spool function of the NJ101-□20 is enabled, the DB Connection Service uses E1_0 to E3_32767 (NJ101-□20).

^{*9.} This number of axes is achieved in a combination of a CPU Unit with unit version 1.06 or later and Sysmac Studio version 1.07 or higher. In other combinations, the maximum number of controlled axes is 8 axes (NJ301-1200) or 4 axes (NJ301-1100).

Itam				NJ501-			NJ301- N			J101	
	H	tem		□5□0	□4□0	□3□0	1200	1200 1100 1 0			
	Cams	Number of Cam Data Points	Maximum Points per Cam Table Maximum	65,535 points			1200	1100		90	
Motion Control	Gams		Points for All Cam Tables	1,048,560 points			262,140 points				
		Tables	ımber of Cam	640 tables 160 tables							
	Position Units			Pulses, millime	eters, microme	ters, nanometer	s, degrees or	inches			
	Override Facto			0.00% or 0.019							
	Supported Ser			Sysmac Studio							
Peripheral	Physical Layer	r		USB 2.0-comp	liant B-type co	nnector					
USB Port	Transmission Distance between Hub and Node Number of port										
	<u> </u>			1							
	Physical Layer Frame length				00Base-TX						
				1514 max.							
	Media Access	Method		CSMA/CD							
	Modulation			Baseband							
	Topology			Star							
	Baud Rate 100 Mbps (100Base-TX)										
	Transmission	Media		STP (shielded	twisted-pair)	cable of Etherne	et category 5,	5e or higher			
	Maximum Trar between Ether			100m							
	Maximum Nun	ber of Cascac	le Connections	There are no r	estrictions if Et	hernet switch is	used.				
		Maximum Nu nections	ımber of Con-	32							
		Packet interv	/al *10	1 to 10,000 ms Can be set for of nodes.)		ements *11 on. (Data will be	refreshed at	the set interva	al, regardless	of the number	
		Permissible Communicat	ions Band	3,000 pps *12	*13 (including	heartbeat)					
	CIP service:	Maximum Nu Tag Sets	ımber of	32							
Built-in	Tag Data	Tag types		Network variables, CIO, Work, Holding, DM, and EM Areas							
EtherNet/IP Port	Links (Cyclic	Number of ta tion (i.e., per	igs per connec- tag set)	8 (7 tags if Controller status is included in the tag set.)							
	Communicati ons)		nk Data Size per size for all tags)	256							
		Maximum nu		19,200 bytes							
		nection	ta Size per Con-	600 bytes							
		Maximum Nu trable Tag Se	ımber of Regis- ets	32 (1 connection = 1 tag set)							
		Maximum Ta		<u> </u>	used if Contro	oller status is inc	cluded in the t	tag set.)			
			ncket Filter *14	Supported.							
		Class 3 (num	nber of connec-	32 (clients plus	s server)						
	Cip Message Service: Explicit Messages	UCMM (non-	Maximum Number of Cli- ents that Can Communicate at One Time	32							
		type)	Maximum Num- ber of Servers								
			that Can Com- municate at One Time	32							

^{*10.}Data is updated on the line in the specified interval regardless of the number of nodes.

*11.The Packet interval of the CPU Unit version 1.02 or earlier is 10 to 10,000 ms in 1.0-ms increments.

*12.Means packets per second, i.e., the number of communications packets that can be sent or received in one second.

*13.The Permissible Communications Band of the CPU Unit version 1.02 or earlier is 1,000 pps.

*14.An IGMP client is mounted for the EtherNet/IP port. If an ethernet switch that supports IGMP snooping is used, filtering of unnecessary multicast packets is performed.

*15.The Maximum number of TCP socket service of the CPU Unit version 1.02 or earlier is 16.

					NJ501-		NJ	301-	N	NJ101	
	It	em		□5□0	□4□0	□3□0	1200	1100	1□□0	9□□0	
		Support Prof	le/Model	Embedded 201 PLCopen Inform			-				
		Default Endp	oint/Port	opc.tcp://192.10							
		Maximum nu sions (Client)		5			-				
		Maximum nu tored Items p	mber of Moni- er server	2,000			-				
		tored Items (ms)		0, 50, 100, 250, if set to 0 (zero)							
				100	, it is accumed						
		Maximum nu	•	10,000							
		Maximum nu	mber of struc- ns that can be	100			-				
EtherNet/IP Serve	OPC UA Server (NJ501-1⊡00)	Restrictions on variables unable to be published		Structures in dimensional structures ne Array which's from 0 Array which's (global varial)	over dimension obal variables cludes double array (global v ested 4 and ov index numbe s element is ov oles)	nal array of) and over ariables) er Unions r don't start					
				None Sign - Basic Sign - Basic Sign - Basic Sign - Aes12 Sign - Aes25 SignAndEnci SignAndEnci SignAndEnci SignAndEnci	256 256Sha256 8Sha256RsaC 6Sha256RsaF ypt - Basic126 ypt - Basic256 ypt - Aes128S	Pss BRsa15 S SSha256 ha256RsaOaep					
		Application Authentica- tion	Authentication	X.509)pt 71002000	nazoortoar oo					
			Maximum number of certification	Trusted certificat Issuer certificat Rejected certifi	ion: 32		-				
		User Authentication	Authentica- tion	User name / Pa Anonymous		*16					
	Communicatio	ns Standard		IEC 61158 Typ	e12		<u> </u>				
	EtherCAT Mass	ter Specification	ns	Class B (Featu	e Pack Motion	Control compli	ant)			·	
	Physical Layer			100BASE-TX							
	Modulation			Baseband							
	Baud Rate			100 Mbps (100	Base-TX)						
	Duplex mode			Auto				-			
	Topology			Line, daisy cha	in, branching a	and ring *17					
Built-in	Transmission I	Media			<u> </u>	y 5 or higher (do	ouble-shielde	d straight ca	ble with alumin	num tape an	
EtherCAT Port	Maximum Tran between Nodes		ince	100m							
	Maximum Num	ber of Slaves		192					64		
	Range of node			1-192					1		
	Maximum Prod			Inputs: 5,736 b Outputs: 5,736							
	Maximum Proc	ess Data Size	per Slave	Inputs: 1,434 b Outputs: 1,434	ytes						
	Communicatio	ns Cycle		500/1,000/2,00	-)			1,000/2,000)/4.000 us	
	Sync Jitter	,		1 μs max.	,σσο μο το				.,500,2,000	,σσο μο	
Internal Cloc				At ambient tem At ambient tem	perature of 25		min error per	r month			

^{*16.}Roles can be set for the unit versions 1.62 or later of CPU Units.
*17.Ring topology is supported with the project version 1.40 or later.
Slaves on a ring topology should support a ring topology. If Omron slaves, please see the user's manual of slaves.
*18.For project unit version earlier than 1.40, the data must be within four frames.
*19.The Maximum Communications Cycle of the NJ301 CPU Unit version 1.02 or earlier and NJ501-R□□ are 1,000/2,000/4,000 μs.
The EtherCAT communications cycle of NJ501-4□□0 for robot control is 1 ms or more.
*20.The values shown are values in continuous operation.

Note: For robot control by NJ501-4□□0, use the G5 series/1S series AC Servo Drive with built-in EtherCAT communications, absolute encoder, and brake and brake.

Performance Specifications Supported by NC Integrated Controller

				NJ501-	
		Item		5300	
	Task Period	Primary periodic cycle		500/1,000/2,000/4,000 μs	
	Task Period	CNC Planner Service per	riod	500 μs to 16 ms	
	Number of CNC motors	Maximum number of CN	C motors	16	
	CNC Coordinate system	Maximum number of CN	C coordinate systems	4	
		Maximum number of CN0 cluded in a CNC coordin (excluding spindle axes)		. 8	
Numerical	5,515	Number of spindle axes nate system	that are included in a CNC coordi-	1	
Control	Number of simu	Iltaneous interpolation axe	es	4	
		Program buffer size *1		16 MB	
	NC Program	Maximum number of	Upper limit of main registrations	512	
		programs	Upper limit of sub registratioins	512	
		P variable		Double-precision floating point 65536 *2	
	NC program variables	Q variable		Double-precision floating point 8192 *2	
		L variable		Double-precision floating point 256	
	CNC motor	Maximum number of CN	C motor compensation tables	32	
	compensation table	Maximum size of all com	pensation tables	1 MB	

^{*1.} The number of programs and their capacities that can be loaded into the CPU Unit at the same time.

The program capacity is the maximum size available. As fragmentation will occur, the size that is actually available will be smaller than the maximum size.

^{*2.} Some parts of the area are reserved by the system.

Function Specifications

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□			
	Function				er program are executed in specify execution conditions				
		Periodically Ex-	Maximum Number of Pri- mary Periodic Tasks	1					
		ecuted Tasks	Maximum Number of Periodic Tasks	3					
Tasks		Conditionally	Maximum number of event tasks	32					
IdSKS		executed tasks *1	Execution conditions	When Activate Event Tas expression for variable is	k instruction is executed or met.	when condition			
		System Service Tasks (NJ501-R□□□)	Maximum number of V+ Tasks	64					
	Setup	System Service	Monitoring Settings		d the percentage of the total e system services (processor om task execution).				
		Programs		POUs that are assigned t	o tasks.				
	POU (program organization	Function Blocks		POUs that are used to cre	eate objects with specific co	onditions.			
	units)	Functions		POUs that are used to cre inputs, such as for data p	eate an object that determir rocessing.	ne unique outputs for the			
	Programming Languages	Types		Ladder diagrams *2 Structured text (ST) V+ (NJ501-R□□□)					
	Namespaces *3	-		A concept that is used to	group identifiers for POU d	efinitions.			
	Variables	External Access of Variables	Network Variables	The function which allows access from the HMI, host computers, or o Controllers					
			Boolean	BOOL					
			Bit Strings	BYTE, WORD, DWORD,	LWORD				
			Integers	INT, SINT, DINT,LINT, UI	NT, USINT, UDINT, ULINT				
			Real Numbers	REAL, LREAL					
		Data Types	Durations	TIME					
			Dates	DATE					
			Times of Day	TIME_OF_DAY					
			Date and Time	DATE_AND_TIME					
			Text Strings	STRING					
		Derivative Data	Function	Structures, unions, enum		different veriable times			
Program- ming	Data Types		Maximum Number of Mem-	2048	t groups together data with	unierent variable types.			
J		Structures	Nesting Maximum	8					
			Levels Member Data Types	Pagia data tupag atrustur	es, unions, enumerations,	arrov variables			
			Specifying Member	21 /	ets to place structure mem				
			Offsets	locations.*3					
			Function	A derivative data type that	t groups together data with	different variable types.			
		Unions	Maximum Number of Members	4					
			Member Data Types	BOOL, BYTE, WORD, D	WORD, LWORD				
		Enumerations	Function	A derivative data type that variable values.	t uses text strings called er	numerators to express			
			Function		ments with the same data t element from the first elem				
		Array Specifi-	Maximum Number of Dimensions	3					
	Data Type Attri- butes	cations	Maximum Number of Elements	65535					
			Array Specifications for FB Instances	Supported.					
		Range Specifica	tions	You can specify a range fooly values that are in the	or a data type in advance.	The data type can take			
		Libraries *3		User libraries					

^{*1.} Supported only by the CPU Units with unit version 1.03 or later.
*2. Inline ST is supported. (Inline ST is ST that is written as an element in a ladder diagram.)
*3. Supported only by the CPU Units with unit version 1.01 or later.

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□				
	Control Modes			position control, velocity of	ontrol, torque control					
	Axis Types			Servo axes, virtual servo	axes, encoder axes, and v	irtual encoder axes				
	Positions that ca	an be managed		Command positions and a	ctual positions					
			Absolute Positioning	Positioning is performed f value.	or a target position that is s	specified with an absolu				
		Single-axis Po-	Relative Positioning	Positioning is performed f current position.	or a specified travel distan	ce from the command				
		sition Control	Interrupt Feeding		or a specified travel distance eived from an external inpu					
			Cyclic synchronous absolute positioning *1	The function which output position control mode.	s command positions in ev	very control period in the				
			Velocity Control	Velocity control is perform	ed in Position Control Mod	de.				
		Single-axis Ve- locity Control	Cyclic Synchronous Velocity Control	A velocity command is output each control period in Velocity Control Mode.						
		Single-axis Torque Control	Torque Control	The torque of the motor is controlled.						
		·	Starting Cam Operation	A cam motion is performe	d using the specified cam	table.				
			Ending Cam Operation	•	is that is specified with the					
			Starting Gear Operation		ecified gear ratio is perforr	ned between a master				
		Single-axis Synchronized	Positioning Gear Operation	A gear motion with the specified gear ratio and sync position is performed between a master axis and slave axis.						
		Control	Ending Gear Operation	The specified gear motion	ar motion or positioning gear motion is ended.					
			Synchronous Positioning	Positioning is performed in sync with a specified master axis.						
			Master Axis Phase Shift		is in synchronized control					
			Combining Axes	·	f two axes are added or su					
		Single-axis	Powering the Servo	The Servo in the Servo D	rive is turned ON to enable	axis motion.				
Motion Control		Manual Operation	Jogging	An axis is jogged at a spe	cified target velocity.					
	Single-axis	•	Resetting Axis Errors	Axes errors are cleared.						
			Homing	A motor is operated and the signal are used to define I	ne limit signals, home prox	imity signal, and home				
			Homing with parameter *1	Specifying the parameter,	a motor is operated and the signal are used to define	-				
			High-speed Homing	-	or an absolute target posit					
			Stopping		a stop at the specified rate					
			Immediately Stopping	An axis is stopped immed	· · · · · · · · · · · · · · · · · · ·					
			Setting Override Factors	The target velocity of an a	<u> </u>					
			Changing the Current Position	,	sition or actual current pos	ition of an axis can be				
			Enabling External Latches		recorded when a trigger or	ccurs.				
		Auxiliary Func-	Disabling External Latches	The current latch is disable	ed.					
		tions for Sin- gle-axis	Zone Monitoring	You can monitor the comr when it is within a specifie	nand position or actual pos d range (zone).	sition of an axis to see				
		Control	Enabling digital cam switches *4	You can turn a digital outp	ut ON and OFF according	to the position of an a				
			Monitoring Axis Following Error		the difference between the ecified axes exceeds a thre					
			Resetting the Following Error	The error between the corset to 0.	nmand current position and	d actual current position				
			Torque Limit	The torque control functio	n of the Servo Drive can be et to control the output torq					
			Slave Axis Position Compensation *5		s the position of the slave					
			Cam monitor (NJ□01-□□00)	Outputs the specified offs	et position for the slave ax	is in synchronous contr				
			Start velocity *6	You can set the initial velo	city when axis motion star	te				

^{*1.} Supported only by the CPU Units with unit version 1.03 or later.
*4. Supported only by the CPU Units with unit version 1.06 or later.
*5. Supported only by the CPU Units with unit version 1.10 or later.
*6. Supported only by the CPU Units with unit version 1.05 or later.

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□		
			Absolute Linear Interpolation	Linear interpolation is perf	ormed to a specified abso	lute position.		
		Multi-axes Co-	Relative Linear Interpola-	Linear interpolation is perf	ormed to a specified relati	ve position.		
		ordinated Con- trol	Circular 2D Interpolation	Circular interpolation is performed for two axes.				
			Axes Group Cyclic Syn- chronous Absolute Posi- tioning	A positioning command is output each control period in Position Cont Mode.*3				
			Resetting Axes Group Errors	Axes group errors and axis errors are cleared.				
	Axes Groups		Enabling Axes Groups	Motion of an axes group is	Motion of an axes group is enabled.			
			Disabling Axes Groups	Motion of an axes group is	disabled.			
		Auxiliary Func-	Stopping Axes Groups	All axes in interpolated mo	tion are decelerated to a s	stop.		
		tions for Multi- axes Coordi-	Immediately Stopping Axes Groups	All axes in interpolated mo	tion are stopped immedia	tely.		
		nated Control	Setting Axes Group Over- ride Factors	The blended target velocity	y is changed during interp	olated motion.		
			Reading Axes Group Positions	The command current pos can be read.*3	itions and actual current p	ositions of an axes grou		
			Changing the Axes in an Axes Group	The Composition Axes par overwritten temporarily.*3	rameter in the axes group	parameters can be		
			Setting Cam Table Properties	The end point index of the cam table that is specified in the input param changed.				
		Cams	Saving Cam Tables	The cam table that is specified with the input parameter is saved in no volatile memory in the CPU Unit.				
	Common Items		Generating cam tables *7	The cam table that is specified with the input parameter is generated from property and cam node.				
		Parameters	Writing MC Settings	Some of the axis paramete temporarily.	ers or axes group paramet	ers are overwritten		
		1 41411101010	Changing axis parameters *7	You can access and chan	ge the axis parameters fro	m the user program.		
lotion Control		Count Modes		You can select either Linea length).	ar Mode (finite length) or F	Rotary Mode (infinite		
		Unit Conversions		You can set the display unit for each axis according to the machine.				
		Acceleration/ Deceleration Control	Automatic Acceleration/ Deceleration Control	Jerk is set for the acceleration/deceleration curve for an axis motion or group motion.				
			Changing the Acceleration and Deceleration Rates	You can change the acceleration or deceleration rate even during acce or deceleration.				
		In-position Check		You can set an in-position range and in-position check time to confirm wh positioning is completed.		ck time to confirm wher		
		Stop Method		You can set the stop method to the immediate stop input signal or limit in signal.		· • ·		
		Re-execution of Motion Control Instruction		You can change the input variables for a motion control instruction during execution and execute the instruction again to change the target values operation.				
	Auxiliary Functions	Multi-execution of Motion Control Instructions (Buffer Mode)		You can specify when to start execution and how to connect the velocitied between operations when another motion control instruction is executed during operation.				
		Continuous Axe Mode)	s Group Motions (Transition	You can specify the Transition Mode for multi-execution of instructions for axes group operation.		tion of instructions for		
			Software Limits	Software limits are set for	each axis.			
			Following Error	The error between the con monitored for an axis.	nmand current value and t	he actual current value		
		Monitoring Functions	Velocity, Acceleration Rate, Deceleration Rate, Torque, Interpolation Velocity, Interpolation Acceleration Rate, And Interpolation Deceleration Rate			s and each axes group		
		Absolute Encod	er Support	You can use an OMRON G Encoder to eliminate the n				
		Input signal logi	c inversion *6	You can inverse the logic of signal, negative limit input	of immediate stop input sig	nal, positive limit input		
	External Interface	Signals		The Servo Drive input sigr proximity signal, positive li signal, and interrupt input	mit signal, negative limit si	•		

^{*3.} Supported only by the CPU Units with unit version 1.01 or later.
*6. Supported only by the CPU Units with unit version 1.05 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□		
	EtherCAT Slaves	Maximum Numb	er of Slaves	192 64				
Unit (I/O)		Maximum numb	er of Units	40		1		
Manage- ment	CJ-Series Units	Basic I/O Units	Load Short-circuit Protection and I/O Disconnection Detection	Alarm information for Basic I/O Units is read.				
	Peripheral USB Po	rt		A port for communications with various kinds of Support Software running on a personal computer.				
	Secure Communica	ations		Function for secure comm	nunication with support sof	tware		
		Communication	s protocol	TCP/IP, UDP/IP				
		CIP Communications	Tag Data Links	Programless cyclic data e EtherNet/IP network.	Programless cyclic data exchange is performed with the devices on the EtherNet/IP network.			
		Service	Message Communications	CIP commands are sent t network.	o or received from the dev	rices on the EtherNet/IP		
		TCP/IP functions	CIDR	The function which perfor (class A to C) of IP addre	ms IP address allocations ss.	without using a class		
			Socket Services	Data is sent to and receive protocol. Socket communications in	ed from any node on Ether	net using the UDP or TC		
	Built-in EtherNet/ IP port Internal Port		FTP client *7	File can be read from or w	ritten to computers at othe imunications instructions a			
	internal Port	TCP/IP Applications	FTP Server	Files can be read from or written to the SD Memory Card in the CPU Unit fro computers at other Ethernet nodes.				
			Automatic Clock Adjust- ment	Clock information is read from the NTP server at the specified time or at a specified interval after the power supply to the CPU Unit is turned ON. The internal clock time in the CPU Unit is updated with the read time.				
Communica-			SNMP Agent	Built-in EtherNet/IP port internal status information is provided to network management software that uses an SNMP manager.				
tions		OPC UA (NJ501-1□00)	Server Function	Functions to respond to requests from clients on the OPC UA network				
		Supported Ser-	Process Data Communications	Control information is exchanged in cyclic communications between the EtherCAT master and slaves.				
		vices	SDO Communications	A communications method to exchange control information in noncyclic ever communications between EtherCAT master and slaves. This communications method is defined by CoE.				
		Network Scanni	ng	Information is read from connected slave devices and the slave configuration is automatically generated.				
	EtherCAT Port	DC (Distributed	Clock)	Time is synchronized by sharing the EtherCAT system time among all EtherCAT devices (including the master).				
		Enable/disable S	Settings for Slaves	The slaves can be enable	ed or disabled as communi	cations targets.		
			Connecting Slaves		a slave from the EtherCAT of the slave, and then conn			
		Supported Application Protocol	СоЕ	SDO messages of the CA	SDO messages of the CAN application can be sent to slaves via EtherCAT.			
	Communications Instructions			message instructions, no-	are supported. uctions, socket communicat protocol communications in t instructions *7, and Modbi	structions, protocol mac		
Operation Management	RUN Output Contact	cts		The output on the Power	Supply Unit turns ON in R	UN mode.		
		Function		Events are recorded in the	e logs.			
System	Frant Laws	Maximum	System event log	1,024	512			
Management	Event Logs	number of	Access event log	1,024	512			
Ī		events	User-defined event log	1,024	512			

^{*6.} Supported only by the CPU Units with unit version 1.05 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.
*8. Supported only by the CPU Units with unit version 1.11 or later.

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□		
	Online Editing	Single			s, functions, and global var s can change different POL			
	Forced Refreshing			The user can force specif	fic variables to TRUE or FA	LSE.		
		Maximum Num-	Device Variables for Ether- CAT Slaves	64				
		ber of Forced Variables	Device Variables for CJ-series Units and Variables with AT Specifications	64				
	MC Test Run *9			Motor operation and wiring can be checked from the Sysmac Studio.				
	Synchronizing			The project file in the Sysmac Studio and the data in the CPU Unit can be made the same when online.				
	Differentiation mon	itoring *1		Rising/falling edge of con	tacts can be monitored.			
		Maximum number	er of contacts *1	8				
		Types	Single Triggered Trace	and then tracing stops au	•	·		
Debugging			Continuous Trace	Data tracing is executed Sysmac Studio.	continuously and the trace	data is collected by the		
		Trace	er of Simultaneous Data	4 *10	2			
		Maximum Number of Records		10,000	<u> </u>			
	Data Tracing	Sampling	Maximum Number of Sam- pled Variables	192 variables	48 variables			
		Timing of Sampl		Sampling is performed for the specified task period, at the specified time, or when a sampling instruction is executed.				
		Triggered Traces	S	- 00	to record data before and			
			Trigger Conditions	When BOOL variable changes to TRUE or FALSE Comparison of non-BOC variable with a constant Comparison Method: Equals (=), Greater than (>), Greater than or equals (\le) Less Than (<), Less than or equals (\le), Not equal (\ne)				
;			Delay	Trigger position setting: A slider is used to set the percentage of sampling before and after the trigger condition is met.				
	Simulation			The operation of the CPU Unit is emulated in the Sysmac Studio.				
		Controller Er- rors	Levels	Major fault, partial fault, minor fault, observation, and information				
Reliability Functions	Self-diagnosis	User-defined errors		User-defined errors are registered in advance and then records are created by executing instructions.				
			Levels	8 levels				
		CPU Unit Names	and Serial IDs	When going online to a CPU Unit from the Sysmac Studio, the CPU Unit name in the project is compared to the name of the CPU Unit being connected to.				
			User Program Transfer with No Restoration Information	You can prevent reading data in the CPU Unit from the Sysmac Studio.				
	Protecting Soft-	Protection	CPU Unit Write Protection	You can prevent writing d Memory Card.	You can prevent writing data to the CPU Unit from the Sysmac Studio or Memory Card.			
Security	ware Assets and Preventing Oper- ating Mistakes		Overall Project File Protection	You can use passwords to Sysmac Studio.	You can use passwords to protect .smc files from unauthorized opening on Sysmac Studio.			
	ating imotation		Data Protection	You can use passwords t	o protect POUs on the Sys	mac Studio.*3		
		Verification of O	peration Authority	Online operations can be restricted by operation rights to prevent damage to equipment or injuries that may be caused by operating mistakes.				
			Number of Groups	5*11 5				
		Verification of User Program Execution ID			The user program cannot be executed without entering a user program execution ID from the Sysmac Studio for the specific hardware (CPU Unit).			
	Storage Type			SD Memory Card, SDHC	Memory Card			
		Automatic transf	fer from SD Memory Card *1	when the power supply to	older on an SD Memory Ca the Controller is turned O	N.		
SD Memo-			m from SD Memory Card *8	The user program on an system-defined variable t	SD Memory Card is loaded of TRUE.	when the user changes		
ry Card Functions	Application	SD Memory Card Instructions	d Operation		ory Cards from instructions			
		File Operations 1	rom the Sysmac Studio	read/write standard docu	ations for Controller files in ment files on the computer.			
	SD Memory Card Life Expiration Detection		Notification of the expiration of the life of the SD Memory Card is provided in a systemdefined variable and event log.					

^{*1.} Supported only by the CPU Units with unit version 1.03 or later.
*3. Supported only by the CPU Units with unit version 1.01 or later.
*8. Supported only by the CPU Units with unit version 1.11 or later.

^{*9.} Cannot be used with the NJ101-9000.

^{*10.}Maximum Number of Simultaneous Data Trace of the NJ501-□□20 CPU Unit with unit version 1.08 or later is 2. *11.When the NJ501 CPU Units with unit version 1.00 is used, this value becomes two.

		Item		NJ501-□□□□	NJ301-□□□□	NJ101-□□□□	
Backup			Using front switch	You can use front switch to backup, compare, or restore data.			
			Using system-defined variables	You can use system-defined variables to backup, compare, or restore data. *12			
functions *1		Backup operation can be performed by using instruction.					
		Protection Prohibiting backing up data to the SD Memory Card		Prohibit SD Memory Card backup functions.			
	Sysmac Studio Controller backup functions			Backup, restore, and verification operations for Units can be performed from the Sysmac Studio.			

^{*1.} Supported only by the CPU Units with unit version 1.03 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.
*12. Restore is supported with unit version 1.14 or later.

Function Specifications of Database Connection CPU Units

 $Besides \ functions \ of \ the \ NJ501-\square\square\square|/NJ101-\square\square\square|, \ functions \ supported \ by \ the \ NJ501-\square\square20/NJ101-\square020 \ are \ as \ follows.$

	Item		NJ501-1□20	ription NJ101-□020		
Supported	port		Built-in EtherNet/IP port	N3 101-1020		
Supported DB *1*2			Microsoft Corporation: SQL Server 2012/2014/2016/2017/2019/2022 Oracle Corporation: Oracle Database 11g /12c/18c/19c/21c/23ai (23c) MySQL Community Edition 5.6/5.7/8.0 *3 International Business Machines Corporation (IBM): DB2 for Linux, UNIX and Windows 9.7/10.1/10.5/11.1 * Firebird Foundation Incorporated: Firebird 2.5 *4 The PostgreSQL Global Development Group: PostgreSQL 9.4/9.5/9.6/10/11/12/13/14/15/16 *4			
	DB Connections databases that ca	n be connected at the	3 connections max. *5			
same time)	Supported opera	tions	The following operations can be performed by exect CPU Units. Inserting records (INSERT), Updating records (UPI records (DELETE), Execute Stored Procedure *6, and the second second second second second second second sec	Liting DB Connection Instructions in the NJ/NX-series DATE), Retrieving records (SELECT), Deleting and Execute Batch Insert *6		
	Max. number of i		32			
	Max. number of c		SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000			
	Max. number of columns in an UPDATE operation Max. number of columns in a SELECT operation		SQL Server: 1,000 SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000			
			SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000			
	Max. number of records in the output of a SELECT operation		65,535 elements, 4 MB	65,535 elements, 2 MB		
	Stored procedure call *6	Supported databases	SQL Server Oracle Database MySQL Community Edition PostgreSQL *7			
		Argument (Sum of IN, OUT and INOUT)	Up to 256 variables *8			
		Return value	One variable			
		Result set	Supported			
		Spool function	Not supported			
	Batch insert ex-	Supported databases	SQL Server Oracle Database MySQL Community Edition PostgreSQL *7			
		Supported data size	Less than 1,000 columns and upper limit of structure	re variable size or less *9		
		Spool function	Not supported			
	Max. number of DB Map Variables for which a mapping can be connected *10		SQL Server: 60 Oracle: 30 DB2: 30 *4 MySQL: 30 Firebird: 15 *4 PostgreSQL: 30 *4	SQL Server: 15 Oracle: 15 DB2: 15 MySQL: 15 Firebird: 15 PostgreSQL: 15		
Run mode o	of the DB Connecti	on Service	Operation Mode or Test Mode Operation Mode: When each instruction is executed, the service actually accesses the DB. Test Mode: When each instruction is executed, the service ends the instruction normally without accessing the DB actually.			
Spool function			Used to store SQL statements when an error occurred and resend the statements when the communications are recovered from the error.			
Spool capacity			1 MB *11 192 KB *11			
Operation Log function			The following three types of logs can be recorded. • Execution Log: Log for tracing the executions of the DB Connection Service. • Debug Log: Detailed log for SQL statement executions of the DB Connection Service. • SQL Execution Failure Log: Log for execution failures of SQL statements in the DB.			
DB Connec	tion Service shutd	own function	Used to shut down the DB Connection Service after automatically saving the Operation Log files into the SD Memory Card.			
Encrypted (Communication	Supported databases	SQL Server Oracle Database MySQL Community Edition PostgreSQL *7			
		TLS Ver.	TLS 1.2			

- SQL Server 2014, Oracle Database 12c and PostgreSQL 9.4 are supported by the DB Connection Service Version 1.02 or higher.
 - SQL Server 2016, My SQL 5.7, DB2 11.1 and Postgre SQL 9.5/9.6 are supported by the DB Connection Service Version 1.03 or higher. SQL Server 2017 is supported by the DB Connection Service Version 1.04 or higher.

 - Oracle Database 18c, MySQL Community Edition 8.0 and PostgreSQL 10 are supported by the DB Connection Service Version 2.00 or higher. You cannot use Oracle 10g with the DB Connection Service version 2.00 or higher.
 - SQL Server 2019, Oracle Database 19c and PostgreSQL 11/12/13 are supported by the DB Connection Service Version 2.01 or higher. SQL Server 2022, Oracle Database 21c/23ai (23c) and PostgreSQL 14/15/16 are supported by the DB Connection Service Version 2.04 or higher.
- Connection to the DB on the cloud is not supported.
- The supported storage engines of the DB are InnoDB and MyISAM.
- *4. NJ501-4320 is not supported.
- When two or more DB Connections are established, the operation cannot be guaranteed if you set different database types for the connections.
- The function is available for the DB Connection Service Version 2.00 or higher.
- The NJ501-4320 does not support PostgreSQL.
- *8. Depends on members of a structure.
- *9. Constrained by the memory capacity for variables. See the specifications for the memory capacity for variables.
- *10.Even if the number of DB Map Variables has not reached the upper limit, the total number of members of structures used as data type of DB Map Variables is 10,000 members max.
- *11.Refer to "NJ/NX-series Database Connection CPU Units User's Manual(W527)" for the information.

Note: The extended support for databases has ended for the following DB versions.

Please consider replacing the current database with a new version.

Item	Discription
Microsoft Corporation: SQL Server	2008/2008R2
Oracle Corporation: Oracle Database	10g
Oracle Corporation: MySQL Community Edition	5.1/5.5
International Business Machines Corporation (IBM): DB2 for Linux, UNIX and Windows	9.5
Firebird Foundation Incorporated: Firebird	2.1
The PostgreSQL Global Development Group: PostgreSQL	9.2/9.3

Function Specifications of SECS/GEM CPU Units

Besides functions of the NJ501-1300, functions supported by the NJ501-1340 are as follows.

Item	Description		
Supported port	Built-in EtherNet/IP port		
Supported standard *1	The Unit conforms to the following SEMI standards: E37-0303, E37.1-0702, E5-0707, and E30-0307		
Fundamental GEM requirement State Model, Equipment Processing State, Host-initiated S1, F13/F14 Scenario, Event Notification, On-Line Id Message, Control (Operator Initiated), Documentation			
Additional GEM capability Establish Communications, Dynamic Event Report Configuration, Variable Data Collection, Trace Data Collection, Alarm Management, Remote Control, Equipment Constant, Process Recipe Management *1, Equipment Terminal Service, Clock, Limit Monitoring, Spooling *2, Control (Host Initiated)			
User-defined message	You can create non-GEM compliant communications messages and have host communications.		
GEM specific instruction	The Unit supports 29 instructions to perform the following: Changing the GEM Service status. Setting HSMS communications. Reporting events and reporting alarms. Acknowledging host commands and enhanced remote commands. Changing equipment constants. Uploading and downloading process programs. Sending and acknowledging equipment terminal messages. Requesting to change time. Sending user-defined messages. Getting SECS communications log.		
GEM Service log *2	Can record the following information. • HSMS communications log: Keeps log of HSMS communications operations. • SECS message log: Keeps log of SECS-II communications messages. • Execution log: Keeps log of executions of GEM instructions.		
Shutting down the GEM Service	Saves the spool data and GEM Service log records into an SD Memory Card and ends the GEM Service.		

^{*1.} E42 recipes, large process programs, and E139 recipes are not supported.

Conformance to Fundamental GEM Requirements and Additional Capabilities

Fundamental GEM requirements	GEM-compliant			
State Model				
Equipment Processing State				
Host-initiated S1, F13/F14 Scenario				
Event Notification	Yes			
On-Line Identification	103			
Error Message				
Control (Operator Initiated)				
Documentation				

Additional capabilities	GEM-compliant
Establish Communications	
Dynamic Event Report Configuration	
Variable Data Collection	
Trace Data Collection	Yes
Status Data Collection	165
Alarm Management	
Remote Control	
Equipment Constant	
Process Recipe Management	Process program: Yes E42 recipes: No E139 recipes: No
Material Movement	
Equipment Terminal Service	
Clock	Yes
Limit Monitoring	165
Spooling	
Control (Host Initiated)	
•	·

Function Specifications of NJ Robotics CPU Units

Besides functions of the NJ501-1 \square 00, functions supported by the NJ501-4 \square \square are as follows.

		Item			NJ501-			
	4500	4400	4300	4310	4320			
		Multi-axes coordinated control	Conveyer tracking	The robot is moved in synchronization with the conveyor during the conveyor tracking operation.				
Robot control functions	Axes groups	Auxiliary functions for multi-axes coordinated control Kinematics Settin		Set parameters for robot operation, such as arm length of Delta3 robot				f Delta3 robot.
	Auxiliary functions Monitoring functions		Work space function	Set the coordinate values for workspace check and check the workspace during operation.			ck the	

^{*2.} The capability is not available when no SD Memory Card is mounted.

Function Specifications of NC Integrated Controller

Besides functions of the NJ501-1 \square 00, functions supported by the NJ501-5300 are as follows.

		Ite	em		NJ501-
		T -			5300
		Axes types	Decitioning evid		Positioning axis, Spindle axis
		Control modes	Positioning axis	5	Position control
			Spindle axis		Velocity control
		Positions that c	an be managed		Absolute position (command), absolute position (actual), program position, remaining travel distance
			Execute		Executes the NC program.
			Reset		Interrupt NC program
			Single step exe	cution	Executes the NC program by block.
			Back trace		Executes back trace of interpolation pass.
		NC program	Feed hold / Fee	d hold reset	Temporarily stops the NC program, and restarts it.
		execution	Optional stop		Stops the NC program with optional signal.
			Optional block	stop	Skips one block of the NC program with optional signal.
			Dry run		Runs operation from the NC program.
			Machine lock		Locks each axis operation during execution of the NC program.
			Auxiliary lock		Locks M code output.
			Override	I	Overrides the feed rate and spindle velocity.
				Rapid Positioning	Rapid feed of each CNC motor according to the motor setting.
			Position	Linear interpolation	Interpolates linearly.
			control	Circular interpolation	Interpolates circularly, helically, spirally, or conically.
				Skip function	Rapid feed until an external signal is input.
		G Code	Return to refere	1 .	Returns to a specified position on the machine.
			Canned cycle	Rigid tap	Performs tapping machining.
			Feed function	Exact stop	Temporarily prevents blending of positioning operations before and after an exact stop direction.
				Exact stop mode	Mode in which anteroposterior positioning operations are not blende
				Continuous-path mode	Mode in which anteroposterior positioning operations are blended.
				Dwell	Waits for the specified period of time.
Numerical Control	CNC coordinate system		Coordinate system selection	Machine Coordinate System	The coordinate system uses the machine home position as the home the system.
				Work Coordinate System	The coordinate system has work offset for the Machine Coordinate System.
				Local Coordinate System	The coordinate system has additional offset for the Work Coordinate System.
			Auxiliary for	Absolute/relative selection	Specifies manipulated variable absolutely, or switches to the relative setting.
				Metric/inch selection	Selects metric or inch as the orthogonal axes unit system.
			coordinate	Scaling	Scales the current coordinates of the orthogonal axes.
			system	Mirroring	Mirrors the current coordinates for the specified orthogonal axes.
				Rotation	Rotate the current coordinates around the coordinates of the specific axis.
				Cutter compensation	Compensation of the tool edge path according to the tool radius.
			Tool functions	Tool length compensation	Compensation of tool center point path according to the tool length.
			M code/M code	reset	Outputs M codes, and interlocks with sequence control program usin reset.
		M code	Spindle svis	CW/CCW/Stop	Outputs/stops velocity commands in velocity loop control mode.
			Spindle axis	Orientation	Stops spindle axis to the specified phase by setting up feed back loo
			Subroutine call		Calls a subroutine of the NC program.
			Arithmetic oper	ation	Performs a calculation in the NC program.
		NC	Branch control		Branches on condition in the NC program.
			User variables		Memory area in the NC program used for processing such as data calculation.
		programming		P variable	System global memory area common to CNC coordinate systems
				Q variable	Global system area unique to each CNC coordinate system
				L variable	Memory area that can be used as the primary area during execution of the NC program
		Auxiliary	Error reset		Function that resets errors or CNC coordinate system and CNC motor
		control functions	Immediate stop		Function that stops all the CNC motors of the CNC coordinate system

					NJ501-	
		Ite	m		5300	
		Positions that ca	an be managed		Commanded positions and actual positions.	
			Absolute positioning		Positioning is performed for a target position that is specified using an absolute value.	
		Position control	Relative position	ning	Positioning is performed for a specified travel distance from the command current position.	
			Cyclic positioni	ing	A commanded position is output at each control period in Position Control Mode.	
		Spindle control	CW/CCW/Stop		Outputs/stops velocity commands in velocity loop control mode.	
		Manual	Powering the S	ervo	The Servo in the servo driver is turned ON to enable CNC motor operation.	
		operation	Jogging		A CNC motor is jogged at a specified target velocity.	
		Auxiliary control	Homing		A CNC motor is operated, and the limit signals, home proximity signal and home signal are used to define home.	
	CNC motor	functions	Immediate stop		A CNC motor is stopped immediately.	
		CNC motor compensation table	Ball screw compensation		Pitch error compensation for one-dimensional ball screw.	
			Cross-axis compensation		Compensation of one-dimensional cross-axis.	
Numerical Control			Editing the CNC motor compensation table		Edit using sequence control program. (Read/write)	
			In-position check		You can set an in-position range and in-position check time to confirm when positioning is completed.	
			Stop method		You can set the stop method to the immediate stop input signal or limit input signal.	
				Monitorina	Software limits	Monitors the movement range of a CNC motor.
		Auxiliary functions	functions	Following error	Monitors the error between the command current value and the actual current value for a CNC motor.	
			Absolute encoder support		You can use an OMRON 1S-series Servomotor or G5-series. Servomotor with an Absolute Encoder to eliminate the need to perform homing at startup.	
			Input signal logic inversion		You can inverse the logic of immediate stop input signal, positive limit input signal, negative limit input signal, or home proximity input signal.	
		External interface signals			The Servo Drive input signals listed on the right are used. Home signal, home proximity signal, positive limit signal, negative limit signal, immediate stop signal, and interrupt input signal.	
	Common items	Parameters	Changing CNC CNC motor para	coordinate system and ameters	You can access and change the CNC coordinate system and CNC motor parameters from the user program.	

Function Specifications of Robot integrated CPU Units

Besides functions of the NJ501-1 \square 0, functions supported by the NJ501-R \square 0 are as follows.

ltem			Description		
			NJ501-R□□0		
	Number of robots	Maximum number of robots	8 robots		
		Basic operation	Joint interpolation operation, Linear motion, Arc motion, Jog motion		
		Coordinate system of Tool	Descent (APPRO), Rising (DEPART), Tool alignment (ALIGN)		
		Joint motion	Each joint operation (DRIVE)		
	Motion Operation	Application	Pick or Place		
		Continous-path motion	ON, OFF		
		Deceleration Stop	Braking current motion		
		Home position	Move to home position (READY)		
		Speed of the robot	Velocity profile, Velocity, Acceleration, Deceleration, Minimum operation time		
		Unit of speed	Ratio for maximum velocity, [mm/s], [inch/s]		
	Motion Modifiers	Arm configuration	ABOVE/BELOW, LEFTY/RIGHTY, FLIP/NOFLIP		
		Hardware servo	High accuracy/Low accuracy		
Robot Control		Axis of rotation	Rotation Range, Rotation Range Over Error		
		Position Deviation	Pending position deviation cancellation		
		Robot position	You can read the robot position in the V+ program when a latch signal occurred.		
	Latching	Local encoder	You can read the counter value of encoder that is connected to the encoder input port of OMRON robot in the V+ program when a latch signal occurred.		
		Coordinate system	World coordinate system, Tool coordinate system, Conversion from/to NJ Robotics function coordinate system		
		Position variable	Conversion, Relative conversion, High accuracy position		
	Other functions	Robot tool	Tool offset setting		
		End effector operation	Open/Close/Loosen Gripper		
		Conveyor tracking	Belt variable, Nominal transformation, Encoder scaling factor, Encoder offset, Belt window, Belt relative motion		
		Stop	Specified time stop (DELAY)		

Version Information

Unit Versions and Programming Devices (NJ-series CPU Units)

Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Unit Versions, DBCon Versions and Programming Devices (Database Connection CPU Units)

Refer to NJ/NX-series Database Connection CPU Units User's Manual (W527).

Unit Versions, Robot Versions and Programming Devices (NJ Robotics CPU Units)

Refer to NJ-series Robotics CPU Units User's Manual (W539).

Unit Versions and Programming Devices (NC Integrated Controller)

Refer to NJ/NY-series NC Integrated Controller User's Manual (O030).

Unit Versions, Robot Control Versions and Programming Devices (Robot Integrated CPU Units)

Refer to NJ-series Robot Integrated CPU Unit User's Manual (O037).

Relationship between Hardware Revisions of CPU Units and Sysmac Studio Versions

Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Functions That Were Added or Changed for Each Unit Version and Sysmac Studio version


Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Performance Improvements for Unit Version Upgrades


Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Components and Functions


CPU Unit NJ□01-□□□□



Power Supply Unit NJ-PA3001




NJ-PD3001



Unit Configuration

NJ-Series CPU Racks

A NJ-Series CPU Rack consists of a CPU Unit, Power Supply Unit, Configuration Units (Basic I/O Units, Special I/O Units, and CPU Bus Units), and an End Cover.



Even though the NJ-Series Controllers do not have Backplanes, the term "slot" still used to refer to the location of Units. Slot numbers are assigned in order to Units from left to right on the CPU Rack (slot 0, slot 1, slot 2, etc.).

Required Units

Rack	Unit name	Required number of Units			
CPU Rack	NJ-Series Power Supply Unit	1			
	NJ-Series CPU Unit	1			
	I/O Control Unit	Required only for mounting to an Expansion Rack. Mount the I/O Control Unit immediately to the right of the CPU Jnit.			
	Number of Configuration Units	10 max. (Same for all models of CPU Unit.) (The number of Basic I/O Units, Special I/O Units, and CPU Bus Units can be varied. The number does not include the I/O Control Unit.)			
	End Cover	1 (Included with CPU Unit.)			
	NJ-Series SD Memory Card	Install as required.			


Types of Configuration Units

In the NJ-Series, Configuration Units are classified into the following three types. The number of Racks differs depending on the type.

Туре	Appearance (example)	Description	Unit recognition method	Max. Units mountable per CPU Unit
Basic I/O Units	900	Units with contact inputs and contact outputs.	Recognized by the CPU Unit according to the position of the Rack and slot.	A maximum of 40 Units can be mounted.
Special I/O Units		Special I/O Units provide more advanced functions than do Basic I/O Units, including I/O other than contact inputs and contact outputs. Examples of Special I/O Units are Analog I/O Units and High-speed Counter Units. They differ from CPU Bus Units (including Network Communications Units) in having a smaller area for exchanging data with the CPU Unit.	Recognized by the CPU Unit according to the unit number (0 to 95) set with the rotary switches on the front panel.	A maximum of 40 Units can be connected. (Multi- ple unit numbers are allo- cated per Unit, depending on the model and settings.)
CPU Bus Units	CPU Bus Units exchange data with the CPU Unit via the CPU Bus. Examples of CPU Bus Units are Network Communications Units and Serial Communications Units. They differ from Special I/O Units in having a larger area for exchanging data with the CPU Unit		Recognized by the CPU Unit according to the unit number (0 to F) set with the rotary switch on the front panel.	A maximum of 16 Units can be mounted.

NJ-Series Expansion Racks

A NJ-Series Expansion Rack consists of a Power Supply Unit, an I/O Interface Unit, Configuration Units (Basic I/O Units, Special I/O Units, and CPU Bus Units), and an End Cover.



Required Units

Rack	Unit name	Required number of Units		
CPU Rack	I/O Control Unit	One Unit. Required only when an Expansion Rack is used. Mount the I/O Control Unit immediately to the right of the CPU Unit. $^{\star}1$		
	Power Supply Unit	One Unit		
Expansion	I/O Interface Unit	One Unit. Mount the I/O Interface Unit immediately to the right of the Power Supply Unit. *2		
Rack	Number of Configuration Units	Ten Units max. (The number of Basic I/O Units, Special I/O Units, and CPU Bus Units can be varied. This number does not include the I/O Interface Unit.)		
	End Cover	One (Included with the I/O Interface Unit.)		

^{*1} Mounting the I/O Control Unit in any other location may cause faulty operation.

Configuration Units

Maximum Number of Configuration Units That Can Be Mounted

CPU Unit	Model	Total Units	No. of Units on CPU Rack	No. of Expansion Racks
	NJ501-□□□□	40	10 per Rack	3 Racks x 10 Units
CPU Unit	NJ301-□□□□			
	NJ101-□□□			

Note: It may not be possible to mount the maximum number of configuration Units depending on the specific Units that are mounted. Refer to the next page for details.

Number of mountable units per Configuration Unit


Basic I/O Units, Special I/O Units, and CPU Bus Units of the CJ-Series are used as Configuration Units of the NJ-Series. All Basic I/O Units are useable. Not all Special I/O Units and CPU Bus Units can be used. Units that can be used are shown in the list. In addition, note that the number of units that can be connected to one CPU vary depending on the units.


^{*2.} Mounting the I/O Interface Unit in any other location may cause faulty operation.

Dimensions (Unit: mm)


CPU Units NJ□01-□□□□









Power Supply Units NJ-PA3001 NJ-PD300





End Cover (included with CPU Units) CJ1W-TER01



Related Manuals

Cat. No.	Model number	Manual	Application	Description
W513	NJ501 NJ301 NJ101	NJ Series Startup Guide (CPU Unit)	Using the NJ-series CPU Unit for the first time	The startup procedures for using an NJ-series CPU Unit and the basic operating instructions for the Sysmac Studio are described with a simple sequence control example.
W514	NX701	NJ/NX-series Startup Guide (Motion Control)	Using the motion control function module of the NJ/NX-series for the first time	The startup procedures for setting axis parameters and performing simple one-axis positioning and two-axis linear interpolation with an NJ/NX-series CPU Unit and the operating instructions for the Sysmac Studio are described.
W500	NJ501 NJ301 NJ101	NJ-series CPU Unit Hardware User's Manual	Learning the basic specifications of the NJ-series CPU Units, including introductory information, designing, installation, and maintenance Mainly hardware information is provided.	An introduction to the entire NJ-series system is provided along with the following information on a Controller built with a CPU Unit. Features and system configuration Introduction Part names and functions General specifications Installation and wiring Maintenance and inspection
W501	NX701	NJ/NX-series CPU Unit Software User's Manual	Learning how to program and set up an NJ/NX-series CPU Unit. Mainly software information is provided.	The following information is provided on a Controller built with an NJ/NX-series CPU Unit. • CPU Unit operation • CPU Unit features • Initial settings • Programming language specifications and programming with the IEC 61131-3 standard.
W507	NX701-	NJ/NX-series CPU Unit Motion Control User's Manual	Learning about motion control settings and programming concepts	The settings and operation of the CPU Unit and programming concepts for motion control are described.
W505	NX701	NJ/NX-series CPU Unit Built-in EtherCAT Port User's Manual	Using the built-in EtherCAT port on an NJ/NX-series CPU Unit	Information on the built-in EtherCAT port is provided. This manual provides an introduction and provides information on the configuration, features, and setup.
W539	NJ501-4□□□ NJ501-R□□□	NJ-series NJ Robotics CPU Unit User's Manual	Controlling robots with NJ-series CPU Units.	Describes the functionality to control robots.
O037	NJ501-R□□□	NJ-series Robot Integrated CPU Unit User's Manual	Using the NJ-series Robot Integrated CPU Unit.	Describes the settings and operation of the CPU Unit and programming concepts for OMRON robot control.
W527	NX701-□20 NX502-1□00 NX102-□20 NJ501-□20 NJ101-□20	NJ/NX-series Database Connection CPU Units User's Manual	Learning about the functions and application procedures of the NJ/ NX-series DB Connection function.	Describes the functions and application procedures of the NJ/NX-series DB Connection function.
W528	NJ501-1340	NJ-series SECS/GEM CPU Unit User's Manual	Learning about the SECS/GEM CPU Unit and how to use it.	Functional outline, GEM instructions, settings with the GEM Configurator and so on are provided.
O030	NJ501-5300 NY532-5400	NJ/NY-Series NC Integrated Controller User's Manual	For numerical control with NJ/NY-series	Describes the numerical control function.
W506	NX701	NJ/NX-series CPU Unit Built-in EtherNet/IP Port User's Manual	Using the built-in EtherNet/IP port on an NJ/NX-series CPU Unit	Information on the built-in EtherNet/IP port is provided. Information is provided on the basic setup, tag data links, FINS communications (non-disclosure), and other features.
W588	NX102-□□□ NX701-1□□□ NX502-1□00 NJ501-1□00	NJ/NX-series CPU Unit OPC UA User's Manual	Using the OPC UA.	Describes the OPC UA.
W502	NX701	NJ/NX-series Instructions Reference Manual	Learning about the specifications of the instruction set that is provided by OMRON	The instructions in the instruction set (IEC 61131-3 specifications) are described.
W508	NX701-	NJ/NX-series Motion Control Instructions Reference Manual	Learning about the specifications of the motion control instructions that are provided by OMRON	The motion control instructions are described.
W503	NX701- NX502- NX102- NX1P2- NJ501- NJ101-	NJ/NX-series Troubleshooting Manual	Learning about the errors that may be detected in an NJ/NX-series Controller.	Concepts on managing errors that may be detected in an NJ/NX-series Controller and information on individual errors are described.

Cat. No.	Model number	Manual	Application	Description
W504	SYSMAC-SE2	Sysmac Studio Version 1 Operation Manual	Learning about the operating procedures and functions of the Sysmac Studio.	Describes the operating procedures of the Sysmac Studio.
O031	NJ501-5300 NY532-5400	NJ/NY-series G code Instruction Reference Manual	Learning about detailed specifications of the G code/M code instructions.	This section describes G code/M code instructions in detail.
W589	SYSMACSE2	Sysmac Studio Project Version Control Function Operation Manual	Learning the overview of the Sysmac Studio project version control function and how to use it.	The manual outlines the Sysmac Studio project version control function, and describes how to install, basic operation, and how to operate its major functions.
O032	SYSMAC-RTNC0 D	CNC Operator Operation Manual	Learning the overview of CNC Operator and how to use it.	Describes the CNC Operator, installation procedure, basic operation, connection operation, and operating procedures for main functions.
W595	SYSMAC-SE2□□□ SYSMAC-SE200D-64	Sysmac Studio Robot Integrated System Building Function with Robot Integrated CPU Unit Operation Manual	Learning about the operating procedures and functions of the Sysmac Studio to configure Robot Integrated System using Robot Integrated CPU Unit.	Describes the operating procedures of the Sysmac Studio for Robot Integrated CPU Unit.
W621	SYSMAC-SE2□□□ SYSMAC-SE200D-64	Sysmac Studio Robot Integrated System Building Function with IPC Application Controller Operation Manual	Learning about the operating procedures and functions of the Sysmac Studio to configure Robot Integrated System using IPC Application Controller.	Describes the operating procedures of the Sysmac Studio for IPC Application Controller.
W490 W498 W491 Z317 W492 W494 W497 W495 W493	CJ1W	CJ-series Special Unit Manuals for NJ-series CPU Unit	Leaning how to connect CJ-series Units	The methods and precautions for using CJ-series Units with an NJ-series CPU Unit are described, including access methods and programming interfaces. Manuals are available for the following Units. Analog I/O Units, Insulated-type Analog I/O Units, Temperature Control Units, ID Sensor Units, High-speed Counter Units, and DeviceNet Units, EtherNet/IP Units, CompoNet Master Units
Y128		Vision & Robot Integrated Simulation Startup Guide	Learning about the operating procedures of Vision & Robot integrated simulation.	Describes the operating procedures of Vision & Robot integrated simulation.
Y213	SYSMAC-SE20 SYSMAC-RA401L NJ501-4 R88D-KN ECT FH-1	Vision & Robot Integrated Simulation Technology In- troduction Guide (Calibra- tion Parameter)	Learning about the calibration parameters created using the 3D Equipment Model Creation Wizard for the Vision & Robot integrated simulation.	Describes calibration parameters created using the 3D Equipment Model Creation Wizard for the Vision & Robot integrated simulation.
Z368		Vision Sensor FH Series Conveyor Tracking Applica- tion Programming Guide	Learning about the setup procedure of the wizard style calibration for cameras, robots, or conveyors.	Describes how to configure and operate Conveyor Tracking Calibration Wizard on Sysmac Studio on FH Sensor Controllers.
Z369		Vision Sensor FH Series Operation Manual Sysmac Studio Calibration Plate Print Tool	Learning about the setup procedure for printing the Pattern on a Calibration Plate used for calibration for cameras and robots on Sysmac Studio.	Describes how to configure and operate Calibration Plate Print Tool on Sysmac Studio on FH Sensor Controllers.
Z370		Vision Sensor FH Series Operation Manual Sysmac Studio Conveyor Tracking Calibration Wizard Tool	Learning about the setting procedure of sample macros for conveyor tracking.	Describes the setting procedure of sample macros used for applications of conveyor tracking on FH Sensor Controllers.
Z371		Vision Sensor FH Series Operation Manual Sysmac Studio Conveyor Panorama Display Tool	Learning about the setup procedure of panorama display for image capture of targets on conveyors.	Describes how to configure and operate the Conveyor Panorama Display tool on Sysmac Studio on FH Sensor Controllers.

Applicable Models for Cable Redundancy Function

For more information on applicable models of Cable Redundancy function, refer to the Applicable Models of Cable Redundancy Function (Cat. No. R200).

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products.

Microsoft, Windows, Windows Vista and SQL Server are registered trademarks of Microsoft Corporation in the United States and other countries.

Oracle, Oracle Database and MySQL are trademarks or registered trademarks of Oracle Corporation and/or its affiliates in the United States and other countries.

IBM and DB2 are trademarks or registered trademarks of International Business Machines Corp., registered in the United States and other countries.

SEMI® is a trademark or registered trademark of Semiconductor Equipment and Materials International in the United States and other countries.

EtherCAT® is a registered trademark of Beckhoff Automation GmbH for their patented technology.

 $\label{eq:therNet/IPTM} \textbf{EtherNet/IP}^{\text{TM}} \ \textbf{and} \ \textbf{DeviceNet}^{\text{TM}} \ \textbf{are} \ \textbf{trademarks} \ \textbf{of} \ \textbf{ODVA}.$

OPC UA is trademark of the OPC Foundation.

 $This \ product \ includes \ software \ developed \ by \ the \ OpenSSL \ Project \ for \ use \ in \ the \ OpenSSL \ Toolkit. \ (http://www.openssl.org/)$

This product includes cryptographic software written by Eric Young (eay@cryptsoft.com).

Other company names and product names in this document are the trademarks or registered trademarks of there respective companies.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability: Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD.
438B Alexandra Road, #08-01/02 Alexandra
Technopark, Singapore 119968
Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.
Room 2211, Bank of China Tower,
200 Yin Cheng Zhong Road,
PuDong New Area, Shanghai, 200120, China
Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388

©OMRON Corporation 2018-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

CSM_6_12

Cat. No. P140-E1-25 0625 (1218)