OMRON

Machine Automation Controller


Controller that covers functions and high-speed processing required for machine control and safety, reliability and maintainability



Features

- Implemented OPC UA as standard feature.
- Integration of Logic and Motion in one CPU.
- Conforms to IEC 61131-3 (JIS B 3503) standard programming and PLCopen function blocks for Motion Control. Programming with variables allows users to create complex programs efficiently.
- Fast and accurate control by synchronizing all EtherCAT devices, such as vision sensors, servo drives, and field devices, with the PLC and Motion Engines.
- Offers speed without compromising on reliability and robustness expected from PLCs.
- Complete RAS functions: Transmission frame error check, timeout, bus diagnosis, Watchdog (WDT), memory check, and topology check, etc.
- Ideal for small-scale control with up to 8 axes. (NJ301-
- Ideal for simple machines. (NJ101-
- Linear and circular interpolation.
- Electronic gear and cam synchronization.
- The Controller can be directly connected to a database. No special Unit, software, nor middleware is required. (NJ501-020/NJ101-020)
- The NJ501 SECS/GEM CPU Unit has built-in the SECS/GEM communications functions which are the standards in the semiconductor industry. (NJ501-1340)
- Control function of parallel link robots, cartesian robots and serial link robots. (NJ501-400)
- Integration of Logic, Motion, OMRON Robot and Kinematics in one CPU. (NJ501-R 0)
- Realize high-accuracy synchronization motion control (MC) and numerical control (NC) functions by ONE controller. G-Code available. (NJ501-5300)

NJ-Series System Configuration



Ordering Information

Applicable standards

Refer to the OMRON website (www.ia.omron.com) or ask your OMRON representative for the most recent applicable standards for each model.

CPU Units

| | | | Specifications | | |
|-----------------------------------|--|---------------------------------|--|----|------------|
| Product name | I/O capacity / maximum number of configuration Units (Expansion Racks) | Units for variables motion avec | | | |
| NJ501 OPC UA CPU Units Support | | | | 64 | NJ501-1500 |
| | | 20 MB | 2 MB: Retained during power interruption 4 MB: Not retained during power interruption | 32 | NJ501-1400 |
| | | | | 16 | NJ501-1300 |
| NJ301 CPU Units | 2,560 points / 40 Units | | | 8 | NJ301-1200 |
| | (3 Expansion Racks) | 5 MB | 0.5 MB: Retained during power interruption | 4 | NJ301-1100 |
| NJ101 CPU Units | | | 2 MB: Not retained during power interruption | 2 | NJ101-1000 |
| | | 3 MB | | 0 | NJ101-9000 |

| | | | | Specifica | ations | | | | | | | | | |
|-----------------------------|---|---------------------|---|--------------------------------|------------------------------------|---------------------------------------|-----------------------------------|--|-----------------------------------|------------|--|--|--|------------|
| Product name | I/O capacity / maximum number of configuration Units (Expansion Racks) | Program capacity | Memory capacity for variables | Number of motion axes | Database Connection function | SECS/GEM Communication function | Number of controlled robots | Number of controlled OMRON robots | Numerical Control Functions | Model | | | | |
| Database | | | 2 MB: Retained during | 64 | | | | | | NJ501-1520 | | | | |
| Connection CPU Units | | 20 MB | power interruption 4 MB: Not retained | 32 | | | | | | NJ501-1420 | | | | |
| | 2,560 points / 40 Units | | during power interruption | 16 | Yes | No | | | No | NJ501-1320 | | | | |
| | (3 Expansion Racks) | 3 MB | 0.5 MB: Retained during power interruption | 2 | | | | | | NJ101-1020 | | | | |
| | | 5 MB | 2 MB: Not retained during power interruption | 0 | | | | - | | NJ101-9020 | | | | |
| SECS/GEM CPU Unit | | | | 16 | No | Yes | | - | | | | | | NJ501-1340 |
| NJ Robotics | | 0 points / | | 64 | | | 8 max. *1 | | No | NJ501-4500 | | | | |
| CPU Units | | | | 32 16 Yes | | | | | | NJ501-4400 | | | | |
| | | | | | | | | | | NJ501-4300 | | | | |
| | | | | | | | 1 | | | NJ501-4310 | | | | |
| | 2,560 points / | | 2 MB: Retained during | | Yes | | | + | | NJ501-4320 | | | | |
| Robot Integrated | 40 Units | 20 MB | power interruption 4 MB: Not retained | 64 | No | | | | | NJ501-R500 | | | | |
| CPU Units | (3 Expansion Racks) | | during power interruption | 64 | Yes | | | | | NJ501-R520 | | | | |
| MIL NI ALM | | | | 32 | No | No | 8 max. *1 | 8 max. | | NJ501-R400 | | | | |
| | | | | 32 | Yes | NU | | o max. | | NJ501-R420 | | | | |
| | | | | 16 | No | | | | | NJ501-R300 | | | | |
| | | | | 10 | Yes | | | | | NJ501-R320 | | | | |
| NC Integrated Controller | | | | 16 *2 | No | | | | Yes *3 | NJ501-5300 | | | | |

*1. The number of controlled robots varies according to the number of axes used for the system.
*2. The number of controlled axes of the MC Control Function Module is included.
*3. One CNC Operator License (SYSMAC-RTNC0001L) is attached with the CPU Unit.

Accessories

The following accessories come with the CPU Unit.

| Product name | Model |
|----------------------------------|---|
| Battery | CJ1W-BAT01 |
| End Cover | CJ1W-TER01 (must be attached to the right end of the CPU Rack) |
| End Plate | PFP-M (2 required) |
| SD Memory Card (Flash Memory) | NJ501-□□20, NJ501-1340, NJ501-R□□: HMC-SD492 NJ101-□□20: HMC-SD292 |

Power Supply Units

One Power Supply Unit is required for each Rack.

| | | Bower cupply | | current | Output capacity | | Options | | |
|---|---------------------|-------------------------|-----------------------------|------------------------------|-------------------------|-----------------------------------|---------------|------------------------------------|-----------|
| | Product name | Power supply voltage | 5-VDC output capacity | 24-VDC output capacity | Total power consumption | 24-VDC service power supply | RUN output | Maintenance forecast monitor | Model |
| Α | C Power Supply Unit | 100 to 240 VAC | | 4.0.4 | 20.14 | No | Yes | No | NJ-PA3001 |
| D | C Power Supply Unit | 24 VDC | 6.0 A | 1.0 A | 30 W | ONI | res | NO | NJ-PD3001 |

Note: Power supply units for the CJ-Series cannot be used as a power supply for a CPU rack of the NJ system or as a power supply for an expansion rack.

Expansion Racks

Select the I/O Control Unit, I/O Interface Unit, Expansion Connecting Cable, and Power Supply Unit.

CJ-Series I/O Control Unit (Mounted on CPU Rack when Connecting Expansion Racks)

| Product name | Specifications | | rent ption (A) | Model |
|-------------------------------|---|------|-------------------|------------|
| | | 5 V | 24 V | |
| CJ-Series I/O Control Unit | Mount one I/O Control Unit on the CJ-Series CPU Rack when connecting one NJ-Series Expansion Racks. Connecting Cable: CS1W-CN 3 Expansion Connecting Cable Connected Unit: CJ1W-II101 I/O Interface Unit Mount to the right of the CPU Unit. | 0.02 | | CJ1W-IC101 |

Note: Mounting the I/O Control Unit in any other location may cause faulty operation.

CJ-Series I/O Interface Unit (Mounted on Expansion Rack)

| Product Name | Specifications | | rent ption (A) | Model |
|---------------------------------|--|------|-------------------|------------|
| | | 5 V | 24 V | |
| CJ-Series I/O Interface Unit | One I/O Interface Unit is required on each Expansion Rack. Connecting Cable: CS1W-CN 3 Expansion Connecting Cable Mount to the right of the Power Supply Unit. | 0.13 | | CJ1W-11101 |

Note: Mounting the I/O Interface Unit in any other location may cause faulty operation.

I/O Connecting Cables

| Product name | Specifications | Model | |
|---|---|---------------------|---------------|
| I/O Connecting Cable Connects an I/O Control Unit on NJ-Series CPU Rack to an I/O Interface Unit on a NJ-Series Expansion Rack. or Connects an I/O Interface Unit on NJ-Series Expansion Rack to an I/O Interface Unit on another NJ-Series Expansion Rack. | | Cable length: 0.3 m | CS1W-CN313 |
| | | Cable length: 0.7 m | CS1W-CN713 |
| | Cable length: 2 m | CS1W-CN223 | |
| | or • Connects an I/O Interface Unit on NJ-Series Expansion Rack to | Cable length: 3 m | CS1W-CN323 |
| | | Cable length: 5 m | CS1W-CN523 |
| | | Cable length: 10 m | CS1W-CN133 |
| | | Cable length: 12 m | CS1W-CN133-B2 |

Automation Software Sysmac Studio

Please purchase a DVD and required number of licenses the first time you purchase the Sysmac Studio. DVDs and licenses are available individually. Each model of licenses does not include any DVD.

| Product name | Specifications | | Media | Model |
|--|--|-------------------|-------------------------------|------------------|
| | The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slaves, and HMI. | _ (Media only) | Sysmac Studio (32 bit) DVD | SYSMAC-SE200D |
| Sysmac Studio Standard Edition Ver.1.□□ | Sysmac Studio runs on the following OS. *1 Windows 7 (32-bit/64-bit version)/Windows 8.1 (32-bit/64-bit version)/ Windows 10 (32-bit/64-bit version)/Windows 11 (64-bit version) | _ (Media only) | Sysmac Studio (64 bit) DVD | SYSMAC-SE200D-64 |
| | The Sysmac Studio Standard Edition DVD includes Support Software to set up EtherNet/IP Units, DeviceNet slaves, Serial Communications Units, and Support Software for creating screens on HMIs (CX-Designer). For details, refer to your OMRON website. | 1 license *2 | _ | SYSMAC-SE201L |
| Sysmac Studio Team Development Option *3 | Sysmac Studio Team Development Option is a licence to enable the project version control function. | 1 license *2 | - | SYSMAC-TA401L |

*1. Model "SYSMAC-SE200D-64" runs on Windows 10 (64 bit) or higher.

*2. Multi licenses are available for the Sysmac Studio (3, 10, 30, or 50 licenses).
*3. This product is a license only. You need the Sysmac Studio Standard Edition DVD media to install it. This option can be used by applying the Team Development Option to Sysmac Studio version 1.20 or higher. Project version control function is supported by CPU Unit version 1.16 or later.

Collection of software functional components Sysmac Library

Please download it from following URL and install to Sysmac Studio.

http://www.ia.omron.com/sysmac_library/

Typical Models

| Product | Features | Model |
|----------------------------------|--|--------------|
| Vibration Suppression Library | The Vibration Suppression Library is used to suppress residual vibration caused by the operation of machines. | SYSMAC-XR006 |
| Device Operation Monitor Library | The Device Operation Monitor Library is used to monitor the operation of devices such as air cylinders, sensors, motors, and other devices. | SYSMAC-XR008 |
| Dimension Measurement Library | The Dimension Measurement Library is used to dimension measurement with ZW-8000/7000/5000 Confocal Fiber Displacement Sensor, or E9NC-TA0 Contact-Type Smart Sensor. | SYSMAC-XR014 |

SECS/GEM Configurator (For NJ-series SECS/GEM CPU Unit NJ501-1340)

Please purchase the required number of SECS/GEM Configurator licenses and a Sysmac Studio Standard Edition DVD the first time you purchase the SECS/GEM Configurator.

The Sysmac Studio Standard Edition DVD includes the SECS/GEM Configurator. The license does not include the DVD.

| | Specifications | | | |
|-----------------------------------|--|-----------------------|-------|------------|
| Product Name | | Number of licenses | Media | Model |
| SECS/GEM Configurator Ver.1.□□ | The SECS/GEM Configurator is the software to make HSMS, SECSII and GEM settings for NJ501 SECS/GEM CPU Units. The SECS/GEM Configurator runs on the following OS. Windows XP (Service Pack3 or higher, 32-bit edition), Windows Vista (32-bit edition), or Windows 7 (32-bit or 64-bit edition) The software is included in the Sysmac Studio Standard Edition DVD. | 1 license | | WS02-GCTL1 |

Operation Software CNC Operator (For NJ-series NC Integrated Controller NJ501-5300)

Please purchase a DVD or download it from following URL.

http://www.ia.omron.com/cnc-operator/

One CNC Operator License (SYSMAC-RTNC0001L) is attached with the CPU Unit.

| | Specifications | | | |
|--|---|-----------------------|----------------|------------------|
| Product Name | | Number of licenses | Media | Model |
| | The CNC Operator is the software that provides a operation interface for NC programming, debugging and maintenance of CNC machine. | (Installer only) | (Download) | SYSMAC-RTNC0000 |
| CNC Operator | CNC Operator runs on the following OS. Windows 7 (32-bit/64-bit version)/Windows 8 (32-bit/64-bit version)/Windows 8.1 (32-bit/64-bit version)/Windows 10 (32-bit/64-bit version) | (Media only) | DVD | SYSMAC-RTNC0000D |
| CNC Operator License | The one license key (hardware key, USB dongle). The CNC Operator needs license key. | 1 license | | SYSMAC-RTNC0001L |
| CNC Operator Software Development Kit | The CNC Operator Software Development Kit provides a environment for customization of CNC Operator. Supported execution environment: NET Framework (4.6.1) Development environment: Visual Studio 2013/2015 Development languages: C# | | DVD | SYSMAC-RTNC0101D |

Recommended EtherCAT and EtherNet/IP Communications Cables

Use a straight STP (shielded twisted-pair) cable of category 5 or higher with double shielding (aluminum tape and braiding) for EtherCAT.

For EtherNet/IP, required specification for the communications cables varies depending on the baud rate.

For 100BASE-TX/10BASE-T, use a straight or cross STP (shielded twisted-pair) cable of category 5 or higher.

For 1000BASE-T, use a straight or cross STP cable of category 5e or higher with double shielding (aluminum tape and braiding).

Cable with Connectors

| | Item | Recommended manufacturer | Cable length (m) | Model |
|---|---|-----------------------------|------------------|----------------------|
| | Cable with Connectors on Both Ends | OMRON | 0.3 | XS6W-6LSZH8SS30CM-Y |
| | (RJ45/RJ45) Standard RJ45 plug type *1 | | 0.5 | XS6W-6LSZH8SS50CM-Y |
| /ire Gauge and Number of Pairs: WG26, 4-pair Cable | Cable color: Yellow *3 | | 1 | XS6W-6LSZH8SS100CM-Y |
| able Sheath material: LSZH *2 | \bigcirc | | 2 | XS6W-6LSZH8SS200CM-Y |
| | | | 3 | XS6W-6LSZH8SS300CM-Y |
| | | | 5 | XS6W-6LSZH8SS500CM-Y |
| | Cable with Connectors on Both Ends | OMRON | 0.3 | XS5W-T421-AMD-K |
| | (RJ45/RJ45) Rugged RJ45 plug type *1 | | 0.5 | XS5W-T421-BMD-K |
| | Cable color: Light blue | | 1 | XS5W-T421-CMD-K |
| | *0* | | 2 | XS5W-T421-DMD-K |
| | | | 5 | XS5W-T421-GMD-K |
| | | | 10 | XS5W-T421-JMD-K |
| | Cable with Connectors on Both Ends (M12 Straight/M12 Straight) Shield Strengthening Connector cable *4 M12/Smartclick Connectors Cable color: Black | OMRON | 0.5 | XS5W-T421-BM2-SS |
| | | | 1 | XS5W-T421-CM2-SS |
| | | | 2 | XS5W-T421-DM2-SS |
| fire Gauge and Number of Pairs: WG22, 2-pair cable | | | 3 | XS5W-T421-EM2-SS |
| | | | 5 | XS5W-T421-GM2-SS |
| | -0 | | 10 | XS5W-T421-JM2-SS |
| | Cable with Connectors on Both Ends (M12 Straight/RJ45) | OMRON | 0.5 | XS5W-T421-BMC-SS |
| | Shield Strengthening Connector cable *4 M12/Smartclick Connectors | | 1 | XS5W-T421-CMC-SS |
| | Rugged RJ45 plug type | | 2 | XS5W-T421-DMC-SS |
| | Cable color: Black | | 3 | XS5W-T421-EMC-SS |
| | -0 | | 5 | XS5W-T421-GMC-SS |
| | ~0 | | 10 | XS5W-T421-JMC-SS |

*1. Cables with standard RJ45 plugs are available in the following lengths: 0.2 m, 0.3 m, 0.5 m, 1 m, 1.5 m, 2 m, 3 m, 5 m, 7.5 m, 10 m, 15 m, 20 m. Cables with rugged RJ45 plugs are available in the following lengths: 0.3 m, 0.5 m, 1 m, 2 m, 3 m, 5 m, 10 m, 15 m. For details, refer to the Industrial Ethernet Connectors Catalog (Cat. No. G019).

*2. The lineup features Low Smoke Zero Halogen cables for in-cabinet use and PUR cables for out-of-cabinet use. Although the LSZH cable is single shielded, its communications and noise characteristics meet the standards.

*3. Cable colors are available in yellow, green, and blue.*4. For details, contact your OMRON representative.

Cables / Connectors

| | Item | | Recommended manufacturer | Model |
|---|---|-------------------------|--------------------------|-----------------------------------|
| Products for EtherCAT or EtherNet/IP | Wire Gauge and Number of | Cables | Hitachi Metals, Ltd. | NETSTAR-C5E SAB 0.5 × 4P CP *1 |
| (1000BASE-T*2/100BASE- | Pairs: AWG24, 4-pair Cable | | Kuramo Electric Co. | KETH-SB *1 |
| TX) | Cable | RJ45 Connectors | Panduit Corporation | MPS588-C *1 |
| Products for EtherCAT or | | Cables | Kuramo Electric Co. | KETH-PSB-OMR *3 |
| EtherNet/IP (100BASE-TX/10BASE-T) | Wire Gauge and Number of Pairs: AWG22, 2-pair Cable | | JMACS Japan Co., Ltd. | PNET/B *3 |
| (1000A3E-17/100A3E-1) | | RJ45 Assembly Connector | OMRON | XS6G-T421-1 *3 |

*1. We recommend you to use the above Cable and RJ45 Connector together.

*2. The products can be used only with the NX701.

*3. We recommend you to use the above Cable and RJ45 Assembly Connector together.


Optional Products and Maintenance Products

| Product name | Specifications | Model |
|--------------|------------------------|--------------|
| | SD memory card, 2GB | HMC-SD292 |
| Memory Cards | SDHC memory card, 4GB | HMC-SD492 |
| | SDHC memory card, 16GB | HMC-SD1A2 *1 |

***1.**16 GB memory card can be used for the NJ \Box 01- \Box \Box 00 version 1.21 or later.

| Product name | | Model | |
|--------------|--|---|------------|
| Battery Set | Battery for NX701/NJ501/ NJ301/NJ101 NJ/NX-Series CPU Unit maintenance | Note: 1. The battery is included as a standard accessory with the CPU Unit. 2. The battery service life is 5 years at 25°C. (The service life depends on the ambient operating temperature and the power conditions.) 3. Use batteries within two years of manufacture. | CJ1W-BAT01 |
| End Cover | Mounted to the right-hand side of NJ-Series CPU Racks or Expansion Racks. | One End Cover is provided as a standard accessory with each CPU Unit and I/O Interface Unit. | CJ1W-TER01 |

DIN Track Accessories



Basic I/O Units Input Units

| Unit classification | Product name | | Specifi | cations | | Number of bits | Response time *1 | | Current consumption (A) | | Model |
|------------------------|-------------------|------------------------------|---|------------------------|--------------------------------|----------------|------------------|----------------|-------------------------------|------|------------------|
| classification | | I/O points | Input voltage and current | Commons | External connection | allocated | ON | OFF | 5 V | 24 V | |
| | | 8 inputs | 12 to 24 VDC, 10 mA | Independent contacts | Removable terminal block | 16 | 20 µs max. | 400 µs max. | 0.08 | | CJ1W-ID201 |
| | DC Input Units | 16 inputs | 24 VDC, 7 mA | 16 points, 1 common | Removable terminal block | 16 | 20 µs max. | 400 µs max. | 0.08 | | CJ1W-ID211 |
| | | 16 inputs High-speed type | 24 VDC, 7 mA | 16 points, 1 common | Removable terminal block | 16 | 15 µs max. | 90 µs max. | 0.13 | | CJ1W-ID212 |
| | | 32 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | Fujitsu connector | 32 | 20 µs max. | 400 µs max. | 0.09 | | CJ1W-ID231 *2 |
| CJ1 | | 32 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | MIL connector | 32 | 20 µs max. | 400 µs max. | 0.09 | | CJ1W-ID232 *2 |
| Basic //O Units | | 32 inputs High-speed type | 24 VDC, 4.1 mA | 16 points, 1 common | MIL connector | 32 | 15 µs max. | 90 µs max. | 0.20 | | CJ1W-ID233 *2 |
| | | 64 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | Fujitsu connector | 64 | 120 µs max. | 400 µs max. | 0.09 | | CJ1W-ID261 *2 |
| | | 64 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | MIL connector | 64 | 120 µs max. | 400 µs max. | 0.09 | | CJ1W-ID262 *2 |
| | AC Input Units | 8 inputs | 200 to 24 VAC, 10 mA (200 V, 50 Hz) | 8 points, 1 common | Removable Terminal Block | 16 | 10 µs max. | 40 µs max. | 0.08 | | CJ1W-IA201 |
| | | 16 inputs | 100 to 120 VAC, 7 mA (100 V, 50 Hz) | 16 points, 1 common | Removable Terminal Block | 16 | 10 µs max. | 40 µs max. | 0.09 | | CJ1W-IA111 |

*1 This is the input response time when no filter (i.e., 0 ms) is set.
*2 The cable-side connector is not provided with Units equipped with cables. Purchase the 40-pin connector separately (Refer to page 11), or use an OMRON XW2K Series Datasheet (Cat. No. G152) and XW2R Series Catalog (Cat. No. G077) or a G7 I/O Relay Terminal.

| Output Un | its | | | | | | | | | |
|----------------|------------------------------------|----------------|-------------------------------|---|------------------------|-----------------------------|-------------------|-------|------------------------|----------------------|
| Unit | Product name | | | Specifications | | | Number of bits | consu | rrent Imption A) | Model |
| classification | | Output type | I/O points | Maximum switching capacity | Commons | External connection | allocated | 5 V | 24 V | |
| | Relay Con- tact Output Units | - | 8 outputs | 250 VAC/24 VDC, 2 A | Independent contacts | Removable terminal block | 16 | 0.09 | 0.048 max. | CJ1W-OC201 |
| | | _ | 16 outputs | 250 VAC/24 VDC, 2 A | 16 points, 1 common | Removable terminal block | 16 | 0.11 | 0.096 max. | CJ1W-OC211 |
| | Triac Output Unit | _ | 8 outputs | 250 VAC, 0.6 A | 8 points, 1 common | Removable terminal block | 16 | 0.22 | - | CJ1W-OA201 |
| | | Sinking | 8 outputs | 12 to 24 VDC, 2 A | 4 points, 1 common | Removable terminal block | 16 | 0.09 | - | CJ1W-OD201 |
| | | Sinking | 8 outputs | 12 to 24 VDC, 0.5 A | 8 points, 1 common | Removable terminal block | 16 | 0.10 | - | CJ1W-OD203 |
| | | Sinking | 16 outputs | 12 to 24 VDC, 0.5 A | 16 points, 1 common | Removable terminal block | 16 | 0.10 | - | CJ1W-OD211 *1 |
| CJ1 Basic | Transistor Output Units | Sinking | 16 outputs High-speed type | 24 VDC, 0.5 A | 16 points, 1 common | Removable terminal block | 16 | 0.15 | - | CJ1W-OD213 *1 |
| I/O Units | | Sinking | 32 outputs | 12 to 24 VDC, 0.5 A | 16 points, 1 common | Fujitsu connector | 32 | 0.14 | - | CJ1W-OD231 *2 |
| | | Sinking | 32 outputs | 12 to 24 VDC, 0.5 A | 16 points, 1 common | MIL connector | 32 | 0.14 | - | CJ1W-OD233 *1, *2 |
| | 5 | Sinking | 32 outputs High-speed type | 24 VDC, 0.5 A | 16 points, 1 common | MIL connector | 32 | 0.22 | - | CJ1W-OD234 *1, *2 |
| | 10 | Sinking | 64 outputs | 12 to 24 VDC, 0.3 A | 16 points, 1 common | Fujitsu connector | 64 | 0.17 | - | CJ1W-OD261 *2 |
| | - | Sinking | 64 outputs | 12 to 24 VDC, 0.3 A | 16 points, 1 common | MIL connector | 64 | 0.17 | - | CJ1W-OD263 *2 |
| | | Sourcing | 8 outputs | 24 VDC, 2 A Short-circuit protection | 4 points, 1 common | Removable terminal block | 16 *1 | 0.11 | - | CJ1W-OD202 |
| | Щ. ¹ | Sourcing | 8 outputs | 24 VDC, 0.5 A Short-circuit protection | 8 points, 1 common | Removable terminal block | 16 *1 | 0.10 | - | CJ1W-OD204 |
| | | Sourcing | 16 outputs | 24 VDC, 0.5 A Short-circuit protection | 16 points, 1 common | Removable terminal block | 16 | 0.10 | - | CJ1W-OD212 |
| | | Sourcing | 32outputs | 24 VDC, 0.5 A Short-circuit protection | 16 points, 1 common | MIL connector | 32 | 0.15 | - | CJ1W-OD232 *2 |
| | | Sourcing | 64 outputs | 12 to 24 VDC, 0.3 A | 16 points, 1 common | MIL connector | 64 | 0.17 | - | CJ1W-OD262 *2 |

 Interview
 Interview

| | | | Specifications | | | | | | rent ption (A) | |
|------------------------|-----------------------|-------------|----------------|---|------------------------|----------------------|--------------------------------|------|-------------------|--------------------------------------|
| Unit classification | Product name | | 1/O nointe | Input voltage, Input current | Commons | External | Number of bits allocated | 5 V | 24 V | Model |
| | | Output type | I/O points | Maximum switching capacity | Commons | connection | anocateu | ъv | 24 V | |
| | | Oistrin a | 16 inputs | 24 VDC, 7 mA | 16 points, 1 common | Fujitsu | 20 | 0.40 | | CJ1W-MD23 |
| | | Sinking | 16 outputs | 250 VAC/24 VDC, 0.5 A | 16 points, 1 common | connector | 32 | 0.13 | | *2 |
| | DC Input/ Transis- | Cinking | 16 inputs | 24 VDC, 7 mA | 16 points, 1 common | - MIL connector | 64 | 0.13 | | CJ1W-MD233 *2 |
| | tor Out- put Units | Sinking | 16 outputs | 12 to 24 VDC, 0.5 A | 16 points, 1 common | | 04 | 0.13 | | |
| | | Sinking | 32 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | Fujitsu connector | 32 | 0.14 | | CJ1W-MD261 *1 CJ1W-MD263 *1 |
| | in series | | 32 outputs | 12 to 24 VDC, 0.3 A | 16 points, 1 common | | 52 | 0.14 | | |
| CJ1 Basic | 5. | | 32 inputs | 24 VDC, 4.1 mA | 16 points, 1 common | | 64 | 0.14 | | |
| /O Units | 20 830 | Sinking | 32 outputs | 12 to 24 VDC, 0.3 A | 16 points, 1 common | | 04 | 0.14 | | |
| | | Sourcing | 16 inputs | 24 VDC, 7 mA | 16 points, 1 common | - MIL connector | | 0.13 | | CJ1W-MD232 |
| | | Sourcing | 16 outputs | 24 VDC, 0.5 A Short-circuit protection | 16 points, 1 common | | 32 | 0.13 | | *2 |
| | TTL I/O Units | | 32 inputs | 5 VDC, 35 mA | 16 points, 1 common | | | | | CJ1W-MD56 |
| | | | 32 outputs | 5 VDC, 35 mA | 16 points, 1 common | MIL connector | 64 | 0.19 | | *1 |

*1 Connectors are not provided with these connector models. Either purchase one of the following 40-pin Connectors, or use an OMRON XW2K

Series Datasheet (Cat. No. G152) and XW2R Series Catalog (Cat. No. G077) or a G7 I/O Relay Terminal.
*2 Connectors are not provided with these connector models. Either purchase one of the following 20-pin or 24-pin Connectors, or use an OMRON XW2R Series Datasheet (Cat. No. G152) and XW2R Series Catalog (Cat. No. G077) or a G7 I/O Relay Terminal.

Applicable Connectors

Fujitsu Connectors for 32-input, 32-output, 64-input, 64-output, 32-input/32-output, and 16-input/16-output Units

| Name | Connection | Remarks | Applicable Units | Model |
|----------------------|-----------------|--|--|------------|
| 40-pin Connectors | Soldered | FCN-361J040-AU Connector FCN-360C040-J2 Connector Cover | Fujitsu Connectors: CJ1W-ID231(32 inputs): 1 per Unit | C500-CE404 |
| | Crimped | FCN-363J040 Housing FCN-363J-AU Contactor FCN-360C040-J2 Connector Cover | CJ1W-ID261 (64 inputs) 2 per Unit CJ1W-OD231 (32 outputs):1 per Unit CJ1W-OD261 (64 outputs): 2 per Unit CJ1W-MD261 (32 inputs, 32 outputs): 2 per Unit | C500-CE405 |
| | Pressure welded | FCN-367J040-AU/F | | C500-CE403 |
| 24-pin Connectors | Soldered | FCN-361J024-AU Connector FCN-360C024-J2 Connector Cover | Fujitsu Connectors: CJ1W-MD231 (16 inputs, 16 outputs): 2 per Unit | C500-CE241 |
| | Crimped | FCN-363J024 Housing FCN-363J-AU Contactor FCN-360C024-J2 Connector Cover | | C500-CE242 |
| | Pressure welded | FCN-367J024-AU/F | | C500-CE243 |

MIL Connectors for 32-input, 32-output, 64-input, 64-output, 32-input/32-output, and 16-input/16-output Units


| Name | Connection | Remarks | Applicable Units | Model |
|----------------------|-----------------|----------------|--|-------------|
| 40-pin Connectors | Pressure welded | FRC5-AO40-3TOS | MIL Connectors: CJ1W-ID232/233 (32 inputs): 1 per Unit CJ1W-OD232/233/234 (32 outputs):1 per Unit CJ1W-ID262 (64 inputs): 2 per Unit CJ1W-OD262/263 (64 outputs): 2 per Unit CJ1W-MD263/563 (32 inputs, 32 outputs): 2 per Unit | XG4M-4030-T |
| 20-pin Connectors | Pressure welded | FRC5-AO20-3TOS | MIL Connectors: CJ1W-MD232/233 (16 inputs, 16 outputs): 2 per Unit | XG4M-2030-T |

Applicable Connector-terminal block conversion unit

Example: With OMRON Connector-terminal block conversion unit

Only main products are shown here.

More detail informations are shown in XW2K Series Datasheet (Cat. No. G152) and XW2R Series Catalog (Cat. No. G077)



Choose the wiring method.

Choose
Grow a following combination table PLC type.

| Wiring method | Model |
|-------------------------------------|--------------|
| Models with Push-In Plus | XW2K-40G-O32 |
| Models with Phillips screw | XW2R-J34GD-C |
| Models with Slotted screw (rise up) | XW2R-E34GD-C |

Combination table

| PLC Type (Connector-terminal block) | | | PLC | | Connecting cables | | | |
|-------------------------------------|---------------|---------------|----------------------|----------------------|-------------------------|------------|--|--|
| XW2K | XW2R | I/O | I/O Points | I/O unit model | Connecting cables | | | |
| | | lanut | 32 | CJ1W-ID231 | XW2Z- | | | |
| O32A | C1 | Input | 64 | CJ1W-ID261 | 32-point Unit: 1 Cable | | | |
| | | Input/Output | 32 | CJ1W-MD261 (inputs) | 64-point Unit: 2 Cables | | | |
| | | | 20 | CJ1W-ID232 | | | | |
| | | Input | 32 | CJ1W-ID233 | XW2Z-DDK | | | |
| O32C | C2 | | 64 | CJ1W-ID262 | 32-point Unit: 1 Cable | | | |
| | | lass t/Outsut | la sut/Outsut | CJ1W-MD263 (inputs) | 64-point Unit: 2 Cables | | | |
| | | Input/Output | 32 | CJ1W-MD563 (inputs) | | | | |
| | | lased | 32 | CJ1W-OD231 | XW2Z-DDB | | | |
| O32B | C3 | Input | 64 | CJ1W-OD261 | 32-point Unit: 1 Cable | | | |
| | | Input/Output | 32 | CJ1W-MD261 (outputs) | 64-point Unit: 2 Cables | | | |
| | | Output | | | | CJ1W-OD232 | | |
| | | | | | 32 | CJ1W-OD233 | | |
| O32C C4 | | | | CJ1W-OD234 | XW2Z-□□□K | | | |
| | C4 | | 64 | CJ1W-OD262 | 32-point Unit: 1 Cable | | | |
| | | | 64 | CJ1W-OD263 | 64-point Unit: 2 Cables | | | |
| | lass t/Outsut | 20 | CJ1W-MD263 (outputs) | | | | | |
| | | Input/Output | 32 | CJ1W-MD563 (outputs) | | | | |

Note: 1. $\Box \Box \Box$ is replaced by the cable length.

2. There is one common for each 32 points.

Connector-terminal block conversion unit

| Product name | Specifications | I/O Points (number of poles) | Model |
|---|--|------------------------------|---------------|
| | Push-In Plus | 32 (36) | XW2K-40G-O32A |
| | Antonionanta | 32 (36) | XW2K-40G-032B |
| | | 32 (36) | XW2K-40G-O32C |
| | Phillips screw | 32 (34) | XW2R-J34GD-C1 |
| 0 · · · · · | THE OWNER OF THE OWNER OWNER OF THE OWNER OWNE | 32 (34) | XW2R-J34GD-C2 |
| Connector-Terminal Block Conversion Unit | Summer / | 32 (34) | XW2R-J34GD-C3 |
| | N N | 32 (34) | XW2R-J34GD-C4 |
| | Slotted screw | 32 (34) | XW2R-E34GD-C1 |
| | (rise up) | 32 (34) | XW2R-E34GD-C2 |
| | | 32 (34) | XW2R-E34GD-C3 |
| | ** | 32 (34) | XW2R-E34GD-C4 |

Connecting cables

| Product name | Appearance | Connectors | Model | Cable length (m) |
|------------------------|------------|--|-----------|------------------|
| | XW2Z- | | XW2Z-050B | 0.5 |
| | | | XW2Z-100B | 1 |
| | | One 40-pin MIL Connector to | XW2Z-150B | 1.5 |
| | | One 40-pin Connector Made by Fujitsu Component, Ltd. | XW2Z-200B | 2 |
| | | | XW2Z-300B | 3 |
| or I/O Unit Connecting | | | XW2Z-500B | 5 |
| Cable | XW2Z-DDK | | XW2Z-C50K | 0.5 |
| | | | XW2Z-100K | 1 |
| | | One 40-pin MIL Connector to | XW2Z-150K | 1.5 |
| | | One 40-pin MIL Connector | XW2Z-200K | 2 |
| | | | XW2Z-300K | 3 |
| | | | XW2Z-500K | 5 |

Quick-response Input Units

| Unit clas- | Product | | Speci | fications | | Number of | Respon | ise time | Currer sumpt | nt con- ion (A) | |
|------------------------------|----------------------------------|---------------|------------------------------------|------------------------|-----------------------------|---------------------|-----------------|----------------|-----------------|--------------------|------------|
| sification | | I/O points | Input voltage, Input current | Commons | External connection | bits allo- cated | ON | OFF | 5 V | 24 V | Model |
| CJ1 Basic I/O Units | Quick- response Input Unit | 16 inputs | 24 VDC, 7 mA | 16 points, 1 common | Removable terminal block | 16 | 0.05 ms max. | 0.5 ms max. | 0.08 | | CJ1W-IDP01 |

B7A Interface Units

| Unit clas- sification | Product name | Specifications | | Number of bits allocated | Current c tion | | Model |
|---------------------------|--------------------------|-------------------|--------------------------|-----------------------------|-------------------|------|------------|
| Sincation | name | I/O points | External connection | bits anocated | 5 V | 24 V | |
| | B7A Inter- face Units | 64 inputs | | | 0.07 | | CJ1W-B7A14 |
| CJ1 Basic I/O Units | P | 64 outputs | Removable terminal block | 64 | 0.07 | | CJ1W-B7A04 |
| | | 32 inputs/outputs | | | 0.07 | | CJ1W-B7A22 |

Special I/O Units and CPU Bus Units

Process I/O Units

Isolated-type Units with Universal Inputs

| Unit clas- sification | Product name | Input points | Signal range | Signal range | Conversion speed | Accuracy (at ambient tempera- | connec- | No. of unit numbers | Currer sumpt | nt con- ion (A) | Model |
|--------------------------------|--|-----------------|---------------------------------------|---|--|---|---------------------------------------|------------------------|-----------------|--------------------|------------------|
| Sincation | name | points | selection | | (resolution) | ture of 25°C) | tion | allocated | 5 V | 24 V | |
| CJ1 Special I/O Units | Process Input Units (Isolated- type Units with Uni- versal Inputs) | 4 inputs | Set sepa- rately for each input | Universal inputs: Pt100 (3-wire), JPt100 (3-wire), Pt1000 (3- wire), Pt1000 (3- wire), Pt100 (4-wire), K, J, T, E, L, U, N, R, S, B, WRe5-26, PL II, 4 to 20 mA, 0 to 20 mA, 1 to 5 V, 0 to 1.25 V, 0 to 1.25 V, 0 to 5 V, 0 to 10 V, ± 100 mV selectable range -1.25 to 1.25 V, -5 to 5 V, -10 to 10 V, ± 10 V selectable range, potentiometer | Resolution (conversion speed): 1/256,000 (conversion cycle: 60 ms/ 4 inputs) 1/64,000 (con- version cycle: 10 ms/ 4 inputs) 1/16,000 (con- version cycle: 5 ms/ 4 inputs) | Standard accuracy: ±0.05% of F.S. | Remov- able ter- minal block | 1 | 0.30 | | CJ1W-PH41U *1 |
| | | 4 inputs | Set sepa- rately for each input | Universal inputs: Pt100, JPt100, Pt1000, K, J, T, L, R, S, B, 4 to 20 mA, 0 to 20 mA, 1 to 5 V, 0 to 5 V, 0 to 10 V | Conversion speed: 250 ms/ 4 inputs | Accuracy: Platinum resistance thermometer input: $(\pm 0.3\% \text{ of PV or}$ $\pm 0.8^{\circ}\text{C}$, whichever is larger) ± 1 digit max. Thermocouple input: $(\pm 0.3\% \text{ of PV}$ or $\pm 1.5^{\circ}\text{C}$, whichever is larger) ± 1 digit max. *2 Voltage or current input: $\pm 0.3\%$ of F.S. ± 1 digit max. | | | 0.32 | | CJ1W-AD04U |

*1 Do not connect a Relay Output Unit to the same CPU Rack or to the same Expansion Rack as the CJ1W-PH41U. *2 L and -100°C or less for K and T are ±2°C±1 digit max., and 200°C or less for R and S is ±3°C±1 digit max. No accuracy is specified for 400°C or less for B.

Isolated-type DC Input Units

| Unit clas- sification | | Input points | Signal range selection | Conversion speed | Accuracy (at ambient tem- | External connection | No. of unit numbers | | nt con- ion (A) | Model |
|--------------------------------|-------------------------------------|-----------------|--|--|---|--------------------------------|------------------------|------|--------------------|------------|
| Sincation | name | points | | (resolution) | perature of 25°C) | connection | allocated | 5 V | 24 V | |
| CJ1 Special I/O Units | Isolated- type DC Input Units | 2 inputs | DC voltage: 0 to 1.25 V, -1.25 to 1.25 V, 0 to 5 V, 1 to 5 V, -5 to 5 V, 0 to 10 V, -10 to 10 V, ±10 V selectable range DC current: 0 to 20 mA, 4 to 20 mA | Conversion speed: 10 ms/ 2 inputs Resolution: 1/ 64,000 | Standard accuracy: ±0.05% of F.S. | Removable terminal block | 1 | 0.18 | 0.09 * | CJ1W-PDC15 |

* This is for an external power supply, and not for internal current consumption.

Analog I/O Units **Analog Input Units**

| Unit clas- sification | | Input points | Signal range selection | Signal range | Resolution | Conversion speed | Accuracy (at ambient temperature of | connec- | No. of unit numbers allocated | consu | rent mption A) | Model |
|--------------------------|--|-----------------|---------------------------------|---|--------------------------------------|--|--|----------------------------|-------------------------------------|-------|----------------------|---------------|
| | | | concorron | | | | 25°C) | uon | unooutou | 5 V | 24 V | |
| CJ1 Special I/O | Analog Input Units (High-speed type | 4 inputs | Set sep- arately for each | 1 to 5 V (1/10 0 to 10 V (1/2 –5 to 5 V (1/2 –10 to 10 V (1 4 to 20 mA (1 | 0,000), 0,000), 1/40,000), and | 20 μs/1 point, 25 μs/2 points, 30 μs/3 points, 35 μs/4 points | Voltage: ±0.2% of F.S. Current: ±0.4% of F.S. | Remov- able terminal | 1 | 0.52 | | CJ1W-AD042 *1 |
| Units | Analog Input Units | 8 inputs | input | 1 to 5 V, 0 to 5 V, 0 to 10 V, – | 1/4000, (Settable to | 1 ms/point max. (Settable to | Voltage: ±0.2% of F.S. | block | | 0.42 | | CJ1W-AD081-V1 |
| | | 4 inputs | | 10 to 10 V, – 10 to 10 V, 4 to 20 mA | 1/8000) *2 | 250 μs/point) *2 | Current: ±0.4% of F.S. *3 | | | 0.42 | | CJ1W-AD041-V1 |

*1 The direct conversion function using the AIDC instruction cannot be used.

*2 The resolution and conversion speed cannot be set independently. If the resolution is set to 1/4,000, then the conversion speed will be 1 ms/ point. *3 At 23 ±2°C

Analog Output Units

| Unit clas- | Product | Output | Signal range | Signal | Resolution | Conver- sion | Accuracy (at ambient | External connec- | External | No. of unit numbers | | ent con- tion (A) | Model |
|--------------------------------|--|--------------|--|--|----------------------|--|-------------------------------------|---------------------------------------|--|------------------------|------|----------------------|-------------------|
| sification | name | points | selection | rango | licooradion | speed | temperature of 25°C) | tion | power supply | allocated | 5 V | 24 V | incusi |
| | Analog Output Units High-speed type | 4 outputs | | 1 to 5 V (1/10 0 to 10 V (1/2 and –10 to 10 V (| 20,000), | 20 μs/ 1 point, 25 μs/ 2 points, 30 μs/ 3 points, 35 μs/ 4 points | ±0.3% of F.S. | | | | 0.40 | | CJ1W-DA042V *1 |
| CJ1 Special I/O Units | Analog | 8 outputs | Set sep- arately for each input | 1 to 5 V, 0 5 to 5 V, 0 to 10 V, -10 to 10 V | 1/4,000 (Settable | 1 ms/ point max. | _ | Remov- able ter- minal block | 24 VDC ^{+10%} , 140 mA max. | 1 | 0.14 | 0.14 *2 | CJ1W-DA08V |
| | Output Units | 8 outputs | | 4 to 20 mA | to 1/8,000) | (Settable to 250 μs/point) | | | 24 VDC ^{+10%} , 170 mA max. | | 0.14 | 0.17 *2 | CJ1W-DA08C |
| | | 4 outputs | | 1 to 5 V, 0 to 5 V, 0 to 10 V. | 1/4000 | 1 ms/ point | Voltage output: ±0.3% of F.S. | | 24 VDC ^{+10%} , 200 mA max. | | 0.12 | 0.2 *2 | CJ1W-DA041 |
| | | 2 outputs | | -10 to 10 V, 4 to 20 mA | 1/4000 | max. | Current output: ±0.5% of F.S. | | 24 VDC ^{+10%} , 140 mA max. | | 0.12 | 0.14 *2 | CJ1W-DA021 |

*1 The direct conversion function using the AODC instruction cannot be used. *2 This is for an external power supply, and not for internal current consumption

Analog I/O Units

| Unit clas- sification | | No. of points | Signal range selection | Signal range | Resolution (See note.) | Conversion speed | (at ambient tem- | connection | No. of unit numbers allocated | Cur cons tion | ump- | Model |
|--------------------------|------------------------|------------------|------------------------------|--|---------------------------|----------------------------|--|-----------------------|-------------------------------------|---------------------|------|----------------|
| | | | Selection | | | (See note.) | perature of 25 C) | | anocateu | 5 V | 24 V | |
| CJ1 Special | Analog I/O Units | 4 inputs | Set sepa- | 1 to 5 V, 0 to 5 V, 0 to 10 V. | 1/4,000 (Settable | 1 ms/point (Settable to | Voltage input: $\pm 0.2\%$ of F.S. Current input: $\pm 0.2\%$ of F.S. | Remov- able termi- | 1 | 0.58 | | CJ1W-MAD42 |
| I/O Units | | 2 outputs | rately for each input | –10 to 10 V, –10 to 10 V, 4 to 20 mA | to 1/8,000) | 500 μs/ point max.) | Voltage output: ±0.3% of F.S. Current output: ±0.3% of F.S. | nal block | I | 0.58 | | CJ I W-INIAD42 |

Note: The resolution and conversion speed cannot be set independently. If the resolution is set to 1/4,000, then the conversion speed will be 1 ms/point.

Temperature Control Units

| Unit classifi- | Product | | Specification | S | No. of unit numbers | Current con- sumption (A) | | Model |
|-------------------|-------------------------|-------------------------------|--|-------------------------------------|------------------------|------------------------------|------|------------|
| cation | name | No. of loops | Temperature sensor inputs | Control outputs | allocated | 5 V | 24 V | Model |
| | Tempera- | | Thermocouple input | Open collector NPN outputs (pulses) | | 0.25 | | CJ1W-TC003 |
| CJ1 Spe- | ture Con- trol Units | 2 loops, heater | (R, S, K, J, T, B, L) | Open collector PNP outputs (pulses) | | 0.25 | | CJ1W-TC004 |
| cial I/O Units | 1 Spe- 1 I/O | burnout detection function | Platinum resistance thermometer input | Open collector NPN outputs (pulses) | 2 | 0.25 | | CJ1W-TC103 |
| | | | (JPt100, Pt100) | Open collector PNP outputs (pulses) | | 0.25 | | CJ1W-TC104 |

High-speed Counter Unit

| Unit classifi- | Product | | Specifications | | No. of unit numbers | | nt con- ion (A) | Model |
|-------------------|-----------------------------------|--------------------|--|--------------------|------------------------|------|--------------------|------------|
| cation | name | Countable channels | Encoder A and B inputs, pulse input Z signals | Max. counting rate | allocated | 5 V | 24 V | Moder |
| CJ1 Spe- | High- speed Counter Unit | | Open collector Input voltage: 5 VDC, 12 V, or 24 V (5 V and 12 V are each for one axis only.) | 50 kHz | | | | |
| cial I/O Units | | 2 | RS-422 line driver | 500 kHz | 4 | 0.28 | | CJ1W-CT021 |

Note: The following functions become unavailable when it is used with the NJ-Series CPU unit.

- Counter value capture using allocation area(CIO)
- The capture, Stop/capture/continue, Stop/capture/reset/continue, and Capture/reset functions using External Control Input Function
- Pulse rate range control using Output Control Mode

The pulse rate measurement function

- · Because the NJ-Series has no power OFF interrupt task, operation cannot be restarted from the position at which the power was interrupted.
- Read or write the data using IORD/IOWR instruction
- Starting of External Interrupt Task by Output and External Control Input

Serial Communications Units

| Unit clas- sification | Product name | s | specifications | No. of unit numbers | Current con- sumption (A) | | Model |
|----------------------------|--|--|---|------------------------|------------------------------|----------|------------|
| Sincation | | Communications Interface | Communications functions | allocated | 5 V | 24 V | |
| | Serial Com- munications Units High-speed type | 2 RS-232C ports | The following functions can be selected | | 0.29 *2 | | CJ1W-SCU22 |
| CJ1 CPU Bus Units | li 1 | 2 RS-422A/485 ports | for each port: Protocol macro *1 Host Link NT Links (1:N mode) Serial Gateway | 1 | 0.46 | | CJ1W-SCU32 |
| | | 1 RS-232C port and 1 RS-422A/485 port | No-protocol *3 Modbus-RTU Slave | | 0.38 *2 | | CJ1W-SCU42 |
| RS-422A (| Converter | Converts RS-233C to RS-422 | 2A/RS-485. | | | <u> </u> | CJ1W-CIF11 |

Note: Simple Backup Function and Interrupt notification function cannot be used.

*1 You can activate protocol macro trace function when the CPU Unit is set to the RUN Mode. (MONITOR Mode is not available with the NJ-Series CPU Units.) *2 When an NT-AL001 RS-232C/RS-422A Conversion Unit is used, this value increases by 0.15 A/Unit. Add 0.20A/Unit when using NV3W-M_20L Programmable Terminals. Add 0.04A/Unit when using CJ1W-CIF11 RS-422A Adapters.

*3 Supported only by the SerialRcvNoClear Instructions with Serial communication unit version 2.1 or later, CPU Units with unit version 1.03 or later and the Sysmac Studio version 1.04 or higher.

EtherNet/IP Unit

| Unit classifi- | Product | | Specifications | | No. of unit numbers | Current con- sumption (A) | | Model |
|---------------------|---------------------|---|----------------------------------|--|------------------------|------------------------------|------|--------------|
| cation | name | Communications cable | Communications func- tions | Max. Units mount- able per CPU Unit | allocated | 5 V | 24 V | Woder |
| CJ1 CPU Bus Unit | EtherNet/IP Unit | STP (shielded twisted- pair) cable of category 5, 5e, or higher | Tag data link message service | 4 | 1 | 0.41 | | CJ1W-EIP21 * |

* Supported only by the EtherNet/IP Units with unit version 2.1 or later, CPU Units with unit version 1.01 or later and the Sysmac Studio version 1.02 or higher.

EtherCAT Slave Unit

| Jnit classifi- cation | | Specifications | Communications type | No. of unit numbers | | nt con- ion (A) | Model |
|--------------------------|------------------------|---|---|------------------------|------|--------------------|--------------|
| cation | | | | allocated | 5 V | 24 V | |
| CJ1 CPU Bus Units | EtherCAT Slave Unit | STP (shielded twisted-pair) cable of category 5 or higher with double shielding | Refreshing methods: Free-Run Mode PDO DATA SIZE: TxPDO 400byte or less/RxPDO: 400byte or less | 1 | 0.34 | | CJ1W-ECT21 * |

* When using with the Machine Automation Controller NJ /NXSeries, use CPU Units with unit version 1.10 or later and the Sysmac Studio version 1.13 or higher.

DeviceNet Unit

| Unit classifi- cation | Product name | Specifications | Communications type | No. of unit numbers | Current con- sumption (A) | | Model |
|--------------------------|-------------------|--|---|------------------------|------------------------------|------|------------|
| | | | | allocated | 5 V | 24 V | |
| CJ1 CPU Bus Units | DeviceNet Unit | Functions as master and/or slave; allows control of 32,000 points max. per master. | Remote I/O communications master (fixed or user-set allocations) Remote I/O communications slave (fixed or user-set allocations) Message communications | 1 | 0.29 | | CJ1W-DRM21 |

Note: 1. Simple backup function cannot be used.

2. DeviceNet configurator cannot be used. Use CX-Integrator.

CompoNet Master Unit

| | Product name | | No. of unit numbers | Current con- sumption (A) | | Model | |
|--------------------------|-------------------------|--|---|------------------------------|-----|-------|--------------|
| | | Communications functions | No. of I/O points per Master Unit | allocated | 5 V | 24 V | Model |
| CJ1 Special I/O Units | CompoNet Master Unit | Remote I/O communications Message communications | Word Slaves: 2,048 max. (1.024 inputs and 1,024 outputs) Bit Slaves: 512 max. (256 inputs and 256 outputs) | 1, 2, 4, or 8 | 0.4 | | CJ1W-CRM21 * |

Note: 1. Simple backup function cannot be used.
2. The FINS command to the CompoNet Master Unit cannot be issued.
* Supported only by the CPU Units with unit version 1.01 or later and the Sysmac Studio version 1.02 or higher.

ID Sensor Units

| | Product name | Specifications | | | No. of unit numbers | Current con- sumption (A) | | Model | |
|---------|--------------------|-------------------------|-------------------------------|--------------------------|------------------------|------------------------------|--------------|--------------|--|
| | | Connected ID Systems | No. of connected R/W heads | External power supply | allocated | 5 V | 24 V | Model | |
| CJ1 CPU | ID Sensor Units | V680-Series RFID | 1 | | 1 | 0.26 | 0.13 * | CJ1W-V680C11 | |
| | System | 2 | Not required. | 2 | 0.32 | 0.26 | CJ1W-V680C12 | | |

Note: The data transfer function using intelligent I/O commands can not be used. * To use a V680-H01 Antenna, refer to the V680 Series RFID System Catalog (Cat. No. Q151).

Peripheral Devices EtherCAT junction slaves

| Product name | | No. of ports | Power supply voltage | Current consumption (A) | Model |
|-----------------|------------------|--------------|--|----------------------------|---------|
| EtherCAT 3 | 20.4 to 28.8 VDC | 0.08 | GX-JC03 | | |
| junction slaves | | 6 | 20.4 to 28.8 VDC (24 VDC -15 to +20%) | 0.17 | GX-JC06 |

Note: 1. Please do not connect EtherCAT junction slaves with OMRON position control unit, Model CJ1W-NC 81/ 82.

2. EtherCAT junction slaves cannot be used for EtherNet/IP and Ethernet.

Industrial Switching Hubs for EtherNet/IP and Ethernet

| Product name | Appearance | Functions | No. of ports | Accessories | Current consumption (A) | Model |
|------------------------------|------------|---|--------------|------------------------|----------------------------|----------|
| Industrial Switching Hubs | | Quality of Service (QoS): EtherNet/IP control data priority 10/100BASE-TX, Auto-Negotiation | 5 | Power supply connector | 0.07 | W4S1-05D |

Note: Industrial switching hubs cannot be used for EtherCAT.

WE70 FA WIRELESS LAN UNITS (Final order entry date: The end of June, 2020)

| Product name | Applicable region | Туре | Model |
|----------------------------|-------------------|-----------------------|-----------------------|
| | Japan | Access Point (Master) | WE70-AP |
| | | Client (Slave) | WE70-CL |
| | Europe | Access Point (Master) | WE70-AP-EU |
| WE70 FA WIRELESS LAN UNITS | | Client (Slave) | WE70-CL-EU |
| | U.S | Access Point (Master) | WE70-AP-US * 1 |
| | 0.5 | Client (Slave) | WE70-CL-US *1 |
| | O an a da | Access Point (Master) | WE70-AP-CA * 2 |
| | Canada | Client (Slave) | WE70-CL-CA *2 |
| | | Access Point (Master) | WE70-AP-CN |
| | China | Client (Slave) | WE70-CL-CN |

Note: 1. A Pencil Antenna, mounting magnet, and screw mounting bracket are included as accessories.

2. Always use a model that is applicable in your region. Refer to the WE70 Catalog (Cat. No. N154). From December 2015, the WE70-AP-US and WE70-CL-US can be used in Mexico.

*1.

The Units will be sold in the USA until the end of May 2016. From January 2016, the WE70-AP-CA and WE70-CL-CA can be used in Singapore. *2.

General Specifications

| | Item | NJ501-□□□ | NJ301 | NJ101-□□□ | | | | | | |
|--------------------------|----------------------------------|---|--|---------------------------|--|--|--|--|--|--|
| Enclosure | | Mounted in a panel | | | | | | | | |
| Grounding Me | thod | Ground to less than 100 Ω | | | | | | | | |
| Dimensions (h | eight×depth×width) | 90 mm × 90 mm × 90 mm | 90 mm × 90 mm × 90 mm | | | | | | | |
| Weight | | 550 g (including the End Cover) | | | | | | | | |
| Current Consumption | | 5 VDC, 1.90 A (including SD Memory C | Card and End Cover) | | | | | | | |
| | Ambient Operating Temperature | 0 to 55°C | to 55°C | | | | | | | |
| | Ambient Operating Humidity | 10% to 90% (with no condensation) | 0% to 90% (with no condensation) | | | | | | | |
| | Atmosphere | Must be free from corrosive gases. | | | | | | | | |
| | Ambient Storage Temperature | -20 to 75°C (excluding battery) | 20 to 75°C (excluding battery) | | | | | | | |
| | Altitude | 2,000 m or less | | | | | | | | |
| Operation Environment | Pollution Degree | 2 or less: Meets IEC 61010-2-201. | | | | | | | | |
| | Noise Immunity | 2 kV on power supply line (Conforms to | DIEC 61000-4-4.) | | | | | | | |
| | Overvoltage Category | Category II: Meets IEC 61010-2-201. | | | | | | | | |
| | EMC Immunity Level | Zone B | | | | | | | | |
| | Vibration Resistance | Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude, 8.4 Acceleration of 9.8 m/s ² for 100 min in | to 150 Hz X, Y, and Z directions (10 sweeps of 10 r | nin each = 100 min total) | | | | | | |
| | Shock Resistance | Conforms to IEC 60068-2-27. 147 m/s ² , 3 times in X, Y, and Z direction | Conforms to IEC 60068-2-27. 147 m/s², 3 times in X, Y, and Z directions (100 m/s² for Relay Output Units) | | | | | | | |
| Battery | Life | 5 years at 25°C | | | | | | | | |
| Dattery | Model | CJ1W-BAT01 | CJ1W-BAT01 | | | | | | | |
| Applicable Sta | andards | Conforms to cULus, NK *1, LR *1, EU | Directives, RCM and KC Registration *2. | | | | | | | |

*1. Not supported by the NJ501-5300.*2. Supported only by the CPU Units with unit version 1.01 or later.

Performance Specifications

| | Item | | | | NJ501- | | NJ3 | 301- | NJ1 | 01- | | | |
|--------------------|-----------------------------------|---------------------------------------|--------------------------------------|----------------------------|--|-------------------------|--|---------------------------|---|---------------|--|--|--|
| | | | | □5□0 | □4□0 | □3□0 | 1200 | 1100 | 10 | 90 | | | |
| Processing | Instruction | LD instruct | ion | 1.1 ns (1.7 n | s or less) | | 1.6 ns (2.5 ns | s or less) *2 | 3.0 ns (4.5 ns | s or less) *2 | | | |
| Processing Time | Execution Times | Math Instru (for Long R | | 24 ns or mor | re *1 | | 35 ns or more | *2 | 63 ns or more | *2 | | | |
| | | Size | | 20 MB (400 KS) | | | 5 MB (100 KS) | | 3 MB (60 KS) | | | | |
| | Program capacity | | POU definition | 3,000 | | | 750 | | 450 | | | | |
| - | *3 | Number | POU instance | Using Sysma | lower : 6,000 | | Using Sysma Ver. 1.04 or I Using Sysma Ver. 1.05 or I | ower : 1,500 | 1,800 | | | | |
| | | No Retain | Size | 4 MB | | | 2 MB | | 1 | | | | |
| | | Attribute *4 | Number | 180,000 *5 | | | 90,000 *6 | | 22,500 | | | | |
| | Variables | _ | Size | 2 MB | | | 0.5 MB | | | | | | |
| Programming | capacity | Retain Attribute *7 | Number | 10,000 | | | Using Sysma 1.04 or lower Using Sysma 1.05 or highe | : 2,500 Ic Studio Ver. | 5,000 | | | | |
| Data type | Number | | 2,000 | | | 1,000 | | | | | | | |
| | M | CIO Area | | 6,144 words | (CIO 0 to CIC | 6143) | | | | | | | |
| | Memory for CJ-Series Units | Work Area | | 512 words (V | V0 to W511) | | | | | | | | |
| (Can be Specified | Holding Ar | ea | 1,536 words | (H0 to H1535 |) | | | | | | | | |
| | with AT Specifications for | DM Area | | 32,768 word | s (D0 to D327 | 67) | | | | | | | |
| | Variables.) | EM Area | | | s × 25 banks o E18_32767) | *8 | 32,768 words × 4 banks (E0_00000 to E3_3 | | | 3_32767) *8 | | | |
| м | Maximum | Maximum r CJ unit per Expansion | CPU Rack or | 10 Units | | | | | | | | | |
| | Number of Connectable Units | Maximum r CJ unit on | | 40 Units | | | | | | | | | |
| Unit | | Maximum r NX unit on | number of the system | 4,096 (on NX serie | s EtherCAT sl | ave terminal) | | | 400 (on NX series slave termina | | | | |
| Configuration | Maximum number | of Expansion Racks | | 3 max. | | | | | | | | | |
| | I/O Capacity | | umber of I/O CJ-series Units | 2,560 points max. | | | | | | | | | |
| | Power Supply | Model | | NJ-P□3001 | | | | | | | | | |
| | Unit for CPU Rack | Power OFF Detection | AC Power Supply | 30 to 45 ms | | | | | | | | | |
| | Racks | Time | DC Power Supply | 22 to 25 ms | | | | | | | | | |
| | | Maximum Montrolled | | Maximum nu 64 axes | Imber of axes 32 axes | which can be 16 axes | defined. 15 axes *9 | 15 axes *9 | 6 axes | | | | |
| | | Moti | on control axes | | umber of motic ontrol function 32 axes | | which can be | defined. 15 axes | 6 axes | | | | |
| | | Maximum r | umber of used | Maximum nu | mber of used | real axes. | | | | | | | |
| | Number of | real axes | | 64 axes | 32 axes | 16 axes | ollowing servo 8 axes | axes and end 4 axes | 2 axes | | | | |
| Viotion | Controlled Axes | liser | I motion control | | | | l motion contro | | 1 | | | | |
| Control | | | o axes | 64 axes | 32 axes | 16 axes | 8 axes | 4 axes | 2 axes | | | | |
| | | | number of axes terpolation axis | | | | | | | | | | |
| | | | axes for circular on axis control | r 2 axes per axes group | | | | | | | | | |
| | Maximum Number | of Axes Gro | ups | 32 groups | | | | | | | | | |
| | Motion Control Pe | riod | | The same co for EtherCA | | s that is used fo | or the process | data communi | The same control period as that is used for the process data communications cycle | | | | |

*1. When the hardware revision for the Unit is A or B.

*2. When the hardware revision for the Unit is A.

*3. This is the capacity for the execution objects and variable tables (including variable names).

*4. Words for CJ-series Units in the Holding, DM, and EM Areas are not included.

*5. The number of variables of the CPU Unit version 1.19 or earlier is 90,000.

*6. The number of variables of the CPU Unit version 1.18 or earlier is 22,500.

*7. Words for CJ-series Units in the CIO and Work Areas are not included.
*8. When the Spool function of the NJ501-__20 is enabled, the DB Connection Service uses E9_0 to E18_32767 (NJ501-1_20). When the Spool function of the NJ101-_20 is enabled, the DB Connection Service uses E1_0 to E3_32767 (NJ101-_20).

*9. This number of axes is achieved in a combination of a CPU Unit with unit version 1.06 or later and Sysmac Studio version 1.07 or higher. In other combinations, the maximum number of controlled axes is 8 axes (NJ301-1200) or 4 axes (NJ301-1100).

| | 14 | em | | | NJ501- | | NJ | 301- | N | J101 | |
|---------------------|---|------------------------------------|--|---|---|----------------------------------|----------------|-----------------|----------------|--------------|--|
| | | .5111 | | □5□0 | □4□0 | □3□0 | 1200 | 1100 | 10 | 90 | |
| | | Number of Cam Data | Maximum Points per Cam Table | 65,535 points | | | | | | | |
| Motion Control | Cams | Points | Maximum Points for All Cam Tables | 1,048,560 poir | nts | | 262,140 pc | pints | | | |
| | | Maximum Nu Tables | mber of Cam | 640 tables | 640 tables 160 tables | | | | | | |
| | Position Units | | | Pulses, millime | Pulses, millimeters, micrometers, nanometers, degrees or inches | | | | | | |
| | Override Facto | ors | | 0.00% or 0.019 | % to 500.00% | | | | | | |
| | Supported Ser | vices | | Sysmac Studio | Sysmac Studio connection | | | | | | |
| Peripheral | Physical Layer | • | | USB 2.0-compliant B-type connector | | | | | | | |
| USB Port | Transmission Node | Distance betwo | een Hub and | 5 m max. | | | | | | | |
| | Number of por | t | | 1 | | | | | | | |
| | Physical Layer | • | | 10Base-T or 1 | 00Base-TX | | | | | | |
| | Frame length | | | 1514 max. | | | | | | | |
| | Media Access | Method | | CSMA/CD | | | | | | | |
| | Modulation | | | Baseband | | | | | | | |
| | Topology | | | Star | | | | | | | |
| | Baud Rate | | | | | | | | | | |
| | Transmission | Media | | STP (shielded, | , twisted-pair) | cable of Etherne | et category 5, | 5e or higher | | | |
| be | Maximum Transmission Distance between Ethernet Switch and Node | | | 100m | | | | | | | |
| | Maximum Number of Cascade Connections | | | There are no r | estrictions if Et | thernet switch is | used. | | | | |
| | Maximum Nu nections | | mber of Con- | 32 | | | | | | | |
| | | Packet interv | al *10 | 1 to 10,000 ms Can be set for of nodes.) | | rements *11 on. (Data will be | refreshed at | the set interva | al, regardless | of the numbe | |
| | | Permissible Communications Band | | | *13 (including | heartbeat) | | | | | |
| | | Maximum Nu Tag Sets | mber of | 32 | | | | | | | |
| Built-in | CIP service: Tag Data | Tag types | | Network variables, CIO, Work, Holding, DM, and EM Areas | | | | | | | |
| EtherNet/IP Port | Links (Cyclic | Number of ta tion (i.e., per | gs per connec- tag set) | 8 (7 tags if Controller status is included in the tag set.) | | | | | | | |
| | Communicati ons) | | k Data Size per ize for all tags) | 256 | | | | | | | |
| | | Maximum nu | mber of tag | 19,200 bytes | | | | | | | |
| | | Maximum Da nection | ta Size per Con- | | | | | | | | |
| | | Maximum Nu trable Tag Se | mber of Regis- ts | 32 (1 connection = 1 tag set) | | | | | | | |
| | | Maximum Ta | g Set Size | 600 bytes (Two bytes are | e used if Contro | oller status is in | cluded in the | tag set.) | | | |
| | | Multi-cast Pa | cket Filter *14 | Supported. | | | | | | | |
| | | Class 3 (num tions) | ber of connec- | 32 (clients plus | s server) | | | | | | |
| | Cip Message Service: Explicit | UCMM (non- | Maximum Number of Cli- ents that Can Communicate at One Time | 32 | | | | | | | |
| | Messages | connection type) | Maximum Num- ber of Servers that Can Com- municate at One Time | 32 | | | | | | | |
| | Maximum num | ber of TCP so | cket service | 30 *15 | | | | | 30 | | |

*10.Data is updated on the line in the specified interval regardless of the number of nodes.
*11.The Packet interval of the CPU Unit version 1.02 or earlier is 10 to 10,000 ms in 1.0-ms increments.
*12.Means packets per second, i.e., the number of communications packets that can be sent or received in one second.
*13.The Permissible Communications Band of the CPU Unit version 1.02 or earlier is 1,000 pps.
*14.An IGMP client is mounted for the EtherNet/IP port. If an ethernet switch that supports IGMP snooping is used, filtering of unnecessary multicast packets is performed.
*15.The Maximum number of TCP socket service of the CPU Unit version 1.02 or earlier is 16.

| | | | | | NJ501- | | N | J301- | | NJ101 |
|---------------------------------|----------------------------------|--|---------------------------------------|--|--|-----------------|--------------|---------------|-----------------|----------------|
| | lt | em | | □5□0 | □4□0 | □3□0 | 1200 | 1100 | 10 | 90 |
| | | Support Prof | ile/Model | Micro Embedded PLCopen Inform | | r Profile | | | | |
| | | Default Endp | oint/Port | opc.tcp://192.16 | 8.250.1:4840/ | | | | | |
| | | Maximum nu sions (Client) | | 5 | | | | | | |
| | | Maximum nu tored Items p | mber of Moni- er server | 2,000 | | | | | | |
| | | Sampling rate tored Items (I | e of the Moni- ms) | 0, 50, 100, 250, 500, 1000,2000, 5000, 10000 if set to 0 (zero), it is assumed that is set to 50. | | | | | | |
| | | Maximum nu Subscription | mber of | 100 | | | | | | |
| | | Maximum number of vari- ables that can be published | | 10,000 | | | | | | |
| | | Maximum nu | mber of value It can be pub- | 10,000 | | | | | | |
| Built-in EtherNet/IP Port | | | mber of struc- ns that can be | 100 | | | | | | |
| | OPC UA Server (NJ501-1⊡00) | erver J501-1⊡00) Restrictions on variables unable to be published | | Double and or structures Structures inc dimensional a Structures nee Array which's from 0 | Structures includes double and over dimensional array Structures nested 4 and over Unions Array which's index number don't start from 0 Array which's element is over 2048 | | | | | |
| | | | | None Sign - Basic1: Sign - Basic2: Sign - Basic2: SignAndEncry SignAndEncry SignAndEncry | 56 56Sha256 /pt - Basic128 /pt - Basic256 | | | | | |
| | | | Authentication | | | | | | | |
| | | Application Authentica- tion | Maximum number of certification | Trusted certification Issuer certification Rejected certific | on: 32 | | | | | |
| | | User Authentication | Authentica- tion | User name / Pas Anonymous | | | | | | |
| | Communicatio | ns Standard | | IEC 61158 Type | 12 | | | | | |
| | EtherCAT Mas | | ons | Class B (Feature | e Pack Motion | Control complia | ant) | | | |
| | Physical Layer | | | 100BASE-TX | | | | | | |
| | Modulation | | | Baseband | | | | | | |
| | Baud Rate | | | 100 Mbps (100Base-TX) | | | | | | |
| | Duplex mode | | | Auto | | | | | | |
| | Topology | | | Line, daisy chair | n, branching a | nd ring *17 | | | | |
| Built-in EtherCAT | Transmission | Media | | Twisted-pair cat braiding) | ble of category | 5 or higher (do | uble-shielde | ed straight o | cable with alum | ninum tape and |
| Port | Maximum Tran between Node | | ance | 100m | | | | | | |
| | Maximum Num | ber of Slaves | | 192 | | | | | 64 | |
| | Range of node Maximum Proc | | | 1-192 Inputs: 5,736 by | | | | | | |
| | Maximum Proc | | per Slave | Outputs: 5,736 I Inputs: 1,434 by | tes | | | | | |
| | | | por olute | Outputs: 1,434 b | | | | | | 0/1.05- |
| | Communicatio | ns Cycle | | 500/1,000/2,000 | /4,000 μs *19 | | | | 1,000/2,00 |)0/4,000 μs |
| | Sync Jitter | | | 1 μs max. | | | | | | |
| Internal Cloc | :k | | | At ambient temp At ambient temp At ambient temp | erature of 25° | C: -1.5 to +1.5 | min error pe | er month | | |

*16.The number of value attributes is defined by the following formula. Number of value attributes = (Number of basic data type variables) + (Number of array-specified elements) + (Number of values in the structure)
*17.Ring topology is supported with the project version 1.40 or later of NJ_01-__00. Slaves on a ring topology should support a ring topology. If Omron slaves, please see the user's manual of slaves.
*18.For project unit version earlier than 1.40, the data must be within four frames.
*19.The Maximum Communications Cycle of the NJ301 CPU Unit version 1.02 or earlier and NJ501-R__ are 1,000/2,000/4,000 µs. The EtherCAT communications cycle of NJ501-4_0 for robot control is 1 ms or more.
Note: For robot control by NJ501-4_0, use the G5 series/1S series AC Servo Drive with built-in EtherCAT communications, absolute encoder, and brake and brake.

Performance Specifications Supported by NC Integrated Controller

| | | | | NJ501- | | |
|-----------|-----------------------------|--|------------------------------------|--|--|--|
| | | Item | | 5300 | | |
| | Task Period | Primary periodic cycle | | 500/1,000/2,000/4,000 μs | | |
| | Task Period | CNC Planner Service per | riod | 500 μs to 16 ms | | |
| | Number of CNC motors | Maximum number of CN | C motors *1 | 16 | | |
| | | Maximum number of CN | C coordinate systems | 4 | | |
| | CNC Coordinate system | Maximum number of CNO cluded in a CNC coordin (excluding spindle axes) | | 8 | | |
| Numerical | - | Number of spindle axes to nate system | that are included in a CNC coordi- | 1 | | |
| Control | Number of simu | Itaneous interpolation axe | es | 4 | | |
| | | Program buffer size *2 | | 16 MB | | |
| | NC Program | Maximum number of | Upper limit of main registrations | 512 | | |
| | | programs | Upper limit of sub registratioins | 512 | | |
| | | P variable | | Double-precision floating point 65536 *3 | | |
| | NC program variables | Q variable | | Double-precision floating point 8192 *3 | | |
| | | L variable | | Double-precision floating point 256 | | |
| | CNC motor | Maximum number of CN | C motor compensation tables | 32 | | |
| | compensation table | Maximum size of all com | pensation tables | 1 MB | | |

*1. The number of controlled axes of the MC Control Function Module is included.

*2. The number of programs and their capacities that can be loaded into the CPU Unit at the same time.
The program capacity is the maximum size available. As fragmentation will occur, the size that is actually available will be smaller than the maximum size.

*3. Some parts of the area are reserved by the system.

NJ-Series Function Specifications

| | | Item | | NJ501-000 NJ301-000 NJ101-00 | | | | | |
|------------------|----------------------------|--|---|--|---------|--|--|--|--|
| | Function | | | I/O refreshing and the user program are executed in units that are calle. Tasks are used to specify execution conditions and execution priority. | d tasks | | | | |
| | | Periodically Ex- | Maximum Number of Pri- mary Periodic Tasks | 1 | | | | | |
| | | ecuted Tasks | Maximum Number of Peri- odic Tasks | 3 | | | | | |
| Tasks | | Conditionally executed tasks | Maximum number of event tasks | 32 | | | | | |
| ruono | | *1 | Execution conditions | When Activate Event Task instruction is executed or when condition expression for variable is met. | | | | | |
| | | System Service Tasks (NJ501-R | Maximum number of V+ Tasks | 64 | | | | | |
| | Setup | System Service | Monitoring Settings | The execution interval and the percentage of the total user program ex time are monitored for the system services (processes that are execut the CPU Unit separate from task execution). | | | | | |
| | | Programs | | POUs that are assigned to tasks. | | | | | |
| | POU (program | Function Blocks | | POUs that are used to create objects with specific conditions. | | | | | |
| | organization units) | Functions | | POUs that are used to create an object that determine unique outputs inputs, such as for data processing. | for the | | | | |
| | Programming Lan- guages | Types | | Ladder diagrams *2 Structured text (ST) V+ (NJ501-R | | | | | |
| | Namespaces *3 | | | A concept that is used to group identifiers for POU definitions. | | | | | |
| | Variables | External Ac- cess of Vari- ables | Network Variables | The function which allows access from the HMI, host computers, or other Controllers | | | | | |
| | | | Boolean | BOOL | | | | | |
| | | | Bit Strings | BYTE, WORD, DWORD, LWORD | | | | | |
| | | | Integers | INT, SINT, DINT,LINT, UINT, USINT, UDINT, ULINT | | | | | |
| | | | Real Numbers | REAL, LREAL | | | | | |
| | | Data Types | Durations | TIME | | | | | |
| | | | Dates | DATE | | | | | |
| | | | Times of Day | TIME_OF_DAY | | | | | |
| | | | Date and Time | DATE_AND_TIME | | | | | |
| | | | Text Strings | STRING | | | | | |
| | | Derivative Data | Гуреѕ | Structures, unions, enumerations | | | | | |
| | | | Function | A derivative data type that groups together data with different variable | types | | | | |
| Program- ming | Data Types | | Maximum Number of Mem- bers | 2048 | | | | | |
| | | Structures | Nesting Maximum Levels | 8 | | | | | |
| | | | Member Data Types | Basic data types, structures, unions, enumerations, array variables | | | | | |
| | | | Specifying Member Offsets | You can use member offsets to place structure members at any memory locations. $\!$ | vry | | | | |
| | | | Function | A derivative data type that groups together data with different variable | types | | | | |
| | | Unions | Maximum Number of Mem- bers | 4 | | | | | |
| | | | Member Data Types | BOOL, BYTE, WORD, DWORD, LWORD | | | | | |
| | | Enumerations | Function | A derivative data type that uses text strings called enumerators to exp variable values. | ess | | | | |
| | | | Function | An array is a group of elements with the same data type. You specify the number (subscript) of the element from the first element to specify the element. | | | | | |
| | | Array Specifi- cations | Maximum Number of Dimensions | 3 | | | | | |
| | Data Type Attri- butes | Cations | Maximum Number of Elements | 65535 | | | | | |
| | | | Array Specifications for FB Instances | Supported. | | | | | |
| | | Range Specifica | tions | You can specify a range for a data type in advance. The data type car only values that are in the specified range. | take | | | | |
| | | Libraries *3 | | User libraries | | | | | |

*1. Supported only by the CPU Units with unit version 1.03 or later.
*2. Inline ST is supported. (Inline ST is ST that is written as an element in a ladder diagram.)
*3. Supported only by the CPU Units with unit version 1.01 or later.

| | | Item | | NJ501-□□□ | NJ301-□□□ | NJ101-□□□ |
|-------------------|--------------------|---------------------------------------|---|---|--|------------------------------|
| | Control Modes | | | position control, velocity c | control, torque control | |
| | Axis Types | | | Servo axes, virtual servo | axes, encoder axes, and v | irtual encoder axes |
| | Positions that can | be managed | | Command positions and actual positions | | |
| | | | Absolute Positioning | Positioning is performed for a target position that is specified with an abso value. | | specified with an absolute |
| | | Single-axis Po- | Relative Positioning | Positioning is performed for a specified travel distance from the command current position. | | |
| | | sition Control | Interrupt Feeding | Positioning is performed for a specified travel distance from the position where an interrupt input was received from an external input. | | |
| | | | Cyclic synchronous absolute positioning *1 | | s command positions in ev | |
| | | | Velocity Control | Velocity control is perform | ned in Position Control Mod | de. |
| | | Single-axis Ve- locity Control | Cyclic Synchronous Velocity Control | | tput each control period in | |
| | | Single-axis Torque Control | Torque Control | The torque of the motor is | controlled. | |
| | | | Starting Cam Operation | A cam motion is performe | d using the specified cam | table. |
| | | | Ending Cam Operation | - | | input parameter is ended. |
| | | | Starting Gear Operation | | ecified gear ratio is perform | |
| | | Single-axis Synchronized | Positioning Gear Operation | A gear motion with the sp between a master axis an | ecified gear ratio and sync d slave axis. | position is performed |
| | | Control | Ending Gear Operation | The specified gear motior | or positioning gear motion | n is ended. |
| | | | Synchronous Positioning | Positioning is performed i | n sync with a specified ma | ster axis. |
| | | | Master Axis Phase Shift | The phase of a master axis in synchronized control is shifted. | | |
| | | | Combining Axes | The command positions of two axes are added or subtracted and the re output as the command position. | | ubtracted and the result is |
| | | Single-axis | Powering the Servo | The Servo in the Servo D | e axis motion. | |
| Motion Control | | Manual Operation | Jogging | An axis is jogged at a specified target velocity. | | |
| | Single-axis | | Resetting Axis Errors | Axes errors are cleared. | | |
| | | | Homing | A motor is operated and the limit signals, home proximity signal, and hor signal are used to define home. | | |
| | | | Homing with parameter *1 | | a motor is operated and t e signal are used to define | |
| | | | High-speed Homing | Positioning is performed f | or an absolute target posit | ion of 0 to return to home. |
| | | | Stopping | An axis is decelerated to | a stop at the specified rate | |
| | | | Immediately Stopping | An axis is stopped immed | liately. | |
| | | | Setting Override Factors | The target velocity of an a | axis can be changed. | |
| | | | Changing the Current Po- sition | The command current position. | sition or actual current pos | ition of an axis can be |
| | | | Enabling External Latches | The position of an axis is | recorded when a trigger of | ccurs. |
| | | Auxiliary Func- | Disabling External Latches | The current latch is disable | led. | |
| | | tions for Sin- gle-axis Control | Zone Monitoring | You can monitor the com when it is within a specifie | mand position or actual po ed range (zone). | sition of an axis to see |
| | | Control | Enabling digital cam switches *4 | You can turn a digital out | out ON and OFF according | to the position of an axis. |
| | | | Monitoring Axis Following Error | You can monitor whether the difference between the command po actual positions of two specified axes exceeds a threshold value. | | |
| | | | Resetting the Following Error | The error between the cor set to 0. | nmand current position and | d actual current position is |
| | | | Torque Limit | The torque control function of the Servo Drive can be enabled or dis the torque limits can be set to control the output torque. | | |
| | | | Slave Axis Position Com- pensation *5 | This function compensate synchronized control. | s the position of the slave | axis currently in |
| | | | Cam monitor (NJ□01-□□00) | Outputs the specified offs | et position for the slave ax | is in synchronous control. |
| | | | Start velocity *6 | You can set the initial velo | ocity when axis motion star | rts. |

*1. Supported only by the CPU Units with unit version 1.03 or later.
*4. Supported only by the CPU Units with unit version 1.06 or later.
*5. Supported only by the CPU Units with unit version 1.10 or later.
*6. Supported only by the CPU Units with unit version 1.05 or later.

| | | Item | | NJ501 NJ301 NJ101 | | |
|-------------------|--------------------------|---|---|--|--|--|
| | | | Absolute Linear Interpola- | Linear interpolation is performed to a specified absolute position. | | |
| | | Multi-axes Co- | tion Relative Linear Interpola- | Linear interpolation is performed to a specified relative position. | | |
| | | ordinated Con- | tion Circular 2D Interpolation | | | |
| | | trol | Axes Group Cyclic Syn- | Circular interpolation is performed for two axes. | | |
| | | | chronous Absolute Posi- tioning | A positioning command is output each control period in Position Control Mode.*3 | | |
| | | | Resetting Axes Group Er- rors | Axes group errors and axis errors are cleared. | | |
| | Axes Groups | | Enabling Axes Groups | Motion of an axes group is enabled. | | |
| | | | Disabling Axes Groups | Motion of an axes group is disabled. | | |
| | | Auxiliary Func- | Stopping Axes Groups | All axes in interpolated motion are decelerated to a stop. | | |
| | | tions for Multi- axes Coordi- | Immediately Stopping Axes Groups | All axes in interpolated motion are stopped immediately. | | |
| | | nated Control | Setting Axes Group Over- ride Factors | The blended target velocity is changed during interpolated motion. | | |
| | | | Reading Axes Group Positions | The command current positions and actual current positions of an axes gro can be read.*3 | | |
| | | | Changing the Axes in an Axes Group | The Composition Axes parameter in the axes group parameters can be overwritten temporarily.*3 | | |
| | | | Setting Cam Table Proper- ties | The end point index of the cam table that is specified in the input parameter changed. | | |
| | | Cams | Saving Cam Tables | The cam table that is specified with the input parameter is saved in non- volatile memory in the CPU Unit. | | |
| | Common Items | | Generating cam tables *7 | The cam table that is specified with the input parameter is generated from t cam property and cam node. | | |
| | | Parameters | Writing MC Settings | Some of the axis parameters or axes group parameters are overwritten temporarily. | | |
| | | T drameters | Changing axis parameters *7 | You can access and change the axis parameters from the user program. | | |
| Motion Control | | Count Modes | | You can select either Linear Mode (finite length) or Rotary Mode (infinite length). | | |
| | | Unit Conversions | | You can set the display unit for each axis according to the machine. | | |
| | | Acceleration/ Deceleration Control | Automatic Acceleration/ Deceleration Control | Jerk is set for the acceleration/deceleration curve for an axis motion or axe group motion. | | |
| | | | Changing the Acceleration and Deceleration Rates | You can change the acceleration or deceleration rate even during acceleration deceleration. | | |
| | | In-position Check | | You can set an in-position range and in-position check time to confirm when positioning is completed. | | |
| | | Stop Method | | You can set the stop method to the immediate stop input signal or limit inp signal. | | |
| | | Re-execution of Motion Control Instructions | | You can change the input variables for a motion control instruction during execution and execute the instruction again to change the target values duri operation. | | |
| | Auxiliary Func- tions | Multi-execution tions (Buffer Mo | of Motion Control Instruc- de) | You can specify when to start execution and how to connect the velocities between operations when another motion control instruction is executed during operation. | | |
| | | Continuous Axe Mode) | s Group Motions (Transition | You can specify the Transition Mode for multi-execution of instructions for ax group operation. | | |
| | | | Software Limits | Software limits are set for each axis. | | |
| | | | Following Error | The error between the command current value and the actual current value monitored for an axis. | | |
| | | Monitoring Functions | Velocity, Acceleration Rate, Deceleration Rate, Torque, Interpolation Velocity, Interpolation Acceleration Rate, And Interpolation Deceleration Rate | You can set and monitor warning values for each axis and each axes group | | |
| | | Absolute Encoder Support | | You can use an OMRON G5-Series or 1S-Series Servomotor with an Absolu Encoder to eliminate the need to perform homing at startup. | | |
| | | Input signal logi | c inversion *6 | You can inverse the logic of immediate stop input signal, positive limit input signal, negative limit input signal, or home proximity input signal. | | |
| | External Interface | Signals | | The Servo Drive input signals listed on the right are used. Home signal, hor proximity signal, positive limit signal, negative limit signal, immediate stop signal, and interrupt input signal | | |

*3. Supported only by the CPU Units with unit version 1.01 or later.
*6. Supported only by the CPU Units with unit version 1.05 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.

| | | Item | | NJ501-□□□□ | NJ301-000 | NJ101-□□□ |
|-----------------------------|--------------------------|---|--|--|---|---------------------------|
| | EtherCAT Slaves | Maximum Numb | er of Slaves | 192 | · · · · · · · · · · · · · · · · · · · | 64 |
| Unit (I/O) | | Maximum numbe | er of Units | 40 | | |
| Manage- ment | CJ-Series Units | Basic I/O Units Load Short-circuit Protec- tion and I/O Disconnection Detection | | Alarm information for Basic I/O Units is read. | | |
| | Peripheral USB Port | | | A port for communications with various kinds of Support Software running on a personal computer. | | |
| | | Communications | s protocol | TCP/IP, UDP/IP | | |
| | | CIP Communications | Tag Data Links | Programless cyclic data exchange is performed with the devices on the EtherNet/IP network. | | |
| | | Service | Message Communications | network. | o or received from the dev | |
| | | TCP/IP functions | CIDR | (class A to C) of IP addre | | _ |
| | Built-in EtherNet/ | | Socket Services | Data is sent to and receive protocol. Socket communications in | ed from any node on Ether | net using the UDP or TCF |
| | IP port Internal Port | | FTP client *7 | | vritten to computers at othe munications instructions a | |
| | | TCP/IP Applica- tions | FTP Server | Files can be read from or computers at other Ethern | written to the SD Memory net nodes. | Card in the CPU Unit from |
| | | | Automatic Clock Adjust- ment | Clock information is read from the NTP server at the specified time or at a specified interval after the power supply to the CPU Unit is turned ON. The internal clock time in the CPU Unit is updated with the read time. | | |
| | | | SNMP Agent | | Built-in EtherNet/IP port internal status information is provided to ne management software that uses an SNMP manager. | |
| Communica- | | OPC UA (NJ501-1⊡00) | Server Function | Functions to respond to requests from clients on the OPC UA network | | |
| tions | | Supported Ser- vices | Process Data Communica- tions | Control information is exchanged in cyclic communications between the EtherCAT master and slaves. | | |
| | | | SDO Communications | A communications method to exchange control information in noncyclic ever communications between EtherCAT master and slaves. This communications method is defined by CoE. | | |
| | | Network Scanning | | Information is read from connected slave devices and the slave configuration is automatically generated. | | |
| | EtherCAT Port | DC (Distributed | Clock) | Time is synchronized by sharing the EtherCAT system time among all EtherCAT devices (including the master). | | |
| | EtherCAT Port | Enable/disable S | ettings for Slaves | | ed or disabled as communi | 5 |
| | | Disconnecting/Connecting Slaves | | Temporarily disconnects a slave from the EtherCAT network for maintenanc such as for replacement of the slave, and then connects the slave again. | | |
| | | Hot connect | | Process data communication with slaves which are registed as "Hot connect group" will start automatically. | | |
| | | Fast connect | I | Quickly ethernet linking fu | inction with slaves to acco | mmodate "Fast connect". |
| | | Supported Ap- plication Proto- col | СоЕ | SDO messages of the CAN application can be sent to slaves via EtherCAT. | | |
| Communications Instructions | | | The following instructions are supported. CIP communications instructions, socket communications instructions, SDO message instructions, no-protocol communications instructions, protocol macru instructions, and FTP client instructions *7, and Modbus RTU protocl instruction *8 | | | |
| Operation Management | RUN Output Conta | cts | | The output on the Power | Supply Unit turns ON in R | JN mode. |
| | | Function | | Events are recorded in the | e logs. | |
| System | Event Lorge | Maximum | System event log | 1,024 | 512 | |
| Management | Event Logs | number of | Access event log | 1,024 | 512 | |
| | | events | User-defined event log | 1,024 | 512 | |

*6. Supported only by the CPU Units with unit version 1.05 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.
*8. Supported only by the CPU Units with unit version 1.11 or later.

| | | Item | | NJ501-□□□□ | NJ301-□□□□ | NJ101-□□□ | | |
|--------------------------|---|--------------------------------|---|--|---|--|--|--|
| | Online Editing | Single | | | s, functions, and global var s can change different POI | | | |
| | Forced Refreshing | | | | The user can force specific variables to TRUE or FALSE. | | | |
| | | Maximum Num- | Device Variables for Ether- CAT Slaves | 64 | | | | |
| | | ber of Forced Variables | Device Variables for CJ-se- ries Units and Variables with AT Specifications | 64 | | | | |
| | MC Test Run *9 | | | Motor operation and wirin | g can be checked from the | e Sysmac Studio. | | |
| | Synchronizing | | | The project file in the Sys made the same when onl | mac Studio and the data ir ine. | n the CPU Unit can be | | |
| | Differentiation mon | itoring *1 | | Rising/falling edge of con | tacts can be monitored. | | | |
| | | Maximum numbe | er of contacts *1 | 8 | | | | |
| Debugging | | Types | Single Triggered Trace | and then tracing stops au | - | • | | |
| | | | Continuous Trace | Data tracing is executed Sysmac Studio. | continuously and the trace | data is collected by the | | |
| | | Trace | er of Simultaneous Data | 4 *10 | 2 | | | |
| | | Maximum Number of Records | | 10,000 | t | | | |
| | Data Tracing | Sampling | Maximum Number of Sam- pled Variables | 192 variables | 48 variables | | | |
| | | Timing of Sampling | | Sampling is performed for the specified task period, at the specified time, or when a sampling instruction is executed. | | | | |
| | | Triggered Traces | 5 | Trigger conditions are set to record data before and after an event. | | after an event. | | |
| | | | Trigger Conditions | When BOOL variable changes to TRUE or FALSE Comparison of non-BOOL variable with a constant Comparison Method: Equals (=), Greater than (>), Greater than or equals (\geq) Less Than (<), Less than or equals (\leq), Not equal (\neq) | | | | |
| | | | | | rigger position setting: A slider is used to set the percentage of sampling efore and after the trigger condition is met. | | | |
| | Simulation | | | | Unit is emulated in the Sy | smac Studio. | | |
| | | Controller Er- rors | Levels | Major fault, partial fault, minor fault, observation, and information | | | | |
| Reliability Functions | Self-diagnosis | User-defined errors | | User-defined errors are registered in advance and then records are created b executing instructions. | | | | |
| | | | Levels | | 8 levels | | | |
| | | CPU Unit Names and Serial IDs | | | PU Unit from the Sysmac S I to the name of the CPU L | Studio, the CPU Unit name Jnit being connected to. | | |
| | | Soft- Protection | User Program Transfer with No Restoration Infor- mation | You can prevent reading data in the CPU Unit from the Sysmac Studio. | | | | |
| | Protecting Soft- | | CPU Unit Write Protection | You can prevent writing of Memory Card. | ata to the CPU Unit from t | he Sysmac Studio or SD | | |
| Security | ware Assets and Preventing Oper- ating Mistakes | | Overall Project File Protec- tion | You can use passwords to Sysmac Studio. | p protect .smc files from un | authorized opening on the | | |
| | ating wistakes | | Data Protection | You can use passwords t | o protect POUs on the Sys | smac Studio.*3 | | |
| | | Verification of O | peration Authority | Online operations can be restricted by operation rights to prevent damage to equipment or injuries that may be caused by operating mistakes. | | | | |
| | | | Number of Groups | 5*11 5 | | | | |
| | | Verification of U | ser Program Execution ID | The user program cannot be executed without entering a user program execution ID from the Sysmac Studio for the specific hardware (CPU Unit). | | | | |
| | Storage Type | | | SD Memory Card, SDHC | Memory Card | | | |
| | | Automatic transf | er from SD Memory Card *1 | | older on an SD Memory Ca the Controller is turned O | ard is automatically loaded N. | | |
| SD Memo- | | Transfer progra | m from SD Memory Card *8 | The user program on an SD Memory Card is loaded when the user changes system-defined variable to TRUE. | | | | |
| ry Card Functions | Application | SD Memory Carc Instructions | I Operation | | ory Cards from instructions | | | |
| | | File Operations f | rom the Sysmac Studio | read/write standard docu | ations for Controller files in ment files on the computer | | | |
| | | SD Memory Card | Life Expiration Detection | Notification of the expirati systemdefined variable a | | mory Card is provided in a | | |

*1. Supported only by the CPU Units with unit version 1.03 or later.
*3. Supported only by the CPU Units with unit version 1.01 or later.
*8. Supported only by the CPU Units with unit version 1.11 or later.

*9. Cannot be used with the NJ101-9000.

*10.Maximum Number of Simultaneous Data Trace of the NJ501-□□20 CPU Unit with unit version 1.08 or later is 2. *11.When the NJ501 CPU Units with unit version 1.00 is used, this value becomes two.

| | Item | | | NJ501-□□□□ | NJ301-□□□ | NJ101-□□□□ | | |
|---|---|--|---|---|---|------------|--|--|
| | | | Using front switch | You can use front switch | You can use front switch to backup, compare, or restore data. | | | |
| Backup ba | | | Using system-defined vari- ables | You can use system-defined variables to backup, compare, or restore data. *12 | | | | |
| | Opera SD Memory Card backup functions | Operation Memory Card Operations Dialog Box on Sysmac Studio | | Backup and verification operations can be performed from the SD Memory Card Operations Dialog Box on the Sysmac Studio. | | | | |
| functions *1 | | | Using instruction *7 | Backup operation can be performed by using instruction. | | ion. | | |
| | | Protection | Prohibiting backing up data to the SD Memory Card | Prohibit SD Memory Card backup functions. | | | | |
| Sysmac Studio Controller backup functions | | | Backup, restore, and verit the Sysmac Studio. | ication operations for Units | can be performed from | | | |

*1. Supported only by the CPU Units with unit version 1.03 or later.
*7. Supported only by the CPU Units with unit version 1.08 or later.
*12. Restore is supported with unit version 1.14 or later.

Function Specifications of Database Connection CPU Units

Besides functions of the NJ501-

| Item | | | NJ501-1⊡20 | Description NJ101-⊡020 | | |
|--|---|--|--|---|--|--|
| Supported | port | | Built-in EtherNet/IP port | | | |
| Supported | | | Microsoft Corporation: SQL Server 2012/2014/2016/2017/2019 Oracle Corporation: Oracle Database 11g /12c/18c/19c MySQL Community Edition 5.6/5.7/8.0 *3 International Business Machines Corporation (IBM): DB2 for Linux, UNIX and Windows 9.7/10.1/10.5/11.1 * Firebird Foundation Incorporated: Firebird 2.5 *4 The PostgreSQL Global Development Group: PostgreSQL 9.4/9.5/9.6/10/11/12/13 *4 | | | |
| Number of DB Connections Number of databases that can be connected at the same time) | | n be connected at the | 3 connections max. *5 | 1 | | |
| same time) | Supported operations | | CPU Units. | executing DB Connection Instructions in the NJ/NX-series (UPDATE), Retrieving records (SELECT), Deleting **6, and Execute Batch Insert *6 | | |
| | Max. number of in for simultaneous | | 32 | | | |
| in an INSERT operation | | | SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000 | | | |
| | Max. number of columns in an UPDATE operation Max. number of columns in a SELECT operation | | SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000 | | | |
| | | | SQL Server: 1,024 Oracle: 1,000 DB2: 1,000 MySQL: 1,000 Firebird: 1,000 PostgreSQL: 1,000 | | | |
| Instruction | Max. number of r in the output of a | ecords SELECT operation | 65,535 elements, 4 MB | 65,535 elements, 2 MB | | |
| | Stored proce- dure call *6 | Supported databases | SQL Server Oracle Database MySQL Community Edition PostgreSQL *7 | | | |
| | | Argument (Sum of IN, OUT and INOUT) | Up to 256 variables *8 | | | |
| | | Return value | One variable | | | |
| | | Result set | Supported | | | |
| | | Spool function | Not supported | | | |
| | Batch insert ex- ecution *6 | Supported databases | SQL Server Oracle Database MySQL Community Edition PostgreSQL *7 | | | |
| | | Supported data size | Less than 1,000 columns and upper limit of str | ructure variable size or less *9 | | |
| | | Spool function | Not supported | | | |
| | | DB Map Variables for can be connected *10 | SQL Server: 60 Oracle: 30 DB2: 30 *4 MySQL: 30 Firebird: 15 *4 PostgreSQL: 30 *4 | SQL Server: 15 Oracle: 15 DB2: 15 MySQL: 15 Firebird: 15 PostgreSQL: 15 | | |
| Run mode of the DB Connection Service Spool function Spool capacity | | on Service | Operation Mode or Test Mode Operation Mode: When each instruction is executed, the service actually accesses the DB. Test Mode: When each instruction is executed, the service ends the instruction normally without accessing the DB actually. | | | |
| | | | Used to store SQL statements when an error of communications are recovered from the error. | | | |
| | | | 1 MB *11 | 192 KB *11 | | |
| Operation Log function | | | The following three types of logs can be recorded. • Execution Log: Log for tracing the executions of the DB Connection Service. • Debug Log: Detailed log for SQL statement executions of the DB Connection Service. • SQL Execution Failure Log: Log for execution failures of SQL statements in the DB. | | | |
| DB Connec | tion Service shutd | own function | Used to shut down the DB Connection Service after automatically saving the Operation Log files into the SD Memory Card. | | | |
| Encrypted Communication | | Supported databases | SQL Server Oracle Database MySQL Community Edition PostgreSQL *7 | | | |
| | | | · · · · · · · · · · · · · · · · · · · | | | |

30

*1. SQL Server 2014, Oracle Database 12c and PostgreSQL 9.4 are supported by the DB Connection Service Version 1.02 or higher. SQL Server 2016, My SQL 5.7, DB2 11.1 and Postgre SQL 9.5/9.6 are supported by the DB Connection Service Version 1.03 or higher. SQL Server 2017 is supported by the DB Connection Service Version 1.04 or higher.

Oracle Database 18c, MySQL Community Edition 8.0 and PostgreSQL 10 are supported by the DB Connection Service Version 2.00 or higher. You cannot use Oracle 10g with the DB Connection Service version 2.00 or higher.

- SQL Server 2019, Oracle Database 19c and PostgreSQL 11/12/13 are supported by the DB Connection Service Version 2.01 or higher. *2. Connection to the DB on the cloud is not supported.
- *3. The supported storage engines of the DB are InnoDB and MyISAM.
- *4. NJ501-4320 is not supported.
- *5. When two or more DB Connections are established, the operation cannot be guaranteed if you set different database types for the connections.
- *6. The function is available for the DB Connection Service Version 2.00 or higher.
- *7. The NJ501-4320 does not support PostgreSQL.
- *8. Depends on members of a structure.
- *9. Constrained by the memory capacity for variables. See the specifications for the memory capacity for variables.
- *10.Even if the number of DB Map Variables has not reached the upper limit, the total number of members of structures used as data type of DB Map Variables is 10,000 members max.
- *11.Refer to "NJ/NX-series Database Connection CPU Units User's Manual(W527)" for the information.

Note: The extended support for databases has ended for the following DB versions.

Please consider replacing the current database with a new version.

| Item | Discription |
|--|-------------|
| Microsoft Corporation: SQL Server | 2008/2008R2 |
| Oracle Corporation: Oracle Database | 10g |
| Oracle Corporation: MySQL Community Edition | 5.1/5.5 |
| International Business Machines Corporation (IBM): DB2 for Linux, UNIX and Windows | 9.5 |
| Firebird Foundation Incorporated: Firebird | 2.1 |
| The PostgreSQL Global Development Group: PostgreSQL | 9.2/9.3 |

NJ-Series Function Specifications of SECS/GEM CPU Units

Besides functions of the NJ501-1300, functions supported by the NJ501-1340 are as follows.

| Item | Description |
|-------------------------------|--|
| Supported port | Built-in EtherNet/IP port |
| Supported standard *1 | The Unit conforms to the following SEMI standards: E37-0303, E37.1-0702, E5-0707, and E30-0307 |
| Fundamental GEM requirement | State Model, Equipment Processing State, Host-initiated S1, F13/F14 Scenario, Event Notification, On-Line Identification, Error Message, Control (Operator Initiated), Documentation |
| Additional GEM capability | Establish Communications, Dynamic Event Report Configuration, Variable Data Collection, Trace Data Collection, Status Data Collection, Alarm Management, Remote Control, Equipment Constant, Process Recipe Management *1, Material Movement, Equipment Terminal Service, Clock, Limit Monitoring, Spooling *2, Control (Host Initiated) |
| User-defined message | You can create non-GEM compliant communications messages and have host communications. |
| GEM specific instruction | The Unit supports 29 instructions to perform the following: • Changing the GEM Service status. • Setting HSMS communications. • Reporting events and reporting alarms. • Acknowledging host commands and enhanced remote commands. • Changing equipment constants. • Uploading and downloading process programs. • Sending and acknowledging equipment terminal messages. • Requesting to change time. • Sending user-defined messages. • Getting SECS communications log. |
| GEM Service log *2 | Can record the following information. • HSMS communications log: Keeps log of HSMS communications operations. • SECS message log: Keeps log of SECS-II communications messages. • Execution log: Keeps log of executions of GEM instructions. |
| Shutting down the GEM Service | Saves the spool data and GEM Service log records into an SD Memory Card and ends the GEM Service. |

*1. E42 recipes, large process programs, and E139 recipes are not supported.

*2. The capability is not available when no SD Memory Card is mounted.

Conformance to Fundamental GEM Requirements and Additional Capabilities

| Fundamental GEM requirements | GEM-compliant | Additional capabilities | GEM-compliant | |
|-------------------------------------|---------------|------------------------------------|---|--|
| State Model | | Establish Communications | | |
| Equipment Processing State | - | Dynamic Event Report Configuration | | |
| Host-initiated S1, F13/F14 Scenario | | Variable Data Collection | | |
| Event Notification | | Trace Data Collection | Yes | |
| On-Line Identification | Yes | Status Data Collection | 163 | |
| Error Message | _ | Alarm Management | _ | |
| ő | | Remote Control | | |
| Control (Operator Initiated) | _ | Equipment Constant | | |
| Documentation | | Process Recipe Management | Process program: Yes E42 recipes: No E139 recipes: No | |
| | | | | |

| Remote Control | | | |
|----------------------------|---|--|--|
| Equipment Constant | | | |
| Process Recipe Management | Process program: Yes E42 recipes: No E139 recipes: No | | |
| Material Movement | | | |
| Equipment Terminal Service | | | |
| Clock | Yes | | |
| Limit Monitoring | 165 | | |
| Spooling | | | |
| Control (Host Initiated) | | | |

Function Specifications of NJ Robotics CPU Units

Besides functions of the NJ501-1 00, functions supported by the NJ501-4 are as follows.

| | | ltem | | | NJ501- | | | |
|----------------------------|--|--|---------------------|--|--------|------|-----------------|------|
| item | | | | | 4400 | 4300 | 4310 | 4320 |
| | | Multi-axes coordinated control | Conveyer tracking | The robot is moved in synchronization with the conveyor during the conveyor tracking operation. | | | | |
| Robot control functions | Axes groups | Auxiliary functions for multi-axes coordinated control | Kinematics Setting | Set parameters for robot operation, such as arm length of Delta3 | | | f Delta3 robot. | |
| | Auxiliary functions Monitoring functions | | Work space function | Set the coordinate values for workspace check and check the workspace during operation. | | | ck the | |

Function Specifications of NC Integrated Controller

Besides functions of the NJ501-1 00, functions supported by the NJ501-5300 are as follows.

| | | 14 | em | | NJ501- |
|--------------------|-----------------------------|-------------------------|---------------------------------------|------------------------------|--|
| | | | | | 5300 |
| | | Axes types | | | Positioning axis, Spindle axis |
| | | Control modes | Positioning axis | 5 | Position control |
| | | | Spindle axis | | Velocity control |
| | | Positions that o | an be managed | | Absolute position (command), absolute position (actual), program position, remaining travel distance |
| | | | Execute | | Executes the NC program. |
| | | | Reset | | Interrupt NC program |
| | | | Single step exe | cution | Executes the NC program by block. |
| | | | Back trace | | Executes back trace of interpolation pass. |
| | | | Feed hold / Fee | d hold reset | Temporarily stops the NC program, and restarts it. |
| | | NC program execution | Optional stop | | Stops the NC program with optional signal. |
| | | excedition | Optional block | stop | Skips one block of the NC program with optional signal. |
| | | | Dry run | | Runs operation from the NC program. |
| | | | Machine lock | | Locks each axis operation during execution of the NC program. |
| | | | Auxiliary lock | | Locks M code output. |
| | | | Override | | Overrides the feed rate and spindle velocity. |
| | | | | Rapid Positioning | Rapid feed of each CNC motor according to the motor setting. |
| | | | Position | Linear interpolation | Interpolates linearly. |
| | | | control | Circular interpolation | Interpolates circularly, helically, spirally, or conically. |
| | | | | Skip function | Rapid feed until an external signal is input. |
| | | G Code | Return to refere | • | Returns to a specified position on the machine. |
| | | | Canned cycle | Rigid tap | Performs tapping machining. |
| | | | Feed function | Exact stop | Temporarily prevents blending of positioning operations before and after an exact stop direction. |
| | | | | Exact stop mode | Mode in which anteroposterior positioning operations are not blende |
| | | | | Continuous-path mode | Mode in which anteroposterior positioning operations are blended. |
| | | | | Dwell | Waits for the specified period of time. |
| umerical ontrol | CNC coordinate system | | Coordinate system selection | Machine Coordinate System | The coordinate system uses the machine home position as the home the system. |
| | | | | Work Coordinate System | The coordinate system has work offset for the Machine Coordinate System. |
| | | | | Local Coordinate System | The coordinate system has additional offset for the Work Coordinate System. |
| | | | Auxiliary for coordinate system | Absolute/relative selection | Specifies manipulated variable absolutely, or switches to the relative setting. |
| | | | | Metric/inch selection | Selects metric or inch as the orthogonal axes unit system. |
| | | | | Scaling | Scales the current coordinates of the orthogonal axes. |
| | | | | Mirroring | Mirrors the current coordinates for the specified orthogonal axes. |
| | | | | Rotation | Rotate the current coordinates around the coordinates of the specifi axis. |
| | | | | Cutter compensation | Compensation of the tool edge path according to the tool radius. |
| | | | Tool functions | Tool length compensation | Compensation of tool center point path according to the tool length. |
| | | | M code/M code | reset | Outputs M codes, and interlocks with sequence control program usi reset. |
| | | M code | Spindle avia | CW/CCW/Stop | Outputs/stops velocity commands in velocity loop control mode. |
| | | | Spindle axis | Orientation | Stops spindle axis to the specified phase by setting up feed back loo |
| | | | Subroutine call | | Calls a subroutine of the NC program. |
| | | | Arithmetic oper | ation | Performs a calculation in the NC program. |
| | | | Branch control | | Branches on condition in the NC program. |
| | | NC | User variables | | Memory area in the NC program used for processing such as data calculation. |
| | | programming | | P variable | System global memory area common to CNC coordinate systems |
| | | | | Q variable | Global system area unique to each CNC coordinate system |
| | | | | L variable | Memory area that can be used as the primary area during execution the NC program |
| | | Auxiliary | Error reset | | Function that resets errors or CNC coordinate system and CNC mot |
| | | control | Immediate stop | | Function that stops all the CNC motors of the CNC coordinate syste |

| | | • | | | NJ501- | |
|----------------------|-----------------|------------------------------------|---|-----------------|--|--|
| | | Ite | m | 5300 | | |
| | | Positions that can be managed | | | Commanded positions and actual positions. | |
| | | Position control | Absolute positioning | | Positioning is performed for a target position that is specified using an absolute value. | |
| | | | Relative positioning | | Positioning is performed for a specified travel distance from the command current position. | |
| | | | Cyclic positioning | | A commanded position is output at each control period in Position Control Mode. | |
| | | Spindle control | CW/CCW/Stop | | Outputs/stops velocity commands in velocity loop control mode. | |
| | | Manual operation | Powering the Servo | | The Servo in the servo driver is turned ON to enable CNC motor operation. | |
| | | | Jogging | | A CNC motor is jogged at a specified target velocity. | |
| | | Auxiliary control functions | Homing | | A CNC motor is operated, and the limit signals, home proximity signa and home signal are used to define home. | |
| | | | Immediate stop | | A CNC motor is stopped immediately. | |
| | | CNC motor compensation table | Ball screw compensation | | Pitch error compensation for one-dimensional ball screw. | |
| | CNC motor | | Cross-axis compensation | | Compensation of one-dimensional cross-axis. | |
| Numerical Control | | | Editing the CNC motor compensation table | | Edit using sequence control program. (Read/write) | |
| | | Auxiliary functions | In-position check | | You can set an in-position range and in-position check time to confirm when positioning is completed. | |
| | | | Stop method | | You can set the stop method to the immediate stop input signal or limit input signal. | |
| | | | Monitoring functions | Software limits | Monitors the movement range of a CNC motor. | |
| | | | | Following error | Monitors the error between the command current value and the actual current value for a CNC motor. | |
| | | | Absolute encoder support | | You can use an OMRON 1S-series Servomotor or G5-series. Servomotor with an Absolute Encoder to eliminate the need to perform homing at startup. | |
| | | | Input signal logic inversion | | You can inverse the logic of immediate stop input signal, positive limit input signal, negative limit input signal, or home proximity input signal. | |
| | | External interface signals | | | The Servo Drive input signals listed on the right are used. Home signal, home proximity signal, positive limit signal, negative limit signal, immediate stop signal, and interrupt input signal. | |
| | Common items | Parameters | Changing CNC coordinate system and CNC motor parameters | | You can access and change the CNC coordinate system and CNC motor parameters from the user program. | |

Function Specifications of Robot integrated CPU Units

Besides functions of the NJ501-1 0, functions supported by the NJ501-R 0 are as follows.

| Item | | | Description NJ501-R□□0 | | |
|---------------|------------------|---------------------------|--|--|--|
| | | | | | |
| | | Basic operation | Joint interpolation operation, Linear motion, Arc motion, Jog motion | | |
| | | Coordinate system of Tool | Descent (APPRO), Rising (DEPART), Tool alignment (ALIGN) | | |
| | | Joint motion | Each joint operation (DRIVE) | | |
| | Motion Operation | Application | Pick or Place | | |
| | | Continous-path motion | ON, OFF | | |
| | | Deceleration Stop | Braking current motion | | |
| | | Home position | Move to home position (READY) | | |
| | Motion Modifiers | Speed of the robot | Velocity profile, Velocity, Acceleration, Deceleration, Minimum operation time | | |
| | | Unit of speed | Ratio for maximum velocity, [mm/s], [inch/s] | | |
| | | Arm configuration | ABOVE/BELOW, LEFTY/RIGHTY, FLIP/NOFLIP | | |
| | | Hardware servo | High accuracy/Low accuracy | | |
| Robot Control | | Axis of rotation | Rotation Range, Rotation Range Over Error | | |
| | | Position Deviation | Pending position deviation cancellation | | |
| | Latching | Robot position | You can read the robot position in the V+ program when a latch signal occurred. | | |
| | | Local encoder | You can read the counter value of encoder that is connected to the encoder input port of OMRON robot in the V+ program when a latch signal occurred. | | |
| | | Coordinate system | World coordinate system, Tool coordinate system, Conversion from/to NJ Robotics function coordinate system | | |
| | | Position variable | Conversion, Relative conversion, High accuracy position | | |
| | Other functions | Robot tool | Tool offset setting | | |
| | | End effector operation | Open/Close/Loosen Gripper | | |
| | | Conveyor tracking | Belt variable, Nominal transformation, Encoder scaling factor, Encoder offset, Belt window, Belt relative motion | | |
| | | Stop | Specified time stop (DELAY) | | |

Version Information

Unit Versions and Programming Devices (NJ-series CPU Units)

Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Unit Versions, DBCon Versions and Programming Devices (Database Connection CPU Units)

Refer to NJ/NX-series Database Connection CPU Units User's Manual (W527).

Unit Versions, Robot Versions and Programming Devices (NJ Robotics CPU Units)

Refer to NJ-series Robotics CPU Units User's Manual (W539).

Unit Versions and Programming Devices (NC Integrated Controller)

Refer to NJ/NY-series NC Integrated Controller User's Manual (0030).

Unit Versions, Robot Control Versions and Programming Devices (Robot Integrated CPU Units)

Refer to NJ-series Robot Integrated CPU Unit User's Manual (0037).

Relationship between Hardware Revisions of CPU Units and Sysmac Studio Versions

Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Functions That Were Added or Changed for Each Unit Version and Sysmac Studio version


Refer to NJ-series CPU Unit Hardware User's Manual (W500).

Performance Improvements for Unit Version Upgrades


Refer to NJ-series CPU Unit Hardware User's Manual (W500).


Components and Functions

CPU Unit



Power Supply Unit NJ-PA3001






Unit Configuration

NJ-Series CPU Racks

A NJ-Series CPU Rack consists of a CPU Unit, Power Supply Unit, Configuration Units (Basic I/O Units, Special I/O Units, and CPU Bus Units), and an End Cover.



Even though the NJ-Series Controllers do not have Backplanes, the term "slot" still used to refer to the location of Units. Slot numbers are assigned in order to Units from left to right on the CPU Rack (slot 0, slot 1, slot 2, etc.).

Required Units

| Rack | Unit name | Required number of Units | |
|----------|----------------------------------|---|--|
| | NJ-Series Power Supply Unit | 1 | |
| | NJ-Series CPU Unit | 1 | |
| CPU Rack | I/O Control Unit | Required only for mounting to an Expansion Rack. Mount the I/O Control Unit immediately to the right of the CPU Unit. | |
| | Number of Configuration Units | 10 max. (Same for all models of CPU Unit.) (The number of Basic I/O Units, Special I/O Units, and CPU Bus Units can be varied. The number does not include the I/O Control Unit.) | |
| | End Cover | 1 (Included with CPU Unit.) | |
| | NJ-Series SD Memory Card | Install as required. | |


Types of Configuration Units

In the NJ-Series, Configuration Units are classified into the following three types. The number of Racks differs depending on the type.

| Туре | Appearance (example) | Description | Unit recognition method | Max. Units mountable per CPU Unit |
|----------------------|----------------------|---|---|---|
| Basic I/O Units | | Units with contact inputs and contact outputs. | Recognized by the CPU Unit accord- ing to the position of the Rack and slot. | A maximum of 40 Units can be mounted. |
| Special I/O Units | | Special I/O Units provide more advanced functions than do Basic I/O Units, including I/O other than contact inputs and contact outputs. Examples of Special I/O Units are Analog I/O Units and High-speed Counter Units. They differ from CPU Bus Units (including Network Communi- cations Units) in having a smaller area for exchanging data with the CPU Unit. | Recognized by the CPU Unit accord- ing to the unit number (0 to 95) set with the rotary switches on the front panel. | A maximum of 40 Units can be connected. (Multi- ple unit numbers are allo- cated per Unit, depending on the model and settings.) |
| CPU Bus Units | | CPU Bus Units exchange data with the CPU Unit via the CPU Bus. Examples of CPU Bus Units are Network Commu- nications Units and Serial Communications Units. They differ from Special I/O Units in having a larger area for exchanging data with the CPU Unit. | Recognized by the CPU Unit accord- ing to the unit number (0 to F) set with the rotary switch on the front panel. | A maximum of 16 Units can be mounted. |

NJ-Series Expansion Racks

A NJ-Series Expansion Rack consists of a Power Supply Unit, an I/O Interface Unit, Configuration Units (Basic I/O Units, Special I/O Units, and CPU Bus Units), and an End Cover.



Configuration Units: 10 max.

Required Units

| Rack Unit name | | Required number of Units | | |
|----------------|-------------------------------|---|--|--|
| | | One Unit. Required only when an Expansion Rack is used. Mount the I/O Control Unit immediately to the right of the CPU Unit. *1 | | |
| | Power Supply Unit | One Unit | | |
| Expansion | I/O Interface Unit | One Unit. Mount the I/O Interface Unit immediately to the right of the Power Supply Unit. *2 | | |
| Rack | Number of Configuration Units | Ten Units max. (The number of Basic I/O Units, Special I/O Units, and CPU Bus Units can be varied. This number does not include the I/O Interface Unit.) | | |
| | End Cover | One (Included with the I/O Interface Unit.) | | |

*1 Mounting the I/O Control Unit in any other location may cause faulty operation.

*2. Mounting the I/O Interface Unit in any other location may cause faulty operation.

Configuration Units

Maximum Number of Configuration Units That Can Be Mounted

| CPU Unit | Model | Total Units | No. of Units on CPU Rack | No. of Expansion Racks |
|-----------|------------|-------------|--------------------------|------------------------|
| NJ-Series | NJ501-□□□□ | 40 | 10 per Rack | 3 Racks x 10 Units |
| CPU Unit | NJ301-□□□ | | | |
| | NJ101-000 | | | |

Note: It may not be possible to mount the maximum number of configuration Units depending on the specific Units that are mounted. Refer to the next page for details.


Number of mountable units per Configuration Unit

Basic I/O Units, Special I/O Units, and CPU Bus Units of the CJ-Series are used as Configuration Units of the NJ-Series. All Basic I/O Units are useable. Not all Special I/O Units and CPU Bus Units can be used. Units that can be used are shown in the list. In addition, note that the number of units that can be connected to one CPU vary depending on the units.


NJ-Series Dimensions


CPU Units NJ□01-□□□□






Power Supply Units NJ-PA3001 NJ-PD300





End Cover (included with CPU Units) CJ1W-TER01



Related Manuals

| Cat. No. | Model number | Manual | Application | Description |
|----------|--|---|---|--|
| W513 | NJ501 NJ301 NJ101 | NJ Series Startup Guide (CPU Unit) | Using the NJ-series CPU Unit for the first time | The startup procedures for using an NJ-series CPU Unit and the basic operating instructions for the Sysmac Studio are described with a simple sequence control example. |
| W514 | NX701 NX1P2 NJ301 NJ301 NJ101 | NJ/NX-series Startup Guide (Motion Control) | Using the motion control function module of the NJ/NX-series for the first time | The startup procedures for setting axis parameters and performing simple one-axis positioning and two-axis linear interpolation with an NJ/NX-series CPU Unit and the operating instructions for the Sysmac Studio are described. |
| W500 | NJ501 NJ301 NJ101 | NJ-series CPU Unit Hardware User's Manual | Learning the basic specifications of the NJ-series CPU Units, including introductory information, designing, installation, and maintenance Mainly hardware information is provided. | An introduction to the entire NJ-series system is provided along with the following information on a Controller built with a CPU Unit. • Features and system configuration • Introduction • Part names and functions • General specifications • Installation and wiring • Maintenance and inspection |
| W501 | NX701 NX102 NJ501 NJ301 NJ101 | NJ/NX-series CPU Unit Software User's Manual | Learning how to program and set up an NJ/NX-series CPU Unit. Mainly software information is provided. | The following information is provided on a Controller built with an NJ/NX-series CPU Unit. • CPU Unit operation • CPU Unit features • Initial settings • Programming language specifications and programming with the IEC 61131-3 standard. |
| W507 | NX701 NX102 NJ501 NJ301 NJ101 | NJ/NX-series CPU Unit Motion Control User's Manual | Learning about motion control settings and programming concepts | The settings and operation of the CPU Unit and programming concepts for motion control are described. |
| W505 | NX701 NX102 NJ501 NJ301 NJ101 NJ101 | NJ/NX-series CPU Unit Built-in EtherCAT Port User's Manual | Using the built-in EtherCAT port on an NJ/NX-series CPU Unit | Information on the built-in EtherCAT port is provided. This manual provides an introduction and provides information on the configuration, features, and setup. |
| W539 | NJ501-4 | NJ-series NJ Robotics CPU Unit User's Manual | Controlling robots with NJ-series CPU Units. | Describes the functionality to control robots. |
| O037 | NJ501-R | NJ-series Robot Integrated CPU Unit User's Manual | Using the NJ-series Robot Integrated CPU Unit. | Describes the settings and operation of the CPU Unit and programming concepts for OMRON robot control. |
| W527 | NX70120 NX10220 NJ50120 NJ10120 | NJ/NX-series Database Connection CPU Units User's Manual | Learning about the functions and application procedures of the NJ/ NX-series DB Connection function. | Describes the functions and application procedures of the NJ/NX-series DB Connection function. |
| W528 | NJ501-1340 | NJ-series SECS/GEM CPU Unit User's Manual | Learning about the SECS/GEM CPU Unit and how to use it. | Functional outline, GEM instructions, settings with the GEM Configurator and so on are provided. |
| O030 | NJ501-5300 NY532-5400 | NJ/NY-Series NC Integrated Controller User's Manual | For numerical control with NJ/NY- series | Describes the numerical control function. |
| W506 | NX701 NX102 NX1P2 NJ501 NJ301 NJ101 | NJ/NX-series CPU Unit Built-in EtherNet/IP Port User's Manual | Using the built-in EtherNet/IP port on an NJ/NX-series CPU Unit | Information on the built-in EtherNet/IP port is provided. Information is provided on the basic setup, tag data links, FINS communications (non-disclosure), and other features. |
| W588 | NX102- NX701-1 NJ501-1 00 | NJ/NX-series CPU Unit OPC UA User's Manual | Using the OPC UA. | Describes the OPC UA. |
| W502 | NX701 NX102 NX1P2 NJ501 NJ301 NJ101 | NJ/NX-series Instructions Reference Manual | Learning about the specifications of the instruction set that is provided by OMRON | The instructions in the instruction set (IEC 61131- 3 specifications) are described. |
| W508 | NX701 NX102 NX1P2 NJ501 NJ301 NJ101 | NJ/NX-series Motion Control Instructions Reference Manual | Learning about the specifications of the motion control instructions that are provided by OMRON | The motion control instructions are described. |
| W503 | NX701 NX102 NJ501 NJ301 NJ101 NJ101 | NJ/NX-series Troubleshooting Manual | Learning about the errors that may be detected in an NJ/NX-series Controller. | Concepts on managing errors that may be detected in an NJ/NX-series Controller and information on individual errors are described. |
| W504 | SYSMAC-SE2 | Sysmac Studio Version 1 Operation Manual | Learning about the operating procedures and functions of the Sysmac Studio. | Describes the operating procedures of the Sysmac Studio. |
| O031 | NJ501-5300 NY532-5400 | NJ/NY-series G code Instruction Reference Manual | Learning about detailed specifications of the G code/M code instructions. | This section describes G code/M code instructions in detail. |

| Cat. No. | Model number | Manual | Application | Description |
|--|--------------------------------|--|--|---|
| W589 | SYSMACSE2 SYSMAC-TA4 | Sysmac Studio Project Version Control Function Operation Manual | Learning the overview of the Sysmac Studio project version control function and how to use it. | The manual outlines the Sysmac Studio project version control function, and describes how to install, basic operation, and how to operate its major functions. |
| O032 | SYSMAC-RTNC0 | CNC Operator Operation Manual | Learning the overview of CNC Operator and how to use it. | Describes the CNC Operator, installation procedure, basic operation, connection operation, and operating procedures for main functions. |
| W595 | SYSMAC-SE2 SYSMAC-SE200D-64 | Sysmac Studio Robot Integrated System Building Function with Robot Integrated CPU Unit Operation Manual | Learning about the operating procedures and functions of the Sysmac Studio to configure Robot Integrated System using Robot Integrated CPU Unit. | Describes the operating procedures of the Sysmac Studio for Robot Integrated CPU Unit. |
| W621 | SYSMAC-SE2 SYSMAC-SE200D-64 | Sysmac Studio Robot Integrated System Building Function with IPC Application Controller Operation Manual | Learning about the operating procedures and functions of the Sysmac Studio to configure Robot Integrated System using IPC Application Controller. | Describes the operating procedures of the Sysmac Studio for IPC Application Controller. |
| W490 W498 W491 Z317 W492 W494 W497 W495 W493 | CJ1W- | CJ-series Special Unit Manuals for NJ-series CPU Unit | Leaning how to connect CJ-series Units | The methods and precautions for using CJ-series Units with an NJ-series CPU Unit are described, including access methods and programming interfaces. Manuals are available for the following Units. Analog I/O Units, Insulated-type Analog I/O Units, Temperature Control Units, ID Sensor Units, High-speed Counter Units, and DeviceNet Units, EtherNet/IP Units, CompoNet Master Units |
| Y128 | | Vision & Robot Integrated Simulation Startup Guide | Learning about the operating pro- cedures of Vision & Robot integrat- ed simulation. | Describes the operating procedures of Vision & Robot integrated simulation. |
| Y213 | _ | Vision & Robot Integrated Simulation Technology In- troduction Guide (Calibra- tion Parameter) | Learning about the calibration pa- rameters created using the 3D Equipment Model Creation Wizard for the Vision & Robot integrated simulation. | Describes calibration parameters created using the 3D Equipment Model Creation Wizard for the Vision & Robot integrated simulation. |
| Z368 | SYSMAC-SE20 SYSMAC-RA401L | Vision Sensor FH Series Conveyor Tracking Applica- tion Programming Guide | Learning about the setup proce- dure of the wizard style calibration for cameras, robots, or conveyors. | Describes how to configure and operate Conveyor Tracking Calibration Wizard on Sysmac Studio on FH Sensor Controllers. |
| Z369 | NJ501-4 R88D-KN-ECT FH-1 | Vision Sensor FH Series Operation Manual Sysmac Studio Calibration Plate Print Tool | Learning about the setup proce- dure for printing the Pattern on a Calibration Plate used for calibra- tion for cameras and robots on Sysmac Studio. | Describes how to configure and operate Calibra- tion Plate Print Tool on Sysmac Studio on FH Sen- sor Controllers. |
| Z370 | | Vision Sensor FH Series Operation Manual Sysmac Studio Conveyor Tracking Calibration Wizard Tool | Learning about the setting proce- dure of sample macros for convey- or tracking. | Describes the setting procedure of sample mac- ros used for applications of conveyor tracking on FH Sensor Controllers. |
| Z371 | | Vision Sensor FH Series Operation Manual Sysmac Studio Conveyor Panorama Display Tool | Learning about the setup proce- dure of panorama display for im- age capture of targets on conveyors. | Describes how to configure and operate the Con- veyor Panorama Display tool on Sysmac Studio on FH Sensor Controllers. |

Applicable Models for Cable Redundancy Function

For more information on applicable models of Cable Redundancy function, refer to the Applicable Models of Cable Redundancy Function (Cat. No. R200).

Sysmac is a trademark or registered trademark of OMRON Corporation in Japan and other countries for OMRON factory automation products. Microsoft, Windows, Windows Vista and SQL Server are registered trademarks of Microsoft Corporation in the United States and other countries. Oracle, Oracle Database and MySQL are trademarks or registered trademarks of Oracle Corporation and/or its affiliates in the United States and other countries. IBM and DB2 are trademarks or registered trademarks of International Business Machines Corp., registered in the United States and other countries. SEMI® is a trademark or registered trademark of Semiconductor Equipment and Materials International in the United States and other countries.

EtherCAT® is a registered trademark of Beckhoff Automation GmbH for their patented technology.

EtherNet/IP[™] and DeviceNet[™] are trademarks of ODVA.

OPC UA is trademark of the OPC Foundation.

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit. (http://www.openssl.org/)

This product includes cryptographic software written by Eric Young (eay@cryptsoft.com).

Other company names and product names in this document are the trademarks or registered trademarks of there respective companies.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-2711 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2220 Fax: (86) 21-5037-2200 Authorized Distributor:

©OMRON Corporation 2018-2022 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_6_2 Cat. No. P140-E1-15 0922 (1218)