DMROI

Safety CPU Unit NX-SL5

Integrate safety into ultra-flexible, ultra-high-speed machine automation and build a distributed safety system

- Automatic generation, from safety programs through to safety functional test reports
- · Data logging with fast cycle time to detect causes of downtime and degradation of safety components
- Integrated safety over EtherCAT[®] for high-speed, high-precision fieldbus communication in a machine
- Integrated safety into EtherNet/IP[™] for safety communication between machines
- · Easy to set up motion and robots that are the key to quality and productivity enhancement









For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Features

- Meets EN ISO 13849-1 (PLe/Category 4) and IEC 61508 (SIL3)
- Safety over EtherCAT (FSoE) allows standard devices and safety devices to be mixed on the same EtherCAT® network
- CIP Safety[™] allows standard devices and safety devices to be mixed on the same EtherNet/IP network
- Reusable safety program POUs according to IEC 61131-3 make programming more efficient
- · PLCopen® Function Blocks for Safety reduce time and cost to learn safety design
- · Safety I/O wiring diagrams, safety circuit programs, and user-defined Function Blocks can be automatically generated, minimizing safety design errors
- · Simple Automatic Test using Offline Simulation is available. Online Functional Test ensures and maintains safety during machine commissioning and operation
- * The Common Industrial Protocol (CIP TM) is an industry standard open network, enabling seamless communication among CIP networks. CIP Safety[™] adds safety functionality to CIP networks.
- 🗱 Safetý over EtherCÁT (FSoE): The open protocol Safety over EtherCAT (abbreviated with FSoE "FailSafe over EtherCAT") defines a safety related communication layer for EtherCAT. Safety over EtherCAT meets the requirements of IEC 61508 SIL 3 and enables the transfer of safe and standard information on the same communication system without limitations with regard to transfer speed and cycle time.

Trademarks

- · Sysmac and SYSMAC are trademarks or registered trademarks of OMRON Corporation in Japan and other countries for OMRON factory automation products.
- · Microsoft, Windows, Windows Vista, Excel, and Visual Basic are either registered trademarks or trademarks of Microsoft Corporation in the United States and other countries
- EtherCAT® is registered trademark and patented technology, licensed by Beckhoff Automation GmbH, Germany.
- Safety over EtherCAT® is a registered trademark and a patented technology licensed by Beckhoff Automation GmbH, Germany.
- ODVA, CIP[™], CompoNet[™], DeviceNet[™], EtherNet/IP[™], and CIP Safety[™] are trademarks of ODVA.
- PLCopen[®] and related logo are registered trademarks of PLCopen[®].
- The SD and SDHC logos are trademarks of SD-3C, LLC

Other company names and product names in this document are the trademarks or registered trademarks of their respective companies.

NX-SL5

Ordering Information

Safety CPU Units NX-SL5

Unit type	Appearance	Specifications				Unit	
		Maximum number of safety I/O points	Program capacity	Number of safety I/O connections	I/O refreshing method	version	Model
Safety CPU Unit (NX-SL5□□□)		1024 points	2048 KB	128	Free-Run refreshing	Ver. 1.4	NX-SL5500
		2032 points	4096 KB	254	Free-Run refreshing	Ver. 1.4	NX-SL5700

Accessories

There is no accessory.

Automation Software Sysmac Studio

The Sysmac Studio is the software that provides an integrated environment for setting, programming, debugging and maintenance of machine automation controllers including the NJ/NX-series CPU Units, NY-series Industrial PC, EtherCAT Slave, and the HMI.

For details, refer to your local OMRON website and Sysmac Studio Catalog (Cat. No. P138).

Regulations and Standards

Safety CPU Units NX-SL5

Certification body	Standards
TÜV Rheinland	 EN ISO 13849-1 EN ISO 13849-2 IEC 61508 parts 1-7 IEC/EN 61131-2 IEC 61326-3-1 IEC 61131-6
UL	 NRAG (UL 61010-1 and UL 61010-2-201 and UL 121201) NRAG7 (CSA C22.2 No. 61010-1 and CSA C22.2 No. 61010-2-201 and CSA C22.2 No. 213) FSPC (IEC 61508 and ISO 13849)
Shipbuilding Standards	NK, LK

Using the NX-series Safety CPU Unit allows you to build a safety control system that meets the following standards:

• Requirements for SIL 3 in IEC 61508

• Requirements for PLe and Category 4 in EN ISO 13849-1

The NX-series Safety CPU Units are also registered for RCM and KC compliance.

General Specifications

Item		Specification
Enclosure		Mounted in a panel (open)
Grounding method		Ground to 100 Ω or less
	Ambient operating temperature	0 to 55°C
	Ambient operating humidity	10% to 95% (with no condensation or icing)
	Atmosphere	Must be free from corrosive gases.
	Ambient storage temperature	-25 to 70°C (with no condensation or icing)
	Altitude	2,000 m max.
	Pollution degree	2 or less
	Noise immunity	Conforms to IEC 61131-2. 2 kV on power supply line
Operating	Insulation class	Class III (SELV)
environment	Overvoltage category	11
	EMC immunity level	Zone B
	Vibration resistance	Conforms to IEC 60068-2-6. 5 to 8.4 Hz with 3.5-mm amplitude 8.4 to 150 Hz, acceleration of 9.8 m/s ² 100 minutes each in X, Y, and Z directions (10 sweeps of 10 min each = 100 min total)
	Shock resistance	Conforms to IEC 60068-2-27. 147 m/s ² , 3 times each in X, Y, and Z directions
	Insulation resistance	$20 \text{ M}\Omega$ between isolated circuits (at 100 VDC)
	Dielectric strength	510 VAC for 1 min between isolated circuits, leakage current: 5 mA max.
Installation method		DIN Track (IEC 60715 TH35-7.5/TH35-15)

NX-SL5

Unit Specifications

Unit name	Safety C	CPU Unit		
Model	NX-SL5500	NX-SL5700		
Maximum number of safety I/O points	1024 points	2032 points		
Program capacity	2048 KB	4096 KB		
Number of safety master connections *1	128	254		
Number of CIP Safety originator connections	128	254		
Number of CIP Safety target connections	4	4		
Number of originators that can be connected with a multi-cast connection	8	8		
Number of FSoE master connections	128	254		
I/O refreshing method	Free-Run refreshing			
External connection terminals	None			
Indicators	Seven-segment indicator [TS] LED, [NS] LED, [FS] LED [P ERR] LED, [RUN] LED, [VALID] LED, [DEBUG] LED	Seven-segment indicator [TS] LED, [NS] LED, [FS] LED [P ERR] LED, [RUN] LED, [VALID] LED, [DEBUG] LED		
Hardware switch settings	SERVICE 1 2 3 4	SERVICE 1 2 3 4		
Dimensions	30 × 100 × 71 mm (W × H × D)			
I/O power supply method	Not supplied.			
Current capacity of I/O power supply terminals	No I/O power supply terminals			
NX Unit power consumption *2	3.35 W max.			
Current consumption from I/O power supply	No consumption			
Weight	130 g max.			
Installation orientation and restrictions *3	Installation orientation: Upright installation Restriction: None.			

*1. This is the maximum number of Safety I/O connections that can be set to this Unit. The value is the total number of CIP Safety originator connections, CIP Safety target connections, and FSoE master connections.
*2. The cable length for the Units (Communication Control Unit and Power Supply Unit for NX Units) that supply power to the corresponding Unit must be up to 20 m.
*3. The NX102 CPU Unit, NX502 CPU Unit, and NX-CSG Communication Control Unit can be connected.

4

Combinations of CPU Unit, Communications Unit, and Software

The following table shows the NX-series CPU Unit, Communications Units, and Sysmac Studio editions that can be used with the NX-SL5

CPU Unit and	NJ/NX Series CPU Unit * 1	Communications Unit		
Unit	NX102-□□□□ NX502-□□□□	EtherCAT Coupler Unit NX-ECC20□	EtherNet/IP Coupler Unit NX-EIC202	Communication Control Unit NX-CSG320
Edition of Sysmac Studio * 2	Standard Edition	Standard Edition	Standard Edition Sysmac Studio Safety Edition	Standard Edition Sysmac Studio Safety Edition
NX-SL5500	YES	No	No	YES
NX-SL5700	YES	No	No	YES

*1. The NX-SL5 Safety CPU Unit cannot be connected directly to the NJ/NX1P/NX7 CPU Unit. The NX-CSG320 Communication Control Unit is required to connect a system using these CPU Units.

*2. Refer to Version Information for the possible combinations of the versions of Units and Sysmac Studio.

Version Information

The following table shows the possible combinations of versions of NX-series Safety Control Units, CPU Units, Communication Control Units, and Sysmac Studio. Available functions that are related to safety control vary depending on the versions of the units and Sysmac Studio. Refer to the *NX-series Safety Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit/Communication Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit User's Manual* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-series Safety Control Unit User's* (Cat. No. Z930) and the *NX-s*

NX-SL5

- NX102 CPU Unit version 1.31 or later and Sysmac Studio version 1.40 or higher
- NX502 CPU Unit version 1.60 or later and Sysmac Studio version 1.54 or higher
- NX-CSG version 1.01 or later and Sysmac Studio version 1.40 or higher

Combinations of versions

Safety Control Unit model and version		NX bus NX102 0	master: CPU Unit	NX bus master: NX502 CPU Unit		NX bus master: Communication Control Unit	
Model	Unit Version	NX102-□□□□	Sysmac Studio	NX502-□□□□ * 1	Sysmac Studio * 2	Communication Control Unit NX-CSG	Sysmac Studio
NX-SI 5500	Ver.1.3	Van 4.24 an latan	Ver.1.24 or higher	Van 4.00 an latan	Ver.1.54 or higher	Van 4.04 an latan	Ver.1.24 or higher
NA-323300	Ver.1.4		Ver.1.40 or higher	ver. 1.00 of later		ver. 1.01 of later	Ver.1.40 or higher
	Ver.1.2					Ver.1.00 only	Ver.1.24 or higher
NX-SL5700	Ver.1.3	Ver.1.31 or later	Ver.1.24 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.01 or later	Ver.1.24 or higher
	Ver.1.4	Ver.1.31 or later	Ver.1.40 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.01 or later	Ver.1.40 or higher
NX-SIH400	Ver.1.0	Ver.1.30 or later	Ver.1.22 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.00 or later Ver.1 Ver.1 hig Ver.1 hig	Ver.1.24 or higher
	Ver.1.1						Ver.1.24 or higher
NX-SID800	Ver.1.0	Ver.1.30 or later	Ver.1.22 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.00 or later	Ver.1.24 or higher
NX-SOH200	Ver.1.0	Ver.1.30 or later	Ver.1.22 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.00 or later	Ver.1.24 or higher
NX-SOD400	Ver.1.0	Ver.1.30 or later	Ver.1.22 or higher	Ver.1.60 or later	Ver.1.54 or higher	Ver.1.00 or later	Ver.1.24 or higher

*1. To use CIP Safety communications, connect the NX-EIP201 EtherNet/IP Unit to the NX502 CPU Unit or use the NX502-1 00 CPU Unit version 1.64 or later.

*2. Use the Sysmac Studio version 1.56 or higher for CIP Safety communications via the built-in EtherNet/IP port on the NX502-1 00 version 1.64 or later.

NX Unit Configuration

CPU Rack (Using NX102 CPU Unit)

The CPU Rack consists of an NX-series NX102 CPU Unit, NX Units, and an End Cover.

Up to 32 NX Units can be connected.



Up to 32 Units can be mounted to each CPU Rack.

For restrictions of the NX unit, refer to NX-series NX102 CPU Unit Hardware User's Manual (Cat. No. W593).

Series	Configuration	Remarks
	NX-series NX102 CPU Unit	One required for every CPU Rack. Up to 32 Units can be mounted to each CPU Rack. For restrictions of the NX unit, refer to <i>NX-series NX102 CPU Unit Hardware</i> <i>User's Manual</i> (W593).
	End Cover	Must be connected to the right end of the CPU Rack. One End Cover is provided with the CPU Unit.
	Safety Control Units	This is a programmable safety controller which supports IEC 61131-3 and PLCopen [®] TC5 Safety. This unit consists of safety CPU unit and safety I/O unit.
NX-series	Safety CPU Unit NX-SL5□□□	This Unit has safety control functions. It operates as an NX Unit. It also operates as an FSoE master. It operates as a CIP-Safety-on-EtherNet/IP device.
	Safety I/O Units	These Units have safety input functions or safety output functions. They operate as NX Units. These Units operate as FSoE slaves.
	Safety Input Unit	These Units have safety input functions.
	Safety Output Unit	These Units have safety output functions.
	System Unit	When the I/O power supply for the NX Unit connected to the CPU Unit is supplied through the NX bus, the IO power supply unit (NX-PF) must be used as well.
	Other NX units	For the latest lineup of NX units, refer to our catalog and our website, or inquire of our local representative.
NJ/NX-series	SD Memory Card	Install as required.

CPU Rack (Using NX502 CPU Unit)

The CPU Rack consists of an NX-series NX502 CPU Unit, NX Units, and an End Cover. Up to 63 NX Units can be connected.



For restrictions of the NX unit, refer to NX-series NX502 CPU Unit Hardware User's Manual (Cat. No. W629).

Series		Configuration	Remarks
	NX-	series NX502 CPU Unit	One required for every CPU Rack. Up to 63 Units can be mounted to each CPU Rack. For restrictions of the NX unit, refer to <i>NX-series NX502 CPU Unit Hardware</i> <i>User's Manual</i> (W629).
	End Cover		Must be connected to the right end of the CPU Rack. One End Cover is provided with the CPU Unit.
	Safety Control Units		This is a programmable safety controller which supports IEC 61131-3 and PLCopen [®] TC5 Safety. This unit consists of safety CPU unit and safety I/O unit.
NX-series		Safety CPU Unit NX-SL5□□□	This Unit has safety control functions. It operates as an NX Unit. It also operates as an FSoE master. It operates as a CIP-Safety-on-EtherNet/IP device.
		Safety I/O Units	These Units have safety input functions or safety output functions. They operate as NX Units. These Units operate as FSoE slaves.
		Safety Input Unit	These Units have safety input functions.
		Safety Output Unit	These Units have safety output functions.
	Sys	tem Unit	When the I/O power supply for the NX Unit connected to the CPU Unit is supplied through the NX bus, the IO power supply unit (NX-PF) must be used as well.
	Other NX units		For the latest lineup of NX units, refer to our catalog and our website, or inquire of our local representative.
NJ/NX-series	SD	Memory Card	Install as required.



CPU Rack (Using NX-CSG Communication Control Unit)

The following shows the CPU Rack Configuration, where NX Units are mounted to a CPU Rack. The CPU Rack is configured with a Communication Control Unit, a Safety CPU Unit, Safety I/O Units, other NX Units, and an End Cover mounted to it. The number of NX Unit connections is up to 32 units.



Refer to the NX-series Safety Control Unit/Communication Control Unit User's Manual (Cat. No. Z395) for details on the configuration of the system using the Communication Control Unit.

Configuration		Remarks
Communication Control Unit		One required for every CPU Rack.
End Cover		Must be connected to the right side of the CPU Rack. One end cover is provided with the Communication Control Unit as a standard accessory.
	Safety CPU Unit NX-SL5□□□	Up to 32 units can be mounted onto the CPU Rack. One Safety
NX Unit	Safety Input Unit	CPU Unit is required for each CPU Rack.
	Safety Output Unit	Manual (Cat.No. Z395) for the NX Units that you can connect.
	Other NX Units	
SD Memory Card		Install as required.

Part Names and Functions

Safety CPU Units NX-SL5500/SL5700



Letter	Name	Specification
(A)	Marker attachment locations	The locations where markers are attached. The markers made by OMRON are installed for the factory setting. Commercially available markers can also be installed.
(B)	Protrusions for removing the Unit	The protrusions to hold when removing the Unit.
(C)	DIN Track mounting hook	This hook is used to mount the NX Unit to a DIN Track.
(D)	NX bus connector	This is the NX-series bus connector.
(E)	Unit hookup guides	These guides are used to connect two Units.
(F)	Indicators	The indicators show the current operating status and power supply status of the Safety CPU Unit.
(G)	Service switch	This switch is used for the start trigger of various functions.
(H)	DIP switch	This switch is used for the Safety Unit Restore and the safety data logging function.
(I)	Unit specifications	The specifications of the Safety CPU Unit are given.

NX-SL5

Indicators



Letter	Name	Function
(A)	Model number display	Displays part of the model number of the Safety CPU Unit.
(B)	Seven-segment Indicator	Displays detailed information on the Safety CPU Unit.
(C)	Indicators	Show the current operating status and communications status of the Safety CPU Unit.

Indicator specifications

[TS] LED	The TS indicator shows the current status of the Safety CPU Unit and the communications status with the NX Bus Master.
[NS] LED	The NS indicator shows the CIP Safety communications status of the Safety CPU Unit.
[FS] LED	The FS indicator shows the FSoE communications status of the Safety CPU Unit.
[RUN] LED	The RUN indicator shows the execution status of the safety programs.
[DEBUG] LED	The DEBUG indicator shows the status whether the debug function can be executed on Safety CPU Unit.
[VALID] LED	The VALID indicator shows whether safety validation has been performed on the safety application data in the Safety CPU Unit.

Seven-segment indicator The two-digit seven-segment indicator shows the detailed information on the Safety CPU Unit in the following cases:

At normal operation, when an error occurs, when a signature code is checked, when the Safety Unit Restore is executed, When the Safety Data Logging is executed

Dimensions

11111 1010

Safety CPU Units NX-SL5500/SL5700



Related Manuals

Manual name	Cat. No.	Model numbers	Application	Description
NX-series Safety Control Unit User's Manual	Z930	NX-SL	Learning how to use the NX-series Safety Control Units.	Describes the hardware, setup methods, and functions of the NX-series Safety Control Units.
NX-series Safety Control Unit Instructions Reference Manual	Z931	NX-SL	Learning about the specifications of instructions for the Safety CPU Unit.	Describes the instructions for the Safety CPU Unit.
NX-series Safety Control Unit / Communication Control Unit User's Manual	Z395	NX-SL5	Learning how to use the NX-series Safety Control Units and Communication Control Units.	Describes the hardware, setup methods, and functions of the NX-series Safety Control Units and Communication Control Units.
Sysmac Studio Version 1 Operation Manual	W504	SYSMAC-SE2	Learning about the operating procedures and functions of the Sysmac Studio.	Describes the operating procedures of the Sysmac Studio.

Safety Precautions

Be sure to read the *Common Precautions for Safety Warning* at the following URL: http://www.ia.omron.com/. Be sure to read the following user's manual for other details required for correct use of the Safety CPU Unit.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

- (a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.
- (b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

OMRON's Products Suppot IoT for Control Panels and Production Lines



Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company

Kyoto, JAPAN

Contact : www.ia.omron.com

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011 **OMRON ELECTRONICS LLC** 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2023-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_5_1 Cat. No. F124-E1-06 0625 (0223)