

Industrial PC Platform NY Series

NY Monitor Link: Put your screen where it's needed

Using Omron's NY Monitor Link connector*, you can place our industrial monitor where it most benefits the operator – even if that's 100m from the industrial PC. Connect using standard Ethernet cable and our unique auto-tuning technology will ensure fast responsiveness – just as if the monitor was next to the PC.




Be more flexible: Monitor placed up to 100m from IPC

In order to improve maintenance efficiency, it makes sense to have the user interface close to the machine operator. However, it was not easy to install the industrial PC and monitor where they were needed due to the limited distance between them. NY Monitor Link enables you to place an industrial monitor up to 100 m from an industrial PC, providing more flexibility to the layout of devices.



Standard Ethernet cable

Simply connect devices using up to 100m of Cat 6A or higher Ethernet cable with standard RJ45 connectors. That's all you need to do – no software to install, no operating system to update.



Unique auto-tune logic

Omron's unique modulation algorithms auto-tune the devices as soon as they are connected, ensuring stable connectivity with no excess latency, no interference, no disturbance.

Controllers

NY Monitor Link works with Omron's Industrial PC with an NY Monitor Link connector.

- NYB Industrial Box PC NYP Industrial Panel PC
- NY512-1/532-1 IPC Machine Controller

NY Monitor Link connector specifications

NY Monitor Link connects Omron's Industrial Monitor and Omron's Industrial PC via NY Monitor Link connectors. The NY Monitor Link communication is a combination of video and USB information.

Item	Specifications
Connector type	RJ45
Transmission media	Twisted pair cable of category 6A or higher (double-shielded straight cable with copper braiding and aluminum foil)
Maximum cable length between industrial PC and industrial monitor	100m
Topology	Line (direct) connection only*
Video resolution	1,280 x 800 pixels at 60 Hz
Data throughput rate	280 Mbps max.

- * Connect directly between Omron's Industrial PC and Omron's Industrial Monitor. Do not use:
 - Ethernet switches Ethernet hubs Daisy chain connections

Company names and product names in this document are the trademarks or registered trademarks of their respective companies. The product photographs and figures that are used in this document may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company Kyoto, JAPAN

Contact: www.ia.omron.com

Regional Headquarters
OMRON EUROPE B.V.

Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31)2356-81-300/Fax: (31)2356-81-388

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2), Alexandra Technopark, Singapore 119967 Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON ELECTRONICS LLC

2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

© OMRON Corporation 2017 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. P126-E1-01

1117(1117)