OMRON

Environment-resistant Series

Oil-resistant Components

Let Us Help You

Eliminate Production Line Stoppages

No Cutting Oil Ingress by Any Path

Unexpected Component Failures:

Approx. 30% Are Caused by Cutting Oil.

OMRON's Oil-resistant Components Resist Oil for 4 Years

*Refer to page 12 for details on oil resistance performance.

Let OMRON help you greatly reduce unexpected production line stoppages by using the Components that shut out cutting oil for four years and thereby increase operation rates.

Five products, more than 140 models are available.



Oil-resistant Fiber Units

OMRON 3

Other causes

Voltage or noise

Dust, dirt, or spatter

Temperature

Cutting oil Shock or

vibration

Environmental Causes of Component Failures *Based on June 2016 OMRON investigation.

Oil-resistant Proximity Sensors Oil-resistant Connectors Oil-resistant Potoelectric Sensors OMRON's Oil-resistant Components Solve Problems at All Phases of Production

Management

Factories must be capable of stable production of scheduled quantities.

Eliminate lost opportunity resulting from unexpected production line stoppages.

POINT The opportunity to invest in new projects is increased.

Maintenance

Reducing unscheduled maintenance through stable operation is important.

Unscheduled maintenance visits and replacement frequencies are greatly reduced.

Time can be used effectively for improvement activities.

Production

New facilities must start stable operation without delay.

The risk of faults in newly commissioned facilities is reduced.

A smooth transition can be made to the next production facility commissioning.

Facility Design

Overseas facilities must provide stable operation.

The risk of faults in newly commissioned overseas facilities is reduced. Maintenance cost for unscheduled visits overseas is reduced.

Resources can be centered on designing new facilities.

No Cutting Oil Ingress by Any Path The Strongest Material

Cables with Fluororesin Sheaths

Patent pending

Soft Fluororesin Cable That Resists Deterioration Due to Cutting Oil. Used for Oil-resistant Components.

Oil-resistant

Connectors XS5 R

Fluororesin Blocks Ingress from Cables



Fluororesin Outer Cable Sheath

Fluororesin, which provides superior resistance to corrosion, is used for the outer cable sheath to suppress cable swelling and deterioration and prevent the ingress of cutting oil into the PCB inside the Sensor.

Oil-resistant Proximity Sensors E2ER/E2ERZ


Proximity Sensors and Photoelectric Sensors, Limit Switches, Connectors


Previous Models Cable Sheath: PVC or PUR

Water-insoluble cutting oils deteriorate PVC and water-soluble cutting oils deteriorate PUR, so the correct cable must be used. Application in an oily environment that causes deterioration makes the cable harden and break, resulting in ingress of cutting oil to the conductor insulation surface. The oil follows this surface to enter the PCB and destroy the circuit.

NEW Cable Sheath: Fluororesin

Fluororesin, which is less likely to be deteriorated by either water-insoluble or water-soluble cutting oils, is used for the cable sheath. This prevents penetration of cutting oils into the cable.






*The Strongest Material: Based on June 2016 OMRON investigation

Fiber Units E32-T11NF

The results of a thorough analysis of the ingress paths of cutting oil show that the deterioration of cable sheaths is a large factor. The cable sheaths of OMRON's Oil-resistant Components are made from fluororesin materials to provide maximum protection against the deterioration with a unique new concept. The result is an oil resistance impregnable to even highly aggressive cutting oils.



No Cutting Oil Ingress by Any Path The Strongest Material

New Rubber Material Combining HNBR and Fluororubber


OMRON-developed Rubber Blocks Ingress through Joints and Moving Sections

Patented


New Rubber Material Combining HNBR and Fluororubber



Hydrogenated nitrile butadiene rubber (HNBR), which provides superior resistance to oil, was blended with fluororubber in a unique OMRON compound to develop a new rubber that provides superior resistance to both swelling and deterioration due to cutting oil. It is used in seals for joints and moving sections that prevent ingress to prevent deterioration and destruction of the seal due to cutting oil, resulting in increased oil resistance performance.





This new material combines the benefits of HNBR and fluororubber




*The Strongest Material: Based on June 2016 OMRON investigation

In addition to deterioration of cable sheaths, deterioration of the rubber used at joints and moving sections is also a major cause of ingress of cutting oil. In order to prevent rubber deterioration, OMRON's Oil-resistant Components use a new fluorinated rubber at joints and moving sections. Combined with fluororesin cables, this double use of the strongest materials forms an impregnable wall of oil resistance.







No Cutting Oil Ingress by Any Path Advanced Sealing Method


Ingress through Cable Joints Is Blocked with a State-of-the-art Sealing Method

Patent Pending

Heat-Sealing Method




A fluororesin cable is heat-welded with a fluoro component which has a high bondability and a melting point close to that of the cable. This blocks the ingress of cutting oil from the joined surfaces. Oil-resistant Proximity Sensors E2ER/E2ERZ



Forming and Sealing Method + Surface Bonding Technique



OMRON's unique over-molding method that combines forming and sealing methods with surface bonding techniques blocks the ingress of cutting oil through the joined surfaces into the connector.





In addition to cable sheaths, joints, and moving sections, cutting oil enters most easily in gaps between different materials. OMRON's Oil-resistant Components completely block the ingress of cutting oil with a state-of-the-art sealing method that does not allow the creation of gaps.

Completely Sealed with Laser Welding

Patent Pending


Method for Complete Sealing without Adhesive



This picture is for illustrative purposes only

The laser beam is controlled with high precision. This method of fusing metal at a precise location with a small laser beam spot enables application to sensors and other small electronic devices.

The gaps at joints between metal parts are sealed by fusing the metal parts together with the laser beam. At other joints, O-rings of the new material are used and the circumference is fastened with laser welding to prevent ingress of cutting oil without any adhesive which can cause swelling and deterioration.




No Cutting Oil Ingress by Any Path Unique Structure

OMRON's Unique Structure without Gaps Blocks Oil Ingress

Mechanical Seal Structure

Fiber Units

An aluminum ring bushing is compressed and deformed by a set screw to seal the structure by pressing against the fluororesin part of the fiber core. This prevents the ingress of cutting oil from the joined surfaces.






Photoelectric Sensors

A bushing made from the new material is compressed and deformed by pressing a metal ring against it to tighten and seal the fluororesin cable. This prevents the ingress of cutting oil through the cable lead section.






In addition to cable sheaths, joints, and moving sections, cutting oil enters most easily in gaps between different materials. OMRON's Oil-resistant Components completely block the ingress of cutting oil with a unique structure that does not allow the creation of gaps.



With traditional screw-tightened structures, differences in tightening torque made achieving oil resistance difficult. The Smartclick structure, however, locks in a single operation. The built-in 0-ring at the lock position is dependably compressed to block the ingress of cutting oil. This structure eliminates the needs to manage screw tightening torque and prevents screw loosening due to vibration, which were issues in environments requiring oil resistance.

Smartclick is a registered trademark of OMRON Corporation.




Verification of Four-year^{*1} Oil Resistance specified in JIS K 2241:2000

OMRON's Unique Evaluation Technology



OMRON's Environment-resistant Series Oil-resistant Components have been evaluated according to IP67G of JIS C 0920*2 as well as according to the strict evaluation standards for OMRON's oil-resistant components.



*2. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards)

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil. *3. This is the evaluation time for products for machining processes where the amount of splashing cutting oil is large. Target products: Oil-resistant Proximity Sensor E2ER/E2ERZ, Oil-resistant Limit Switch D4ER-□N, Oil-resistant Connector XS5□R, Oil-resistant Fiber Unit E32-T11NF

*4. This is the evaluation time for products for conveyance processes where the amount of splashing cutting oil is small. Target products: Oil-resistant Photoelectric Sensor E3ZR-C

Patent Pending OMRON's Unique Accelerated Evaluation Tests with Failure Mode

To verify a four-year oil resistance, the most aggressive of the water-soluble cutting oils (A1) was used without dilution. (Normally, it is diluted 20 to 30 times with water.) In addition, an environmental temperature^{*5} of 55°C, a temperature that is eight times as severe as room temperature, was used in a unique OMRON evaluation method that enables the verification of four-year oil resistance in a short period of time by analyzing failure caused by cutting oils and deriving the time until occurrence of the failure in the field and time until reproduction in accelerated testing linked with the failure state. (Because conveyance processes have less splashing of cutting oil than manufacturing processes, conveyance processes were evaluated for approximately 1/3 the time.)

Also, the criterion, no labeling text loss, was added so that laser-marked lot numbers can be accurately confirmed over the life of the product for reliable usage for four years.



A1 (water-soluble Test oil cutting oil) Evaluation time 2.000 hours Evaluation 55°C temperature

Undiluted

Note: The photograph shows an E2ER Proximity Sensor.


*5. Deterioration proceeds twice as quickly for every 10°C increase in the ambient operating temperature (Arrhenius law). Therefore, a 30°C increase over room temperature (25°C) to an evaluation temperature of 55°C would make the evaluation eight times stricter.



Four-year^{*6} Stable Operation Verified in Oil Resistance Testing with Representative Cutting Oils

Based on OMRON's oil-resistant component evaluation standards, we performed oil resistance testing with eight representative cutting oils that are used in manufacturing sites (see Table 1). In the results, the four-year⁶ stable operation of the "Oil-resistant Components" was demonstrated, and the evaluation of oil resistance for four years was proven.

*6. Years in actual usage environment in OMRON's unique accelerated evaluation tests.




We offer the reassurance of no failure for four years on all these products.

*7. The 0% degree of deterioration: a condition that meets OMRON's oil-resistant component evaluation standards (Table 1)

Sample number	Test oil type	Oil	JIS classifi- cation	Kinetic viscosity (mm²/s, 40°C)	pH*8
- 1		Yushiroken EC50T-3	A1	-	10.2
- 2		Yushiroken FGE2002	A1	-	8.9
— 3		Yushiroken FGE366	A1	-	9.3
🛨 4		Yushiroken FX90	A1	-	9.6
	Water-	Yushiroken GC	A1	-	9.6
→ 6	soluble	Yushiroken FGM427	A2	-	10.2
- 7	cutting	Yushiroken FGM520	A2	-	9.3
- 8	oil	Yushiroken FGS700	A2	-	9.9
- 9		Yushiroken FGS795	A2	-	9.6
- 10		Yushiroken CN-100	A3	-	9.7
++ 11		Yushiroken FGC826	A3	-	9.5
++ 12		Yushiroken FGC950PR	A3	-	10.1
🛨 13		Yushiron Oil CA26	N1	15	-
- 14	Water-	Yushiron Oil CL	N1	2	-
🛨 15	insoluble	Yushiron Cut Abas BZ135	N3	2	-
— 16	cutting	Yushiron Cut Abas BZ224K	N3	10	_
	oil	Yushiron Cut Abas KZ440	N4	19	_
<mark>→</mark> 18		Yushiron Cut Abas SF33	N4	3	-

Note. Cutting oil givein in (table 1) are all manufactured by YUSHIRO CHEMICAL INDUSTRY CO., LTD.

*8. pH values recommended by the cutting oil manufacturer are listed. These values are reference values only. For more information, refer to the YUSHIRO CHEMICAL INDUSTRY CO., LTD. website.



Select a product that suits your application Product Lineup



Oil-resistant Fiber Unit

Oil-resistant Proximity Sensors E2ER/E2ERZ

Proximity Sensors That Withstand Cutting Oil to Reduce Failures Caused by Ingress of Cutting Oil

- Fluororesin cable that withstands cutting oil.
- · A sealing method that eliminates gaps at cable joints and the resin filling work together to block ingress of cutting oil.
- IP67G * degree of protection (JIS C 0920 Annex 1).

Refer to Safety Precautions on page 22.

The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

Features

Fluororesin Outer Cable Sheath

Fluororesin, which is less likely to be deteriorated by either water-insoluble or water-soluble cutting oils, is used for the cable sheath.


This prevents penetration of cutting oils into the cable.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Heat-Sealing Method

A fluororesin cable is heat-welded with a fluoro component which has a high bondability and a melting point close to that of the cable. This blocks the ingress of cutting oil from the joined surfaces.






Cable with fluororesin sheath

Applications

Detection of Cylinders



Detection of Cutting Workpieces



Ordering Information

Sensors

Standard Proximity Sensors [Refer to Dimensions on page 25.]

Annorr		Sar	aina dia	tonoo	Connection	Cable	Мо	del
Appeara	ance	Ser	nsing dis	stance	method specificatio		Operation mode: NO	Operation mode: NC
					Pre-wired Models (2 m)		E2ER-X2D1 2M *	E2ER-X2D2 2M *
	M8	2 mm			M12 Pre-wired Smartclick Connector Models (0.3 m)		E2ER-X2D1-M1TGJ 0.3M	E2ER-X2D2-M1TGJ 0.3M
					Pre-wired Models (2 m)		E2ER-X3D1 2M *	E2ER-X3D2 2M *
Shielded	M12	3 mr	m		M12 Pre-wired Smartclick Connector Models (0.3 m)	Fluororesin	E2ER-X3D1-M1TGJ 0.3M	E2ER-X3D2-M1TGJ 0.3M
					Pre-wired Models (2 m)	Fluororesin	E2ER-X7D1 2M *	E2ER-X7D2 2M *
	M18	7	mm		M12 Pre-wired Smartclick Connector Models (0.3 m)		E2ER-X7D1-M1TGJ 0.3M	E2ER-X7D2-M1TGJ 0.3M
					Pre-wired Models (2 m)	-	E2ER-X10D1 2M *	E2ER-X10D2 2M *
	M30		10 mm		M12 Pre-wired Smartclick Connector Models (0.3 m)		E2ER-X10D1-M1TGJ 0.3M	E2ER-X10D2-M1TGJ 0.3M

* Models with 5-m cable length are also available with "5M" suffix. (Example: E2ER-X2D1 5M)

Chip-immune Proximity Sensors [Refer to Dimensions on page 25.]

Annoor		Sensing distance	Connection	Cable	Мо	del
Appeara	ance	Sensing distance	method	specifications	Operation mode: NO	Operation mode: NC
			Pre-wired Models (2 m)		E2ERZ-X2D1 2M *	E2ERZ-X2D2 2M *
	M12	2 mm	M12 Pre-wired Smartclick Connector Models (0.3 m)		E2ERZ-X2D1-M1TGJ 0.3M	E2ERZ-X2D2-M1TGJ 0.3M
Shielded			Pre-wired Models (2 m)	-	E2ERZ-X4D1 2M *	E2ERZ-X4D2 2M *
	M18	4 mm	M12 Pre-wired Smartclick Connector Models (0.3 m)	Fluororesin	E2ERZ-X4D1-M1TGJ 0.3M	E2ERZ-X4D2-M1TGJ 0.3M
			Pre-wired Models (2 m)		E2ERZ-X8D1 2M *	E2ERZ-X8D2 2M *
	M30	8 mm	M12 Pre-wired Smartclick Connector Models (0.3 m)		E2ERZ-X8D1-M1TGJ 0.3M	E2ERZ-X8D2-M1TGJ 0.3M

* Models with 5-m cable length are also available with "5M" suffix. (Example: E2ERZ-X2D1 5M)

Accessories (Sold Separately)

Sensor I/O Connectors (M12, Sockets on One Cable End)

(Models for Pre-wired Connectors) A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable diameter (mm)	Cable length	Sensor I/O Connector model number	Applicable Proximity Sensor model number
Straight, Smartclick Oil-resistant		2 m	XS5FR-D423-D80-RB1	
Connectors	4 dia.	5 m	XS5FR-D423-G80-RB1	E2ER-X□D□-M1TGJ E2ERZ-X□D□-M1TGJ
		10 m	XS5FR-D423-J80-RB1	

Note: Refer to the XS5 R on page 53 for connector details and for information on cables with connectors on both ends.

16

Ratings and Specifications

Standard Proximity Sensors

ltem Sensina d	Shielded						
			Shie	lded			
Sensina d	Model	E2ER-X2D	E2ER-X3D	E2ER-X7D	E2ER-X10D		
	distance	2 mm ±10%	3 mm ±10%	7 mm ±10%	10 mm ±10%		
Set distar	nce *1	0 to 1.6 mm	0 to 2.4 mm	0 to 5.6 mm	0 to 8 mm		
Differenti	al travel	15% max. of sensing distance	10% max. of sensing distance	e			
Detectabl	e object	Ferrous metal (The sensing of	distance decreases with non-f	errous metal. Refer to Engin	neering Data on page 19.)		
Standard object	sensing	Iron, $8 \times 8 \times 1 \text{ mm}$	Iron, $12 \times 12 \times 1$ mm	Iron, $18 \times 18 \times 1$ mm	Iron, $30 \times 30 \times 1$ mm		
Response 2	e frequency	1.5 kHz	1 kHz	0.5 kHz	0.4 kHz		
Power sup	ply voltage	10 to 30 VDC, (including 10%	% ripple (p-p))				
Leakage	current	0.8 mA max.					
Control	Load current	3 to 100 mA					
output	Residual voltage	3 V max. (Load current: 100	,				
Indicators	6	D1 Models: Operation indica D2 Models: Operation indica	tor (red), Setting indicator (gre tor (red)	een)			
Operatior (with sen approach	sing object	D1 Models: NO D2 Models: NC Refer to the timing charts under <i>I/O Circuit Diagrams</i> on page 21 for details.					
Protectio	n circuits	Surge suppressor, Load short-circuit protection					
Ambient temperati	ure range	Operating: -25 to 70°C, Storage: -40 to 85°C (with no icing or condensation)					
Ambient humidity	range	Operating and Storage: 35% to 95% (with no condensation)					
Temperat influence		\pm 15% max. of sensing distance at 23°C in the temperature range of –25 to 70°C	±10% max. of sensing distar	nce at 23°C in the temperatu	re range of –25 to 70°C		
Voltage in	nfluence	±1% max. of sensing distance	e at rated voltage in the rated	voltage ±15% range			
nsulatior	n resistance	50 $M\Omega$ min. (at 500 VDC) be	tween current-carrying parts a	and case			
Dielectric	strength	1,000 VAC, 50/60 Hz for 1 m	inute between current-carryin	g parts and case			
Vibration (destructi	resistance ion)	10 to 55 Hz, 1.5-mm double	amplitude for 2 hours each in	X, Y, and Z directions			
Shock res (destructi		500 m/s ² 10 times each in X, Y, and Z directions	1,000 m/s ² 10 times each in	X, Y, and Z directions			
Degree of	f protection		* ³ (JIS C 0920 Annex 1) ant Component Evaluation Sta JIS K 2241:2000, Temperatu				
Connecti	on method	Pre-wired Models (Standard	cable length: 2 m) and Pre-wi	red Connector Models (Star	ndard cable length: 300 mm		
Weight	Pre-wired Models	Approx. 65 g	Approx. 75 g	Approx. 145 g	Approx. 215 g		
(packed state)	Pre-wired Connector Models	Approx. 30 g	Approx. 40 g	Approx. 90 g	Approx. 155 g		
	Case	Stainless steel (SUS303) Nickel-plated brass					
Motori	Sensing surface	Polybutylene terephthalate (PBT) Nickel-plated brass					
Materi- als	Clamping nuts						
-	Toothed washer	Zinc-plated iron					

*1. Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

*2. The response frequency is an average value.

Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

*3. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

*4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

The Pre-wired Connector Model meets the degree of protection when it is correctly connected with an XS5 R Oil-resistant Connector. The degree of protection is not satisfied with the part where there is no XS5FR Oil-resistant Connector connected and cable wires are uncovered.

And as for the Pre-wired Models, the degree of protection is not satisfied with the part where cable wires are uncovered.

Oil-resistant Connectors

Chip-immune Proximity Sensors

Sensing distance 2 mm ±10%, 4 mm ±10%, 8 mm ±10%, 0 m ±10%, Set distance 10 to 1.6 mm 0 to 2.2 mm 0 to 6.4 mm Differential travel 20% max. of sensing distance 0 to 6.4 mm 0 to 6.4 mm Detectable object Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on pa Standard sensing tron, 12 × 12 × 1 mm Iron, 30 × 30 × 1 mm Iron, 54 × 54 × 1 mm Response frequency 200 Hz 100 Hz 30 Hz Power supply voltage 10 to 30 VDC, (including 10% ripple (p-p)) Leakage current 0.8 mA max. Control Residual voltage 3 V max. (Load current: 100 mA, Cable length: 2 m) Di Models: Operation indicator (red). Di Models: Operation indicator (red) Di Models: Operation indicator (red). Di Models: NC Operating and Storage: 0 to 50°C (with no icing or condensation) Operating and Storage: 36% to 95% (with no condensation) Temperature range Operating and Storage: 36% to 95% (with no condensation) Insulation resistance 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance 10 to 05 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruc		Size	M12	M18	M30				
Sensing distance 2 mm ±10% 4 mm ±10% 8 mm ±10% Set distance '1 0 to 1.6 mm 0 to 3.2 mm 0 to 6.4 mm Detectable object Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on pastandard sensing) Standard sensing tron, 12 × 12 × 1 mm tron, 30 × 30 × 1 mm tron, 54 × 54 × 1 mm Responses frequency 200 Hz 100 Hz 30 Hz Power supply voltage 10 to 30 VDC, (including 10% ripple (p-p)) 0.8 mA max. Control Responses frequency 200 HZ 100 Hz 30 HZ Power supply voltage 10 to 30 VDC, (including 10% ripple (p-p)) 0.8 mA max. 0.8 mA max. Control Responses frequency 200 HZ 100 Hz 30 HZ Power supply voltage 3 to 100 mA Current 0.8 mA max. 0.8 mA max. Di Models: Operation indicator (red). Setting indicator (green) D2 Models: Operation indicator (red) 00 Endedis. Portection circuits Surge suppressor, Load short-circuit protection 00 perating and Storage: 35% to 95% (with no condensation) Comportang and Storage: 35% to 95% (with no condensation) 00 to 50°C 00 to 50°C Coltage influence <td< th=""><th></th><th>Shielded</th><th></th><th>Shielded</th><th></th></td<>		Shielded		Shielded					
Set distance *1 0 to 1.6 mm 0 to 3.2 mm 0 to 6.4 mm Differential travel 20% max. of sensing distance 20% max. of sensing distance decreases with non-ferrous metal. Refer to Engineering Data on past and ard sensing Diplect Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on past and sensing distance 30 Hz Dower supply voltage 10 to 30 VDC, (including 10% ripple (p-p)) 30 Hz cakage current 0.8 mA max. 3 to 100 mA Control Current 3 to 100 mA Residual 3 V max. (Load current: 100 mA, Cable length: 2 m) D1 Models: Operation indicator (red), Setting indicator (green) D2 Models: Operation indicator (red) D1 Models: Operation indicator (red) Setting indicator (green) D2 Models: NC D1 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Vminiet in the set of the timing charts under I/O Circuit Diagrams on page 21 for details. Viblent Operating and Storage: 0 to 50°C (with no condensation) +20% max. of sensing distance at rated voltage in the rated voltage ±10% range Isolar min, (at 500 VDC) between current-carrying parts and case 100 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Viblettrient 100 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions <	em	Model	E2ERZ-X2D	E2ERZ-X4D	E2ERZ-X8D				
Differential travel 20% max. of sensing distance Detectable object Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on passandard sensing) bipect Iron, 12 × 12 × 1 mm Iron, 30 × 30 × 1 mm Iron, 54 × 54 × 1 mm Response frequency 200 Hz 100 Hz 30 Hz Power supply voltage 10 to 30 VDC, (including 10% ripple (p-p))	ensing di	istance	2 mm ±10%	4 mm ±10%	8 mm ±10%				
Detectable object Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on pa standard sensing) bject Iron, 12 × 12 × 1 mm Iron, 30 × 30 × 1 mm Iron, 54 × 54 × 1 mm Response frequency 2 200 Hz 100 Hz 30 Hz 30 Hz Ower supply voltage 10 to 30 VDC, (including 10% ripple (p-p))	et distan	ce *1		0 to 3.2 mm					
Detectable object Standard sensing bject Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to Engineering Data on pa tron, 12 × 12 × 1 mm Iron, 30 × 30 × 1 mm Iron, 54 × 54 × 1 mm Response frequency 2 200 Hz 100 Hz 30 Hz 30 Hz Power supply voltage 10 to 30 VDC. (including 10% ripple (p-p)) 0.8 mA max. 30 Hz 30 Hz Control current 3 to 100 mA 3 vmx. (Load current: 100 mA, Cable length: 2 m) 10 to 30 VDC. (including 10% ripple (p-p)) 0.8 mA max. Decrement 0.1 Models: Operation indicator (red). Setting indicator (green) D2 Models: Operation indicator (red) 10 to 30 VDC. (including 10% ripple (p-p)) 0.8 mA max. Operation mode with sensing object ipproaching 01 Models: Operation indicator (red). Setting indicator (green) D2 Models: NC D2 Models: NC D2 Models: NC 10 Models: NO D2 Models: NC 10 Models: NO D2 Models: NC Preterion circuits Surge suppressor, Load short-circuit protection 10 Models: NO D2 Models: NC 10 Models: NO D2 Models: NC Preterion resistance insulation resistance fiberation resistance Operating and Storage: 35% to 95% (with no condensation) 20% max. of sensing distance at rated voltage in the rated voltage ±10% range Shock resistance destruction 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z direct	ifferentia	l travel	20% max. of sensing distance						
Standard sensing bject Iron, 12 × 12 × 1 mm Iron, 30 × 30 × 1 mm Iron, 54 × 54 × 1 mm Sepsonse frequency 2 200 Hz 100 Hz 30 Hz Power supply voltage 10 to 30 VDC, (including 10% ripple (p-p)) 30 Hz Leadag current 0.8 mA max. 30 Hz Control voltage 20 Max 100 mA 30 Hz Durput Lead voltage 3 to 100 mA 30 Hz Di Models: Operation indicator (red), Setting indicator (green) D2 Models: NO D2 Models: NO Potettion indicator (red) D1 Models: Operation indicator (red) Di Models: NO retection circuits Surge suppressor, Load short-circuit protection D1 Models: NO Potettion Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection To words with ansing object D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Ambient unmidity range Operating and Storage: 35% to 95% (with no condensation) Error Correst and stato rage is 50 M2 min. (at 500 VDC) between current-carrying parts and case D10 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Dielectric strength 1,000 V	etectable	object		decreases with non-ferrous metal. Re	fer to Engineering Data on page 19.)				
2 200 H2 100 H2 30 H2 Prover supply voltage 10 to 30 VDC, (including 10% ripple (p-p))	tandard s	-							
Leakage current 0.8 mA max. Control Durput Load voltage 3 to 100 mA Residual voltage 3 V max. (Load current: 100 mA, Cable length: 2 m) D1 Models: Operation indicator (red), Setting indicator (green) D2 Models: Operation indicator (red) D1 Models: Operation indicator (red) Operation mode with sensing object D1 Models: Operation indicator (red) D1 Models: NO D2 Models: NO D2 Models: NO D2 Models: NO D2 Models: NO Developerature range D1 Models: Operation indicator (red) Ambient memperature range Operating and Storage: 0 to 50°C (with no icing or condensation) Unit operating and Storage: 35% to 95% (with no condensation) Ambient numidity range Operating and Storage: 35% to 95% (with no condensation) E20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Foltage influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C E25% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Foltage influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C E25% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Foltage influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C E25% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Foltage influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C <td></td> <td>frequency</td> <td>200 Hz</td> <td>100 Hz</td> <td>30 Hz</td>		frequency	200 Hz	100 Hz	30 Hz				
Load current voltage 3 to 100 mA Residual voltage 3 V max. (Load current: 100 mA, Cable length: 2 m) Indicators D1 Models: Operation indicator (red). Setting indicator (green) D2 Models: Operation indicator (red) Operation mode with sensing object D1 Models: Operation indicator (red). D1 Models: Operation indicator (red) D2 Models: Operation indicator (red) Operation mode with sensing object D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection D1 Models: NC Ambient numidity range Operating and Storage: 0 to 50°C (with no icing or condensation) Femperature raftuence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at rated voltage in the rated voltage ±10% range Isolation resistance 0.00 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Objecter strength 1,000 m/s² 10 times each in X, Y, and Z directions Shock resistance 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable le	ower supp	bly voltage	10 to 30 VDC, (including 10% ripple	(p-p))					
Control Nutry in Residual voltage Control Residual voltage 3 to 100 mA 3 V max. (Load current: 100 mA, Cable length: 2 m) 3 V max. (Load current: 100 mA, Cable length: 2 m) Indicators D1 Models: Operation indicator (red). Setting indicator (green) D2 Models: Operation indicator (red) 5 Models: Operation indicator (red) Operation mode with sensing object interpersenting D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Operating and Storage: 0 to 50°C (with no icing or condensation) Ambient munidity range Operating and Storage: 35% to 95% (with no condensation) Image: 215% max. of sensing distance at rated voltage in the rated voltage ±10% range Storage influence ±25% max. of sensing distance at rated voltage in the rated voltage ±10% range Image: 215% max. of sensing distance at rated voltage in the rated voltage ±10% range Storage influence 10.00 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Image: 215% max. 1000 m/s² 10 times each in X, Y, and Z directions Shock resistance destruction 10.00 m/s² 10 times each in X, Y, and Z directions Image: 215 G max. Perewired Connector Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable leng	eakage c	urrent	0.8 mA max.						
voltage 3 V max. (Load current: 100 mA, Cable length: 2 m) ndicators D1 Models: Operation indicator (red). Setting indicator (green) D2 Models: Operation indicator (red) Operation mode with sensing object D1 Models: NO Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Ambient unmidity range Operating and Storage: 0 to 50°C (with no icing or condensation) Protection circuits Surge suppressor, Load short-circuit protection Ambient unmidity range Operating and Storage: 35% to 95% (with no condensation) Premerature finduence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at 23°C in the temperature range 1.000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Dielectric strength 1.000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case 1.000 m/s ² 10 times each in X, Y, and Z directions Shock resistance destruction 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired			3 to 100 mA						
Decention mode (with sensing object approaching) D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Operating and Storage: 0 to 50°C (with no icing or condensation) Ambient temperature range Operating and Storage: 35% to 95% (with no condensation) Image: 120% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Temperature influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at rated voltage in the rated voltage ±10% range Insulation resistance (destruction) 1000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Vibration resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1000 m/s ² 10 times each in X, Y, and Z directions Degree of protection PF67 (IEC 60529) and IP67G ⁺⁴ (JIS C 0920 Annex 1) Passed OMRON'S Oil-resistant Component Evaluation Standards ⁺⁴ (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connector Pre-wired Models Approx. 75 g Approx. 145 g Approx. 215 g Weight (packed) Pre-wired Models Approx. 40 g Approx. 90 g Approx. 155 g Sensing Polybuty	-		3 V max. (Load current: 100 mA, Cab	ble length: 2 m)					
Operating object approaching) D1 Models: NO D2 Models: NC Refer to the timing charts under I/O Circuit Diagrams on page 21 for details. Protection circuits Surge suppressor, Load short-circuit protection Ambient Ambient temperature range Operating and Storage: 0 to 50°C (with no icing or condensation) Ambient Armbient temperature influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence Voltage influence ±2.5% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence Insulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Models State) Rerewired Models Approx. 75 g	dicators		D1 Models: Operation indicator (red) D2 Models: Operation indicator (red)	, Setting indicator (green)					
Ambient temperature range Operating and Storage: 0 to 50°C (with no icing or condensation) Ambient temperature range Operating and Storage: 35% to 95% (with no condensation) Ambient unmidity range Operating and Storage: 35% to 95% (with no condensation) Temperature influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at rated voltage in the rated voltage ±10% range Insulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Vibration resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions IP67 (IEC 60529) and IP67G ⁻³ (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards ⁻⁴ (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connector method Pre-wired Models (Standard cable length: 2m) and Pre-wired Connector Models (Standard cable length: 2m/acce Weight (packed) Approx. 75 g Approx. 145 g Approx. 215 g Materi- als Approx. 40 g Approx. 90 g Approx. 155 g Case Nickel-plated brass Sensing surface	vith sens	ing object	Releficitie infinitio	charts under I/O Circuit Diagrams on	page 21 for details.				
emperature range Operating and Storage: 0 to 50°C (with no roing or condensation) Ambient numidity range Operating and Storage: 35% to 95% (with no condensation) Femperature numidity range ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at rated voltage in the rated voltage ±10% range nsulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Objectric strength 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Degree of protection Prof (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's OUrceistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connector method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector	rotection	circuits	Surge suppressor, Load short-circuit	protection					
numidity range Operating and Storage: 35% to 95% (with no condensation) Femperature nfluence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C voltage influence ±2.5% max. of sensing distance at 23°C in the temperature range of 0 to 50°C nsulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case //ibration resistance 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance destruction) 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection 1000 m/s² 10 times each in X, Y, and Z directions Connector method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired C		re range	Operating and Storage: 0 to 50°C (w	age: 0 to 50°C (with no icing or condensation)					
influence ±20% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Voltage influence ±2.5% max. of sensing distance at 23°C in the temperature range of 0 to 50°C Insulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Vibration resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 models Weight (packed State) Pre-wired Connector Approx. 40 g Approx. 90 g Approx. 155 g Materials Case Nickel-plated brass Sensing surface Polybutylene terephth		ange	Operating and Storage: 35% to 95% (with no condensation)						
Insulation resistance 50 MΩ min. (at 500 VDC) between current-carrying parts and case Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Vibration resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models Approx. 75 g Prewired State) Approx. 40 g Materials Provined Connector Models Sensing surface Nickel-plated brass Sensing surface Zinc-plated iron		ıre	±20% max. of sensing distance at 23	°C in the temperature range of 0 to 50	°C				
Dielectric strength 1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case Vibration resistance (destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance (destruction) 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connector method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 models Materials Raprox. 75 g Approx. 145 g Approx. 215 g Materials Rase Nickel-plated brass Sensing surface Polybutylene terephthalate (PBT) Materials Zinc-plated iron Zinc-plated iron Toothed Final Approx	oltage in	fluence	$\pm 2.5\%$ max. of sensing distance at ra	ted voltage in the rated voltage $\pm 10\%$	range				
/ibration resistance destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions Shock resistance destruction) 1,000 m/s ² 10 times each in X, Y, and Z directions Shock resistance destruction) 1,000 m/s ² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G * ³ (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards * ⁴ (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: Pre-wired Models Neight packed state) Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models Neight packed Pre-wired Connector Models Approx. 75 g Approx. 145 g Approx. 215 g Materi-alis Case Nickel-plated brass Sensing surface Polybutylene terephthalate (PBT) Inc-plated iron Toothed Toothed Toothed Toothed Toothed Toothed	sulation	resistance	50 M Ω min. (at 500 VDC) between c	urrent-carrying parts and case					
destruction) 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and 2 directions Shock resistance destruction) 1,000 m/s ² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: Models Neight packed state) Pre-wired Models Approx. 75 g Approx. 145 g Approx. 215 g Veight packed state) Pre-wired Connector Models Approx. 40 g Approx. 90 g Approx. 155 g Materials Case Nickel-plated brass Surface Polybutylene terephthalate (PBT) Clamping nuts Zinc-plated iron Zinc-plated iron Toothed Free-wited iron	ielectric	strength	1,000 VAC, 50/60 Hz for 1 minute be	tween current-carrying parts and case					
Indestruction 1,000 m/s² 10 times each in X, Y, and Z directions Degree of protection IP67 (IEC 60529) and IP67G *3 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: packed state) Neight packed state) Pre-wired Models Approx. 75 g Approx. 145 g Approx. 215 g Veright packed state) Re-wired Models Approx. 40 g Approx. 90 g Approx. 155 g Vateri- als Case Nickel-plated brass Polybutylene terephthalate (PBT) Inc-plated iron			10 to 55 Hz, 1.5-mm double amplitud	le for 2 hours each in X, Y, and Z direc	tions				
Degree of protection Passed OMRON's Oil-resistant Component Evaluation Standards *4 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35 °C max.) Connection method Pre-wired Models (Standard cable length: 2 m) and Pre-wired Connector Models (Standard cable length: 2 m) and Pre-wired Connector Models (PBT)			1,000 m/s ² 10 times each in X, Y, and	d Z directions					
Pre-wired (packed state) Pre-wired Connector Models Approx. 75 g Approx. 145 g Approx. 215 g Pre-wired Connector Models Approx. 40 g Approx. 90 g Approx. 155 g Case Nickel-plated brass Sensing surface Polybutylene terephthalate (PBT) Clamping nuts Zinc-plated iron Toothed	egree of	protection	Passed OMRON's Oil-resistant Com	ponent Evaluation Standards *4					
Models Approx. 75 g Approx. 145 g Approx. 215 g Ipacked state) Pre-wired Connector Models Approx. 40 g Approx. 90 g Approx. 155 g Image: Sensing surface Nickel-plated brass Polybutylene terephthalate (PBT) Image: Sensing surface Polybutylene terephthalate (PBT) Image: Toothed Image: Sensing surface	onnectio	n method	Pre-wired Models (Standard cable le	ngth: 2 m) and Pre-wired Connector M	odels (Standard cable length: 300 mm				
Pre-wired State) Pre-wired Connector Models Approx. 40 g Approx. 90 g Approx. 155 g Materi- als Case Nickel-plated brass Sensing surface Polybutylene terephthalate (PBT) Vertical connector Clamping nuts Zinc-plated iron Zinc-plated iron Vertical connector Vertical connector			Approx. 75 g	Approx. 145 g	Approx. 215 g				
Sensing surface Polybutylene terephthalate (PBT) Clamping nuts Zinc-plated iron	acked tate)	Connector	Approx. 40 g	Арргох. 90 д	Approx. 155 g				
Materi- als Surface Polybutylene terephthalate (PBT) Clamping nuts Zinc-plated iron		Case	Nickel-plated brass						
Clamping nuts Zinc-plated iron Toothed Image: Clamping nuts			•						
Toothed Zinc plated iron	ateri-	Clamping	Zinc-plated iron	Zinc-plated iron					
washer			Zinc-plated iron						

*1. Use the Sensor within the range in which the setting indicator (green LED) is ON (except D2 Models).

*2. The response frequency is an average value.

Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

*3. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).


The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil. *4. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.


4. The Oil-resistant Component Evaluation Standards are Oil RON's own durability evaluation standards. The Pre-wired Connector Model meets the degree of protection when it is correctly connected with an XS5 ROII-resistant Connector. The degree of protection is not satisfied with the part where there is no XS5FR Oil-resistant Connector connected and cable wires are uncovered.

And as for the Pre-wired Models, the degree of protection is not satisfied with the part where cable wires are uncovered.


Engineering Data (Reference Value)

Sensing Area






Chip-immune Proximity Sensors E2ERZ-X




Influence of Sensing Object Size and Material Standard Proximity Sensors E2ER-X2 E2E




E2ER-X3 Distance X (mm) d×|-=1 mr 3.5 , the 3.0 lror 2.5 Stainless stee (SUS304) 2.0 1.5 Brass Aluminum 1.0 Copper 0.5 0 25 30 35 20 40 Side length of sensing object: d (mm)








E2ER-X10




Chip-immune Proximity Sensors E2ERZ-X2











Chip-immune Proximity Sensors




Residual Output Voltage

Standard Proximity Sensors / Chip-immune Proximity Sensors



I/O Circuit Diagrams



Connections to Sensor I/O Connectors

Prox	cimity Sen	sor	Sensor I/O Connector	Connections		
Туре	Operation mode	Model	model number			
DC 2-wire	NO	E2ER-X□D1 -M1TGJ E2ERZ-X□D1 -M1TGJ	XS5FR-D423- D: 2-m cable G: 5-m cable J: 10-m cable	E2ER/E2ERZ XS5FR U U U U U U U U U U U U U		
(Smartclick)	NC	E2ER-X□D2 -M1TGJ E2ERZ-X□D2 -M1TGJ	XS5FR-D423- B0-RB1 D: 2-m cable G: 5-m cable J: 10-m cable	E2ER/E2ERZ XS5FR		

Note: Different from Proximity Sensor wire colors.

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Meaning of Product Safety Symbols

\bigcirc	General prohibition Indicates the instructions of unspecified prohibited action.			
Caution, explosion Indicates the possibility of explosion under specific conditions.				

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion. Do not connect sensor to AC power supply.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation. (1) Do not use the product in an environment where flammable or

- explosive gas is present.
- (2) Do not attempt to disassemble, repair, or modify the product.
- (3) Power Supply Voltage

Do not use a voltage that exceeds the rated operating voltage range. Applying a voltage that is higher than the operating voltage range may result in damage or burnout.

(4) Incorrect Wiring

Be sure that the power supply polarity and other wiring is correct. Incorrect wiring may cause explosion or burnout.

(5) Connection without a Load

If the power supply is connected directly without a load, the internal elements may explode or burn. Be sure to insert a load when connecting the power supply.

(6) Protective structure

Do not use the product with degrade protective structure such as swelling and crack in housing and/or sealing components. Otherwise cutting oil or other substance may enter the product. resulting in a risk of corruption or burning.

(7) Dispose of this product as industrial waste.

Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.

Operating Environment

- (1) Do not install the product in the following locations.
 - Doing so may result in product failure or malfunction.
 - 1. Outdoor locations directly subject to sunlight, rain, snow, water droplets, or oil.
 - 2. Locations subject to atmospheres with chemical vapors, in particular solvents and acids.
 - 3. Locations subject to corrosive gases.
- (2) The Sensor may malfunction if used near ultrasonic cleaning equipment, high-frequency equipment, transceivers, cellular phones, inverters, or other devices that generate a high-frequency electric field. Please refer to the Precautions for Correct Use on the OMRON website (www.ia.omron.com) for typical measures.
- (3) Laying the Proximity Sensor wiring in the same conduit or duct as high-voltage wires or power lines may result in incorrect operation and damage due to induction. Wire the Sensor using a separate conduit or independent conduit.
- (4) Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- (5) The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.

- (6) Connecting Connectors
 - The E2ER/E2ERZ can be used in conditions of cutting oil use described in the specifications.


The oil resistance may not be ensured when the products are not mated to XS5 \Box R Connectors, so use the products correctly.

- When mating the products to XS2 or other M12 Connectors, tighten the lock to a torque of 0.39 to 0.49 N·m.

Design

Influence of Surrounding Metal

When mounting the Sensor within a metal panel, ensure that the clearances given in the following table are maintained. Failure to maintain these distances may cause deterioration in the performance of the Sensor.




Influence of Surrounding Metal (Unit: mm)

	ltem					
Model	Embedded material	Ι	d	D	m	n
E2ER-X2D□ E2ER-X2D□-M1TGJ			8		4.5	12
E2ER-X3D E2ER-X3D -M1TGJ		0	12	0	8	18
E2ER-X7D E2ER-X7D -M1TGJ		0	18	0	20	27
E2ER-X10D E2ER-X10D -M1TGJ			30		40	45
E2ERZ-X2D	Iron	0	12	0	8	18
E2ERZ-X2D -M1TGJ	Aluminum	2	25	2	0	36
E2ERZ-X4D	Iron	0	18	0	16	27
E2ERZ-X4D -M1TGJ	Aluminum	5	40	5	10	54
E2ERZ-X8D	Iron	0	30	0	32	45
E2ERZ-X8D -M1TGJ	Aluminum	10	70	10	52	90

Mutual Interference

When installing Sensors face-to-face or side-by-side, ensure that the minimum distances given in the following table are maintained.





Mutual Interference

			(
Model	ltem	Α	В
E2ER-X2D E2ER-X2D -M1TGJ		20	15
E2ER-X3D E2ER-X3D -M1TGJ		30	20
E2ER-X7D E2ER-X7D -M1TGJ		50	35
E2ER-X10D E2ER-X10D -M1TGJ		100	70
E2ERZ-X2D E2ERZ-X2D -M1TGJ		30	20
E2ERZ-X4D E2ERZ-X4D -M1TGJ		40	50
E2ERZ-X8D□ E2ERZ-X8D□-M1TGJ		60	100

(Unit: mm)

Aluminum and Iron Cuttings (Only for Chip-immune Proximity Sensors)

Normally aluminum or iron cuttings will not be detected even if they adhere to or accumulate on the sensing surface. Detection signals may be output for the following:


If this occurs, remove the cuttings from the sensing surface.

- 1. Relationship between the Size of the Cutting (d) and the Size of the Sensing Surface (D)
- Cuttings of the size $d \ge \frac{2}{3}D$ on the sensing surface *


		(Unit: mm)
Model	Size	D
E2ERZ-X2D		10 *
E2ERZ-X4D		16
E2ERZ-X8D		28

* E2ERZ-X2D: $d \ge \frac{1}{3}D$ on the sensing surface.

2. Cuttings Pressed against the Sensing Surface




Pressed against



Mounting

Tightening Force

Do not tighten the nut with excessive force. A washer must be used with the nut.



- Note: 1. The allowable tightening strength depends on the distance from the edge of the head, as shown in the following table. (A is the distance from the edge of the head. B includes the nut on the head side. If the edge of the nut is in part A, the tightening torque for part A applies instead.)
 - 2. The following strengths assume washers are being used.

Туре	Part	Part B		
Type	Dimension (mm) Torque		Torque	
M8	9 9 N·m 12 N·m			
M12	30 N·m			
M18	70 N·m			
M30	180 N·m			

Oil-resistant Proximity Sensors

Oil-resistant Limit Switches


Oil-resistant Fiber Unit

Oil-resistant Photoelectric Sensors

Oil-resistant Connectors

Dimensions

(Unit: mm) Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.



M12

M18

M30

18.5^{+0.5} dia.

30.5^{+0.5} dia.

31

M12


M18

M30

R

Pre-wired Connector Models





Angle R of the Bending Wire **Mounting Hole Dimensions** Dimension F (mm) Dimension R (mm) 10 mm M8 8.5^{+0.5} dia. M8 22 $12.5^{+0.5}_{0}$ dia. M12 M12 $18.5^{+0.5}_{0}$ dia. M18 M18 31 M30 30.5^{+0.5} dia. M30

Oil-resistant Photoelectric Sensors

Oil-resistant Connectors

Even Better Oil Resistance Than D4E-N Switches


- Material combining HNBR and fluororubber used for superior resistance to oil.
 - Prevents ingress of cutting oil from moving sections.
- Fluororesin cable that withstands cutting oils is provided as standard.
- Models available with Smartclick connectors for easy connection.
- Minute load model with gold cladding is optimal for electronic control.
- Approved by EN (TÜV).
- Same mounting pitch as D4E-N Switches.
- IP67G degree of protection (JIS C 0920 Annex 1). *

Be sure to read Safety Precautions on pages 37 to 38 and Safety Precautions for All Limit Switches.

Features

Material Combining HNBR and Fluororubber for Superior Resistance to Oil

Moving sections are protected from ingress of cutting oil. Important Sealing Sections for Moving Parts



Applications

Table Overrun Detection





For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

 The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).
 The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

Fluororesin Cable Provided as Standard to Withstand Cutting Oils

In addition to prewired models, models are also available with prewired Smartclick connectors for easy connection. Cable type



Table Position Detection



D4ER-

Model Number Structure

Model Number Legend (Not all combinations are possible. Ask your OMRON representative for details.)

D4ER-

(1)(2)(3)(4)

(1) Rated Current

1: 1 A at 30 VDC (Standard load)

2: 0.1 A at 30 VDC (Micro load)

(2) Actuator

- A: Roller plunger
- B: Crossroller plunger
- C: Plunger
- D: Sealed roller plunger
- E: Sealed crossroller plunger
- G: Roller lever
- L: Long roller plunger

(3) Terminals

- 21: Cable (right-hand)
- 22: Cable (left-hand)

Note: The terminal specifications in model numbers are not the same for D4ER-□N and D4E Switches.

Comparison of New and Old Terminal Models

Model Location of lead outlet	D4ER-⊡N	D4E
Right-hand	D4ER-D21N	D4E-□□21
Left-hand	D4ER-D22N	D4E-023
Bottom	-	D4E-022

(4) Pre-wired Connector

-DTK1EJ: Pre-wired connector

(30-cm oil-resistant cable, M12 Smartclick connector) Blank : No connector (oil-resistance cable: 2 m)

Note: D4ER-IN Switches are not available with operation indicators.

Ordering Information

	Туре	Cable	e type
		Standa	rd load
		Right-hand	Left-hand
Actuator		Model	Model
Roller plunger	þ	D4ER-1A21N	D4ER-1A22N
Crossroller plunger	臣	D4ER-1B21N	D4ER-1B22N
Plunger	脚	D4ER-1C21N	D4ER-1C22N
Sealed roller plunger		D4ER-1D21N	D4ER-1D22N
Sealed crossroller plunger	<u>A</u>	D4ER-1E21N	D4ER-1E22N
Roller lever		D4ER-1G21N	D4ER-1G22N
Long roller plunger		D4ER-1L21N	D4ER-1L22N

	Туре	Cable type				
		Micro	load			
		Right-hand	Left-hand			
Actuator		Model	Model			
Roller plunger	þтө	D4ER-2A21N	D4ER-2A22N			
Crossroller plunger	þæ	D4ER-2B21N	D4ER-2B22N			
Plunger	वम	D4ER-2C21N	D4ER-2C22N			
Sealed roller plunger	þ	D4ER-2D21N	D4ER-2D22N			
Sealed crossroller plunger		D4ER-2E21N	D4ER-2E22N			
Roller lever	- P	D4ER-2G21N	D4ER-2G22N			
Long roller plunger	llice	D4ER-2L21N	D4ER-2L22N			

28

	Туре	Pre-wired Connector type				
		Standa	rd load			
		Right-hand	Left-hand			
Actuator		Model	Model			
Roller plunger	e H H	D4ER-1A21N-DTK1EJ	D4ER-1A22N-DTK1EJ			
Crossroller plunger	白白	D4ER-1B21N-DTK1EJ	D4ER-1B22N-DTK1EJ			
Plunger	盘	D4ER-1C21N-DTK1EJ	D4ER-1C22N-DTK1EJ			
Sealed roller plunger	<u> </u>	D4ER-1D21N-DTK1EJ	D4ER-1D22N-DTK1EJ			
Sealed crossroller plunger	<u>A</u>	D4ER-1E21N-DTK1EJ	D4ER-1E22N-DTK1EJ			
Roller lever	<u></u>	D4ER-1G21N-DTK1EJ	D4ER-1G22N-DTK1EJ			
Long roller plunger		D4ER-1L21N-DTK1EJ	D4ER-1L22N-DTK1EJ			

	Туре	Pre-wired Connector type				
		Micro	load			
		Right-hand	Left-hand			
Actuator		Model	Model			
Roller plunger	end	D4ER-2A21N-DTK1EJ	D4ER-2A22N-DTK1EJ			
Crossroller plunger	þæ	D4ER-2B21N-DTK1EJ	D4ER-2B22N-DTK1EJ			
Plunger	山	D4ER-2C21N-DTK1EJ	D4ER-2C22N-DTK1EJ			
Sealed roller plunger		D4ER-2D21N-DTK1EJ	D4ER-2D22N-DTK1EJ			
Sealed crossroller plunger	<u>A</u>	D4ER-2E21N-DTK1EJ	D4ER-2E22N-DTK1EJ			
Roller lever	<u></u>	D4ER-2G21N-DTK1EJ	D4ER-2G22N-DTK1EJ			
Long roller plunger		D4ER-2L21N-DTK1EJ	D4ER-2L22N-DTK1EJ			

Connector Sockets

For models with connectors, select one of the specified Connector Sockets from the following table.

Applicable Limit Switches	Current type	Appearance	No. of conductors	Cable length	Socket
		Straight, Smartclick Oil-resistant		2 m	XS5FR-D423-D80-RB1
D4ER-□□21N-DTK1EJ D4ER-□□22N-DTK1EJ	DC	Connectors	4	5 m	XS5FR-D423-G80-RB1
				10 m	XS5FR-D423-J80-RB1

Note: Refer to the XS5 R on page 53 for connector details and for information on cables with connectors on both ends.

29

Specifications

Approved Standards

Agency	Standard	File No.	Approved models
TÜV Rheinland	EN 60947-5-1	R9551015, J9951016	
CCC	-	-	Ask your OMRON representative for information on approved models.
UL	-	-	

Ratings

		Standard load								load		
Rated	Non-inductive load (A)			Non-inductive load (A) Inductive load (A)					Non-induct	ive load (A)		
voltage	Resistive load Lamp load		oad Inductive load Motor load		Resistive load							
	NC	NC NO NC N		NO	NC	NO	NC	NO	NC	NO		
8 VDC	1		1		-	_				_	0.	.1
14 VDC	1		-		1		-		0.1			
30 VDC	1	1 –		_		I		_	0.	.1		

Minimum	Standard load	Micro load
applicable load	160 mA at 5 VDC	1 mA at 5 VDC

Approved Standard Ratings

TÜV (EN 60947-5-1)

D4ER-1 G 21 N

ТПШ

	Model		Applicable category	Thermal current
I	- 11	=	and ratings	(Ithe)
1		21/22	DC-12 1 A/30 VDC	1 A
2		21/22	DC-12 0.1 A/30 VDC	0.1 A

Note: 1. : Actuator variation of item II

2. DC-12 1 A/30 VDC means as follows: Applicable category: DC-12

Rated operating current (Ie): 1 A

Rated operating voltage (Ue): 30 VDC

Characteristics (Standard Load Model and Micro Load Model)

Degree of protection		IP67 (IEC 60529) and IP67G (JIS C 0920 Annex 1) *1 Passed OMRON's Oil-resistant Component Evaluation Standards *2 (Cutting oil type: specified in JIS K 2241:2000; Temperature: 35°C max.)			
	Mechanical	4,000,000 operations min.			
Durability	Electrical	500,000 operations min. (Standard load: 1 A at 30 VDC, resistive load/Micro load: 0.1 A at 30 VDC, resistive load) 4,000,000 operations min. (10 mA at 24 VDC, resistive load)			
Operating sp	beed	0.1 mm/sec to 0.5 m/sec			
Operating fro	equency	Mechanical: 120 operations/min Electrical: 30 operations/min			
Insulation re	sistance	100 MΩ min. (at 500 VDC) *3			
Contact resi	stance	Standard load : D4ER-1 Image: N max. (initial value for the built-in switch whentested alone) Micro load : D4ER-2 Image: N max. (initial value for the built-in switch whentested alone)			
Dielectric	Between terminals of same polarity	1,000 VAC, 50/60 Hz for 1 min			
strength Between each terminal and noncurrent-carrying metal part		1,500 VAC, 50/60 Hz for 1 min/Uimp at 2.5 kV (EN 60947-5-1)			
Rated insula	tion voltage (Ui)	250 V			
Pollution de	gree (operating environment)	3 (EN 60947-5-1)			
Short-circuit	protective device (SCPD)	10 A fuse (type gG or type gI, IEC 60269 approved)			
Conditional	short-circuit current	100 A (EN 60947-5-1)			
Conventiona	I enclosed thermal current (Ithe)	5 A (EN 60947-5-1)			
Protection a	gainst electric shock	Class II (grounding not required with double insulation)			
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude			
Shock	Destruction	1,000 m/s ² max. (IEC 68-2-27)			
resistance Malfunction		300 m/s ² max. (IEC 68-2-27)			
Ambient operat	ing temperature/Ambient storage temperature	5°C to 70°C (with no icing or condensation)			
Ambient ope	erating humidity	35% to 95%RH (with no condensation)			
Weight		(in case of roller plunger) Cable type (2 m): Approx. 140 g Pre-wired Connector type: Approx. 103 g			

Note: 1. The following values are initial values.

2. The following ratings may vary depending on the model. Contact your OMRON representative for further details.

*1. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).


The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil. *2. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

The Pre-wired Connector type meets the degree of protection when it is correctly connected with an XS5 R Oil-resistant Connector. The degree of protection is not satisfied with the part where there is no XS5FR Oil-resistant Connector connected and cable wires are uncovered. And as for the Cable type, the degree of protection is not satisfied with the part where cable wires are uncovered. *3. This value represents the condition when the Switch is shipped from the factory.

- NC Inrush 10 A max. current NO 10 A max.
- Note: 1. The above current ratings are for a standard current.
 - 2. Inductive loads have a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).
 - 3. Lamp load has an inrush current of 10 times the steady-state current.
 - 4. Motor load has an inrush current of 6 times the steady-state current.

Structure and Nomenclature

Structure



Degree of Protection

The D4ER- \Box N uses rubber seals to provide a protective structure for the charged parts to achieve an IP rating of IP67G^{*} (JIS C 0920). The charged parts in the switching section are sealed with the two rubber seals shown in figure 1. The charged parts in the terminal section are sealed with the two rubber seals shown in figure 2.

Material combining HNBR and fluororubber with excellent resistance to oil is used for the rubber seals.





Figure 1. Switching Section Protective Structure

Figure 2. Terminal Section Protective Structure

* The various parts of IP67G have the following meanings: IP6 indicates that dust will not enter the interior, IP 7 indicates protection again submersion in water, and IP G indicates resistance to oil.

Contact Form

Cable type



Pre-wired Connector type




* The position of the positioning piece is not always the same. If using an L-shaped connector causes problems in application, use a straight connector.

31

Dimensions and Operating Characteristics

Cable type




Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

D4ER-⊡N

Oil-resistant Proximity Sensors


Oil-resistant Limit Switches

Oil-resistant Fiber Unit




Note: Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

Pre-wired Connector type




Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

2. The location of the positioning piece on the connector is not always the same.



Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

2. The location of the positioning piece on the connector is not always the same.



Note: 1. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.

2. The location of the positioning piece on the connector is not always the same.

Safety Precautions

Refer to Safety Precautions for All Limit Switches on your OMRON website for general precautions.

Warning Indications

Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.

Precautions for Safe Use

• Protective structure

Do not use the product with degrade protective structure such as swelling and crack in housing and/or sealing components. Otherwise cutting oil or other substance may enter the product, resulting in a risk of corruption or burning.

- Do not disassemble or remodel the switch in any case, or the switch will not operate normally.
- The durability of the Switch greatly varies with switching conditions. Before using the Switch, be sure to test the Switch under actual conditions. Make sure that the number of switching operations is within the permissible range.
- If an actuator is kept pressed for an extended period of time, the actuator will deteriorate quickly and faulty reset of the Switch may occur. Check the Switch periodically and replace it when necessary.

Precautions for Correct Use

- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ration recommended by its manufacturer
 - Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.

The D4ER-____N-DTK1EJ can be used in conditions of cutting oil use described in the specifications.

The oil resistance may not be ensured when the products are not mated to $XS5\Box R$ Connectors, so use the products correctly.

- When mating the products to XS2 or other M12 Connectors, tighten the lock to a torque of 0.39 to 0.49 N·m.
- To protect the Switch from damage due to short-circuits, be sure to connect a quick-response fuse with a breaking current 1.5 to 2 times larger than the rated current in series with the Switch.
- Do not connect lead wires directly to the terminals. Use crimp terminals and attached them securely.
- The switch is intended for indoor use only.

Do not use the switch outdoor, or the switch will malfunction.

- Do not use the switch in the atmosphere of hazardous gases (H2S, SO₂, NH₃, HNO₃, Cl₂, etc.) or high temperature and humidity, or it will cause the imperfect closing of the contacts or the breakage thereof stemming from corrosion.
- When storing the Switch, do not subject it to hazardous gases (H2S, SO2, NH3, HNO3, Cl2, etc.), dust, dirt, high temperature, or high humidity.
- Do not use the switch under any of the conditions mentioned below.
 - Locations subject to severe temperature changes
 - Locations where the interior of a protective door may come into direct contact with cutting chips, metal filings, or chemicals
 - Locations subject to high humidity or condensation
 - Locations subject to severe vibration
 Locations subject to detergents, thinners, or other solvents
 - Locations subject to detergents, thinners, or other solvents
 Locations where flammable or explosive gases are present
- If the Switch is not turned ON and OFF for an extended period of time, contact oxidation may reduce the contact reliability. Continuity failure may result in an accident.
- Do not drop the Switch. Doing so may prevent it from functioning to its full capacity.
- Do not place an excessive load on the Switch.
- Be sure to keep the load current less than the rated value.
- Do not supply electric power when wiring. Otherwise electric shock may result.
- Setting the stroke close to the operating position (OP) or releasing position (RP) will cause unstable contact. If the full stroke is set to the total travel position (TTP), the actuator or Switch may be damaged due to the inertia of the dog. Therefore, adjust the stroke with the mounting panel or the dog.
- The body of the Switch is protected from the ingress of dirt, water, and other foreign matter, but the head is not protected from water or fine foreign matter. You must take measures to prevent water and fine foreign matter from entering the head. Not providing sufficient protection may result in accelerated wear or damage.
- Perform inspections and tests to confirm the operating characteristics, insulation resistance, dielectric strength, and contact resistance of the Switch if it is left in a location that does not meet the storage conditions, if it is subjected to condensation, if it is dropped, or if it is stored for more than one year.
- The user of the system must not attempt to perform maintenance and repairs. Contact the manufacturer of the system concerning maintenance and repairs.

D4ER-□N

- Make sure that the dog does not strike the actuator of the Switch at an angle. If a load is placed on the actuator at an angle, the actuator may be deformed or damaged or the rotary shaft may be deformed or damaged.
- Do not normally leave the Switch in oil or water. Water or oil may enter the Switch.
- Perform scheduled, periodic inspections.

Handling

• Be sure to connect a fuse with a breaking current 1.5 to 2 times the rated current to the Limit Switch in series in order to protect the Limit Switch from damage due to short-circuiting. When using the Limit Switch under the EN ratings, use a gl or gG 10-A fuse that conforms to IEC 60269.

Mounting

• Use M4 screws to mount the Switch. Use washers or other means to prevent the screws from becoming loose and tighten the screws to a torque of 1.18 to 1.37 N·m.

Mounting Holes



- When mounting the panel mount-type Switch with screws on a side surface, remove the hexagonal nuts from the actuator.
- When mounting the panel mount type on a panel, tighten the hexagonal nuts of the actuator to a torque less than 7.85 N·m. The two nuts can be attached at the top or bottom and from either side.





- Operating method, shape of cam or dog, operating frequency, and the overtravel (OT) have significant effect on the service life and precision of the Limit Switch. Make sure that the shape of the cam or dog is smooth enough.
- If the Limit Switch is used in a normally open condition (NO), sufficiently press the actuator to 70% to 100% of the value specified for the OT.
- Do not change the operating position by remodeling the actuator.
- Do not bend the cable to a radius that is smaller than 25 mm.

Oil-resistant Fiber Units E32-T11NF

Fiber Units for Reliable, Stable Operation in Cutting Oil Environments

- · Fluororesin cable and glass lens that withstand cutting oil.
- · Mechanical seal structure that eliminates gaps works together with resin filling to block ingress of cutting oil.
- Maintains high-power output for stable workpiece detection even when covered in cutting oil.
- IP68G * degree of protection (JIS C 0920 Annex 1).
- Highly-requested M4-mounting models join the series. With retaining the oil resistance performance, they can be used in locations with limited space.

* The IP68G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

Fiber core

The IP68 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.

Features

Fluororesin Outer Cable Sheath



No ingress of

into fiber core

cutting oil

Cutting

Fiber covering

(fluororesin)


oil

The fluororesin that covers the entire surface of the cable sheath (fiber covering) prevents the penetration of cutting oil.



Mechanical Seal Structure

An aluminum ring bushing is compressed and deformed by a set screw to seal the structure by pressing against the fluororesin part of the fiber core. This prevents the ingress of cutting oil from the joined surfaces.



Structure Around Sensing Surface Also **Resists Cutting Oil and Cutting Chips**

Shape that prevents accumulation of Spherical glass oil drops and cutting chips

High-power Output Even When Covered in Cutting Oil

lens resists


oils adhered




Applications

Fiber coré

Detection of Drill Breakage



Detection of Cutting Workpieces





Oil-resistant Fiber Unit

E32-T11NF

Ratings and Specifications

Specifications

Through-beam Fiber Units

			Dandina	Se	ensing dis	stance (mm)		Optical axis	
Туре	Sensing	Appearance (mm)	radius	Bending E3X-H		HD E3NX-F		diameter (minimum	Model
Type	direction Appearance (mm)	of cable	GIGA HS	Other modes	GIGA HS	Other modes	sensing object)	model	
Oil-	Right-angle	19.1 M8 *1 IP68G	Flexible, R1	4,000 *2	*2 ST: 4,000 SHS: 2,200	4,000 *2 4,000 *2	*2 ST: 4,000 SHS: 2,200	4 dia. (0.1 dia./ 0.03 dia.)	E32-T11NF 2M
resistant	Right-angle	16 M4 *1 IPSSin	Flexible, R1	2,200	ST: 1,100 SHS: 270	3,300	ST: 1,600 SHS: 270	2 dia. (0.1 dia./ 0.03 dia.)	E32-T11NFS 2M

*1. The IP68G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP68 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil. Passed OMRON's Oil-resistant Component Evaluation Standards (OMRON's own durability evaluation standards) (Cutting oil type: specified in JIS K 2241:2000; Temperature: 35 °C max.)

*2. The optical fiber is 2 m long on each side, so the sensing distance is 4,000 mm.

Note: 1. The following mode names and response times apply to the modes given in the Sensing distance column.

[E3X-HD] GIGA: Giga-power mode (16 ms), HS: High-speed mode (250 µs), ST: Standard mode (1 ms), and SHS: Super-high-speed mode (NPN output: 50 µs, PNP output: 55 µs)

[E3NX-FA] GIGA: Giga-power mode (16 ms), HS: High-speed mode (250 µs), ST: Standard mode (1 ms), and SHS: Super-high-speed mode (30 µs) 2. The values for the minimum sensing object are reference values that indicate values obtained in standard mode with the sensing distance and sensitivity set to the optimum values. The first value is for the E3X-HD and the second value is for the E3NX-FA.

Installation Information


Installation			Cable					Weight		
Models	Ambient temperature	Tightening torque	Mounting hole	Bending radius	Unbendable length	Tensile strength	Sheath material	Core material	Emitter/receiver differentiation	(packed state) (g)
E32-T11NF 2M	–25 to 70 °C	12 N·m	8.5 ^{+0.5} dia.	R1	0	29.4 N	Fluororesin	Plastic	None	80
E32-T11NFS 2M	–25 to 70 °C	0.78 N·m	4.2 ^{+0.5} dia.	R1	0	29.4 N	Fluororesin	Plastic	None	70

Dimensions

(Unit: mm) Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.

E32-T11NF 2M (Free Cutting)

E32-T11NFS 2M (Free Cutting)



Combined Fiber Amplifier Units

Item	Series	E3X-HD Series	E3NX-FA Series
Appearance			State Stat
Output		1 output	1 or 2 outputs (depending on the model)
External input		Not supported	Supported or not supported (depending on the model)
Response time *		50 μs (55 μs)/250 μs/1 ms/16 ms (Default: 250 μs)	30 μs (32 μs)/250 μs/1 ms/16 ms (Default: 250 μs)

Note: The Fiber Amplifier Units are not oil resistant.

These are the response times for super-high-speed mode (SHS), high-speed mode (HS), standard mode (ST), and GIGA-power mode (GIGA). The value in parentheses for the super-high-speed mode is for a model with a PNP output.

40

Oil-resistant Photoelectric Sensors E3ZR-C

Photoelectric Sensors That Withstand Cutting Oil to Reduce Failures Caused by Ingress of Cutting Oil

- Fluororesin cables that strongly resist cutting oil.
- · Sealing methods that prevent gaps at joints block the ingress of cutting oil.
- IP67G * degree of protection (JIS C 0920 Annex 1).

Refer to Safety Precautions on page 47.

*The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.



For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Method for Complete

Sealing without Adhesive

Features

Â

Fluororesin Outer Cable Sheath




Fluororesin, which provides superior resistance to corrosion, is used for the outer cable sheath to suppress cable swelling and deterioration and prevent the ingress of cutting oil into the PCB inside the Sensor.


New Rubber Material **Combining HNBR and Fluororubber Provides** Superior Resistance to Oil

This new rubber material has been used in all vital seals to prevent the ingress of cutting oils.


Important Sealing Sections



Joints between Metal Parts Gaps are sealed by fusing the metal case and cover with a laser beam. Secured and sealed with laser welding Cutting oil



Joints between Metal and Non-metal Parts Securing the metal case and lens cover with laser welding makes the compressed O-ring seal the gap.



Lens material




Applications

Engine Block Passage Detection



Metal Workpiece Detection





Oil-resistant Connectors

E3ZR-C **Ordering Information**

Sensors [Refer to Dimensions on page 49.]

Sensing		Connection	Se	nsing	Oper-					
method		method	distanco		ation mode	NPN output	PNP output			
		Pre-wired (2 m)				E3ZR-CT61L 2M	E3ZR-CT81L 2M			
		*4			Light	Emitter E3ZR-CT61L-L 2M Receiver E3ZR-CT61L-D 2M	Emitter E3ZR-CT81L-L 2M Receiver E3ZR-CT81L-D 2M			
		M12 Smartclick pre-wired			ON	E3ZR-CT61L-M1TJ 0.3M	E3ZR-CT81L-M1TJ 0.3M			
Through-beam (Emitter +		connector (0.3 m)				Emitter E3ZR-CT61L-L-M1TJ 0.3M Receiver E3ZR-CT61L-D-M1TJ 0.3M	Emitter E3ZR-CT81L-L-M1TJ 0.3M Receiver E3ZR-CT81L-D-M1TJ 0.3M			
Receiver) *1		Pre-wired (2 m)		<mark>30 n م</mark>	1	E3ZR-CT61D 2M	E3ZR-CT81D 2M			
·		*4			Dark	Emitter E3ZR-CT61D-L 2M Receiver E3ZR-CT61D-D 2M	Emitter E3ZR-CT81D-L 2M Receiver E3ZR-CT81D-D 2M			
		M12 Smartclick pre-wired			ON	E3ZR-CT61D-M1TJ 0.3M	E3ZR-CT81D-M1TJ 0.3M			
		connector (0.3 m)				Emitter E3ZR-CT61D-L-M1TJ 0.3M Receiver E3ZR-CT61D-D-M1TJ 0.3M	Emitter E3ZR-CT81D-L-M1TJ 0.3M Receiver E3ZR-CT81D-D-M1TJ 0.3M			
		Pre-wired (2 m) *4			Light	E3ZR-CR61L 2M	E3ZR-CR81L 2M			
Retro-reflective	1	M12 Smartclick pre-wired connector (0.3 m)		2.5 m * (100 mm		E3ZR-CR61L-M1TJ 0.3M	E3ZR-CR81L-M1TJ 0.3M			
with MSR function	*2	Pre-wired (2 m) *4	(When using Oil-resistant	g È39-R1R	, Dark	E3ZR-CR61D 2M	E3ZR-CR81D 2M			
		M12 Smartclick pre-wired connector (0.3 m)			ON	E3ZR-CR61D-M1TJ 0.3M	E3ZR-CR81D-M1TJ 0.3M			
		Pre-wired (2 m) *4			Light	E3ZR-CD61L 2M	E3ZR-CD81L 2M			
Diffuse-		M12 Smartclick pre-wired connector (0.3 m)	- 0.5 m -		ON	E3ZR-CD61L-M1TJ 0.3M	E3ZR-CD81L-M1TJ 0.3M			
reflective		Pre-wired (2 m) *4		- U 0.5 m	U.5 m	n 	0.5 m		Dark	E3ZR-CD61D 2M
		M12 Smartclick pre-wired connector (0.3 m)			ON	E3ZR-CD61D-M1TJ 0.3M	E3ZR-CD81D-M1TJ 0.3M			

*1. Through-beam Sensors are sold in sets that include both the Emitter and Receiver. An order for the Emitter or Receiver alone cannot be accepted.

*2. The Reflector is sold separately. Select the Reflector model most suited to the application.

*3. Values in parentheses indicate the minimum required distance between the Sensor and Reflector. *4. Models with 5-m cable length are also available with "5M" suffix. (Example: E3ZR-CT61L 5M)

Accessories (Sold Separately)

Sensor I/O Connectors (M12, Sockets on One Cable End)

(Models for Pre-wired Connectors) A Sensor I/O Connector is not provided with the Sensor. It must be ordered separately as required.

Appearance	Cable diameter (mm)	Cable length	Sensor I/O Connector model number	Applicable Photoelectric Sensor model number
Straight, Smartclick Oil-resistant		2 m	XS5FR-D423-D80-RB1	
Connectors	4 dia.	5 m	XS5FR-D423-G80-RB1	E3ZR-C□□1□-M1TJ
		10 m	XS5FR-D423-J80-RB1	

Note: Refer to the XS5_R on page 53 for connector details and for information on cables with connectors on both ends.

Slit (A Slit is not provided with Through-beam Sensors) Order a Slit separately if required.

Slit width	Sensing distance (Reference value) E3ZR-CT□	Model	Contents
1-mm dia.	0.2 m	E39-S77A	One set (contains Slits for both the
2-mm dia.	0.8 m	E39-S77B	Emitter and Receiver)

Appearance	Model (material)	Quantity	Remarks		
	E39-L153 (SUS304)	1			
	E39-L104 (SUS304)	1	Mounting Brackets		
	E39-L196 (SUS304)	1			
	E39-L197 (SUS304)	1			
	E39-L98 (SUS304)	1	Metal Protective Cover Bracket		

Mounting Brackets A Mounting Bracket is not provided with the Sensor. Order a Mounting Bracket separately if required.

Note:1. When using Through-beam models, order one bracket for the Receiver and one for the Emitter. 2. Refer to *Mounting Brackets on E39-L/E39-S/E39-R* on your OMRON website for details.

Reflector (A Reflector is required for each Retro-reflective Sensor: A Reflector is not provided with the Sensor. Be sure to order a Reflector.)

Name	E3ZM-CR sensing distance		Model	Quantity	Remarks
Name	Rated value	Reference value	WOUEI	Quantity	Remarks
Oil-resistant Reflector	2.5 m (100 mm) *		E39-R1R	1	 Reflectors are not provided with Retro-reflective models. The MSR function is enabled.

Note: Refer to *Reflectors on E39-L/E39-S/E39-R* on your OMRON website for details. *Values in parentheses indicate the minimum required distance between the Sensor and Reflector.

E3ZR-C **Ratings and Specifications**

Sensors

	Sensing method	Through-beam	Retro-reflective with MSR function	Diffuse-reflective			
Model	NPN output	E3ZR-CT61 (-M1TJ)	E3ZR-CR61 (-M1TJ)	E3ZR-CD61 (-M1TJ)			
Item	PNP output	E3ZR-CT81 (-M1TJ)	E3ZR-CR81 (-M1TJ)	E3ZR-CD81 (-M1TJ)			
Sensing distance		30 m	2.5 m [100 mm] *1 (Using E39-R1R)	0.5 m (White paper 300 × 300 mm)			
Standard se	ensing object	Opaque: 12-mm dia. min.	Opaque: 75-mm dia. min.				
Differential (travel	-	-	20% of sensing distance max.			
Directional a	angle	Emitter, Receiver: 3° to 15° (Distance between emitter and receiver. Rated sensing distance)	Sensor: 2° to 10° Reflector: 30° (Distance to Reflector. Rated sensing distance)				
Light source	e (wavelength)	Red LED (624 nm)	Red LED (660 nm)	Red LED (624 nm)			
Power supp	ly voltage	12 to 24 VDC ±10%, ripple (p-p) 106	% max.				
Current con	sumption	35 mA max. (Emitter 15 mA max., Receiver 20 mA max.)	30 mA max.				
Control out	out	Open-collector output (NPN/PNP ou	/DC max., Output current: 100 mA m itput depending on model)	ax. (Residual voltage: 2 V max.)			
Protection o	ircuits	Reversed power supply polarity protection, output short-circuit protection, and reversed output polarity protection	Reversed power supply polarity prote reversed output polarity protection, function (with up to two Units)				
Response ti	me	Operate or reset: 1 ms max.					
Sensitivity a	adjustment	None					
Ambient illumi	nation (Receiver side)	Incandescent lamp: 5,000 lx max., \$	Sunlight: 10,000 lx max.				
Ambient ten	nperature range	Operating: -25 to 55°C, Storage: -4	0 to 70°C (with no icing or condensa	tion)			
Ambient hu	midity range	Operating: 35% to 85%, Storage: 35	5% to 95% (with no condensation)				
Insulation re	esistance	20 MΩ min. at 500 VDC					
Dielectric st	rength	1,000 VAC, 50/60 Hz for 1 min					
Vibration re	sistance	Destruction: 10 to 55 Hz, 1.5-mm do	puble amplitude for 2 hours each in X	, Y, and Z directions			
Shock resis	tance	Destruction: 1,000 m/s ² 3 times eac	h in X, Y, and Z directions				
Degree of p	rotection	IP67 (IEC 60529) and IP67G *2 (JIS Passed OMRON's Oil-resistant Con (Cutting oil type: specified in JIS K 2					
Connection	method	Pre-wired (standard length: 2 m), -M	11TJ: Pre-wired connector (standard	length: 0.3 m)			
ndicators		Operation indicator (orange) and sta	ability indicator (green) (The Emitter h	nas only a power indicator (green).)			
Weight	Pre-wired models	Approx. 200 g	Approx. 100 g				
packed state)	Pre-wired connector	Approx. 140 g Approx. 70 g					
Housing ma	terial	SUS316L					
Cable mater	ial	Fluororesin					
Lens materi	al	Methacrylate resin (Oil-resistant hig	h molecular weight type)				
Indicator ma	aterial	Polyetherimide resin					
Accessories	6	Instruction manual					

*1. Values in parentheses indicate the minimum required distance between the Sensor and Reflector.
*2. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.
*3. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. The Pre-wired Connector Model meets the degree of protection when it is correctly connected with an XS5 CR Oil-resistant Connector. The degree of protection is not satisfied with the part where there is no XS5FR Oil-resistant Connector connected and cable wires are uncovered. And as for the Pre-wired Models, the degree of protection is not satisfied with the part where cable wires are uncovered.

Accessories (Sold Separately)

Reflector

Na	ne Oil-resistant Reflector
Item Mod	E39-R1R
Directional angle	30° min.
Ambient temperature range Operating: -25 to 55°C, Storage: -40 to 70°C (with no icing or condensation)	
Ambient humidity range Operating: 35% to 85%, Storage: 35% to 95% (with no condensation)	
Degree of protection	IP67 (IEC 60529) and IP67G *1 (JIS C 0920 Annex 1) Passed OMRON's Oil-resistant Component Evaluation Standards *2 (Cutting oil type: specified in JIS K 2241:2000, Temperature: 35°C max.)


*1. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.


*2. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards.

Engineering Data (Reference Value)

Parallel Operating Range Through-beam Models

E3ZR-CT□1□






Through-beam Models Retro-reflective Models


(A Slit is mounted to the Emitter and Receiver.)

E3ZR-CT□1□ and Slit


Retro-reflective Models E3ZR-CR□1□




Operating Range Diffuse-reflective Models E3ZR-CD□1□



Excess Gain vs. Distance Through-beam Models E3ZR-CT□1□



Sensing Object Size vs. Distance Diffuse-reflective Models E3ZR-CD□1□



Retro-reflective Models E3ZR-CR[]1]


6

Distance (m)

0.3

0.1

Diffuse-reflective Models E3ZR-CD□1□



Oil-resistant Proximity Sensors

E3ZR-C I/O Circuit Diagrams


NPN Output

Model	Operation mode	Timing charts	Output circuit		
E3ZR-CT61L E3ZR-CR61L E3ZR-CD61L	Light ON	Incident light No incident light Operation indicator ON (orange) OFF Output transistor ON OFF Load (e.g., relay) Operate Reset (Between brown (1) and black (4) leads)	Through-beam Receivers, Retro-reflective Models, Diffuse-reflective Models Operation Indicator U(creace)		
E3ZR-CT61D E3ZR-CR61D E3ZR-CD61D	Dark ON	Incident light Operation indicator (orange) Output transistor Load (e.g., relay) Oterate (Between brown (1) and black (4) leads)	(orange) (green) (Control 100 mA (Relay) Photo- electric Sensor main circuit 0 zb Blue 0 V		

PNP Output

Model	Operation mode	Timing charts	Output circuit
E3ZR-CT81L E3ZR-CR81L E3ZR-CD81L	Light ON	Incident light No incident light Operation indicator ON (orange) OFF Output transistor OFF Load (e.g., relay) Operate (Between blue (3) and black (4) leads)	Through-beam Receivers, Retro-reflective Models, Diffuse-reflective Models Operation
E3ZR-CT81D E3ZR-CR81D E3ZR-CD81D	Dark ON	Incident light No incident light Operation indicator (orange) Otput transistor Load (e.g., relay) (Between blue (3) and black (4) leads)	(orange) (green) Photo- electric Sensor main circuit Black Black (Control Blue Black Blue Blue Blue Black O O V

Emitter (Either NPN or PNP Output)




Connector Pin Arrangement

M12 Pre-wired Connector M12 Connector Pin Arrangement




Plugs (Sensor I/O Connectors)

M12 Smartclick Connector



Nomenclature



OMRON

Safety Precautions

Be sure to read the precautions for all models in the website at: http://www.ia.omron.com/.

Warning Indications

	Warning level Indicates a potentially hazardous situation which, if not avoided, will result in minor or moderate injury, or may result in serious injury or death. Additionally there may be significant property damage.
	Caution level Indicates a potentially hazardous situation which, if not avoided, may result in minor or moderate injury or in property damage.
Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.


Meaning of Product Safety Symbols



General prohibition

Indicates the instructions of unspecified prohibited action.

Caution, fire Indicates the possibility of fires under specific conditions.



Indicates the possibility of explosion under specific conditions.

General caution Indicates unspecified general alert.

Caution, high temperature Indicates the possibility of injuries by high temperature under specific conditions.

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.



Risk of explosion.

Do not use it exceeding the rated voltage. There is a possibility of failure and fire.

Do not connect the product to an AC power supply.



Do not jet the high pressure water concentrating on one place when washing the product, because it might damage of parts and deteriorate the degree of protection.

Do not use this product under ambient conditions that exceed the ratings. High-temperature environments may result in burn injury.



Precautions for Safe Use

The following precautions must be observed to ensure safe operation. (1) Operating Environment

- 1. Do not use the product in an environment where flammable or explosive gas is present.
- 2. Do not use the product in environments subject to cleaners and disinfectants. They may reduce the degree of protection.
- (2) Output short-circuit

Please do not connect a output short-circuit. Please do not throw the current that exceeds ratings into the control output. When an excessive electric current was thrown, the output short-circuit protection function installed, but it'll be the cause which breaks down.

(3) Low-temperature Environments

Do not touch the metal surface with your bare hands when the temperature is low.


Touching the surface may result in a cold burn.

- (4) Modifications
- Do not attempt to disassemble, repair, or modify the product.
- (5) Protective structure Do not use the product with degrade protective structure such as swelling and crack in housing and/or sealing components. Otherwise cutting oil or other substance may enter the product, resulting in a risk of corruption or burning.

Precautions for Correct Use

- (1) Do not install the product in the following locations.
 - 1. In the place exposed to the direct sunlight.
 - 2. In the place where humidity is high and condensation may occur.
 - 3. In the place where corrosive gas exists.
 - **4.** In the place where vibration or shock is directly transmitted to the product.
- (2) Connection and Mounting
 - Be sure that before making supply the supply voltage is less than the maximum rated supply voltage. (26.4V DC)
 - If the Sensor wiring is placed in the same conduits or ducts as high-voltage or high-power lines, inductive noise may cause malfunction or damage. Wire the cables separately or use a shielded cable.
 - For extending cable, use a cable $0.3\,mm^2\,min.\,and\,100\,m\,max.$ in length.
 - Do not pull the cable strongly.
 - Excessive force (hitting by hammer, etc.) should not be put on the Sensor because it may damage its water-resistance and oil-resistance characteristic.
 - Mount the Sensor either using the bracket (sold separately) or on a flat surface.
 - Use M3 screws to mount the Sensor.
 - Use tightening torque 0.5 N·m max.
 - Be sure to turn OFF the power supply before inserting or removing the connector.

Mounting Diagram



- (3) Connecting Connectors
 - Be sure to hold the connector cover when inserting or removing the connector.

Be sure to tighten the connector lock by hand; do not use pliers or other tools.

If the tightening is insufficient, the degree of protection will not be maintained and the Sensor may become loose due to vibration.

- (4) Pre-wired Connector Model
 - The E3ZR-C can be used in conditions of cutting oil use described in the specifications.

The oil resistance may not be ensured when the products are not mated to XS5 Connectors, so use the products correctly.

- When mating the products to XS2 or other M12 Connectors, tighten the lock to a torque of 0.39 to 0.49 N m.
- (5) Oil resistance

The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.

- Usage under the cutting oil condition designated by the specification
- Usage under the cutting oil dilution ratio recommended by its manufacturer
- Usage in oil or water is prohibited
- Impact on the product life may differ depending on the oil you use.

Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.

(6) Water resistance This product fit in with IP67/67G, but this product isn't perfect waterproofing.

Avoid using the product in the water or locations subject to water drops.


- (7) Power supply When using a commercially available switching regulator, be sure to ground the FG (Frame Ground) terminals.
- (8) Power supply reset time The Sensor will begin sensing no later than 100 ms after the power is turned on.
 If the load and the Sensor is connected to different power supply,
 - the Sensor must be always turned on first.
- (9) Turning off the power supply When turning off the power, output pulse may be generated. We recommend turning off the power supply of the load or load line first.
- (10) Overcurrent External overcurrent protection of 1 A for AWG25 wire must be provided for cable protection.
- (11) Output short-circuit protection
 If the output short-circuit occurs, the output will turn off. Check the wiring before turning ON the power supply again.
 The output short-circuit protection will operate when the current flow reaches 1.8 times the rated load current.
 When using a capacitive load, use an inrush current of 1.8 times the rated load current or lower.
- (12) Cleaning
 - Never use thinner or other solvents. Otherwise, the Sensor surface may be dissolved.
- (13) Disposing
 - Please process this product as industrial waste.

E3ZR-C

Dimensions

(Unit: mm) Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.


Sensors



*Models numbers for Through-beam Sensors (E3ZR-CT□1□(-M1TJ)) are for sets that include both the Emitter and Receiver.

The model number of the Emitter is expressed by adding "-L" to the set model number (example: E3ZR-CT61L-L 2M), the model number of the Receiver, by adding "-D" (example: E3ZR-CT61L-D 2M.) Refer to Ordering Information to confirm model numbers for Emitters and Receivers.

Cable bend radius



OMRON

Oil-resistant Fiber Unit

Oil-resistant Photoelectric Sensors

Oil-resistant Connectors

Accessories (Sold Separately)










Reflective surface: Methacrylate resin (Oil-resistant high molecular weight type) Rear surface: Aluminium Oil-resistant M3 special screws: Stainless steel (SUS302)

Slits E39-S77A E39-S77B



Model


E39-S77A

E39-S77B

Α


1 dia.


2 dia.



11.55

Photoelectric Sensor Accessory are installed (Example of E3ZR-CT61L)






4.7


38

28.7



29

E3ZR-C



 ИЕМО

Oil-resistant Fiber Unit

Oil-resistant Photoelectric Sensors

Oil-resistant Connectors

Smartclick Oil-resistant Connectors with Improved Oil Resistance

- Fluororesin cable that withstands cutting oil.
- Structured to provide greater oil resistance.
- A newly developed lock mechanism that is compatible with round M12 connectors.
- Simply insert the Connectors, then turn them approx. 1/8 of a turn to complete the connection and block the ingress of cutting oil.
- A positive click indicates locking.

Refer to Safety Precautions on page 57.

• IP67G degree of protection (JIS C 0920 Annex 1). *



* The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards). The IP67 indicates the same level of protection as defined by the

IEC, and the G indicates that a device has resistance to oil.

For the most recent information on models that have been certified for safety standards, refer to your OMRON website.

Features

Fluororesin Cable and Structure to Increase Oil Resistance

Fluororesin, which suppresses deterioration by either water-insoluable or water-soluable cutting oils, is used for the cable sheath. Ingress from the joined surfaces is prevented by unique OMRON technology that combines forming and sealing methods with surface bonding techniques. Ingress between Connectors is prevented by the unique Smartclick mechanism.






Smartclick Structure + O-ring Unique Smartclick Structure Connector tabs O-ring Seal Cutting oil Plug Socket O-ring (New rubber material combining HNBR and fluororubber) O-ring (New rubber material combining HNBR and fluororubber)

Application

Replacement of Sensors and Wiring



Benefits of Using Connectors:

- Less wiring work in comparison with connecting discrete wires to terminal blocks
- No wiring mistakes

Additional Benefits of Using Smartclick Connectors:

- Reduced connection and disconnection time (1 click, approx. 1/8 turn)
- No need for torque management to facilitate work standardization
- The built-in O-ring is dependably compressed to block the ingress of cutting oil.

confirmation with visible marks.

Connection

53

Oil-resistant Connectors

Ratings and Specifications

Rated current	1 A	
Rated voltage	30 VDC	
Contact resistance (connector)	40 mΩ max. (20 mV max., 100 mA max.)	
Insulation resistance	1,000 MΩ min. (at 500 VDC) *1	
Dielectric strength (connector)	1,500 VAC for 1 min (leakage current: 1 mA max.)	
Degree of protection	IP67 (IEC 60529) and IP67G (JIS C 0920 Annex 1) *2 Passed OMRON's Oil-resistant Component Evaluation Standards*3 (Cutting oil type: specified in JIS K 2241:2000; Temperature: 35°C max.)	
Insertion tolerance	50 times min.	
Lock strength	Tensile: 100 N/15 s, Torsion: 1 N·m/15 s	
Cable holding strength	Tensile: 100 N/15 s	
Ambient operating temperature range/ Ambient storage temperature range -25 to +70°C		
Ambient humidity range	20% to 85%	

*1. This value represents the condition when the Connector is shipped from the factory.

*2. The IP67G is the degree of protection which is defined according to the JIS (Japanese Industrial Standards).

The IP67 indicates the same level of protection as defined by the IEC, and the G indicates that a device has resistance to oil.
*3. The Oil-resistant Component Evaluation Standards are OMRON's own durability evaluation standards. The Pre-wired Connector type meets the degree of protection when it is correctly connected with an XS5 R Oil-resistant Connector. The degree of protection is not satisfied with the part where there is no XS5FR Oil-resistant Connector connected and cable wires are uncovered.

Materials and Finishes

Contacts	Phosphor bronze/Gold plating	
Fixtures	Zinc alloy/Nickel plating	
Fixtures (Lock)	Stainless steel	
Pin block	PA resin (UL 94 HB)	
O-ring	New rubber material combining HNBR and fluororubber	
Cover	PA resin (UL 94 HB)	
Cable	Cable with fluororesin sheath: 4-mm dia. Core wire: 0.2mm ²	

Connector Pinout Diagram (from Mating Side)

ltem	No. of poles	4 poles
A-coding	Male (plug) contacts	
(For DC sensor)	Female (socket) contacts	

XS5⊡R

Smartclick

XS5FR Connector Connected to Cable, Socket on One Cable End

3: Straight, 4-mm dia.

G: 5 m

8. Connectors on One End/Both Ends

8: 1 Brown, 2 White, 3 Blue, 4 Black

6. Cable Length

0: One end

D: 2 m

Cable with fluororesin sheath

XS5FR-D423-080-RB1

Model Number Structure

Model Number Legend

$XS5F_{1}R - D_{2} + A_{3} + A_{5} + D_{6} + B_{7} + B_{8} + B_{7} +$

Use this model number legend to identify products from their model number. When ordering, use a model number from the table in Ordering Information.

5. Cable Connection Direction, Cable Outer Diameter

J: 10 m

7. Connections (Numbers inside circles are terminal numbers)


- 1. Type
 - F: Connector connected to cable, socket on one cable end
- 2. Mating Section Form
 - D: A-coding (For DC sensor)
- **3. Connector Poles**
 - 4: 4 poles
- 4. Contact Plating
 - 2: Gold plating

Ordering Information


Туре	Cable outer diameter (mm)	No. of conductors	Cable length (m)	Model	UL
			2	XS5FR-D423-D80-RB1	
Socket on One Cable End	4 dia.	4	5	XS5FR-D423-G80-RB1	
			10	XS5FR-D423-J80-RB1	

Dimensions

Straight



Wiring Diagram for 4 Cores



Smartclick is a registered trademark of OMRON Corporation.



Cable with fluororesin sheath

XS5WR-D425-081-RB1

Smartclick

Model Number Structure

Model Number Legend

$XS5\underline{W}R - \underline{D}_{\frac{1}{2}} + \underline{2}_{\frac{1}{3}} + \underline{5}_{\frac{1}{5}} - \underline{D}_{\frac{1}{6}} + \underline{8}_{\frac{1}{7}} + RB1$

Use this model number legend to identify products from their model number. When ordering, use a model number from the table in Ordering Information.

1. Type

- W: Connectors connected to cable, socket and plug on cable ends
- 2. Mating Section Form D: A-coding (For DC sensor)
- **3. Connector Poles** 4: 4 poles
- 4. Contact Plating
 - 2: Gold plating

Ordering Information

- 5. Cable Connection Direction, Cable Outer Diameter
- 5: Straight (Socket)/straight (Plug), 4-mm dia.


6. Cable Length


- D: 2 m G: 5 m J: 10 m
- 7. Connections (Numbers inside circles are terminal numbers) 8: 1 Brown, 2 White, 3 Blue, 4 Black
- 8. Connectors on One End/Both Ends 1: Both ends

Cable outer No. of Cable length (m) Model UL Type diameter (mm) conductors XS5WR-D425-D81-RB1 2 Socket and XS5WR-D425-G81-RB1 4 dia 4 5 Plug on Cable Ends 10 XS5WR-D425-J81-RB1


Dimensions

(Unit: mm)





Wiring Diagram for 4 Cores



Smartclick is a registered trademark of OMRON Corporation.

56

Safety Precautions

Warning Indications

Precautions for Safe Use	Supplementary comments on what to do or avoid doing, to use the product safely.	
Precautions for Correct Use	Supplementary comments on what to do or avoid doing, to prevent failure to operate, malfunction or undesirable effect on product performance.	

Precautions for Safe Use

Protective structure

 Do not use the product with degrade protective structure such as swelling and crack in housing and/or sealing components.
 Otherwise cutting oil or other substance may enter the product, resulting in a risk of corruption or burning.

Connector Connection and Disconnection

- When connecting or disconnecting Connectors, be sure to hold the Connectors by hand.
- Do not hold the cable when disconnecting Connectors. Check the direction of the key groove before you use the Connector.
- Do not wiring the Connector when your hands are wet. Malfunctions or device damage may occur when power is supplied to a device.
- When mating Connectors, be sure to insert the plug all the way to the back of the socket before attempting to lock the Connectors. After you lock a Connector, always confirm that it is mated properly.
- Do not use tools of any sort to mate the Connectors. Always use your hands. Pliers or other tools may damage the Connectors.
- When you replace a Connector, make sure that there is no liquid, cutting oil, or other foreign matter on the mating surfaces before you mate the Connector.

Precautions for Correct Use

- Do not use the Connectors in an atmosphere or environment that exceeds the specifications.
- Always turn OFF the power supply before wiring the Connector. Electric shock or device damage may result.
- The following conditions shall be observed if you use the product under an environment using cutting oil that may affect product's life and/or performance.
 - Usage under the cutting oil condition designated by the specification
 - Usage under the cutting oil dilution ratio recommended by its manufacturer
 - Usage in oil or water is prohibited

Impact on the product life may differ depending on the oil you use. Before using the cutting oil, make sure that it should not cause deterioration or degradation of sealing components.

• The XS5 IR can be used in conditions of cutting oil use described in the specifications.

The oil resistance may not be ensured when the products are not mated to OMRON Oil-resistant Components or XS5 R Connectors, so use the products correctly.

- Do not use a Connector in a location subject to corrosive gas, high humidity, or high temperatures. Contact failure or corrosion may damage the Connector and interfere with functionality.
- Do not pull excessively on the Connectors or cables.
- Install the Connectors and cables where they will not be stepped on to prevent the wires inside the cables from being broken and to prevent the Connectors from being damaged. If the Connectors or cables must be installed where they might be stepped on, protect them with covers.
- If a sensor or switch is not connected during installation or if the plug connector is not mated, use a XS5Z-11 or XS2Z-11 Waterproof Cover or XS2Z-14/15 Dust Cover to protect the mating surface of the Connector.

Wiring


- Do not wire the ends of the cable in any location that is subject to water, cutting oils, or other liquids.
- Wire the cable according to the wiring diagram. Before you use a sensor or limit switch, confirm that connection is possible.
- Lay the cables so that external force is not applied to the Connectors. Otherwise, the degree of protection (IP67G) may not be achieved.

Degree of Protection (IP67)

- The degree of protection of Connectors (IP67) is not for a fully watertight structure. Do not use the Connectors underwater.
- Do not step on or place any objects on the Connectors. Doing so may damage the Connectors.

Setup

- Do not install the Connectors or cables in any way that would place a load directly on the mating section or cable connections. Doing so can damage the Connectors or break the wires inside the cables.
- Do not bend the cable to a radius that is smaller than 25 mm.



XS5⊡R

Connecting

1. Connecting the XS5 R Plug and Socket

• Align the projection on the plug cover with the polarity key on the socket, then insert the plug all the way in.



• Hold the knurled socket grip, then insert the projection on the plug into the groove of the socket.



• Turn the knurled grips of the socket clockwise approximately 1/8 turn in respect to the plug. A click will indicate that the Connectors are locked. The locking condition can also be confirmed by the alignment marks on the plug and socket.



2. Connecting the XS5 R and XS2

- Align the projection on the plug cover with the polarity key on the socket, then insert the plug all the way in.
- In the same way as when connecting two XS2 Connectors, screw the knurled grip in the clockwise direction.
- When mating the products to XS2 or other M12 Connectors, tighten the lock to a torque of 0.39 to 0.49 N m.

Terms and Conditions Agreement

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions.

Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

Company names and product names in this document are the trademarks or registered trademarks of their respective companies.

The product photographs and figures that are used in this catalog may vary somewhat from the actual products.

Note: Do not use this document to operate the Unit.

OMRON Corporation Industrial Automation Company Contact : www.ia.omron.com

Kyoto, JAPAN

Regional Headquarters

OMRON EUROPE B.V. Wegalaan 67-69, 2132 JD Hoofddorp The Netherlands Tel: (31) 2356-81-300 Fax: (31) 2356-81-388

OMRON ASIA PACIFIC PTE. LTD. 438B Alexandra Road, #08-01/02 Alexandra Technopark, Singapore 119968 Tel: (65) 6835-3011 Fax: (65) 6835-3011

OMRON ELECTRONICS LLC 2895 Greenspoint Parkway, Suite 200 Hoffman Estates, IL 60169 U.S.A. Tel: (1) 847-843-7900 Fax: (1) 847-843-7787

OMRON (CHINA) CO., LTD. Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, PuDong New Area, Shanghai, 200120, China Tel: (86) 21-6023-0333 Fax: (86) 21-5037-2388 Authorized Distributor:

©OMRON Corporation 2016-2025 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice. CSM_6_4 Cat. No. Y215-E1-07 0525 (0616)