Host Link Cables (RS-232C Cables for Programmable Controller)

XW2Z-DDP-V/S-V/S-CV/T

CSM_XW2Z-___P-V_S-V_S-CV_T_DS_E_3_2

Ideal Cables for between Programmable Controllers and Host Computers







XW2Z Host Link Cable



- Host
- Personal computer
- Factory Intelligent Terminal
- Programmable Terminal

Ordering Information

SYSMAC PLC Units *1	SYSMAC Host Link Cable (RS-232C Cabl	e for Programmable Contr	ollers)	Heat
SYSMAC PLC UNITS "I	Wiring patterns	Cable length L *2	Model	Host
C20-LK201-V1 C500-LK203 C500-LK201-V1 C120-LK201-V1	D-sub, 25-pin Plug D-sub, 9-pin Socket PLC Shield Host Connector Hood FG 1 FG 1 SD 2 2 RD RD 3 SD 2	2 m	XW2Z-200P-V	
C200H-LK201 CV500-LK201 (Port 1, full-duplex mode)	RS 4 ER CS 5 SG DR 6 DR SG 7 RS : : : ER 20 9	5 m	XW2Z-500P-V	
C200HS-CPU31/33/21/23 CQM1-CPU21 CQM1-CPU41 CQM1-CPU42 CQM1-CPU42 CQM1-CPU44 CV500/1000/2000 CVM1 CV500-LK201	D-sub, 9-pin Plug PLC Connector Hood FG SD 2 RD 3 BD 2 BD 2 BD 2 	2 m	XW2Z-200S-V	Personal
(Communications port 2) C200HE-CPU42 C200HG-CPU43/63 C200HX-CPU44/64 C200HW-COM02 C200HW-COM04 C200HW-COM05 C200HW-COM06 CPM1-CIF01	RS 4 CS 5 6 7 RS 8 CS 5	5 m	XW2Z-500S-V	IBM PC/AT or compatible
CJ-series CPU Units CS-series CPU Units	D-sub, 9-pin Plug D-sub, 9-pin Socket PLC Shield Host Connector Hood FG 1 FG 1 SD 2 2 RD 3 SD	2 m	XW2Z-200S-CV	
Serial Communications Unit	RS 4 ER CS 5 SG 6 6 DR 7 RS ER 8 CS SG 9	5 m	XW2Z-500S-CV	

SYSMAC PLC Units *1	Programmable Terminal	Heat		
STSMAC PLC UNITS T	Wiring patterns	Cable length L *2	Model	
CQM1-CPU21 CQM1-CPU41 CQM1-CPU42 CQM1-CPU43 CQM1-CPU44 (Units with R5-232C port) C200HS-CPU31/33/21/23 CV500/1000/2000-CPU01 CVM1-CPU01/11 CV500-LK201 (Communications port 2) C200HE-CPU42 C200HG-CPU43/63 C200HW-CPU43/63 C200HW-COM04 C200HW-COM04 C200HW-COM04 C200HW-COM05 C200HW-COM06 CPM1-CIF01	D-sub, 9-pin Plug PLC Connector Hood FG , Shield L Connector Hood FG	2 m	XW2Z-200T	Programmable Terminal (PT):
	SD 2 SD RD 3 3 RS 4 CS 5 SG 9	5 m	XW2Z-500T	 NT20S NT600S/NT620S/ NT620C NT30/NT30C

*1. Including models whose production were discontinued.

*2. Cable length L

Ratings and Specifications

Item Type	XW2Z-□P/S/T		
Rated current	1 A		
Rated voltage	125 VAC		
Contact resistance	15 m Ω max. (at 20 mV, 100 mA max.) *1		
Insulation resistance	100 MΩ min. (at 500 VDC)		
Dielectric strength	500 VAC for 1 min (leakage current: 1 mA max.) *2		
Degree of protection	IP00		
Electrical protection class	Class 0		
Ambient operating temperature	0 to 80°C		

*1. Contact resistance of the Connector. *2. Dielectric strength of the Connector.

Materials and Finish

Item	Part name			Materials and finish	
		Housing		Fiber-glass reinforced PBT resin (UL94V-0)/milky white	
Connectors	XM3A-0921 XM3A-2521	Contacts	Mating ends	Brass/nickel base, 0.4-µm gold plating	
			Terminals	Brass/nickel base, 3-µm tin plating	
		Shell		Steel/nickel plated	
	XM2S-0911/2511 Housing			ABS resin/nickel plated	
Cable	UL2464 Interface Cable			AWG28 or the equivalent	

Read and understand this catalog.

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranties.

(a) Exclusive Warranty. Omron's exclusive warranty is that the Products will be free from defects in materials and workmanship for a period of twelve months from the date of sale by Omron (or such other period expressed in writing by Omron). Omron disclaims all other warranties, express or implied.

(b) Limitations. OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, ABOUT NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OF THE PRODUCTS. BUYER ACKNOWLEDGES THAT IT ALONE HAS DETERMINED THAT THE

PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE.

Omron further disclaims all warranties and responsibility of any type for claims or expenses based on infringement by the Products or otherwise of any intellectual property right. (c) Buyer Remedy. Omron's sole obligation hereunder shall be, at Omron's election, to (i) replace (in the form originally shipped with Buyer responsible for labor charges for removal or replacement thereof) the non-complying Product, (ii) repair the non-complying Product, or (iii) repay or credit Buyer an amount equal to the purchase price of the non-complying Product; provided that in no event shall Omron be responsible for warranty, repair, indemnity or any other claims or expenses regarding the Products unless Omron's analysis confirms that the Products were properly handled, stored, installed and maintained and not subject to contamination, abuse, misuse or inappropriate modification. Return of any Products by Buyer must be approved in writing by Omron before shipment. Omron Companies shall not be liable for the suitability or unsuitability or the results from the use of Products in combination with any electrical or electronic components, circuits, system assemblies or any other materials or substances or environments. Any advice, recommendations or information given orally or in writing, are not to be construed as an amendment or addition to the above warranty.

See http://www.omron.com/global/ or contact your Omron representative for published information.

Limitation on Liability; Etc.

OMRON COMPANIES SHALL NOT BE LIABLE FOR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR PRODUCTION OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED IN CONTRACT, WARRANTY, NEGLIGENCE OR STRICT LIABILITY.

Further, in no event shall liability of Omron Companies exceed the individual price of the Product on which liability is asserted.

Suitability of Use.

Omron Companies shall not be responsible for conformity with any standards, codes or regulations which apply to the combination of the Product in the Buyer's application or use of the Product. At Buyer's request, Omron will provide applicable third party certification documents identifying ratings and limitations of use which apply to the Product. This information by itself is not sufficient for a complete determination of the suitability of the Product in combination with the end product, machine, system, or other application or use. Buyer shall be solely responsible for determining appropriateness of the particular Product with respect to Buyer's application, product or system. Buyer shall take application responsibility in all cases.

NEVER USE THE PRODUCT FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY OR IN LARGE QUANTITIES WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT(S) IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Programmable Products.

Omron Companies shall not be responsible for the user's programming of a programmable Product, or any consequence thereof.

Performance Data.

Data presented in Omron Company websites, catalogs and other materials is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of Omron's test conditions, and the user must correlate it to actual application requirements. Actual performance is subject to the Omron's Warranty and Limitations of Liability.

Change in Specifications.

Product specifications and accessories may be changed at any time based on improvements and other reasons. It is our practice to change part numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the Product may be changed without any notice. When in doubt, special part numbers may be assigned to fix or establish key specifications for your application. Please consult with your Omron's representative at any time to confirm actual specifications of purchased Product.

Errors and Omissions. Information presented by Omron Companies has been checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical or proofreading errors or omissions.

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation Industrial Automation Company