

Original



## EU DECLARATION OF CONFORMITY

**1. Product Models/Products:**

E2K-C25M (DC 3-wire) series

**2. Name and address of the manufacturer:**

OMRON Corporation

Shiokoji Horikawa, Shimogyo-Ku, Kyoto, 600-8530 Japan

**3. This declaration of conformity is issued under the sole responsibility of the manufacturer.**

**4. Objects of the declaration:**

E2K-C25M (DC 3-wire) series, Capacitive Sensor

**5. The objects of the declaration described above are in conformity with the relevant Union harmonisation legislation:**

2014/30/EU EMC Directive

2011/65/EU RoHS Directive

**6. References to the relevant harmonised standards used or references to the other technical specifications in relation to which conformity is declared:**

EMC Directive: EN IEC 60947-5-2: 2020

RoHS Directive: EN IEC 63000:2018

Signed and on behalf of: OMRON Corporation

Place and date of issue: Kyoto, Japan 2022/2/18

Signature: 三島 行正

Name: Yukimasa Mishima

Function: General Manager, Sensor Division, Product Business Division HQ.  
Industrial Automation Company

**Name and address of contact in EU**

OMRON Europe B.V.

Quality & Environment Department

Attn: J.J.P.W. Vogelaar, European Quality & Environment Manager

Zilverenberg 2, 5234 GM, 's-Hertogenbosch, The Netherlands

**Additional information**

## Model list

Type	Model
Capacitive adjustable sensitivity	SW E2K-C25ME1 10M
	SW E2K-C25ME1 2M
	SW E2K-C25ME1 5M
	SW E2K-C25ME1-10 2M
	SW E2K-C25ME1-8 2M
	SW E2K-C25ME2 2M
	SW E2K-C25ME2 5M
	SW E2K-C25ME2-10 2M
	SW E2K-C25ME2-8 2M
	SW E2K-C25MF1 10M
	SW E2K-C25MF1 2M
	SW E2K-C25MF1 5M
	SW E2K-C25MF2 2M
	SW E2K-C25MF2 5M
	SW E2K-C25MF1-M1TJ