

Original



EU DECLARATION OF CONFORMITY

- 1. Product Models/Products:**
E2KQ series
- 2. Name and address of the manufacturer:**
OMRON Corporation
Shiokoji Horikawa, Shimogyo-Ku, Kyoto, 600-8530 Japan
- 3. This declaration of conformity is issued under the sole responsibility of the manufacturer.**
- 4. Objects of the declaration:**
E2KQ series, Capacitive Sensor
- 5. The objects of the declaration described above are in conformity with the relevant Union harmonisation legislation:**
2014/30/EU EMC Directive
2011/65/EU RoHS Directive
- 6. References to the relevant harmonised standards used or references to the other technical specifications in relation to which conformity is declared:**
EMC Directive: EN IEC 60947-5-2: 2020
RoHS Directive: EN IEC 63000:2018

Signed and on behalf of: OMRON Corporation

Place and date of issue: Kyoto, Japan 2022/2/18

Signature: 三島 行正

Name: Yukimasa Mishima

Function: General Manager, Sensor Division, Product Business Division HQ.
Industrial Automation Company

Name and address of contact in EU

OMRON Europe B.V.
Quality & Environment Department
Attn: J.J.P.W. Vogelaar, European Quality & Environment Manager
Zilverenberg 2, 5234 GM, 's-Hertogenbosch, The Netherlands

Additional information

Model list

Type	Model
Fluororesin-coated, Capacitive	E2KQ-X10ME1 10M
	E2KQ-X10ME1 2M
	E2KQ-X10ME1 5M
	E2KQ-X10ME1-6 4M
	E2KQ-X10ME1-R 4M
	E2KQ-X10ME2 2M
	E2KQ-X10ME2-6 4M
	E2KQ-X10ME2-R 4M
	E2KQ-X10MF1 2M
	E2KQ-X10MF1 5M