

Products Name	Model
Controllers for Area Scanner	F3ZP-M1N-FLK
	F3ZP-M1N-FLK-B1
	F3ZP-M1N-FLK-CM
	F3ZP-M1P-FLK
Data Storage Units for Displacement & Measurement Sensors	ZS-DSU11-□□
	ZS-DSU41-□□
Controllers for Vision Sensors	F160-C10-□□□
	F160-C15E-2
	F210-C10-□□□
	F210-C15-□□□
	F250-C10
	F250-C50-□□□
	F250-C55
	F270-C1□
	F500-C10-□□□
	F500-C15-ETN
	FZ-3□□-□□
	FZ3-3□□-□□
	FZ3-7□□-□□
	FZ3-H3□□-□□
	FZ3-H7□□-□□
	FZD-5□□-□□
	3Z49-BAT1
ZFX-C□	
Microscope	VC3□□□-□□
	VC4□□□-□□
	VC7□□□-□□
	VCR8□□-□□□
Digital Time Switch	H5S Series
Counters	H7BR Series
	H7EC-N Series
	H7ET-N Series
	H7ER-N Series
Batteries for H7E□-N	Y92S-36 (BATTERY FOR H7E□-N)
Programmable Controllers SYSMAC CJ1 Series CPU Units	CJ1M-CPU11
	CJ1M-CPU11-ETN
	CJ1M-CPU12
	CJ1M-CPU12-ETN
	CJ1M-CPU13
	CJ1M-CPU13-ETN
	CJ1M-CPU21
	CJ1M-CPU22
CJ1M-CPU23	
Batteries for SYSMAC CJ1 Series	CJ1W-BAT01
Programmable Controllers SYSMAC CJ2 Series CPU Units	CJ2H-CPU66-EIP
	CJ2H-CPU65-EIP
	CJ2H-CPU68-EIP
	CJ2H-CPU64-EIP
	CJ2H-CPU67-EIP
Programmable Controllers SYSMAC CS1 Series CPU Unit	CS1W-LC001
Programmable Controllers SYSMAC CP1H Series	CP1H-Y20DT-D
	CP1H-X40DR-A
	CP1H-X40DT-D
	CP1H-X40DT1-D
	CP1H-XA40DT-D
	CP1H-XA40DT1-D
CP1H-XA40DR-A	

Products Name	Model
Programmable Controllers SYSMAC CP1L Series	CP1L-L10D□□-□
	CP1L-L14D□□-□
	CP1L-L20D□□-□
	CP1L-M30D□□-□
	CP1L-M40D□□-□
	CP1L-M60D□□-□
Programmable Controllers SYSMAC C200H Series	C200HE-CPU□□-□□
	C200HG-CPU□□-□□
	C200HX-CPU□□-□□
	C200H-ASC□□
	C200H-BAT09
Programmable Controllers NSJ Series	NSJ12-TS□□□□-G5D
	NSJ10-TV□□□□-G5D
	NSJ8-TV□□□□-G5D
	NSJ8-TV□□□□-M3D
	NSJ5-SQ□□□□-G5D
	NSJ5-SQ□□□□-M3D
	NSJ5-TQ□□□□-G5D
	NSJ5-TQ□□□□-M3D□
SYSMAC Boards	C200PC-ISA03
	C200PC-ISA03-DRM
	C200PC-ISA03-DRM-E
	C200PC-ISA03-E
	C200PC-ISA03-SRM
	C200PC-ISA03-SRM-E
	C200PC-ISA13-DRM
	C200PC-ISA13-DRM-E
	C200PC-ISA13-SRM
C200PC-ISA13-SRM-E	
Programmable Terminals	NS12-TS□□□□-□□□□
	NS10-TV□□□□-□□□□
	NS8-TV□□□□-□□□□
	NS5-MQ□□□□-□□□□
	NS5-SQ□□□□-□□□□
	NS5-TQ□□□□-□□□□
	NSH5-SQG□□□□-V2
	NSH5-SQR□□□□-V2
RFID Systems Data Carriers	V600-D2KR16
	V690-D8KR01A
Controllers for Code Leaders	V530-R160□□-□□
	V530-R2000-□
	V530-R2000P
Wireless Components	WK30-A-07
	WK30-ATX-07
Air Particle Sensor	ZN-PD03-S
	ZN-PD50-S