

Category	Model	Implementation	Implementation period	Display change pattern
Sensors	E2C-E			
Sensors	E2C-ED			
Sensors	E2CY			
Sensors	E2E	○	FY21-2Q	Packing Label
Sensors	E2E2			
Sensors	E2EC			
Sensors	E2EF			
Sensors	E2EH			
Sensors	E2EM			
Sensors	E2EN			
Sensors	E2END			
Sensors	E2ENQ			
Sensors	E2ENS			
Sensors	E2ENT			
Sensors	E2EQ	○	FY21-2Q	Packing Label
Sensors	E2EQD	○	FY21-2Q	Packing Label
Sensors	E2EQI	○	FY21-2Q	Packing Label
Sensors	E2EQN	○	FY21-2Q	Packing Label
Sensors	E2EQN3	○	FY21-2Q	Packing Label
Sensors	E2EQS	○	FY21-2Q	Packing Label
Sensors	E2EQT	○	FY21-2Q	Packing Label
Sensors	E2ER			
Sensors	E2EWQ			
Sensors	E2EWS			
Sensors	E2EWT			
Sensors	E2EZ			
Sensors	E2F	○	FY21-2Q	Packing Label
Sensors	E2FM			
Sensors	E2FQ			
Sensors	E2J			
Sensors	E2K			
Sensors	E2K-F			
Sensors	E2K-L			
Sensors	E2KQ			
Sensors	E2K-X			
Sensors	E2S	○	FY21-2Q	Packing Label
Sensors	E2V			
Sensors	E32-A			
Sensors	E32-C			
Sensors	E32-CN			
Sensors	E32-D			
Sensors	E32-DA			
Sensors	E32-DB			
Sensors	E32-DF			
Sensors	E32-DH			
Sensors	E32-DL			
Sensors	E32-DN			
Sensors	E32-DR			
Sensors	E32-DS			
Sensors	E32-DU			
Sensors	E32-L			
Sensors	E32-LD			
Sensors	E32-LT			
Sensors	E32-N			
Sensors	E32-R			
Sensors	E32-T			
Sensors	E32-TA			
Sensors	E32-TB			
Sensors	E32-TF			
Sensors	E32-TH			
Sensors	E32-TL			
Sensors	E32-TN			
Sensors	E32-TR			
Sensors	E39			

Sensors	E39-F			
Sensors	E39-R			
Sensors	E3AS			
Sensors	E3C-L			
Sensors	E3C-LD			
Sensors	E3FA			
Sensors	E3FB			
Sensors	E3JK			
Sensors	E3JM			
Sensors	E3NC-L			
Sensors	E3NC-S			
Sensors	E3NW			
Sensors	E3NX			
Sensors	E3NX-C			
Sensors	E3RB			
Sensors	E3S			
Sensors	E3S:A			
Sensors	E3S:C			
Sensors	E3S-D			
Sensors	E3S-GN			
Sensors	E3S-LN			
Sensors	E3S-N			
Sensors	E3T			
Sensors	E3X			
Sensors	E3X-HD			
Sensors	E3X-MZ			
Sensors	E3X-ZV			
Sensors	E3Z			
Sensors	E3ZM			
Sensors	E3ZR			
Sensors	E4E2			
Sensors	E4PA			
Sensors	E6A2-C			
Sensors	E6C2	○	FY21-2Q	Unit Label
Sensors	E6C3-A			
Sensors	E6C3-C			
Sensors	E6CP-A	○	FY21-2Q	Unit Label
Sensors	E6F-A			
Sensors	E6F-C			
Sensors	E6H-C			
Sensors	E8F2			
Sensors	E8FC			
Sensors	E8PC			
Sensors	E9NC-T			
Sensors	EE-CN			
Sensors	EESA8			
Sensors	EE-SPW			
Sensors	EE-SPX			
Sensors	EE-SPY			
Sensors	EE-SX6			
Sensors	EESX67			
Sensors	EE-SX8			
Sensors	EE-SX9			
Sensors	EESX95			
Sensors	EE-SY6			
Sensors	F3W-E			
Sensors	F430-F			
Sensors	F92A			
Sensors	FHV			
Sensors	FHV7H			Unit Label
Sensors	FJ-V			
Sensors	FL			
Sensors	FL-2			
Sensors	FLV			
Sensors	FQ2-D			

Sensors	FQ2-S			
Sensors	FQ-CR			
Sensors	FQM-W			
Sensors	FQ-W			
Sensors	FQ-X			
Sensors	FS	○	FY21-1Q	Unit Label
Sensors	FZ			
Sensors	FZ-3			
Sensors	FZ5			
Sensors	FZ-V			
Sensors	GLS			
Sensors	K7L			
Sensors	K7L-B			
Sensors	MS-3			
Sensors	QX-830			
Sensors	QX-870			
Sensors	STC	○	FY21-1Q	Unit Label
Sensors	TLN			
Sensors	TL-Q	○	FY21-2Q	Packing Label
Sensors	TL-W	○	FY21-2Q	Packing Label
Sensors	V400-W			
Sensors	V420-F			
Sensors	V430-A			
Sensors	V430-F			
Sensors	V430-W			
Sensors	V60D23			
Sensors	V68C			
Sensors	V68HS			
Sensors	Y92E			
Sensors	ZG2-C			
Sensors	ZG2-S			
Sensors	ZN9-S			
Sensors	ZS-H			
Sensors	ZS-HD			
Sensors	ZS-L			
Sensors	ZS-LD			
Sensors	ZS-X			
Sensors	ZW-C			
Sensors	ZW-S			
Sensors	ZW-SQ			
Sensors	ZW-X			
Sensors	ZX0-XC			
Sensors	ZX1-LD			
Sensors	ZX2-L			
Sensors	ZX2-LD			
Sensors	ZX2-S			
Sensors	ZX2-XC			
Sensors	ZX-E			
Sensors	ZX-ED			
Sensors	ZX-L			
Sensors	ZX-LD			
Sensors	ZX-T			
Sensors	ZX-TD			
Sensors	ZX-X			
Sensors	ZX-XC			
Switches	61FGPN			
Switches	A16			
Switches	A16E			
Switches	A22			
Switches	A22E			
Switches	A22NE			
Switches	A22NK			
Switches	A22NKP			
Switches	A22NL			
Switches	A22NLP			

Switches	A22NN		
Switches	A22NNP		
Switches	A22NS		
Switches	A22NSP		
Switches	A22NW		
Switches	A22NWP		
Switches	A22NZ		
Switches	A22NZP		
Switches	A2W		
Switches	A30NK		
Switches	A30NKP		
Switches	A30NL		
Switches	A30NLP		
Switches	A30NN		
Switches	A30NNP		
Switches	A30NS		
Switches	A30NSP		
Switches	A30NW		
Switches	A30NWP		
Switches	BUHIN		
Switches	D4B-N		
Switches	D4C		
Switches	D4CC		
Switches	D4E		
Switches	D4EN		
Switches	D4F		
Switches	D4MC		
Switches	D4N		
Switches	D4N-R		
Switches	M22N		
Switches	M22NP		
Switches	SHL		
Switches	WL		
Switches	WL-N		
Switches	ZC		
Switches	ZE		
Safety Components	E3ZS		
Safety Components	F39B		
Safety Components	F39G		
Safety Components	F39J		
Safety Components	F39N		
Safety Components	F39R		
Safety Components	F39S		
Safety Components	F39X		
Safety Components	F39Z		
Safety Components	F3SG		
Safety Components	F3SG2		
Safety Components	F3SJ-A		
Safety Components	F3SJ-B		
Safety Components	F3SJ-E		
Safety Components	F3SP		
Safety Components	F3W-D		
Safety Components	F3W-MA		
Safety Components	A22TK		
Safety Components	A4E		
Safety Components	A4EG		
Safety Components	D40A		
Safety Components	D40Z		
Safety Components	D4BL		
Safety Components	D4BS		
Safety Components	D4GS-N		
Safety Components	D4JL		
Safety Components	D4NH		
Safety Components	D4NL		
Safety Components	D4NS		

Safety Components	D4SL-N			
Safety Components	DST1			
Safety Components	GI			
Safety Components	NE1A			
Safety Components	NXSG			
Safety Components	NXSL			
Safety Components	NXST			
Safety Components	G9SA			
Safety Components	G9SB			
Safety Components	G9SE			
Safety Components	G9SP			
Safety Components	G9SX			
Safety Components	OS32C			
Safety Components	P7SE			
Relays	G7J			
Relays	G7Z			
Relays	LY		Not required	Marking is planned to be on the socket side
Relays	MY		Not required	Marking is planned to be on the socket side
Relays	MYH		Not required	Marking is planned to be on the socket side
Relays	MYK		Not required	Marking is planned to be on the socket side
Relays	MYQ		Not required	Marking is planned to be on the socket side
Relays	MYS		Not required	Marking is planned to be on the socket side
Relays	G32A			
Relays	G3B			
Relays	G3BD			
Relays	G3F			
Relays	G3FD			
Relays	G3H			
Relays	G3HD			
Relays	G3J			
Relays	G3NE			
Relays	G3PA			
Relays	G3PE			
Relays	G3PF			
Relays	G3PH			
Relays	G3PJ			
Relays	G3PW			
Relays	G3R			
Relays	G3RV			
Relays	G3ZA			
Relays	J73KC			
Relays	J73MC			
Relays	J74KC			
Relays	J75KC			
Relays	J76KC			
Relays	J77KC			
Relays	J77MC			
Relays	J78KC			
Relays	J7KC			
Relays	J7KCA			
Relays	J7KCR			
Relays	J7MC			
Relays	J7TC			
Control Components	H3CA	○	FY21-2Q	Packing Label
Control Components	H3CR-A	○	FY21-2Q	Packing Label
Control Components	H3CR-F	○	FY21-2Q	Packing Label
Control Components	H3CR-G	○	FY21-2Q	Packing Label
Control Components	H3CR-H	○	FY21-2Q	Packing Label
Control Components	H3DK	○	FY21-2Q	Packing Label

Control Components	H3DS	○	FY21-2Q	Packing Label
Control Components	H3DT	○	FY21-2Q	Packing Label
Control Components	H3RN			
Control Components	H3RN-B			
Control Components	H3Y	○	FY21-2Q	Packing Label
Control Components	H3Y-B	○	FY21-2Q	Packing Label
Control Components	H3YN	○	FY21-2Q	Packing Label
Control Components	H3YN-B	○	FY21-2Q	Packing Label
Control Components	H5AN			
Control Components	H5CN			
Control Components	H5CX	○	FY21-2Q	Packing Label
Control Components	H5CZ	○	FY21-2Q	Packing Label
Control Components	H5F			
Control Components	H5S			
Control Components	H7AN			
Control Components	H7BX			
Control Components	H7CC	○	FY21-2Q	Packing Label
Control Components	H7CN			
Control Components	H7CX	○	FY21-2Q	Packing Label
Control Components	H7CZ	○	FY21-2Q	Packing Label
Control Components	H7E-N	○	FY21-2Q	Packing Label
Control Components	H7GP			
Control Components	H7HP			
Control Components	H8BM			
Control Components	H8PS			
Control Components	3F88L			
Control Components	E58			
Control Components	E5AC	○	FY21-2Q	Packing Label
Control Components	E5ACT	○	FY21-2Q	Packing Label
Control Components	E5AN(H			
Control Components	E5AN(T			
Control Components	E5C2N	○	FY21-2Q	Packing Label
Control Components	E5CB	○	FY21-2Q	Packing Label
Control Components	E5CC	○	FY21-2Q	Packing Label
Control Components	E5CC8	○	FY21-2Q	Packing Label
Control Components	E5CCB	○	FY21-2Q	Packing Label
Control Components	E5CCT	○	FY21-2Q	Packing Label
Control Components	E5CCU	○	FY21-2Q	Packing Label
Control Components	E5CD	○	FY21-2Q	Packing Label
Control Components	E5CDB	○	FY21-2Q	Packing Label
Control Components	E5CN(H			
Control Components	E5CN(T			
Control Components	E5CS(N	○	FY21-2Q	Packing Label
Control Components	E5CSV	○	FY21-2Q	Packing Label
Control Components	E5DC	○	FY21-2Q	Packing Label
Control Components	E5DCB	○	FY21-2Q	Packing Label
Control Components	E5EC	○	FY21-2Q	Packing Label
Control Components	E5ECB	○	FY21-2Q	Packing Label
Control Components	E5ECT	○	FY21-2Q	Packing Label
Control Components	E5ED	○	FY21-2Q	Packing Label
Control Components	E5EDB	○	FY21-2Q	Packing Label
Control Components	E5EN(H			
Control Components	E5EN(T			
Control Components	E5GC	○	FY21-2Q	Packing Label
Control Components	E5L			
Control Components	E5LC			
Control Components	E6B2-C	○	FY21-2Q	Unit Label
Control Components	EJ1C			
Control Components	EJ1N			
Control Components	ES1(N	○	FY21-2Q	Unit Label
Control Components	ES1B	○	FY21-2Q	Packing Label
Control Components	ES1C			
Control Components	K3GN			
Control Components	K3HBC			
Control Components	K3HBH			

Control Components	K3HBP			
Control Components	K3HBR			
Control Components	K3HBS			
Control Components	K3HBV			
Control Components	K3HBX			
Control Components	K3MA			
Control Components	K3FP			
Control Components	K3SC			
Automation Systems	NJ	○	FY21-2Q	Unit Label
Automation Systems	NJ101			
Automation Systems	NJ301			
Automation Systems	NJ501			
Automation Systems	NX			
Automation Systems	NX102			
Automation Systems	NX1P2			
Automation Systems	NX1W			
Automation Systems	NXTC			
Automation Systems	NY000			
Automation Systems	NY512			
Automation Systems	NYB17			
Automation Systems	NYB1E			
Automation Systems	NYB25			
Automation Systems	NYB2A			
Automation Systems	NYB2C			
Automation Systems	NYB35			
Automation Systems	NYM15			
Automation Systems	NYM19W			
Automation Systems	NYP17			
Automation Systems	NYP1C			
Automation Systems	NYP2A			
Automation Systems	NYP2C			
Automation Systems	NYP35			
Automation Systems	CK3E			
Automation Systems	CK3M			
Automation Systems	CK3W			
Automation Systems	3G8F7			
Automation Systems	C200HW			
Automation Systems	CJ1G			
Automation Systems	CJ1W			
Automation Systems	CJ2H			
Automation Systems	CP1E			
Automation Systems	CP1ES			
Automation Systems	CP1H			
Automation Systems	CP1L			
Automation Systems	CP1W			
Automation Systems	CP2E			
Automation Systems	CP2W			
Automation Systems	CPM2C			
Automation Systems	CRS1			
Automation Systems	CRT1	○	FY21-2Q	Unit Label
Automation Systems	CRT1B			
Automation Systems	CS1D			
Automation Systems	CS1G			
Automation Systems	CS1H			
Automation Systems	CS1PC			
Automation Systems	CS1W			
Automation Systems	DRT1			
Automation Systems	DRT2			
Automation Systems	DRTA			
Automation Systems	GCN2			
Automation Systems	GQ			
Automation Systems	GRT1			
Automation Systems	GT1			
Automation Systems	GX			
Automation Systems	HMC			

Automation Systems	NXR		
Automation Systems	SRM1		
Automation Systems	SRT1		
Automation Systems	SRT2		
Automation Systems	XWT		
Automation Systems	ZEN		
Automation Systems	NB		
Automation Systems	NB10W		
Automation Systems	NB3Q		
Automation Systems	NB5Q		
Automation Systems	NB7W		
Automation Systems	NS		
Automation Systems	NS10		
Automation Systems	NS12		
Automation Systems	NS15		
Automation Systems	NS5		
Automation Systems	NS8		
Automation Systems	NSH5		
Automation Systems	NSJ10		
Automation Systems	NSJ12		
Automation Systems	NSJ5		
Automation Systems	NSJ8		
Automation Systems	NSJW		
Automation Systems	NT631C		
Automation Systems	NV3Q		
Automation Systems	NV3W		
Automation Systems	NV4W		
Automation Systems	W4S1		
Automation Systems	V60HS		
Automation Systems	V60A		
Automation Systems	V60C		
Automation Systems	V60H		
Automation Systems	V60HAM		
Automation Systems	V68D1K		
Automation Systems	V68D2K		
Automation Systems	V68HA		
Automation Systems	V68HAM		
Automation Systems	V68SA		
Automation Systems	V68SD2		
Automation Systems	V68SD8		
Automation Systems	V68SH		
Automation Systems	V70A		
Motion/Drives	3G3AXM		
Motion/Drives	3G3AXR		
Motion/Drives	3G3RX2		
Motion/Drives	R7DB		
Motion/Drives	R8A1		
Motion/Drives	R8D1S		
Motion/Drives	R8D1SA		
Motion/Drives	R8DG		
Motion/Drives	R8DK		
Motion/Drives	R8M1		
Motion/Drives	R8M1A		
Motion/Drives	R8MG		
Motion/Drives	R8MK		
Motion/Drives	FQM1		
Energy Conservation Support/ Environment Measure Equipment	D6FZ		
Energy Conservation Support/ Environment Measure Equipment	KE1		
Energy Conservation Support/ Environment Measure Equipment	KM1		
Energy Conservation Support/ Environment Measure Equipment	KM50		

Energy Conservation Support/ Environment Measure Equipment	KMN2			
Energy Conservation Support/ Environment Measure Equipment	KMN3			
Energy Conservation Support/ Environment Measure Equipment	ZN9-X			
Energy Conservation Support/ Environment Measure Equipment	ZN-PS			
Energy Conservation Support/ Environment Measure Equipment	ZN-T			
Power Supplies/In Addition	S82S			
Power Supplies/In Addition	S8AS			
Power Supplies/In Addition	S8FS-G			
Power Supplies/In Addition	S8JX-P			
Power Supplies/In Addition	S8M			
Power Supplies/In Addition	S8T			
Power Supplies/In Addition	S8TS			
Power Supplies/In Addition	S8VK-G			
Power Supplies/In Addition	S8VK-R			
Power Supplies/In Addition	S8VK-S			
Power Supplies/In Addition	S8VK-T			
Power Supplies/In Addition	S8VK-W			
Power Supplies/In Addition	S8VK-X			
Power Supplies/In Addition	S8VS			
Power Supplies/In Addition	R87B			
Power Supplies/In Addition	R87F			
Power Supplies/In Addition	R87T			
Power Supplies/In Addition	R89F			
Power Supplies/In Addition	ZJ-FA			
Power Supplies/In Addition	K8AC			
Power Supplies/In Addition	K8AK			
Power Supplies/In Addition	K8DS			
Power Supplies/In Addition	K8DT			
Power Supplies/In Addition	B7A			
Power Supplies/In Addition	K6CM-M			
Power Supplies/In Addition	K6CM-S			
Power Supplies/In Addition	K6PM-M			
Power Supplies/In Addition	K6PM-S			
Power Supplies/In Addition	K7GE			
Power Supplies/In Addition	G3DZ4			
Power Supplies/In Addition	G3DZPU			
Power Supplies/In Addition	G3RVSR			
Power Supplies/In Addition	G6B4			
Power Supplies/In Addition	G6D4			
Power Supplies/In Addition	G6D4PU			
Power Supplies/In Addition	G70D			
Power Supplies/In Addition	G70V			
Power Supplies/In Addition	G70V-C			
Power Supplies/In Addition	XW5T			
Power Supplies/In Addition	XW6T			